

# Surface Mount Coaxial-Ceramic Resonator Filters and Multiplexers

50Ω DC to 6 GHz

## The Big Deal

- Low insertion loss with excellent power handling
- Passbands up to 6 GHz
- Fractional bandwidth from <1 to 25%
- Low profile designs with min. height of 0.120"
- Excellent temperature stability
- Rugged construction to handle demanding environmental conditions



## Product Overview

Mini-Circuits' *Coaxial-Ceramic Resonator filters* offer low insertion loss in very small form factors, using ceramic material with high dielectric constant and superior Q factor. Bandpass and bandstop filters, diplexer and multiplexer designs can be constructed using this technology. Low insertion loss combined with excellent power handling makes these filters well suited for transmitter and receiver signal chains. Advanced filter design and construction can achieve stopband width greater than 3x the center frequency as high as 20 GHz.

All our coaxial-ceramic resonator filters are built with rugged construction, qualified to withstand multiple demanding reflow cycles. Custom integrated assembly with LNA in greatly simplifying system integration. They can be realized in small form factors with high-quality, precise machining for applications where size is critical. Excellent repeatability across units is achieved through precise tuning and process control.

## Key Features

| Feature                  | Advantages                                                                                                                                                                            |
|--------------------------|---------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Low insertion loss       | Low signal loss results in better SNR in signal chain                                                                                                                                 |
| Fast roll-off            | Higher selectivity results in better adjacent channel rejection and dynamic range                                                                                                     |
| Wide stop band           | Wide spur-free stopband results in better receiver sensitivity                                                                                                                        |
| Excellent power handling | Well suited for transmitter applications                                                                                                                                              |
| Rugged Construction      | These filter assemblies have been qualified over a wide range of thermal, mechanical and environmental conditions including withstanding the stress of extensive solder reflow cycles |
| Small Size               | Very well suited for high performance applications where size is a constraint.                                                                                                        |
| Temperature stability    | Very minimal change in electrical performance across temperature makes these filters suitable for a wide range of operating conditions.                                               |

### Notes


- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.  
B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.  
C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at [www.minicircuits.com/MCLStore/terms.jsp](http://www.minicircuits.com/MCLStore/terms.jsp)



# Surface Mount Bandpass Filter

50Ω 1030 to 1090 MHz

CBP-1060Q+



Generic photo used for illustration purposes only  
CASE STYLE: HQ2299

## Features

- Broad stopband performance up to 20 GHz
- High selectivity
- Miniature shielded package

## Applications

- Aeronautical radio navigation
- Fixed satellite
- Radio astronomy
- Radar and navigation systems

## Electrical Specifications at 25°C


| Parameter        |                  | F#    | Frequency (MHz) | Min. | Typ. | Max. | Unit |
|------------------|------------------|-------|-----------------|------|------|------|------|
| Pass Band        | Center Frequency | -     | -               | -    | 1060 | -    | MHz  |
|                  | Insertion Loss   | F1-F2 | 1030-1090       | -    | 1.6  | 2.5  | dB   |
|                  | VSWR             | F1-F2 | 1030-1090       | -    | 1.3  | 1.7  | :1   |
| Stop Band, Lower | Insertion Loss   | DC-F3 | DC-500          | 60   | 68   | -    | dB   |
|                  |                  | F3-F4 | 500-930         | 20   | 32   | -    | dB   |
|                  | VSWR             | DC-F4 | DC-930          | -    | 20   | -    | :1   |
| Stop Band, Upper | Insertion Loss   | F5-F6 | 1190-1400       | 20   | 30   | -    | dB   |
|                  |                  | F6-F7 | 1400-2800       | 45   | 52   | -    | dB   |
|                  |                  | F7-F8 | 2800-20000      | -    | 20   | -    | dB   |
|                  | VSWR             | F5-F8 | 1190-20000      | -    | 8    | -    | :1   |

## Maximum Ratings


|                       |                |
|-----------------------|----------------|
| Operating Temperature | -40°C to 85°C  |
| Storage Temperature   | -55°C to 100°C |
| RF Power Input        | 8 W Max.       |

Passband rating, derate linearly to 3.5W at 85°C ambient.  
Permanent damage may occur if any of these limits are exceeded.

## Functional Schematic



## Typical Frequency Response







## +RoHS Compliant

The +Suffix identifies RoHS Compliance. See our web site for RoHS Compliance methodologies and qualifications

## Typical Performance Data at 25°C

| Frequency (MHz) | Insertion Loss (dB) | VSWR (:1) | Frequency (MHz) | Group Delay (ns) |
|-----------------|---------------------|-----------|-----------------|------------------|
| 10              | 74.37               | 362.04    | 1030            | 9.91             |
| 100             | 90.40               | 303.37    | 1032            | 9.80             |
| 500             | 72.71               | 40.93     | 1034            | 9.70             |
| 930             | 35.44               | 18.49     | 1036            | 9.61             |
| 940             | 31.00               | 18.17     | 1038            | 9.53             |
| 960             | 20.77               | 15.72     | 1040            | 9.46             |
| 990             | 4.22                | 2.90      | 1042            | 9.40             |
| 1030            | 1.65                | 1.16      | 1044            | 9.35             |
| 1060            | 1.57                | 1.11      | 1046            | 9.30             |
| 1090            | 1.64                | 1.17      | 1048            | 9.25             |
| 1130            | 4.94                | 3.59      | 1050            | 9.21             |
| 1160            | 20.56               | 12.18     | 1052            | 9.18             |
| 1180            | 28.97               | 13.69     | 1054            | 9.15             |
| 1190            | 32.62               | 14.09     | 1056            | 9.12             |
| 1400            | 62.89               | 16.03     | 1060            | 9.07             |
| 2800            | 69.84               | 26.38     | 1066            | 9.05             |
| 7100            | 24.49               | 3.59      | 1070            | 9.06             |
| 10000           | 40.07               | 18.84     | 1080            | 9.22             |
| 15000           | 40.75               | 2.39      | 1086            | 9.40             |
| 20000           | 35.21               | 1.49      | 1090            | 9.55             |



## Notes

- Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- Electrical specifications and performance data contained in this specification document are based on Mini-Circuits' applicable established test performance criteria and measurement instructions.
- The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at [www.minicircuits.com/MCLStore/terms.jsp](http://www.minicircuits.com/MCLStore/terms.jsp)



[www.minicircuits.com](http://www.minicircuits.com) P.O. Box 350166, Brooklyn, NY 11235-0003 (718) 934-4500 [sales@minicircuits.com](mailto:sales@minicircuits.com)


REV.B  
ECO-004071  
CBP-1060Q+  
EDU2473/1  
URJ  
201116  
Page 2 of 3

Pad Connections

|        |                              |
|--------|------------------------------|
| INPUT  | 1                            |
| OUTPUT | 8                            |
| GROUND | 2,3,4,5,6,7,9,10,11,12,13,14 |

Demo Board MCL P/N: TB-1006+  
Suggested PCB Layout (PL-543)

SUGGESTED MOUNTING CONFIGURATION FOR  
HQ2218 & HQ2299 CASE STYLE "14FL01" PIN CODE




NOTES:


- 1. TRACE WIDTH IS SHOWN FOR FR4, IT180A WITH DIELECTRIC THICKNESS .025"±.002". COPPER: 1/2 Oz EACH SIDE.
- 2. FOR OTHER MATERIALS TRACE WIDTH MAY NEED TO BE MODIFIED.
- 3. BOTTOM SIDE OF THE PCB IS CONTINUOUS GROUND PLANE.

- DENOTES PCB COPPER LAYOUT WITH SMOBC (SOLDER MASK OVER BARE COPPER)
- DENOTES COPPER LAND PATTERN FREE OF SOLDERMASK

Outline Drawing



PCB Land Pattern



Outline Dimensions ( inch )

| A    | B     | C     | D    | E     | F     | G    | H    | J    | K     |
|------|-------|-------|------|-------|-------|------|------|------|-------|
| -    | -     | Min   | Max  | -     | -     | -    | -    | -    | -     |
| .365 | 1.360 | .240  | .270 | .483  | 1.200 | .305 | .150 | .118 | .100  |
| 9.27 | 34.54 | 6.10  | 6.86 | 12.27 | 30.48 | 7.75 | 3.81 | 3.00 | 2.54  |
| L    | M     | N     | P    | Q     | R     | S    | T    | U    | Wt.   |
| .180 | 1.400 | .405  | .153 | .285  | .263  | .120 | .155 | .275 | grams |
| 4.57 | 35.56 | 10.29 | 3.87 | 7.24  | 6.67  | 3.05 | 3.94 | 6.99 | 5.0   |

Note: Please refer to case style drawing for details






Notes  
A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.  
B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.  
C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at [www.minicircuits.com/MCLStore/terms.jsp](http://www.minicircuits.com/MCLStore/terms.jsp)

## Typical Performance Data

| FREQ. | INSERTION LOSS | INPUT RETURN LOSS | OUTPUT RETURN LOSS |
|-------|----------------|-------------------|--------------------|
| (MHz) | (dB)           | (dB)              | (dB)               |
| 10    | 74.37          | 0.05              | 0.05               |
| 20    | 79.43          | 0.04              | 0.05               |
| 50    | 76.87          | 0.05              | 0.06               |
| 100   | 90.40          | 0.06              | 0.07               |
| 250   | 89.93          | 0.15              | 0.17               |
| 500   | 72.71          | 0.42              | 0.42               |
| 750   | 64.41          | 0.76              | 0.89               |
| 800   | 62.65          | 0.83              | 0.98               |
| 850   | 57.94          | 0.89              | 1.03               |
| 930   | 35.44          | 0.94              | 0.92               |
| 940   | 31.00          | 0.96              | 0.91               |
| 950   | 26.12          | 1.00              | 0.92               |
| 954   | 24.04          | 1.03              | 0.94               |
| 960   | 20.77          | 1.11              | 1.01               |
| 964   | 18.49          | 1.19              | 1.08               |
| 970   | 14.93          | 1.42              | 1.31               |
| 974   | 12.50          | 1.70              | 1.59               |
| 976   | 11.29          | 1.91              | 1.80               |
| 980   | 8.93           | 2.52              | 2.42               |
| 984   | 6.76           | 3.54              | 3.48               |
| 986   | 5.80           | 4.26              | 4.24               |
| 990   | 4.22           | 6.24              | 6.35               |
| 994   | 3.13           | 9.00              | 9.44               |
| 996   | 2.76           | 10.65             | 11.40              |
| 998   | 2.48           | 12.46             | 13.70              |
| 1000  | 2.28           | 14.37             | 16.40              |
| 1010  | 1.84           | 21.75             | 25.63              |
| 1020  | 1.72           | 22.21             | 18.69              |
| 1030  | 1.65           | 22.78             | 17.44              |
| 1040  | 1.60           | 25.34             | 19.08              |
| 1050  | 1.56           | 28.14             | 24.60              |
| 1060  | 1.57           | 25.31             | 32.08              |
| 1070  | 1.59           | 23.30             | 23.38              |
| 1080  | 1.61           | 23.25             | 20.17              |
| 1090  | 1.64           | 22.17             | 19.05              |
| 1126  | 3.49           | 7.45              | 7.76               |
| 1140  | 10.10          | 2.32              | 2.68               |
| 1150  | 15.59          | 1.64              | 1.96               |
| 1160  | 20.56          | 1.43              | 1.69               |
| 1180  | 28.97          | 1.27              | 1.44               |
| 1184  | 30.47          | 1.26              | 1.40               |
| 1190  | 32.62          | 1.24              | 1.35               |
| 1200  | 35.99          | 1.21              | 1.29               |
| 1300  | 66.68          | 1.05              | 0.87               |
| 1400  | 62.89          | 1.09              | 0.75               |
| 1500  | 58.37          | 1.49              | 1.03               |
| 2000  | 60.52          | 1.09              | 1.02               |
| 2800  | 69.84          | 0.66              | 0.47               |
| 4000  | 39.82          | 0.16              | 0.41               |
| 5000  | 32.86          | 0.87              | 1.22               |
| 6000  | 38.36          | 3.22              | 0.29               |
| 7000  | 35.73          | 2.94              | 0.64               |
| 8000  | 43.59          | 0.85              | 0.16               |
| 9000  | 53.85          | 0.42              | 0.12               |
| 10000 | 40.07          | 0.92              | 1.00               |
| 11000 | 35.85          | 1.16              | 0.94               |
| 12500 | 33.46          | 0.73              | 0.11               |
| 15000 | 40.75          | 7.75              | 0.47               |
| 17500 | 25.56          | 1.54              | 0.97               |
| 20000 | 35.21          | 14.12             | 4.54               |


| FREQ. | GROUP DELAY |
|-------|-------------|
| (MHz) | (ns)        |
| 1020  | 10.72       |
| 1022  | 10.52       |
| 1024  | 10.33       |
| 1026  | 10.17       |
| 1028  | 10.03       |
| 1030  | 9.91        |
| 1032  | 9.80        |
| 1034  | 9.70        |
| 1036  | 9.61        |
| 1038  | 9.53        |
| 1040  | 9.46        |
| 1042  | 9.40        |
| 1044  | 9.35        |
| 1046  | 9.30        |
| 1048  | 9.25        |
| 1050  | 9.21        |
| 1052  | 9.18        |
| 1054  | 9.15        |
| 1056  | 9.12        |
| 1058  | 9.09        |
| 1060  | 9.07        |
| 1062  | 9.06        |
| 1064  | 9.05        |
| 1066  | 9.05        |
| 1068  | 9.05        |
| 1070  | 9.06        |
| 1072  | 9.08        |
| 1074  | 9.10        |
| 1076  | 9.14        |
| 1078  | 9.17        |
| 1080  | 9.22        |
| 1082  | 9.27        |
| 1084  | 9.33        |
| 1086  | 9.40        |
| 1088  | 9.47        |
| 1090  | 9.55        |
| 1092  | 9.64        |
| 1094  | 9.74        |
| 1096  | 9.86        |
| 1098  | 9.99        |
| 1100  | 10.15       |
| 1102  | 10.34       |
| 1104  | 10.57       |
| 1106  | 10.84       |
| 1108  | 11.16       |
| 1110  | 11.54       |
| 1112  | 11.96       |
| 1114  | 12.42       |
| 1116  | 12.91       |
| 1118  | 13.36       |
| 1120  | 13.76       |
| 1122  | 14.07       |
| 1124  | 14.23       |
| 1126  | 14.24       |
| 1128  | 14.07       |
| 1130  | 13.73       |
| 1132  | 13.22       |
| 1134  | 12.58       |
| 1136  | 11.85       |
| 1138  | 11.05       |

## Typical Performance Curves




## Outline Dimensions

HQ2299



## PCB Land Pattern



| CASE#  | A              | B                | C              |                | D               | E                | F              | G              | H              | J              | K              | L              |
|--------|----------------|------------------|----------------|----------------|-----------------|------------------|----------------|----------------|----------------|----------------|----------------|----------------|
|        |                |                  | MIN            | MAX            |                 |                  |                |                |                |                |                |                |
| HQ2299 | .365<br>(9.27) | 1.360<br>(34.54) | .240<br>(6.10) | .270<br>(6.86) | .483<br>(12.27) | 1.200<br>(30.48) | .305<br>(7.75) | .150<br>(3.81) | .118<br>(3.00) | .100<br>(2.54) | .140<br>(3.56) | .180<br>(4.57) |

| CASE#  | M                | N               | P              | Q              | R              | S              | T              | U              | WT.GRAMS |
|--------|------------------|-----------------|----------------|----------------|----------------|----------------|----------------|----------------|----------|
| HQ2299 | 1.400<br>(35.56) | .405<br>(10.29) | .153<br>(3.87) | .285<br>(7.24) | .263<br>(6.67) | .120<br>(3.05) | .155<br>(3.94) | .275<br>(6.99) | 5.0      |

Dimensions are in inches (mm). Tolerances: 2Pl.  $\pm .03$ ; 3Pl.  $\pm .015$

### Notes:

- Case material: Nickel-Silver alloy.
- Base: Printed wiring laminate.
- Termination finish:  
For RoHS Case Styles: 3-5  $\mu$  inch Gold over 120-240  $\mu$  inch Nickel plate.  
For RoHS-5 Case Styles: Tin-Lead plate.

**Mini-Circuits®**  
ISO 9001 ISO 14001 CERTIFIED

ALL NEW  
**minicircuits.com**


P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site



The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: [www.minicircuits.com](http://www.minicircuits.com)

RF/IF MICROWAVE COMPONENTS

# Tape & Reel Packaging TR-F121



| Tape Width,<br>mm | Device Cavity<br>Pitch, mm | Reel Size,<br>inches | Devices per Reel |
|-------------------|----------------------------|----------------------|------------------|
| 56                | 20                         | 13                   | 100              |

Mini-Circuits carrier tape materials provide protection from ESD (Electro-Static Discharge) during handling and transportation. Tapes are static dissipative and comply with industry standards EIA-481/EIA-541.


Go to: [www.minicircuits.com/pages/pdfs/tape.pdf](http://www.minicircuits.com/pages/pdfs/tape.pdf)



**INTERNET** <http://www.minicircuits.com>  
P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661  
**Distribution Centers** NORTH AMERICA 800-654-7949 • 417-335-5935 • Fax 417-335-5945 • EUROPE 44-1252-832600 • Fax 44-1252-837010  
**Mini-Circuits ISO 9001 & ISO 14001 Certified**

|                        |     |           |             |        |    |      |
|------------------------|-----|-----------|-------------|--------|----|------|
| THIRD ANGLE PROJECTION |     | REVISIONS |             |        |    |      |
|                        | REV | ECN No.   | DESCRIPTION | DATE   | DR | AUTH |
|                        | OR  | M165612   | NEW RELEASE | MAR 18 | TM | MD   |
|                        |     |           |             |        |    |      |
|                        |     |           |             |        |    |      |

SUGGESTED MOUNTING CONFIGURATION FOR  
HQ2218 & HQ2299 CASE STYLE "14FL01" PIN CODE



NOTES:

- 1. TRACE WIDTH IS SHOWN FOR FR4, IT180A WITH DIELECTRIC THICKNESS .025"±.002". COPPER: 1/2 Oz EACH SIDE.  
FOR OTHER MATERIALS TRACE WIDTH MAY NEED TO BE MODIFIED.
- 2. BOTTOM SIDE OF THE PCB IS CONTINUOUS GROUND PLANE.



DENOTES PCB COPPER LAYOUT WITH SMOBC  
(SOLDER MASK OVER BARE COPPER)





DENOTES COPPER LAND PATTERN FREE OF SOLDERMASK

|                                                                                                                                                                                                                                                                                                                                                                                                                                                                           |  |          |     |           |  |                                                                                                                                         |  |                     |  |                          |  |            |  |
|---------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|--|----------|-----|-----------|--|-----------------------------------------------------------------------------------------------------------------------------------------|--|---------------------|--|--------------------------|--|------------|--|
| UNLESS OTHERWISE SPECIFIED                                                                                                                                                                                                                                                                                                                                                                                                                                                |  | INITIALS |     | DATE      |  | <div><div><div></div><div></div><div></div><div></div></div><div>Mini-Circuits®<br/>13 Neptune Avenue<br/>Brooklyn NY 11235</div></div> |  |                     |  |                          |  |            |  |
| DIMENSIONS ARE IN INCHES<br><br>TOLERANCES ON:<br>2 PL DECIMALS ±<br>3 PL DECIMALS ± .005"<br>ANGLES ±<br>FRACTIONS ±<br><div><div></div><div></div></div>                                                                                                                                                                                                                                                                                                                |  | DRAWN    | TM  | 12 MAR 18 |  |                                                                                                                                         |  |                     |  |                          |  |            |  |
|                                                                                                                                                                                                                                                                                                                                                                                                                                                                           |  | CHECKED  | MD  | 12 MAR 18 |  |                                                                                                                                         |  |                     |  |                          |  |            |  |
|                                                                                                                                                                                                                                                                                                                                                                                                                                                                           |  | APPROVED | PTB | 12 MAR 18 |  |                                                                                                                                         |  |                     |  |                          |  |            |  |
|                                                                                                                                                                                                                                                                                                                                                                                                                                                                           |  |          |     |           |  | PL,14FL01,HQ2218, HQ2299,CBP<br>TB-1006+, 50 Ohm                                                                                        |  |                     |  |                          |  |            |  |
|                                                                                                                                                                                                                                                                                                                                                                                                                                                                           |  |          |     |           |  |                                                                                                                                         |  |                     |  |                          |  |            |  |
| <div><div></div>Mini-Circuits®</div> <p>THIS DOCUMENT AND ITS CONTENTS ARE THE PROPERTY OF MINI-CIRCUITS. EXCEPT FOR USE EXPRESSLY GRANTED, IN WRITING, TO ITS VENDORS, VENDEE AND THE UNITED STATES GOVERNMENT, MINI-CIRCUITS RESERVES ALL PROPRIETARY DESIGN, USE, MANUFACTURING AND REPRODUCTION RIGHTS THERETO. THESE CONTENTS SHALL NOT BE USED, DUPLICATED OR DISCLOSED TO ANY OUTSIDE PARTY, IN WHOLE OR IN PART, WITHOUT WRITTEN PERMISSION OF MINI-CIRCUITS.</p> |  |          |     |           |  | SIZE<br>A                                                                                                                               |  | CODE IDENT<br>15542 |  | DRAWING NO:<br>98-PL-543 |  | REV:<br>OR |  |
| ASHEETA1.DWG REV:A DATE:01/12/95                                                                                                                                                                                                                                                                                                                                                                                                                                          |  |          |     |           |  | FILE:<br>98PL543                                                                                                                        |  | SCALE:<br>2.25:1    |  | SHEET:<br>1 OF 1         |  |            |  |



# Evaluation Board and Circuit



Schematic Diagram

**Notes:**

1. PCB Material: FR4, GADE IT-180A OR Equivalent  
Dielectric Constant=4.7, Thickness=.025 inch.

 **Mini-Circuits®**

All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

| Specification              | Test/Inspection Condition                                         | Reference/Spec                                        |
|----------------------------|-------------------------------------------------------------------|-------------------------------------------------------|
| Operating Temperature      | -40° to 85°C<br>Ambient Environment                               | Individual Model Data Sheet                           |
| Storage Temperature        | -55° to 100° C<br>Ambient Environment                             | Individual Model Data Sheet                           |
| Humidity                   | 90 to 95% RH, 96 hours, 40°C                                      | MIL-STD-202, Method 103B, Condition B, Except 50°C    |
| Thermal Shock              | -55° to 100°C, 100 cycles                                         | MIL-STD-202, Method 107, Condition A-3, except +100°C |
| Solder Reflow Heat         | Sn-Pb Eutectic Process: 225°C peak<br>Pb-Free Process, 245°C peak | J-STD-020, Table 4-1, 4-2 and 5-2, Figure 5-1         |
| Solderability              | 10X Magnification                                                 | J-STD-002, Para 4.2.5, Test S, 95% Coverage           |
| Vibration (High Frequency) | 20g peak, 10-2000 Hz, 4 times in each of three axes (total 12)    | MIL-STD-202, Method 204, Condition D                  |
| Mechanical Shock           | 50g, 11 ms, 1/2-sine, 18 shocks: 3 each direction, each of 3 axes | MIL-STD-202, Method 213, Condition A                  |