


Surface Mount Bandpass Filter

CBP-1250C+

50Ω 1215 to 1285 MHz

The Big Deal

- Excellent Rejection
- Low passband Insertion Loss
- Miniature shielded package



Generic photo used for illustration purposes only
CASE STYLE: MP1766

Product Overview

CBP-1250C+ is a ceramic-coaxial-resonator based bandpass filter in a shielded package fabricated using SMT technology. This filter offers outstanding close in rejection, low insertion loss and high power handling for use in aviation, mobile radio, broadband and fixed wireless.

Key Features

Feature	Advantages
High Selectivity	The CBP-1250C+ filter incorporates High-Q ceramic resonators that enables sharp rejection near passband.
Low Passband VSWR	This filter maintains typical VSWR over passband frequency range making this filter easier to integrate into receiver and transmitter RF chains with less concerns for in band frequency ripple.
Rugged construction	The CBP-1250C+ has been qualified over wide range of thermal, mechanical and environmental conditions including withstanding the stress of extensive solder reflow cycles.

Notes


- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp



Surface Mount Bandpass Filter

CBP-1250C+

50Ω 1215 to 1285 MHz



Generic photo used for illustration purposes only
CASE STYLE: MP1766


Features

- Low Insertion loss
- High selectivity
- Miniature shielded package


Applications

- Traffic collision avoidance system (TCAS)
- Aeronautical radio navigation
- Fixed satellite
- Radio astronomy
- Radar and navigation system

Functional Schematic



Typical Frequency Response



Electrical Specifications at 25°C

Parameter	F#	Frequency (MHz)	Min.	Typ.	Max.	Unit
Pass Band	Center Frequency	—	—	1250	—	MHz
	Insertion Loss	F1-F2	1215-1285	0.8	2	dB
	VSWR	F1-F2	1215-1285	1.2	—	:1
Stop Band, Lower	Insertion Loss	DC-F3	DC-1055	20	30	dB
	VSWR	DC-F3	DC-1055	—	20	:1
Stop Band, Upper	Insertion Loss	F4-F5	1510-2500	20	30	dB
	VSWR	F4-F5	1510-2500	—	20	:1

Maximum Ratings





Operating Temperature	-40°C to 85°C
Storage Temperature	-55°C to 100°C
RF Power Input	5W

Permanent damage may occur if any of these limits are exceeded.

Typical Performance Data at 25°C

Frequency (MHz)	Insertion Loss (dB)	VSWR (:1)	Frequency (MHz)	Group Delay (nsec)
1	103.53	1737.18	1215	5.23
970	51.48	49.64	1218	5.18
1055	31.64	36.20	1223	5.07
1115	15.08	19.76	1226	5.01
1136	8.79	10.31	1230	4.96
1150	5.18	5.52	1234	4.90
1168	2.33	2.58	1237	4.86
1187	1.28	1.60	1240	4.84
1215	0.92	1.23	1245	4.80
1226	0.87	1.16	1250	4.76
1250	0.81	1.02	1255	4.75
1275	0.82	1.08	1258	4.74
1285	0.83	1.08	1261	4.73
1331	2.26	2.69	1265	4.74
1350	5.07	6.26	1268	4.75
1390	13.22	24.83	1272	4.76
1510	31.48	49.64	1276	4.78
1725	59.97	46.96	1280	4.82
2100	52.89	44.55	1283	4.86
2500	46.78	39.49	1285	4.89

+RoHS Compliant
The +Suffix identifies RoHS Compliance. See our web site for RoHS Compliance methodologies and qualifications



Notes

- Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
- The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp




www.minicircuits.com P.O. Box 350166, Brooklyn, NY 11235-0003 (718) 934-4500 sales@minicircuits.com

REV.B
M174392
CBP-1250C+
EDU1782
URJ
200811
Page 2 of 3

Pad Connections

INPUT	1
OUTPUT	10
GROUND	2,3,4,5,6,7,8,9,11,12,13

Demo Board MCL P/N: TB-684+
Suggested PCB Layout (PL-373)




NOTES:


- TRACE WIDTH IS SHOWN FOR OAK (OAK-602) WITH DIELECTRIC THICKNESS .022" ± .0015". COPPER: 1/2 OZ. EACH SIDE. FOR OTHER MATERIALS TRACE WIDTH MAY NEED TO BE MODIFIED.
- BOTTOM SIDE OF THE PCB IS CONTINUOUS GROUND PLANE.

- DENOTES PCB COPPER LAYOUT WITH SMOBC (SOLDER MASK OVER BARE COPPER)
- DENOTES COPPER LAND PATTERN FREE OF SOLDERMASK

Outline Drawing



PCB Land Pattern



Outline Dimensions (inch)

A	B	C	D	E	F	G	H	J	K	L	M	N
.750	.750	.210	.139	.157	.215	.160	.218	.157	.100	.060	.069	.149
19.05	19.05	5.33	3.53	3.99	5.46	4.06	5.54	3.99	2.54	1.52	1.75	3.78
P	Q	R	S	T	U	V	W	X	Y	Z	wt.	
.790	.541	.790	.499	.384	.203	.080	.069	.630	.630	.145	grams	
20.07	13.74	20.07	12.67	9.75	5.16	2.03	1.75	16.00	16.00	3.68	4.6	

Note: Please refer to case style drawing for details

Notes

- Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
- The parts covered by this specification document are subject to Mini-Circuit's standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuit's website at www.minicircuits.com/MCLStore/terms.jsp

Band Pass Filter

CBP-1250C+

Typical Performance Data

FREQ. (MHz)	INSERTION LOSS			INPUT RETURN LOSS			OUTPUT RETURN LOSS		
	(dB)			(dB)			(dB)		
	@-40°C	@+25°C	@+85°C	@-40°C	@+25°C	@+85°C	@-40°C	@+25°C	@+85°C
1	105.25	103.53	98.10	0.00	0.00	0.00	0.00	0.00	0.00
250	97.73	100.77	99.47	0.01	0.03	0.04	0.01	0.03	0.03
475	82.30	81.27	82.15	0.05	0.08	0.09	0.05	0.08	0.08
650	76.63	75.58	75.74	0.10	0.15	0.16	0.11	0.15	0.15
800	74.86	75.07	74.52	0.17	0.23	0.24	0.18	0.23	0.24
900	71.42	70.13	70.24	0.23	0.29	0.31	0.24	0.30	0.30
915	65.56	65.15	64.94	0.24	0.30	0.32	0.25	0.31	0.31
930	61.29	60.94	60.72	0.25	0.31	0.34	0.26	0.32	0.32
955	55.15	54.76	54.67	0.27	0.33	0.36	0.28	0.34	0.34
975	50.62	50.33	50.15	0.28	0.35	0.38	0.30	0.36	0.36
1000	44.99	44.66	44.48	0.31	0.38	0.41	0.33	0.39	0.40
1020	40.41	40.05	39.86	0.33	0.41	0.44	0.35	0.42	0.43
1055	32.05	31.64	31.42	0.38	0.48	0.51	0.40	0.49	0.50
1060	30.80	30.38	30.16	0.40	0.49	0.52	0.41	0.50	0.51
1080	25.61	25.15	24.90	0.45	0.56	0.60	0.47	0.57	0.59
1095	21.48	20.98	20.71	0.51	0.65	0.69	0.53	0.65	0.69
1100	20.06	19.54	19.26	0.54	0.69	0.74	0.56	0.69	0.73
1115	15.63	15.08	14.78	0.69	0.88	0.95	0.71	0.90	0.96
1120	14.13	13.57	13.27	0.78	0.99	1.07	0.80	1.01	1.08
1125	12.61	12.05	11.75	0.90	1.14	1.24	0.92	1.16	1.25
1138	8.73	8.23	7.96	1.44	1.84	2.00	1.47	1.86	2.02
1150	5.54	5.18	4.99	2.55	3.18	3.44	2.58	3.22	3.50
1155	4.44	4.16	4.01	3.28	4.03	4.34	3.32	4.09	4.41
1162	3.18	3.03	2.94	4.62	5.55	5.92	4.66	5.62	6.03
1170	2.17	2.15	2.12	6.56	7.66	8.10	6.62	7.77	8.25
1200	0.86	1.04	1.09	15.00	16.18	16.59	15.12	16.46	16.97
1215	0.73	0.92	0.97	18.64	19.72	20.10	18.71	20.03	20.56
1230	0.66	0.85	0.91	22.86	23.99	24.39	22.73	24.35	25.09
1250	0.61	0.81	0.87	37.99	39.12	36.20	32.41	38.49	45.32
1275	0.62	0.82	0.88	26.49	28.26	29.21	27.28	29.61	30.87
1285	0.63	0.83	0.89	25.54	28.24	30.09	27.90	32.86	37.04
1300	0.66	0.90	0.98	24.21	23.17	22.25	30.88	26.31	24.04
1308	0.73	1.00	1.10	19.34	17.48	16.55	21.26	18.45	17.18
1329	1.55	2.07	2.29	8.27	7.40	6.99	8.50	7.57	7.13
1338	2.46	3.11	3.38	5.41	4.90	4.65	5.54	5.00	4.73
1344	3.30	4.02	4.32	4.02	3.70	3.53	4.12	3.78	3.59
1385	11.49	12.22	12.51	0.69	0.79	0.81	0.71	0.81	0.82
1405	15.45	16.09	16.34	0.42	0.54	0.57	0.44	0.55	0.57
1430	19.87	20.41	20.63	0.31	0.42	0.45	0.32	0.43	0.45
1500	29.89	30.26	30.42	0.25	0.35	0.38	0.27	0.36	0.37
1510	31.13	31.48	31.63	0.25	0.35	0.38	0.27	0.35	0.37
1585	40.01	40.31	40.44	0.26	0.35	0.38	0.28	0.35	0.36
1630	45.22	45.51	45.59	0.27	0.35	0.38	0.28	0.35	0.36
1670	50.38	50.75	50.88	0.28	0.36	0.38	0.29	0.36	0.36
1700	55.07	55.52	55.80	0.28	0.36	0.38	0.29	0.36	0.37
1725	59.54	59.97	60.45	0.28	0.37	0.39	0.30	0.37	0.37
1750	71.41	72.67	72.82	0.29	0.37	0.39	0.30	0.37	0.37
1775	71.36	69.32	68.84	0.29	0.37	0.39	0.30	0.37	0.37
1825	58.94	58.43	58.05	0.29	0.37	0.39	0.30	0.37	0.37
1875	55.87	55.77	55.63	0.30	0.38	0.39	0.31	0.37	0.38
1975	53.57	53.24	52.98	0.30	0.38	0.40	0.31	0.38	0.38
2000	54.57	54.33	54.22	0.30	0.38	0.40	0.31	0.38	0.38
2050	51.41	51.63	52.00	0.31	0.39	0.40	0.32	0.39	0.39
2175	53.13	53.02	53.24	0.30	0.39	0.40	0.31	0.39	0.39
2225	53.66	53.27	52.73	0.30	0.39	0.40	0.31	0.39	0.40
2300	52.68	52.44	52.22	0.30	0.40	0.41	0.31	0.40	0.41
2350	51.66	51.56	51.15	0.30	0.41	0.41	0.32	0.41	0.42
2400	50.47	50.11	50.06	0.30	0.41	0.43	0.32	0.42	0.43
2450	49.93	49.52	48.68	0.31	0.42	0.44	0.33	0.44	0.46
2500	46.92	46.78	46.58	0.32	0.44	0.46	0.35	0.46	0.48



P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 • Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site
 The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: www.minicircuits.com

REV. OR
 CBP-1250C+
 130409
 Page 1 of 2

Band Pass Filter

CBP-1250C+

Typical Performance Data

FREQ. (MHz)	GROUP DELAY		
	(nsec)		
	@-40°C	@+25°C	@+85°C
1215	5.31	5.23	5.21
1216	5.28	5.20	5.18
1217	5.25	5.19	5.15
1218	5.24	5.18	5.15
1219	5.21	5.15	5.12
1220	5.18	5.12	5.09
1221	5.17	5.11	5.09
1222	5.13	5.07	5.06
1223	5.12	5.07	5.05
1224	5.10	5.05	5.03
1225	5.07	5.02	5.01
1226	5.07	5.01	4.99
1227	5.05	5.00	4.98
1228	5.03	4.98	4.96
1229	5.02	4.97	4.95
1230	5.00	4.96	4.94
1231	4.99	4.94	4.92
1232	4.98	4.93	4.92
1233	4.96	4.92	4.91
1234	4.94	4.90	4.88
1235	4.93	4.89	4.87
1236	4.92	4.88	4.87
1237	4.91	4.86	4.86
1239	4.88	4.85	4.84
1240	4.87	4.84	4.82
1241	4.86	4.83	4.82
1242	4.86	4.82	4.82
1243	4.84	4.81	4.81
1244	4.84	4.81	4.80
1245	4.83	4.80	4.79
1246	4.82	4.78	4.78
1247	4.81	4.78	4.78
1248	4.80	4.77	4.77
1250	4.78	4.76	4.75
1251	4.77	4.75	4.75
1255	4.76	4.75	4.74
1256	4.75	4.74	4.74
1257	4.75	4.75	4.75
1258	4.75	4.74	4.74
1260	4.75	4.74	4.74
1261	4.75	4.73	4.73
1262	4.75	4.75	4.74
1263	4.74	4.74	4.74
1265	4.74	4.74	4.74
1266	4.75	4.75	4.75
1269	4.75	4.75	4.76
1270	4.76	4.76	4.77
1272	4.75	4.76	4.78
1273	4.76	4.77	4.79
1274	4.76	4.77	4.79
1275	4.76	4.78	4.80
1276	4.77	4.78	4.80
1278	4.78	4.79	4.81
1279	4.79	4.81	4.83
1280	4.79	4.82	4.84
1281	4.81	4.84	4.86
1282	4.82	4.85	4.87
1283	4.82	4.86	4.88
1284	4.83	4.87	4.90
1285	4.85	4.89	4.92









P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 • Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site
The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: www.minicircuits.com



IF/RF MICROWAVE COMPONENTS


Typical Performance Curves



Band Pass Filter


CBP-1250C+

Typical Performance Curves




Outline Dimensions

MP1766



PCB Land Pattern



CASE#	A	B	C	D	E	F	G	H	J	K	L	M	N
MP1766	.750 (19.05)	.750 (19.05)	.210 (5.33)	.139 (3.53)	.157 (3.99)	.215 (5.46)	.160 (4.06)	.218 (5.54)	.157 (3.99)	.100 (2.54)	.060 (1.52)	.069 (1.75)	.149 (3.78)

CASE#	P	Q	R	S	T	U	V	W	X	Y	Z	WT.GRAMS
MP1766	.790 (20.07)	.541 (13.74)	.790 (20.07)	.499 (12.67)	.384 (9.75)	.203 (5.16)	.080 (2.03)	.069 (1.75)	.630 (16.00)	.630 (16.00)	.145 (3.68)	4.6

Dimensions are in inches (mm). Tolerances: 2PL. ± .03; 3PL. ± .015

Notes:

- Case material: Nickel-Silver alloy.
- Base: Printed wiring laminate.
- Termination finish:
For RoHS Case Styles: 2-5 μ inch (.05-.13 microns) Gold over 120-240 μ inch (3.05-6.10 microns) Nickel plate.
All models, (+) suffix.

Mini-Circuits®
ISO 9001 ISO 14001 CERTIFIED

ALL NEW
minicircuits.com


P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site



The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: www.minicircuits.com

RF/IF MICROWAVE COMPONENTS

Tape & Reel Packaging TR-F111



Applicable Case styles:

Applicable Case styles:RS1539

Tape Width, mm	Device Cavity Pitch, mm	Reel Size, inches	Devices per Reel
32	24	13	250

Mini-Circuits carrier tape materials provide protection from ESD (Electro-Static Discharge) during handling and transportation. Tapes are static dissipative and comply with industry standards EIA-481/EIA-541.

Go to: www.minicircuits.com/pages/pdfs/tape.pdf




INTERNET <http://www.minicircuits.com>

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661

Distribution Centers NORTH AMERICA 800-654-7949 • 417-335-5935 • Fax 417-335-5945 • EUROPE 44-1252-832600 • Fax 44-1252-837010

Mini-Circuits ISO 9001 & ISO 14001 Certified


THIRD ANGLE PROJECTION



REVISIONS

REV	ECN No.	DESCRIPTION	DATE	DR	AUTH
OR	M137721	NEW RELEASE	JUN 12	DDR	KG

SUGGESTED MOUNTING CONFIGURATION FOR
MP1766 CASE STYLE "13FL01" PIN CODE




NOTES:

- TRACE WIDTH IS SHOWN FOR OAK (OAK-602) WITH DIELECTRIC THICKNESS .022"±.0015". COPPER: 1/2 OZ. EACH SIDE.
FOR OTHER MATERIALS TRACE WIDTH MAY NEED TO BE MODIFIED.
- BOTTOM SIDE OF THE PCB IS CONTINUOUS GROUND PLANE.

 DENOTES PCB COPPER LAYOUT WITH SMOBC
(SOLDER MASK OVER BARE COPPER)


 DENOTES COPPER LAND PATTERN FREE OF SOLDERMASK

UNLESS OTHERWISE SPECIFIED	INITIALS	DATE
DIMENSIONS ARE IN INCHES TOLERANCES ON: 2 PL DECIMALS ± 3 PL DECIMALS ± .005" ANGLES ± FRACTIONS ±	DRAWN	DDR 22 JUN 12
	CHECKED	MD 22 JUN 12
	APPROVED	GM 22 JUN 12


 **Mini-Circuits®** 13 Neptune Avenue
Brooklyn NY 11235

PL, 13FL01, MP1766, BPF,
TB-684+, 50 Ohm


SIZE A	CODE IDENT 15542	DRAWING NO: 98-PL-373	REV: OR
FILE: 98PL373	SCALE: 4:1	SHEET: 1 OF 1	

 Mini-Circuits®
THIS DOCUMENT AND ITS CONTENTS ARE THE PROPERTY OF MINI-CIRCUITS.
EXCEPT FOR USE EXPRESSLY GRANTED, IN WRITING, TO ITS VENDORS, VENDEE
AND THE UNITED STATES GOVERNMENT, MINI-CIRCUITS RESERVES ALL PROPRIETARY
DESIGN, USE, MANUFACTURING AND REPRODUCTION RIGHTS THERE TO.
THESE CONTENTS SHALL NOT BE USED, DUPLICATED OR DISCLOSED TO ANY OUTSIDE
PARTY, IN WHOLE OR IN PART, WITHOUT WRITTEN PERMISSION OF MINI-CIRCUITS.

Evaluation Board and Circuit




TB-684+



Schematic Diagram

Notes:

1. 50 Ohm SMA Female connectors.
2. PCB Material: OAK-602 OR Equivalent
Dielectric Constant=2.50±.04, Thickness=.022 inch.



All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

Specification	Test/Inspection Condition	Reference/Spec
Operating Temperature	-40° to 85°C Ambient Environment	Individual Model Data Sheet
Storage Temperature	-55° to 100° C Ambient Environment	Individual Model Data Sheet
Humidity	90 to 95% RH, 96 hours, 40°C	MIL-STD-202, Method 103B, Condition B, Except 50°C
Thermal Shock	-55° to 100°C, 100 cycles	MIL-STD-202, Method 107, Condition A-3, except +100°C
Solder Reflow Heat	Sn-Pb Eutectic Process: 225°C peak Pb-Free Process, 245°C peak	J-STD-020, Table 4-1, 4-2 and 5-2, Figure 5-1
Solderability	10X Magnification	J-STD-002, Para 4.2.5, Test S, 95% Coverage
Vibration (High Frequency)	20g peak, 10-2000 Hz, 4 times in each of three axes (total 12)	MIL-STD-202, Method 204, Condition D
Mechanical Shock	50g, 11 ms, 1/2-sine, 18 shocks: 3 each direction, each of 3 axes	MIL-STD-202, Method 213, Condition A