

Engineering Development Model

Power Splitter/Combiner

GP2-ED13012A/3

2 Way-0°

Important Note

This model has been designed, built and tested in our engineering department. Performance data represents model capability. At present it is a non-catalog model. On request, we can supply a final specification sheet, part number and price/delivery information.



Please click "Back", and then click "Contact Us" for Applications support.

CASE STYLE : DQ1225

ELECTRICAL SPECIFICATIONS 50Ω @ +25°C				
Parameter		Min.	Typ.	Max. Units
Frequency		2630		8350 MHz
Isolation	2630 - 8350 MHz		21	dB
Insertion Loss Above 3.0 dB	2630 - 8350 MHz		0.70	dB
Phase Unbalance	2630 - 8350 MHz		4.29	deg.
Amplitude Unbalance	2630 - 8350 MHz		0.05	dB
VSWR	SUM Port		1.32	(:1)
	OUT Ports		1.16	(:1)

MAXIMUM RATINGS	
Operating Temperature	-40°C to 85°C
Storage Temperature	-65°C to 150°C

PIN CONNECTIONS	
SUM PORT	2
PORT 1	7
PORT 2	9
GROUND	1,3,4,5,6,8,10,11,12,Paddle

Functional Diagram



P.O. Box 350188, Brooklyn, New York 11235-0000 (718) 934-4500 Fax (718) 332-4851 For detailed performance specs & shopping online see Mini-Circuits web site



The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINN-CIRCUITS At: www.minn-circuits.com

IF/RF MICROWAVE COMPONENTS



REV. X1

GP2-ED13012A/3

12/15/2008

Page 1 of 1

2 Way-0° Power Splitter/Combiner

GP2-ED13012A/3

Typical Performance Data

FREQUENCY (MHz)	TOTAL LOSS ¹ (dB)		AMPLITUDE UNBALANCE (dB)	ISOLATION (dB)	PHASE UNBALANCE (Deg)	FREQUENCY (MHz)	VSWR (:1)		
	S-1	S-2					S	1	2
2560.0	4.66	4.75	0.10	11.11	2.45	2560.0	2.06	1.28	1.23
2630.0	4.35	4.43	0.08	13.37	2.33	2630.0	1.75	1.27	1.22
2690.0	4.15	4.23	0.08	15.32	2.30	2690.0	1.54	1.24	1.20
2760.0	3.98	4.05	0.07	17.66	2.33	2760.0	1.35	1.20	1.16
2830.0	3.86	3.92	0.06	19.96	2.37	2830.0	1.20	1.17	1.13
2900.0	3.78	3.84	0.06	22.02	2.44	2900.0	1.08	1.14	1.11
3000.0	3.71	3.77	0.06	23.54	2.53	3000.0	1.07	1.13	1.10
3180.0	3.66	3.71	0.05	22.58	2.72	3180.0	1.23	1.14	1.12
3360.0	3.64	3.68	0.04	21.14	2.92	3360.0	1.33	1.16	1.13
3540.0	3.61	3.64	0.03	20.67	3.08	3540.0	1.36	1.15	1.11
3720.0	3.57	3.59	0.03	20.82	3.20	3720.0	1.34	1.14	1.08
3900.0	3.52	3.55	0.02	21.57	3.30	3900.0	1.28	1.12	1.04
4080.0	3.48	3.52	0.03	22.89	3.42	4080.0	1.20	1.09	1.01
4270.0	3.46	3.49	0.04	25.19	3.58	4270.0	1.12	1.05	1.06
4450.0	3.44	3.49	0.04	29.16	3.77	4450.0	1.09	1.01	1.11
4630.0	3.45	3.49	0.04	38.44	3.97	4630.0	1.13	1.05	1.15
4810.0	3.47	3.51	0.03	37.75	4.17	4810.0	1.21	1.09	1.19
4990.0	3.51	3.53	0.02	28.55	4.38	4990.0	1.29	1.13	1.22
5170.0	3.55	3.56	0.01	24.69	4.58	5170.0	1.36	1.16	1.22
5360.0	3.58	3.59	0.01	22.40	4.75	5360.0	1.41	1.18	1.21
5540.0	3.61	3.62	0.01	20.83	4.94	5540.0	1.45	1.18	1.18
5720.0	3.62	3.64	0.03	19.75	5.14	5720.0	1.45	1.17	1.13
5900.0	3.61	3.66	0.05	18.68	5.49	5900.0	1.45	1.16	1.09
6080.0	3.60	3.65	0.05	17.77	5.73	6080.0	1.43	1.13	1.05
6260.0	3.59	3.65	0.05	17.10	6.01	6260.0	1.40	1.10	1.05
6450.0	3.58	3.64	0.06	16.51	6.22	6450.0	1.36	1.05	1.09
6600.0	3.57	3.63	0.06	16.13	6.37	6600.0	1.33	1.03	1.14
7470.0	3.69	3.73	0.04	13.51	7.31	7470.0	1.27	1.40	1.38
8350.0	4.24	3.88	0.36	10.27	10.71	8350.0	1.44	1.76	1.51
10110.0	3.74	5.11	1.37	17.38	12.66	10110.0	1.36	1.22	1.41

¹Total Loss = Insertion Loss + 3dB Splitter Loss








P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 • Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site
 The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: www.minicircuits.com


IF/RF MICROWAVE COMPONENTS

REV. X2
 GP2-ED13012A/3
 8/25/2010
 Page 1 of 1


Typical Performance Curves



Outline Dimensions



PCB Land Pattern



SUGGESTED LAYOUT,
TOLERANCE TO BE WITHIN ± 0.002

Weight: .02 Grams

Dimensions are in inches (mm). Tolerances: 2Pl. $\pm .01$; 3 Pl. $\pm .004$

Notes:

- Case material: Plastic.
- Termination finish:
 - For RoHS Case Styles: Tin-Silver alloy plate over Nickel barrier or Matte-Tin. All models, (+) suffix. See Data sheet.
 - For RoHS-5 Case Styles: Tin-Lead plate. All models, no (+) suffix.




INTERNET <http://www.minicircuits.com>

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661

Distribution Centers NORTH AMERICA 800-654-7949 • 417-335-5935 • Fax 417-335-5945 • EUROPE 44-1252-832600 • Fax 44-1252-837010

Mini-Circuits ISO 9001 & ISO 14001 Certified

Tape & Reel Packaging TR-F66



Tape Width, mm	Device Cavity Pitch, mm	Reel Size, inches	Devices per Reel see note	
8	4	7	Small quantity standard	20
				50
				100
				200
				500
		7	Standard	1000, 2000, 3000

Note: Please consult individual model data sheet to determine device per reel availability.

Mini-Circuits carrier tape materials provide protection from ESD (Electro-Static Discharge) during handling and transportation. Tapes are static dissipative and comply with industry standards EIA-481/EIA-541.

Go to: www.minicircuits.com/pages/pdfs/tape.pdf



INTERNET <http://www.minicircuits.com>



P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661

Distribution Centers NORTH AMERICA 800-654-7949 • 417-335-5935 • Fax 417-335-5945 • EUROPE 44-1252-832600 • Fax 44-1252-837010

Mini-Circuits ISO 9001 & ISO 14001 Certified

Evaluation Board and Circuit

For Pins Connections Refer to Data Sheet of the DUT



Notes:

Schematic Diagram

1. SMA Female connectors.
2. PCB Material: Rogers R04350 or equivalent,
Dielectric Constant=3.5, Thickness=.020 inch.

 **Mini-Circuits®**



All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

Specification	Test/Inspection Condition	Reference/Spec
Operating Temperature	-40° to 85° C Ambient Environment	Individual Model Data Sheet
Storage Temperature	-65° to 150° C Ambient Environment	Individual Model Data Sheet
Autoclave	15 psig, 100% RH, 121°C, 96 hours	JESD22-A102-C, Condition C
Temperature Cycling	-65° to 150°C, 100 cycles	JESD22-A104
Temperature Humidity	85°C/ 85% RH, 168 hours	JESD22-113
Solder Reflow Heat	Sn-Pb Eutetic Process: 240°C peak Pb-Free Process: 260°C peak	J-STD-020, Table 4-1, 4-2 and 5-2; Figure 5-1
Moisture Sensitivity: Level 1	Bake at 125°C for 24 hours Soak at 85°C/85% RH for 168 hours, Reflow 3 cycles at 240°C peak (Non-RoHS) or 260°C (RoHS)	J-STD-020
Solderability	10X magnification, 95% coverage	JESD22-B102, Method 1: Dip and Look Test
Mechanical Shock	50g, 11 ms, 1/2-sine, 18 shocks: 3 each direction, each of 3 axes	MIL-STD-202, Method 213, Condition A
Vibration (High Frequency)	20g peak, 10-2000 Hz, 12 times in each of three perpendicular directions (total 36)	MIL-STD-202, Method 204, Condition D