CERAMIC RESONATOR SURFACE MOUNT

Bandpass Filter

CBP3-2700BR+

50Ω 2646 to 2754 MHz

THE BIG DEAL

- Low Insertion Loss, 1.3 dB Typ.
- High Rejection, 60 dB Typ.
- Fractional Bandwidth from <1 to 25%
- Power Handling: 7 Watts
- Compact Size, 13 x 12.5 mm

Generic photo used for illustration purposes only

APPLICATIONS

- Telecom
  - Train Radio Communications
  - Point-to-Point Communications
  - 5G Sub 6 GHz

FUNCTIONAL DIAGRAM



PRODUCT OVERVIEW

All our Surface Mount Ceramic Resonator filters are built with rugged construction, qualified to withstand multiple demanding reflow cycles. Excellent repeatability across units is achieved through precise tuning and process control.

KEY FEATURES

Features	Advantages
Low Insertion Loss, 1.3 dB Typ.	Low signal loss results in better SNR in signal chain.
Fast roll-off (95.6%, 0.15dB/MHz at 20dB point)	Higher selectivity results in better adjacent channel rejection and dynamic range.
Excellent power handling, 7W	Well suited for transmitter applications.
Rugged Construction	These filter assemblies have been qualified over a wide range of thermal, mechanical and environmental conditions including withstanding the stress of extensive solder reflow cycles.
Small Size, 13 x 12.5 mm	Very well suited for high performance applications where size is a constraint.

Bandpass Filter

CBP3-2700BR+

50Ω 2646 to 2754 MHz

ELECTRICAL SPECIFICATIONS[1,2] AT +25°C

Parameter		F#	Frequency (MHz)	Min.	Typ.	Max.	Units
Passband	Center Frequency	—	—	—	2700	—	MHz
	Insertion Loss	F1-F2	2646 - 2754	—	1.3	2	dB
	Return Loss	F1-F2	2646 - 2754	10	15	—	dB
Stop Band, Lower	Rejection	DC-F3	DC - 1900	50	60	—	dB
		F3-F4	1900 - 2400	20	28	—	
Stop Band, Upper	Rejection	F5-F6	2960 - 3200	20	28	—	dB
		F6-F7	3200 - 4200	40	55	—	

1. Tested in Evaluation Board P/N TB-CBP3-2700BR+.
2. Bi-directional RF1 and RF2 ports can be interchanged.

ABSOLUTE MAXIMUM RATINGS[3]

Parameter	Ratings
Operating Temperature	-40°C to +85°C
Storage Temperature	-55°C to +100°C
Input Power[4]	7W at 25°C

3. Permanent damage may occur if any of these limits are exceeded.
4. Passband rating

TYPICAL FREQUENCY RESPONSE



Bandpass Filter

CBP3-2700BR+

50Ω 2646 to 2754 MHz

TYPICAL PERFORMANCE GRAPHS









CERAMIC RESONATOR SURFACE MOUNT

Bandpass Filter

CBP3-2700BR+

50Ω 2646 to 2754 MHz

FUNCTIONAL DIAGRAM



PAD DESCRIPTION

Function	Pad Number	Description
RF1 (Note 2)	1	Connects to RF Input Port
RF2 (Note 2)	8	Connects to RF Output Port
GROUND	2,3,4,5,6,7 9,10	Connects to Ground on PCB, (See drawing PL-735)
NC	—	No connection, not used internally. See drawing PL-735 for connection to PCB

SUGGESTED PCB LAYOUT (PL-735)



NOTES:

1. COPLANER WAVEGUIDE PARAMETERS ARE SHOWN FOR ROGERS (RO4350B), WITH DIELECTRIC THICKNESS .020"±.0015". COPPER: 1/2 Oz EACH SIDE. FOR OTHER MATERIALS TRACE WIDTH MAY NEED TO BE MODIFIED.
2. BOTTOM SIDE OF THE PCB IS CONTINUOUS GROUND PLANE.

DENOTES PCB COPPER LAYOUT WITH SMOBC (SOLDER MASK OVER BARE COPPER)

DENOTES COPPER LAND PATTERN FREE OF SOLDERMASK

CASE STYLE DRAWING



Weight: 1.0 grams

Dimensions are in inches[mm]. Tolerance: 2PL. ± .03; 3PL. ± .015

PRODUCT MARKING*: CBP3-2700BR

*Marking may contain other features or characters for internal lot control.

CERAMIC RESONATOR SURFACE MOUNT

Bandpass Filter

CBP3-2700BR+

50Ω 2646 to 2754 MHz

ADDITIONAL DETAILED INFORMATION IS AVAILABLE ON OUR DASH BOARD. CLICK HERE

Performance Data and Graphs	Data Graphs S-Parameter (S2P Files) Data Set (.zip file) De-embedded to device pads
Case Style	YG3251 Lead Finish: Electroless Nickel Immersion Gold
RoHs Status	Compliant
Tape and Reel	TR-F113
Suggested Layout for PCB Design	PL-735
Evaluation Board	TB-CBP3-2700BR+
	Gerber File
Environmental Rating	ENV54

NOTES

A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuits' applicable established test performance criteria and measurement instructions.
C. The parts covered by this specification document are subject to Mini-Circuits' standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the standard terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/terms/viewterm.html

Surface mount Band Pass Filter CBP3-2700BR+

Typical Performance Data

FREQ. (MHz)	INSERTION LOSS (dB)			INPUT RETURN LOSS (dB)			OUTPUT RETURN LOSS (dB)		
	@-40°C	@+25°C	@+85°C	@-40°C	@+25°C	@+85°C	@-40°C	@+25°C	@+85°C
0.5	97.17	109.22	98.61	0.04	0.05	0.05	0.05	0.05	0.05
5.0	104.33	101.14	97.36	0.04	0.04	0.05	0.04	0.05	0.05
20.0	89.04	87.96	88.19	0.06	0.06	0.07	0.06	0.06	0.07
40.0	82.99	81.10	81.86	0.08	0.09	0.11	0.08	0.09	0.09
60.0	79.48	80.04	78.45	0.10	0.11	0.13	0.10	0.11	0.11
80.0	77.26	76.89	76.27	0.10	0.12	0.13	0.11	0.12	0.11
100.0	74.73	74.74	75.01	0.11	0.13	0.14	0.12	0.13	0.12
200.0	68.93	68.95	69.47	0.14	0.15	0.17	0.14	0.16	0.16
300.0	66.17	66.07	66.21	0.14	0.16	0.18	0.14	0.16	0.17
400.0	64.06	64.00	63.92	0.13	0.16	0.18	0.13	0.16	0.18
500.0	62.75	62.72	62.72	0.12	0.15	0.17	0.11	0.14	0.16
600.0	62.15	62.15	62.29	0.10	0.13	0.15	0.10	0.13	0.15
700.0	61.80	61.93	61.77	0.08	0.12	0.14	0.08	0.11	0.13
800.0	61.10	61.10	61.01	0.06	0.10	0.12	0.05	0.09	0.11
900.0	61.72	61.73	61.59	0.04	0.08	0.10	0.03	0.07	0.10
1000.0	60.91	61.17	60.97	0.03	0.07	0.09	0.02	0.06	0.09
1100.0	62.13	62.26	62.12	0.00	0.05	0.07	0.00	0.04	0.07
1200.0	63.71	63.86	63.72	0.00	0.05	0.07	0.01	0.04	0.08
1300.0	64.86	65.10	64.70	0.01	0.04	0.07	0.02	0.04	0.07
1400.0	65.82	65.94	65.84	0.02	0.04	0.07	0.02	0.04	0.07
1900.0	59.90	59.78	59.85	0.02	0.09	0.12	0.02	0.09	0.13
2200.0	43.35	43.36	43.34	0.07	0.13	0.16	0.06	0.13	0.17
2400.0	28.24	28.16	28.09	0.13	0.20	0.23	0.13	0.20	0.24
2470.0	20.66	20.53	20.42	0.23	0.32	0.35	0.22	0.30	0.35
2540.0	10.58	10.33	10.22	0.91	1.09	1.18	0.85	1.02	1.12
2586.0	3.07	2.98	2.99	5.21	6.02	6.42	4.95	5.68	6.05
2646.0	0.85	1.03	1.13	16.22	15.77	15.74	15.52	15.20	15.17
2660.0	0.83	1.00	1.10	15.39	15.45	15.59	15.09	15.23	15.37
2670.0	0.79	0.95	1.05	16.10	16.47	16.69	15.92	16.37	16.60
2680.0	0.74	0.91	1.01	17.89	18.64	18.94	17.75	18.58	18.91
2700.0	0.67	0.85	0.96	26.89	29.87	30.46	26.82	29.95	30.73
2720.0	0.67	0.87	0.98	30.21	27.47	27.01	30.71	27.46	26.79
2730.0	0.70	0.90	1.01	26.08	24.74	24.71	26.55	24.96	24.73
2740.0	0.72	0.93	1.05	26.06	25.31	25.63	27.01	26.19	26.25
2754.0	0.78	1.00	1.14	28.26	26.95	26.81	34.56	32.82	31.32
2790.0	2.26	2.72	2.96	6.79	6.47	6.41	6.84	6.51	6.47
2834.0	9.55	10.16	10.39	1.07	1.17	1.24	1.10	1.19	1.27
2900.0	20.80	21.25	21.41	0.24	0.35	0.41	0.26	0.36	0.43
2960.0	28.73	29.08	29.20	0.13	0.24	0.28	0.15	0.25	0.31
3200.0	54.79	55.22	55.43	0.06	0.14	0.17	0.05	0.14	0.19
3250.0	63.43	64.40	65.84	0.05	0.13	0.16	0.05	0.14	0.18
3300.0	76.50	78.06	83.97	0.04	0.12	0.15	0.04	0.13	0.17
3340.0	71.93	71.29	69.70	0.04	0.12	0.15	0.03	0.12	0.17
3380.0	67.37	67.48	66.75	0.03	0.11	0.14	0.03	0.12	0.16
3420.0	65.83	65.64	64.45	0.02	0.10	0.13	0.02	0.11	0.16
3460.0	62.65	62.23	62.12	0.02	0.10	0.13	0.02	0.11	0.16
3500.0	61.48	60.86	61.08	0.02	0.11	0.13	0.01	0.10	0.15
3540.0	61.27	60.16	60.63	0.01	0.09	0.12	0.01	0.10	0.15
3580.0	61.71	60.36	60.93	0.01	0.09	0.12	0.00	0.10	0.15
3620.0	61.38	60.17	60.53	0.00	0.09	0.12	0.00	0.10	0.15
3660.0	60.46	59.49	59.48	0.00	0.08	0.11	0.01	0.09	0.14
3700.0	60.18	59.20	59.03	0.01	0.08	0.11	0.01	0.09	0.14
3740.0	59.33	58.74	58.39	0.01	0.07	0.11	0.01	0.09	0.14
3780.0	59.07	58.71	58.13	0.01	0.08	0.11	0.02	0.08	0.13
3820.0	58.85	58.56	58.01	0.02	0.07	0.11	0.01	0.09	0.14
3860.0	58.53	58.55	57.92	0.03	0.06	0.10	0.03	0.08	0.13
3900.0	58.18	58.43	57.57	0.03	0.06	0.10	0.03	0.08	0.14
4000.0	56.72	57.30	55.89	0.04	0.06	0.10	0.03	0.08	0.14
4100.0	56.18	56.50	54.74	0.05	0.05	0.00	0.04	0.07	0.15
4200.0	56.56	56.39	54.84	0.05	0.06	0.11	0.07	0.05	0.13

Typical Performance Data

FREQ.	GROUP DELAY		
(MHz)	(nsec)		
	@-40°C	@+25°C	@+85°C
2646	3.32	3.27	3.24
2648	3.29	3.24	3.22
2650	3.25	3.21	3.19
2652	3.23	3.19	3.17
2654	3.20	3.16	3.16
2656	3.19	3.16	3.14
2658	3.16	3.14	3.13
2660	3.15	3.13	3.11
2662	3.14	3.12	3.11
2664	3.12	3.10	3.09
2666	3.12	3.11	3.09
2668	3.11	3.10	3.09
2670	3.11	3.10	3.09
2672	3.11	3.10	3.09
2674	3.10	3.10	3.09
2676	3.11	3.10	3.09
2678	3.10	3.09	3.09
2680	3.11	3.11	3.09
2684	3.12	3.11	3.10
2690	3.13	3.13	3.12
2700	3.17	3.17	3.16
2710	3.21	3.20	3.19
2712	3.21	3.20	3.20
2714	3.23	3.22	3.21
2716	3.22	3.22	3.22
2718	3.24	3.24	3.23
2720	3.25	3.26	3.25
2722	3.27	3.27	3.26
2724	3.28	3.28	3.28
2726	3.29	3.30	3.29
2728	3.32	3.33	3.32
2730	3.33	3.34	3.34
2732	3.36	3.37	3.37
2734	3.39	3.41	3.41
2736	3.41	3.42	3.43
2738	3.45	3.47	3.47
2740	3.47	3.50	3.51
2742	3.52	3.54	3.54
2744	3.55	3.58	3.59
2746	3.60	3.64	3.64
2754	3.80	3.85	3.86

Typical Performance Curves

INSERTION LOSS vs. TEMPERATURE
INPUT POWER = 0 dBm



INSERTION LOSS vs. TEMPERATURE (Zoomed)
INPUT POWER = 0 dBm



INPUT RETURN LOSS vs. TEMPERATURE
INPUT POWER = 0 dBm



OUTPUT RETURN LOSS vs. TEMPERATURE
INPUT POWER = 0 dBm



GROUP DELAY vs. TEMPERATURE
INPUT POWER = 0 dBm



Case Style YG

Outline Dimensions

YG3251



CASE#	A	B	C	D	E	F	G	H	J	K	L	M
YG3251	.512 (13.00)	.492 (12.50)	.175 (4.45)	.547 (13.89)	.175 (4.45)	.100 (2.54)	.346 (8.79)	.422 (10.72)	.090 (2.29)	.246 (6.25)	.297 (7.54)	.070 (1.78)

CASE#	N	P	Q	R	S	T	U	V	W	X	Y	Z
YG3251	.166 (4.22)	.180 (4.57)	.110 (2.79)	.120 (3.05)	.146 (3.71)	.186 (4.72)	.552 (14.02)	.130 (3.30)	.532 (13.51)	.272 (6.91)	.212 (5.38)	.167 (4.24)

AA	WT.GRAMS
292 (7.42)	1.0

Dimensions are in inches (mm). Tolerances: 2PL. ± .03; 3PL. ± .015

Notes:

1. Case material: Nickel-Silver alloy.
2. Base: Printed wiring laminate.
3. Termination finish:
   For RoHS Case Styles: 2-5 µ inch (.05-.13 microns) Gold over 120-240 µ inch (3.05-6.10 microns) Nickel plate.
   All models, (+) suffix.

Mini-Circuits®
ISO 9001 ISO 14001 CERTIFIED
ALL NEW minicircuits.com
P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site
The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: www.minicircuits.com
RF/IF MICROWAVE COMPONENTS

This document and its contents are the property of Mini-Circuits

Tape & Reel Packaging TR-F113

DEVICE ORIENTATION IN T&R



Tape Width, mm	Device Cavity Pitch, mm	Reel Size, inches	Devices per Reel
24	20	13	400

Mini-Circuits carrier tape materials provide protection from ESD (Electro-Static Discharge) during handling and transportation. Tapes are static dissipative and comply with industry standards EIA-481/EIA-541.

Go to: www.minicircuits.com/pages/pdfs/tape.pdf

Mini-Circuits®
INTERNET http://www.minicircuits.com
P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661
Distribution Centers NORTH AMERICA 800-654-7949 • 417-335-5935 • Fax 417-335-5945 • EUROPE 44-1252-832600 • Fax 44-1252-837010
Mini-Circuits ISO 9001 & ISO 14001 Certified

This document and its contents are the property of Mini-Circuits.

THIRD ANGLE PROJECTION



REVISIONS					
REV	ECN No.	DESCRIPTION	DATE	DR	AUTH
OR	NPO-002916	NEW RELEASE	AUG 22	AP	VC

SUGGESTED MOUNTING CONFIGURATION FOR YG3251 CASE STYLE



NOTES:

1. COPLANER WAVEGUIDE PARAMETERS ARE SHOWN FOR ROGERS (RO4350B), WITH DIELECTRIC THICKNESS .020"±.0015". COPPER: 1/2 Oz EACH SIDE. FOR OTHER MATERIALS TRACE WIDTH MAY NEED TO BE MODIFIED.
2. BOTTOM SIDE OF THE PCB IS CONTINUOUS GROUND PLANE.

DENOTES PCB COPPER LAYOUT WITH SMOBC (SOLDER MASK OVER BARE COPPER)

DENOTES COPPER LAND PATTERN FREE OF SOLDERMASK

UNLESS OTHERWISE SPECIFIED		INITIALS	DATE
DIMENSIONS ARE IN INCHES	DRAWN	AP	01 AUG 22
TOLERANCES ON:	CHECKED	MD	01 AUG 22
2 PL DECIMALS ± .005"	APPROVED	PTB	01 AUG 22
3 PL DECIMALS ±			
ANGLES ±			
FRACTIONS ±			

Mini-Circuits®
THIS DOCUMENT AND ITS CONTENTS ARE THE PROPERTY OF MINI-CIRCUITS. EXCEPT FOR USE EXPRESSLY GRANTED, IN WRITING, TO ITS VENDORS, VENDEE AND THE UNITED STATES GOVERNMENT, MINI-CIRCUITS RESERVES ALL PROPRIETARY DESIGN, USE , MANUFACTURING AND REPRODUCTION RIGHTS THERETO. THESE CONTENTS SHALL NOT BE USED, DUPLICATED OR DISCLOSED TO ANY OUTSIDE PARTY, IN WHOLE OR IN PART, WITHOUT WRITTEN PERMISSION OF MINI-CIRCUITS.

ASHEETA1.DWG REV:A DATE:01/12/95

Mini-Circuits® 13 Neptune Avenue Brooklyn NY 11235

PL DWG, YG3251 C.S, 50 OHM, CBP3

SIZE	CODE IDENT	DRAWING NO:	REV:
A	15542	98-PL-735	OR

FILE:	SCALE:	SHEET:
98-PL-735	2:1	1 OF 1

Evaluation Board and Circuit

TB-CBP3-2700BR+



Schematic diagram



Notes:

1. PCB Material: ROGERS (RO4350B) OR Equivalent, Dielectric Constant=3.48±.05
Dielectric Thickness: .020±.0015
2. 50 Ohm SMA Female Connectors.

Mini-Circuits®

THIS DOCUMENT AND ITS CONTENTS ARE THE PROPERTY OF MINI-CIRCUITS.

Mini-Circuits

Environmental Specifications ENV54

All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

Specification	Test/Inspection Condition	Reference/Spec
Operating Temperature	-40° to 85°C Ambient Environment	Individual Model Data Sheet
Storage Temperature	-55° to 100° C Ambient Environment	Individual Model Data Sheet
Humidity	90 to 95% RH, 96 hours, 40°C	MIL-STD-202, Method 103B, Condition B, Except 50°C
Thermal Shock	-55° to 100°C, 100 cycles	MIL-STD-202, Method 107, Condition A-3, except +100°C
Solder Reflow Heat	Sn-Pb Eutectic Process: 225°C peak Pb-Free Process, 245°C peak	J-STD-020, Table 4-1, 4-2 and 5-2, Figure 5-1
Solderability	10X Magnification	J-STD-002, Para 4.2.5, Test S, 95% Coverage
Vibration (High Frequency)	20g peak, 10-2000 Hz, 4 times in each of three axes (total 12)	MIL-STD-202, Method 204, Condition D
Mechanical Shock	50g, 11 ms, 1/2-sine, 18 shocks: 3 each direction, each of 3 axes	MIL-STD-202, Method 213, Condition A

This document and its contents are the property of Mini-Circuits.