

Coaxial-Ceramic Resonator Filters and Multiplexers

50Ω

DC to 6 GHz

The Big Deal

- Low insertion loss with excellent power handling
- Passbands up to 6 GHz
- Fractional bandwidth from <1 to 25%
- Low profile designs with min. height of 0.120"
- Excellent temperature stability
- Rugged construction to handle demanding environmental conditions



Product Overview

Mini-Circuits' *Coaxial-Ceramic Resonator filters* offer low insertion loss in very small form factors, using ceramic material with high dielectric constant and superior Q factor. Bandpass and bandstop filters, diplexer and multiplexer designs can be constructed using this technology. Low insertion loss combined with excellent power handling makes these filters well suited for transmitter and receiver signal chains. Advanced filter design and construction can achieve stopband width greater than 3x the center frequency as high as 20 GHz.

All our coaxial-ceramic resonator filters are built with rugged construction, qualified to withstand multiple demanding reflow cycles. Excellent repeatability across units is achieved through precise tuning and process control.

Key Features

Feature	Advantages
Low insertion loss	Low signal loss results in better SNR in signal chain
Fast roll-off	Higher selectivity results in better adjacent channel rejection and dynamic range
Wide stop band	Wide spur-free stopband results in better receiver sensitivity
Excellent power handling	Well suited for transmitter applications
Rugged Construction	These filter assemblies have been qualified over a wide range of thermal, mechanical and environmental conditions including withstanding the stress of extensive solder reflow cycles
Small Size	Very well suited for high performance applications where size is a constraint.
Temperature stability	Very minimal change in electrical performance across temperature makes these filters suitable for a wide range of operating conditions.

Notes


- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp



Surface Mount Bandpass Filter

50 Ω 925 to 960 MHz

CBP4-942C+



Generic photo used for illustration purposes only
CASE STYLE: MP1766

Features

- Low Insertion Loss, 1dB typ.
- High rejection, 60dB typ.
- Miniature shielded package

Applications

- Public mobile
- Private land mobile
- GSM downlink band

Electrical Specifications at 25°C

Parameter		F#	Frequency (MHz)	Min.	Typ.	Max.	Unit
Pass Band	Center Frequency	-	-	-	942	-	MHz
	Insertion Loss	F1-F2	925 - 960	-	1.0	1.6	dB
	VSWR	F1-F2	925 - 960	-	1.29	1.67	:1
Stop Band, Lower	Insertion Loss	DC-F3	DC - 650	65	75	-	dB
		F3-F4	650 - 840	20	26	-	dB
Stop Band, Upper	Insertion Loss	F5-F6	1045 - 1250	20	26	-	dB
		F6-F7	1250 - 1750	50	60	-	dB


1. Measured on Mini-Circuits Characterization Test Board TB-CBP4-942C+

Maximum Ratings


Operating Temperature	-40°C to 85°C
Storage Temperature	-55°C to 100°C
RF Power Input	5W at 25°C

Permanent damage may occur if any of these limits are exceeded.

Functional Schematic



Typical Frequency Response







+RoHS Compliant

The +Suffix identifies RoHS Compliance. See our web site for RoHS Compliance methodologies and qualifications

Typical Performance Data at 25°C

Frequency (MHz)	Insertion Loss (dB)	VSWR (:1)	Frequency (MHz)	Group Delay (ns)
1	104.28	42841.20	925	8.83
10	104.29	2322.56	927	8.75
650	86.43	218.22	928	8.71
834	30.36	53.82	930	8.64
840	27.77	48.58	932	8.58
856	20.06	32.53	934	8.53
886	3.34	3.14	936	8.49
900	1.15	1.15	938	8.46
925	0.88	1.06	940	8.44
935	0.85	1.05	942	8.43
942	0.85	1.04	944	8.44
950	0.86	1.08	946	8.45
960	0.89	1.13	947	8.46
980	1.38	1.52	948	8.47
989	3.08	3.20	950	8.50
1029	20.25	52.90	952	8.54
1045	25.93	76.69	954	8.59
1060	30.59	93.33	956	8.66
1250	66.62	94.50	958	8.74
1750	60.06	53.87	960	8.85



Notes

- Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
- The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp




www.minicircuits.com P.O. Box 350166, Brooklyn, NY 11235-0003 (718) 934-4500 sales@minicircuits.com

REV. OR
ECO-007604
CBP4-942C+
EDU3721
URJ
210511
Page 2 of 3

Pad Connections


INPUT	1
OUTPUT	10
GROUND	2,3,4,5,6,7,8,9,11,12,13

Demo Board MCL P/N: TB-CBP4-942C+
Suggested PCB Layout (PL-373)




- NOTES:
- TRACE WIDTH IS SHOWN FOR OAK (OAK-602) WITH DIELECTRIC THICKNESS .022"±.0015". COPPER: 1/2 OZ. EACH SIDE.
FOR OTHER MATERIALS TRACE WIDTH MAY NEED TO BE MODIFIED.
 - BOTTOM SIDE OF THE PCB IS CONTINUOUS GROUND PLANE.
-  DENOTES PCB COPPER LAYOUT WITH SMOBC (SOLDER MASK OVER BARE COPPER)
-  DENOTES COPPER LAND PATTERN FREE OF SOLDERMASK

Outline Drawing



PCB Land Pattern



Outline Dimensions (inch mm)

A	B	C	D	E	F	G	H	J	K	L	M	N
.750	.750	.210	.139	.157	.215	.160	.218	.157	.100	.060	.069	.149
19.05	19.05	5.33	3.53	3.99	5.46	4.06	5.54	3.99	2.54	1.52	1.75	3.78
P	Q	R	S	T	U	V	W	X	Y	Z		wt.
.790	.541	.790	.499	.384	.203	.080	.069	.630	.630	.145		grams
20.07	13.74	20.07	12.67	9.75	5.16	2.03	1.75	16.00	16.00	3.68		4.6

Note: Please refer to case style drawing for details

Notes

A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.

B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.

C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp






Typical Performance Data

FREQ.	INSERTION LOSS			INPUT RETURN LOSS			OUTPUT RETURN LOSS		
(MHz)	(dB)			(dB)			(dB)		
	@-40°C	@+25°C	@+85°C	@-40°C	@+25°C	@+85°C	@-40°C	@+25°C	@+85°C
1	112.70	100.86	108.47	0.00	0.00	0.00	0.00	0.00	0.00
10	107.48	106.57	108.99	0.00	0.00	0.00	0.00	0.00	0.00
100	101.49	99.57	92.85	0.00	0.01	0.01	0.00	0.01	0.01
150	96.75	98.73	101.29	0.01	0.01	0.02	0.01	0.01	0.02
200	107.98	104.86	95.54	0.01	0.02	0.03	0.01	0.02	0.03
250	94.43	95.72	97.07	0.02	0.03	0.04	0.02	0.04	0.05
280	100.16	95.56	96.70	0.02	0.04	0.05	0.02	0.04	0.05
300	94.56	97.17	99.47	0.02	0.04	0.05	0.02	0.05	0.06
350	91.24	92.29	92.54	0.03	0.05	0.06	0.04	0.06	0.07
380	87.44	94.62	93.78	0.03	0.06	0.07	0.04	0.07	0.08
400	89.86	87.72	86.78	0.04	0.06	0.08	0.05	0.07	0.09
450	87.26	88.69	85.05	0.05	0.08	0.09	0.07	0.10	0.11
500	84.22	83.54	83.52	0.06	0.10	0.11	0.08	0.12	0.13
550	81.35	82.74	80.74	0.08	0.11	0.13	0.10	0.14	0.16
600	81.10	79.66	81.97	0.10	0.14	0.16	0.13	0.17	0.19
650	86.41	88.68	87.76	0.12	0.17	0.19	0.15	0.20	0.22
700	75.45	75.29	75.12	0.15	0.20	0.22	0.19	0.24	0.26
750	58.69	58.55	58.41	0.19	0.24	0.27	0.23	0.29	0.32
800	43.10	43.00	42.86	0.25	0.31	0.34	0.31	0.37	0.41
834	30.56	30.32	30.29	0.34	0.42	0.46	0.41	0.49	0.54
840	27.96	27.73	27.68	0.37	0.45	0.50	0.44	0.53	0.58
856	20.22	20.01	19.96	0.52	0.63	0.69	0.61	0.72	0.79
873	10.40	10.26	10.26	1.27	1.48	1.60	1.39	1.64	1.77
887	2.89	3.01	3.14	6.09	6.63	6.82	6.37	7.06	7.28
925	0.78	0.95	1.06	27.79	30.69	33.17	26.75	30.57	33.12
928	0.77	0.94	1.04	28.20	32.59	35.40	26.36	30.79	32.85
932	0.76	0.93	1.03	28.08	33.35	35.85	25.53	29.70	31.07
935	0.76	0.93	1.02	27.98	33.42	35.91	25.08	28.96	30.14
940	0.75	0.92	1.02	28.29	33.89	36.72	24.81	28.34	29.33
942	0.75	0.92	1.02	28.41	33.71	35.99	24.80	28.14	28.98
946	0.75	0.92	1.02	28.01	31.52	31.99	24.67	27.41	27.77
950	0.75	0.93	1.03	26.44	28.27	27.93	24.13	26.04	25.90
954	0.76	0.94	1.04	24.59	25.69	25.10	23.30	24.57	24.11
958	0.78	0.96	1.06	23.29	24.21	23.46	22.71	23.66	22.97
960	0.79	0.97	1.07	23.02	23.96	23.11	22.67	23.56	22.75
989	2.84	3.17	3.19	5.57	5.59	5.94	5.55	5.57	5.94
1006	10.15	10.40	10.33	1.01	1.14	1.24	1.02	1.16	1.27
1029	20.22	20.34	20.26	0.30	0.40	0.45	0.34	0.44	0.49
1045	25.94	26.02	25.93	0.22	0.31	0.35	0.26	0.35	0.40
1060	30.62	30.67	30.57	0.20	0.28	0.32	0.24	0.32	0.36
1100	41.18	41.20	41.05	0.18	0.25	0.29	0.23	0.30	0.34
1150	53.24	53.23	53.01	0.20	0.26	0.29	0.25	0.31	0.34
1180	62.18	61.91	62.00	0.21	0.26	0.29	0.25	0.31	0.35
1200	74.31	71.25	73.29	0.21	0.27	0.30	0.26	0.32	0.35
1250	66.44	66.24	66.58	0.22	0.28	0.31	0.28	0.33	0.36
1280	64.40	63.61	64.17	0.23	0.29	0.32	0.28	0.34	0.37
1300	62.68	63.11	62.80	0.24	0.30	0.32	0.29	0.35	0.38
1330	61.74	62.49	61.93	0.25	0.30	0.33	0.29	0.35	0.38
1360	62.25	62.48	62.26	0.25	0.30	0.33	0.30	0.35	0.38
1380	62.73	63.13	62.60	0.26	0.31	0.34	0.30	0.36	0.39
1410	63.51	63.74	63.21	0.26	0.31	0.34	0.31	0.37	0.40
1440	64.92	64.96	64.48	0.27	0.32	0.35	0.31	0.37	0.40
1460	65.90	65.41	65.86	0.27	0.32	0.35	0.31	0.37	0.40
1500	70.31	65.80	70.35	0.28	0.33	0.36	0.31	0.38	0.41
1550	58.20	62.31	58.53	0.29	0.34	0.37	0.33	0.38	0.42
1600	60.61	61.94	60.74	0.29	0.34	0.37	0.32	0.39	0.42
1650	61.78	62.05	62.05	0.29	0.35	0.37	0.31	0.38	0.42
1700	61.09	61.05	61.13	0.30	0.35	0.38	0.32	0.39	0.42
1730	60.84	60.30	60.28	0.30	0.35	0.38	0.32	0.39	0.42
1750	59.52	59.62	59.87	0.30	0.36	0.39	0.31	0.39	0.43

Typical Performance Data



FREQ.	GROUP DELAY		
(MHz)	(nsec)		
	@-40°C	@+25°C	@+85°C
912	10.03	9.94	9.91
913	9.92	9.83	9.80
914	9.82	9.75	9.72
915	9.73	9.65	9.62
916	9.65	9.58	9.55
917	9.57	9.50	9.47
918	9.50	9.43	9.40
919	9.43	9.37	9.34
920	9.37	9.31	9.28
921	9.31	9.25	9.22
923	9.21	9.15	9.12
924	9.16	9.10	9.07
925	9.10	9.05	9.01
926	9.06	9.01	8.98
927	9.01	8.97	8.93
928	8.98	8.93	8.90
929	8.94	8.90	8.86
930	8.91	8.87	8.83
931	8.88	8.84	8.80
932	8.84	8.81	8.77
933	8.82	8.78	8.75
934	8.79	8.76	8.72
935	8.77	8.74	8.70
936	8.75	8.72	8.69
937	8.74	8.70	8.67
938	8.73	8.69	8.66
939	8.71	8.68	8.65
940	8.70	8.67	8.64
941	8.70	8.67	8.63
942	8.70	8.67	8.63
943	8.69	8.66	8.63
944	8.70	8.67	8.63
945	8.70	8.67	8.64
946	8.71	8.68	8.65
947	8.72	8.69	8.65
948	8.72	8.70	8.66
949	8.74	8.71	8.67
950	8.76	8.73	8.69
951	8.78	8.75	8.71
952	8.80	8.77	8.73
953	8.82	8.80	8.75
954	8.85	8.83	8.78
955	8.88	8.86	8.81
956	8.91	8.89	8.84
957	8.95	8.93	8.88
958	9.00	8.98	8.93
959	9.05	9.03	8.98
960	9.10	9.09	9.03
961	9.16	9.15	9.09
962	9.23	9.22	9.15
963	9.30	9.29	9.22

Typical Performance Curves




Outline Dimensions

MP1766



PCB Land Pattern



CASE#	A	B	C	D	E	F	G	H	J	K	L	M	N
MP1766	.750 (19.05)	.750 (19.05)	.210 (5.33)	.139 (3.53)	.157 (3.99)	.215 (5.46)	.160 (4.06)	.218 (5.54)	.157 (3.99)	.100 (2.54)	.060 (1.52)	.069 (1.75)	.149 (3.78)

CASE#	P	Q	R	S	T	U	V	W	X	Y	Z	WT.GRAMS
MP1766	.790 (20.07)	.541 (13.74)	.790 (20.07)	.499 (12.67)	.384 (9.75)	.203 (5.16)	.080 (2.03)	.069 (1.75)	.630 (16.00)	.630 (16.00)	.145 (3.68)	4.6

Dimensions are in inches (mm). Tolerances: 2PL. $\pm .03$; 3PL. $\pm .015$

Notes:

- Case material: Nickel-Silver alloy.
- Base: Printed wiring laminate.
- Termination finish:
For RoHS Case Styles: 2-5 μ inch (.05-.13 microns) Gold over 120-240 μ inch (3.05-6.10 microns) Nickel plate.
All models, (+) suffix.




P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site



The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: www.minicircuits.com

RF/IF MICROWAVE COMPONENTS

Tape & Reel Packaging TR-F111



Applicable Case styles:

Applicable Case styles: RS1539

Tape Width, mm	Device Cavity Pitch, mm	Reel Size, inches	Devices per Reel
32	24	13	250

Mini-Circuits carrier tape materials provide protection from ESD (Electro-Static Discharge) during handling and transportation. Tapes are static dissipative and comply with industry standards EIA-481/EIA-541.

Go to: www.minicircuits.com/pages/pdfs/tape.pdf





INTERNET <http://www.minicircuits.com>

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661

Distribution Centers NORTH AMERICA 800-654-7949 • 417-335-5935 • Fax 417-335-5945 • EUROPE 44-1252-832600 • Fax 44-1252-837010

Mini-Circuits ISO 9001 & ISO 14001 Certified

Evaluation Board and Circuit



Schematic diagram

Notes:

1. 50 Ohm SMA female connectors.
2. PCB Material: OAK-602 OR Equivalent
Dielectric Constant= $2.50 \pm .04$, Thickness= $.022$ inch.

Mini-Circuits®



All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

Specification	Test/Inspection Condition	Reference/Spec
Operating Temperature	-40° to 85°C Ambient Environment	Individual Model Data Sheet
Storage Temperature	-55° to 100° C Ambient Environment	Individual Model Data Sheet
Humidity	90 to 95% RH, 96 hours, 40°C	MIL-STD-202, Method 103B, Condition B, Except 50°C
Thermal Shock	-55° to 100°C, 100 cycles	MIL-STD-202, Method 107, Condition A-3, except +100°C
Solder Reflow Heat	Sn-Pb Eutectic Process: 225°C peak Pb-Free Process, 245°C peak	J-STD-020, Table 4-1, 4-2 and 5-2, Figure 5-1
Solderability	10X Magnification	J-STD-002, Para 4.2.5, Test S, 95% Coverage
Vibration (High Frequency)	20g peak, 10-2000 Hz, 4 times in each of three axes (total 12)	MIL-STD-202, Method 204, Condition D
Mechanical Shock	50g, 11 ms, 1/2-sine, 18 shocks: 3 each direction, each of 3 axes	MIL-STD-202, Method 213, Condition A