



LTCC SMT

High Pass Filter

HFCG-1630+

50Ω 1.85 to 11 GHz

THE BIG DEAL

- Low Insertion Loss, 0.7 dB Typ.
- Return Loss, 19 dB Typ.
- Stop Band Rejection, 49 dB Typ.
- 0805 Surface Mount Footprint
- Power Handling: 4 Watts



Generic photo used for illustration purposes only

CASE STYLE: GE0805C-9

+RoHS Compliant

The +Suffix identifies RoHS Compliance. See our website for methodologies and qualifications

APPLICATIONS

- Test and Measurement Equipment
- Communications, Radar, EW, and ECM Defense Systems
- 5G MIMO and Back Haul Radio Systems
- 5G Sub 6 GHz
- WiFi 6E

PRODUCT OVERVIEW

HFCG-1630+ is a miniature low temperature co-fired ceramic (LTCC) high pass filter with a 1.85 to 11 GHz passband supporting a variety of applications. This model provides 0.7 dB typical insertion loss over a wide band due to its rugged monolithic construction. Housed in a tiny 0805 ceramic form factor with inspectable wrap-around terminations, the filter is ideal for dense signal chain PCB layouts where it complements MMIC size and performance. The LTCC fabrication process assures minimal RF performance variation while delivering a product that is well suited for environmental extremes of high humidity and temperature.

KEY FEATURES

| Feature | Advantages |
|-------------------------|---|
| Small size, 0805 | Accommodates tight space requirements for dense PCB layouts. |
| Wrap around termination | Provides excellent solderability and easy visual inspection capability. |
| LTCC construction | Provides a rugged package that is well suited for tough environments including high humidity and high temperature extremes. |
| Ultra-wide pass band | This filter has a very wide passband from 1.85 to 11 GHz. |
| Rugged Power handling | Handles up to 4 Watts in a small 0805 package. |

REV. B
ECO-016177
HFCG-1630+
EDU4457
URJ
221220





LTCC SMT

High Pass Filter

HFCG-1630+

ELECTRICAL SPECIFICATIONS^{1,2} AT 25°C

| Parameter | | F# | Frequency (GHz) | Min. | Typ. | Max. | Units |
|-----------|----------------|------------------------|-----------------|------|------|------|-------|
| Stopband | Rejection | DC-F1 | DC - 1 | 42 | 49 | — | dB |
| | | F1-F2 | 1 - 1.3 | 20 | 33 | — | |
| | Freq. Cut-Off | F3 ^(note 3) | 1.63 | — | 3 | — | |
| Passband | Insertion Loss | F4-F5 | 1.85 - 2.8 | — | 1.6 | — | dB |
| | | F5-F6 | 2.8 - 10 | — | 0.7 | 1.5 | |
| | | F6-F7 | 10 - 11 | — | 1.5 | — | |
| | Return Loss | F4-F5 | 1.85 - 2.8 | — | 13 | — | |
| | | F5-F6 | 2.8 - 10 | — | 19 | — | |
| | | F6-F7 | 10 - 11 | — | 17 | — | |

1. This component should not be employed as a DC-block. DC blocking capacitors are required in applications where DC voltage and/or current is present at either input or output ports. Please contact Mini-Circuits for further support.

2. Measured on Mini-Circuits Characterization Test Board TB-HFCG-1630+

3. Typically, a ±5% frequency deviation from the stated value may occur on a unit-to-unit basis.


ABSOLUTE MAXIMUM RATINGS¹

| Parameter | Ratings |
|-----------------------------|----------------|
| Operating temperature | -55°C to 125°C |
| Storage temperature | -55°C to 125°C |
| RF Power Input ² | 4W @25°C |


1. Permanent damage may occur if any of these limits are exceeded.

2. Power rating applies only to signals within the passband. Power rating above +25°C should be derated linearly to 0.9W at +125°C.

TYPICAL FREQUENCY RESPONSE



FUNCTIONAL DIAGRAM





LTCC SMT

High Pass Filter


HFCG-1630+

PAD CONNECTIONS

| | |
|--------|---------|
| RF IN | 1 |
| RF OUT | 3 |
| GROUND | 2,4,5,6 |

PRODUCT MARKING: VV


DEMO BOARD MCL P/N: TB-HFCG-1630+
SUGGESTED PCB LAYOUT (PL-633)



NOTES:

1. COPLANAR WAVEGUIDE PARAMETERS ARE SHOWN FOR ROGERS (R04350B) WITH DIELECTRIC THICKNESS .020±.0015. COPPER: 1/2 Oz. EACH SIDE. FOR OTHER MATERIALS TRACE WIDTH AND GAP MAY NEED TO BE MODIFIED.
 2. BOTTOM SIDE OF THE PCB IS CONTINUOUS GROUND PLANE.
- DENOTES PCB COPPER PATTERN WITH SMOBC (SOLDER MASK OVER BARE COPPER)
- DENOTES PCB COPPER PATTERN FREE OF SOLDERMASK

OUTLINE DRAWING



OUTLINE DIMENSIONS (Inches)

| A | B | C | D | E | F | G | Wt. |
|------|------|------|------|------|------|------|-------|
| .079 | .049 | .037 | .014 | .012 | .012 | .026 | grams |
| 2.00 | 1.25 | 0.95 | 0.35 | 0.30 | 0.30 | 0.65 | .008 |






LTCC SMT

High Pass Filter

HFCG-1630+

TYPICAL PERFORMANCE DATA AT 25°C

| Frequency (MHz) | Insertion Loss (dB) | Return Loss (dB) |
|-----------------|---------------------|------------------|
| 10 | 77.64 | 0.05 |
| 100 | 64.21 | 0.07 |
| 500 | 51.70 | 0.23 |
| 1000 | 49.40 | 0.31 |
| 1200 | 48.72 | 0.47 |
| 1300 | 33.38 | 0.65 |
| 1400 | 21.76 | 1.04 |
| 1500 | 11.05 | 2.69 |
| 1630 | 2.82 | 16.98 |
| 1850 | 1.24 | 22.67 |
| 2800 | 0.46 | 27.22 |
| 4000 | 0.32 | 23.88 |
| 7000 | 0.28 | 32.81 |
| 10000 | 0.44 | 24.27 |
| 11000 | 0.62 | 30.68 |



NOTES

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
- C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the standard. Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp








Typical Performance Data

| FREQ. (MHz) | INSERTION LOSS | | | INPUT RETURN LOSS | | | OUTPUT RETURN LOSS | | |
|--------------------|----------------|--------|---------|-------------------|--------|---------|--------------------|--------|---------|
| | (dB) | | | (dB) | | | (dB) | | |
| | @-55°C | @+25°C | @+125°C | @-55°C | @+25°C | @+125°C | @-55°C | @+25°C | @+125°C |
| 10 | 78.56 | 77.64 | 78.88 | 0.02 | 0.05 | 0.07 | 0.04 | 0.08 | 0.11 |
| 50 | 69.55 | 70.98 | 71.51 | 0.01 | 0.05 | 0.08 | 0.04 | 0.08 | 0.11 |
| 100 | 64.04 | 64.21 | 64.17 | 0.03 | 0.07 | 0.09 | 0.05 | 0.09 | 0.12 |
| 150 | 60.57 | 60.69 | 60.70 | 0.05 | 0.09 | 0.12 | 0.07 | 0.11 | 0.14 |
| 200 | 58.24 | 58.27 | 58.36 | 0.07 | 0.12 | 0.15 | 0.09 | 0.13 | 0.17 |
| 250 | 56.44 | 56.54 | 56.58 | 0.09 | 0.14 | 0.17 | 0.11 | 0.15 | 0.19 |
| 300 | 55.11 | 55.18 | 55.17 | 0.12 | 0.17 | 0.21 | 0.12 | 0.17 | 0.21 |
| 350 | 53.99 | 54.03 | 54.06 | 0.14 | 0.19 | 0.23 | 0.13 | 0.18 | 0.23 |
| 400 | 53.07 | 53.12 | 53.15 | 0.16 | 0.21 | 0.26 | 0.14 | 0.20 | 0.25 |
| 450 | 52.29 | 52.33 | 52.37 | 0.17 | 0.22 | 0.28 | 0.15 | 0.21 | 0.26 |
| 500 | 51.66 | 51.70 | 51.71 | 0.17 | 0.23 | 0.29 | 0.16 | 0.22 | 0.28 |
| 550 | 51.10 | 51.16 | 51.16 | 0.18 | 0.24 | 0.31 | 0.16 | 0.23 | 0.29 |
| 600 | 50.62 | 50.68 | 50.69 | 0.18 | 0.25 | 0.31 | 0.17 | 0.24 | 0.30 |
| 650 | 50.20 | 50.27 | 50.28 | 0.18 | 0.25 | 0.32 | 0.18 | 0.25 | 0.32 |
| 700 | 49.84 | 49.90 | 49.91 | 0.17 | 0.25 | 0.32 | 0.18 | 0.26 | 0.33 |
| 750 | 49.50 | 49.56 | 49.57 | 0.17 | 0.25 | 0.32 | 0.19 | 0.27 | 0.34 |
| 800 | 49.21 | 49.27 | 49.28 | 0.16 | 0.25 | 0.33 | 0.20 | 0.28 | 0.36 |
| 850 | 48.96 | 49.03 | 49.04 | 0.16 | 0.26 | 0.34 | 0.20 | 0.30 | 0.38 |
| 900 | 48.81 | 48.90 | 48.94 | 0.17 | 0.27 | 0.35 | 0.22 | 0.31 | 0.40 |
| 950 | 48.84 | 48.97 | 49.05 | 0.18 | 0.29 | 0.37 | 0.23 | 0.33 | 0.42 |
| 1000 | 49.10 | 49.40 | 49.56 | 0.19 | 0.31 | 0.40 | 0.24 | 0.35 | 0.45 |
| 1050 | 50.08 | 50.62 | 50.99 | 0.21 | 0.34 | 0.44 | 0.26 | 0.38 | 0.48 |
| 1100 | 52.48 | 53.66 | 53.95 | 0.24 | 0.37 | 0.49 | 0.28 | 0.41 | 0.52 |
| 1150 | 58.19 | 55.12 | 53.48 | 0.28 | 0.42 | 0.55 | 0.31 | 0.45 | 0.57 |
| 1200 | 51.10 | 48.72 | 46.18 | 0.32 | 0.47 | 0.62 | 0.35 | 0.49 | 0.63 |
| 1250 | 41.70 | 40.15 | 38.32 | 0.38 | 0.55 | 0.72 | 0.40 | 0.56 | 0.72 |
| 1300 | 34.74 | 33.38 | 31.83 | 0.46 | 0.65 | 0.85 | 0.47 | 0.65 | 0.84 |
| 1400 | 23.03 | 21.76 | 20.40 | 0.75 | 1.04 | 1.39 | 0.78 | 1.05 | 1.38 |
| 1500 | 12.09 | 11.05 | 9.99 | 1.93 | 2.69 | 3.71 | 2.05 | 2.73 | 3.65 |
| 1630 | 2.65 | 2.82 | 2.89 | 14.05 | 16.98 | 19.43 | 15.00 | 16.38 | 17.42 |
| 1850 | 1.07 | 1.24 | 1.41 | 21.78 | 22.67 | 22.46 | 29.16 | 33.26 | 33.88 |
| 2000 | 0.85 | 1.02 | 1.19 | 17.89 | 16.83 | 15.99 | 19.63 | 18.09 | 17.10 |
| 2200 | 0.76 | 0.91 | 1.05 | 13.61 | 13.53 | 13.50 | 14.04 | 13.89 | 13.88 |
| 2400 | 0.61 | 0.73 | 0.86 | 14.73 | 14.95 | 15.20 | 14.84 | 15.06 | 15.31 |
| 2600 | 0.45 | 0.57 | 0.68 | 18.52 | 18.99 | 19.40 | 18.61 | 19.12 | 19.58 |
| 2800 | 0.34 | 0.46 | 0.57 | 25.97 | 27.22 | 27.89 | 26.20 | 27.71 | 28.90 |
| 3000 | 0.29 | 0.41 | 0.52 | 43.65 | 38.07 | 36.96 | 33.19 | 33.64 | 34.85 |
| 3200 | 0.27 | 0.38 | 0.49 | 26.07 | 25.13 | 25.09 | 25.86 | 25.24 | 25.45 |
| 3400 | 0.25 | 0.37 | 0.48 | 22.83 | 22.23 | 22.28 | 23.24 | 22.71 | 22.88 |
| 3600 | 0.23 | 0.35 | 0.47 | 22.29 | 21.72 | 21.71 | 22.69 | 22.14 | 22.18 |
| 3800 | 0.21 | 0.34 | 0.45 | 23.01 | 22.40 | 22.22 | 23.25 | 22.72 | 22.52 |
| 4000 | 0.19 | 0.32 | 0.43 | 24.56 | 23.88 | 23.42 | 25.11 | 24.53 | 23.97 |
| 4200 | 0.17 | 0.30 | 0.42 | 26.87 | 26.20 | 25.28 | 28.57 | 27.90 | 26.57 |
| 4400 | 0.17 | 0.29 | 0.41 | 29.71 | 29.27 | 27.92 | 33.99 | 33.55 | 30.35 |
| 4600 | 0.16 | 0.28 | 0.41 | 30.96 | 31.72 | 30.89 | 36.98 | 39.99 | 34.72 |
| 4800 | 0.15 | 0.28 | 0.40 | 29.74 | 30.99 | 32.52 | 33.56 | 35.44 | 36.20 |
| 5000 | 0.15 | 0.29 | 0.41 | 28.12 | 28.59 | 31.64 | 30.47 | 30.49 | 33.19 |
| 5200 | 0.16 | 0.29 | 0.42 | 26.46 | 26.59 | 29.79 | 28.41 | 27.94 | 30.67 |
| 5400 | 0.15 | 0.29 | 0.42 | 24.98 | 25.07 | 27.86 | 27.22 | 26.66 | 29.31 |
| 5600 | 0.14 | 0.29 | 0.42 | 24.28 | 24.35 | 27.00 | 26.67 | 26.18 | 28.59 |
| 5800 | 0.13 | 0.29 | 0.42 | 24.33 | 24.36 | 26.83 | 26.72 | 26.23 | 28.28 |
| 6000 | 0.14 | 0.29 | 0.43 | 25.19 | 24.95 | 27.11 | 27.36 | 26.71 | 28.33 |
| 6500 | 0.12 | 0.29 | 0.44 | 27.43 | 26.96 | 27.57 | 29.85 | 29.32 | 29.86 |
| 7000 | 0.12 | 0.28 | 0.45 | 33.71 | 32.81 | 29.98 | 31.99 | 32.89 | 31.30 |
| 7500 | 0.11 | 0.29 | 0.47 | 48.60 | 41.90 | 31.18 | 35.19 | 36.78 | 30.11 |
| 8000 | 0.11 | 0.30 | 0.48 | 34.36 | 36.19 | 29.88 | 38.95 | 34.18 | 26.33 |
| 9000 | 0.14 | 0.34 | 0.55 | 24.20 | 24.55 | 23.21 | 24.24 | 24.17 | 22.26 |
| 10000 | 0.22 | 0.44 | 0.67 | 23.78 | 24.27 | 23.07 | 22.44 | 23.93 | 24.81 |
| 10500 | 0.26 | 0.50 | 0.76 | 27.93 | 28.28 | 25.97 | 25.91 | 27.79 | 31.09 |
| 11000 | 0.36 | 0.62 | 0.91 | 35.27 | 30.68 | 25.96 | 32.48 | 31.06 | 28.16 |


Typical Performance Data

| FREQ. (MHz) | GROUP DELAY | | |
|--------------------|-------------|--------|---------|
| | (nsec) | | |
| | @-55°C | @+25°C | @+125°C |
| 1850 | 0.85 | 0.82 | 0.80 |
| 2000 | 0.62 | 0.60 | 0.59 |
| 2200 | 0.44 | 0.43 | 0.42 |
| 2400 | 0.35 | 0.34 | 0.34 |
| 2600 | 0.29 | 0.28 | 0.28 |
| 2800 | 0.24 | 0.24 | 0.24 |
| 3000 | 0.21 | 0.21 | 0.21 |
| 3200 | 0.18 | 0.18 | 0.18 |
| 3400 | 0.16 | 0.16 | 0.16 |
| 3600 | 0.14 | 0.14 | 0.14 |
| 3800 | 0.13 | 0.13 | 0.13 |
| 4000 | 0.12 | 0.12 | 0.12 |
| 4200 | 0.11 | 0.11 | 0.11 |
| 4400 | 0.10 | 0.10 | 0.11 |
| 4600 | 0.10 | 0.10 | 0.10 |
| 4800 | 0.09 | 0.09 | 0.10 |
| 5000 | 0.09 | 0.09 | 0.09 |
| 5200 | 0.08 | 0.08 | 0.09 |
| 5400 | 0.08 | 0.08 | 0.08 |
| 5600 | 0.08 | 0.08 | 0.08 |
| 5800 | 0.08 | 0.08 | 0.08 |
| 6000 | 0.07 | 0.07 | 0.08 |
| 6200 | 0.07 | 0.07 | 0.07 |
| 6400 | 0.07 | 0.07 | 0.07 |
| 6600 | 0.07 | 0.07 | 0.07 |
| 6800 | 0.07 | 0.07 | 0.07 |
| 7000 | 0.07 | 0.07 | 0.07 |
| 7200 | 0.07 | 0.07 | 0.07 |
| 7400 | 0.07 | 0.07 | 0.07 |
| 7600 | 0.06 | 0.07 | 0.07 |
| 7800 | 0.06 | 0.07 | 0.07 |
| 8000 | 0.06 | 0.07 | 0.07 |
| 8200 | 0.07 | 0.07 | 0.07 |
| 8400 | 0.07 | 0.07 | 0.07 |
| 8600 | 0.07 | 0.07 | 0.07 |
| 8800 | 0.07 | 0.07 | 0.07 |
| 9000 | 0.07 | 0.07 | 0.07 |
| 10000 | 0.07 | 0.07 | 0.08 |
| 10500 | 0.08 | 0.08 | 0.08 |
| 11000 | 0.08 | 0.08 | 0.09 |


Typical Performance Curves



Outline Dimensions



PCB Land Pattern



Suggested Layout,
Tolerance to be within $\pm .002$

| CASE # | A | B | C | D | E | F | G | H | J | K | WT.GRAM |
|-----------|----------------|----------------|----------------|----------------|----------------|----------------|----------------|----------------|----------------|----------------|---------|
| GE0805C-9 | .079 (2.00) | .049 (1.25) | .037 (0.95) | .014 (0.35) | .012 (0.30) | .012 (0.30) | .026 (0.65) | .014 (0.35) | .039 (1.00) | .110 (2.80) | .008 |

Dimensions are in inches (mm). Tolerances: 2Pl. $\pm .01$; 3 Pl. $\pm .005$

Notes:

- Open style, ceramic base.
- Termination finish: For RoHS Case Styles: Tin plate over Nickel plate. All models, (+) suffix.
For RoHS-5 Case Styles: Tin-Lead plate over Nickel plate. All models, no (+) suffix.



P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site



The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: www.minicircuits.com

RF/IF MICROWAVE COMPONENTS

Tape & Reel Packaging TR-F114

DEVICE ORIENTATION IN T&R




ILLUSTRATION 1

| Applicable Case Styles | |
|------------------------|-----------|
| GE0805C | JC0603C |
| GE0805C-1 | JC0603C-4 |
| GE0805C-1AP | JC0603C-6 |
| GE0805C-7 | |
| GE0805C-9 | |
| GE0805C-10 | |
| GE0805C-11 | |
| GE0805C-12 | |




ILLUSTRATION 2

| Applicable Case Styles | |
|------------------------|-----------|
| GE0805C-2 | JC0603C-1 |
| GE0805C-3 | JC0603C-2 |
| GE0805C-4 | JC0603C-3 |
| GE0805C-5 | JC0603C-5 |
| GE0805C-6 | JC0603C-7 |
| GE0805C-8 | JV1210C-1 |
| GE0805C-15 | |

| Tape Width, mm | Device Cavity Pitch, mm | Reel Size, inches | Devices per Reel | |
|----------------|-------------------------|-------------------|-------------------------------------|------|
| 8 | 4 | 7 | Small quantity standards (see note) | 20 |
| | | | | 50 |
| | | | | 100 |
| | | | | 200 |
| | | | | 500 |
| | | | | 1000 |
| | | | Standard | 4000 |

Note: Please Consult individual model data sheet to determine device per reel availability.

Mini-Circuits carrier tape materials provide protection from ESD (Electro-Static Discharge) during handling and transportation. Tapes are static dissipative and comply with industry standards EIA-481/EIA-541.

Go to: www.minicircuits.com/pages/pdfs/tape.pdf




INTERNET <http://www.minicircuits.com>

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661

Distribution Centers NORTH AMERICA 800-654-7949 • 417-335-5935 • Fax 417-335-5945 • EUROPE 44-1252-832600 • Fax 44-1252-837010

Mini-Circuits ISO 9001 & ISO 14001 Certified


THIRD ANGLE PROJECTION



REVISIONS


| REV OR | ECN No. | DESCRIPTION | DATE | DR | AUTH |
|--------|---------|-------------|--------|-----|------|
| | M174039 | NEW RELEASE | MAY 19 | DDR | VC |
| | | | | | |
| | | | | | |

SUGGESTED MOUNTING CONFIGURATION FOR
GE0805C-9 CASE STYLE "06FL02" PIN CODE



NOTES:

1. TRACE WIDTH IS SHOWN FOR ROGERS (R04350B) WITH DIELECTRIC THICKNESS .020"±.0015". COPPER: 1/2 Oz. EACH SIDE.
FOR OTHER MATERIALS TRACE WIDTH MAY NEED TO BE MODIFIED.
2. BOTTOM SIDE OF THE PCB IS CONTINUOUS GROUND PLANE.



DENOTES PCB COPPER LAYOUT WITH SMOBC
(SOLDER MASK OVER BARE COPPER)



DENOTES COPPER LAND PATTERN FREE OF SOLDERMASK

| UNLESS OTHERWISE SPECIFIED | INITIALS | DATE |
|----------------------------|---------------|-----------|
| DIMENSIONS ARE IN INCHES | DRAWN: DDR | 08 MAY 19 |
| TOLERANCES ON: | CHECKED: RV | 08 MAY 19 |
| 2 PL DECIMALS ± | APPROVED: RKS | 08 MAY 19 |
| 3 PL DECIMALS ± .005" | | |
| ANGLES ± | | |
| FRACTIONS ± | | |



Mini-Circuits® 13 Neptune Avenue
Brooklyn NY 11235



PL, 06FL02, GE0805C-9
TB-1104+, 50 OHM

| | | | |
|------------------|---------------------|--------------------------|------------|
| SIZE A | CODE IDENT 15542 | DRAWING NO: 98-PL-633 | REV: OR |
| FILE: 98PL633 | SCALE: 9:1 | SHEET: 1 OF 1 | |

THIS DOCUMENT AND ITS CONTENTS ARE THE PROPERTY OF MINI-CIRCUITS. EXCEPT FOR USE EXPRESSLY GRANTED, IN WRITING, TO ITS VENDORS, VENDEE AND THE UNITED STATES GOVERNMENT, MINI-CIRCUITS RESERVES ALL PROPRIETARY DESIGN, USE, MANUFACTURING AND REPRODUCTION RIGHTS THERETO. THESE CONTENTS SHALL NOT BE USED, DUPLICATED OR DISCLOSED TO ANY OUTSIDE PARTY, IN WHOLE OR IN PART, WITHOUT WRITTEN PERMISSION OF MINI-CIRCUITS.

Evaluation Board and Circuit

TB-HFCG-1630+



Notes:

1. PCB Material: ROGERS (R04350B) OR Equivalent, Dielectric Constant= 3.48 ± 0.05
Dielectric Thickness: $.020 \pm .0015$ inch
2. 50 Ohm SMA Female Connectors.

 **Mini-Circuits®**

All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

| Specification | Test/Inspection Condition | Reference/Spec |
|----------------------------|---|--|
| Operating Temperature | -55° to 125° C Ambient Environment | Individual Model Data Sheet |
| Storage Temperature | -55° to 125° C Ambient Environment | Individual Model Data Sheet |
| Humidity | 90 to 95% RH, 240 hours, 50°C | MIL-STD-202, Method 103, Condition A, Except 50°C and end-point electrical test done within 12 hours |
| Solder Reflow Heat | Sn-Pb Eutectic Process 225°C peak Pb-Free Process 245° - 250°C peak | J-STD-020C, Table 4-1, 4-2 and 5-2, Figure 5-1 |
| Solderability | 10X Magnification | J-STD-002, Para 4.2.5, Test S, 95% Coverage |
| Vibration (High Frequency) | 20g peak, 10-2000 Hz, 12 times in each of three perpendicular directions (total 36) | MIL-STD-202, Method 204, Condition D |
| Mechanical Shock | 50g, 11 ms, 1/2-sine, 18 shocks: 3 each direction, each of 3 axes | MIL-STD-202, Method 213, Condition A |