


**THE BIG DEAL**

- Low Cost
- Small Size
- 7 Sections
- Temperature Stable
- DC Block In/Out, Breakdown Voltage, 1 kV Typ.
- Excellent Power Handling, 7 W
- Hermetically Sealed

*Generic photo used for illustration purposes only*

CASE STYLE: FV1206

**+RoHS Compliant**

The +Suffix identifies RoHS Compliance. See our website for RoHS Compliance methodologies and qualifications

**APPLICATIONS**

- Sub-Harmonic Rejection
- Transmitters/Receivers
- Lab Use

**PRODUCT OVERVIEW**

The HFCN-1150+ LTCC High Pass Filter is constructed with 12 layers in order to achieve a miniature size and high repeatability of performance. Wrap-around terminations minimize variations in performance due to parasitics. Covering 1220-4500 MHz, these units offer low insertion loss and good rejection.

**KEY FEATURES**

| Feature                                 | Advantages                                                                                                                  |
|-----------------------------------------|-----------------------------------------------------------------------------------------------------------------------------|
| Small Size (3.20x1.6 mm)                | Allows for high layout density of circuit boards, while minimizing affects of parasitics.                                   |
| Rejection Peaks at Harmonic Frequencies | Provides good rejection of signals at harmonic frequencies, for improved system performance.                                |
| Wrap-Around Termination                 | Provides excellent solderability and easy visual inspection capability.                                                     |
| LTCC Construction                       | Provides a rugged package that is well suited for tough environments including high humidity and high temperature extremes. |



Mini-Circuits

CERAMIC

## High Pass Filter

HFCN-1150+

50Ω 1220 to 4500 MHz

ELECTRICAL SPECIFICATIONS<sup>1,2</sup> AT +25°C

| Parameter | F#             | Frequency (MHz) | Min.      | Typ. | Max. | Units |
|-----------|----------------|-----------------|-----------|------|------|-------|
| Stopband  | Rejection Loss | DC-F1           | DC-650    | 40   |      | dB    |
|           |                | F1-F2           | DC-850    | 20   |      |       |
|           | Freq. Cut-Off  | F3              | 1150      | 3.0  |      | dB    |
|           | VSWR           | DC-F2           | DC-850    | 20   |      | :1    |
| Passband  | Insertion Loss | F4-F7           | 1220-4500 |      | 2.0  | dB    |
|           |                | F5-F6           | 1320-3700 |      | 1.4  | dB    |
|           | VSWR           | F4-F7           | 1220-4500 | 2.0  |      | :1    |

1. In Application where DC voltage is present at either input or output ports, coupling capacitors are required.

2. Measured on Mini-Circuits Characterization Test Board TB-HFCN-1150+.


## ABSOLUTE MAXIMUM RATINGS

| Parameter                   | Ratings           |
|-----------------------------|-------------------|
| Operating Temperature       | -55°C to +100°C   |
| Storage Temperature         | -55°C to +100°C   |
| RF Power Input <sup>3</sup> | 7 W max. at +25°C |


3. Passband rating, derate linearly to 3 W at +100°C ambient.

Permanent damage may occur if any of these limits are exceeded.

## TYPICAL FREQUENCY RESPONSE



## FUNCTIONAL SCHEMATIC





Mini-Circuits®

CERAMIC

## High Pass Filter

HFCN-1150+


50Ω 1220 to 4500 MHz

## PIN CONNECTIONS

|        |     |
|--------|-----|
| RF IN  | 1   |
| RF OUT | 3   |
| GROUND | 2,4 |

PRODUCT MARKING: N/A

DEMO BOARD MCL P/N: TB-HFCN-1150+  
SUGGESTED PCB LAYOUT (PL-137)




**NOTES:** 1. COPLANAR WAVEGUIDE PARAMETERS ARE SHOWN FOR ROGERS RO4350B WITH THICKNESS .020" ± .0015". COPPER: 1/2 OZ. EACH SIDE. FOR OTHER MATERIALS TRACE WIDTH & GAP MAY NEED TO BE MODIFIED.

2. BOTTOM SIDE OF THE PCB IS CONTINUOUS GROUND PLANE.


 DENOTES PCB COPPER LAYOUT WITH SMOBC (SOLDER MASK OVER BARE COPPER)

 DENOTES COPPER LAND PATTERN FREE OF SOLDER MASK

## OUTLINE DRAWING



## PCB Land Pattern



Suggested Layout,  
Tolerance to be within ±.002

## OUTLINE DIMENSIONS (Inches mm)

| A    | B    | C    | D    | E    | F    | G    | H    | J    | K    | L    | M    | N    | P    | wt    |
|------|------|------|------|------|------|------|------|------|------|------|------|------|------|-------|
| .126 | .063 | .037 | .020 | .032 | .009 | .169 | .087 | .024 | .122 | .024 | .087 | .012 | .071 | grams |
| 3.20 | 1.60 | 0.94 | 0.51 | 0.81 | 0.23 | 4.29 | 2.21 | 0.61 | 3.10 | 0.61 | 2.21 | 0.30 | 1.80 | .020  |

TAPE &amp; REEL INFORMATION: F71



CERAMIC

# High Pass Filter


HFCN-1150+

Mini-Circuits

50Ω 1220 to 4500 MHz

## TYPICAL PERFORMANCE DATA AT +25°C

| Frequency (MHz) | Insertion Loss (dB) | VSWR (:1) |
|-----------------|---------------------|-----------|
| 10              | 97.78               | 1737.18   |
| 650             | 54.14               | 82.73     |
| 850             | 29.93               | 42.38     |
| 1150            | 3.39                | 2.91      |
| 1220            | 1.43                | 1.31      |
| 1300            | 1.01                | 1.23      |
| 3860            | 0.72                | 1.73      |
| 3940            | 0.79                | 1.82      |
| 4460            | 1.45                | 2.44      |
| 4520            | 1.49                | 2.66      |



### NOTES

- Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
- The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the standard terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at [www.minicircuits.com/terms/viewterm.html](http://www.minicircuits.com/terms/viewterm.html)






## Typical Performance Data

| FREQUENCY<br>(MHz) | INSERTION LOSS<br>(dB) |         |          | INPUT RETURN LOSS<br>(dB) |         |          | OUTPUT RETURN LOSS<br>(dB) |         |          |
|--------------------|------------------------|---------|----------|---------------------------|---------|----------|----------------------------|---------|----------|
|                    | @ -55°C                | @ +25°C | @ +100°C | @ -55°C                   | @ +25°C | @ +100°C | @ -55°C                    | @ +25°C | @ +100°C |
| 10.0               | 96.20                  | 97.78   | 100.84   | 0.00                      | 0.01    | 0.00     | 0.01                       | 0.01    | 0.01     |
| 30.0               | 86.06                  | 83.44   | 83.08    | 0.00                      | 0.01    | 0.00     | 0.02                       | 0.02    | 0.02     |
| 50.0               | 78.23                  | 78.46   | 79.84    | 0.00                      | 0.00    | 0.00     | 0.01                       | 0.01    | 0.01     |
| 70.0               | 75.71                  | 76.38   | 77.45    | 0.01                      | 0.00    | 0.01     | 0.01                       | 0.01    | 0.01     |
| 100.0              | 72.10                  | 71.88   | 73.27    | 0.00                      | 0.02    | 0.01     | 0.01                       | 0.02    | 0.03     |
| 110.0              | 71.81                  | 71.90   | 72.89    | 0.00                      | 0.01    | 0.02     | 0.01                       | 0.02    | 0.03     |
| 200.0              | 67.61                  | 68.10   | 69.37    | 0.00                      | 0.03    | 0.04     | 0.01                       | 0.03    | 0.06     |
| 290.0              | 63.34                  | 57.36   | 68.08    | 0.02                      | 0.07    | 0.06     | 0.02                       | 0.06    | 0.08     |
| 380.0              | 62.68                  | 63.56   | 66.59    | 0.03                      | 0.08    | 0.09     | 0.03                       | 0.07    | 0.10     |
| 470.0              | 61.28                  | 61.20   | 64.51    | 0.05                      | 0.11    | 0.14     | 0.05                       | 0.11    | 0.14     |
| 560.0              | 66.68                  | 66.85   | 69.49    | 0.08                      | 0.16    | 0.19     | 0.07                       | 0.14    | 0.19     |
| 650.0              | 54.62                  | 54.14   | 52.54    | 0.13                      | 0.21    | 0.25     | 0.12                       | 0.20    | 0.24     |
| 670.0              | 51.26                  | 50.91   | 49.67    | 0.14                      | 0.23    | 0.26     | 0.13                       | 0.21    | 0.26     |
| 700.0              | 47.00                  | 46.65   | 45.79    | 0.16                      | 0.25    | 0.29     | 0.15                       | 0.23    | 0.28     |
| 730.0              | 43.21                  | 42.85   | 42.21    | 0.18                      | 0.28    | 0.32     | 0.16                       | 0.26    | 0.31     |
| 760.0              | 39.72                  | 39.37   | 38.85    | 0.20                      | 0.30    | 0.36     | 0.19                       | 0.29    | 0.35     |
| 790.0              | 36.42                  | 36.11   | 35.64    | 0.23                      | 0.33    | 0.39     | 0.21                       | 0.31    | 0.38     |
| 820.0              | 33.28                  | 32.96   | 32.53    | 0.25                      | 0.37    | 0.44     | 0.24                       | 0.35    | 0.42     |
| 850.0              | 30.24                  | 29.93   | 29.53    | 0.29                      | 0.41    | 0.49     | 0.28                       | 0.39    | 0.48     |
| 860.0              | 29.22                  | 28.92   | 28.52    | 0.30                      | 0.43    | 0.51     | 0.29                       | 0.41    | 0.50     |
| 900.0              | 25.34                  | 25.07   | 24.74    | 0.36                      | 0.50    | 0.59     | 0.35                       | 0.48    | 0.57     |
| 950.0              | 20.53                  | 20.26   | 19.98    | 0.48                      | 0.64    | 0.74     | 0.47                       | 0.63    | 0.74     |
| 1000.0             | 15.78                  | 15.50   | 15.24    | 0.69                      | 0.91    | 1.04     | 0.70                       | 0.90    | 1.04     |
| 1050.0             | 11.13                  | 10.86   | 10.59    | 1.18                      | 1.48    | 1.71     | 1.18                       | 1.49    | 1.71     |
| 1100.0             | 6.79                   | 6.59    | 6.40     | 2.37                      | 2.88    | 3.28     | 2.39                       | 2.91    | 3.32     |
| 1150.0             | 3.40                   | 3.39    | 3.37     | 5.34                      | 6.22    | 6.87     | 5.40                       | 6.31    | 7.05     |
| 1160.0             | 2.91                   | 2.94    | 2.96     | 6.29                      | 7.27    | 7.95     | 6.37                       | 7.37    | 8.18     |
| 1170.0             | 2.50                   | 2.56    | 2.60     | 7.36                      | 8.45    | 9.19     | 7.45                       | 8.59    | 9.48     |
| 1190.0             | 1.83                   | 1.96    | 2.05     | 10.03                     | 11.37   | 12.21    | 10.17                      | 11.60   | 12.71    |
| 1200.0             | 1.58                   | 1.74    | 1.85     | 11.66                     | 13.17   | 14.03    | 11.86                      | 13.49   | 14.77    |
| 1220.0             | 1.23                   | 1.43    | 1.56     | 15.63                     | 17.53   | 18.34    | 16.18                      | 18.40   | 20.25    |
| 1230.0             | 1.11                   | 1.32    | 1.46     | 18.13                     | 20.23   | 20.79    | 19.04                      | 21.77   | 24.20    |
| 1260.0             | 0.90                   | 1.12    | 1.27     | 26.25                     | 25.15   | 23.26    | 32.62                      | 28.70   | 26.97    |
| 1300.0             | 0.79                   | 1.01    | 1.15     | 20.82                     | 19.61   | 18.77    | 21.11                      | 19.74   | 18.99    |
| 1320.0             | 0.77                   | 0.98    | 1.12     | 18.79                     | 18.10   | 17.56    | 18.96                      | 18.15   | 17.63    |
| 1560.0             | 0.43                   | 0.61    | 0.71     | 27.07                     | 29.46   | 29.06    | 25.16                      | 26.13   | 25.55    |
| 1810.0             | 0.36                   | 0.55    | 0.63     | 17.42                     | 16.92   | 17.38    | 17.35                      | 16.84   | 17.24    |
| 2060.0             | 0.44                   | 0.62    | 0.69     | 13.13                     | 13.04   | 13.44    | 13.29                      | 13.22   | 13.61    |
| 2310.0             | 0.45                   | 0.62    | 0.70     | 12.70                     | 12.82   | 13.21    | 13.00                      | 13.16   | 13.49    |
| 2550.0             | 0.37                   | 0.55    | 0.63     | 13.99                     | 14.17   | 14.71    | 14.36                      | 14.65   | 15.09    |
| 2800.0             | 0.23                   | 0.42    | 0.51     | 17.76                     | 18.09   | 18.16    | 18.14                      | 18.72   | 18.91    |
| 3050.0             | 0.14                   | 0.35    | 0.44     | 25.32                     | 25.53   | 26.33    | 27.98                      | 30.13   | 29.73    |
| 3300.0             | 0.17                   | 0.42    | 0.46     | 22.48                     | 21.22   | 23.37    | 24.15                      | 23.10   | 24.56    |
| 3310.0             | 0.17                   | 0.41    | 0.47     | 22.14                     | 21.09   | 23.02    | 23.53                      | 22.73   | 24.21    |
| 3380.0             | 0.28                   | 0.54    | 0.54     | 18.93                     | 18.01   | 20.03    | 21.22                      | 20.49   | 21.45    |
| 3460.0             | 0.56                   | 0.72    | 0.71     | 15.66                     | 15.75   | 17.42    | 21.15                      | 19.93   | 20.75    |
| 3540.0             | 0.81                   | 1.09    | 1.00     | 13.56                     | 13.32   | 14.68    | 21.70                      | 22.70   | 20.86    |
| 3620.0             | 0.42                   | 0.70    | 0.86     | 13.91                     | 13.51   | 13.94    | 15.46                      | 15.74   | 16.98    |
| 3700.0             | 0.42                   | 0.64    | 0.74     | 13.34                     | 13.24   | 13.42    | 14.04                      | 14.05   | 14.34    |
| 3780.0             | 0.44                   | 0.69    | 0.76     | 12.51                     | 12.30   | 12.75    | 12.81                      | 12.67   | 13.00    |
| 3860.0             | 0.45                   | 0.72    | 0.80     | 11.70                     | 11.48   | 11.92    | 11.68                      | 11.53   | 12.04    |
| 3940.0             | 0.52                   | 0.79    | 0.86     | 10.90                     | 10.70   | 10.97    | 10.81                      | 10.65   | 11.09    |
| 4020.0             | 0.58                   | 0.85    | 0.94     | 10.11                     | 9.88    | 10.23    | 10.14                      | 9.99    | 10.36    |
| 4100.0             | 0.66                   | 0.94    | 1.05     | 9.48                      | 9.29    | 9.63     | 9.62                       | 9.35    | 9.73     |
| 4110.0             | 0.67                   | 0.96    | 1.05     | 9.42                      | 9.26    | 9.59     | 9.51                       | 9.32    | 9.60     |
| 4160.0             | 0.73                   | 1.00    | 1.12     | 9.16                      | 8.94    | 9.20     | 9.22                       | 9.03    | 9.28     |
| 4220.0             | 0.79                   | 1.09    | 1.20     | 8.77                      | 8.61    | 8.75     | 8.79                       | 8.59    | 8.82     |
| 4280.0             | 0.82                   | 1.13    | 1.24     | 8.39                      | 8.26    | 8.48     | 8.43                       | 8.23    | 8.46     |
| 4340.0             | 0.91                   | 1.21    | 1.33     | 8.04                      | 7.93    | 8.16     | 8.18                       | 7.99    | 8.30     |
| 4400.0             | 1.04                   | 1.34    | 1.43     | 7.75                      | 7.67    | 7.81     | 7.72                       | 7.60    | 7.87     |
| 4460.0             | 1.06                   | 1.45    | 1.52     | 7.62                      | 7.56    | 7.55     | 7.47                       | 7.27    | 7.46     |
| 4520.0             | 1.15                   | 1.49    | 1.61     | 7.19                      | 6.87    | 7.15     | 7.13                       | 6.99    | 7.20     |
| 4700.0             | 1.31                   | 1.65    | 1.76     | 6.41                      | 6.31    | 6.42     | 6.52                       | 6.40    | 6.65     |
| 4720.0             | 1.30                   | 1.66    | 1.79     | 6.30                      | 6.20    | 6.30     | 6.53                       | 6.38    | 6.53     |
| 5130.0             | 1.67                   | 2.05    | 2.20     | 5.11                      | 5.09    | 5.28     | 5.14                       | 5.12    | 5.31     |
| 5330.0             | 1.95                   | 2.32    | 2.47     | 4.66                      | 4.68    | 4.79     | 4.69                       | 4.70    | 4.88     |
| 5740.0             | 2.46                   | 2.85    | 2.89     | 3.69                      | 3.84    | 4.11     | 3.73                       | 3.86    | 4.05     |
| 5950.0             | 2.72                   | 3.07    | 3.15     | 3.40                      | 3.57    | 3.85     | 3.43                       | 3.60    | 3.86     |
| 6360.0             | 3.25                   | 3.52    | 3.65     | 2.79                      | 3.11    | 3.35     | 2.92                       | 3.20    | 3.52     |
| 6560.0             | 3.51                   | 3.75    | 3.96     | 2.72                      | 2.97    | 3.34     | 2.76                       | 3.00    | 3.40     |
| 6970.0             | 3.93                   | 4.19    | 4.23     | 2.36                      | 2.72    | 3.09     | 2.42                       | 2.83    | 3.14     |
| 7790.0             | 3.87                   | 4.24    | 4.46     | 2.44                      | 2.81    | 3.05     | 2.34                       | 2.65    | 2.84     |
| 8000.0             | 4.12                   | 4.70    | 5.20     | 2.52                      | 2.88    | 3.11     | 2.35                       | 2.66    | 2.80     |

# Ceramic High Pass Filter

## Typical Performance Curves

HFCN-1150+



**Mini-Circuits®**  
ISO 9001 ISO 14001 AS 9100 CERTIFIED

[minicircuits.com](http://minicircuits.com)


P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 • Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site  
The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: [www.minicircuits.com](http://www.minicircuits.com)




IF/RF MICROWAVE COMPONENTS

REV. X1  
HFCN-1150+  
5/31/2011  
Page 1 of 1

### Outline Dimensions



### PCB Land Pattern



Suggested Layout,  
Tolerance to be within  $\pm .002$

| CASE # | A              | B              | C              | D              | E              | F              | G              | H              | J              | K              | L              | M              | N              | P              | WT. GRAM |
|--------|----------------|----------------|----------------|----------------|----------------|----------------|----------------|----------------|----------------|----------------|----------------|----------------|----------------|----------------|----------|
| FV1206 | .126<br>(3.20) | .063<br>(1.60) | .037<br>(0.94) | .020<br>(0.51) | .032<br>(0.81) | .009<br>(0.23) | .169<br>(4.29) | .087<br>(2.21) | .024<br>(0.61) | .122<br>(3.10) | .024<br>(0.61) | .087<br>(2.21) | .012<br>(0.30) | .071<br>(1.80) | .020     |

Dimensions are in inches (mm). Tolerances: 2 Pl.  $\pm .01$ ; 3 Pl.  $\pm .005$

#### Notes:

- Open style, ceramic base.
- Termination finish: **as shown below or indicated on Data Sheet.**  
For RoHS Case Styles: Tin plate over Nickel plate. All models, (+) suffix.  
For RoHS-5 Case Styles: Tin-Lead plate. All models, no (+) suffix.



P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site



The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: [www.minicircuits.com](http://www.minicircuits.com)

RF/IF MICROWAVE COMPONENTS

# Tape & Reel Packaging TR-F71




ILLUSTRATION 1

| Tape Width, mm | Device Cavity Pitch, mm | Reel Size, inches | Devices per Reel                    |      |
|----------------|-------------------------|-------------------|-------------------------------------|------|
| 8              | 4                       | 7                 | Small quantity standards (see note) | 20   |
|                |                         |                   |                                     | 50   |
|                |                         |                   |                                     | 100  |
|                |                         |                   |                                     | 200  |
|                |                         |                   |                                     | 500  |
|                |                         |                   |                                     | 1000 |
|                |                         |                   | Standard                            | 3000 |

Note: Please Consult individual model data sheet to determine device per reel availability.

Mini-Circuits carrier tape materials provide protection from ESD (Electro-Static Discharge) during handling and transportation. Tapes are static dissipative and comply with industry standards EIA-481/EIA-541.

Go to: [www.minicircuits.com/pages/pdfs/tape.pdf](http://www.minicircuits.com/pages/pdfs/tape.pdf)




P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site



The Design Engineers Search Engine Provides ACTUAL Data Instantly From Mini-Circuits At: [www.minicircuits.com](http://www.minicircuits.com)

RF/IF MICROWAVE COMPONENTS


## THIRD ANGLE PROJECTION



## REVISIONS

| REV | ECN No. | DESCRIPTION           | DATE     | DR  | AUTH |
|-----|---------|-----------------------|----------|-----|------|
| OR  | M88634  | NEW RELEASE           | 08/28/03 | GF  | ABD  |
| A   | M102713 | ADDED "...WITH SMOBC" | 01/17/06 | MMG | IL   |
|     |         |                       |          |     |      |
|     |         |                       |          |     |      |

SUGGESTED MOUNTING CONFIGURATION  
FOR FV1206 CASE STYLE, "nx" PIN CONNECTION




NOTES: 1. COPLANAR WAVEGUIDE PARAMETERS ARE SHOWN FOR ROGERS R04350B WITH THICKNESS .020"  $\pm$  .0015".  
 COPPER: 1/2 OZ. EACH SIDE.  
 FOR OTHER MATERIALS TRACE WIDTH & GAP MAY NEED TO BE MODIFIED.

2. BOTTOM SIDE OF THE PCB IS CONTINUOUS GROUND PLANE.



DENOTES PCB COPPER LAYOUT WITH SMOBC  
 (SOLDER MASK OVER BARE COPPER)



DENOTES COPPER LAND PATTERN FREE OF SOLDER MASK

UNLESS OTHERWISE SPECIFIED

INITIALS

DATE

DIMENSIONS ARE IN INCHES

TOLERANCES ON:

2 PL DECIMALS  $\pm$ 3 PL DECIMALS  $\pm$  .005ANGLES  $\pm$ FRACTIONS  $\pm$ 

DRAWN

GF

08/27/03

CHECKED

AV

08/28/03

APPROVED

ABD

08/28/03



**Mini-Circuits®**

13 Neptune Avenue  
 Brooklyn NY 11235

PL, nx, FV1206, LFCN/HFCN, TB-270

SIZE

A

CODE IDENT

15542

DRAWING NO:

98-PL-137

REV:

A

FILE:

98PL137

SCALE:

10:1

SHEET:



1 OF 1

Mini-Circuits®

THIS DOCUMENT AND ITS CONTENTS ARE THE PROPERTY OF MINI-CIRCUITS. EXCEPT FOR USE EXPRESSLY GRANTED, IN WRITING, TO ITS VENDORS, VENDEE AND THE UNITED STATES GOVERNMENT, MINI-CIRCUITS RESERVES ALL PROPRIETARY DESIGN, USE, MANUFACTURING AND REPRODUCTION RIGHTS THERETO. THESE CONTENTS SHALL NOT BE USED, DUPLICATED OR DISCLOSED TO ANY OUTSIDE PARTY, IN WHOLE OR IN PART, WITHOUT WRITTEN PERMISSION OF MINI-CIRCUITS.

ASHEETA1.DWG REV:A DATE:01/12/95

# Evaluation Board and Circuit



Schematic Diagram

## Notes:

1. SMA Female connectors.
2. PCB Material: ROGERS RO4350 or equivalent,  
Dielectric Constant=3.5, Thickness=.020 inch.

 **Mini-Circuits®**



All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

| Specification              | Test/Inspection Condition                                                           | Reference/Spec                                                                                       |
|----------------------------|-------------------------------------------------------------------------------------|------------------------------------------------------------------------------------------------------|
| Operating Temperature      | -55° to 100°C<br>Ambient Environment                                                | Individual Model Data Sheet                                                                          |
| Storage Temperature        | -55° to 100° C<br>Ambient Environment                                               | Individual Model Data Sheet                                                                          |
| Humidity                   | 90 to 95% RH, 240 hours, 50°C                                                       | MIL-STD-202, Method 103, Condition A, Except 50°C and end-point electrical test done within 12 hours |
| Solder Reflow Heat         | Sn-Pb Eutetic Process: 225°C peak<br>Pb-Free Process 245° - 250°C peak              | J-STD-020, Table 4-1, 4-2 and 5-2, Figure 5-1                                                        |
| Solderability              | 10X Magnification                                                                   | J-STD-002, Para 4.2.5, Test S, 95% Coverage                                                          |
| Vibration (High Frequency) | 20g peak, 10-2000 Hz, 12 times in each of three perpendicular directions (total 36) | MIL-STD-202, Method 204, Condition D                                                                 |
| Mechanical Shock           | 50g, 11 ms, 1/2-sine, 18 shocks: 3 each direction, each of 3 axes                   | MIL-STD-202, Method 213, Condition A                                                                 |