NON-CATALOG

Surface Mount

Directional Coupler

D18P

50Ω 1710 to 1990 MHz

Not Recommended For New Designs
Recommended Replacement Part:
D18PA+

CASE STYLE: CA531-1
PRICE: Contact Sales Dept.

Maximum Ratings

Operating Temperature	-40°C to 85°C
Storage Temperature	-65°C to 150°C

Permanent damage may occur if any of these limits are exceeded.

Pin Connections

INPUT	4
OUTPUT	6
COUPLED	3
GROUND	1,2,5

Features

- low mainline loss, 0.3 dB typ.
- excellent VSWR, 1.2:1 typ.
- excellent repeatability
- miniature low profile package
- aqueous washable

Applications

- PCS

Outline Drawing



Outline Dimensions (inch / mm)

A	B	C	D	E	F	G	H	J
.052	.067	.106	.122	.035	.064	.087	.118	.067
1.32	1.70	2.69	3.10	0.89	1.63	2.21	3.00	1.70

K	L	M	N	P	Q	R	S	wt
.083	.033	.042	.012	.020	.012	.006	.018	grams
2.11	0.84	1.07	0.30	0.51	0.30	0.15	0.46	0.020

Demo Board MCL P/N: TB-396+
Suggested PCB Layout (PL-270)



NOTES:
1. TRACE WIDTH IS SHOWN FOR ROGERS RO4350B WITH DIELECTRIC THICKNESS 0.020" ± 0.0015". COPPER: 1/2 OZ. EACH SIDE. FOR OTHER MATERIALS TRACE WIDTH MAY NEED TO BE MODIFIED.
2. BOTTOM SIDE OF THE PCB IS CONTINUOUS GROUND PLANE.

DENOTES PCB COPPER LAYOUT WITH SMOBC (SOLDER MASK OVER BARE COPPER)

DENOTES COPPER LAND PATTERN FREE OF SOLDER MASK

Directional Coupler Electrical Specifications

FREQ. RANGE (MHz)	COUPLING (dB)	MAINLINE LOSS[1] (dB)		DIRECTIVITY (dB)		VSWR (:1)	POWER INPUT[2] (W)
	Nominal	Typ.	Max.	Typ.	Min.	Typ.	Max.
1710-1990	18.0±1.8	0.3	0.5	15	10	1.2	1.0

1. Mainline loss includes theoretical power loss at coupled port.
2. 4W CW when operating with a 2.0:1 maximum VSWR on all ports at 25°C.

Frequency (MHz)	Mainline Loss (dB) In-Out	Coupling (dB) In-Cpl	Directivity (dB)	Return Loss (dB) In	Return Loss (dB) Out	Return Loss (dB) Cpl
1710.00	0.26	17.73	16.81	30.82	30.11	18.45
1724.00	0.24	17.65	16.85	30.48	29.84	18.24
1752.00	0.26	17.53	16.74	29.83	29.32	17.88
1780.00	0.28	17.39	16.66	29.50	29.04	17.68
1836.00	0.26	17.20	16.64	29.22	29.07	17.32
1864.00	0.27	17.06	16.52	28.92	28.54	17.01
1920.00	0.28	16.89	16.40	28.70	27.62	16.63
1948.00	0.29	16.75	16.32	28.78	27.69	16.51
1976.00	0.29	16.64	16.25	28.69	27.69	16.29
1990.00	0.30	16.64	16.22	28.56	27.53	16.13







Electrical Schematic



* ELECTRICAL SCHEMATIC FOR DIRECTIONAL COUPLER THAT IS DESIGNED WITHOUT INTERNAL TRANSFORMERS.

ESD Rating
Human Body Model (HBM): Class 1A (250 v to <500 v) in accordance with ANSI/ESD STM 5.1 - 2001
Machine Model (MM): Class M1 (< 100 v) in accordance with ANSI/ESD STM 5.2 - 1999 (pass 50V)

Notes
A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp

REV. D
M119986
D18P
JS/TD/CP/AM
140908

Directional Coupler D18P

Typical Performance Data

TEST CONDITIONS: INPUT POWER =0 dBm @Temperature = +25°C

FREQUENCY (MHz)	INSERTION LOSS (dB)	COUPLING LOSS (dB)	DIRECTIVITY (dB)	RETURN LOSS (dB)		
				IN	OUT	CPL
10	0.04	62.47	14.94	45.69	45.72	41.28
25	0.05	54.62	14.40	44.38	44.48	40.91
50	0.06	48.87	14.35	43.26	43.12	40.48
100	0.08	42.87	13.93	41.15	41.35	39.73
250	0.11	34.97	13.82	38.91	38.92	39.56
500	0.15	29.06	13.76	35.58	35.03	41.40
750	0.18	25.62	13.90	32.40	31.88	39.17
1000	0.22	23.22	14.09	29.41	28.97	33.76
1250	0.25	21.40	14.43	26.64	26.37	29.38
1500	0.29	19.97	14.84	24.12	23.98	26.21
1600	0.31	19.48	15.03	23.23	23.09	25.12
1650	0.32	19.24	15.16	22.82	22.64	24.65
1690	0.33	19.06	15.22	22.44	22.32	24.27
1700	0.32	19.02	15.22	22.36	22.25	24.16
1710	0.33	18.97	15.26	22.28	22.17	24.07
1720	0.33	18.93	15.30	22.21	22.08	23.99
1730	0.33	18.88	15.30	22.13	22.00	23.90
1750	0.34	18.80	15.33	21.95	21.85	23.71
1800	0.35	18.59	15.45	21.61	21.48	23.30
1850	0.35	18.39	15.59	21.22	21.08	22.91
1900	0.36	18.19	15.70	20.88	20.75	22.51
1950	0.37	18.00	15.83	20.54	20.41	22.14
1960	0.37	17.97	15.85	20.48	20.34	22.07
1970	0.38	17.94	15.87	20.40	20.26	21.99
1980	0.38	17.90	15.91	20.34	20.17	21.92
1990	0.38	17.86	15.94	20.28	20.10	21.86
2000	0.39	17.82	15.95	20.22	20.06	21.81
2010	0.39	17.79	15.98	20.15	20.02	21.74
2050	0.39	17.65	16.12	19.93	19.76	21.46
2100	0.40	17.48	16.27	19.61	19.45	21.14
2200	0.43	17.16	16.55	19.06	18.92	20.55
2300	0.45	16.86	16.89	18.52	18.37	19.98
2400	0.47	16.58	17.37	18.03	17.89	19.52
2500	0.49	16.32	17.79	17.58	17.42	18.99
2600	0.51	16.07	18.26	17.14	16.99	18.59
2700	0.54	15.84	18.82	16.69	16.56	18.16
2800	0.56	15.63	19.41	16.26	16.15	17.76
2900	0.59	15.42	20.08	15.87	15.70	17.40
3000	0.62	15.24	20.70	15.46	15.31	17.00
3100	0.65	15.07	21.40	15.03	14.90	16.67
3200	0.68	14.91	21.95	14.61	14.47	16.30
3300	0.71	14.76	22.55	14.25	14.08	15.98
3400	0.74	14.62	22.99	13.84	13.65	15.60
3500	0.77	14.49	23.32	13.49	13.25	15.28
3600	0.81	14.38	23.55	13.09	12.84	14.90
3700	0.85	14.28	23.63	12.69	12.41	14.56
3800	0.89	14.18	23.67	12.29	12.03	14.18
3900	0.93	14.10	23.45	11.91	11.64	13.84
4000	0.97	14.03	23.05	11.52	11.24	13.47
4500	1.29	13.86	18.87	9.41	9.12	11.79
5000	1.80	14.04	14.49	7.21	6.92	10.33
5500	2.64	14.64	10.05	5.17	4.97	9.20
6000	4.11	15.97	5.10	3.38	3.27	8.45

Mini-Circuits®
IF/RF MICROWAVE COMPONENTS • ISO 9001 ISO 14001 AS9100 CERTIFIED RoHS compliant
P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661
The Design Engineers Search Engine finds the model you need, Instantly • For detailed performance specs & shopping online see minicircuits.com

Directional Coupler D18P

Typical Performance Data

TEST CONDITIONS: INPUT POWER =0 dBm @Temperature = -40°C

FREQUENCY (MHz)	INSERTION LOSS (dB)	COUPLING LOSS (dB)	DIRECTIVITY (dB)	RETURN LOSS (dB)		
				IN	OUT	CPL
10	0.03	63.05	16.30	49.60	48.05	43.02
25	0.04	54.75	14.88	49.76	44.87	41.19
50	0.05	48.96	14.61	51.99	41.41	38.84
100	0.06	42.93	14.44	42.39	42.40	38.92
250	0.07	35.03	14.22	39.37	41.73	40.00
500	0.09	29.09	14.12	37.17	37.13	43.21
750	0.11	25.62	14.17	33.96	33.50	40.78
1000	0.13	23.21	14.34	30.84	30.44	34.06
1250	0.15	21.37	14.66	27.63	27.37	29.36
1500	0.18	19.92	15.03	24.60	24.45	26.22
1600	0.19	19.42	15.19	23.57	23.42	25.12
1650	0.20	19.18	15.35	23.11	22.94	24.69
1690	0.21	19.00	15.43	22.67	22.54	24.01
1700	0.20	18.96	15.46	22.58	22.45	23.84
1710	0.21	18.92	15.49	22.49	22.36	23.72
1720	0.21	18.87	15.51	22.41	22.27	23.64
1730	0.21	18.82	15.53	22.34	22.18	23.57
1750	0.22	18.74	15.58	22.15	22.03	23.51
1800	0.23	18.52	15.71	21.74	21.58	23.35
1850	0.23	18.32	15.82	21.21	21.00	22.79
1900	0.23	18.12	15.92	21.05	20.87	22.35
1950	0.24	17.94	16.00	20.88	20.72	21.90
1960	0.24	17.90	16.05	20.79	20.64	21.80
1970	0.24	17.86	16.08	20.68	20.52	21.70
1980	0.25	17.82	16.12	20.57	20.39	21.61
1990	0.25	17.78	16.15	20.47	20.26	21.53
2000	0.25	17.75	16.14	20.37	20.16	21.47
2010	0.25	17.71	16.16	20.26	20.07	21.42
2050	0.26	17.57	16.27	19.92	19.70	21.28
2100	0.27	17.40	16.44	19.60	19.39	21.07
2200	0.28	17.07	16.77	18.96	18.78	20.38
2300	0.30	16.77	17.07	18.29	18.06	19.84
2400	0.32	16.48	17.55	17.79	17.56	19.30
2500	0.34	16.21	18.00	17.34	17.09	18.84
2600	0.36	15.96	18.56	17.00	16.73	18.58
2700	0.37	15.73	19.21	16.63	16.38	17.85
2800	0.40	15.51	19.84	16.18	15.92	17.69
2900	0.41	15.29	20.50	15.61	15.24	17.18
3000	0.44	15.10	21.08	15.35	15.07	16.71
3100	0.46	14.93	21.84	14.75	14.45	16.31
3200	0.48	14.76	22.60	14.58	14.27	15.99
3300	0.49	14.60	23.34	14.47	14.14	15.41
3400	0.52	14.45	23.89	13.99	13.59	15.13
3500	0.54	14.32	24.18	13.75	13.34	14.73
3600	0.58	14.21	24.29	13.22	12.76	14.28
3700	0.62	14.09	24.33	12.69	12.21	13.99
3800	0.65	14.00	24.10	12.28	11.81	13.66
3900	0.69	13.92	23.77	11.87	11.39	13.27
4000	0.73	13.83	23.29	11.50	11.00	13.05
4500	1.01	13.64	19.17	9.40	8.89	11.41
5000	1.52	13.76	14.50	7.11	6.61	10.23
5500	2.34	14.30	10.15	5.05	4.65	9.17
6000	3.79	15.56	5.22	3.23	2.90	8.20

Mini-Circuits®
IF/RF MICROWAVE COMPONENTS • ISO 9001 ISO 14001 AS9100 CERTIFIED RoHS compliant
P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661
The Design Engineers Search Engine finds the model you need, Instantly • For detailed performance specs & shopping online see minicircuits.com

Directional Coupler D18P

Typical Performance Data

TEST CONDITIONS: INPUT POWER =0 dBm @Temperature = +85°C

FREQUENCY (MHz)	INSERTION LOSS (dB)	COUPLING LOSS (dB)	DIRECTIVITY (dB)	RETURN LOSS (dB)		
				IN	OUT	CPL
10	0.06	62.58	14.33	43.35	43.70	39.93
25	0.07	54.55	14.46	41.28	43.15	40.29
50	0.08	48.90	13.88	39.91	43.85	41.81
100	0.10	42.82	13.58	40.59	41.39	40.66
250	0.14	34.93	13.39	38.16	37.46	39.46
500	0.19	29.01	13.43	34.14	33.60	40.20
750	0.23	25.60	13.53	31.07	30.51	37.88
1000	0.28	23.23	13.74	28.31	27.77	33.19
1250	0.32	21.42	14.14	25.96	25.64	29.22
1500	0.37	19.99	14.59	24.00	23.83	26.25
1600	0.39	19.50	14.76	23.22	23.08	25.19
1650	0.41	19.27	14.88	22.84	22.66	24.70
1690	0.42	19.09	14.96	22.49	22.35	24.34
1700	0.41	19.05	14.96	22.40	22.28	24.23
1710	0.42	19.01	14.99	22.32	22.20	24.14
1720	0.42	18.96	15.01	22.23	22.12	24.07
1730	0.42	18.92	15.02	22.14	22.02	23.98
1750	0.43	18.83	15.08	21.99	21.86	23.82
1800	0.44	18.63	15.18	21.75	21.64	23.39
1850	0.45	18.42	15.33	21.42	21.32	23.06
1900	0.46	18.23	15.44	21.10	21.02	22.68
1950	0.47	18.05	15.56	20.77	20.67	22.30
1960	0.47	18.02	15.60	20.70	20.61	22.22
1970	0.48	17.98	15.65	20.64	20.54	22.14
1980	0.48	17.94	15.67	20.60	20.47	22.07
1990	0.48	17.90	15.69	20.56	20.41	22.02
2000	0.48	17.87	15.70	20.51	20.38	21.97
2010	0.48	17.83	15.72	20.45	20.35	21.91
2050	0.49	17.70	15.86	20.32	20.19	21.64
2100	0.51	17.53	16.01	20.02	19.91	21.25
2200	0.53	17.22	16.28	19.48	19.40	20.72
2300	0.56	16.91	16.59	18.98	18.89	20.13
2400	0.58	16.64	17.01	18.50	18.43	19.67
2500	0.61	16.38	17.36	18.00	17.94	19.17
2600	0.64	16.15	17.78	17.46	17.41	18.71
2700	0.67	15.93	18.33	16.95	16.93	18.32
2800	0.70	15.72	18.87	16.49	16.50	17.89
2900	0.73	15.52	19.48	16.14	16.09	17.55
3000	0.76	15.34	20.04	15.64	15.59	17.13
3100	0.79	15.17	20.68	15.21	15.20	16.83
3200	0.84	15.03	21.12	14.61	14.56	16.44
3300	0.87	14.88	21.62	14.12	14.04	16.17
3400	0.92	14.76	21.99	13.64	13.56	15.74
3500	0.96	14.64	22.35	13.21	13.06	15.48
3600	1.01	14.54	22.56	12.84	12.70	15.10
3700	1.05	14.43	22.76	12.51	12.34	14.71
3800	1.10	14.36	22.84	12.07	11.91	14.32
3900	1.15	14.28	22.82	11.73	11.56	14.02
4000	1.20	14.22	22.48	11.27	11.08	13.61
4500	1.55	14.07	18.48	9.23	9.06	11.98
5000	2.07	14.26	14.27	7.23	7.07	10.45
5500	2.89	14.90	9.86	5.28	5.21	9.31
6000	4.35	16.31	4.85	3.52	3.58	8.66

Mini-Circuits®
IF/RF MICROWAVE COMPONENTS • ISO 9001 ISO 14001 AS9100 CERTIFIED RoHS compliant
P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661
The Design Engineers Search Engine finds the model you need, Instantly • For detailed performance specs & shopping online see minicircuits.com

Directional Coupler D18P

Typical Performance Curves

Insertion Loss



Insertion Loss vs. TEMPERATURE



Coupling Loss vs. TEMPERATURE



Directivity vs. TEMPERATURE



Mini-Circuits®
IF/RF MICROWAVE COMPONENTS • ISO 9001 ISO 14001 AS9100 CERTIFIED RoHS compliant
P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661
The Design Engineers Search Engine finds the model you need, Instantly • For detailed performance specs & shopping online see minicircuits.com

Typical Performance Curves

Return Loss



Return Loss In vs. TEMPERATURE



Return Loss Out vs. TEMPERATURE



Return Loss Cpl vs. TEMPERATURE



Mini-Circuits®
IF/RF MICROWAVE COMPONENTS • ISO 9001 ISO 14001 AS9100 CERTIFIED RoHS compliant
P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661
The Design Engineers Search Engine finds the model you need, Instantly • For detailed performance specs & shopping online see minicircuits.com

Case Style CA

CA531-1

Outline Dimensions



PCB Land Pattern



Suggested Layout,
Tolerance to be within ±.002





CASE #	A	B	C	D	E	F	G	H	J	K
CA531-1	.052 (1.32)	.067 (1.70)	.106 (2.69)	.122 (3.10)	.035 (0.89)	.064 (1.63)	.087 (2.21)	.118 (3.00)	.067 (1.70)	.083 (2.11)

CASE #	L	M	N	P	Q	R	S	WT. GRAM
CA531-1	.033 (0.84)	.042 (1.07)	.012 (0.30)	.020 (0.51)	.012 (0.30)	.006 (0.15)	.018 (0.46)	.020

Dimensions are in inches (mm). Tolerances: 2Pl. ± .01; 3Pl. ± .005

Notes:

1. Case material: Plastic.
2. Termination finish:
   For RoHS Case Styles: Tin plate over Nickel plate. All models, (+) suffix.
   For RoHS-5 Case Styles: Tin-Lead plate. All models, no (+) suffix.

Mini-Circuits®
INTERNET http://www.minicircuits.com
P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661
Distribution Centers NORTH AMERICA 800-654-7949 • 417-335-5935 • Fax 417-335-5945 • EUROPE 44-1252-832600 • Fax 44-1252-837010
Mini-Circuits ISO 9001 & ISO 14001 Certified

This document and its contents are the property of Mini-Circuits

Tape & Reel Packaging TR-F31

DEVICE ORIENTATION IN T&R



Tape Width, mm	Device Cavity Pitch, mm	Reel Size, inches	Devices per Reel	
8	4	7	Small quantity standards (see note)	20
				50
				100
				200
				500
			Standard	1000

Note: Please Consult individual model data sheet to determine device per reel availability

Mini-Circuits carrier tape materials provide protection from ESD (Electro-Static Discharge) during handling and transportation. Tapes are static dissipative and comply with industry standards EIA-481/EIA-541.

Go to: www.minicircuits.com/pages/pdfs/tape.pdf

Mini-Circuits®
INTERNET http://www.minicircuits.com
P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661
Distribution Centers NORTH AMERICA 800-654-7949 • 417-335-5935 • Fax 417-335-5945 • EUROPE 44-1252-832600 • Fax 44-1252-837010
Mini-Circuits ISO 9001 & ISO 14001 Certified

This document and its contents are the property of Mini-Circuits.

THIRD ANGLE PROJECTION

REVISIONS					
REV	ECN No.	DESCRIPTION	DATE	DR	AUTH
OR	M110291	NEW RELEASE	03/20/07	AV	WP

SUGGESTED MOUNTING CONFIGURATION FOR CA531 CASE STYLE, "jn" PIN CONNECTION



NOTES:
1. TRACE WIDTH IS SHOWN FOR ROGERS RO4350B WITH DIELECTRIC THICKNESS 0.020" ± 0.0015". COPPER: 1/2 OZ. EACH SIDE. FOR OTHER MATERIALS TRACE WIDTH MAY NEED TO BE MODIFIED.
2. BOTTOM SIDE OF THE PCB IS CONTINUOUS GROUND PLANE.

DENOTES PCB COPPER LAYOUT WITH SMOBC (SOLDER MASK OVER BARE COPPER)

DENOTES COPPER LAND PATTERN FREE OF SOLDER MASK

UNLESS OTHERWISE SPECIFIED		INITIALS	DATE
DIMENSIONS ARE IN INCHES	DRAWN	AV	03/07/07
TOLERANCES ON:	CHECKED	IL	03/20/07
2 PL DECIMALS ±	APPROVED	WP	03/20/07
3 PL DECIMALS ± .005			
ANGLES ±			
FRACTIONS ±			

Mini-Circuits®

THIS DOCUMENT AND ITS CONTENTS ARE THE PROPERTY OF MINI-CIRCUITS. EXCEPT FOR USE EXPRESSLY GRANTED, IN WRITING, TO ITS VENDORS, VENDEE AND THE UNITED STATES GOVERNMENT, MINI-CIRCUITS RESERVES ALL PROPRIETARY DESIGN, USE , MANUFACTURING AND REPRODUCTION RIGHTS THERETO. THESE CONTENTS SHALL NOT BE USED, DUPLICATED OR DISCLOSED TO ANY OUTSIDE PARTY, IN WHOLE OR IN PART, WITHOUT WRITTEN PERMISSION OF MINI-CIRCUITS.

ASHEETA1.DWG REV:A DATE:01/12/95

Mini-Circuits® 13 Neptune Avenue Brooklyn NY 11235

PL, jn, CA531, D20C+, TB-396+

SIZE	CODE IDENT	DRAWING NO:	REV:
A	15542	98-PL-270	OR

FILE:	SCALE:	SHEET:
98PL270	10:1	1 OF 1

Evaluation Board and Circuit



TB-396+



Schematic Diagram

Notes:

1. 50 Ohm SMA Female connectors.
2. PCB Material: Rogers RO4350B or its equivalent, Dielectric Constant=3.5, Thickness=.020"

Mini-Circuits®

THIS DOCUMENT AND ITS CONTENTS ARE THE PROPERTY OF MINI-CIRCUITS.

Mini-Circuits

Environmental Specifications ENV12

All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

Specification	Test/Inspection Condition	Reference/Spec
Operating Temperature	-40° to 85° C Ambient Environment	Individual Model Data Sheet
Storage Temperature	-65° to 150° C Ambient Environment	Individual Model Data Sheet
Autoclave	15 psig, 100% RH, 121°C, 96 hours	JESD22-A102-C, Condition C
Temperature Cycling	-65° to 150°C, 100 cycles	JESD22-A104
Temperature Humidity	85°C/ 85% RH, 168 hours	JESD22-113
Solder Reflow Heat	Sn-Pb Eutetic Process: 240°C peak Pb-Free Process: 260°C peak	J-STD-020, Table 4-1, 4-2 and 5-2; Figure 5-1
Moisture Sensitivity: Level 1	Bake at 125°C for 24 hours Soak at 85°C/85% RH for 168 hours, Reflow 3 cycles at 240°C peak (Non-RoHS) or 260°C (RoHS)	J-STD-020
Solderability	10X magnification, 95% coverage	JESD22-B102, Method 1: Dip and Look Test
Mechanical Shock	50g, 11 ms, 1/2-sine, 18 shocks: 3 each direction, each of 3 axes	MIL-STD-202, Method 213, Condition A
Vibration (High Frequency)	20g peak, 10-2000 Hz, 12 times in each of three perpendicular directions (total 36)	MIL-STD-202, Method 204, Condition D

This document and its contents are the property of Mini-Circuits.