



Mini-Circuits®

SURFACE MOUNT 

Directional Coupler

DBTC-7-152X+

50Ω 7 dB 10 to 1500 MHz

FEATURES

- Very Flat Coupling
- Very Broadband, Multi Octave
- Temperature Stable, LTCC Base
- All Welded Construction
- Leads Attached for Better Solderability
- Micro Miniature Coupler
- Aqueous Washable
- Protected by US Patents 6,140,887 & 6,784,521

*Generic photo used for illustration purposes only*

CASE STYLE: AT1667-1

+RoHS CompliantThe +Suffix identifies RoHS Compliance.
See our website for methodologies and qualifications

APPLICATIONS

- VHF/UHF Transmitters
- Cellular

ELECTRICAL SPECIFICATIONS AT +25°C


Parameter	Condition (MHz)	Min.	Typ.	Max.	Unit
Frequency Range		10		1500	MHz
Mainline Loss	10-100		2.2	2.7	dB
	100-750		2.2	2.6	
	750-1500		2.3	3.2	
Nominal Coupling	10-1500		7.0±0.5		dB
Coupling Flatness	10-1500			±0.5	dB
Directivity	10-100	20	32		dB
	100-750	15	29		
	750-1500	9	16		
VSWR	10-1500		1.4		:1
Input Power	10-100			0.5	W
	100-750			1.0	
	750-1500			1.0	

ABSOLUTE MAXIMUM RATINGS

Parameter	Ratings
Operating Temperature	-40°C to +85°C
Storage Temperature	-55°C to +100°C

Permanent damage may occur if any of these limits are exceeded.

ELECTRICAL SCHEMATIC



* Electrical schematic is for directional coupler with internal transformer(s) that routes DC from RF ports to ground.

Mini-Circuits®

www.minicircuits.com P.O. Box 350166, Brooklyn, NY 11235-0003 (718) 934-4500 sales@minicircuits.com

REV. B
ECO-027378
DBTC-7-152X+
MCL NY
251017
PAGE 1 OF 3



Mini-Circuits

SURFACE MOUNT 

Directional Coupler


DBTC-7-152X+

50Ω 7 dB 10 to 1500 MHz

PIN CONNECTIONS

INPUT	3
OUTPUT	4
COUPLED	1
GROUND	2
ISOLATE (DO NOT USE)	6


PRODUCT MARKING: EP

DEMO BOARD MCL P/N: TB-DBTC-7-152X+
SUGGESTED PCB LAYOUT (PL-150)


- NOTES: 1. TRACE WIDTH IS SHOWN FOR ROGERS RO4350B WITH DIELECTRIC THICKNESS $0.020" \pm 0.0015"$; COPPER: 1/2 OZ. EACH SIDE. FOR OTHER MATERIALS TRACE WIDTH MAY NEED TO BE MODIFIED.
2. BOTTOM SIDE OF THE PCB IS CONTINUOUS GROUND PLANE.

-  DENOTES PCB COPPER LAYOUT WITH SMOBC (SOLDER MASK OVER BARE COPPER)
-  DENOTES COPPER LAND PATTERN FREE OF SOLDER MASK

OUTLINE DRAWING



PCB Land Pattern

Suggested Layout,
Tolerance to be within $\pm .002$ OUTLINE DIMENSIONS (Inches)
mm

A	B	C	D	E	F
.150	.150	.150	.050	.030	.025
3.81	3.81	3.81	1.27	0.76	0.64
G	H	J	K		wt
.028	.050	.160	.030		grams
0.71	1.27	4.06	0.76		0.10

TAPE & REEL INFORMATION: F15



Mini-Circuits

SURFACE MOUNT 




Directional Coupler

DBTC-7-152X+

50Ω 7 dB 10 to 1500 MHz

TYPICAL PERFORMANCE DATA

Frequency (MHz)	Mainline Loss (dB)	Coupling (dB)	Directivity (dB)	Return Loss (dB)		
	In-Out			In	Out	Cpl
5	2.17	7.07	27.17	12.45	21.18	21.33
50	2.12	6.92	33.24	13.24	21.93	26.08
150	2.15	6.97	32.95	13.44	21.26	25.04
300	2.17	6.98	29.37	13.82	19.97	23.43
500	2.16	6.91	24.56	14.71	18.49	22.88
700	2.18	6.84	20.96	15.84	17.26	24.92
1000	2.24	6.72	17.31	18.52	15.82	46.44
1200	2.33	6.69	15.48	21.27	15.02	24.76
1400	2.47	6.72	13.83	25.55	14.19	18.44
1500	2.57	6.76	13.09	28.03	13.74	16.40



NOTES

- Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- Electrical specifications and performance data contained in this specification document are based on Mini-Circuits' applicable established test performance criteria and measurement instructions.
- The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the standard. Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/terms/viewterm.html



Directional Coupler

DBTC-7-152X+

Typical Performance Data

TEST CONDITIONS: INPUT POWER =0 dBm @Temperature = +25°C

FREQUENCY (MHz)	INSERTION LOSS (dB)	COUPLING LOSS (dB)	DIRECTIVITY (dB)	RETURN LOSS (dB)		
				IN	OUT	CPL
10.0	2.08	6.85	36.06	13.19	22.11	25.94
20.0	2.09	6.86	35.81	13.24	22.17	26.44
50.0	2.11	6.88	34.64	13.31	22.11	26.58
100.0	2.12	6.90	31.88	13.44	21.79	26.08
150.0	2.13	6.90	29.32	13.59	21.47	25.61
200.0	2.12	6.90	27.12	13.75	21.21	25.18
250.0	2.12	6.90	25.31	13.91	20.95	24.81
300.0	2.12	6.89	23.74	14.10	20.70	24.53
350.0	2.12	6.88	22.45	14.27	20.53	24.29
400.0	2.11	6.86	21.30	14.47	20.37	24.08
450.0	2.11	6.85	20.25	14.69	20.22	23.96
500.0	2.11	6.84	19.36	14.93	20.06	23.89
550.0	2.11	6.82	18.53	15.17	19.94	23.85
600.0	2.11	6.81	17.78	15.44	19.84	23.77
650.0	2.12	6.79	17.12	15.74	19.72	23.72
700.0	2.12	6.78	16.47	16.02	19.66	23.69
750.0	2.12	6.77	15.89	16.32	19.63	23.62
800.0	2.14	6.76	15.36	16.62	19.59	23.45
850.0	2.15	6.74	14.88	16.92	19.53	23.23
900.0	2.17	6.74	14.41	17.20	19.53	22.97
950.0	2.19	6.73	13.98	17.48	19.52	22.61
1000.0	2.21	6.72	13.59	17.71	19.53	22.15
1050.0	2.24	6.71	13.22	17.90	19.56	21.63
1100.0	2.27	6.71	12.86	18.04	19.58	21.05
1150.0	2.31	6.71	12.55	18.08	19.54	20.42
1200.0	2.35	6.72	12.24	18.09	19.48	19.76
1250.0	2.40	6.72	11.94	18.00	19.43	19.11
1300.0	2.45	6.73	11.66	17.83	19.31	18.45
1350.0	2.51	6.74	11.38	17.58	19.15	17.80
1400.0	2.57	6.76	11.13	17.32	18.93	17.19
1450.0	2.63	6.78	10.88	16.97	18.72	16.60
1500.0	2.71	6.80	10.63	16.58	18.50	16.03
1550.0	2.79	6.83	10.39	16.17	18.20	15.49
1600.0	2.87	6.85	10.16	15.76	17.82	14.99
1700.0	3.07	6.93	9.71	14.89	17.04	14.04
1800.0	3.28	7.01	9.28	14.03	16.23	13.21
1900.0	3.53	7.11	8.85	13.22	15.31	12.46
2000.0	3.79	7.22	8.46	12.45	14.45	11.82
2100.0	4.08	7.36	8.08	11.78	13.58	11.24
2200.0	4.39	7.50	7.71	11.14	12.73	10.74
2300.0	4.71	7.67	7.33	10.57	12.03	10.29
2400.0	5.02	7.86	6.94	10.08	11.39	9.90
2500.0	5.33	8.07	6.55	9.69	10.83	9.54
2750.0	5.97	8.74	5.44	8.91	9.91	8.86
3000.0	6.39	9.70	4.02	8.43	9.87	8.46
3250.0	6.74	11.11	2.10	8.02	10.99	8.29
3500.0	7.38	13.24	0.46	7.44	14.30	8.25
3750.0	8.74	15.99	3.28	6.78	18.16	7.91
4000.0	10.92	18.01	4.96	6.23	13.74	7.23
4250.0	13.56	18.20	4.56	5.86	9.98	6.39
4500.0	16.17	17.67	3.41	5.62	7.93	5.67
4750.0	18.21	17.16	2.34	5.39	6.78	5.20
5000.0	19.47	16.94	1.66	5.17	6.16	4.85



REV. OR
DBTC-7-152X+

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 • Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site
The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: www.minicircuits.com



IF/RF MICROWAVE COMPONENTS

Page 1 of 3

Directional Coupler

DBTC-7-152X+

Typical Performance Data

TEST CONDITIONS: INPUT POWER =0 dBm @Temperature = -40°C

FREQUENCY (MHz)	INSERTION LOSS (dB)	COUPLING LOSS (dB)	DIRECTIVITY (dB)	RETURN LOSS (dB)		
				IN	OUT	CPL
10.0	2.09	6.85	33.06	12.83	20.48	20.13
20.0	2.00	6.70	38.20	13.43	20.58	21.81
50.0	1.96	6.62	39.16	13.80	20.24	22.32
100.0	1.96	6.62	33.47	14.09	20.15	22.35
150.0	1.96	6.62	30.28	14.30	20.24	22.54
200.0	1.97	6.62	27.94	14.32	19.92	22.32
250.0	1.97	6.63	25.99	14.47	19.89	22.54
300.0	1.98	6.63	24.26	14.57	19.79	22.49
350.0	1.98	6.62	22.86	14.68	19.65	22.54
400.0	1.98	6.61	21.64	14.87	19.63	22.64
450.0	1.98	6.60	20.59	15.06	19.53	22.63
500.0	1.98	6.59	19.69	15.29	19.46	22.83
550.0	1.98	6.58	18.85	15.48	19.35	22.92
600.0	1.98	6.56	18.08	15.73	19.25	23.04
650.0	1.98	6.54	17.40	16.06	19.29	23.15
700.0	1.98	6.53	16.75	16.33	19.29	23.27
750.0	1.99	6.51	16.17	16.63	19.24	23.47
800.0	2.00	6.49	15.65	16.92	19.20	23.53
850.0	2.01	6.48	15.15	17.24	19.12	23.67
900.0	2.03	6.46	14.66	17.54	19.14	23.65
950.0	2.04	6.44	14.21	17.87	19.19	23.52
1000.0	2.06	6.43	13.80	18.17	19.30	23.16
1050.0	2.08	6.42	13.41	18.35	19.34	22.55
1100.0	2.10	6.41	13.03	18.53	19.33	22.01
1150.0	2.14	6.40	12.69	18.58	19.35	21.28
1200.0	2.17	6.40	12.34	18.58	19.25	20.45
1250.0	2.21	6.39	12.02	18.61	19.21	19.70
1300.0	2.25	6.39	11.73	18.42	19.31	18.92
1350.0	2.30	6.39	11.45	18.11	19.08	18.15
1400.0	2.36	6.39	11.20	17.96	18.57	17.49
1450.0	2.42	6.40	10.95	17.75	18.12	16.87
1500.0	2.48	6.41	10.68	17.37	17.95	16.22
1550.0	2.55	6.43	10.41	16.71	18.02	15.58
1600.0	2.63	6.45	10.15	16.19	17.62	14.99
1700.0	2.81	6.49	9.68	15.29	16.64	13.92
1800.0	3.02	6.55	9.22	14.32	15.71	12.92
1900.0	3.26	6.62	8.80	13.41	14.83	12.13
2000.0	3.53	6.71	8.42	12.63	13.73	11.37
2100.0	3.81	6.82	8.02	11.82	12.95	10.73
2200.0	4.16	6.91	7.70	11.27	11.56	10.19
2300.0	4.46	7.08	7.28	10.48	11.23	9.67
2400.0	4.80	7.24	6.98	10.05	10.32	9.19
2500.0	5.11	7.42	6.63	9.67	9.73	8.88
2750.0	5.75	8.09	5.55	8.79	8.91	8.05
3000.0	6.13	9.10	4.10	8.15	8.83	7.50
3250.0	6.36	10.61	2.08	7.75	10.14	7.34
3500.0	6.93	13.05	0.77	7.13	13.40	7.26
3750.0	8.42	16.56	4.36	6.16	15.96	6.97
4000.0	10.82	19.16	6.52	5.59	11.66	6.37
4250.0	13.73	19.08	5.71	5.28	8.58	5.55
4500.0	16.38	18.23	4.12	5.12	7.07	4.89
4750.0	18.24	17.48	2.84	5.00	6.20	4.67
5000.0	19.19	17.20	2.01	4.82	5.79	4.31



REV. OR
DBTC-7-152X+

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 • Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site
The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: www.minicircuits.com



IF/RF MICROWAVE COMPONENTS

Page 2 of 3

Directional Coupler

DBTC-7-152X+

Typical Performance Data

TEST CONDITIONS: INPUT POWER = 0 dBm @Temperature = +85°C

FREQUENCY (MHz)	INSERTION LOSS (dB)	COUPLING LOSS (dB)	DIRECTIVITY (dB)	RETURN LOSS (dB)		
				IN	OUT	CPL
10.0	2.34	7.22	31.92	12.29	25.59	31.28
20.0	2.35	7.22	31.92	12.37	25.72	33.68
50.0	2.37	7.24	31.64	12.50	25.64	34.54
100.0	2.37	7.26	30.20	12.62	24.85	32.74
150.0	2.37	7.26	28.25	12.74	23.65	30.05
200.0	2.35	7.25	26.27	12.98	23.08	28.94
250.0	2.33	7.24	24.56	13.18	22.59	27.97
300.0	2.32	7.23	23.08	13.39	21.97	27.09
350.0	2.31	7.22	21.86	13.62	21.61	26.62
400.0	2.30	7.21	20.76	13.87	21.30	26.07
450.0	2.29	7.20	19.80	14.13	20.92	25.65
500.0	2.28	7.19	18.97	14.41	20.57	25.37
550.0	2.27	7.18	18.22	14.69	20.31	25.08
600.0	2.26	7.17	17.54	15.01	20.08	24.79
650.0	2.26	7.16	16.95	15.35	19.86	24.57
700.0	2.26	7.15	16.39	15.68	19.71	24.32
750.0	2.26	7.14	15.89	16.02	19.62	24.04
800.0	2.27	7.14	15.45	16.36	19.58	23.68
850.0	2.28	7.14	15.03	16.67	19.49	23.27
900.0	2.30	7.14	14.63	16.95	19.43	22.86
950.0	2.32	7.14	14.26	17.22	19.39	22.40
1000.0	2.35	7.15	13.92	17.46	19.40	21.87
1050.0	2.38	7.15	13.61	17.66	19.45	21.32
1100.0	2.42	7.17	13.29	17.80	19.41	20.77
1150.0	2.46	7.18	13.02	17.89	19.36	20.19
1200.0	2.50	7.20	12.75	17.91	19.40	19.62
1250.0	2.55	7.21	12.48	17.82	19.35	19.04
1300.0	2.61	7.23	12.23	17.69	19.19	18.46
1350.0	2.66	7.25	11.97	17.53	19.11	17.93
1400.0	2.72	7.29	11.73	17.29	19.06	17.39
1450.0	2.79	7.32	11.50	16.95	18.92	16.87
1500.0	2.86	7.36	11.26	16.63	18.71	16.38
1550.0	2.94	7.39	11.03	16.27	18.47	15.90
1600.0	3.03	7.43	10.79	15.89	18.24	15.44
1700.0	3.20	7.54	10.33	15.06	17.77	14.51
1800.0	3.40	7.64	9.91	14.36	16.99	13.81
1900.0	3.62	7.76	9.49	13.68	16.24	13.20
2000.0	3.84	7.89	9.07	12.97	15.60	12.62
2100.0	4.09	8.04	8.68	12.36	14.88	12.01
2200.0	4.34	8.20	8.26	11.76	14.29	11.56
2300.0	4.60	8.36	7.85	11.23	13.50	11.13
2400.0	4.86	8.54	7.42	10.77	12.92	10.75
2500.0	5.11	8.73	6.99	10.36	12.46	10.37
2750.0	5.71	9.29	5.79	9.47	11.44	9.67
3000.0	6.18	9.98	4.47	8.98	11.02	9.30
3250.0	6.61	10.97	2.73	8.42	11.57	9.11
3500.0	7.16	12.43	0.56	7.75	14.09	9.16
3750.0	8.16	14.34	1.78	7.10	20.45	8.99
4000.0	9.89	16.06	3.53	6.39	18.29	8.27
4250.0	12.28	16.52	3.62	5.81	11.76	7.22
4500.0	15.10	16.22	2.80	5.40	8.53	6.27
4750.0	18.01	15.94	1.97	5.04	6.79	5.47
5000.0	20.48	15.84	1.40	4.75	5.80	4.92



REV. OR
DBTC-7-152X+

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 • Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site
The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: www.minicircuits.com



IF/RF MICROWAVE COMPONENTS


Page 3 of 3

Directional Coupler


Typical Performance Curves

DBTC-7-152X+


Insertion Loss




Insertion Loss vs. TEMPERATURE



Coupling Loss vs. TEMPERATURE



Directivity vs. TEMPERATURE




Directional Coupler


Typical Performance Curves

DBTC-7-152X+


Return Loss




Return Loss In vs. TEMPERATURE



Return Loss Out vs. TEMPERATURE




Return Loss Cpl vs. TEMPERATURE




Outline Dimensions

AT1667-1



PCB Land Pattern



Suggested Layout,
Tolerance to be within $\pm .002$

CASE #	A	B	C	D	E	F	G	H	J	K	L	WT. GRAMS
AT1667-1	.150 (3.81)	.150 (3.81)	.150 (3.81)	.050 (1.27)	.030 (0.76)	.025 (0.64)	.028 (0.71)	.050 (1.27)	.160 (4.06)	.030 (0.76)	-- --	.10

Dimensions are in inches (mm). Tolerances: 2 Pl. $\pm .01$; 3 Pl. $\pm .005$

Notes:

1. Open style, Ceramic base.
2. Termination finish: Silver Palladium or Gold Over Nickel based on stock availability.
3. Top-hat total thickness: .013 inches MAX.
4. Orientation Dot on Top Hat & Marking on the Substrate both refers to Pin #6 of the Unit.



P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site




The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: www.minicircuits.com

RF/IF MICROWAVE COMPONENTS

Tape & Reel Packaging TR-F15

DEVICE ORIENTATION IN T&R



Tape Width, mm	Device Cavity Pitch, mm	Reel Size, inches	Devices per Reel
12	8	7	20
			50
			100
			200
		13	500
			1000
			2000

Note: Please consult individual model data sheet to determine device per reel availability.

Mini-Circuits carrier tape materials provide protection from ESD (Electro-Static Discharge) during handling and transportation. Tapes are static dissipative and comply with industry standards EIA-481/EIA-541.

Go to: www.minicircuits.com/pages/pdfs/tape.pdf




Distribution Centers NORTH AMERICA 800-654-7949 • 417-335-5935 • Fax 417-335-5945 • EUROPE 44-1252-832600 • Fax 44-1252-837010

Mini-Circuits ISO 9001 & ISO 14001 Certified

INTERNET <http://www.minicircuits.com>

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661


THIRD ANGLE PROJECTION



REVISIONS

REV	ECN No.	DESCRIPTION	DATE	DR	AUTH
OR	M90454	NEW RELEASE	01/16/04	AV	WP
A	M93049	AT1030 WAS AT1029	07/02/04	MMG	WP
B	M102713	ADDED "...WITH SMOBC"	01/17/06	MMG	IL


SUGGESTED MOUNTING CONFIGURATION FOR AT1030 CASE STYLE, "na" PIN CONNECTION



- NOTES: 1. TRACE WIDTH IS SHOWN FOR ROGERS RO4350B WITH DIELECTRIC THICKNESS $0.020'' \pm 0.0015''$; COPPER: 1/2 OZ. EACH SIDE. FOR OTHER MATERIALS TRACE WIDTH MAY NEED TO BE MODIFIED.
2. BOTTOM SIDE OF THE PCB IS CONTINUOUS GROUND PLANE.



DENOTES PCB COPPER LAYOUT WITH SMOBC
(SOLDER MASK OVER BARE COPPER)



DENOTES COPPER LAND PATTERN FREE OF SOLDER MASK

UNLESS OTHERWISE SPECIFIED

INITIALS

DATE

DIMENSIONS ARE IN INCHES

TOLERANCES ON:

2 PL DECIMALS $\pm$ 3 PL DECIMALS $\pm$.005ANGLES $\pm$ FRACTIONS $\pm$

DRAWN

AV

01/08/04

CHECKED

IL

01/16/04

APPROVED

WP

01/16/04



Mini-Circuits®

13 Neptune Avenue
Brooklyn NY 11235

PL, na, AT1030, DBTC, TB-278

SIZE

A

CODE IDENT

15542

DRAWING NO:

98-PL-150

REV:

B

FILE:


98PL150

SCALE:

10:1

SHEET:


1 OF 1




THIS DOCUMENT AND ITS CONTENTS ARE THE PROPERTY OF MINI-CIRCUITS. EXCEPT FOR USE EXPRESSLY GRANTED, IN WRITING, TO ITS VENDORS, VENDEE AND THE UNITED STATES GOVERNMENT, MINI-CIRCUITS RESERVES ALL PROPRIETARY DESIGN, USE, MANUFACTURING AND REPRODUCTION RIGHTS THERETO. THESE CONTENTS SHALL NOT BE USED, DUPLICATED OR DISCLOSED TO ANY OUTSIDE PARTY, IN WHOLE OR IN PART, WITHOUT WRITTEN PERMISSION OF MINI-CIRCUITS.

ASHEETA1.DWG REV:A DATE:01/12/95

Evaluation Board and Circuit



TB-278



Schematic Diagram

Notes:

1. 50 Ohm SMA Female connectors.
2. PCB Material: Rogers R04350B or its equivalent, Dielectric Constant=3.5, Thickness=.020"

 **Mini-Circuits®**



All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

Specification	Test/Inspection Condition	Reference/Spec
Operating Temperature	-40° to 85°C Ambient Environment	Individual Model Data Sheet
Storage Temperature	-55° to 100° C Ambient Environment	Individual Model Data Sheet
Humidity	90 to 95% RH, 240 hours, 50°C	MIL-STD-202, Method 103, Condition A, Except 50°C and end-point electrical test done within 12 hours
Thermal Shock	-55° to 100°C, 100 cycles	MIL-STD-202, Method 107, Condition A-3, except +100°C
Solder Reflow Heat	Sn-Pb Eutetic Process: 225°C peak Pb-Free Process 245° - 250°C peak	J-STD-020, Table 4-1, 4-2 and 5-2, Figure 5-1
Solderability	10X Magnification	J-STD-002, 95% Coverage
Vibration (High Frequency)	20g peak, 10-2000 Hz, 12 times in each of three perpendicular directions (total 36)	MIL-STD-202, Method 204, Condition D
Mechanical Shock	50g, 11 ms, 1/2-sine, 18 shocks: 3 each direction, each of 3 axes	MIL-STD-202, Method 213, Condition A
Marking Resistance to Solvents	Isopropyl alcohol + mineral spirits at 25°C; terpene defluxer at 25°C; distilled water + proylene glycol monomethyl ether + monoethanolamine at 63°C to 70°C	MIL-STD-202, Method 215