

High Pass Filter

50Ω 5000 to 11000 MHz

NON-CATALOG

HFCN-4600D+


CASE STYLE: FV1206-1

PRICE: Contact Sales Dept.

Maximum Ratings

Operating Temperature -55°C to 100°C

Storage Temperature -55°C to 100°C

RF Power Input* 7W max. at 25°C

Max. DC Voltage at pins 1&3 25 VDC

*Passband rating, derate linearly to 3W at 100°C ambient.
Permanent damage may occur if any of these limits are exceeded.


Pin Connections

RF IN 1


RF OUT 3

GROUND 2,4,5,6

Outline Drawing



PCB Land Pattern



Suggested Layout,
Tolerance to be within ±.002

Outline Dimensions (inch)

A	B	C	D	E	F
.126	.063	.035	.024	.022	.011
3.20	1.60	0.89	0.61	0.56	0.28
G	H	J	K	L	M
.039	.024	.042	.123	.034	.017
0.99	0.61	1.07	3.12	0.87	0.43

Demo Board MCL P/N: TB-285

Suggested PCB Layout (PL-158)


NOTE: 1. TRACE WIDTH IS SHOWN FOR ROGERS RO4350
WITH DIELECTRIC THICKNESS: .020 ± .0015;
COPPER: 1/2 OZ. EACH SIDE.
FOR OTHER MATERIALS TRACE WIDTH MAY NEED
TO BE MODIFIED.

2. BOTTOM SIDE OF THE PCB IS CONTINUOUS GROUND PLANE.

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661 The Design Engineers Search Engine Provides ACTUAL Data Instantly at minicircuits.com

Features

- Low cost
- Small size
- 5 sections
- Temperature stable
- Excellent power handling, 7W
- Hermetically sealed
- LTCC construction
- Protected by US Patent 7,760,485

Applications


- Sub-harmonic rejection and DC blocking
- Transmitters / receivers

Electrical Specifications¹ at 25°C


STOPBAND (MHz)	fco, MHz Nom.	PASSBAND (MHz)	VSWR Typ. Frequency (MHz)	POWER INPUT (W)	NO. OF SECTIONS
(Loss > 30dB) Typ.	(Loss > 20dB) Min.	(Loss < 1.5dB) Typ.	(Loss < 2dB) Max.	Stopband 1.5:1	Max.
3700	3800	4600	5200-10500 5000-11000	20:1 4720-11000	7

1. DC Resistance to ground is 100 Mohms min.

typical frequency response




electrical schematic




Typical Performance Data at 25°C

Frequency (MHz)	Insertion Loss (dB)	VSWR (:1)
50	62.56	1737.18
1500	35.68	217.15
2470	47.59	86.86
3700	33.77	38.61
3800	37.24	34.07
4150	18.50	19.32
4380	8.52	7.90
4500	4.77	3.97
4600	2.78	2.25
4720	1.66	1.31
5000	1.27	1.39
5200	1.25	1.54
8000	1.11	1.73
10500	0.66	1.12
11000	0.85	1.45
14000	5.72	4.32
15000	3.27	2.75

HFCN-4600D+ INSERTION LOSS



HFCN-4600D+ VSWR


Mini-Circuits
ISO 9001 ISO 14001 AS 9100 CERTIFIED

The Design Engineers Search Engine Provides ACTUAL Data Instantly at minicircuits.com

IF/RF MICROWAVE COMPONENTS

Notes: 1. Performance and quality attributes and conditions not expressly stated in this specification sheet are intended to be excluded and do not form a part of this specification sheet. 2. Electrical specifications and performance data contained herein are based on Mini-Circuit's applicable established test performance criteria and measurement instructions. 3. The parts covered by this specification sheet are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp.

REV. B
M132298
EDR-8120/1
HFCN-4600D+
RAV/CP/AM
110708
page 1

Ceramic High Pass Filter

HFCN-4600D+

Typical Performance Data

FREQ. (MHz)	INSERTION LOSS (dB)			INPUT RETURN LOSS (dB)			OUTPUT RETURNLOSS (dB)		
	@ -55° C	@ +25° C	@ +100° C	@ -55° C	@ +25° C	@ +100° C	@ -55° C	@ +25° C	@ +100° C
50	62.08	63.88	61.65	0.02	0.04	0.02	0.01	0.00	0.00
200	50.18	49.92	49.76	0.01	0.00	0.01	0.00	0.01	0.03
700	39.58	39.60	39.64	0.02	0.01	0.03	0.02	0.02	0.05
1500	35.54	35.62	35.70	0.02	0.08	0.12	0.04	0.11	0.16
2170	38.75	39.18	39.60	0.10	0.18	0.21	0.09	0.14	0.19
2470	46.44	47.81	49.37	0.07	0.16	0.20	0.15	0.22	0.29
3000	37.29	36.90	36.49	0.17	0.27	0.31	0.20	0.32	0.42
3600	31.20	31.53	31.97	0.27	0.42	0.50	0.33	0.47	0.61
3650	31.74	32.20	32.79	0.31	0.43	0.52	0.33	0.48	0.62
3700	32.31	32.95	33.83	0.32	0.46	0.55	0.29	0.45	0.59
4000	29.89	27.61	25.66	0.44	0.62	0.77	0.45	0.63	0.81
4150	19.96	18.52	17.27	0.60	0.85	1.07	0.66	0.87	1.10
4380	9.26	8.47	7.76	1.62	2.18	2.76	1.63	2.10	2.63
4500	5.17	4.71	4.33	3.50	4.47	5.53	3.37	4.17	5.11
4600	2.87	2.72	2.61	6.72	8.31	10.04	6.30	7.51	8.86
4720	1.53	1.61	1.70	14.07	17.49	21.63	12.18	13.74	15.18
4750	1.34	1.46	1.59	17.01	21.62	28.49	13.94	15.30	16.43
4770	1.27	1.41	1.54	19.64	25.86	40.50	15.16	16.23	16.99
4800	1.18	1.33	1.49	25.35	42.51	30.84	16.72	17.16	17.26
4880	1.04	1.24	1.42	26.06	21.98	19.78	17.71	16.85	16.24
5000	0.99	1.18	1.36	16.49	15.71	15.33	15.06	14.56	14.34
5500	0.89	1.07	1.22	13.90	14.30	15.10	13.75	14.20	15.03
5750	0.77	0.95	1.10	16.09	17.25	18.49	16.32	17.11	18.20
6000	0.70	0.87	1.04	19.37	21.79	23.96	20.14	21.65	22.80
6500	0.58	0.79	0.98	25.48	23.59	23.65	30.75	27.78	27.88
7000	0.66	0.89	1.11	16.01	15.75	15.40	17.13	17.22	17.88
7500	0.79	1.01	1.26	12.46	12.80	12.60	13.20	13.83	14.26
8000	0.92	1.08	1.32	10.73	11.77	11.96	11.34	12.55	12.93
8500	0.91	1.08	1.27	10.88	11.86	12.66	11.51	12.44	12.82
9000	0.71	0.95	1.13	12.70	12.82	14.02	13.45	13.23	13.61
9500	0.52	0.79	1.00	15.51	15.13	15.50	16.26	15.31	14.84
10000	0.38	0.64	0.89	19.40	19.64	18.02	19.29	19.86	17.57
11000	0.44	0.78	1.09	15.90	15.55	15.70	15.38	15.30	14.57
11500	0.80	1.19	1.50	10.98	10.70	10.90	10.33	10.62	10.99
12000	1.31	1.80	2.15	8.54	8.04	8.08	8.03	7.96	8.49
12250	1.53	2.11	2.54	7.93	7.30	7.12	7.58	7.14	7.36
12500	1.79	2.47	3.07	7.34	7.08	6.79	6.97	6.55	6.52
13000	3.71	4.75	5.33	9.24	7.99	5.79	5.38	5.12	4.84
14000	6.76	5.76	5.07	3.11	4.40	5.24	9.89	8.29	8.26
15000	3.28	3.55	3.30	5.70	6.02	7.74	5.95	5.75	6.95

REV. X1

HFCN-4600D+

090118

Page 1 of 1



IF/RF MICROWAVE COMPONENTS • ISO 9001 ISO 14001 AS9100 CERTIFIED RoHS compliant

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661




The Design Engineers Search Engine finds the model you need, Instantly • For detailed performance specs & shopping online see




Typical Performance Curves


INSERTION LOSS vs. TEMPERATURE




INPUT RETURN LOSS vs. TEMPERATURE



OUTPUT RETURN LOSS vs. TEMPERATURE



Outline Dimensions



PCB Land Pattern



Suggested Layout,
Tolerance to be within $\pm .002$

CASE #	A	B	C	D	E	F	G	H	J	K	L	M	N	P	WT. GRAM
FV1206-1	.126 (3.20)	.063 (1.60)	.035 (0.89)	.024 (0.61)	.022 (0.56)	.011 (0.28)	.039 (0.99)	.024 (0.61)	.042 (1.07)	.123 (3.12)	--	--	--	--	.020

Dimensions are in inches (mm). Tolerances: 2 PL. $\pm .01$; 3 PL. $\pm .005$

Notes:

- Open style, ceramic base.
- Termination finish: **as shown below or indicated on Data Sheet.**
 For RoHS Case Styles: Tin plate over Nickel plate. All models, (+) suffix.
 For RoHS-5 Case Styles: Tin-Lead plate. All models, no (+) suffix.



ISO 9001 ISO 14001 CERTIFIED

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site



The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: www.minicircuits.com

RF/IF MICROWAVE COMPONENTS

DEVICE ORIENTATION IN T&R




ILLUSTRATION 1



ILLUSTRATION 2



ILLUSTRATION 3

Applicable Case Styles

FV1206-1
FV1206-3

Applicable Case Styles

FV1206-4
FV1206-5
FV1206-6
FV1206-7
FV1206-9

Applicable Case Styles

FV1206-11
FV1206-12
GE0805C-18
NL1008C-6
NL1008C-7
NL1008C-9
NL1008C-10
NL1008C-12

Tape Width, mm	Device Cavity Pitch, mm	Reel Size, inches	Devices per Reel	
8	4	7	Small quantity standards (see note)	20
				50
				100
				200
				500
				1000
			Standard	3000

Note: Please consult individual model data sheet to determine device per reel availability.

Mini-Circuits carrier tape materials provide protection from ESD (Electro-Static Discharge) during handling and transportation. Tapes are static dissipative and comply with industry standards EIA-481/EIA-541.

Go to: www.minicircuits.com/pages/pdfs/tape.pdf




Distribution Centers NORTH AMERICA 800-654-7949 • 417-335-5935 • Fax 417-335-5945 • **EUROPE** 44-1252-832600 • Fax 44-1252-837010
Mini-Circuits ISO 9001 & ISO 14001 Certified

INTERNET <http://www.minicircuits.com>

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661


THIRD ANGLE PROJECTION



REVISIONS

REV	ECN No.	DESCRIPTION	DATE	DR	AUTH
OR	M92199	NEW RELEASE	05/24/04	AV	ABD
A	M99247	ADD GROUND PTH	06/05	RZ	RZ
A	R60782	ADD GROUND PTH	06/05	RZ	RZ
B	M102713	ADDED "...WITH SMOBC"	01/12/06	GF	IL


SUGGESTED MOUNTING CONFIGURATION
FOR FV1206-1 CASE STYLE, "pr" PIN CONNECTION.



- NOTE: 1. TRACE WIDTH IS SHOWN FOR ROGERS RO4350B WITH DIELECTRIC THICKNESS .020" ± .0015". COPPER: 1/2 OZ. EACH SIDE. FOR OTHER MATERIALS TRACE WIDTH MAY NEED TO BE MODIFIED.
2. BOTTOM SIDE OF THE PCB IS CONTINUOUS GROUND PLANE.



DENOTES PCB COPPER LAYOUT WITH SMOBC (SOLDER MASK OVER BARE COPPER)



DENOTES COPPER LAND PATTERN FREE OF SOLDER MASK

UNLESS OTHERWISE SPECIFIED

INITIALS

DATE

DIMENSIONS ARE IN INCHES

TOLERANCES ON:

2 PL DECIMALS ±

3 PL DECIMALS ± .005

ANGLES ±

FRACTIONS ±

DRAWN

AV

05/03/04

CHECKED

IL

05/24/04

APPROVED

ABD

05/24/04

Mini-Circuits®

THIS DOCUMENT AND ITS CONTENTS ARE THE PROPERTY OF MINI-CIRCUITS. EXCEPT FOR USE EXPRESSLY GRANTED, IN WRITING, TO ITS VENDORS, VENDEE AND THE UNITED STATES GOVERNMENT, MINI-CIRCUITS RESERVES ALL PROPRIETARY DESIGN, USE, MANUFACTURING AND REPRODUCTION RIGHTS THERETO. THESE CONTENTS SHALL NOT BE USED, DUPLICATED OR DISCLOSED TO ANY OUTSIDE PARTY, IN WHOLE OR IN PART, WITHOUT WRITTEN PERMISSION OF MINI-CIRCUITS.

ASHEETA1.DWG REV:A DATE:01/12/95



Mini-Circuits®

13 Neptune Avenue
Brooklyn NY 11235

PL, pr, FV1206-1, HFCN, TB-285

SIZE

A

CODE IDENT

15542

DRAWING NO:

98-PL-158

REV:

B

FILE:

98PL158



SCALE:

12:1

SHEET:

1 OF 1

Evaluation Board and Circuit



Schematic Diagram

Notes:

1. SMA Female connectors.
2. PCB Material: Rogers R04350 or equivalent,
Dielectric Constant=3.5, Thickness=.020 inch.

 **Mini-Circuits®**



All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

Specification	Test/Inspection Condition	Reference/Spec
Operating Temperature	-55° to 100°C Ambient Environment	Individual Model Data Sheet
Storage Temperature	-55° to 100° C Ambient Environment	Individual Model Data Sheet
Humidity	90 to 95% RH, 240 hours, 50°C	MIL-STD-202, Method 103, Condition A, Except 50°C and end-point electrical test done within 12 hours
Solder Reflow Heat	Sn-Pb Eutetic Process: 225°C peak Pb-Free Process 245° - 250°C peak	J-STD-020, Table 4-1, 4-2 and 5-2, Figure 5-1
Solderability	10X Magnification	J-STD-002, Para 4.2.5, Test S, 95% Coverage
Vibration (High Frequency)	20g peak, 10-2000 Hz, 12 times in each of three perpendicular directions (total 36)	MIL-STD-202, Method 204, Condition D
Mechanical Shock	50g, 11 ms, 1/2-sine, 18 shocks: 3 each direction, each of 3 axes	MIL-STD-202, Method 213, Condition A