

Ceramic High Pass Filter

SMT

HFCN-ED14070/1

Important Note

This model has been designed, built and tested in our engineering department. Performance data represents model capability. At present it is a non-catalog model. On request, we can supply a final specification sheet, part number and price/delivery information.


Please click "Back", and then click "Contact Us" for Applications support.



CASE STYLE : FV1206

ELECTRICAL SPECIFICATIONS 50Ω @ +25°C							
Parameters		F#	Frequency (MHz)	Min.	Typ.	Max.	Units
Stop Band	Insertion Loss	DC-F1	DC-600	40	--	--	dB
		DC-F2	DC-780	20	--	--	dB
	Frequency cutoff	F3	1080	--	3	--	dB
	VSWR	DC-F2	DC-780	--	20	--	:1
Pass Band	Insertion Loss	F5-F7	1190-4240	--	--	1.3	dB
		F4-F8	1140-4600	--	--	2	dB
	VSWR	F5-F6	1190-3200	--	1.5	--	:1

MAXIMUM RATINGS	
Operating Temperature	-55°C to 100°C
Storage Temperature	-55°C to 100°C
RF Power Input	7W max.




Functional Schematic

PIN CONNECTIONS	
RF IN	1
RF OUT	3
GROUND	2,4

Typical Performance Data

FREQUENCY (MHz)	INSERTION LOSS (dB)			INPUT RETURN LOSS (dB)			OUTPUT RETURN LOSS (dB)		
	@ -55°C	@ +25°C	@ +100°C	@ -55°C	@ +25°C	@ +100°C	@ -55°C	@ +25°C	@ +100°C
10.0	91.61	94.10	94.25	0.01	0.00	0.00	0.01	0.01	0.02
30.0	82.60	79.69	81.75	0.01	0.00	0.01	0.01	0.01	0.02
50.0	76.21	75.55	79.51	0.01	0.01	0.01	0.01	0.02	0.02
70.0	73.60	73.42	74.22	0.00	0.01	0.01	0.01	0.01	0.02
100.0	71.85	70.30	71.15	0.00	0.01	0.02	0.01	0.02	0.03
120.0	69.48	68.25	69.64	0.00	0.01	0.03	0.00	0.02	0.03
210.0	66.44	65.28	66.03	0.01	0.04	0.06	0.00	0.03	0.07
310.0	64.65	64.41	64.94	0.04	0.08	0.11	0.01	0.05	0.09
500.0	63.11	66.25	61.85	0.11	0.18	0.23	0.04	0.11	0.17
600.0	48.76	49.17	48.17	0.18	0.26	0.32	0.09	0.17	0.24
620.0	46.42	46.68	45.93	0.19	0.28	0.33	0.10	0.19	0.24
660.0	41.97	42.03	41.51	0.23	0.32	0.38	0.13	0.22	0.28
700.0	37.69	37.65	37.25	0.26	0.36	0.43	0.16	0.26	0.33
740.0	33.63	33.49	33.15	0.31	0.42	0.49	0.20	0.31	0.38
780.0	29.63	29.42	29.11	0.36	0.48	0.56	0.25	0.37	0.45
800.0	27.63	27.42	27.11	0.38	0.51	0.61	0.28	0.41	0.50
850.0	22.71	22.48	22.19	0.48	0.63	0.74	0.38	0.54	0.65
910.0	16.86	16.62	16.36	0.70	0.89	1.04	0.63	0.82	0.98
960.0	12.09	11.84	11.59	1.10	1.38	1.59	1.07	1.35	1.57
1020.0	6.83	6.63	6.43	2.37	2.88	3.31	2.41	2.94	3.40
1080.0	3.01	3.02	3.00	5.87	6.82	7.67	6.04	7.06	8.06
1100.0	2.23	2.32	2.36	7.83	8.94	9.93	8.08	9.30	10.55
1120.0	1.67	1.82	1.91	10.25	11.49	12.56	10.65	12.05	13.54
1140.0	1.30	1.49	1.62	13.14	14.51	15.58	13.75	15.41	17.19
1150.0	1.17	1.37	1.51	14.76	16.20	17.22	15.55	17.36	19.31
1170.0	0.98	1.20	1.35	18.46	19.98	20.73	19.78	22.08	24.43
1190.0	0.86	1.08	1.23	22.76	24.24	24.29	25.36	28.74	31.08
1200.0	0.82	1.04	1.19	25.09	26.35	25.85	29.06	33.46	34.00
1380.0	0.50	0.70	0.83	42.70	37.00	31.95	41.68	34.10	29.97
1560.0	0.44	0.64	0.77	18.32	17.59	16.74	18.02	17.31	16.38
1740.0	0.48	0.67	0.81	13.98	13.70	13.44	13.81	13.53	13.22
1920.0	0.50	0.68	0.80	12.52	12.60	12.66	12.48	12.55	12.52
2100.0	0.47	0.65	0.75	12.48	12.77	13.07	12.64	12.88	13.12
2290.0	0.40	0.57	0.67	13.24	13.79	14.43	13.58	14.09	14.65
2470.0	0.31	0.48	0.60	14.95	15.71	16.73	15.41	16.16	17.28
2650.0	0.28	0.42	0.56	17.24	18.72	20.18	17.69	19.47	21.17
2830.0	0.19	0.37	0.59	23.50	24.04	29.02	24.17	25.77	30.25
3010.0	0.13	0.35	0.50	34.03	32.92	28.79	43.05	45.87	31.15
3200.0	0.13	0.37	0.53	24.43	23.14	21.33	23.75	23.05	21.40
3220.0	0.14	0.38	0.54	23.51	22.43	20.66	22.83	22.24	20.71
3320.0	0.16	0.41	0.60	20.18	19.22	18.16	19.80	19.12	18.21
3420.0	0.20	0.44	0.70	17.52	16.92	16.66	17.29	16.86	16.57
3520.0	0.26	0.50	0.79	15.23	14.97	14.59	15.03	14.93	14.33
3620.0	0.39	0.58	0.80	13.32	13.38	12.79	13.16	13.45	12.91
3730.0	0.42	0.66	0.87	11.76	12.02	11.55	11.89	12.11	11.75
3830.0	0.51	0.74	0.95	10.80	10.98	10.76	11.02	11.07	10.85
3930.0	0.63	0.85	1.11	9.78	10.07	9.70	10.19	10.10	10.01
4030.0	0.66	0.95	1.16	9.12	9.26	8.99	9.27	9.31	9.18
4130.0	0.75	1.06	1.28	8.49	8.61	8.43	8.62	8.64	8.54
4240.0	0.86	1.18	1.42	7.94	7.98	7.87	7.98	7.98	7.93
4250.0	0.87	1.20	1.42	7.88	7.92	7.81	7.92	7.93	7.88
4320.0	0.95	1.29	1.58	7.50	7.52	7.54	7.51	7.52	7.58
4390.0	1.04	1.38	1.64	7.09	7.16	7.02	7.17	7.18	7.16
4460.0	1.13	1.48	1.78	6.86	6.85	6.76	6.93	6.85	6.90
4530.0	1.20	1.56	1.85	6.66	6.57	6.51	6.60	6.53	6.56
4600.0	1.45	1.64	1.91	6.83	6.29	6.33	6.58	6.25	6.32
4760.0	1.56	1.87	2.22	5.73	5.75	6.21	5.66	5.68	5.96
4900.0	1.89	2.04	2.58	5.15	5.37	5.22	5.06	5.26	5.07
5180.0	1.99	2.36	2.70	4.38	4.78	4.63	4.38	4.62	4.57
5320.0	2.10	2.50	2.83	4.21	4.55	4.46	4.11	4.36	4.40
5600.0	2.39	2.77	3.07	3.79	4.19	4.25	3.65	3.99	4.08
5740.0	2.46	2.86	3.13	3.64	4.04	4.11	3.50	3.85	3.97
6020.0	2.61	2.97	3.24	3.47	3.92	4.00	3.27	3.68	3.80
6160.0	2.70	3.05	3.34	3.40	3.80	3.95	3.20	3.60	3.77
6450.0	2.81	3.14	3.37	3.24	3.70	3.89	2.99	3.52	3.67
6590.0	2.92	3.18	3.42	3.29	3.68	3.79	3.06	3.53	3.71
6870.0	3.04	3.29	3.45	3.15	3.57	3.93	2.94	3.49	3.71
7010.0	3.11	3.34	3.51	2.96	3.49	3.79	2.81	3.47	3.67
7290.0	3.26	3.54	3.62	2.77	3.30	3.61	2.80	3.33	3.70
7430.0	3.46	3.70	3.83	2.67	3.21	3.50	2.70	3.29	3.79
7710.0	3.88	4.15	4.36	2.50	2.97	3.30	2.58	3.01	3.40
7850.0	4.28	4.62	5.04	2.24	2.74	3.04	2.33	2.78	3.18
8000.0	4.99	5.68	6.49	2.19	2.66	3.25	2.02	2.41	2.76

Typical Performance Curves



Outline Dimensions



PCB Land Pattern



Suggested Layout,
Tolerance to be within $\pm .002$

CASE #	A	B	C	D	E	F	G	H	J	K	L	M	N	P	WT. GRAM
FV1206	.126 (3.20)	.063 (1.60)	.037 (0.94)	.020 (0.51)	.032 (0.81)	.009 (0.23)	.169 (4.29)	.087 (2.21)	.024 (0.61)	.122 (3.10)	.024 (0.61)	.087 (2.21)	.012 (0.30)	.071 (1.80)	.020

Dimensions are in inches (mm). Tolerances: 2 Pl. $\pm .01$; 3 Pl. $\pm .005$

Notes:

- Open style, ceramic base.
- Termination finish: **as shown below or indicated on Data Sheet.**
For RoHS Case Styles: Tin plate over Nickel plate. All models, (+) suffix.
For RoHS-5 Case Styles: Tin-Lead plate. All models, no (+) suffix.



P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site



The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: www.minicircuits.com

RF/IF MICROWAVE COMPONENTS

Tape & Reel Packaging TR-F71



ILLUSTRATION 1

Tape Width, mm	Device Cavity Pitch, mm	Reel Size, inches	Devices per Reel	
8	4	7	Small quantity standards (see note)	20
				50
				100
				200
				500
				1000
			Standard	3000

Note: Please Consult individual model data sheet to determine device per reel availability.

Mini-Circuits carrier tape materials provide protection from ESD (Electro-Static Discharge) during handling and transportation. Tapes are static dissipative and comply with industry standards EIA-481/EIA-541.

Go to: www.minicircuits.com/pages/pdfs/tape.pdf



P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site



The Design Engineers Search Engine Provides ACTUAL Data Instantly From Mini-Circuits At: www.minicircuits.com

RF/IF MICROWAVE COMPONENTS

THIRD ANGLE PROJECTION



REVISIONS

REV	ECN No.	DESCRIPTION	DATE	DR	AUTH
OR	M88634	NEW RELEASE	08/28/03	GF	ABD
A	M102713	ADDED "...WITH SMOBC"	01/17/06	MMG	IL

SUGGESTED MOUNTING CONFIGURATION
FOR FV1206 CASE STYLE, "nx" PIN CONNECTION



NOTES: 1. COPLANAR WAVEGUIDE PARAMETERS ARE SHOWN FOR ROGERS R04350B WITH THICKNESS .020" $\pm$.0015".
 COPPER: 1/2 OZ. EACH SIDE.
 FOR OTHER MATERIALS TRACE WIDTH & GAP MAY NEED TO BE MODIFIED.

2. BOTTOM SIDE OF THE PCB IS CONTINUOUS GROUND PLANE.



DENOTES PCB COPPER LAYOUT WITH SMOBC
 (SOLDER MASK OVER BARE COPPER)



DENOTES COPPER LAND PATTERN FREE OF SOLDER MASK

UNLESS OTHERWISE SPECIFIED

INITIALS

DATE

DIMENSIONS ARE IN INCHES

TOLERANCES ON:

2 PL DECIMALS $\pm$ 3 PL DECIMALS $\pm$.005ANGLES $\pm$ FRACTIONS $\pm$

DRAWN

GF

08/27/03

CHECKED

AV

08/28/03

APPROVED

ABD

08/28/03



Mini-Circuits®

13 Neptune Avenue
 Brooklyn NY 11235

PL, nx, FV1206, LFCN/HFCN, TB-270

SIZE

A

CODE IDENT

15542

DRAWING NO:

98-PL-137

REV:

A

FILE:

98PL137

SCALE:

10:1

SHEET:


1 OF 1

Mini-Circuits®

THIS DOCUMENT AND ITS CONTENTS ARE THE PROPERTY OF MINI-CIRCUITS. EXCEPT FOR USE EXPRESSLY GRANTED, IN WRITING, TO ITS VENDORS, VENDEE AND THE UNITED STATES GOVERNMENT, MINI-CIRCUITS RESERVES ALL PROPRIETARY DESIGN, USE, MANUFACTURING AND REPRODUCTION RIGHTS THERETO. THESE CONTENTS SHALL NOT BE USED, DUPLICATED OR DISCLOSED TO ANY OUTSIDE PARTY, IN WHOLE OR IN PART, WITHOUT WRITTEN PERMISSION OF MINI-CIRCUITS.

ASHEETA1.DWG REV:A DATE:01/12/95

Evaluation Board and Circuit



Schematic Diagram

Notes:

1. SMA Female connectors.
2. PCB Material: ROGERS RO4350 or equivalent,
Dielectric Constant=3.5, Thickness=.020 inch.

 **Mini-Circuits®**