MMIC SURFACE MOUNT

Power Splitter/Combiner EP2RCW+

2 Way-0° 50Ω DC to 8 GHz

THE BIG DEAL

- Ultra-Wide Bandwidth, DC to 8 GHz
- High Isolation, 23 dB Typ. at 0.7 to 7.5 GHz
- Excellent Amplitude Unbalance, 0.01 dB Typ. to 8 GHz
- Good Phase Unbalance, 0.9 Deg. Typ. at 0.7 to 7.5 GHz
- Small Size, 5x5 mm
- Aqueous Washable
- Protected by US Patent US11189902B1



Generic photo used for illustration purposes only

CASE STYLE: DG1677-2

+RoHS Compliant
The +Suffix identifies RoHS Compliance. See our website for RoHS Compliance methodologies and qualifications

APPLICATIONS

- WIMAX
- ISM
- Instrumentation
- Radar
- WLAN
- Satellite Communications
- LTE

PRODUCT OVERVIEW

Mini-Circuits' EP2RCW+ is a MMIC 2-way 0° splitter/combiner designed for wideband operation from DC to 8.0 GHz supporting many applications requiring high performance across a wide frequency range including alll the LTE bands through WiMax and WiFi, as well as instrumentation and more. This models provides excellent power handling up to 0.6 W (as a splitter/combiner) with low insertion loss, good isolation, and low phase and amplitude unbalance in a tiny 5x5 mm QFN package. Manufactured using GaAs IPD technology, the EP2RCW+ not only provides a repeatable performance, but also a high level of ESD protection.

KEY FEATURES

Feature	Advantages
Wideband, DC to 8.0 GHz	One power splitter can be used in all the LTE bands through WiMax and WiFi, saving component count. Also ideal for wideband applications such as military and instrumentation.
High Isolation, 23 dB Typ. at 0.7 to 7.5 GHz Excellent Power Handling, • 0.6 W as a Splitter/Combiner	In power combiner applications, half the power is dissipated internally. EP2RCW+ is designed to handle 0.6 W internal dissipation as a combiner allowing reliable operation without excessive temperature rise.
Excellent Amplitude Unbalance, 0.01 dB Typ. Good Phase Unbalance, 0.9 Deg Typ. at 0.7 to 7.5 GHz	Ideal for Applications such as MIMO & phased array radars.
Tiny Size, 5x5 mm QFN Package	Tiny footprint saves space in dense layouts while providing low inductance, repeatable transitions, and excellent thermal contact to the PCB.

REV. B
ECO-012024
EP2RCW+
MCL NY
250904

MMIC SURFACE MOUNT

Power Splitter/Combiner EP2RCW+

2 Way-0° 50Ω DC to 8 GHz

ELECTRICAL SPECIFICATIONS[1] AT +25°C

Parameter		Frequency (GHz)	Min.	Typ.	Max.	Unit
Frequency Range			DC		8.0	GHz
Insertion Loss[2], Above 3.0 dB		DC-0.4 0.4-0.7 0.7-7.5 7.5-8.0		5.5 5.5 4.8 4.3	5.8 5.9 6.1 4.9	dB
Isolation		DC-0.4 0.4-0.7 0.7-7.5 7.5-8.0	13 15 17 17	16.7 19.5 23.0 22.0		dB
Phase Unbalance		DC-0.4 0.4-0.7 0.7-7.5 7.5-8.0		0.04 0.2 0.9 1.7	2 2 9 9	Degree
Amplitude Unbalance		DC-0.4 0.4-0.7 0.7-7.5 7.5-8.0		0.01 0.01 0.02 0.01	0.3 0.3 0.4 0.3	dB
VSWR (Port S)		DC-0.4 0.4-0.7 0.7-7.5 7.5-8.0		1.1 1.1 1.5 1.3		:1
VSWR (Port 1-2)		DC-0.4 0.4-0.7 0.7-7.5 7.5-8.0		1.6 1.8 1.7 1.1		:1
Power Handling	As a Splitter	DC-8			0.6	W
	As a Combiner[3]	DC-8			0.6	

1. Tested on Mini-Circuits Test Board TB-EP2RCW+.
2. De-embedded from Test Board Loss.
3. As a combiner of non-coherent signals, max. power per port is 0.3 Watts.

ABSOLUTE MAXIMUM RATINGS

Parameter	Ratings
Operating Temperature	-55°C to +105°C
Storage Temperature	-65°C to +150°C

Permanent damage may occur if any of these limits are exceeded.

PAD CONNECTIONS

Function	Pad Number
RF IN	21
RF OUT 1	10
RF OUT 2	31
GROUND	9,11,20,22,30,32 & Paddle
NOT USED GROUND EXTERNALLY	1-8, 12-19, 23-29

PRODUCT MARKING



Marking may contain other features or characters for internal lot control.

SIMPLIFIED ELECTRICAL SCHEMATIC



Power Splitter/Combiner EP2RCW+

2 Way-0° 50Ω DC to 8 GHz

ADDITIONAL DETAILED TECHNICAL INFORMATION IS AVAILABLE ON OUR DASHBOARD. TO ACCESS CLICK HERE

Performance Data	Data Table Swept Graphs S-Parameter (S3P Files) Data Set (.zip file)
Case Style	DG1677-2 Plastic package, exposed paddle; Lead Finish: Matte Tin
Tape & Reel **Standard Quantities Available on Reel**	F68 7" Reels with 20, 50, 100, 200, 500 & 1000 devices 13" Reels with 2000, 3000 & 4000 devices
Suggested Layout for PCB Design	PL-647
Evaluation Board	TB-EP2RCW
Environmental Ratings	ENV08T1

ESD RATING

Human Body Model (HBM): Class 2 (Pass 2000 V) in accordance with ANSI/ESD STM 5.1 - 2001

MSL TEST FLOW CHART



NOTES

A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the standard terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/terms/viewterm.html

2 Way-0° Power Splitter/Combiner EP2RCW+

Typical Performance Data

TEST CONDITIONS: Input Power = -10dBm @Temperature = +25°C

FREQ. (MHz)	TOTAL LOSS[1] (dB) S-1	TOTAL LOSS[1] (dB) S-2	AMP. UNBAL. (dB)	PHASE UNBAL. (deg.)	ISOLATION (dB) 2-1	VSWR (:1) S	VSWR (:1) 1	VSWR (:1) 2
100	8.44	8.45	0.00	0.01	16.41	1.11	1.57	1.57
200	8.46	8.46	0.00	0.04	16.85	1.10	1.61	1.61
300	8.47	8.47	0.00	0.06	17.49	1.10	1.66	1.66
400	8.48	8.48	0.00	0.11	18.23	1.10	1.71	1.71
500	8.49	8.49	0.00	0.13	19.05	1.10	1.76	1.75
600	8.49	8.50	0.00	0.16	19.90	1.09	1.79	1.79
700	8.49	8.50	0.00	0.20	20.77	1.10	1.83	1.83
800	8.49	8.50	0.00	0.24	21.63	1.10	1.86	1.86
900	8.49	8.50	0.00	0.26	22.48	1.11	1.88	1.89
1000	8.49	8.49	0.01	0.30	23.27	1.13	1.91	1.92
1200	8.48	8.49	0.01	0.36	24.56	1.20	1.95	1.97
1400	8.47	8.49	0.02	0.40	25.27	1.29	1.99	2.02
1600	8.47	8.50	0.02	0.44	25.40	1.40	2.03	2.06
1800	8.48	8.51	0.03	0.48	25.22	1.52	2.06	2.10
2000	8.49	8.52	0.03	0.52	25.02	1.62	2.08	2.12
2200	8.48	8.51	0.03	0.55	24.93	1.70	2.08	2.13
2400	8.43	8.47	0.03	0.58	24.94	1.73	2.07	2.12
2600	8.36	8.39	0.03	0.59	24.91	1.72	2.04	2.09
2800	8.26	8.29	0.03	0.62	24.66	1.69	1.99	2.04
3000	8.15	8.17	0.03	0.65	24.05	1.65	1.95	1.99
3200	8.05	8.07	0.02	0.68	23.16	1.63	1.89	1.93
3400	7.98	7.99	0.01	0.70	22.22	1.65	1.84	1.87
3600	7.92	7.93	0.00	0.75	21.40	1.69	1.80	1.82
3800	7.87	7.87	0.00	0.80	20.87	1.73	1.75	1.76
4000	7.81	7.80	0.01	0.86	20.67	1.74	1.71	1.71
4200	7.72	7.71	0.01	0.91	20.84	1.70	1.67	1.66
4400	7.61	7.60	0.01	0.96	21.34	1.62	1.63	1.61
4600	7.50	7.48	0.02	1.00	22.07	1.53	1.60	1.57
4800	7.40	7.38	0.02	1.05	22.80	1.46	1.58	1.54
5000	7.34	7.32	0.03	1.12	23.16	1.46	1.57	1.51
5200	7.33	7.30	0.03	1.19	22.96	1.56	1.56	1.49
5400	7.35	7.32	0.03	1.30	22.40	1.69	1.56	1.47
5600	7.37	7.34	0.03	1.42	21.83	1.82	1.54	1.45
5800	7.37	7.35	0.03	1.55	21.48	1.88	1.52	1.42
6000	7.32	7.30	0.02	1.68	21.45	1.86	1.48	1.38
6200	7.23	7.22	0.01	1.79	21.72	1.75	1.42	1.33
6400	7.11	7.11	0.00	1.88	22.19	1.57	1.35	1.28
6600	7.00	7.01	0.01	1.92	22.66	1.37	1.27	1.23
6800	6.95	6.97	0.02	1.93	22.73	1.22	1.20	1.19
7000	6.96	6.98	0.02	1.94	22.31	1.20	1.15	1.15
7200	7.03	7.05	0.02	1.93	21.81	1.28	1.11	1.14
7400	7.12	7.13	0.01	1.93	21.62	1.33	1.10	1.13
7600	7.21	7.22	0.01	1.95	21.93	1.30	1.09	1.14
7800	7.32	7.32	0.01	1.98	22.48	1.22	1.07	1.14
8000	7.48	7.48	0.00	2.00	22.43	1.22	1.05	1.13
8200	7.75	7.75	0.00	2.02	21.20	1.40	1.05	1.11
8400	8.13	8.12	0.00	2.06	19.74	1.63	1.07	1.13
8600	8.52	8.51	0.01	2.11	18.98	1.76	1.10	1.17
8800	8.87	8.85	0.02	2.19	19.46	1.66	1.11	1.20
9000	9.32	9.29	0.03	2.30	21.36	1.32	1.07	1.17
9200	10.55	10.51	0.04	2.41	20.35	1.24	1.12	1.15
9400	13.42	13.37	0.04	2.54	16.06	1.92	1.31	1.35
9600	17.68	17.64	0.04	2.65	13.92	2.79	1.50	1.62
9800	22.46	22.43	0.03	2.72	13.17	3.77	1.65	1.84
10000	27.27	27.24	0.03	2.74	12.95	5.03	1.77	2.02

[1] Total Loss = Insertion Loss + 3dB Splitter Loss

2 Way-0° Power Splitter/Combiner EP2RCW+

Typical Performance Data

TEST CONDITIONS: Input Power = -10dBm @Temperature = -55°C

FREQ. (MHz)	TOTAL LOSS[1] (dB) S-1	TOTAL LOSS[1] (dB) S-2	AMP. UNBAL. (dB)	PHASE UNBAL. (deg.)	ISOLATION (dB) 2-1	VSWR (:1) S	VSWR (:1) 1	VSWR (:1) 2
100	8.39	8.39	0.00	0.02	16.31	1.12	1.57	1.56
200	8.40	8.40	0.00	0.05	16.78	1.11	1.62	1.61
300	8.41	8.41	0.00	0.07	17.42	1.10	1.67	1.67
400	8.41	8.41	0.00	0.11	18.17	1.11	1.72	1.72
500	8.41	8.41	0.00	0.14	18.99	1.11	1.77	1.76
600	8.41	8.41	0.00	0.17	19.85	1.11	1.80	1.80
700	8.40	8.40	0.00	0.21	20.73	1.11	1.84	1.84
800	8.39	8.39	0.00	0.25	21.59	1.12	1.87	1.88
900	8.38	8.39	0.00	0.28	22.45	1.13	1.90	1.90
1000	8.37	8.38	0.01	0.32	23.25	1.15	1.92	1.93
1200	8.35	8.36	0.01	0.40	24.57	1.21	1.96	1.98
1400	8.33	8.35	0.02	0.45	25.33	1.30	2.00	2.03
1600	8.32	8.35	0.03	0.48	25.45	1.42	2.04	2.08
1800	8.32	8.36	0.03	0.49	25.24	1.54	2.07	2.11
2000	8.33	8.36	0.03	0.53	25.01	1.64	2.09	2.14
2200	8.31	8.35	0.04	0.54	24.85	1.73	2.10	2.15
2400	8.27	8.31	0.03	0.57	24.84	1.77	2.09	2.14
2600	8.20	8.23	0.03	0.60	24.84	1.76	2.06	2.11
2800	8.09	8.12	0.03	0.62	24.60	1.73	2.02	2.07
3000	7.98	8.00	0.02	0.64	24.07	1.69	1.97	2.01
3200	7.87	7.88	0.02	0.69	23.19	1.67	1.92	1.96
3400	7.78	7.79	0.01	0.72	22.22	1.68	1.87	1.90
3600	7.71	7.71	0.00	0.78	21.35	1.72	1.82	1.84
3800	7.65	7.65	0.00	0.83	20.76	1.77	1.77	1.78
4000	7.58	7.57	0.01	0.89	20.51	1.78	1.72	1.72
4200	7.49	7.47	0.02	0.94	20.61	1.75	1.68	1.67
4400	7.37	7.35	0.02	1.00	21.06	1.68	1.64	1.62
4600	7.24	7.22	0.02	1.04	21.77	1.58	1.61	1.57
4800	7.13	7.11	0.03	1.09	22.53	1.51	1.59	1.54
5000	7.06	7.03	0.03	1.17	22.96	1.51	1.58	1.52
5200	7.04	7.00	0.03	1.25	22.85	1.59	1.57	1.50
5400	7.04	7.01	0.03	1.35	22.37	1.72	1.57	1.49
5600	7.06	7.03	0.03	1.47	21.78	1.85	1.56	1.47
5800	7.06	7.03	0.03	1.60	21.39	1.92	1.55	1.45
6000	7.01	6.98	0.02	1.75	21.28	1.92	1.52	1.41
6200	6.91	6.90	0.01	1.87	21.45	1.83	1.46	1.37
6400	6.78	6.78	0.00	1.97	21.86	1.66	1.39	1.31
6600	6.65	6.66	0.01	2.02	22.36	1.46	1.31	1.26
6800	6.56	6.58	0.02	2.04	22.61	1.29	1.23	1.20
7000	6.54	6.55	0.02	2.05	22.35	1.23	1.16	1.16
7200	6.58	6.59	0.02	2.03	21.84	1.28	1.11	1.13
7400	6.65	6.66	0.01	2.02	21.51	1.35	1.09	1.12
7600	6.72	6.73	0.01	2.04	21.63	1.36	1.08	1.12
7800	6.80	6.81	0.01	2.07	22.18	1.29	1.06	1.12
8000	6.91	6.91	0.00	2.09	22.49	1.24	1.04	1.11
8200	7.11	7.11	0.00	2.12	21.61	1.35	1.03	1.09
8400	7.43	7.43	0.00	2.17	19.97	1.60	1.05	1.09
8600	7.80	7.80	0.01	2.22	18.80	1.82	1.08	1.13
8800	8.12	8.10	0.02	2.30	18.78	1.83	1.08	1.17
9000	8.39	8.36	0.03	2.41	20.53	1.52	1.05	1.17
9200	9.12	9.09	0.04	2.54	21.94	1.12	1.07	1.10
9400	11.36	11.32	0.04	2.68	16.98	1.80	1.24	1.25
9600	15.32	15.29	0.04	2.80	13.93	2.85	1.43	1.53
9800	20.07	20.05	0.02	2.85	12.86	3.98	1.60	1.78
10000	24.95	24.93	0.01	2.83	12.56	5.38	1.73	1.99

[1] Total Loss = Insertion Loss + 3dB Splitter Loss

2 Way-0° Power Splitter/Combiner EP2RCW+

Typical Performance Data

TEST CONDITIONS: Input Power = -10dBm @Temperature = +105°C

FREQ. (MHz)	TOTAL LOSS[1] (dB) S-1	TOTAL LOSS[1] (dB) S-2	AMP. UNBAL. (dB)	PHASE UNBAL. (deg.)	ISOLATION (dB) 2-1	VSWR (:1) S	VSWR (:1) 1	VSWR (:1) 2
100	8.50	8.50	0.00	0.00	16.51	1.10	1.58	1.57
200	8.52	8.52	0.00	0.01	16.93	1.09	1.61	1.61
300	8.54	8.54	0.00	0.03	17.56	1.09	1.66	1.65
400	8.55	8.55	0.00	0.05	18.30	1.09	1.70	1.70
500	8.57	8.57	0.00	0.07	19.11	1.09	1.75	1.74
600	8.58	8.58	0.00	0.09	19.96	1.08	1.79	1.78
700	8.59	8.59	0.00	0.12	20.83	1.08	1.82	1.82
800	8.59	8.59	0.00	0.14	21.68	1.09	1.85	1.85
900	8.60	8.60	0.00	0.15	22.51	1.10	1.88	1.88
1000	8.60	8.60	0.00	0.18	23.29	1.12	1.90	1.91
1200	8.60	8.60	0.00	0.23	24.52	1.19	1.95	1.96
1400	8.61	8.62	0.01	0.27	25.18	1.29	2.00	2.01
1600	8.62	8.63	0.01	0.30	25.33	1.40	2.04	2.05
1800	8.64	8.65	0.01	0.35	25.24	1.52	2.07	2.09
2000	8.64	8.65	0.01	0.39	25.15	1.61	2.08	2.11
2200	8.62	8.64	0.02	0.43	25.15	1.67	2.08	2.11
2400	8.57	8.59	0.02	0.46	25.17	1.69	2.06	2.09
2600	8.50	8.51	0.02	0.48	25.05	1.67	2.03	2.06
2800	8.40	8.42	0.02	0.51	24.65	1.63	1.98	2.02
3000	8.31	8.32	0.01	0.54	23.90	1.60	1.93	1.96
3200	8.23	8.24	0.01	0.55	22.98	1.60	1.88	1.91
3400	8.17	8.17	0.01	0.56	22.09	1.64	1.82	1.85
3600	8.12	8.12	0.00	0.59	21.39	1.69	1.77	1.80
3800	8.07	8.06	0.00	0.61	20.98	1.72	1.72	1.74
4000	8.00	7.99	0.01	0.65	20.89	1.71	1.67	1.68
4200	7.91	7.90	0.01	0.68	21.14	1.65	1.62	1.63
4400	7.81	7.80	0.01	0.71	21.68	1.55	1.58	1.59
4600	7.71	7.69	0.01	0.74	22.37	1.45	1.55	1.55
4800	7.63	7.62	0.02	0.78	22.98	1.40	1.53	1.52
5000	7.59	7.58	0.02	0.82	23.19	1.43	1.51	1.49
5200	7.60	7.58	0.02	0.87	22.93	1.55	1.50	1.48
5400	7.63	7.60	0.03	0.94	22.44	1.69	1.49	1.45
5600	7.65	7.62	0.03	1.02	21.99	1.80	1.47	1.43
5800	7.64	7.62	0.03	1.11	21.75	1.84	1.45	1.39
6000	7.60	7.58	0.02	1.22	21.79	1.78	1.41	1.35
6200	7.52	7.50	0.02	1.30	22.07	1.65	1.37	1.31
6400	7.43	7.42	0.01	1.38	22.43	1.47	1.31	1.27
6600	7.35	7.35	0.00	1.43	22.71	1.30	1.26	1.23
6800	7.33	7.34	0.00	1.46	22.66	1.19	1.21	1.20
7000	7.37	7.38	0.01	1.49	22.33	1.20	1.17	1.17
7200	7.46	7.46	0.00	1.51	22.02	1.26	1.15	1.16
7400	7.56	7.57	0.00	1.53	21.99	1.27	1.14	1.16
7600	7.68	7.68	0.00	1.56	22.29	1.22	1.14	1.16
7800	7.83	7.83	0.00	1.60	22.53	1.18	1.13	1.16
8000	8.05	8.05	0.00	1.62	22.06	1.27	1.12	1.15
8200	8.38	8.38	0.00	1.64	20.84	1.46	1.12	1.15
8400	8.78	8.78	0.00	1.68	19.73	1.62	1.15	1.17
8600	9.20	9.20	0.01	1.72	19.37	1.65	1.17	1.21
8800	9.63	9.62	0.01	1.76	20.18	1.47	1.18	1.22
9000	10.35	10.34	0.02	1.84	21.46	1.17	1.15	1.18
9200	12.15	12.14	0.02	1.91	18.82	1.36	1.22	1.24
9400	15.60	15.58	0.01	1.99	15.47	2.01	1.43	1.46
9600	20.08	20.08	0.01	2.05	13.96	2.83	1.63	1.70
9800	24.84	24.84	0.01	2.11	13.42	3.79	1.78	1.88
10000	29.51	29.53	0.02	2.11	13.26	4.96	1.90	2.03

[1] Total Loss = Insertion Loss + 3dB Splitter Loss

2 Way-0° Power Splitter/Combiner EP2RCW+

Typical Performance Curves

Total Loss



Total Loss S-1 vs Temperature



Amplitude Unbalance vs Temperature



Phase Unbalance vs Temperature



Isolation 1-2 vs Temperature



VSWR



VSWR SUM vs Temperature



VSWR Out1 vs Temperature



DG1677-2

Outline Dimensions



PCB Land Pattern



Suggested Layout,
Tolerance to be within ±.002

CASE #	A	B	C MAX	C MIN	D	E	F	G	H	J
DG1677-2	.197 (5.00)	.197 (5.00)	.039 (1.00)	.031 (0.80)	.008 (0.20)	.142 (3.60)	.142 (3.60)	.009 (0.23)	- -	.016 (0.40)

CASE #	K	L	M	N	P	Q	R	S	WT. GRAM
DG1677-2	.020 (0.50)	.193 (4.90)	.193 (4.90)	.110 (2.79)	.012 (0.30)	.035 (0.89)	.110 (2.79)	.008 (0.20)	.05

Dimensions are in inches (mm). Tolerances: 2 Pl. ± .01; 3 Pl. ± .005

Notes:

1. Case material: Plastic.
4. Termination finish:

For RoHS Case Styles: Tin-Silver alloy plate over Nickel barrier transitioning to Matte-Tin. All models, (+) suffix. See Data sheet.

For RoHS-5 Case Styles: Tin-Lead plate. All models, no (+) suffix.

Tape & Reel Packaging TR-F68

DEVICE ORIENTATION IN T&R



Tape Width, mm	Device Cavity Pitch, mm	Reel Size, inches	Devices per Reel see note	
12	8	7	Small quantity standard	20
				50
				100
				200
				500
		7	Standard	1000
		13	Standard	2000
				3000
				4000

Mini-Circuits carrier tape materials provide protection from ESD (Electro-Static Discharge) during handling and transportation. Tapes are static dissipative and comply with industry standards EIA-481/EIA-541.

Go to: www.minicircuits.com/pages/pdfs/tape.pdf

Mini-Circuits®
INTERNET http://www.minicircuits.com
P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661
Distribution Centers NORTH AMERICA 800-654-7949 • 417-335-5935 • Fax 417-335-5945 • EUROPE 44-1252-832600 • Fax 44-1252-837010
Mini-Circuits ISO 9001 & ISO 14001 Certified

This document and its contents are the property of Mini-Circuits.

THIRD ANGLE PROJECTION

REVISIONS					
REV	ECN No.	DESCRIPTION	DATE	DR	AUTH
OR	M175739	NEW RELEASE	09/10/19	ITG	CM

SUGGESTED MOUNTING CONFIGURATION FOR DG1677-2 CASE STYLE



NOTES:

1. TRACE WIDTH & GAP ARE SHOWN FOR ROGERS RO4350B WITH DIELECTRIC THICKNESS .010"±.001"; COPPER: 1/2 OZ. EACH SIDE. FOR OTHER MATERIALS TRACE WIDTH & GAP MAY NEED TO BE MODIFIED.
2. BOTTOM SIDE OF THE PCB IS CONTINUOUS GROUND PLANE.

DENOTES PCB COPPER LAYOUT WITH SMOBC (SOLDER MASK OVER BARE COPPER).

DENOTES COPPER LAND PATTERN FREE OF SOLDER MASK.

UNLESS OTHERWISE SPECIFIED		INITIALS	DATE
DIMENSIONS ARE IN INCHES	DRAWN	ITG	08/28/19
TOLERANCES ON:	CHECKED	GF	09/03/19
2 PL DECIMALS ±	APPROVED	CM	09/10/19
3 PL DECIMALS ± .005			
ANGLES ±			
FRACTIONS ±			

Mini-Circuits®
THIS DOCUMENT AND ITS CONTENTS ARE THE PROPERTY OF MINI-CIRCUITS. EXCEPT FOR USE EXPRESSLY GRANTED, IN WRITING, TO ITS VENDORS, VENDEE AND THE UNITED STATES GOVERNMENT, MINI-CIRCUITS RESERVES ALL PROPRIETARY DESIGN, USE , MANUFACTURING AND REPRODUCTION RIGHTS THERETO. THESE CONTENTS SHALL NOT BE USED, DUPLICATED OR DISCLOSED TO ANY OUTSIDE PARTY, IN WHOLE OR IN PART, WITHOUT WRITTEN PERMISSION OF MINI-CIRCUITS.

ASHEETA1.DWG REV:A DATE:01/12/95

Mini-Circuits® 13 Neptune Avenue Brooklyn NY 11235

PL, DG1677-2, TB-EP2RCW+

SIZE	CODE IDENT	DRAWING NO:	REV:
A	15542	98-PL-647	OR

FILE:	SCALE:	SHEET:
98PL647	10:1	1 OF 1

Evaluation Board and Circuit





DETAIL "A"
LOCATION OF INTERCONNECTOR
AND UNITS COMPONENTS
(SCALE 5:1)



SCHEMATIC DIAGRAM
(SCALE 5:1)

Notes:

1. 50 Ohm SMA Female Connectors.
2. PCB Material: Roger RO4350B or equivalent,
   Dielectric constant=3.5, Thickness=0.010 inch

Mini-Circuits®

THIS DOCUMENT AND ITS CONTENTS ARE THE PROPERTY OF MINI-CIRCUITS.

Mini-Circuits

Environmental Specifications ENV08T1

All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

Specification	Test/Inspection Condition	Reference/Spec
Operating Temperature	-40° to 85° C or -45° to 85° C or -55° to 105° C or -40° to 105° C or -40° to 95° C Ambient Environment	Individual Model Data Sheet
Storage Temperature	-55° to 100° C or -65° to 150° Ambient Environment	Individual Model Data Sheet
HTOL	1000 hours at 125°C	MIL-STD-883, Method 1005, Condition B
Thermal Shock	-55° to 100°C, 100 cycles	MIL-STD-202, Method 107, Condition A-3, except +100°C
Mechanical Shock	1.5Kg, 0.5 ms, 5 shock pulses, Y1 direction only	MIL-STD-883, Method 2002, Condition B, except Y1 direction only
Vibration (Variable Frequency)	50g peak	MIL-STD-883, Method 2007, Condition B
Autoclave	15 psig, 100% RH, 121°C, 96 hours	JESD22-A102, Condition C
HAST	130°C, 85% RH, 96 hours	JESD22-A110
Solderability	10X Magnification	J-STD-002, Para 4.2.5, Test S, 95% Coverage
Solder Reflow Heat	Sn-Pb Eutetic Process: 240°C peak Pb-Free Process: 260°C peak	J-STD-020, Table 4-1, 4-2 and 5-2; Figure 5-1
Moisture Sensitivity: Level 1	Bake at 125°C for 24 hours Soak at 85°C/85% RH for 168 hours, Reflow 3 cycles at 260°C peak	J-STD-020

This document and its contents are the property of Mini-Circuits.

All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

Specification	Test/Inspection Condition	Reference/Spec
Marking Resistance to Solvents	Isopropyl alcohol + mineral spirits at 25°C; terpene defluxer at 25°C; distilled water + proylene glycol monomethyl ether + monoethanolamine at 63°C to 70°C	MIL-STD-202, Method 215

This document and its contents are the property of Mini-Circuits.