

# Ceramic High Pass Filter

## HFCW-7500+

50Ω      8200 to 21000 MHz

### The Big Deal

- Very good rejection, 44 dB typical
- Small size 0603 (0.063" X 0.032" X 0.024")
- Good Power handling, 2.5W
- Ceramic construction



Generic photo used for illustration purposes only  
CASE STYLE: JC0603C

### Product Overview

HFCW-7500+ is a high pass filter with passband from 8200 MHz to 21000 MHz supporting a variety of applications. This model provides good insertion loss over a wide band due to strategically constructed layout. Housed in a tiny 0603 ceramic form factor with wraparound terminations, the filter is ideal for dense PCB layouts with minimal performance variation due to parasitics.

### Key Features

| Feature                                     | Advantages  |
|---|---|
| Small size, 0603 (0.063" X 0.032" X 0.024") | Accommodates tight space requirements for dense PCB layouts.  |
| Wrap around termination                     | Provides excellent solderability and easy visual inspection capability.   |
| LTCC construction                           | Provides a rugged package that is well suited for tough environments including high humidity and high temperature extremes. |
| Ultra-wide pass band                        | This filter has a very wide passband from 8.2 GHz to 21 GHz.  |

#### Notes

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.  
B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.  
C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at [www.minicircuits.com/MCLStore/terms.jsp](http://www.minicircuits.com/MCLStore/terms.jsp)



# Ceramic High Pass Filter

## HFCW-7500+

50Ω 8200 to 21000 MHz



Generic photo used for illustration purposes only  
CASE STYLE: JC0603C

**+RoHS Compliant**

The +Suffix identifies RoHS Compliance. See our web site for RoHS Compliance methodologies and qualifications

### Features

- Very good rejection, 44 dB typ.
- Small size 0603 (0.063" X 0.032" X 0.024")
- Temperature stable
- LTCC construction

### Applications

- Test and measurements
- Military applications
- Telecommunications and broadband wireless systems

### Functional Schematic



### Electrical Specifications<sup>(1,2)</sup> at 25°C

| Parameter |                | F#    | Frequency (MHz) | Min. | Typ. | Max. | Unit |
|-----------|----------------|-------|-----------------|------|------|------|------|
| Stop Band | Rejection Loss | DC-F1 | DC - 4000       | 38   | 44   | -    | dB   |
|           |                | F1-F2 | 4000 - 6000     | 25   | 34   | -    | dB   |
|           | Freq. Cut-Off  | F3*   | 7600            | -    | 3.0  | -    | dB   |
| Pass Band | Insertion Loss | F4-F5 | 8200 - 9500     | -    | 1.8  | -    | dB   |
|           |                | F5-F6 | 9500 - 15000    | -    | 0.8  | 1.5  | dB   |
|           | Return Loss    | F6-F7 | 15000 - 21000   | -    | 1.0  | -    | dB   |
|           |                | F4-F6 | 8200 - 15000    | -    | 10   | -    | dB   |
|           |                | F6-F7 | 15000 - 21000   | -    | 7    | -    | dB   |

<sup>1</sup> This component is not intended to act as a DC block. Please consult with Mini-Circuits for further details

<sup>2</sup> Measured on Mini-Circuits Characterization Test Board TB-HFCW-7500+

\* Typically, a ±5% frequency deviation from the stated value may occur on a unit-to-unit basis.

### Maximum Ratings




|                       |                |
|-----------------------|----------------|
| Operating Temperature | -55°C to 125°C |
| Storage Temperature   | -55°C to 125°C |
| RF Power Input*       | 2.5W @ 25°C    |

\* Passband rating, derate linearly to 0.7W at 125°C ambient  
Permanent damage may occur if any of these limits are exceeded.

### Typical Performance Data at 25°C

| Frequency (MHz) | Insertion Loss (dB) | Return Loss (dB) |
|-----------------|---------------------|------------------|
| 10              | 72.74               | 0.09             |
| 100             | 66.69               | 0.11             |
| 500             | 53.69               | 0.16             |
| 2000            | 44.17               | 0.16             |
| 4000            | 51.93               | 0.17             |
| 6000            | 37.61               | 0.54             |
| 6360            | 30.31               | 0.68             |
| 6800            | 20.49               | 0.98             |
| 7240            | 10.43               | 2.17             |
| 7500            | 5.43                | 4.90             |
| 7600            | 4.02                | 6.97             |
| 7700            | 2.98                | 9.96             |
| 8200            | 1.34                | 18.61            |
| 9500            | 0.77                | 15.59            |
| 11000           | 0.57                | 18.30            |
| 13000           | 0.49                | 22.76            |
| 15000           | 0.45                | 18.90            |
| 16000           | 0.63                | 12.77            |
| 18000           | 1.33                | 7.60             |
| 21000           | 0.65                | 26.47            |

### Typical Frequency Response



### Notes

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.  
 B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.  
 C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at [www.minicircuits.com/MCLStore/terms.jsp](http://www.minicircuits.com/MCLStore/terms.jsp)



[www.minicircuits.com](http://www.minicircuits.com) P.O. Box 350166, Brooklyn, NY 11235-0003 (718) 934-4500 sales@minicircuits.com


REV. OR  
ECO-009063  
HFCW-7500+  
EDU3856  
URJ  
210804  
Page 2 of 3

## Pad Connections

|        |         |
|--------|---------|
| INPUT  | 1       |
| OUTPUT | 3       |
| GROUND | 2,4,5,6 |

Product Marking: R


Demo Board MCL P/N: TB-HFCW-7500+  
Suggested PCB Layout (PL-703)



### NOTES:

- COPLANAR WAVEGUIDE PARAMETERS ARE SHOWN FOR ROGERS (RO4350B) WITH DIELECTRIC THICKNESS .0200±.0015. COPPER: 1/2 Oz. EACH SIDE. FOR OTHER MATERIALS TRACE WIDTH AND GAP MAY NEED TO BE MODIFIED.
  - BOTTOM SIDE OF THE PCB IS CONTINUOUS GROUND PLANE.
-  DENOTES PCB COPPER PATTERN WITH SMOBC (SOLDER MASK OVER BARE COPPER)  
 DENOTES PCB COPPER PATTERN FREE OF SOLDERMASK

## Outline Drawing



### Outline Dimensions (inch)

| A    | B    | C    | D    | E    | F    | G    | Wt.   |
|------|------|------|------|------|------|------|-------|
| .063 | .032 | .024 | .012 | .008 | .006 | .020 | grams |
| 1.60 | 0.80 | 0.60 | 0.30 | 0.20 | 0.15 | 0.50 | .005  |

Note: Please refer to case style drawing for details.

### Notes

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
- C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at [www.minicircuits.com/MCLStore/terms.jsp](http://www.minicircuits.com/MCLStore/terms.jsp)





*Typical Performance Data*

| FREQ.<br><br>(MHz) | INSERTION LOSS |        |         | INPUT RETURN LOSS |        |         | OUTPUT RETURN LOSS |        |         |
|--------------------|----------------|--------|---------|-------------------|--------|---------|--------------------|--------|---------|
|                    | (dB)           |        |         | (dB)              |        |         | (dB)               |        |         |
|                    | @-55°C         | @+25°C | @+125°C | @-55°C            | @+25°C | @+125°C | @-55°C             | @+25°C | @+125°C |
| 10                 | 68.39          | 72.74  | 69.55   | 0.07              | 0.09   | 0.09    | 0.07               | 0.08   | 0.10    |
| 30                 | 69.01          | 72.22  | 70.24   | 0.07              | 0.09   | 0.10    | 0.07               | 0.09   | 0.11    |
| 50                 | 69.47          | 71.71  | 70.37   | 0.08              | 0.09   | 0.10    | 0.07               | 0.09   | 0.12    |
| 100                | 65.96          | 66.69  | 66.04   | 0.09              | 0.11   | 0.13    | 0.08               | 0.11   | 0.14    |
| 200                | 61.79          | 61.83  | 61.80   | 0.10              | 0.13   | 0.15    | 0.09               | 0.12   | 0.16    |
| 300                | 58.04          | 58.06  | 58.02   | 0.11              | 0.14   | 0.17    | 0.10               | 0.13   | 0.18    |
| 500                | 53.66          | 53.69  | 53.68   | 0.12              | 0.16   | 0.20    | 0.11               | 0.15   | 0.20    |
| 700                | 50.89          | 50.92  | 50.93   | 0.12              | 0.17   | 0.21    | 0.12               | 0.16   | 0.22    |
| 1000               | 48.14          | 48.16  | 48.18   | 0.13              | 0.18   | 0.22    | 0.12               | 0.17   | 0.23    |
| 1200               | 46.85          | 46.87  | 46.90   | 0.12              | 0.18   | 0.22    | 0.12               | 0.17   | 0.23    |
| 1400               | 45.86          | 45.88  | 45.91   | 0.12              | 0.18   | 0.22    | 0.11               | 0.17   | 0.23    |
| 1600               | 45.09          | 45.11  | 45.14   | 0.11              | 0.17   | 0.22    | 0.11               | 0.16   | 0.23    |
| 1800               | 44.52          | 44.55  | 44.59   | 0.10              | 0.16   | 0.22    | 0.10               | 0.16   | 0.22    |
| 2000               | 44.13          | 44.17  | 44.22   | 0.09              | 0.16   | 0.21    | 0.09               | 0.15   | 0.22    |
| 2200               | 43.90          | 43.95  | 44.01   | 0.08              | 0.15   | 0.21    | 0.08               | 0.15   | 0.22    |
| 2400               | 43.82          | 43.90  | 43.97   | 0.07              | 0.14   | 0.20    | 0.07               | 0.14   | 0.21    |
| 2600               | 43.91          | 44.01  | 44.10   | 0.06              | 0.14   | 0.20    | 0.07               | 0.14   | 0.21    |
| 2800               | 44.17          | 44.29  | 44.42   | 0.06              | 0.14   | 0.20    | 0.06               | 0.13   | 0.21    |
| 3000               | 44.63          | 44.79  | 44.92   | 0.05              | 0.14   | 0.21    | 0.05               | 0.13   | 0.21    |
| 3200               | 45.29          | 45.49  | 45.65   | 0.05              | 0.14   | 0.21    | 0.05               | 0.13   | 0.21    |
| 3400               | 46.23          | 46.46  | 46.68   | 0.05              | 0.14   | 0.22    | 0.04               | 0.13   | 0.22    |
| 3600               | 47.47          | 47.75  | 48.02   | 0.05              | 0.15   | 0.23    | 0.04               | 0.13   | 0.23    |
| 3800               | 49.14          | 49.50  | 49.86   | 0.05              | 0.16   | 0.25    | 0.04               | 0.14   | 0.24    |
| 4000               | 51.44          | 51.93  | 52.39   | 0.06              | 0.17   | 0.27    | 0.05               | 0.15   | 0.26    |
| 4200               | 54.81          | 55.49  | 56.24   | 0.07              | 0.19   | 0.29    | 0.06               | 0.17   | 0.28    |
| 4400               | 60.76          | 62.09  | 63.68   | 0.09              | 0.21   | 0.32    | 0.07               | 0.18   | 0.30    |
| 4600               | 70.94          | 70.25  | 69.25   | 0.11              | 0.24   | 0.35    | 0.09               | 0.20   | 0.33    |
| 4800               | 61.54          | 60.25  | 59.10   | 0.14              | 0.27   | 0.39    | 0.11               | 0.23   | 0.36    |
| 5000               | 54.92          | 54.31  | 53.65   | 0.17              | 0.30   | 0.43    | 0.13               | 0.26   | 0.39    |
| 5200               | 51.03          | 50.55  | 49.95   | 0.20              | 0.34   | 0.48    | 0.16               | 0.29   | 0.44    |
| 5500               | 46.50          | 45.94  | 45.21   | 0.25              | 0.40   | 0.56    | 0.21               | 0.35   | 0.51    |
| 6000               | 38.61          | 37.61  | 36.35   | 0.37              | 0.54   | 0.73    | 0.31               | 0.47   | 0.65    |
| 6360               | 31.60          | 30.31  | 28.76   | 0.47              | 0.68   | 0.90    | 0.41               | 0.59   | 0.81    |
| 6800               | 21.94          | 20.49  | 18.77   | 0.70              | 0.98   | 1.32    | 0.62               | 0.89   | 1.22    |
| 7240               | 11.81          | 10.43  | 8.97    | 1.51              | 2.17   | 3.07    | 1.42               | 2.04   | 2.91    |
| 7500               | 6.38           | 5.43   | 4.60    | 3.43              | 4.90   | 6.89    | 3.28               | 4.67   | 6.55    |
| 7600               | 4.70           | 4.02   | 3.50    | 4.96              | 6.97   | 9.63    | 4.74               | 6.63   | 9.06    |
| 7700               | 3.38           | 2.98   | 2.74    | 7.22              | 9.96   | 13.48   | 6.87               | 9.36   | 12.32   |
| 8200               | 1.13           | 1.34   | 1.53    | 21.41             | 18.61  | 16.86   | 18.42              | 17.25  | 16.12   |
| 8600               | 0.94           | 1.12   | 1.30    | 13.87             | 14.08  | 14.05   | 13.77              | 14.01  | 14.00   |
| 8800               | 0.86           | 1.03   | 1.20    | 13.42             | 13.93  | 14.08   | 13.43              | 13.94  | 14.12   |
| 9000               | 0.78           | 0.95   | 1.11    | 13.53             | 14.18  | 14.45   | 13.60              | 14.26  | 14.55   |
| 9200               | 0.71           | 0.87   | 1.03    | 13.95             | 14.66  | 15.00   | 14.04              | 14.78  | 15.16   |
| 9500               | 0.61           | 0.77   | 0.93    | 14.88             | 15.59  | 15.99   | 14.96              | 15.71  | 16.18   |
| 9800               | 0.52           | 0.70   | 0.85    | 15.92             | 16.40  | 16.91   | 16.07              | 16.61  | 17.28   |
| 10000              | 0.48           | 0.66   | 0.81    | 16.62             | 16.91  | 17.44   | 16.78              | 17.15  | 17.86   |
| 10200              | 0.45           | 0.63   | 0.79    | 17.17             | 17.27  | 17.83   | 17.40              | 17.58  | 18.37   |
| 10400              | 0.44           | 0.62   | 0.77    | 17.72             | 17.57  | 18.14   | 18.03              | 17.93  | 18.77   |
| 10600              | 0.41           | 0.61   | 0.76    | 18.19             | 17.87  | 18.37   | 18.60              | 18.28  | 19.07   |
| 10800              | 0.40           | 0.59   | 0.74    | 18.53             | 18.08  | 18.49   | 19.04              | 18.64  | 19.26   |
| 11000              | 0.38           | 0.57   | 0.73    | 18.85             | 18.30  | 18.66   | 19.36              | 18.85  | 19.36   |
| 12000              | 0.34           | 0.53   | 0.70    | 19.64             | 19.51  | 19.14   | 20.30              | 20.17  | 19.62   |
| 13000              | 0.30           | 0.49   | 0.65    | 22.13             | 22.76  | 22.25   | 22.57              | 23.40  | 22.40   |
| 14000              | 0.24           | 0.43   | 0.60    | 26.58             | 26.62  | 27.87   | 26.63              | 27.57  | 28.85   |
| 15000              | 0.25           | 0.45   | 0.66    | 18.84             | 18.90  | 18.29   | 18.92              | 19.25  | 18.66   |
| 16000              | 0.40           | 0.63   | 0.88    | 12.86             | 12.77  | 12.35   | 13.00              | 12.94  | 12.54   |
| 17000              | 0.69           | 0.97   | 1.24    | 9.54              | 9.27   | 9.17    | 9.55               | 9.29   | 9.21    |
| 18000              | 1.05           | 1.33   | 1.61    | 7.59              | 7.60   | 7.54    | 7.51               | 7.51   | 7.50    |
| 19000              | 1.16           | 1.36   | 1.64    | 7.14              | 7.61   | 7.62    | 7.06               | 7.50   | 7.55    |
| 21000              | 0.37           | 0.65   | 0.96    | 23.06             | 26.47  | 25.97   | 22.67              | 25.31  | 25.23   |

## Typical Performance Data

| FREQ.<br><br>(MHz) | GROUP DELAY |        |         |
|--------------------|-------------|--------|---------|
|                    | (nsec)      |        |         |
|                    | @-55°C      | @+25°C | @+125°C |
| 8200               | 0.29        | 0.27   | 0.25    |
| 8400               | 0.24        | 0.23   | 0.21    |
| 8600               | 0.21        | 0.20   | 0.19    |
| 8800               | 0.18        | 0.17   | 0.17    |
| 9000               | 0.16        | 0.16   | 0.15    |
| 9200               | 0.15        | 0.15   | 0.14    |
| 9500               | 0.13        | 0.13   | 0.13    |
| 9800               | 0.12        | 0.12   | 0.12    |
| 10000              | 0.11        | 0.11   | 0.11    |
| 10300              | 0.10        | 0.10   | 0.10    |
| 10600              | 0.09        | 0.09   | 0.09    |
| 10900              | 0.09        | 0.09   | 0.09    |
| 11200              | 0.08        | 0.08   | 0.08    |
| 11500              | 0.08        | 0.08   | 0.08    |
| 11800              | 0.07        | 0.07   | 0.07    |
| 12100              | 0.07        | 0.07   | 0.07    |
| 12400              | 0.07        | 0.07   | 0.07    |
| 12700              | 0.06        | 0.06   | 0.06    |
| 13000              | 0.06        | 0.06   | 0.06    |
| 13300              | 0.06        | 0.06   | 0.06    |
| 13600              | 0.06        | 0.06   | 0.06    |
| 13900              | 0.06        | 0.06   | 0.06    |
| 14200              | 0.06        | 0.06   | 0.06    |
| 14500              | 0.06        | 0.06   | 0.06    |
| 14800              | 0.06        | 0.06   | 0.06    |
| 15000              | 0.06        | 0.06   | 0.06    |
| 15300              | 0.06        | 0.06   | 0.06    |
| 15600              | 0.06        | 0.05   | 0.06    |
| 15900              | 0.05        | 0.05   | 0.06    |
| 16200              | 0.05        | 0.05   | 0.05    |
| 16500              | 0.05        | 0.05   | 0.05    |
| 16800              | 0.05        | 0.05   | 0.05    |
| 17100              | 0.05        | 0.05   | 0.05    |
| 17400              | 0.05        | 0.05   | 0.05    |
| 17700              | 0.05        | 0.05   | 0.05    |
| 18000              | 0.05        | 0.04   | 0.05    |
| 18500              | 0.04        | 0.04   | 0.04    |
| 19000              | 0.04        | 0.04   | 0.05    |
| 20000              | 0.05        | 0.06   | 0.06    |
| 21000              | 0.07        | 0.07   | 0.07    |

## Typical Performance Curves





# Case Style

JC

## Outline Dimensions

JC0603C



Weight: .005 grams

Dimensions are in mm [inch]. Tolerances:  $\pm 0.13$  mm

### Notes:

1. Open style, ceramic base.
2. Termination finish:

For RoHS Case Styles: Tin plate over Nickel plate. All models, (+) suffix.

**Mini-Circuits®**  
ISO 9001 ISO 14001 CERTIFIED

ALL NEW  
minicircuits.com

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site



The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: [www.minicircuits.com](http://www.minicircuits.com)

RF/IF MICROWAVE COMPONENTS

# Tape & Reel Packaging TR-F114

## DEVICE ORIENTATION IN T&R




ILLUSTRATION 1

| Applicable Case Styles |           |
|------------------------|-----------|
| GE0805C                | JC0603C   |
| GE0805C-1              | JC0603C-4 |
| GE0805C-1AP            | JC0603C-6 |
| GE0805C-7              |           |
| GE0805C-9              |           |
| GE0805C-10             |           |
| GE0805C-11             |           |
| GE0805C-12             |           |




ILLUSTRATION 2

| Applicable Case Styles |           |
|------------------------|-----------|
| GE0805C-2              | JC0603C-1 |
| GE0805C-3              | JC0603C-2 |
| GE0805C-4              | JC0603C-3 |
| GE0805C-5              | JC0603C-5 |
| GE0805C-6              | JC0603C-7 |
| GE0805C-8              | JV1210C-1 |
| GE0805C-15             |           |

| Tape Width, mm | Device Cavity Pitch, mm | Reel Size, inches | Devices per Reel                    |      |
|----------------|-------------------------|-------------------|-------------------------------------|------|
| 8              | 4                       | 7                 | Small quantity standards (see note) | 20   |
|                |                         |                   |                                     | 50   |
|                |                         |                   |                                     | 100  |
|                |                         |                   |                                     | 200  |
|                |                         |                   |                                     | 500  |
|                |                         |                   |                                     | 1000 |
|                |                         |                   | Standard                            | 4000 |

Note: Please Consult individual model data sheet to determine device per reel availability.

Mini-Circuits carrier tape materials provide protection from ESD (Electro-Static Discharge) during handling and transportation. Tapes are static dissipative and comply with industry standards EIA-481/EIA-541.

Go to: [www.minicircuits.com/pages/pdfs/tape.pdf](http://www.minicircuits.com/pages/pdfs/tape.pdf)




INTERNET <http://www.minicircuits.com>

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661

Distribution Centers NORTH AMERICA 800-654-7949 • 417-335-5935 • Fax 417-335-5945 • EUROPE 44-1252-832600 • Fax 44-1252-837010

Mini-Circuits ISO 9001 & ISO 14001 Certified


THIRD ANGLE PROJECTION



REVISIONS

| REV | ECN No.    | DESCRIPTION | DATE   | DR  | AUTH |
|-----|------------|-------------|--------|-----|------|
| OR  | ECO-006344 | NEW RELEASE | FEB 21 | DDR | VC   |
|     |            |             |        |     |      |
|     |            |             |        |     |      |

SUGGESTED MOUNTING CONFIGURATION  
FOR JC0603C CASE STYLE



NOTES:

1. COPLANAR WAVEGUIDE PARAMETERS ARE SHOWN FOR ROGERS (R04350B) WITH DIELECTRIC THICKNESS  $.0200 \pm .0015$ . COPPER: 1/2 Oz. EACH SIDE. FOR OTHER MATERIALS TRACE WIDTH AND GAP MAY NEED TO BE MODIFIED.
2. BOTTOM SIDE OF THE PCB IS CONTINUOUS GROUND PLANE.

 DENOTES PCB COPPER PATTERN WITH SMOBC (SOLDER MASK OVER BARE COPPER)  
 DENOTES PCB COPPER PATTERN FREE OF SOLDERMASK

| UNLESS OTHERWISE SPECIFIED | INITIALS      | DATE      |
|----------------------------|---------------|-----------|
| DIMENSIONS ARE IN INCHES   | DRAWN: DDR    | 17 FEB 21 |
| TOLERANCES ON:             | CHECKED: RV   | 17 FEB 21 |
| 2 PL DECIMALS ±            | APPROVED: RKS | 17 FEB 21 |
| 3 PL DECIMALS ± .005       |               |           |
| ANGLES ±                   |               |           |
| FRACTIONS ±                |               |           |


 **Mini-Circuits®** 13 Neptune Avenue  
Brooklyn NY 11235

PL DWG, JC0603C C.S, 50 OHM, HFCW

| Mini-Circuits®  |  | SIZE  | CODE IDENT | DRAWING NO: | REV:               |
|---|--|-------|------------|-------------|--------------------|
| THIS DOCUMENT AND ITS CONTENTS ARE THE PROPERTY OF MINI-CIRCUITS. EXCEPT FOR USE EXPRESSLY GRANTED, IN WRITING, TO ITS VENDORS, VENDEE AND THE UNITED STATES GOVERNMENT, MINI-CIRCUITS RESERVES ALL PROPRIETARY DESIGN, USE, MANUFACTURING AND REPRODUCTION RIGHTS THERETO. THESE CONTENTS SHALL NOT BE USED, DUPLICATED OR DISCLOSED TO ANY OUTSIDE PARTY, IN WHOLE OR IN PART, WITHOUT WRITTEN PERMISSION OF MINI-CIRCUITS. |  | A     | 15542      | 98-PL-703   | OR                 |
| ASHEETA1.DWG REV:A DATE:01/12/95  |  | FILE: | 98PL703    | SCALE:      | 15:1 SHEET: 1 OF 1 |

# Evaluation Board and Circuit

TB-HFCW-7500+



## Notes:

1. PCB Material: ROGERS (R04350B) OR Equivalent, Dielectric Constant= $3.48 \pm 0.05$   
Dielectric Thickness:  $.020 \pm 0.0015$
2. 50 Ohm 2.92mm Female Connectors.
3. Connectors on the test board shall not be subjected to temperature greater than 200°C to avoid permanent damage to the connectors.

 **Mini-Circuits®**



All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

| Specification              | Test/Inspection Condition   | Reference/Spec   |
|----------------------------|---|--|
| Operating Temperature      | -55° to 100°C<br>Ambient Environment  | Individual Model Data Sheet  |
| Storage Temperature        | -55° to 100° C<br>Ambient Environment   | Individual Model Data Sheet  |
| Humidity                   | 90 to 95% RH, 240 hours, 50°C   | MIL-STD-202, Method 103, Condition A, Except 50°C and end-point electrical test done within 12 hours |
| Solder Reflow Heat         | Sn-Pb Eutetic Process: 225°C peak<br>Pb-Free Process 245° - 250°C peak              | J-STD-020, Table 4-1, 4-2 and 5-2, Figure 5-1  |
| Solderability              | 10X Magnification   | J-STD-002, Para 4.2.5, Test S, 95% Coverage  |
| Vibration (High Frequency) | 20g peak, 10-2000 Hz, 12 times in each of three perpendicular directions (total 36) | MIL-STD-202, Method 204, Condition D   |
| Mechanical Shock           | 50g, 11 ms, 1/2-sine, 18 shocks: 3 each direction, each of 3 axes                   | MIL-STD-202, Method 213, Condition A   |