CERAMIC

High Pass Filter

HFCW-8400+

50Ω 9200 to 18000 MHz

THE BIG DEAL

- Low loss, 0.9 dB typ.
- Return loss, 11 dB typ.
- Stop Band Rejection, 36 dB typ.
- Small size 0603 (0.063" x 0.032" x 0.024")



Generic photo used for illustration purposes only

CASE STYLE: JC0603C

+RoHS Compliant

The +Suffix identifies RoHS Compliance. See our web site for RoHS Compliance methodologies and qualifications

APPLICATIONS

- Test and measurements
- Military applications
- Telecommunications and broadband wireless systems

PRODUCT OVERVIEW

HFCW-8400+ is a high pass filter with passband from 9200 MHz to 18000 MHz supporting a variety of applications. This model provides good insertion loss over a wide band due to strategically constructed layout. Housed in a tiny 0603 ceramic form factor with wraparound terminations, the filter is ideal for dense PCB layouts.

KEY FEATURES

Feature	Advantages
Wide passband	This filter has a very wide passband from 9.2 GHz to 18 GHz.
LTCC Construction	Provides repeatable performance in a rugged, ceramic package well suited for tough environments such as high humidity and temperature extremes.
Small size, 0603 (0.063" X 0.032" X 0.024")	Saves space in dense circuit board layouts and minimizes the effects of parasitics.
Wrap-around terminations	Provides excellent solderability and easy visual inspection.

REV. OR
ECO-015161
HFCW-8400+
EDU4353
URJ
220924

CERAMIC

High Pass Filter

HFCW-8400+

ELECTRICAL SPECIFICATIONS[1,2] AT 25°C

Parameter		F#	Frequency (MHz)	Min.	Typ.	Max.	Units
Stopband	Rejection Loss	DC-F1	DC - 5200	29	36	—	dB
		F1-F2	5200 - 6500	23	37	—	dB
	Freq. Cut-Off	F3*	8400	—	3	—	dB
Passband	Insertion Loss	F4-F5	9200 - 11500	—	1.8	—	dB
		F5-F6	11500 - 17000	—	0.9	1.6	dB
		F6-F7	17000 - 18000	—	1.8	—	dB
	Return Loss	F4-F5	9200 - 11500	—	11	—	dB
		F5-F6	11500 - 17000	—	11	—	dB
		F6-F7	17000 - 18000	—	8	—	dB


1 This component should not be employed as a DC-block. DC de-coupling capacitors are required in Applications where DC voltage and/or current is present at either input or output ports. Please contact Mini-Circuits for further support.
2 Measured on Mini-Circuits Characterization Test Board TB-HFCW-8400+
* Typically, a ±5% frequency deviation from the stated value may occur on a unit-to-unit basis.

MAXIMUM RATINGS


Parameter	Ratings
Operating temperature	-55°C to 125°C
Storage temperature	-55°C to 125°C
RF Power Input*	2.5W @25°C

*Passband rating, derate linearly to 0.6W at 125°C ambient
Permanent damage may occur if any of these limits are exceeded.

TYPICAL FREQUENCY RESPONSE



FUNCTIONAL SCHEMATIC



High Pass Filter


HFCW-8400+

PAD CONNECTIONS


INPUT	1
OUTPUT	3
GROUND	2,4,5,6

PRODUCT MARKING: VB

OUTLINE DRAWING



DEMO BOARD MCL P/N: TB-HFCW-8400+
SUGGESTED PCB LAYOUT (PL-704)



NOTES:
1. COPLANAR WAVEGUIDE PARAMETERS ARE SHOWN FOR ROGERS (RO3003) WITH DIELECTRIC THICKNESS .020±.001 COPPER: 1/2 Oz. EACH SIDE. FOR OTHER MATERIALS TRACE WIDTH AND GAP MAY NEED TO BE MODIFIED.
2. BOTTOM SIDE OF THE PCB IS CONTINUOUS GROUND PLANE.

DENOTES PCB COPPER PATTERN WITH SMOBC (SOLDER MASK OVER BARE COPPER)
DENOTES PCB COPPER PATTERN FREE OF SOLDERMASK

OUTLINE DIMENSIONS (Inches / mm)

A	B	C	D	E	F	G	Wt.
.063	**.032**	**.024**	**.012**	**.008**	**.006**	**.020**	grams
1.60	0.80	0.60	0.30	0.20	0.15	0.50	.005


Note: Please refer to case style drawing for details


High Pass Filter


HFCW-8400+

TYPICAL PERFORMANCE DATA AT 25°C

Frequency (MHz)	Insertion Loss (dB)	Return Loss (dB)
10	76.70	0.06
100	61.42	0.07
3000	36.55	0.04
5200	38.35	0.09
6500	39.32	0.33
6800	31.38	0.45
7300	21.22	0.78
7900	9.82	2.29
8400	2.97	9.72
9200	1.16	24.73
10000	0.82	32.13
11500	0.60	22.24
15000	0.56	20.93
17000	0.48	22.24
18000	0.48	21.80







NOTES

A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.

B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.

C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the standard. Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp

Ceramic High Pass Filter HFCW-8400+

Typical Performance Data


FREQ.	INSERTION LOSS			INPUT RETURN LOSS			OUTPUT RETURN LOSS		
(MHz)	(dB)			(dB)			(dB)		
	@-55°C	@+25°C	@+125°C	@-55°C	@+25°C	@+125°C	@-55°C	@+25°C	@+125°C
10	76.39	76.70	71.66	0.03	0.06	0.07	0.02	0.02	0.03
100	61.43	61.42	61.35	0.01	0.07	0.08	0.03	0.03	0.04
300	54.22	54.21	54.26	0.02	0.07	0.09	0.01	0.04	0.06
500	49.54	49.58	49.60	0.02	0.08	0.11	0.01	0.07	0.10
700	46.64	46.68	46.70	0.02	0.08	0.12	0.02	0.08	0.11
900	44.54	44.59	44.60	0.01	0.08	0.12	0.00	0.07	0.10
1000	43.69	43.73	43.75	0.01	0.08	0.12	0.01	0.06	0.09
1200	42.25	42.28	42.30	0.01	0.08	0.12	0.03	0.04	0.08
1400	41.08	41.11	41.13	0.00	0.08	0.11	0.04	0.03	0.06
1600	40.10	40.15	40.16	0.01	0.08	0.11	0.05	0.03	0.05
1800	39.29	39.34	39.35	0.01	0.07	0.11	0.05	0.03	0.06
2000	38.59	38.65	38.66	0.02	0.07	0.10	0.05	0.03	0.06
2200	38.00	38.06	38.07	0.03	0.06	0.10	0.06	0.03	0.06
2400	37.51	37.57	37.59	0.04	0.05	0.10	0.06	0.02	0.06
2600	37.09	37.16	37.18	0.05	0.05	0.09	0.07	0.02	0.05
2800	36.73	36.82	36.85	0.06	0.04	0.09	0.08	0.02	0.05
3000	36.45	36.55	36.59	0.06	0.04	0.09	0.08	0.01	0.05
3200	36.22	36.33	36.39	0.07	0.03	0.08	0.09	0.01	0.05
3400	36.05	36.18	36.25	0.08	0.03	0.08	0.10	0.00	0.04
3600	35.95	36.10	36.17	0.08	0.03	0.08	0.10	0.00	0.04
3800	35.90	36.07	36.14	0.09	0.03	0.09	0.11	0.00	0.04
4000	35.91	36.10	36.19	0.09	0.03	0.09	0.11	0.00	0.05
4500	36.26	36.52	36.65	0.09	0.04	0.11	0.09	0.04	0.09
5000	37.24	37.60	37.83	0.08	0.07	0.15	0.08	0.06	0.12
5200	37.93	38.35	38.65	0.06	0.09	0.17	0.07	0.07	0.14
6000	47.02	48.84	49.51	0.03	0.20	0.31	0.02	0.18	0.27
6500	42.13	39.32	37.50	0.13	0.33	0.46	0.13	0.31	0.41
6800	33.23	31.38	30.05	0.22	0.45	0.60	0.21	0.41	0.54
7300	22.84	21.22	19.96	0.47	0.78	1.02	0.43	0.71	0.92
7900	11.43	9.82	8.64	1.47	2.29	3.06	1.34	2.10	2.80
8400	3.55	2.97	2.72	6.56	9.72	12.37	6.19	9.11	11.49
9200	0.94	1.16	1.28	23.31	24.73	27.73	21.51	23.04	25.46
9400	0.84	1.05	1.17	22.11	25.78	30.84	21.01	24.16	27.97
9600	0.75	0.96	1.08	23.20	29.11	36.53	22.08	26.92	32.89
9800	0.67	0.88	1.00	25.30	33.11	33.20	24.09	31.19	36.16
10000	0.60	0.82	0.95	27.91	32.13	28.60	26.81	35.06	32.86
10200	0.55	0.77	0.90	29.77	28.65	25.90	30.08	34.01	29.81
10400	0.51	0.73	0.86	29.04	26.28	24.37	32.12	31.26	28.12
10600	0.47	0.70	0.82	27.45	24.89	23.59	31.79	29.64	27.43
10800	0.45	0.67	0.79	26.02	23.96	23.21	30.43	28.79	27.35
11000	0.42	0.64	0.76	24.93	23.38	22.91	29.09	28.00	27.34
11200	0.40	0.62	0.74	24.09	22.95	22.74	27.45	26.98	26.72
11500	0.38	0.60	0.72	23.00	22.24	22.07	25.69	25.69	25.43
11800	0.37	0.59	0.70	22.06	21.68	21.54	24.27	24.25	23.83
12000	0.36	0.58	0.69	21.66	21.39	21.16	23.45	23.47	22.90
12200	0.35	0.58	0.69	21.33	20.99	20.91	22.80	22.67	22.20
12400	0.34	0.57	0.68	20.99	20.72	20.66	22.13	22.08	21.69
12600	0.35	0.57	0.67	20.50	20.48	20.44	21.67	21.61	21.15
12800	0.33	0.57	0.67	20.44	20.29	20.34	21.37	21.28	20.86
13000	0.34	0.58	0.66	20.19	20.14	20.35	21.29	21.20	20.77
13500	0.34	0.54	0.66	20.09	20.75	20.61	20.58	20.65	20.61
14000	0.34	0.56	0.66	20.16	20.61	20.83	20.97	21.13	21.25
14500	0.34	0.55	0.66	20.25	20.85	20.80	21.45	21.65	21.98
15000	0.33	0.56	0.66	20.51	20.93	20.96	21.99	22.82	22.77
15500	0.31	0.53	0.67	20.86	21.36	21.12	22.97	23.33	23.80
16000	0.29	0.53	0.64	21.13	21.43	21.58	24.29	24.42	24.49
16500	0.26	0.50	0.62	21.22	21.72	21.84	25.54	24.86	25.15
17000	0.24	0.48	0.60	21.66	22.24	22.63	26.39	25.05	25.16
17500	0.22	0.47	0.61	21.86	22.41	22.81	26.19	24.97	24.78
18000	0.22	0.48	0.63	21.50	21.80	22.31	25.05	23.53	23.00

Typical Performance Data


FREQ. (MHz)	GROUP DELAY (nsec)		
	@-55°C	@+25°C	@+125°C
9200	0.24	0.22	0.22
9400	0.21	0.20	0.20
9600	0.19	0.18	0.18
9800	0.18	0.17	0.17
10000	0.16	0.16	0.15
10200	0.15	0.15	0.14
10400	0.14	0.14	0.13
10600	0.13	0.13	0.13
10800	0.12	0.12	0.12
11000	0.12	0.11	0.11
11200	0.11	0.11	0.10
11500	0.10	0.10	0.10
11800	0.09	0.09	0.09
12000	0.09	0.08	0.08
12200	0.08	0.08	0.08
12400	0.08	0.08	0.08
12600	0.08	0.07	0.08
12800	0.07	0.07	0.07
13000	0.07	0.07	0.07
13200	0.07	0.07	0.07
13400	0.07	0.06	0.07
13600	0.06	0.06	0.06
13800	0.06	0.06	0.06
14000	0.06	0.06	0.06
14200	0.06	0.05	0.06
14400	0.06	0.06	0.06
14600	0.05	0.05	0.05
14800	0.05	0.05	0.05
15000	0.05	0.05	0.05
15200	0.05	0.05	0.05
15400	0.05	0.05	0.05
15600	0.05	0.05	0.05
15800	0.05	0.05	0.05
16000	0.05	0.05	0.05
16200	0.05	0.05	0.05
16500	0.05	0.05	0.05
16800	0.05	0.05	0.05
17000	0.05	0.05	0.05
17500	0.05	0.05	0.05
18000	0.05	0.05	0.05

Typical Performance Curves


INSERTION LOSS vs. TEMPERATURE
INPUT POWER = 0 dBm




INSERTION LOSS vs. TEMPERATURE (Zoomed)
INPUT POWER = 0 dBm




INPUT RETURN LOSS vs. TEMPERATURE
INPUT POWER = 0 dBm



OUTPUT RETURN LOSS vs. TEMPERATURE
INPUT POWER = 0 dBm




GROUP DELAY vs. TEMPERATURE
INPUT POWER = 0 dBm



Case Style JC

Outline Dimensions JC0603C



METALLIZATION

Weight: .005 grams

Dimensions are in mm [inch]. Tolerances: ±0.13 mm

Notes:

1. Open style, ceramic base.
2. Termination finish:
   For RoHS Case Styles: Tin plate over Nickel plate. All models, (+) suffix.

Mini-Circuits®
ISO 9001 ISO 14001 CERTIFIED
ALL NEW minicircuits.com
P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site
The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: www.minicircuits.com
RF/IF MICROWAVE COMPONENTS

Tape & Reel Packaging TR-F114

DEVICE ORIENTATION IN T&R




ILLUSTRATION 1

Applicable Case Styles	
GE0805C	JC0603C
GE0805C-1	JC0603C-4
GE0805C-1AP	JC0603C-6
GE0805C-7	
GE0805C-9	
GE0805C-10	
GE0805C-11	
GE0805C-12	




ILLUSTRATION 2

Applicable Case Styles	
GE0805C-2	JC0603C-1
GE0805C-3	JC0603C-2
GE0805C-4	JC0603C-3
GE0805C-5	JC0603C-5
GE0805C-6	JC0603C-7
GE0805C-8	
GE0805C-15	

Tape Width, mm	Device Cavity Pitch, mm	Reel Size, inches	Devices per Reel	
8	4	7	Small quantity standards (see note)	20
				50
				100
				200
				500
				1000
			Standard	4000

Note: Please Consult individual model data sheet to determine device per reel availability.


Mini-Circuits carrier tape materials provide protection from ESD (Electro-Static Discharge) during handling and transportation. Tapes are static dissipative and comply with industry standards EIA-481/EIA-541.

Go to: www.minicircuits.com/pages/pdfs/tape.pdf

Mini-Circuits®
INTERNET http://www.minicircuits.com
P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661
Distribution Centers NORTH AMERICA 800-654-7949 • 417-335-5935 • Fax 417-335-5945 • EUROPE 44-1252-832600 • Fax 44-1252-837010
Mini-Circuits ISO 9001 & ISO 14001 Certified


This document and its contents are the property of Mini-Circuits.

THIRD ANGLE PROJECTION



REVISIONS					
REV	ECN No.	DESCRIPTION	DATE	DR	AUTH
OR	ECO-006344	NEW RELEASE	FEB 21	KKR	VC

SUGGESTED MOUNTING CONFIGURATION FOR JC0603C CASE STYLE



NOTES:

1. COPLANAR WAVEGUIDE PARAMETERS ARE SHOWN FOR ROGERS (RO3003) WITH DIELECTRIC THICKNESS .020±.001 COPPER: 1/2 Oz. EACH SIDE. FOR OTHER MATERIALS TRACE WIDTH AND GAP MAY NEED TO BE MODIFIED.
2. BOTTOM SIDE OF THE PCB IS CONTINUOUS GROUND PLANE.

DENOTES PCB COPPER PATTERN WITH SMOBC (SOLDER MASK OVER BARE COPPER)

DENOTES PCB COPPER PATTERN FREE OF SOLDERMASK

UNLESS OTHERWISE SPECIFIED		INITIALS	DATE
DIMENSIONS ARE IN INCHES	DRAWN	KKR	17 FEB 21
TOLERANCES ON:	CHECKED	DDR	17 FEB 21
2 PL DECIMALS ±	APPROVED	RV	17 FEB 21
3 PL DECIMALS ± .005			
ANGLES ±			
FRACTIONS ±			

Mini-Circuits ®

THIS DOCUMENT AND ITS CONTENTS ARE THE PROPERTY OF MINI-CIRCUITS. EXCEPT FOR USE EXPRESSLY GRANTED, IN WRITING, TO ITS VENDORS, VENDEE AND THE UNITED STATES GOVERNMENT, MINI-CIRCUITS RESERVES ALL PROPRIETARY DESIGN, USE , MANUFACTURING AND REPRODUCTION RIGHTS THERETO. THESE CONTENTS SHALL NOT BE USED, DUPLICATED OR DISCLOSED TO ANY OUTSIDE PARTY, IN WHOLE OR IN PART, WITHOUT WRITTEN PERMISSION OF MINI-CIRCUITS.

ASHEETA1.DWG REV:A DATE:01/12/95

Mini-Circuits®
13 Neptune Avenue
Brooklyn NY 11235


PL DWG, JC0603C C.S, 50 OHM, HFCW

SIZE	CODE IDENT	DRAWING NO:	REV:
A	15542	98-PL-704	OR

FILE:	SCALE:	SHEET:
98PL704	15:1	1 OF 1

Evaluation Board and Circuit

TB-HFCW-8400+



Notes:

1. PCB Material: ROGERS (RO3003) OR Equivalent, Dielectric Constant=3.00±.04
Dielectric Thickness: .020±.001
2. 50 Ohm 2.92mm Female Connectors.
3. Connectors on the test board shall not be subjected to temperature greater than 200°C to avoid permanent damage to the connectors.

Mini-Circuits®

THIS DOCUMENT AND ITS CONTENTS ARE THE PROPERTY OF MINI-CIRCUITS.

Mini-Circuits

Environmental Specifications ENV126

All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

Specification	Test/Inspection Condition	Reference/Spec
Operating Temperature	-55° to 125° C Ambient Environment	Individual Model Data Sheet
Storage Temperature	-55° to 125° C Ambient Environment	Individual Model Data Sheet
Humidity	90 to 95% RH, 240 hours, 50°C	MIL-STD-202, Method 103, Condition A, Except 50°C and end-point electrical test done within 12 hours
Solder Reflow Heat	Sn-Pb Eutectic Process 225°C peak Pb-Free Process 245° - 250°C peak	J-STD-020C, Table 4-1, 4-2 and 5-2, Figure 5-1
Solderability	10X Magnification	J-STD-002, Para 4.2.5, Test S, 95% Coverage
Vibration (High Frequency)	20g peak, 10-2000 Hz, 12 times in each of three perpendicular directions (total 36)	MIL-STD-202, Method 204, Condition D
Mechanical Shock	50g, 11 ms, 1/2-sine, 18 shocks: 3 each direction, each of 3 axes	MIL-STD-202, Method 213, Condition A

This document and its contents are the property of Mini-Circuits.