



FLEXIBLE

Coaxial Cable

FL086-24NM+

50Ω 24 inch DC to 18 GHz N-Type Male

THE BIG DEAL

- Wideband Frequency Coverage, DC to 18 GHz
- Low Insertion Loss, 1.4 dB Typ. at 18 GHz
- Excellent Return Loss, 32 dB Typ. at 18 GHz
- 6 mm Bend Radius for Tight Installations
- Insulated Outer Jacket Standard
- Connector Interface, Meets MIL-STD-348
- Ideal for Interconnect of Assembled Systems



Generic photo used for illustration purposes only

| | |
|-------------------|-------------|
| Model No. | FL086-24NM+ |
| Case Style | SE2633-24 |
| Connectors | N-Type Male |

APPLICATIONS

- Replacement for Custom Bent 0.086" Semi-Rigid Cables
- Communication Receivers and Transmitters
- Military and Aerospace Systems
- Environmental and Test Chambers
- Test Accessory

+RoHS Compliant
 The +Suffix identifies RoHS Compliance.
 See our website for methodologies and qualifications

PRODUCT OVERVIEW

The FL086 Series Flexible Coaxial Cables are ideal for interconnection of coaxial components or sub-systems. The construction includes a silver-plated copper-clad steel center conductor. The outer shield is silver-plated copper braid, which minimizes signal leakage and at the same time is flexible for easy bending Dielectric is low loss PTFE. Connectors have brass coupling nut over nickel-plated body with a gold-plated brass center conductor. The FL086 Series Flexible cables are available in variety of length to meet your requirements.

KEY FEATURES

| Feature | Advantages |
|--|---|
| Flexible RF Cables | The FL086 Series Flexible cables are ideal for use integrating coaxial components and sub-assemblies without the need for special cable-bending tools and alleviating the risk of damage during the bending process typical of semi-rigid coaxial cable assemblies. |
| Tight Bend Radius: 6 mm | Capable of only 6 mm bend radius, the FL086 Flexible series is able to make connections in tight spaces making these cables ideal for dense system integration |
| Excellent Return loss | The FL086 Series Flexible Cables are ideally suited for interconnecting a wide variety of RF components while minimizing VSWR ripple contribution due to mating cables & connectors. |
| Good Power Handling Capability: <ul style="list-style-type: none"> • 198 W at 0.5 GHz • 33 W at 18 GHz | Mini-Circuits FL086 Cable series can support medium to high RF power levels enabling these cables to be used in the transmit path. NOTE: power rating is at sea-level altitudes. |





FLEXIBLE

Coaxial Cable

FL086-24NM+

Mini-Circuits

50Ω 24 inch DC to 18 GHz N-Type Male

ELECTRICAL SPECIFICATIONS AT +25 °C

| Parameter | Frequency (GHz) | Min. | Typ. | Max. | Units |
|---------------------|-----------------|------|------|------|--------|
| Frequency Range | | DC | | 18 | GHz |
| Length ¹ | | 24 | | | inches |
| Insertion Loss | DC - 2 | — | 0.4 | 0.9 | dB |
| | 2 - 6 | — | 0.7 | 1.6 | |
| | 6 - 10 | — | 1.1 | 2.1 | |
| | 10 - 18 | — | 1.4 | 3.0 | |
| Return Loss | DC - 2 | 23 | 44 | — | dB |
| | 2 - 6 | 23 | 39 | — | |
| | 6 - 10 | 18 | 33 | — | |
| | 10 - 18 | 18 | 32 | — | |

1. Custom sizes available, consult factory.

ABSOLUTE MAXIMUM RATINGS²

| Parameter | Ratings |
|-------------------------------------|-------------------|
| Operating Temperature | -55 °C to +105 °C |
| Storage Temperature | -55 °C to +105 °C |
| Power Handling at +25 °C, Sea Level | 198 W at 0.5 GHz |
| | 140 W at 1 GHz |
| | 99 W at 2 GHz |
| | 57 W at 6 GHz |
| | 45 W at 10 GHz |
| | 33W at 18 GHz |

2. Permanent damage may occur if any of these limits are exceeded.





FLEXIBLE


Coaxial Cable

FL086-24NM+

Mini-Circuits

50Ω 24 inch DC to 18 GHz N-Type Male


CABLE CONSTRUCTION



- Center Conductor: Silver Plated Copper Clad Steel
- Dielectric: Solid PTFE
- Inner Shield: Silver Plated Copper Strip
- Outer Shield: Silver Plated Copper Braid
- Jacket: FEP, Blue
(Unjacketed cable also available upon request)

Connectors:
 Coupling Nut: Brass, Nickel Plated
 Body: Brass, Nickel Plated
 Center Pin: Brass, Gold Plated

OUTLINE DRAWING



OUTLINE DIMENSIONS (Inch/mm)

| A | B | C1 | C2 | D | E1 | E2 | F | wt |
|--------|------|------|------|------|------|------|-----------|-------|
| 24.0 | .88 | .750 | .375 | .88 | .750 | .375 | .106±.004 | grams |
| 609.60 | 22.0 | 19.0 | 9.5 | 22.0 | 19.0 | 9.5 | 4.14±0.10 | 80.64 |





FLEXIBLE

Coaxial Cable



FL086-24NM+



50Ω 24 inch DC to 18 GHz N-Type Male

TYPICAL PERFORMANCE DATA AND CHARTS

| Frequency (MHz) | Insertion Loss (dB) | Return Loss (dB) | |
|-----------------|---------------------|------------------|-------------|
| | | N-Type Male | N-Type Male |
| 100 | 0.12 | 39.5 | 41.2 |
| 1000 | 0.38 | 44.6 | 43.1 |
| 2000 | 0.54 | 40.1 | 41.0 |
| 2500 | 0.61 | 43.4 | 49.6 |
| 4000 | 0.76 | 40.1 | 45.3 |
| 5000 | 0.87 | 28.4 | 28.6 |
| 6000 | 0.94 | 39.8 | 44.8 |
| 7000 | 1.05 | 23.6 | 23.3 |
| 8000 | 1.12 | 35.4 | 46.1 |
| 9000 | 1.19 | 21.2 | 21.3 |
| 10000 | 1.25 | 39.3 | 34.5 |
| 12000 | 1.38 | 45.0 | 36.8 |
| 14000 | 1.52 | 26.8 | 34.7 |
| 17000 | 1.67 | 26.0 | 27.6 |
| 18000 | 1.72 | 37.9 | 40.7 |





- NOTES**
- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
 - B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuits' applicable established test performance criteria and measurement instructions.
 - C. The parts covered by this specification document are subject to Mini-Circuits' standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the standard terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/terms/viewterm.html




Typical Performance Data

| FREQUENCY (MHz) | INSERTION LOSS (dB) | N-MALE 1 RETURN LOSS (dB) | N-MALE 2 RETURN LOSS (dB) |
|--------------------|---------------------------|---------------------------------|---------------------------------|
| 100 | 0.12 | 39.5 | 41.2 |
| 200 | 0.17 | 55.7 | 48.6 |
| 300 | 0.21 | 40.2 | 40.9 |
| 400 | 0.24 | 50.3 | 46.6 |
| 500 | 0.27 | 39.7 | 40.7 |
| 600 | 0.30 | 48.9 | 43.7 |
| 700 | 0.32 | 39.7 | 39.8 |
| 800 | 0.34 | 46.5 | 45.0 |
| 900 | 0.36 | 41.7 | 40.6 |
| 1000 | 0.38 | 44.6 | 43.1 |
| 1100 | 0.41 | 43.4 | 41.0 |
| 1250 | 0.43 | 41.9 | 41.8 |
| 1500 | 0.47 | 48.6 | 41.7 |
| 1750 | 0.51 | 46.4 | 55.6 |
| 2000 | 0.54 | 40.1 | 41.0 |
| 2001 | 0.54 | 40.1 | 40.9 |
| 2250 | 0.57 | 42.9 | 38.6 |
| 2500 | 0.61 | 45.2 | 43.6 |
| 2750 | 0.64 | 41.0 | 44.2 |
| 3000 | 0.66 | 39.1 | 37.2 |
| 3250 | 0.69 | 38.6 | 39.5 |
| 3500 | 0.72 | 37.5 | 40.6 |
| 3750 | 0.74 | 33.5 | 32.4 |
| 4000 | 0.76 | 38.8 | 38.1 |
| 4250 | 0.81 | 32.8 | 33.9 |
| 4500 | 0.83 | 31.8 | 30.5 |
| 5000 | 0.87 | 29.0 | 29.6 |
| 5500 | 0.91 | 32.5 | 33.1 |
| 6000 | 0.94 | 39.8 | 44.8 |
| 6500 | 1.06 | 25.9 | 26.6 |
| 7000 | 1.09 | 24.3 | 23.7 |
| 7500 | 1.09 | 27.1 | 26.5 |
| 8000 | 1.12 | 31.6 | 34.1 |
| 8500 | 1.16 | 23.4 | 23.1 |
| 9000 | 1.24 | 21.6 | 21.7 |
| 9500 | 1.24 | 24.6 | 25.3 |
| 10000 | 1.25 | 39.3 | 34.5 |
| 10500 | 1.25 | 22.0 | 22.9 |
| 11000 | 1.40 | 25.7 | 25.0 |
| 11500 | 1.36 | 34.9 | 29.6 |
| 12000 | 1.36 | 31.5 | 31.5 |
| 12500 | 1.41 | 28.6 | 28.3 |
| 13000 | 1.42 | 43.0 | 41.6 |
| 13500 | 1.45 | 32.1 | 37.1 |
| 14000 | 1.48 | 29.9 | 40.1 |
| 14500 | 1.54 | 36.2 | 39.7 |
| 15000 | 1.54 | 25.7 | 26.3 |
| 15500 | 1.57 | 25.5 | 24.4 |
| 16000 | 1.60 | 35.8 | 37.4 |
| 16500 | 1.68 | 30.4 | 26.7 |
| 17000 | 1.66 | 26.1 | 28.4 |
| 17500 | 1.72 | 44.6 | 29.1 |
| 18000 | 1.72 | 37.9 | 40.7 |

Typical Performance Curves



Outline Dimensions



SE2633 SERIES N MALE (CONN)

| CASE STYLE # | A | | B | C1 | C2 | D | E1 | E2 | F FL086-ANM+ | T | | WEIGHT GRAMS |
|--------------|-------|--------|---------------|----------------|---------------|---------------|----------------|---------------|-------------------------|------|------|--------------|
| | INCH | MM | | | | | | | | INCH | MM | |
| SE2633-6 | 6.00 | 152.40 | .88 (22.0) | .750 (19.0) | .375 (9.5) | .88 (22.0) | .750 (19.0) | .375 (9.5) | .106±.004 (2.64±0.1) | 0.05 | 1.27 | 71.91 |
| SE2633-12 | 12.00 | 304.80 | | | | | | | | 0.10 | 2.54 | 74.82 |
| SE2633-24 | 24.00 | 609.60 | | | | | | | | 0.15 | 3.81 | 80.64 |

Unless otherwise specified dimensions are in inches (mm).

Tolerances: 2Pl. ± .03; 3Pl. ± .015

Note:

1. 086 Flexible Coaxial Cable.
2. "A" Represents Length of Cable.



All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

| Specification | Test/Inspection Condition | Reference/Spec |
|-----------------------|---|-----------------------------|
| Operating Temperature | -55° to 105°C Ambient Environment | Individual Model Data Sheet |
| Storage Temperature | -55° to 105°C Ambient Environment | Individual Model Data Sheet |
| Thermal Shock | -55° to 105°C, 25 cycles | MIL-STD-202F: Method 107G |
| Multiple Bend Radius | 40mm, 5 times for FL141 series cables 30 mm, 5 times for FL086 series cables | |
| Single Bend Radius | 10 mm for FL141 series cables 6 mm for FL086 series cables | |