

50Ω Bi-Phase 10 to 1000 MHz

Maximum Ratings


Operating Temperature	-55°C to 100°C
Storage Temperature	-55°C to 100°C
Control Current	30mA
Permanent damage may occur if any of these limits are exceeded.	

Pin Connections

INPUT	1
OUTPUT	8
CONTROL	3,4 [^]
GROUND	2,5,6,7
CASE GROUND	2,5,6,7




[^] pins must be connected together externally

Outline Drawing



Outline Dimensions (inch)

A	B	C	D	E	F
.770	.800	.240	.250	.370	.400
19.56	20.32	6.10	6.35	9.40	10.16
G	H	J	K		
.200	.20	.14	.031		
5.08	5.08	3.56	0.79		
				wt	
				grams	3.7



Features

- wideband, 10 to 1000 MHz
- rugged shielded case

Applications

- bi-phase modulator
- electronic attenuator



Generic photo used for illustration purposes only

CASE STYLE: A05

+RoHS Compliant

The +Suffix identifies RoHS Compliance. See our web site for RoHS Compliance methodologies and qualifications


Attenuator/Switch Electrical Specifications

FREQUENCY (MHz)		INSERTION LOSS (dB) ±20 mA				MAX. INPUT PWR (dBm) ±20 mA		IN-OUT ISOLATION (dB) 0 mA						BI-PHASE X (±20 mA) Typ.			
IN	CON	Mid-Band m		Total Range		1 dB compr.	no damage	L	M	U				Δ AMP (dB)	Phase (deg.) deviation from 180°		
f _L -f _U		Typ.	Max.	Typ.	Max.			Typ.	Min.	Typ.	Min.	Typ.	Min.	m	Total Range	m	Total Range
10-1000	DC-0.05	4.3	6	5.2	8.5	20	25	55	40	35	25	28	20	0.10	0.3	1.5	3.0


L = low range [f_L to 10 f_L] M = mid range [10 f_L to f_U/2] U = upper range [f_U/2 to f_U] m = [2 f_L to f_U/2]

Performance specifications apply for input power up to 10 dB below stated 1 dB compression.

suggested control port biasing configuration



electrical schematic



Typical Performance Data

Freq. (MHz)	I. Loss (dB) at 20mA		±Control, 20mA		Isolation (dB) (in-out) (in-con)		Input R. Loss (dB)	Control Current (mA)	Attenuation (dB)			Phase Δ ref at 15mA Ctrl			Input VSWR				
			ΔAMP (dB)	ΔPhase (deg.)							10 MHz	500 MHz	1000 MHz	10 MHz	500 MHz	1000 MHz	10 MHz	500 MHz	1000 MHz
	̄	σ	̄	̄	̄	̄	̄	deg.	deg.	deg.									
10.0	3.50	0.025	0.01	180.00	70	47	12.3	0.0000	71.8	43.8	38.2	-37.1	96.0	63.6	3.6	2.9	7.5		
19.9	3.52	0.015	0.01	180.00	68	40	12.7	0.0003	63.7	44.2	38.1	-34.3	93.2	62.4	3.6	2.9	7.5		
39.7	3.61	0.008	0.01	179.90	67	35	12.6	0.0004	55.7	43.8	38.1	-12.5	86.0	57.8	3.6	2.9	7.5		
59.5	3.63	0.006	0.01	179.90	65	31	12.5	0.0016	51.2	43.3	38.1	-8.5	80.1	52.8	3.6	2.8	7.4		
79.3	3.66	0.006	0.01	179.90	64	29	12.5	0.0057	45.4	41.1	36.8	-4.6	55.5	35.7	3.6	2.8	7.3		
86.7	3.68	0.006	0.01	179.90	63	28	12.5	0.0105	41.5	38.6	35.6	-1.2	42.6	23.4	3.5	2.8	7.1		
99.1	3.73	0.006	0.01	179.90	62	27	12.4	0.0161	38.3	36.0	33.7	1.5	34.4	12.9	3.5	2.8	6.9		
163.5	3.95	0.006	0.01	179.80	58	23	12.3	0.0286	33.9	31.8	30.1	3.6	24.5	0.6	3.4	2.7	6.6		
237.7	4.03	0.007	0.01	179.70	55	20	12.1	0.0437	30.3	28.4	27.1	4.3	20.7	-5.6	3.3	2.6	6.2		
314.4	4.05	0.008	0.01	179.37	52	18	12.0	0.0734	26.2	24.4	23.2	5.1	16.3	-9.9	3.1	2.4	5.6		
391.2	4.23	0.012	0.02	179.60	50	17	12.1	0.1029	23.6	21.8	20.8	5.0	14.4	-11.4	2.9	2.3	5.2		
467.9	4.36	0.017	0.04	179.60	48	17	12.3	0.1510	20.7	19.1	18.2	5.0	12.8	-11.9	2.7	2.1	4.7		
500.1	4.38	0.021	0.04	179.60	47	17	12.4	0.2540	17.1	15.6	15.1	4.6	10.4	-11.1	2.4	1.8	4.0		
542.1	4.48	0.027	0.06	179.50	46	17	12.5	0.3743	14.6	13.3	13.1	4.3	9.0	-9.9	2.1	1.6	3.6		
618.9	4.63	0.040	0.10	179.50	44	18	12.6	0.6438	11.5	10.6	10.8	3.5	6.9	-7.5	1.7	1.3	3.1		
695.6	4.90	0.053	0.13	179.60	43	20	12.1	0.9350	9.7	9.1	9.6	3.0	5.4	-6.0	1.5	1.2	2.9		
772.3	5.02	0.064	0.16	179.38	41	23	10.8	1.7496	7.2	7.2	8.2	2.0	3.6	-3.6	1.2	1.1	2.7		
846.6	5.51	0.073	0.16	179.70	41	21	9.1	2.6537	5.5	5.9	7.3	1.3	1.9	-1.8	1.2	1.3	2.7		
923.3	6.21	0.087	0.21	179.80	40	17	7.5	7.3045	4.3	4.9	6.7	0.5	0.6	-0.7	1.4	1.5	2.6		
1000.0	7.06	0.093	0.36	180.40	40	14	6.3	15.1437	3.6	4.5	6.4	0.1	0.1	-0.1	1.5	1.6	2.6		

Notes

- Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- Electrical specifications and performance data contained in this specification document are based on Mini-Circuits' applicable established test performance criteria and measurement instructions.
- The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp



Typical Performance Data

FREQ. (MHz)	INSERTION LOSS (dB) at 20mA Control Current	AMP. UNBAL. (dB) at ± 20 mA Control Current	PHASE UNBAL. (deg.) at ± 20 mA Control Current	ISOLATION at 0 mA Control Current (dB)		RETURN LOSS (dB) Input
				In-Out	In-Con	
10.0	3.50	0.01	180.0	70	47	12.3
19.9	3.52	0.01	180.0	68	40	12.7
39.7	3.61	0.01	179.9	67	35	12.6
59.5	3.63	0.01	179.9	65	31	12.5
79.3	3.66	0.01	179.9	64	29	12.5
86.7	3.68	0.01	179.9	63	28	12.5
99.1	3.73	0.01	179.9	62	27	12.4
163.5	3.95	0.01	179.8	58	23	12.3
237.7	4.03	0.01	179.7	55	20	12.1
314.4	4.05	0.01	179.4	52	18	12.0
391.2	4.23	0.02	179.6	50	17	12.1
467.9	4.36	0.04	179.6	48	17	12.3
500.1	4.38	0.04	179.6	47	17	12.4
542.1	4.48	0.06	179.5	46	17	12.5
618.9	4.63	0.10	179.5	44	18	12.6
695.6	4.90	0.13	179.6	43	20	12.1
772.3	5.02	0.16	179.4	41	23	10.8
846.6	5.51	0.16	179.7	41	21	9.1
923.3	6.21	0.21	179.8	40	17	7.5
1000.0	7.06	0.36	180.4	40	14	6.3

CONTROL CURRENT (mA)	ATTENUATION (dB)			PHASE UNBALANCE REF AT 15 mA CONTROL (deg.)			INPUT VSWR (:1)		
	10 MHz	500 MHz	1000 MHz	10 MHz	500 MHz	1000 MHz	10 MHz	500 MHz	1000 MHz
0.0000	71.8	43.8	38.2	-37.1	96.0	63.6	3.6	2.9	7.5
0.0003	63.7	44.2	38.1	-34.3	93.2	62.4	3.6	2.9	7.5
0.0004	55.7	43.8	38.1	-12.5	86.0	57.8	3.6	2.9	7.5
0.0016	51.2	43.3	38.1	-8.5	80.1	52.8	3.6	2.8	7.4
0.0057	45.4	41.1	36.8	-4.6	55.5	35.7	3.6	2.8	7.3
0.0105	41.5	38.6	35.6	-1.2	42.6	23.4	3.5	2.8	7.1
0.0161	38.3	36.0	33.7	1.5	34.4	12.9	3.5	2.8	6.9
0.0286	33.9	31.8	30.1	3.6	24.5	0.6	3.4	2.7	6.6
0.0437	30.3	28.4	27.1	4.3	20.7	-5.6	3.3	2.6	6.2
0.0734	26.2	24.4	23.2	5.1	16.3	-9.9	3.1	2.4	5.6
0.1029	23.6	21.8	20.8	5.0	14.4	-11.4	2.9	2.3	5.2
0.1510	20.7	19.1	18.2	5.0	12.8	-11.9	2.7	2.1	4.7
0.2540	17.1	15.6	15.1	4.6	10.4	-11.1	2.4	1.8	4.0
0.3743	14.6	13.3	13.1	4.3	9.0	-9.9	2.1	1.6	3.6
0.6438	11.5	10.6	10.8	3.5	6.9	-7.5	1.7	1.3	3.1
0.9350	9.7	9.1	9.6	3.0	5.4	-6.0	1.5	1.2	2.9
1.7496	7.2	7.2	8.2	2.0	3.6	-3.6	1.2	1.1	2.7
2.6537	5.5	5.9	7.3	1.3	1.9	-1.8	1.2	1.3	2.7
7.3045	4.3	4.9	6.7	0.5	0.6	-0.7	1.4	1.5	2.6
15.1437	3.6	4.5	6.4	0.1	0.1	-0.1	1.5	1.6	2.6

REV. X1

GAS-2+

120214

Page 1 of 1



IF/RF MICROWAVE COMPONENTS • ISO 9001 ISO 14001 AS 9100 CERTIFIED • RoHS compliant

P.O. Box 350166, Brooklyn, New York 11235-0006 (718) 934-4500 Fax (718) 332-4661




The Design Engineers Search Engine finds the model you need, instantly • For detailed performance specs & shopping online see




Typical Performance Curves


Insertion Loss @ 20 mA




Amplitude Unbalance @ ± 20 mA




Phase Unbalance @ ± 20 mA




Isolation @ 0 mA




Return Loss Input




Attenuation



Phase Unbalance ref @ 15 mA



Input VSWR



REV. X1

GAS-2+

120214

Page 1 of 1



IF/RF MICROWAVE COMPONENTS • ISO 9001 ISO 14001 AS 9100 CERTIFIED • RoHS compliant

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661




The Design Engineers Search Engine finds the model you need, instantly • For detailed performance specs & shopping online see



A01
A04
A05
A06

Outline Dimensions



CASE#	A	B	C	D	E	F	G	H	J	K	WT, GRAM
A01	.770 (19.56)	.800 (20.32)	.385 (9.78)	.400 (10.16)	.370 (9.40)	.400 (10.16)	.200 (5.08)	.20 (5.08)	.14 (3.56)	.031 (.79)	5.2
A04			.200 (5.08)	.210 (5.33)							3.7
A05			.240 (6.10)	.250 (6.35)							3.7
A06			.285 (7.24)	.310 (7.87)							5.2

Dimensions are in inches (mm). Tolerances: 2 Pl. $\pm .03$; 3 Pl. $\pm .015$

Notes:

- Header material: C.R.S.
Pin material: #52 alloy.
Cover material: Cupro-Nickel.
- Pin finish: Electro Tin-Silver.
- Insulated spacer available. Request P/N B14-045-01.
- Tolerance on pin diameter $\pm .005$ inch.
- Glass meniscus 0.015 inch max.
- Blue bead indicates Pin 1. Pin numbers do not appear on unit, for reference only.



Distribution Centers NORTH AMERICA 800-654-7949 • 417-335-5935 • Fax 417-335-5945 • EUROPE 44-1252-832600 • Fax 44-1252-837010

Mini-Circuits ISO 9001 & ISO 14001 Certified

INTERNET <http://www.minicircuits.com>

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661



All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

Specification	Test/Inspection Condition	Reference/Spec
Operating Temperature	-55° to 100° C Ambient Environment	Individual Model Data Sheet
Storage Temperature	-55° to 100° C Ambient Environment	Individual Model Data Sheet
Thermal Shock	-55° to 100°C, 100 cycles	MIL-STD-202, Method 107, Condition A-3, except +100°C
Vibration (High Frequency)	20g peak, 10-2000 Hz, 12 times in each of three perpendicular directions (total 36)	MIL-STD-202, Method 204, Condition D
Mechanical Shock	50g, 11 ms, 1/2-sine, 18 shocks: 3 each direction, each of 3 axes	MIL-STD-202, Method 213, Condition A
Moisture Resistance	10 cycles, 24 hours per cycle	MIL-STD-202, Method 106, Condition A, except 50°C and end point electrical test done within 12 hours
Solderability	10X Magnification	J-STD-002, 95% Coverage
Resistance to Solder Heat	260°C for 10 seconds	MIL-STD-202, Method 210, Condition B
Marking Resistance to Solvents	Isopropyl alcohol + mineral spirits at 25°C; terpene defluxer at 25°C; distilled water + proylene glycol monomethyl ether + monoethanolamine at 63°C to 70°C	MIL-STD-202, Method 215
Terminal Strength	4 1/2 Pound Pull	MIL-STD-202, Method 211, Condition A



All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

Specification	Test/Inspection Condition	Reference/Spec
Gross Leak	125°C Bubble Test	MIL-STD-202, Method 112, Condition D
Barometric Pressure	100,000 Feet	MIL-STD-202, Method 105, Condition D