LTCC SURFACE MOUNT

High Pass Filter

HFCG-1760+

50Ω 1800 to 8000 MHz

THE BIG DEAL

- Insertion Loss, Typ. 1 dB
- Stopband Rejection, Typ. 38 dB
- Passband Return Loss, Typ. 12 dB
- 0805 Surface Mount Footprint
- Power Handling: 2.5 W




Generic photo used for illustration purposes only

APPLICATIONS

- Test & Measurement Equipment
- Transmitters / Receivers
- Military Applications
- Telecommunications and Broadband Wireless Systems

FUNCTIONAL DIAGRAM



PRODUCT OVERVIEW

Mini-Circuits' HFCG-1760+ is a miniature low temperature co-fired ceramic (LTCC) high pass filter with a 1800 to 8000 MHz passband supporting a variety of applications. This model provides 1 dB typical insertion loss over a wide band due to its rugged monolithic construction. Housed in a tiny 0805 ceramic form factor with inspectable wrap-around terminations, the filter is ideal for dense signal chain PCB layouts where it complements MMIC size and performance. The LTCC fabrication process assures minimal RF performance variation while delivering a product that is well suited for environmental extremes of high humidity and temperature.

KEY FEATURES

Features	Advantages
Wide Passband, 6200 MHz	This filter has a very wide passband, from 1800 to 8000 MHz.
LTCC Construction	The use of LTCC technology allows for repeatable performance in a rugged ceramic package, well suited for tough environments such as high humidity and temperature extremes. See Mini-Circuits Environmental Rating ENV06 for more information.
Small Size, 0805	0805 package allows for space to be saved in dense circuit board layouts, while also minimizing the effects of parasitics.
Rugged Power Handling, 2.5 W	Handles up to 2.5 Watts in a small 0805 package.

High Pass Filter

HFCG-1760+

50Ω 1800 to 8000 MHz

ELECTRICAL SPECIFICATIONS[1,2,3] AT +25°C

Parameter		F#	Frequency (MHz)	Min.	Typ.	Max.	Units
Passband	Insertion Loss	F3-F4	1800 - 2100	—	2	—	dB
		F4-F5	2100 - 5200	—	1	1.6	
		F5-F6	5200 - 8000	—	2	—	
	Return Loss	F3-F6	1800 - 8000	—	13	—	dB
Stopband	Rejection	DC-F1	DC - 800	30	38	—	dB
		F1-F2	800 - 1200	28	36	—	
	Freq. Cut-Off[4]	Fc	1560	—	3	—	


1. Tested on Evaluation Board P/N TB-HFCG-1760+.
2. Bi-directional, RF1 and RF2 can be interchanged.
3. This component should not be used as a DC-block. In applications where DC voltage and/or current is present at either the input or output ports, external DC blocking capacitors are required.
4. Typical variation ±5%.

ABSOLUTE MAXIMUM RATINGS[5]

Parameter	Ratings
Operating Temperature	-55°C to +125°C
Storage Temperature	-55°C to +125°C
Input Power[6]	2.5 W @ +25°C

5. Permanent damage may occur if any of these limits are exceeded.
6. Power rating applies only to signals within the passband. Power rating above +25°C operating temperature decreases linearly to 0.4 W at +125°C.

TYPICAL FREQUENCY RESPONSE AT +25°C




High Pass Filter

HFCG-1760+


50Ω 1800 to 8000 MHz

TYPICAL PERFORMANCE GRAPHS


HFCG-1760+
INSERTION LOSS




HFCG-1760+
INSERTION LOSS (Zoomed)




HFCG-1760+
RETURN LOSS



HFCG-1760+
RETURN LOSS(Zoomed)



HFCG-1760+
GROUP DELAY



High Pass Filter

HFCG-1760+

50Ω 1800 to 8000 MHz

FUNCTIONAL DIAGRAM





Figure 1. HFCG-1760+ Functional Diagram

PAD DESCRIPTION

Function	Pad Number	Description
RF1[2]	1	Connects to RF Input Port
RF2[2]	3	Connects to RF Output Port
GROUND	2,4,5,6	Connects to Ground on PCB, (See drawing PL-633)

SUGGESTED PCB LAYOUT (PL-633)




NOTES:
1. COPLANAR WAVEGUIDE PARAMETERS ARE SHOWN FOR ROGERS (RO4350B) WITH DIELECTRIC THICKNESS .020±.0015. COPPER: 1/2 Oz. EACH SIDE. FOR OTHER MATERIALS TRACE WIDTH AND GAP MAY NEED TO BE MODIFIED.
2. BOTTOM SIDE OF THE PCB IS CONTINUOUS GROUND PLANE.

DENOTES PCB COPPER PATTERN WITH SMOBC (SOLDER MASK OVER BARE COPPER)
DENOTES PCB COPPER PATTERN FREE OF SOLDERMASK

Figure 2. Suggested PCB Layout PL-633

CASE STYLE DRAWING



Weight: .008 grams.
Dimensions are in inches (mm). Tolerances: 2Pl. ± .01; 3 Pl. ± .005

PRODUCT MARKING*: LT

*Marking may contain other features or characters for internal lot control.

High Pass Filter

HFCG-1760+

50Ω 1800 to 8000 MHz

ADDITIONAL DETAILED INFORMATION IS AVAILABLE ON OUR DASH BOARD. CLICK HERE

Performance Data and Graphs	Data Graphs S-Parameter (S2P Files) Data Set (.zip file) De-embedded to device pads
Case Style	GE0805C-9 Lead Finish: Tin over Nickel Plating.
RoHS Status	Compliant
Tape and Reel	F114
Suggested Layout for PCB Design	PL-633
Evaluation Board	TB-HFCG-1760+
	Gerber File
Environmental Rating	ENV06

NOTES

A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuits' applicable established test performance criteria and measurement instructions.
C. The parts covered by this specification document are subject to Mini-Circuits' standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the standard terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/terms/viewterm.html

Ceramic High Pass Filter HFCG-1760+

Typical Performance Data


FREQ. (MHz)	INSERTION LOSS (dB)			INPUT RETURN LOSS (dB)			OUTPUT RETURN LOSS (dB)		
	@-55°C	@+25°C	@+100°C	@-55°C	@+25°C	@+100°C	@-55°C	@+25°C	@+100°C
10	80.01	75.05	69.99	0.09	0.13	0.16	0.03	0.07	0.10
20	70.04	67.29	69.18	0.09	0.12	0.16	0.04	0.07	0.11
80	57.20	57.39	57.09	0.07	0.12	0.15	0.01	0.05	0.08
100	55.65	55.31	55.56	0.07	0.13	0.16	0.01	0.05	0.09
200	49.58	49.66	49.60	0.11	0.17	0.19	0.02	0.08	0.11
300	46.27	46.38	46.40	0.14	0.20	0.23	0.04	0.11	0.14
400	44.07	44.09	44.17	0.16	0.24	0.27	0.05	0.15	0.19
500	42.35	42.43	42.47	0.17	0.26	0.31	0.06	0.17	0.22
600	40.97	41.06	41.09	0.18	0.30	0.34	0.08	0.20	0.25
700	39.75	39.85	39.87	0.20	0.33	0.38	0.09	0.22	0.28
800	38.60	38.69	38.67	0.21	0.35	0.41	0.10	0.25	0.32
900	37.49	37.59	37.57	0.23	0.39	0.46	0.12	0.29	0.37
1000	36.66	36.77	36.78	0.27	0.45	0.54	0.16	0.34	0.43
1100	36.97	37.29	37.46	0.35	0.55	0.66	0.21	0.43	0.53
1200	42.88	42.86	41.89	0.49	0.74	0.87	0.32	0.58	0.71
1270	32.67	30.27	28.81	0.69	1.01	1.20	0.49	0.80	0.97
1300	26.98	25.01	23.78	0.85	1.22	1.45	0.62	0.96	1.17
1330	22.05	20.32	19.23	1.10	1.56	1.86	0.80	1.21	1.48
1360	17.55	15.99	15.01	1.50	2.12	2.55	1.12	1.64	2.00
1500	3.32	3.31	3.34	19.02	29.50	31.06	9.94	11.37	12.06
1560	2.14	2.35	2.46	16.58	15.77	15.46	12.63	13.10	13.49
1700	1.24	1.46	1.57	16.05	17.08	17.43	19.16	22.06	23.96
1760	1.04	1.27	1.39	17.81	18.01	17.78	27.64	27.57	25.83
1800	0.96	1.20	1.32	17.41	17.08	16.68	24.28	21.95	20.78
1900	0.85	1.10	1.21	14.50	14.26	14.09	15.94	15.42	15.18
2000	0.79	1.03	1.13	12.86	12.92	12.98	13.36	13.36	13.41
2100	0.71	0.94	1.03	12.56	12.80	12.95	12.77	12.98	13.16
2200	0.62	0.83	0.93	12.98	13.40	13.61	13.02	13.43	13.65
2300	0.51	0.72	0.81	14.11	14.71	14.94	14.03	14.60	14.87
2400	0.41	0.62	0.71	15.81	16.60	16.83	15.50	16.26	16.52
2500	0.32	0.54	0.63	18.10	19.09	19.36	17.53	18.50	18.80
2600	0.25	0.48	0.57	21.16	22.52	22.67	20.08	21.31	21.67
2700	0.20	0.43	0.52	25.12	26.78	26.87	23.07	24.44	25.03
2800	0.16	0.40	0.49	31.16	31.30	30.56	26.02	26.79	27.57
2900	0.14	0.38	0.47	31.22	29.27	28.23	26.49	26.51	26.95
3000	0.12	0.36	0.45	26.83	25.70	25.18	24.86	24.77	24.93
3100	0.10	0.35	0.45	24.42	23.66	23.48	23.40	23.31	23.52
3200	0.09	0.34	0.44	22.70	22.33	22.23	22.18	22.25	22.47
3300	0.07	0.33	0.43	21.72	21.49	21.47	21.56	21.69	21.96
3400	0.06	0.32	0.42	21.39	21.24	21.16	21.30	21.53	21.77
3500	0.04	0.31	0.41	21.56	21.45	21.47	21.64	21.89	22.17
3600	0.03	0.30	0.40	22.02	21.96	21.98	22.28	22.63	22.83
3700	0.01	0.28	0.39	22.74	22.67	22.59	23.19	23.60	23.65
3800	0.00	0.27	0.38	24.06	23.83	23.64	24.90	25.24	25.20
3900	0.02	0.26	0.37	25.78	25.41	25.00	27.39	27.73	27.34
4000	0.02	0.26	0.37	27.41	26.92	26.60	30.30	30.47	30.05
4100	0.01	0.28	0.39	28.86	28.67	28.39	32.96	34.31	33.99
4200	0.04	0.25	0.36	27.56	27.68	28.18	33.25	35.71	38.95
4300	0.03	0.27	0.37	26.83	27.23	28.21	29.79	30.91	34.55
4400	0.05	0.25	0.36	24.47	24.56	25.76	26.77	27.23	29.01
4500	0.04	0.26	0.39	22.27	22.41	23.62	23.79	24.02	25.52
4600	0.03	0.26	0.38	20.61	20.83	21.67	21.69	21.96	23.06
5000	0.00	0.31	0.44	15.86	15.99	16.37	16.23	16.33	16.76
5200	0.04	0.37	0.49	14.32	14.53	14.94	14.53	14.73	15.12
6000	0.16	0.52	0.67	10.96	11.34	11.57	10.94	11.32	11.58
6100	0.20	0.57	0.72	10.75	11.19	11.35	10.68	11.10	11.35
6500	0.26	0.63	0.78	9.97	10.44	10.55	9.87	10.37	10.51
7000	0.26	0.66	0.84	9.87	10.16	10.15	9.87	10.23	10.30
7500	0.25	0.67	0.86	9.98	10.21	10.06	9.92	10.23	10.16
8000	0.21	0.65	0.85	10.53	10.62	10.49	10.37	10.53	10.50

Typical Performance Data


FREQ. (MHz)	GROUP DELAY (nsec)		
	@-55°C	@+25˚C	@+100˚C
1800	0.73	0.71	0.69
1960	0.53	0.51	0.50
2000	0.50	0.48	0.47
2060	0.45	0.44	0.43
2100	0.42	0.41	0.41
2200	0.37	0.36	0.36
2300	0.33	0.33	0.32
2400	0.30	0.30	0.29
2500	0.27	0.27	0.26
2600	0.25	0.25	0.24
2700	0.23	0.23	0.22
2800	0.21	0.21	0.20
2900	0.20	0.19	0.19
3000	0.18	0.18	0.17
3100	0.17	0.17	0.16
3200	0.16	0.15	0.15
3300	0.15	0.15	0.14
3400	0.14	0.14	0.13
3500	0.13	0.13	0.13
3600	0.13	0.12	0.12
3700	0.12	0.12	0.12
3800	0.12	0.11	0.11
4000	0.11	0.10	0.10
4200	0.10	0.10	0.09
4500	0.09	0.09	0.09
4700	0.09	0.08	0.08
5000	0.08	0.08	0.07
5300	0.07	0.07	0.07
5600	0.07	0.06	0.06
5900	0.06	0.06	0.06
6000	0.06	0.06	0.06
6200	0.06	0.06	0.05
6300	0.06	0.06	0.05
6500	0.06	0.05	0.05
7000	0.06	0.05	0.05
7100	0.06	0.05	0.05
7200	0.06	0.05	0.05
7500	0.05	0.05	0.05
7600	0.05	0.05	0.05
7800	0.05	0.05	0.05
8000	0.05	0.05	0.05

Typical Performance Curves


INSERTION LOSS vs. TEMPERATURE
INPUT POWER = 0 dBm




INSERTION LOSS vs. TEMPERATURE (Zoomed)
INPUT POWER = 0 dBm




INPUT RETURN LOSS vs. TEMPERATURE
INPUT POWER = 0 dBm



OUTPUT RETURN LOSS vs. TEMPERATURE
INPUT POWER = 0 dBm




GROUP DELAY vs. TEMPERATURE
INPUT POWER = 0 dBm




GE0805C-9

Outline Dimensions



PCB Land Pattern



Suggested Layout,
Tolerance to be within ±.002

CASE #	A	B	C	D	E	F	G	H	J	K	WT.GRAM
GE0805C-9	.079 (2.00)	.049 (1.25)	.037 (0.95)	.014 (0.35)	.012 (0.30)	.012 (0.30)	.026 (0.65)	.014 (0.35)	.039 (1.00)	.110 (2.80)	.008

Dimensions are in inches (mm). Tolerances: 2Pl. ± .01; 3 Pl. ± .005

Notes:

1. Open style, ceramic base.
2. Termination finish: For RoHS Case Styles: Tin plate over Nickel plate. All models, (+) suffix.
   For RoHS-5 Case Styles: Tin-Lead plate over Nickel plate. All models, no (+) suffix.

This document and its contents are the property of Mini-Circuits.

Tape & Reel Packaging TR-F114

DEVICE ORIENTATION IN T&R




ILLUSTRATION 1

Applicable Case Styles	
GE0805C	JC0603C
GE0805C-1	JC0603C-4
GE0805C-1AP	JC0603C-6
GE0805C-7	
GE0805C-9	
GE0805C-10	
GE0805C-11	
GE0805C-12	




ILLUSTRATION 2

Applicable Case Styles	
GE0805C-2	JC0603C-1
GE0805C-3	JC0603C-2
GE0805C-4	JC0603C-3
GE0805C-5	JC0603C-5
GE0805C-6	JC0603C-7
GE0805C-8	
GE0805C-15	

Tape Width, mm	Device Cavity Pitch, mm	Reel Size, inches	Devices per Reel	
8	4	7	Small quantity standards (see note)	20
				50
				100
				200
				500
				1000
			Standard	4000

Note: Please Consult individual model data sheet to determine device per reel availability.


Mini-Circuits carrier tape materials provide protection from ESD (Electro-Static Discharge) during handling and transportation. Tapes are static dissipative and comply with industry standards EIA-481/EIA-541.

Go to: www.minicircuits.com/pages/pdfs/tape.pdf

Mini-Circuits®
INTERNET http://www.minicircuits.com
P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661
Distribution Centers NORTH AMERICA 800-654-7949 • 417-335-5935 • Fax 417-335-5945 • EUROPE 44-1252-832600 • Fax 44-1252-837010
Mini-Circuits ISO 9001 & ISO 14001 Certified

This document and its contents are the property of Mini-Circuits.


THIRD ANGLE PROJECTION



REVISIONS

REV	ECN No.	DESCRIPTION	DATE	DR	AUTH
OR	M174039	NEW RELEASE	MAY 19	DDR	VC

SUGGESTED MOUNTING CONFIGURATION FOR GE0805C-9 CASE STYLE "06FL02" PIN CODE



NOTES:

1. TRACE WIDTH IS SHOWN FOR ROGERS (RO4350B) WITH DIELECTRIC THICKNESS .020"±.0015". COPPER: 1/2 Oz. EACH SIDE.
   FOR OTHER MATERIALS TRACE WIDTH MAY NEED TO BE MODIFIED.
2. BOTTOM SIDE OF THE PCB IS CONTINUOUS GROUND PLANE.

DENOTES PCB COPPER LAYOUT WITH SMOBC (SOLDER MASK OVER BARE COPPER)

DENOTES COPPER LAND PATTERN FREE OF SOLDERMASK

UNLESS OTHERWISE SPECIFIED		INITIALS	DATE
DIMENSIONS ARE IN INCHES	DRAWN	DDR	08 MAY 19
TOLERANCES ON:	CHECKED	RV	08 MAY 19
2 PL DECIMALS ±	APPROVED	RKS	08 MAY 19
3 PL DECIMALS ± .005"			
ANGLES ±			
FRACTIONS ±			

Mini-Circuits ®

THIS DOCUMENT AND ITS CONTENTS ARE THE PROPERTY OF MINI-CIRCUITS. EXCEPT FOR USE EXPRESSLY GRANTED, IN WRITING, TO ITS VENDORS, VENDEE AND THE UNITED STATES GOVERNMENT, MINI-CIRCUITS RESERVES ALL PROPRIETARY DESIGN, USE , MANUFACTURING AND REPRODUCTION RIGHTS THERETO. THESE CONTENTS SHALL NOT BE USED, DUPLICATED OR DISCLOSED TO ANY OUTSIDE PARTY, IN WHOLE OR IN PART, WITHOUT WRITTEN PERMISSION OF MINI-CIRCUITS.

ASHEETA1.DWG REV:A DATE:01/12/95


Mini-Circuits®
13 Neptune Avenue
Brooklyn NY 11235

PL, 06FL02, GE0805C-9
TB-1104+, 50 OHM


SIZE	CODE IDENT	DRAWING NO:	REV:
A	15542	98-PL-633	OR
FILE: 98PL633		SCALE: 9:1	SHEET: 1 OF 1

Evaluation Board and Circuit

TB-1104+



Schematic diagram



Notes:

1. 50 Ohm SMA Female connectors.
2. PCB Material: ROGERS (RO4350B), OR Equivalent
   Dielectric Constant=3.48, Thickness=.020inch.

Mini-Circuits®

THIS DOCUMENT AND ITS CONTENTS ARE THE PROPERTY OF MINI-CIRCUITS.

Mini-Circuits

Environmental Specifications ENV06

All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

Specification	Test/Inspection Condition	Reference/Spec
Operating Temperature	-55° to 100°C Ambient Environment	Individual Model Data Sheet
Storage Temperature	-55° to 100° C Ambient Environment	Individual Model Data Sheet
Humidity	90 to 95% RH, 240 hours, 50°C	MIL-STD-202, Method 103, Condition A, Except 50°C and end-point electrical test done within 12 hours
Solder Reflow Heat	Sn-Pb Eutetic Process: 225°C peak Pb-Free Process 245° - 250°C peak	J-STD-020, Table 4-1, 4-2 and 5-2, Figure 5-1
Solderability	10X Magnification	J-STD-002, Para 4.2.5, Test S, 95% Coverage
Vibration (High Frequency)	20g peak, 10-2000 Hz, 12 times in each of three perpendicular directions (total 36)	MIL-STD-202, Method 204, Condition D
Mechanical Shock	50g, 11 ms, 1/2-sine, 18 shocks: 3 each direction, each of 3 axes	MIL-STD-202, Method 213, Condition A

This document and its contents are the property of Mini-Circuits.