



Mini-Circuits®

CERAMIC

High Pass Filter

HFCN-1500+


50Ω 1600 to 5500 MHz

THE BIG DEAL

- Small size
- 7 sections
- Temperature stable
- Excellent power handling, 7 W
- Hermetically sealed
- LTCC construction
- Low cost

APPLICATIONS

- Sub-harmonic rejection
- Transmitters/receivers
- Lab use



Generic photo used for illustration purposes only

CASE STYLE: FV1206-15

+RoHS Compliant

The +Suffix identifies RoHS Compliance.
See our website for methodologies and qualifications

ELECTRICAL SPECIFICATIONS^{1,2} AT +25 °C

Parameter	Frequency (MHz)	Min.	Typ.	Max.	Units
Stop Band	Rejection Loss	1060	40	—	dB
		1250	20	—	
	Freq. Cut-Off	1550	3.0	—	dB
	VSWR	1060–1250	20	—	
Pass Band	Insertion Loss	1600–5500	2.0	—	dB
		1850–4400	—	1.3	
	VSWR	1620–3450	1.5	—	:1

1. In Application where DC voltage is present at either input or output ports, coupling capacitors are required. Alternatively, Mini-Circuits' "D" suffix version of this model will provide >100 MOhm isolation to ground.


2. Measured on Mini-Circuits Characterization Test Board TB-270.

MAXIMUM RATINGS


Parameter	Ratings
Operating temperature	-55°C to +100°C
Storage temperature	-55°C to +100°C
RF Power Input ³	7 W max. at +25°C

3. Passband rating, derate linearly to 3 W at 100°C ambient.
Permanent damage may occur if any of these limits are exceeded.

TYPICAL FREQUENCY RESPONSE



FUNCTIONAL SCHEMATIC



REV. Q
ECO-030200
HFCN-1500+
MCL NY
260626

Mini-Circuits®

www.minicircuits.com P.O. Box 350166, Brooklyn, NY 11235-0003 (718) 934-4500 sales@minicircuits.com

PAGE 1 OF 3



Mini-Circuits®

CERAMIC

High Pass Filter


HFCN-1500+

PIN CONNECTIONS

RF IN	1
RF OUT	3
GROUND	2,4


PRODUCT MARKING: B1

**DEMO BOARD MCL P/N: TB-270
SUGGESTED PCB LAYOUT (PL-137)**



- NOTES:**
1. COPLANAR WAVEGUIDE PARAMETERS ARE SHOWN FOR ROGERS RO4350B WITH THICKNESS .020" ± .0015". COPPER: 1/2 OZ. EACH SIDE. FOR OTHER MATERIALS TRACE WIDTH & GAP MAY NEED TO BE MODIFIED.
 2. BOTTOM SIDE OF THE PCB IS CONTINUOUS GROUND PLANE.
-  DENOTES PCB COPPER LAYOUT WITH SMOBC (SOLDER MASK OVER BARE COPPER)
 DENOTES COPPER LAND PATTERN FREE OF SOLDER MASK

OUTLINE DRAWING



Weight: .020 grams.
Dimensions are in inches [mm]. Tolerances: 2 Pl. ± .01; 3 Pl. ± .005

TAPE & REEL INFORMATION: F71




CERAMIC

High Pass Filter

HFCN-1500+

TYPICAL PERFORMANCE DATA AT +25°C

Frequency (MHz)	Insertion Loss (dB)	VSWR (:1)
1.00	105.45	1737.18
100.00	63.65	579.06
1060.00	48.22	46.96
1250.00	31.52	28.03
1400.00	14.81	12.89
1480.00	7.64	5.56
1550.00	3.50	2.35
1600.00	2.13	1.54
1620.00	1.83	1.41
1850.00	1.00	1.49
2000.00	0.76	1.31
3450.00	0.45	1.15
4400.00	0.94	1.82
5500.00	2.10	3.04
7000.00	3.85	4.99
9000.00	5.89	5.89



NOTES

- Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
- The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the standard. Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp



Ceramic High Pass Filter

HFCN-1500+

Typical Performance Data

FREQ. (MHz)	INSERTION LOSS (dB)			INPUT RETURN LOSS (dB)			OUTPUT RETURNLOSS (dB)		
	@ -55° C	@ +25° C	@ +100° C	@ -55° C	@ +25° C	@ +100° C	@ -55° C	@ +25° C	@ +100° C
1	96.15	105.45	107.90	0.02	0.01	0.02	0.01	0.01	0.02
50	61.07	72.31	74.03	0.06	0.02	0.05	0.01	0.01	0.03
100	66.09	63.65	69.00	0.04	0.03	0.09	0.03	0.00	0.00
500	59.66	59.75	59.91	0.04	0.07	0.16	0.05	0.10	0.13
870	48.63	48.51	48.45	0.15	0.20	0.27	0.17	0.23	0.28
1060	47.35	48.22	48.69	0.27	0.37	0.44	0.23	0.33	0.41
1100	50.33	51.58	52.59	0.27	0.37	0.47	0.28	0.40	0.46
1140	56.91	53.96	50.27	0.33	0.41	0.53	0.33	0.44	0.50
1165	50.32	46.53	44.13	0.37	0.46	0.59	0.34	0.44	0.55
1245	33.69	32.22	30.86	0.43	0.59	0.71	0.43	0.55	0.65
1250	33.02	31.52	30.18	0.47	0.62	0.76	0.43	0.55	0.66
1280	29.05	27.76	26.53	0.54	0.69	0.85	0.45	0.58	0.73
1340	21.98	20.94	19.85	0.70	0.91	1.12	0.57	0.75	0.94
1390	16.84	15.86	14.81	0.93	1.21	1.54	0.81	1.03	1.30
1445	11.48	10.57	9.73	1.58	2.06	2.69	1.32	1.71	2.16
1500	6.82	6.21	5.65	3.14	4.10	5.22	2.53	3.26	4.07
1510	6.12	5.55	5.04	3.58	4.69	5.96	2.93	3.71	4.59
1530	4.80	4.40	4.06	4.73	6.10	7.67	3.86	4.79	5.84
1540	4.23	3.93	3.67	5.43	6.95	8.64	4.39	5.45	6.51
1550	3.78	3.50	3.31	6.22	7.90	9.83	4.98	6.14	7.25
1560	3.34	3.10	2.99	7.14	8.95	11.07	5.73	6.84	8.02
1600	2.09	2.13	2.16	11.17	13.39	15.61	8.58	9.68	10.57
1620	1.75	1.83	1.95	13.38	15.45	16.97	9.98	10.83	11.55
1650	1.48	1.62	1.72	15.21	16.13	16.49	11.38	11.82	12.23
1700	1.23	1.38	1.53	14.72	14.71	14.73	12.38	12.50	12.79
1850	0.87	1.00	1.13	13.82	14.16	14.59	13.37	13.80	14.42
1870	0.86	1.01	1.10	14.09	14.42	14.91	13.72	14.19	14.84
2045	0.57	0.69	0.84	18.36	18.68	19.11	18.63	19.19	19.98
2500	0.35	0.47	0.60	23.45	23.09	23.17	24.35	23.80	23.51
3000	0.28	0.43	0.55	26.40	27.95	30.03	27.51	28.14	27.88
3440	0.32	0.50	0.61	23.31	23.27	23.33	22.85	22.88	22.46
3450	0.27	0.45	0.55	23.01	22.96	23.13	22.63	22.65	22.26
4000	0.45	0.65	0.78	14.66	14.48	14.53	14.44	14.16	14.17
4400	0.74	0.94	1.07	10.69	10.72	11.02	10.56	10.52	10.68
4500	0.78	0.99	1.11	9.86	10.06	10.12	9.79	9.85	9.84
5000	1.32	1.54	1.70	7.14	7.52	7.56	7.02	7.25	7.16
5500	1.86	2.10	2.27	5.72	5.93	6.03	5.53	5.68	5.72
6000	2.34	2.64	2.99	4.77	4.86	4.85	4.55	4.62	4.59
6300	2.66	3.06	3.32	4.35	4.27	4.48	4.16	4.15	4.35
7000	3.59	3.85	4.16	3.31	3.53	3.71	3.18	3.43	3.67
7500	4.08	4.30	4.57	2.89	3.14	3.34	2.77	3.02	3.23
8000	4.55	4.68	4.92	2.74	2.95	3.05	2.47	2.81	2.99
8500	4.69	4.99	5.33	2.48	2.72	2.83	2.42	2.69	2.80
9000	5.37	5.89	6.70	2.53	2.98	3.83	2.26	2.37	2.56
9500	3.99	4.19	4.37	3.58	3.64	3.76	3.15	3.23	3.44
10000	3.81	3.81	3.93	3.05	3.52	3.97	3.16	3.63	4.07

REV. X1

HFCN-1500+

080723

Page 1 of 1



IF/RF MICROWAVE COMPONENTS • ISO 9001 ISO 14001 AS9100 CERTIFIED • RoHS compliant

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661



The Design Engineers Search Engine finds the model you need, Instantly • For detailed performance specs & shopping online see




Ceramic High Pass Filter


Typical Performance Curves

HFCN-1500+


INSERTION LOSS vs. TEMPERATURE



INPUT RETURN LOSS vs. TEMPERATURE



OUTPUT RETURN LOSS vs. TEMPERATURE



REV. X1
HFCN-1500+
080723
Page 1 of 1



The Design Engineers Search Engine finds the model you need, Instantly • For detailed performance specs & shopping online see





Mini-Circuits®

IF/RF MICROWAVE COMPONENTS • ISO 9001 ISO 14001 AS9100 CERTIFIED • RoHS compliant
P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661



Outline Dimensions

FV1206-15



METALLIZATION

Weight: .020 grams.

Dimensions are in inches (mm). Tolerances: 2 Pl. $\pm$.01; 3 Pl. $\pm$.005

Notes:

1. Case material: Ceramic.
2. Termination Finish: **as shown below or indicated on Data Sheet.**
For RoHS Case Styles: Tin plate over Nickel plate. All models, (+) suffix.




P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site



The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: www.minicircuits.com

RF/IF MICROWAVE COMPONENTS


THIRD ANGLE PROJECTION



REVISIONS

REV	ECN No.	DESCRIPTION	DATE	DR	AUTH
OR	M88634	NEW RELEASE	08/28/03	GF	ABD
A	M102713	ADDED "...WITH SMOBC"	01/17/06	MMG	IL

**SUGGESTED MOUNTING CONFIGURATION
FOR FV1206 CASE STYLE, "nx" PIN CONNECTION**




NOTES: 1. COPLANAR WAVEGUIDE PARAMETERS ARE SHOWN FOR ROGERS R04350B WITH THICKNESS .020" $\pm$.0015".
COPPER: 1/2 OZ. EACH SIDE.
FOR OTHER MATERIALS TRACE WIDTH & GAP MAY NEED TO BE MODIFIED.

2. BOTTOM SIDE OF THE PCB IS CONTINUOUS GROUND PLANE.



DENOTES PCB COPPER LAYOUT WITH SMOBC
(SOLDER MASK OVER BARE COPPER)



DENOTES COPPER LAND PATTERN FREE OF SOLDER MASK

UNLESS OTHERWISE SPECIFIED

INITIALS

DATE

DIMENSIONS ARE IN INCHES

TOLERANCES ON:

2 PL DECIMALS $\pm$ 3 PL DECIMALS $\pm$.005ANGLES $\pm$ FRACTIONS $\pm$

DRAWN

GF

08/27/03

CHECKED

AV

08/28/03

APPROVED

ABD

08/28/03



Mini-Circuits®

13 Neptune Avenue
Brooklyn NY 11235

PL, nx, FV1206, LFCN/HFCN, TB-270

SIZE

A

CODE IDENT

15542

DRAWING NO:

98-PL-137

REV:

A

FILE:

98PL137

SCALE:

10:1

SHEET:

1 OF 1

Mini-Circuits®

THIS DOCUMENT AND ITS CONTENTS ARE THE PROPERTY OF MINI-CIRCUITS. EXCEPT FOR USE EXPRESSLY GRANTED, IN WRITING, TO ITS VENDORS, VENDEE AND THE UNITED STATES GOVERNMENT, MINI-CIRCUITS RESERVES ALL PROPRIETARY DESIGN, USE, MANUFACTURING AND REPRODUCTION RIGHTS THERETO. THESE CONTENTS SHALL NOT BE USED, DUPLICATED OR DISCLOSED TO ANY OUTSIDE PARTY, IN WHOLE OR IN PART, WITHOUT WRITTEN PERMISSION OF MINI-CIRCUITS.

ASHEETA1.DWG REV:A DATE:01/12/95



All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

Specification	Test/Inspection Condition	Reference/Spec
Operating Temperature	-55° to 100°C Ambient Environment	Individual Model Data Sheet
Storage Temperature	-55° to 100° C Ambient Environment	Individual Model Data Sheet
Humidity	90 to 95% RH, 240 hours, 50°C	MIL-STD-202, Method 103, Condition A, Except 50°C and end-point electrical test done within 12 hours
Solder Reflow Heat	Sn-Pb Eutetic Process: 225°C peak Pb-Free Process 245° - 250°C peak	J-STD-020, Table 4-1, 4-2 and 5-2, Figure 5-1
Solderability	10X Magnification	J-STD-002, Para 4.2.5, Test S, 95% Coverage
Vibration (High Frequency)	20g peak, 10-2000 Hz, 12 times in each of three perpendicular directions (total 36)	MIL-STD-202, Method 204, Condition D
Mechanical Shock	50g, 11 ms, 1/2-sine, 18 shocks: 3 each direction, each of 3 axes	MIL-STD-202, Method 213, Condition A