



Mini-Circuits

CERAMIC


## High Pass Filter

50Ω 3400 to 9900 MHz

HFCN-3100+

## FEATURES

- Small Size
- 5 Sections
- Temperature Stable
- Excellent Power Handling, 7 W
- Hermetically Sealed
- LTCC Construction
- Low Cost
- Protected by US Patent 7,760,485



Generic photo used for illustration purposes only

CASE STYLE: FV1206-1

## +RoHS Compliant

The +Suffix identifies RoHS Compliance.  
See our website for methodologies and qualifications

## APPLICATIONS

- Sub-harmonic Rejection
- Transmitters/Receivers

ELECTRICAL SPECIFICATIONS<sup>1,2</sup> AT +25°C

| Parameter | Frequency (MHz) | Min.       | Typ. | Max. | Units |
|-----------|-----------------|------------|------|------|-------|
| Stop Band | Rejection Loss  | 2500       | —    | 30   | dB    |
|           |                 | 2450       | 20   | —    |       |
|           | Freq. Cut-Off   | 3100       | —    | 3.0  | dB    |
|           | VSWR            | 2450-2500  | —    | 20   |       |
| Pass Band | Insertion Loss  | 3400-9900  | —    | 2.0  | dB    |
|           |                 | 3500-9500  | —    | 1.5  |       |
|           | VSWR            | 3100-10500 | —    | 1.5  | :1    |

1. In Application where DC voltage is present at either input or output ports, coupling capacitors are required. Alternatively, Mini-Circuits' "D" suffix version of this model will provide >100 MOhm isolation to ground.


2. Measured on Mini-Circuits Characterization Test Board TB-285.

## ABSOLUTE MAXIMUM RATINGS


| Parameter                   | Ratings           |
|-----------------------------|-------------------|
| Operating Temperature       | -55°C to +100°C   |
| Storage Temperature         | -55°C to +100°C   |
| RF Power Input <sup>3</sup> | 7 W max. at +25°C |

3. Passband rating, derate linearly to 3 W at +100°C ambient.  
Permanent damage may occur if any of these limits are exceeded.

## TYPICAL FREQUENCY RESPONSE



## FUNCTIONAL SCHEMATIC



REV. G  
ECO-028231  
HFCN-3100+  
MCL NY/RAV  
250116

Mini-Circuits

www.minicircuits.com P.O. Box 350166, Brooklyn, NY 11235-0003 (718) 934-4500 sales@minicircuits.com

PAGE 1 OF 3



Mini-Circuits®

CERAMIC

## High Pass Filter

HFCN-3100+


50Ω 3400 to 9900 MHz

## PIN CONNECTIONS

|        |         |
|--------|---------|
| RF IN  | 1       |
| RF OUT | 3       |
| GROUND | 2,4,5,6 |

PRODUCT MARKING: M1


DEMO BOARD MCL P/N: TB-285  
SUGGESTED PCB LAYOUT (PL-158)




- NOTE:** 1. TRACE WIDTH IS SHOWN FOR ROGERS R04350 WITH DIELECTRIC THICKNESS: .020 ± .0015; COPPER: 1/2 OZ. EACH SIDE. FOR OTHER MATERIALS TRACE WIDTH MAY NEED TO BE MODIFIED.
2. BOTTOM SIDE OF THE PCB IS CONTINUOUS GROUND PLANE.

|  |                                                |
|--|------------------------------------------------|
|  | DENOTES PCB COPPER LAYOUT                      |
|  | DENOTES COPPER LAND PATTERN FREE OF SOLDERMASK |

## OUTLINE DRAWING



## PCB Land Pattern



Suggested Layout,  
Tolerance to be within ±.002

## OUTLINE DIMENSIONS (Inches mm)

| A    | B    | C    | D    | E    | F     |
|------|------|------|------|------|-------|
| .126 | .063 | .035 | .024 | .022 | .011  |
| 3.20 | 1.60 | 0.89 | 0.61 | 0.56 | 0.28  |
| G    | H    | J    | K    |      | wt    |
| .039 | .024 | .042 | .123 |      | grams |
| 0.99 | 0.61 | 1.07 | 3.12 |      | .020  |

## TAPE &amp; REEL INFORMATION: F75



CERAMIC

## High Pass Filter



HFCN-3100+

Mini-Circuits

50Ω 3400 to 9900 MHz

## TYPICAL PERFORMANCE DATA AT +25°C

| Frequency (MHz) | Insertion Loss (dB) | VSWR (:1) |
|-----------------|---------------------|-----------|
| 50              | 54.41               | 1737.18   |
| 800             | 32.66               | 115.81    |
| 1810            | 54.18               | 59.91     |
| 2450            | 40.03               | 26.74     |
| 2500            | 33.38               | 25.19     |
| 2700            | 16.65               | 15.00     |
| 2920            | 6.20                | 4.89      |
| 3100            | 2.22                | 1.87      |
| 3400            | 1.01                | 1.27      |
| 3500            | 0.94                | 1.32      |
| 5000            | 0.66                | 1.09      |
| 7000            | 0.68                | 1.31      |
| 9000            | 0.88                | 1.21      |
| 9500            | 0.78                | 1.29      |
| 9900            | 0.88                | 1.39      |
| 10500           | 1.21                | 1.52      |
| 11000           | 1.76                | 1.68      |



## NOTES

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
- C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the standard. Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at [www.minicircuits.com/MCLStore/terms.jsp](http://www.minicircuits.com/MCLStore/terms.jsp)



# Ceramic High Pass Filter

**HFCN-3100+**

## Typical Performance Data

| FREQ.<br>(MHz) | INSERTION LOSS<br>(dB) |          |           | INPUT RETURN LOSS<br>(dB) |          |           | OUTPUT RETURNLOSS<br>(dB) |          |           |
|----------------|------------------------|----------|-----------|---------------------------|----------|-----------|---------------------------|----------|-----------|
|                | @ -55° C               | @ +25° C | @ +100° C | @ -55° C                  | @ +25° C | @ +100° C | @ -55° C                  | @ +25° C | @ +100° C |
| 50             | 43.14                  | 41.38    | 42.73     | 0.07                      | 0.29     | 0.11      | 0.03                      | 0.14     | 0.07      |
| 100            | 48.29                  | 48.65    | 47.75     | 0.11                      | 0.12     | 0.12      | 0.13                      | 0.14     | 0.14      |
| 280            | 40.07                  | 39.61    | 39.56     | 0.09                      | 0.11     | 0.14      | 0.12                      | 0.14     | 0.16      |
| 540            | 34.60                  | 34.44    | 34.46     | 0.09                      | 0.14     | 0.18      | 0.13                      | 0.16     | 0.20      |
| 1000           | 31.65                  | 31.68    | 31.69     | 0.11                      | 0.19     | 0.26      | 0.16                      | 0.21     | 0.26      |
| 1670           | 40.37                  | 41.65    | 42.90     | 0.19                      | 0.29     | 0.38      | 0.23                      | 0.31     | 0.37      |
| 1810           | 56.94                  | 56.75    | 54.86     | 0.21                      | 0.31     | 0.40      | 0.25                      | 0.33     | 0.40      |
| 2000           | 39.82                  | 38.72    | 38.02     | 0.24                      | 0.36     | 0.45      | 0.28                      | 0.38     | 0.46      |
| 2240           | 33.34                  | 33.42    | 33.51     | 0.30                      | 0.44     | 0.55      | 0.36                      | 0.48     | 0.57      |
| 2250           | 33.36                  | 33.52    | 33.64     | 0.30                      | 0.44     | 0.55      | 0.36                      | 0.48     | 0.57      |
| 2280           | 33.31                  | 33.68    | 34.18     | 0.31                      | 0.45     | 0.57      | 0.37                      | 0.49     | 0.59      |
| 2300           | 33.57                  | 34.04    | 34.81     | 0.31                      | 0.45     | 0.58      | 0.38                      | 0.50     | 0.60      |
| 2450           | 38.00                  | 39.73    | 39.29     | 0.37                      | 0.54     | 0.69      | 0.45                      | 0.59     | 0.72      |
| 2500           | 39.74                  | 38.22    | 35.07     | 0.40                      | 0.58     | 0.74      | 0.47                      | 0.63     | 0.77      |
| 2630           | 28.09                  | 25.36    | 23.10     | 0.48                      | 0.70     | 0.92      | 0.56                      | 0.76     | 0.96      |
| 2700           | 22.32                  | 20.22    | 18.36     | 0.56                      | 0.83     | 1.10      | 0.65                      | 0.89     | 1.15      |
| 2920           | 9.58                   | 8.40     | 7.36      | 1.56                      | 2.24     | 3.04      | 1.68                      | 2.33     | 3.11      |
| 3050           | 4.72                   | 4.02     | 3.53      | 3.79                      | 5.23     | 6.82      | 3.85                      | 5.27     | 6.90      |
| 3100           | 3.41                   | 2.93     | 2.65      | 5.34                      | 7.24     | 9.25      | 5.36                      | 7.24     | 9.33      |
| 3140           | 2.60                   | 2.29     | 2.14      | 6.98                      | 9.31     | 11.76     | 6.93                      | 9.23     | 11.79     |
| 3150           | 2.43                   | 2.16     | 2.03      | 7.45                      | 9.90     | 12.49     | 7.38                      | 9.79     | 12.49     |
| 3180           | 1.98                   | 1.82     | 1.78      | 9.05                      | 11.90    | 14.98     | 8.86                      | 11.63    | 14.78     |
| 3200           | 1.75                   | 1.66     | 1.65      | 10.26                     | 13.41    | 16.85     | 9.96                      | 12.98    | 16.41     |
| 3270           | 1.03                   | 1.25     | 1.34      | 15.78                     | 20.72    | 26.06     | 14.83                     | 18.68    | 22.24     |
| 3300           | 1.03                   | 1.14     | 1.27      | 19.23                     | 25.85    | 28.93     | 17.39                     | 21.03    | 23.02     |
| 3400           | 0.79                   | 0.98     | 1.14      | 29.23                     | 24.13    | 21.63     | 22.76                     | 20.83    | 19.48     |
| 3500           | 0.71                   | 0.91     | 1.08      | 19.66                     | 18.32    | 17.75     | 18.89                     | 17.41    | 16.74     |
| 4000           | 0.58                   | 0.73     | 0.86      | 14.04                     | 14.84    | 15.46     | 14.16                     | 14.78    | 15.18     |
| 4500           | 0.49                   | 0.67     | 0.85      | 16.67                     | 16.36    | 16.14     | 16.92                     | 16.71    | 16.73     |
| 5000           | 0.34                   | 0.50     | 0.68      | 22.97                     | 21.80    | 20.67     | 25.46                     | 23.29    | 22.25     |
| 6000           | 0.13                   | 0.33     | 0.52      | 27.19                     | 27.15    | 27.11     | 35.79                     | 29.16    | 26.89     |
| 6500           | 0.01                   | 0.17     | 0.37      | 25.28                     | 24.32    | 24.04     | 26.90                     | 24.86    | 24.52     |
| 7000           | 0.00                   | 0.18     | 0.38      | 20.41                     | 20.90    | 21.21     | 20.87                     | 21.64    | 22.01     |
| 7500           | 0.08                   | 0.16     | 0.38      | 18.32                     | 18.20    | 17.87     | 18.88                     | 19.03    | 18.95     |
| 8000           | 0.15                   | 0.11     | 0.38      | 16.65                     | 15.96    | 14.97     | 17.10                     | 16.34    | 15.15     |
| 8050           | 0.18                   | 0.10     | 0.35      | 17.58                     | 16.12    | 14.93     | 17.76                     | 16.28    | 14.99     |
| 8100           | 0.20                   | 0.08     | 0.36      | 18.24                     | 16.31    | 15.08     | 18.34                     | 16.35    | 15.00     |
| 8150           | 0.24                   | 0.04     | 0.32      | 18.20                     | 16.58    | 15.28     | 18.74                     | 16.70    | 15.25     |
| 8200           | 0.23                   | 0.04     | 0.29      | 17.85                     | 16.85    | 15.67     | 18.71                     | 17.21    | 15.71     |
| 9000           | 0.29                   | 0.03     | 0.32      | 19.18                     | 20.25    | 21.43     | 17.99                     | 18.35    | 18.48     |
| 9500           | 0.32                   | 0.09     | 1.08      | 17.39                     | 20.02    | 21.91     | 16.13                     | 18.62    | 20.78     |
| 9900           | 0.39                   | 0.10     | 0.18      | 17.99                     | 19.69    | 21.76     | 17.87                     | 19.57    | 22.12     |
| 10000          | 0.37                   | 0.09     | 0.18      | 17.09                     | 19.23    | 21.31     | 17.42                     | 19.66    | 22.64     |
| 11000          | 0.18                   | 0.24     | 0.73      | 16.82                     | 14.97    | 13.19     | 16.14                     | 14.39    | 12.71     |


### Notes

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.  
 B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuits' applicable established test performance criteria and measurement instructions.  
 C. The parts covered by this specification document are subject to Mini-Circuits' standard limited warranty and terms and conditions (collectively, "Standard Terms"). Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at [www.minicircuits.com/MCStore/terms.jsp](http://www.minicircuits.com/MCStore/terms.jsp)




## Typical Performance Curves


### INSERTION LOSS vs. TEMPERATURE



### INPUT RETURN LOSS vs. TEMPERATURE



### OUTPUT RETURN LOSS vs. TEMPERATURE




#### Notes


- Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- Electrical specifications and performance data contained in this specification document are based on Mini-Circuits' applicable established test performance criteria and measurement instructions.
- The parts covered by this specification document are subject to Mini-Circuits' standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at [www.minicircuits.com/MCLStore/terms.jsp](http://www.minicircuits.com/MCLStore/terms.jsp)



### Outline Dimensions



### PCB Land Pattern



Suggested Layout,  
Tolerance to be within  $\pm .002$

| CASE #   | A              | B              | C              | D              | E              | F              | G              | H              | J              | K              | L  | M  | N  | P  | WT. GRAM |
|----------|----------------|----------------|----------------|----------------|----------------|----------------|----------------|----------------|----------------|----------------|----|----|----|----|----------|
| FV1206-1 | .126<br>(3.20) | .063<br>(1.60) | .035<br>(0.89) | .024<br>(0.61) | .022<br>(0.56) | .011<br>(0.28) | .039<br>(0.99) | .024<br>(0.61) | .042<br>(1.07) | .123<br>(3.12) | -- | -- | -- | -- | .020     |

Dimensions are in inches (mm). Tolerances: 2 PL.  $\pm .01$ ; 3 PL.  $\pm .005$

#### Notes:

- Open style, ceramic base.
- Termination finish: **as shown below or indicated on Data Sheet.**  
For RoHS Case Styles: Tin plate over Nickel plate. All models, (+) suffix.  
For RoHS-5 Case Styles: Tin-Lead plate. All models, no (+) suffix.



P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site



Provides ACTUAL Data Instantly From MINI-CIRCUITS At: [www.minicircuits.com](http://www.minicircuits.com)

RF/IF MICROWAVE COMPONENTS

## DEVICE ORIENTATION IN T&R




ILLUSTRATION 1




ILLUSTRATION 2




ILLUSTRATION 3

### Applicable Case Styles

FV1206-1  
FV1206-3

### Applicable Case Styles

FV1206-4  
FV1206-5  
FV1206-6  
FV1206-7  
FV1206-9

### Applicable Case Styles

FV1206-11  
FV1206-12  
GE0805C-18  
NL1008C-6  
NL1008C-7  
NL1008C-9  
NL1008C-10  
NL1008C-12

| Tape Width, mm | Device Cavity Pitch, mm | Reel Size, inches | Devices per Reel                    |      |
|----------------|-------------------------|-------------------|-------------------------------------|------|
| 8              | 4                       | 7                 | Small quantity standards (see note) | 20   |
|                |                         |                   |                                     | 50   |
|                |                         |                   |                                     | 100  |
|                |                         |                   |                                     | 200  |
|                |                         |                   |                                     | 500  |
|                |                         |                   |                                     | 1000 |
|                |                         |                   | Standard                            | 3000 |

Note: Please consult individual model data sheet to determine device per reel availability.

Mini-Circuits carrier tape materials provide protection from ESD (Electro-Static Discharge) during handling and transportation. Tapes are static dissipative and comply with industry standards EIA-481/EIA-541.

Go to: [www.minicircuits.com/pages/pdfs/tape.pdf](http://www.minicircuits.com/pages/pdfs/tape.pdf)




**Distribution Centers NORTH AMERICA** 800-654-7949 • 417-335-5935 • Fax 417-335-5945 • **EUROPE** 44-1252-832600 • Fax 44-1252-837010  
Mini-Circuits ISO 9001 & ISO 14001 Certified

INTERNET <http://www.minicircuits.com>

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661


## THIRD ANGLE PROJECTION



## REVISIONS

| REV | ECN No. | DESCRIPTION           | DATE     | DR | AUTH |
|-----|---------|-----------------------|----------|----|------|
| OR  | M92199  | NEW RELEASE           | 05/24/04 | AV | ABD  |
| A   | M99247  | ADD GROUND PTH        | 06/05    | RZ | RZ   |
| A   | R60782  | ADD GROUND PTH        | 06/05    | RZ | RZ   |
| B   | M102713 | ADDED "...WITH SMOBC" | 01/12/06 | GF | IL   |


SUGGESTED MOUNTING CONFIGURATION  
FOR FV1206-1 CASE STYLE, "pr" PIN CONNECTION.



- NOTE: 1. TRACE WIDTH IS SHOWN FOR ROGERS RO4350B WITH DIELECTRIC THICKNESS .020"  $\pm$  .0015".  
 COPPER: 1/2 OZ. EACH SIDE.  
 FOR OTHER MATERIALS TRACE WIDTH MAY NEED TO BE MODIFIED.
2. BOTTOM SIDE OF THE PCB IS CONTINUOUS GROUND PLANE.



DENOTES PCB COPPER LAYOUT WITH SMOBC (SOLDER MASK OVER BARE COPPER)



DENOTES COPPER LAND PATTERN FREE OF SOLDER MASK

UNLESS OTHERWISE SPECIFIED

INITIALS

DATE

DIMENSIONS ARE IN INCHES

TOLERANCES ON:

2 PL DECIMALS  $\pm$ 3 PL DECIMALS  $\pm$  .005ANGLES  $\pm$ FRACTIONS  $\pm$ 

DRAWN

AV

05/03/04

CHECKED

IL

05/24/04

APPROVED

ABD

05/24/04

Mini-Circuits®

THIS DOCUMENT AND ITS CONTENTS ARE THE PROPERTY OF MINI-CIRCUITS. EXCEPT FOR USE EXPRESSLY GRANTED, IN WRITING, TO ITS VENDORS, VENDEE AND THE UNITED STATES GOVERNMENT, MINI-CIRCUITS RESERVES ALL PROPRIETARY DESIGN, USE, MANUFACTURING AND REPRODUCTION RIGHTS THERETO. THESE CONTENTS SHALL NOT BE USED, DUPLICATED OR DISCLOSED TO ANY OUTSIDE PARTY, IN WHOLE OR IN PART, WITHOUT WRITTEN PERMISSION OF MINI-CIRCUITS.

ASHEETA1.DWG REV:A DATE:01/12/95



Mini-Circuits®

 13 Neptune Avenue  
 Brooklyn NY 11235

PL, pr, FV1206-1, HFCN, TB-285

SIZE

A

CODE IDENT

15542

DRAWING NO:

98-PL-158

REV:

B

FILE:

98PL158



SCALE:

12:1

SHEET:

1 OF 1

# Evaluation Board and Circuit



Schematic Diagram

## Notes:

1. SMA Female connectors.
2. PCB Material: Rogers R04350 or equivalent,  
Dielectric Constant=3.5, Thickness=.020 inch.

 **Mini-Circuits®**



All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

| Specification              | Test/Inspection Condition                                                           | Reference/Spec                                                                                       |
|----------------------------|-------------------------------------------------------------------------------------|------------------------------------------------------------------------------------------------------|
| Operating Temperature      | -55° to 100°C<br>Ambient Environment                                                | Individual Model Data Sheet                                                                          |
| Storage Temperature        | -55° to 100° C<br>Ambient Environment                                               | Individual Model Data Sheet                                                                          |
| Humidity                   | 90 to 95% RH, 240 hours, 50°C                                                       | MIL-STD-202, Method 103, Condition A, Except 50°C and end-point electrical test done within 12 hours |
| Solder Reflow Heat         | Sn-Pb Eutetic Process: 225°C peak<br>Pb-Free Process 245° - 250°C peak              | J-STD-020, Table 4-1, 4-2 and 5-2, Figure 5-1                                                        |
| Solderability              | 10X Magnification                                                                   | J-STD-002, Para 4.2.5, Test S, 95% Coverage                                                          |
| Vibration (High Frequency) | 20g peak, 10-2000 Hz, 12 times in each of three perpendicular directions (total 36) | MIL-STD-202, Method 204, Condition D                                                                 |
| Mechanical Shock           | 50g, 11 ms, 1/2-sine, 18 shocks: 3 each direction, each of 3 axes                   | MIL-STD-202, Method 213, Condition A                                                                 |