

High Pass Filter

SMT

HFCV-ED13423/4

Important Note

This model has been designed, built and tested in our engineering department. Performance data represents model capability. At present it is a non-catalog model. On request, we can supply a final specification sheet, part number and price/delivery information.




Please click "Back", and then click "Contact Us" for Applications support.

CASE STYLE : JV1210C

| ELECTRICAL SPECIFICATIONS 50Ω @ +25°C | | | | | | | |
|---------------------------------------|------------------|-------|-----------------|------|------|------|-------|
| Parameters | | F# | Frequency (MHz) | Min. | Typ. | Max. | Units |
| Stop Band | Insertion Loss | DC-F1 | DC-80 | 20 | -- | -- | dB |
| | | DC-F2 | DC-115 | 15 | -- | -- | dB |
| | Frequency cutoff | F3 | 132 | -- | 3 | -- | dB |
| | VSWR | DC-F2 | DC-115 | -- | 20 | -- | :1 |
| Pass Band | Insertion Loss | F5-F6 | 145-1050 | -- | -- | 1.5 | dB |
| | | F4-F7 | 140-1150 | -- | -- | 2 | dB |
| | VSWR | F4-F7 | 140-1150 | -- | 1.5 | -- | :1 |

| MAXIMUM RATINGS | |
|-----------------------|----------------|
| Operating Temperature | -55°C to 100°C |
| Storage Temperature | -55°C to 100°C |
| RF Power Input | 8.5W max. |

Functional Schematic



| PIN CONNECTIONS | |
|-----------------|-----|
| RF IN | 1 |
| RF OUT | 3 |
| GROUND | 2,4 |



High Pass Filter

HFCV-ED13423/4

Typical Performance Data


| FREQUENCY (MHz) | INSERTION LOSS (dB) | RETURN LOSS (dB) |
|--------------------|---------------------------|------------------------|
| 0.3 | 63.96 | 0.04 |
| 1.0 | 53.29 | 0.00 |
| 10.0 | 33.38 | 0.00 |
| 40.0 | 23.59 | 0.06 |
| 70.0 | 28.65 | 0.20 |
| 100.0 | 20.05 | 0.74 |
| 101.0 | 19.73 | 0.78 |
| 102.0 | 19.46 | 0.82 |
| 103.0 | 19.23 | 0.87 |
| 104.0 | 19.06 | 0.91 |
| 105.0 | 18.95 | 0.96 |
| 106.0 | 18.90 | 1.02 |
| 107.0 | 18.92 | 1.07 |
| 108.0 | 19.02 | 1.14 |
| 109.0 | 19.21 | 1.20 |
| 110.0 | 19.50 | 1.28 |
| 115.0 | 22.35 | 1.80 |
| 120.0 | 15.57 | 2.98 |
| 125.0 | 7.42 | 6.11 |
| 130.0 | 3.50 | 13.18 |
| 135.0 | 2.03 | 29.70 |
| 140.0 | 1.46 | 24.91 |
| 141.0 | 1.39 | 23.61 |
| 145.0 | 1.17 | 21.29 |
| 146.0 | 1.13 | 21.09 |
| 147.0 | 1.09 | 20.98 |
| 148.0 | 1.06 | 20.94 |
| 149.0 | 1.02 | 20.97 |
| 150.0 | 0.99 | 21.06 |
| 151.0 | 0.96 | 21.19 |
| 152.0 | 0.94 | 21.36 |
| 153.0 | 0.91 | 21.57 |
| 154.0 | 0.89 | 21.82 |
| 155.0 | 0.86 | 22.08 |
| 156.0 | 0.84 | 22.37 |
| 157.0 | 0.82 | 22.69 |
| 158.0 | 0.80 | 23.04 |
| 159.0 | 0.79 | 23.40 |
| 160.0 | 0.77 | 23.78 |
| 180.0 | 0.56 | 26.62 |
| 200.0 | 0.48 | 21.52 |
| 400.0 | 0.37 | 18.85 |
| 600.0 | 0.39 | 20.64 |
| 800.0 | 0.49 | 18.09 |
| 1000.0 | 0.80 | 12.73 |
| 1110.0 | 1.18 | 9.66 |
| 1120.0 | 1.23 | 9.39 |
| 1130.0 | 1.28 | 9.12 |
| 1140.0 | 1.33 | 8.86 |
| 1150.0 | 1.38 | 8.61 |

Typical Performance Curves




Outline Dimensions

JV1210C



PCB Land Pattern



Suggested Layout,
Tolerance to be within $\pm .002$

| CASE # | A | B | C | D | E | F | G | H | J | K | L | M | N | P | Q | WT. GRAM |
|---------|---------------|---------------|---------------|--------------|--------------|--------------|---------------|---------------|----------------|----------------|----------------|---------------|---------------|--------------|--------------|----------|
| JV1210C | .126 (3.2) | .098 (2.5) | .059 (1.5) | .012 (.3) | .024 (.6) | .016 (.4) | .209 (5.3) | .091 (2.3) | .128 (3.25) | .175 (4.45) | .057 (1.45) | .059 (1.5) | .059 (1.5) | .028 (.7) | .020 (.5) | .03 |

Dimensions are in inches (mm). Tolerances: 2 Pl. $\pm .01$; 3 Pl. $\pm .005$

Notes:

1. Open style, ceramic base.
2. Termination finish: **as shown below or indicated on Data Sheet.**
For RoHS Case Styles: Tin plate over Nickel plate. All models, (+) suffix.
For RoHS-5 Case Styles: Tin-Lead plate. All models, no (+) suffix.
3. Pad tolerance is non-cumulative. Minimum spacing between each pad is .004.



P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site



The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: www.minicircuits.com

RF/IF MICROWAVE COMPONENTS

Tape & Reel Packaging TR-F74

DEVICE ORIENTATION IN T&R




ILLUSTRATION 1

Applicable Case Styles

GE0805C-1
GE0805C-1AP
JV1210C-1
GU2939




ILLUSTRATION 2

Applicable Case Styles

JV1210C
JV1210C-2
JV1210C-3
JV1210C-4
JV1210C-5
JV1210C-6
JV1210C-11

ILLUSTRATION 3

Applicable Case Styles

JC0603C-8
JC0603C-9
JV1210C-7
JV1210C-8
JV1210C-9
JV1210C-10
JV1210C-13
GE0805C-13
GE0805C-19
GE0805C-20

| Tape Width, mm | Device Cavity Pitch, mm | Real Size, inches | Devices per Reel | |
|-------------------|----------------------------|----------------------|--|------|
| 8 | 4 | 7 | Small quantity standards (see note) | 20 |
| | | | | 50 |
| | | | | 100 |
| | | | | 200 |
| | | | | 500 |
| | | | | 1000 |
| | | | Standard | 2000 |
| | | | | 4000 |

Note: Small reel availability varies by model. Refer to pricing and availability on individual model dashboard.

Mini-Circuits carrier tape materials provide protection from ESD (Electro-Static Discharge) during handling and transportation. Tapes are static dissipative and comply with industry standards EIA-481/EIA-541.

Go to: www.minicircuits.com/pages/pdfs/tape.pdf




Distribution Centers NORTH AMERICA 800-654-7949 • 417-335-5935 • Fax 417-335-5945 • EUROPE 44-1252-832600 • Fax 44-1252-837010

Mini-Circuits ISO 9001 & ISO 14001 Certified


INTERNET <http://www.minicircuits.com>

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661



| REVISIONS | | | | | |
|-----------|---------|-------------|----------|----|------|
| REV OR | ECN No. | DESCRIPTION | DATE | DR | AUTH |
| | M123026 | NEW RELEASE | 06/08/09 | PW | ABD |
| | | | | | |
| | | | | | |

**SUGGESTED MOUNTING CONFIGURATION
FOR JV1210C CASE STYLE, "04FL01" PIN CONNECTIONS**




NOTES:

1. COPLANAR WAVEGUIDE PARAMETERS ARE SHOWN FOR ROGERS RO4350B WITH DIELECTRIC THICKNESS 0.020" ± 0.0015"; COPPER: 1/2 OZ. EACH SIDE. FOR OTHER MATERIALS TRACE WIDTH AND GAP MAY NEED TO BE MODIFIED.
2. BOTTOM SIDE OF THE PCB IS CONTINUOUS GROUND PLANE.



DENOTES PCB COPPER LAYOUT WITH SMOBC (SOLDER MASK OVER BARE COPPER)



DENOTES COPPER LAND PATTERN FREE OF SOLDER MASK

| UNLESS OTHERWISE SPECIFIED | INITIALS | DATE |
|----------------------------|--------------|----------|
| DIMENSIONS ARE IN INCHES | DRAWN PW | 05/27/09 |
| TOLERANCES ON: | CHECKED IL | 06/04/09 |
| 2 PL DECIMALS ± | APPROVED ABD | 06/08/09 |
| 3 PL DECIMALS ± .005 | | |
| ANGLES ± | | |
| FRACTIONS ± | | |



Mini-Circuits®


13 Neptune Avenue
Brooklyn NY 11235

PL, 04FL01, JV1210C, LFCF, TB-526+


Mini-Circuits®
THIS DOCUMENT AND ITS CONTENTS ARE THE PROPERTY OF MINI-CIRCUITS. EXCEPT FOR USE EXPRESSLY GRANTED, IN WRITING, TO ITS VENDORS, VENDEE AND THE UNITED STATES GOVERNMENT, MINI-CIRCUITS RESERVES ALL PROPRIETARY DESIGN, USE, MANUFACTURING AND REPRODUCTION RIGHTS THERETO. THESE CONTENTS SHALL NOT BE USED, DUPLICATED OR DISCLOSED TO ANY OUTSIDE PARTY, IN WHOLE OR IN PART, WITHOUT WRITTEN PERMISSION OF MINI-CIRCUITS.

| | | | |
|------------------|---------------------|--------------------------|------------|
| SIZE A | CODE IDENT 15542 | DRAWING NO: 98-PL-307 | REV: OR |
| FILE: 98PL307 | SCALE: 10:1 | SHEET: 1 OF 1 | |

Evaluation Board and Circuit




TB-526+



Schematic Diagram

Notes:

1. 50 Ohm SMA Female connectors.
2. PCB Material: R04350 or equivalent,
Dielectric Constant=3.5, Thickness=.020 inch.

 Mini-Circuits®

All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

| Specification | Test/Inspection Condition | Reference/Spec |
|----------------------------|---|--|
| Operating Temperature | -55° to 100°C Ambient Environment | Individual Model Data Sheet |
| Storage Temperature | -55° to 100° C Ambient Environment | Individual Model Data Sheet |
| Humidity | 90 to 95% RH, 240 hours, 50°C | MIL-STD-202, Method 103, Condition A, Except 50°C and end-point electrical test done within 12 hours |
| Solder Reflow Heat | Sn-Pb Eutetic Process: 225°C peak Pb-Free Process 245° - 250°C peak | J-STD-020, Table 4-1, 4-2 and 5-2, Figure 5-1 |
| Solderability | 10X Magnification | J-STD-002, Para 4.2.5, Test S, 95% Coverage |
| Vibration (High Frequency) | 20g peak, 10-2000 Hz, 12 times in each of three perpendicular directions (total 36) | MIL-STD-202, Method 204, Condition D |
| Mechanical Shock | 50g, 11 ms, 1/2-sine, 18 shocks: 3 each direction, each of 3 axes | MIL-STD-202, Method 213, Condition A |