

Engineering Development Model

Bi-Directional Coupler

JC-ED12981/1

Important Note

This model has been designed, built and tested in our engineering department. Performance data represents model capability. At present it is a non-catalog model. On request, we can supply a final specification sheet, part number and price/delivery information.



Please click "Back", and then click "Contact Us" for Applications support.

CASE STYLE : 99-01-508


ELECTRICAL SPECIFICATIONS 50Ω @ +25°C				
Parameter		Min.	Typ.	Max. Units
Frequency		3		1200 MHz
Coupling	Nominal		7.5 ± 0.5	dB
	Flatness		± 0.25	dB
Mainline Loss **	3-30 MHz		1.50	dB
	30-600 MHz		1.60	dB
	600-1200 MHz		2.40	dB
Directivity	3-30 MHz		25	dB
	30-600 MHz		21	dB
	600-1200 MHz		11	dB
VSWR	3-1200 MHz		1.32	(:1)
Power Input	3-1200 MHz			0.25 W

Note: ** Mainline loss includes theoretical coupled power loss of 0.85 dB at 7.5 dB coupling.

MAXIMUM RATINGS	
Operating Temperature	-20°C to 85°C
Storage Temperature	-55°C to 100°C

PIN CONNECTIONS	
INPUT	1
OUTPUT	6
COUPLED FORWARD	3
COUPLED REVERSE	4
NOT USED	5
GROUND	2

Electrical Schematic



* ELECTRICAL SCHEMATIC IS FOR BI-DIRECTIONAL COUPLER WITH INTERNAL TRANSFORMER(S) THAT ROUTES DC FROM RF PORTS TO GROUND.

Bi-Directional Coupler

JC-ED12981/1





Typical Performance Data

FREQ. (MHz)	INSERTION LOSS (dB) IN-OUT	COUPLING (dB)		DIRECTIVITY (dB)		RETURN LOSS (dB)			
		IN-FWD	OUT-REV	IN-REV	OUT-FWD	IN	OUT	FWD	REV
1.0	1.66	7.37	8.68	11.29	14.00	12.61	11.19	9.18	8.78
3.0	1.62	7.49	8.39	12.39	20.60	17.07	19.59	13.19	16.89
5.0	1.57	7.47	8.25	12.59	22.59	17.95	21.86	14.00	19.63
7.0	1.53	7.44	8.15	12.71	23.78	18.46	22.71	14.46	21.29
9.0	1.50	7.42	8.08	12.81	24.67	18.80	22.99	14.79	22.51
10.0	1.49	7.41	8.05	12.84	25.07	18.91	23.04	14.94	23.02
15.0	1.44	7.38	7.94	12.99	26.54	19.44	23.01	15.44	25.02
20.0	1.41	7.37	7.87	13.05	27.58	19.81	22.78	15.74	26.37
25.0	1.39	7.36	7.83	13.10	28.34	20.03	22.59	15.96	27.32
30.0	1.38	7.35	7.80	13.14	28.91	20.14	22.46	16.11	27.93
50.0	1.37	7.35	7.75	13.21	30.02	20.43	21.89	16.52	28.80
100.0	1.38	7.37	7.72	13.20	28.78	20.16	20.90	16.80	28.56
150.0	1.41	7.40	7.72	13.13	26.89	19.46	19.97	16.88	27.43
200.0	1.45	7.43	7.72	13.05	24.65	18.47	19.06	16.82	26.32
250.0	1.49	7.45	7.72	12.91	22.81	17.49	18.20	16.60	25.22
300.0	1.53	7.47	7.73	12.74	21.21	16.56	17.36	16.50	24.17
350.0	1.58	7.50	7.73	12.60	19.70	15.73	16.66	16.20	23.48
400.0	1.63	7.52	7.74	12.40	18.44	15.00	15.97	16.08	22.46
450.0	1.69	7.54	7.76	12.14	17.20	14.35	15.45	15.78	22.03
500.0	1.77	7.53	7.80	11.79	16.17	13.74	14.86	15.56	21.07
550.0	1.82	7.56	7.75	11.65	15.33	13.23	14.31	15.36	20.53
600.0	1.89	7.57	7.75	11.46	14.63	12.80	13.84	15.17	19.75
650.0	1.97	7.59	7.75	11.18	13.88	12.39	13.44	15.07	19.45
700.0	2.04	7.60	7.76	10.93	13.18	12.05	13.05	14.80	18.79
750.0	2.13	7.61	7.76	10.66	12.64	11.76	12.71	14.83	18.45
800.0	2.21	7.63	7.77	10.37	11.99	11.46	12.37	14.53	17.92
850.0	2.31	7.63	7.76	10.09	11.57	11.24	12.06	14.58	17.46
900.0	2.40	7.66	7.76	9.82	11.00	11.04	11.83	14.37	17.18
950.0	2.50	7.67	7.76	9.53	10.63	10.84	11.54	14.39	16.63
1000.0	2.60	7.70	7.75	9.29	10.11	10.68	11.36	14.27	16.52
1100.0	2.83	7.75	7.71	8.79	9.31	10.37	11.01	14.24	15.96
1200.0	3.09	7.82	7.62	8.39	8.58	10.15	10.84	14.14	15.48
1300.0	3.39	7.91	7.47	8.13	7.88	9.89	10.81	14.03	15.16
1400.0	3.74	8.04	7.24	8.07	7.25	9.61	10.99	13.76	14.96
1500.0	4.16	8.22	6.93	8.24	6.72	9.26	11.40	13.37	15.00
1600.0	4.64	8.46	6.59	8.66	6.30	8.83	12.10	12.81	15.19
1700.0	5.23	8.76	6.24	9.21	6.03	8.28	13.14	12.21	15.69
1800.0	5.90	9.12	5.91	10.03	6.05	7.75	14.60	11.62	16.17
1900.0	6.66	9.50	5.62	11.01	6.34	7.26	16.69	11.23	16.81
2000.0	7.55	9.94	5.43	12.16	6.95	6.90	19.78	11.06	17.38

Bi-Directional Coupler

Typical Performance Curves

JC-ED12981/1





All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

Specification	Test/Inspection Condition	Reference/Spec
Operating Temperature	-20° to 85°C Ambient Environment	Individual Model Data Sheet
Storage Temperature	-55° to 100° C Ambient Environment	Individual Model Data Sheet
Humidity	90 to 95% RH, 240 hours, 50°C	MIL-STD-202, Method 103, Condition A, Except 50°C and end-point electrical test done within 12 hours
Thermal Shock	-55° to 100°C, 100 cycles	MIL-STD-202, Method 107, Condition A-3, except +100°C
Solder Reflow Heat	Sn-Pb Eutetic Process: 225°C peak Pb-Free Process 245° - 250°C peak	J-STD-020, Table 4-1, 4-2 and 5-2, Figure 5-1
Solderability	10X Magnification	J-STD-002, 95% Coverage
Vibration (High Frequency)	20g peak, 10-2000 Hz, 12 times in each of three perpendicular directions (total 36)	MIL-STD-202, Method 204, Condition D
Mechanical Shock	50g, 11 ms, 1/2-sine, 18 shocks: 3 each direction, each of 3 axes	MIL-STD-202, Method 213, Condition A
Marking Resistance to Solvents	Isopropyl alcohol + mineral spirits at 25°C; terpene defluxer at 25°C; distilled water + proylene glycol monomethyl ether + monoethanolamine at 63°C to 70°C	MIL-STD-202, Method 215