

Non-Catalog Model

Modulator

JCBM-1000DR

Important Note

This is a non-catalog model and can be manufactured on specific request. Pricing and delivery information can be supplied upon request.



CASE STYLE: BG291

Please click "Back", and then click "Contact Us" for Applications support.

ELECTRICAL SPECIFICATIONS 50Ω @ +25°C

Parameter	Min.	Typ.	Max.	Units
Frequency	LO (f_L to f_U)	500	1000	MHz
	RF (f_L to f_U)	500	1000	MHz
	Baseband	DC	20	MHz
Insertion Loss		2.7	5.0	dB
Amplitude Unbalance		0.2	0.6	dB
Phase Unbalance Rel. to 180°		±1	±6	Degrees
Supply Current at ±5.0V		12	20	mA

MAXIMUM RATINGS

Operating Temperature	-20°C to 85°C
Storage Temperature	-55°C to 100°C

PIN CONNECTIONS



LO (carrier)	8
RF (signal)	1
Baseband	14
+5V	12
-5V	3
Ground Extention	all others

Typical Performance Data

FREQUENCY (MHz)	INSERTION LOSS (dB)		AMPLITUDE UNBALANCE (dB)	PHASE UNBALANCE* (deg.)
	S-1 (LO)	S-1 (HI)		
500.0	2.38	2.72	0.34	1.27
520.0	2.51	2.84	0.33	1.42
540.0	2.63	2.97	0.34	1.60
560.0	2.59	2.92	0.32	1.61
580.0	2.62	2.92	0.30	1.83
600.0	2.90	3.20	0.30	1.99
620.0	2.89	3.18	0.28	2.00
640.0	2.97	3.24	0.27	2.10
660.0	2.96	3.22	0.26	2.22
680.0	3.17	3.41	0.24	2.35
700.0	3.23	3.46	0.23	2.29
720.0	3.26	3.48	0.22	2.36
740.0	3.40	3.61	0.21	2.44
760.0	3.52	3.72	0.20	2.44
780.0	3.54	3.72	0.19	2.44
800.0	3.46	3.62	0.16	2.46
820.0	3.81	3.95	0.15	2.50
840.0	3.90	4.03	0.14	2.45
860.0	3.89	4.01	0.12	2.48
880.0	3.77	3.88	0.11	2.38
900.0	4.00	4.08	0.09	2.32
920.0	4.37	4.46	0.09	2.32
940.0	4.14	4.21	0.07	2.27
960.0	4.15	4.20	0.05	2.18
980.0	4.25	4.28	0.03	2.10
1000.0	4.65	4.66	0.01	2.06

* Phase Unbalance is relative to 180°



Typical Performance Curves



* Phase Unbalance is relative to 180°

Outline Dimensions

BG291



 DENOTES METALLIZATION

Weight: 4 gram

Dimensions are in inches[mm]. Tolerances: 2PL $\pm$ 0.03[0.76]; 3 PL $\pm$ 0.015 [0.381] inches[mm], unless otherwise specified

Notes:

1. Case material: Copper-Nickel alloy.
2. Base material: Printed wiring laminate.
3. Termination finish:

For RoHS Case Styles: Tin plate over Nickel plate. All models, (+) suffix.

For RoHS-5 Case Styles: Tin-Lead plate. All models, no (+) suffix.

Mini-Circuits®
ISO 9001 ISO 14001 CERTIFIED

ALL NEW
minicircuits.com


P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site



The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: www.minicircuits.com

RF/IF MICROWAVE COMPONENTS

Tape & Reel Packaging TR-F21



Tape Width, mm	Device Cavity Pitch, mm	Reel Size, inches	Devices per Reel
32	32	13	200

Mini-Circuits carrier tape materials provide protection from ESD (Electro-Static Discharge) during handling and transportation. Tapes are static dissipative and comply with industry standards EIA-481/EIA-541.

Go to: www.minicircuits.com/pages/pdfs/tape.pdf



INTERNET <http://www.minicircuits.com>
P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661
Distribution Centers NORTH AMERICA 800-654-7949 • 417-335-5935 • Fax 417-335-5945 • EUROPE 44-1252-832600 • Fax 44-1252-837010
Mini-Circuits ISO 9001 & ISO 14001 Certified



All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

Specification	Test/Inspection Condition	Reference/Spec
Operating Temperature	-20° to 85°C Ambient Environment	Individual Model Data Sheet
Storage Temperature	-55° to 100° C Ambient Environment	Individual Model Data Sheet
Humidity	90 to 95% RH, 240 hours, 50°C	MIL-STD-202, Method 103, Condition A, Except 50°C and end-point electrical test done within 12 hours
Thermal Shock	-55° to 100°C, 100 cycles	MIL-STD-202, Method 107, Condition A-3, except +100°C
Solder Reflow Heat	Sn-Pb Eutetic Process: 225°C peak Pb-Free Process 245° - 250°C peak	J-STD-020, Table 4-1, 4-2 and 5-2, Figure 5-1
Solderability	10X Magnification	J-STD-002, 95% Coverage
Vibration (High Frequency)	20g peak, 10-2000 Hz, 12 times in each of three perpendicular directions (total 36)	MIL-STD-202, Method 204, Condition D
Mechanical Shock	50g, 11 ms, 1/2-sine, 18 shocks: 3 each direction, each of 3 axes	MIL-STD-202, Method 213, Condition A
Marking Resistance to Solvents	Isopropyl alcohol + mineral spirits at 25°C; terpene defluxer at 25°C; distilled water + proylene glycol monomethyl ether + monoethanolamine at 63°C to 70°C	MIL-STD-202, Method 215