

Surface Mount Directional Coupler

50Ω 50 to 1500 MHz


Maximum Ratings

Operating Temperature	-40°C to 85°C
Storage Temperature	-55°C to 100°C
Permanent damage may occur if any of these limits are exceeded.	

Pin Connections

INPUT	1
OUTPUT	6
COUPLED	3
GROUND	2,5
50 OHM TERM EXTERNAL	4

Outline Drawing




Outline Dimensions (inch mm)

A	B	C	D	E	F	G
.280	.310	--	.100	.225	.055	.100
7.11	7.87	--	2.54	5.72	1.40	2.54

H	J	K	L	wt
.047	.065	.065	.300	grams
1.19	1.65	1.65	7.62	0.45

Demo Board MCL P/N: TB-176 Suggested PCB Layout (PL-041)



- NOTES: 1. TRACE WIDTH IS SHOWN FOR ROGERS RO4350B WITH DIELECTRIC THICKNESS .030" ± .002"; COPPER: 1/2 OZ. EACH SIDE. FOR OTHER MATERIALS TRACE WIDTH MAY NEED TO BE MODIFIED.
2. BOTTOM SIDE OF THE PCB IS CONTINUOUS GROUND PLANE.
3. DENOTES PCB COPPER LAYOUT WITH SMOBC (SOLDER MASK OVER BARE COPPER)
4. DENOTES COPPER LAND PATTERN FREE OF SOLDER MASK

Notes

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp

Features

- wideband, 50 to 1500 MHz
- low mainline loss, 0.5 dB typ.
- excellent solderability

Applications

- VHF/UHF
- satellite distribution
- cellular
- ISM/GSM

JDC-20-5+
JDC-20-5



Generic photo used for illustration purposes only

CASE STYLE: BH292

+RoHS Compliant

The +Suffix identifies RoHS Compliance. See our web site for RoHS Compliance methodologies and qualifications

Directional Coupler Electrical Specifications




FREQ. (MHz)	COUPLING (dB)		MAINLINE LOSS¹ (dB)						DIRECTIVITY (dB)						VSWR (:1)	POWER INPUT, W	
			L		M		U		L		M		U				
	f _L -f _U	Nom.	Flatness	Typ.	Max.	Typ.	Max.	Typ.	Max.	Typ.	Min.	Typ.	Min.	Typ.	Min.	Typ.	Max.
50-1500	20.5±0.5	±0.75	0.4	0.8	0.5	0.9	1.0	1.5	25	18	22	16	20	13	1.2	0.5	0.5

L = 50-500 MHz M = 500-750 MHz U = 750-1500 MHz


1. Mainline loss includes theoretical power loss at coupled port.

Typical Performance Data

Frequency (MHz)	Mainline Loss (dB) In-Out	Coupling (dB) In-Cpl	Directivity (dB)	Return Loss (dB)		
				In	Out	Cpl
50.00	0.35	20.55	24.91	29.45	28.54	26.32
100.00	0.36	20.62	25.28	30.98	30.40	29.94
300.00	0.45	20.74	27.95	29.40	28.96	30.58
600.00	0.51	20.63	34.60	26.50	25.05	27.36
900.00	0.63	20.46	27.05	25.05	22.25	24.18
1000.00	0.68	20.37	25.02	24.77	21.36	22.99
1200.00	0.88	20.20	22.37	24.24	19.64	20.77
1320.00	0.91	20.12	21.35	24.06	18.68	19.46
1400.00	0.98	20.06	20.97	23.74	17.96	18.59
1500.00	1.08	20.07	20.69	23.62	17.22	17.51



Electrical Schematic



* ELECTRICAL SCHEMATIC IS FOR DIRECTIONAL COUPLER WITH INTERNAL TRANSFORMER(S) AND EXTERNAL TERMINATION.



www.minicircuits.com P.O. Box 350166, Brooklyn, NY 11235-0003 (718) 934-4500 sales@minicircuits.com

REV. F
M151107
JDC-20-5
WZ/TD/CP/AM
200413

Directional Coupler

JDC-20-5

Typical Performance Data

TEST CONDITIONS: INPUT POWER =0 dBm @Temperature = +25°C

FREQUENCY (MHz)	INSERTION LOSS (dB)	COUPLING LOSS (dB)	DIRECTIVITY (dB)	RETURN LOSS		
				IN	OUT	CPL
50	0.40	20.43	30.42	29.22	30.49	28.10
75	0.40	20.49	30.59	30.66	32.00	29.90
100	0.40	20.53	30.78	31.48	33.07	31.32
125	0.40	20.57	31.10	32.30	33.82	32.53
150	0.41	20.60	31.30	32.87	34.43	33.70
175	0.42	20.62	31.63	33.14	34.86	34.80
200	0.42	20.64	31.82	33.41	35.13	35.92
250	0.44	20.68	32.17	33.83	35.53	38.35
300	0.46	20.71	32.17	33.58	35.35	41.17
350	0.48	20.73	31.83	33.55	35.51	44.62
400	0.49	20.75	30.69	33.01	35.39	46.19
425	0.50	20.75	29.93	32.79	35.22	45.14
450	0.51	20.75	29.36	32.62	35.07	43.52
475	0.52	20.76	28.46	32.29	35.09	41.86
500	0.53	20.77	27.83	31.99	35.00	40.06
525	0.54	20.76	27.09	31.67	34.88	38.51
550	0.55	20.75	26.40	31.45	34.74	37.15
575	0.57	20.74	25.81	31.09	34.71	35.92
600	0.57	20.73	25.12	30.66	34.56	34.77
650	0.60	20.72	23.95	30.08	34.34	32.87
700	0.63	20.71	22.59	29.30	34.15	31.22
725	0.63	20.69	22.33	29.11	34.54	30.46
750	0.64	20.69	21.69	28.93	34.40	29.72
775	0.66	20.65	21.46	28.63	34.51	29.04
800	0.67	20.62	21.21	28.41	34.74	28.43
850	0.69	20.59	20.25	27.71	34.54	27.23
900	0.71	20.51	19.96	27.30	34.98	26.20
950	0.74	20.48	19.26	26.80	34.93	25.19
1000	0.76	20.42	18.83	26.42	35.34	24.26
1050	0.79	20.36	18.56	26.02	35.31	23.40
1100	0.81	20.30	18.35	25.70	35.58	22.57
1150	0.84	20.25	18.13	25.33	35.68	21.80
1200	0.87	20.21	17.87	25.03	35.85	21.03
1250	0.90	20.15	17.89	24.75	36.16	20.31
1300	0.93	20.09	18.11	24.37	36.23	19.65
1350	0.96	20.10	18.00	24.16	36.56	18.98
1400	0.99	20.06	18.10	23.89	36.97	18.31
1425	1.00	20.04	18.29	23.82	37.20	17.98
1450	1.02	20.05	18.48	23.70	37.11	17.69
1475	1.03	20.01	18.79	23.53	37.06	17.37
1500	1.05	20.02	18.88	23.38	36.54	17.06

REV. X1
JDC-20-5
090830
Page 1 of 3



IF/RF MICROWAVE COMPONENTS • ISO 9001 ISO 14001 AS9100 CERTIFIED RoHS compliant

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661



The Design Engineers Search Engine finds the model you need, Instantly • For detailed performance specs & shopping online see



Directional Coupler

JDC-20-5

Typical Performance Data

TEST CONDITIONS: INPUT POWER =0 dBm @Temperature = -40°C

FREQUENCY (MHz)	INSERTION LOSS (dB)	COUPLING LOSS (dB)	DIRECTIVITY (dB)	RETURN LOSS		
				IN	OUT	CPL
50	0.35	20.41	28.99	30.42	31.63	29.65
75	0.35	20.47	28.87	32.08	33.20	31.33
100	0.36	20.50	28.87	32.78	33.90	32.19
125	0.36	20.53	28.87	33.11	33.85	33.28
150	0.37	20.55	28.88	32.93	33.46	35.00
175	0.37	20.57	28.89	32.45	33.02	36.85
200	0.38	20.57	28.91	32.09	32.60	37.92
250	0.39	20.59	28.95	31.86	32.34	39.23
300	0.41	20.59	28.89	31.66	32.30	42.82
350	0.42	20.59	28.62	31.71	32.56	44.47
400	0.44	20.57	27.97	31.07	32.33	46.11
425	0.45	20.56	27.52	30.70	32.02	45.84
450	0.46	20.54	27.16	30.38	31.75	44.11
475	0.47	20.54	26.59	29.99	31.55	42.66
500	0.48	20.53	26.21	29.62	31.28	41.67
525	0.49	20.51	25.90	29.37	31.12	40.55
550	0.50	20.49	25.40	29.17	30.91	39.06
575	0.51	20.48	24.96	28.88	30.90	37.64
600	0.52	20.45	24.54	28.56	30.78	36.53
650	0.54	20.42	23.74	28.02	30.46	35.18
700	0.56	20.36	22.99	27.44	30.25	33.33
725	0.57	20.33	22.69	27.10	30.24	32.48
750	0.59	20.31	22.05	26.90	30.03	31.82
775	0.61	20.31	21.00	26.60	29.78	31.14
800	0.62	20.29	21.32	26.29	30.07	30.42
850	0.63	20.19	21.04	26.09	30.11	29.05
900	0.65	20.13	20.57	25.63	30.21	27.85
950	0.68	20.06	20.15	25.26	30.23	26.78
1000	0.71	20.01	19.81	24.83	30.34	25.70
1050	0.74	19.95	19.47	24.43	30.14	24.71
1100	0.77	19.89	19.24	24.21	30.16	23.76
1150	0.80	19.84	19.07	23.97	30.17	22.96
1200	0.82	19.79	19.06	23.66	30.13	22.16
1250	0.86	19.72	19.09	23.34	30.12	21.32
1300	0.89	19.68	19.42	22.91	30.08	20.57
1350	0.93	19.67	19.44	22.37	29.72	19.83
1400	0.96	19.79	19.15	22.40	31.34	19.01
1425	0.96	19.70	19.98	22.35	31.62	18.75
1450	0.98	19.69	20.31	22.25	31.43	18.43
1475	1.00	19.66	20.52	22.10	31.38	18.09
1500	1.01	19.66	20.96	22.02	31.21	17.77

REV. X1
JDC-20-5
090830
Page 2 of 3



Mini-Circuits®
IF/RF MICROWAVE COMPONENTS • ISO 9001 ISO 14001 AS9100 CERTIFIED • RoHS compliant

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661

The Design Engineers Search Engine finds the model you need, Instantly • For detailed performance specs & shopping online see



Directional Coupler

JDC-20-5

Typical Performance Data

TEST CONDITIONS: INPUT POWER =0 dBm @Temperature = -85°C

FREQUENCY (MHz)	INSERTION LOSS (dB)	COUPLIN LOSS (dB)	DIRECTIVITY (dB)	RETURN LOSS		
				IN	OUT	CPL
50	0.45	20.46	31.45	27.75	28.97	26.22
75	0.45	20.53	31.86	28.96	30.31	27.57
100	0.45	20.58	32.45	29.74	31.42	28.78
125	0.45	20.63	33.12	30.59	32.39	29.88
150	0.46	20.67	33.78	31.38	33.33	30.68
175	0.47	20.71	34.64	32.03	34.31	31.25
200	0.47	20.76	35.48	32.71	35.19	31.77
250	0.49	20.83	37.77	33.97	36.80	33.36
300	0.51	20.90	39.53	34.46	37.63	35.17
350	0.52	20.97	38.05	34.93	38.31	36.57
400	0.54	21.02	34.09	34.78	38.73	37.49
425	0.55	21.04	32.51	34.84	38.80	37.69
450	0.56	21.05	31.03	34.88	38.96	37.62
475	0.57	21.07	29.60	34.85	39.66	37.30
500	0.59	21.10	28.29	34.64	40.16	36.56
525	0.59	21.10	27.33	34.57	40.77	35.71
550	0.61	21.11	26.35	34.52	41.25	34.85
575	0.62	21.12	25.49	34.28	41.87	33.90
600	0.63	21.12	24.61	33.91	42.26	33.01
650	0.66	21.13	23.22	33.30	42.10	31.37
700	0.67	21.12	21.96	32.83	42.09	29.87
725	0.69	21.11	21.39	32.30	42.12	29.17
750	0.71	21.16	20.43	31.96	41.81	28.37
775	0.71	21.08	20.44	31.94	42.60	27.78
800	0.72	21.05	20.14	31.55	43.07	27.20
850	0.73	21.01	19.37	30.67	43.23	26.11
900	0.75	20.95	18.84	29.93	43.76	25.13
950	0.77	20.90	18.32	29.44	43.53	24.20
1000	0.80	20.84	17.87	29.02	43.88	23.31
1050	0.83	20.78	17.53	28.64	42.32	22.51
1100	0.85	20.72	17.28	28.39	42.22	21.73
1150	0.88	20.65	17.07	28.03	42.19	21.00
1200	0.90	20.60	17.01	27.68	43.35	20.32
1250	0.92	20.50	16.89	27.31	43.68	19.64
1300	0.95	20.44	17.04	26.72	43.92	19.03
1350	1.01	20.60	15.90	25.79	41.18	18.35
1400	0.99	20.39	16.51	26.18	49.85	17.72
1425	1.00	20.36	16.93	26.10	50.31	17.45
1450	1.01	20.31	16.99	25.98	48.29	17.12
1475	1.03	20.29	17.17	25.79	47.20	16.83
1500	1.04	20.26	17.30	25.72	45.00	16.52

REV. X1
JDC-20-5
090830
Page 3 of 3



IF/RF MICROWAVE COMPONENTS • ISO 9001 ISO 14001 AS9100 CERTIFIED RoHS compliant

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661



The Design Engineers Search Engine finds the model you need, Instantly • For detailed performance specs & shopping online see




Directional Coupler


Typical Performance Curves

JDC-20-5


Insertion Loss




Insertion Loss vs. TEMPERATURE



Coupling Loss vs. TEMPERATURE



Directivity vs. TEMPERATURE



REV. X1
JDC-20-5
090830
Page 1 of 2

Mini-Circuits®

IF/RF MICROWAVE COMPONENTS • ISO 9001 ISO 14001 AS 9100 CERTIFIED RoHS compliant
P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661



The Design Engineers Search Engine finds the model you need, Instantly • For detailed performance specs & shopping online see




Directional Coupler


JDC-20-5

Typical Performance Curves


Return Loss




Return Loss In vs. TEMPERATURE



Return Loss Out vs. TEMPERATURE



Return Loss Cpl vs. TEMPERATURE



REV. X1

JDC-20-5

090830

Page 2 of 2

Mini-Circuits®

IF/RF MICROWAVE COMPONENTS • ISO 9001 ISO 14001 AS 9100 CERTIFIED RoHS compliant


P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661




The Design Engineers Search Engine finds the model you need, Instantly • For detailed performance specs & shopping online see



Outline Dimensions



PCB Land Pattern



Suggested Layout,
Tolerance to be within $\pm .002$

CASE #	A	B	C	D	E	F	G	H	J	K	L	WT. GRAM
BH292	.280 (7.11)	.310 (7.87)	- -	.100 (2.54)	.225 (5.72)	.055 (1.40)	.100 (2.54)	.047 (1.19)	.065 (1.65)	.065 (1.65)	.300 (7.62)	.45

Dimensions are in inches (mm). Tolerances: 2Pl. $\pm .01$; 3Pl. $\pm .005$

Notes:

- Case material: Ceramic.
- Termination finish:
For RoHS Case Styles: Tin plate over Nickel plate. All models, (+) suffix.
For RoHS-5 Case Styles: Tin-Lead plate. All models, no (+) suffix.

Tape & Reel Packaging TR-F24



Tape Width, mm	Device Cavity Pitch, mm	Reel Size, inches	Devices per Reel
16	12	13	500

Mini-Circuits carrier tape materials provide protection from ESD (Electro-Static Discharge) during handling and transportation. Tapes are static dissipative and comply with industry standards EIA-481/EIA-541.

Go to: www.minicircuits.com/pages/pdfs/tape.pdf




INTERNET <http://www.minicircuits.com>

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661

Distribution Centers NORTH AMERICA 800-654-7949 • 417-335-5935 • Fax 417-335-5945 • EUROPE 44-1252-832600 • Fax 44-1252-837010

Mini-Circuits ISO 9001 & ISO 14001 Certified


THIRD ANGLE PROJECTION



REVISIONS

REV	ECN No.	DESCRIPTION	DATE	DR	AUTH
OR	M81002	NEW RELEASE	08/05/02	MMG	LC
A	M102713	ADDED NOTE 2 & "...WITH SMOBC"	01/17/06	MMG	IL


SUGGESTED MOUNTING CONFIGURATION FOR BH292/CD542 CASE STYLE, "It" PIN CONNECTION



RESISTOR R1: 49.9 Ohm, 0603 SIZE.

- NOTES: 1. TRACE WIDTH IS SHOWN FOR ROGERS R04350B WITH DIELECTRIC THICKNESS .030" $\pm$.002"; COPPER: 1/2 OZ. EACH SIDE.
FOR OTHER MATERIALS TRACE WIDTH MAY NEED TO BE MODIFIED.
2. BOTTOM SIDE OF THE PCB IS CONTINUOUS GROUND PLANE.

 DENOTES PCB COPPER LAYOUT WITH SMOBC
(SOLDER MASK OVER BARE COPPER)

 DENOTES COPPER LAND PATTERN FREE OF SOLDER MASK

UNLESS OTHERWISE SPECIFIED

INITIALS

DATE

DIMENSIONS ARE IN INCHES

DRAWN

MMG

08/05/02

TOLERANCES ON:

CHECKED

AV

08/05/02

2 PL DECIMALS $\pm$

APPROVED

LC

08/05/02

3 PL DECIMALS $\pm$.005ANGLES $\pm$ FRACTIONS $\pm$
 Mini-Circuits®

THIS DOCUMENT AND ITS CONTENTS ARE THE PROPERTY OF MINI-CIRCUITS.
EXCEPT FOR USE EXPRESSLY GRANTED, IN WRITING, TO ITS VENDORS, VENDEE
AND THE UNITED STATES GOVERNMENT, MINI-CIRCUITS RESERVES ALL PROPRIETARY
DESIGN, USE, MANUFACTURING AND REPRODUCTION RIGHTS THERETO.
THESE CONTENTS SHALL NOT BE USED, DUPLICATED OR DISCLOSED TO ANY OUTSIDE
PARTY, IN WHOLE OR IN PART, WITHOUT WRITTEN PERMISSION OF MINI-CIRCUITS.

ASHEETA1.DWG REV:A DATE:01/12/95



Mini-Circuits®

13 Neptune Avenue
Brooklyn NY 11235

PL, It, BH292/CD542, JDC/ADC, TB-176


SIZE
ACODE IDENT
15542DRAWING NO:
98-PL-041REV:
A

FILE: 98PL041


SCALE: 8:1

SHEET: 1 OF 1

Evaluation Board and Circuit




TB-176



Schematic Diagram

Notes:

1. SMA Female connectors.
2. PCB Material: Rogers R04350 or equivalent,
Dielectric Constant=3.5, Thickness=.030 inch.

 **Mini-Circuits®**



All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

Specification	Test/Inspection Condition	Reference/Spec
Operating Temperature	-40° to 85°C Ambient Environment	Individual Model Data Sheet
Storage Temperature	-55° to 100° C Ambient Environment	Individual Model Data Sheet
Humidity	90 to 95% RH, 240 hours, 50°C	MIL-STD-202, Method 103, Condition A, Except 50°C and end-point electrical test done within 12 hours
Thermal Shock	-55° to 100°C, 100 cycles	MIL-STD-202, Method 107, Condition A-3, except +100°C
Solder Reflow Heat	Sn-Pb Eutetic Process: 225°C peak Pb-Free Process 245° - 250°C peak	J-STD-020, Table 4-1, 4-2 and 5-2, Figure 5-1
Solderability	10X Magnification	J-STD-002, 95% Coverage
Vibration (High Frequency)	20g peak, 10-2000 Hz, 12 times in each of three perpendicular directions (total 36)	MIL-STD-202, Method 204, Condition D
Mechanical Shock	50g, 11 ms, 1/2-sine, 18 shocks: 3 each direction, each of 3 axes	MIL-STD-202, Method 213, Condition A
Marking Resistance to Solvents	Isopropyl alcohol + mineral spirits at 25°C; terpene defluxer at 25°C; distilled water + proylene glycol monomethyl ether + monoethanolamine at 63°C to 70°C	MIL-STD-202, Method 215