

Engineering Development Model

Power Splitter/Combiner

4 Way-0°

JEPS-4-ED12484/1

Important Note

This model has been designed, built and tested in our engineering department. Performance data represents model capability.

At present it is a non-catalog model. On request, we can supply a final specification sheet, part number and price/delivery information.

Please click "Back", and then click "Contact Us" for Applications support.

CASE STYLE : BL301

ELECTRICAL SPECIFICATIONS 50Ω @ +25°C				
Parameter		Min.	Typ.	Max. Units
Frequency		700		2600 MHz
Isolation	700 - 2600 MHz		20	dB
Insertion Loss Above 6.0 dB	700 - 2600 MHz		1.00	dB
Phase Unbalance	700 - 2600 MHz		4.845	deg.
Amplitude Unbalance	700 - 2600 MHz		0.371	dB
VSWR	SUM Port		1.70	(:1)
	OUT Ports		1.20	(:1)

MAXIMUM RATINGS	
Operating Temperature	-40°C to 85°C
Storage Temperature	-55°C to 100°C

PIN CONNECTIONS	
SUM PORT	18
PORT 1	2
PORT 2	5
PORT 3	8
PORT 4	11
GND	All Other Pins

Functional Diagram



4 Way-0° Power Splitter/Combiner






JEPS-4-ED12484/1

Typical Performance Data


FREQ. (MHz)	TOTAL LOSS ¹ (dB)				AMP. UNBAL. (dB)	ISOLATION (dB)			PHASE UNBAL. (deg.)	FREQ. (MHz)	VSWR (:1)				
	S-1	S-2	S-3	S-4		1-2	2-3	3-4			S	1	2	3	4
700.0	6.40	6.64	6.76	6.62	0.36	20.38	19.91	20.85	2.46	700.0	1.75	1.22	1.28	1.30	1.23
750.0	6.33	6.56	6.68	6.54	0.35	21.45	20.95	22.02	2.65	750.0	1.61	1.18	1.25	1.26	1.19
800.0	6.28	6.50	6.62	6.49	0.35	22.21	22.01	22.90	2.85	800.0	1.50	1.16	1.22	1.23	1.16
850.0	6.25	6.47	6.59	6.47	0.34	22.43	22.94	23.21	2.98	850.0	1.42	1.14	1.19	1.21	1.14
900.0	6.25	6.47	6.59	6.46	0.33	22.17	23.66	22.97	3.17	900.0	1.38	1.13	1.17	1.19	1.13
950.0	6.28	6.48	6.60	6.49	0.32	21.57	24.07	22.34	3.36	950.0	1.38	1.12	1.16	1.18	1.12
1000.0	6.33	6.52	6.64	6.53	0.31	20.82	24.14	21.55	3.54	1000.0	1.43	1.12	1.16	1.17	1.12
1050.0	6.39	6.57	6.69	6.59	0.30	20.11	23.93	20.80	3.74	1050.0	1.49	1.12	1.15	1.17	1.12
1100.0	6.47	6.63	6.75	6.66	0.28	19.45	23.58	20.12	3.93	1100.0	1.57	1.12	1.15	1.16	1.12
1150.0	6.54	6.69	6.81	6.74	0.27	18.97	23.28	19.62	4.12	1150.0	1.65	1.12	1.15	1.17	1.12
1200.0	6.63	6.76	6.88	6.82	0.25	18.57	22.94	19.21	4.30	1200.0	1.73	1.12	1.15	1.16	1.12
1250.0	6.70	6.82	6.94	6.89	0.23	18.33	22.70	18.98	4.49	1250.0	1.79	1.11	1.15	1.16	1.13
1300.0	6.78	6.87	6.99	6.96	0.22	18.17	22.53	18.82	4.64	1300.0	1.85	1.11	1.15	1.16	1.13
1350.0	6.84	6.91	7.04	7.03	0.20	18.15	22.51	18.83	4.80	1350.0	1.88	1.11	1.15	1.16	1.13
1400.0	6.89	6.95	7.07	7.08	0.19	18.24	22.54	18.94	4.95	1400.0	1.91	1.10	1.15	1.15	1.13
1450.0	6.94	6.97	7.09	7.12	0.19	18.44	22.68	19.18	5.11	1450.0	1.91	1.10	1.15	1.15	1.13
1500.0	6.96	6.97	7.10	7.15	0.19	18.78	22.99	19.55	5.23	1500.0	1.89	1.10	1.14	1.14	1.12
1550.0	6.98	6.97	7.10	7.18	0.20	19.20	23.36	20.02	5.38	1550.0	1.87	1.10	1.13	1.13	1.12
1600.0	6.98	6.95	7.09	7.19	0.23	19.80	23.89	20.68	5.48	1600.0	1.82	1.10	1.12	1.12	1.12
1650.0	6.98	6.93	7.07	7.19	0.26	20.51	24.54	21.47	5.58	1650.0	1.76	1.10	1.12	1.11	1.11
1700.0	6.97	6.90	7.04	7.19	0.28	21.45	25.43	22.51	5.64	1700.0	1.69	1.10	1.11	1.10	1.11
1750.0	6.96	6.88	7.02	7.18	0.31	22.55	26.45	23.74	5.72	1750.0	1.62	1.10	1.10	1.09	1.10
1800.0	6.94	6.84	6.99	7.18	0.33	23.98	27.78	25.38	5.74	1800.0	1.54	1.10	1.09	1.08	1.10
1850.0	6.92	6.81	6.97	7.16	0.35	25.73	29.40	27.43	5.77	1850.0	1.47	1.11	1.08	1.07	1.10
1900.0	6.90	6.78	6.95	7.16	0.38	28.12	31.70	30.44	5.80	1900.0	1.38	1.11	1.07	1.06	1.10
1950.0	6.89	6.76	6.93	7.16	0.40	31.22	34.59	34.63	5.82	1950.0	1.31	1.11	1.07	1.05	1.09
2000.0	6.88	6.75	6.93	7.17	0.42	35.39	38.03	41.98	5.82	2000.0	1.24	1.12	1.06	1.05	1.10
2050.0	6.89	6.74	6.93	7.18	0.44	37.51	39.56	38.90	5.83	2050.0	1.17	1.12	1.06	1.04	1.10
2100.0	6.90	6.75	6.95	7.21	0.46	33.49	35.91	32.87	5.83	2100.0	1.12	1.13	1.06	1.04	1.11
2150.0	6.93	6.77	6.97	7.24	0.48	29.79	32.42	29.15	5.84	2150.0	1.09	1.14	1.06	1.05	1.12
2200.0	6.96	6.79	7.01	7.29	0.50	27.04	29.65	26.68	5.79	2200.0	1.10	1.15	1.08	1.05	1.13
2250.0	7.00	6.82	7.06	7.35	0.52	25.01	27.50	24.82	5.74	2250.0	1.14	1.16	1.09	1.07	1.16
2300.0	7.05	6.87	7.11	7.42	0.54	23.44	25.76	23.44	5.64	2300.0	1.18	1.19	1.12	1.09	1.19
2350.0	7.11	6.92	7.18	7.49	0.57	22.21	24.29	22.35	5.51	2350.0	1.24	1.22	1.15	1.13	1.23
2400.0	7.16	6.98	7.25	7.57	0.59	21.28	23.09	21.61	5.35	2400.0	1.28	1.26	1.20	1.17	1.28
2450.0	7.22	7.06	7.34	7.66	0.60	20.53	21.99	21.05	5.15	2450.0	1.34	1.32	1.26	1.23	1.35
2500.0	7.26	7.13	7.43	7.75	0.62	20.08	21.10	20.85	4.94	2500.0	1.38	1.40	1.33	1.32	1.44
2550.0	7.31	7.22	7.55	7.86	0.64	19.75	20.24	20.83	5.07	2550.0	1.45	1.50	1.43	1.41	1.56
2600.0	7.35	7.32	7.70	7.97	0.65	19.70	19.53	21.25	5.18	2600.0	1.49	1.63	1.54	1.55	1.72
2650.0	7.37	7.45	7.86	8.09	0.72	19.79	18.81	22.01	5.19	2650.0	1.57	1.80	1.71	1.70	1.92
2700.0	7.39	7.59	8.08	8.22	0.83	20.15	18.21	23.42	5.04	2700.0	1.64	2.02	1.89	1.93	2.18

¹Total Loss = Insertion Loss + 6dB Splitter Loss


Typical Performance Curves



Outline Dimensions



PCB Land Pattern



Suggested Layout,
Tolerance to be within ±.002


CASE #	A	B	C	D	E	F	G	H	J	K	L	WT. GRAM
BL301	.940 (23.88)	1.260 (32.00)	-- --	.100 (2.54)	.390 (9.91)	.080 (2.03)	.100 (2.54)	.047 (1.19)	.065 (1.65)	.065 (1.65)	.970 (24.64)	7.2

Dimensions are in inches (mm). Tolerances: 2Pl. ±.01; 3Pl. ±.005

Notes:

- Case material: Plastic.
- Base material: Printed wiring laminate.
- Termination finish:
 - For RoHS Case Styles: Tin plate over Nickel plate. All models, (+) suffix.
 - For RoHS-5 Case Styles: Tin-Lead plate. All models, no (+) suffix.

Tape & Reel Packaging TR-F25



Tape Width, mm	Device Cavity Pitch, mm	Reel Size, inches	Devices per Reel	
44	32	13	Small quantity standards (see note)	20
				50
				100
			Standard	125

Note: Please consult individual model data sheet to determine device per reel availability.

Mini-Circuits carrier tape materials provide protection from ESD (Electro-Static Discharge) during handling and transportation. Tapes are static dissipative and comply with industry standards EIA-481/EIA-541.

Go to: www.minicircuits.com/pages/pdfs/tape.pdf



Distribution Centers NORTH AMERICA 800-654-7949 • 417-335-5935 • Fax 417-335-5945 • EUROPE 44-1252-832600 • Fax 44-1252-837010

Mini-Circuits ISO 9001 & ISO 14001 Certified

INTERNET <http://www.minicircuits.com>

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661



All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

Specification	Test/Inspection Condition	Reference/Spec
Operating Temperature	-40° to 85°C Ambient Environment	Individual Model Data Sheet
Storage Temperature	-55° to 100° C Ambient Environment	Individual Model Data Sheet
Humidity	90 to 95% RH, 240 hours, 50°C	MIL-STD-202, Method 103, Condition A, Except 50°C and end-point electrical test done within 12 hours
Thermal Shock	-55° to 100°C, 100 cycles	MIL-STD-202, Method 107, Condition A-3, except +100°C
Solder Reflow Heat	Sn-Pb Eutetic Process: 225°C peak Pb-Free Process 245° - 250°C peak	J-STD-020, Table 4-1, 4-2 and 5-2, Figure 5-1
Solderability	10X Magnification	J-STD-002, 95% Coverage
Vibration (High Frequency)	20g peak, 10-2000 Hz, 12 times in each of three perpendicular directions (total 36)	MIL-STD-202, Method 204, Condition D
Mechanical Shock	50g, 11 ms, 1/2-sine, 18 shocks: 3 each direction, each of 3 axes	MIL-STD-202, Method 213, Condition A
Marking Resistance to Solvents	Isopropyl alcohol + mineral spirits at 25°C; terpene defluxer at 25°C; distilled water + proylene glycol monomethyl ether + monoethanolamine at 63°C to 70°C	MIL-STD-202, Method 215