

Engineering Development Model

Power Splitter/Combiner

JS4PS-ED14695/1

4 Way-0°

Important Note

This model has been designed, built and tested in our engineering department. Performance data represents model capability. At present it is a non-catalog model. On request, we can supply a final specification sheet, part number and price/delivery information.



Please click "Back", and then click "Contact Us" for Applications support.

CASE STYLE: BJ360

ELECTRICAL SPECIFICATIONS 50Ω @ +25°C				
Parameter		Min.	Typ.	Max. Units
Frequency		10		700 MHz
Isolation	10-100 MHz		26	dB
	100-350 MHz		32	dB
	350-700 MHz		32	dB
Insertion Loss Above 6.0 dB	10-100 MHz		0.50	dB
	100-350 MHz		0.50	dB
	350-700 MHz		0.75	dB
Phase Unbalance	10-100 MHz		0.10	deg.
	100-350 MHz		0.15	deg.
	350-700 MHz		0.40	deg.
Amplitude Unbalance	10-100 MHz		0.01	dB
	100-350 MHz		0.05	dB
	350-700 MHz		0.15	dB
VSWR	SUM Port		1.20	(:1)
	OUT Ports		1.25	(:1)

MAXIMUM RATINGS	
Operating Temperature	-40°C to 85°C
Storage Temperature	-55°C to 100°C

PIN CONNECTIONS	
SUM PORT	2
PORT 1	8
PORT 2	7
PORT 3	6
PORT 4	5
GROUND	1,3,4

electrical schematic



4 Way-0° Power Splitter/Combiner

JS4PS-ED14695/1

Typical Performance Data

FREQ. (MHz)	TOTAL LOSS ¹ (dB)				AMP. UNBAL. (dB)	ISOLATION (dB)			PHASE UNBAL. (deg.)	FREQ. (MHz)	VSWR (:1)				
	S-1	S-2	S-3	S-4		1-2	2-3	3-4			S	1	2	3	4
10.0	6.55	6.54	6.55	6.54	0.01	23.63	30.94	23.39	0.02	10.0	1.22	1.55	1.55	1.55	1.55
20.0	6.53	6.52	6.53	6.52	0.01	25.54	33.52	25.41	0.04	20.0	1.15	1.38	1.38	1.38	1.38
30.0	6.51	6.50	6.51	6.51	0.01	26.36	34.51	26.24	0.05	30.0	1.13	1.33	1.33	1.33	1.33
40.0	6.49	6.49	6.50	6.49	0.01	26.91	35.11	26.77	0.06	40.0	1.11	1.30	1.30	1.30	1.30
50.0	6.48	6.48	6.48	6.48	0.01	27.32	35.55	27.17	0.07	50.0	1.10	1.27	1.27	1.27	1.27
60.0	6.47	6.47	6.48	6.47	0.01	27.62	35.83	27.47	0.08	60.0	1.09	1.26	1.26	1.26	1.26
70.0	6.47	6.47	6.48	6.47	0.01	27.85	36.04	27.70	0.08	70.0	1.09	1.24	1.24	1.25	1.25
80.0	6.47	6.47	6.47	6.47	0.01	28.03	36.16	27.88	0.09	80.0	1.08	1.23	1.23	1.23	1.24
90.0	6.46	6.46	6.47	6.46	0.01	28.17	36.21	28.04	0.10	90.0	1.08	1.23	1.23	1.23	1.23
100.0	6.46	6.46	6.47	6.46	0.01	28.28	36.21	28.16	0.10	100.0	1.07	1.22	1.22	1.22	1.22
125.0	6.47	6.47	6.47	6.47	0.01	28.50	36.08	28.39	0.12	125.0	1.06	1.21	1.21	1.20	1.20
150.0	6.47	6.47	6.48	6.47	0.01	28.67	35.79	28.59	0.13	150.0	1.06	1.20	1.20	1.20	1.19
175.0	6.48	6.48	6.49	6.48	0.01	28.84	35.47	28.76	0.13	175.0	1.05	1.19	1.19	1.19	1.19
200.0	6.49	6.50	6.50	6.48	0.02	29.05	35.13	28.96	0.13	200.0	1.04	1.18	1.18	1.18	1.18
225.0	6.50	6.51	6.51	6.49	0.02	29.29	34.80	29.19	0.13	225.0	1.04	1.18	1.18	1.18	1.18
250.0	6.51	6.52	6.52	6.49	0.02	29.57	34.51	29.45	0.14	250.0	1.04	1.18	1.18	1.18	1.17
275.0	6.52	6.53	6.53	6.50	0.03	29.94	34.25	29.77	0.13	275.0	1.04	1.17	1.18	1.17	1.17
300.0	6.53	6.54	6.54	6.50	0.04	30.38	34.02	30.18	0.13	300.0	1.04	1.17	1.18	1.17	1.16
325.0	6.54	6.56	6.56	6.51	0.05	30.93	33.85	30.65	0.12	325.0	1.06	1.17	1.18	1.17	1.16
350.0	6.55	6.57	6.57	6.52	0.06	31.59	33.74	31.21	0.11	350.0	1.07	1.17	1.18	1.17	1.16
375.0	6.57	6.59	6.58	6.53	0.06	32.41	33.68	31.89	0.13	375.0	1.09	1.17	1.18	1.17	1.16
400.0	6.58	6.61	6.59	6.53	0.07	33.43	33.67	32.69	0.12	400.0	1.11	1.17	1.18	1.18	1.16
425.0	6.60	6.62	6.61	6.54	0.08	34.64	33.74	33.57	0.13	425.0	1.14	1.17	1.19	1.18	1.17
450.0	6.61	6.65	6.63	6.55	0.09	36.03	33.85	34.48	0.15	450.0	1.16	1.18	1.20	1.19	1.17
475.0	6.63	6.67	6.66	6.57	0.10	37.37	34.05	35.19	0.18	475.0	1.20	1.19	1.20	1.20	1.18
490.0	6.64	6.68	6.67	6.57	0.11	37.84	34.19	35.38	0.21	490.0	1.22	1.19	1.21	1.20	1.18
500.0	6.65	6.69	6.68	6.58	0.11	37.93	34.31	35.37	0.23	500.0	1.23	1.19	1.22	1.21	1.19
510.0	6.66	6.71	6.69	6.59	0.12	37.71	34.44	35.20	0.24	510.0	1.25	1.20	1.22	1.21	1.19
520.0	6.67	6.72	6.70	6.59	0.12	37.24	34.57	34.88	0.28	520.0	1.26	1.20	1.22	1.22	1.19
530.0	6.68	6.73	6.72	6.60	0.13	36.55	34.71	34.44	0.29	530.0	1.28	1.21	1.23	1.22	1.20
540.0	6.69	6.75	6.73	6.61	0.14	35.71	34.86	33.89	0.34	540.0	1.30	1.21	1.24	1.23	1.20
550.0	6.70	6.76	6.74	6.62	0.14	34.77	35.04	33.24	0.36	550.0	1.31	1.22	1.24	1.24	1.21
575.0	6.74	6.80	6.78	6.65	0.16	32.36	35.48	31.43	0.44	575.0	1.36	1.23	1.26	1.25	1.23
600.0	6.77	6.85	6.83	6.68	0.17	30.09	35.88	29.56	0.53	600.0	1.42	1.25	1.28	1.27	1.24
625.0	6.82	6.90	6.88	6.72	0.19	28.03	36.14	27.75	0.64	625.0	1.48	1.27	1.30	1.29	1.27
650.0	6.87	6.97	6.95	6.77	0.20	26.18	36.09	26.05	0.76	650.0	1.55	1.30	1.33	1.32	1.29
675.0	6.94	7.05	7.03	6.83	0.22	24.50	35.64	24.48	0.88	675.0	1.63	1.32	1.36	1.35	1.32
700.0	7.01	7.14	7.12	6.90	0.24	22.97	34.72	23.03	1.04	700.0	1.72	1.35	1.39	1.38	1.35

¹Total Loss = Insertion Loss + 6dB Splitter Loss



P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 • Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site
The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: www.minicircuits.com

IF/RF MICROWAVE COMPONENTS

REV. X2

JS4PS-ED14695/1






8/27/2010

Page 1 of 1


4 Way-0° Power Splitter/Combiner

JS4PS-ED14695/1


Typical Performance Curves



Outline Dimensions



PCB Land Pattern



Suggested Layout,
Tolerance to be within ±.002

CASE#	A	B	C	D	E	F	G	H	J	K	L	WT. GRAMS
BJ360	.450 (11.43)	.800 (20.32)	-- --	.100 (2.54)	.250 (6.35)	.100 (2.54)	.200 (5.08)	.047 (1.19)	.065 (1.65)	.065 (1.65)	.480 (12.19)	1.7

Dimensions are in inches (mm). Tolerances: 2Pl. ± .01; 3Pl. ± .005

Notes:

- Case material: Nickel-Silver alloy.
- Base material: Printed wiring laminate.
- Termination finish:
 - For RoHS Case Styles: Tin plate over Nickel plate. All models, (+) suffix.
 - For RoHS-5 Case Styles: Tin-Lead plate. All models, no (+) suffix.



INTERNET <http://www.minicircuits.com>

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661

Distribution Centers NORTH AMERICA 800-654-7949 • 417-335-5935 • Fax 417-335-5945 • EUROPE 44-1252-832600 • Fax 44-1252-837010

Mini-Circuits ISO 9001 & ISO 14001 Certified

Tape & Reel Packaging TR-F5



Tape Width, mm	Device Cavity Pitch, mm	Reel Size, inches	Devices per Reel
32	16	13	500

Mini-Circuits carrier tape materials provide protection from ESD (Electro-Static Discharge) during handling and transportation. Tapes are static dissipative and comply with industry standards EIA-481/EIA-541.

Go to: www.minicircuits.com/pages/pdfs/tape.pdf





Distribution Centers NORTH AMERICA 800-654-7949 • 417-335-5935 • Fax 417-335-5945 • EUROPE 44-1252-832600 • Fax 44-1252-837010

Mini-Circuits ISO 9001 & ISO 14001 Certified

INTERNET <http://www.minicircuits.com>

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661

Evaluation Board and Circuit



Schematic Diagram

Notes:

1. SMA Female connectors.
2. PCB Material: Rogers R04350 or equivalent,
Dielectric Constant=3.5, Thickness=.030 inch.

 **Mini-Circuits®**



All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

Specification	Test/Inspection Condition	Reference/Spec
Operating Temperature	-40° to 85°C Ambient Environment	Individual Model Data Sheet
Storage Temperature	-55° to 100° C Ambient Environment	Individual Model Data Sheet
Humidity	90 to 95% RH, 240 hours, 50°C	MIL-STD-202, Method 103, Condition A, Except 50°C and end-point electrical test done within 12 hours
Thermal Shock	-55° to 100°C, 100 cycles	MIL-STD-202, Method 107, Condition A-3, except +100°C
Solder Reflow Heat	Sn-Pb Eutetic Process: 225°C peak Pb-Free Process 245° - 250°C peak	J-STD-020, Table 4-1, 4-2 and 5-2, Figure 5-1
Solderability	10X Magnification	J-STD-002, 95% Coverage
Vibration (High Frequency)	20g peak, 10-2000 Hz, 12 times in each of three perpendicular directions (total 36)	MIL-STD-202, Method 204, Condition D
Mechanical Shock	50g, 11 ms, 1/2-sine, 18 shocks: 3 each direction, each of 3 axes	MIL-STD-202, Method 213, Condition A
Marking Resistance to Solvents	Isopropyl alcohol + mineral spirits at 25°C; terpene defluxer at 25°C; distilled water + proylene glycol monomethyl ether + monoethanolamine at 63°C to 70°C	MIL-STD-202, Method 215