

# Coaxial High Power Amplifier

## HPA-100W-63+

50Ω    100W    2500 to 6000 MHz

### The Big Deal

- High output power at saturation, 100W typ.
- High gain, 58 dB typ.
- Operates from AC line power: 85-264V
- Rugged design for rigorous lab applications
- Built-in over-temperature protections



CASE STYLE: NG1942

### Product Overview

The HPA-100W-63+ is a high power, rack mount amplifier with a self-contained AC power supply which can be used for a wide variety of laboratory testing applications. This rugged amplifier is capable of amplifying signals up to 100W output power over its entire operating bandwidth of 2500 to 6000 MHz. Built-in safety features include fans alarms and automatic shut down mechanism to prevent damage in the event of excessive internal temperatures. The amplifier's output stage is further protected in the event of a fault condition, allowing high power operation for up to 5 minutes into an open or short load (refer to the maximum input power specifications).

### Key Features

Feature	Advantages
Wideband frequency range	2500 to 6000 MHz bandwidth covers popular wireless communications, SATCOM and radar bands in a single instrument, useful for many test applications.
100W output power at saturation	Supports high power test applications such as EMI, max power handling, and reliability testing
High Gain	58 dB typical gain allows the HPA-100W-63+ to be driven to full output power with nearly all commercially available signal generators
High Reverse Isolation	Insulates load reflections to protect sensitive signal sources from potential damage and performance variation due to load pulling
A/C Power	Operating from standard AC line power supply - the HPA-100W-63+ can be powered from 85-264V at 47~63 Hz making this HPA versatile in supporting global markets
Cooling system	Front to back forced air cooling fans makes this ideal for usage in test equipment racks.
Built-in protections	The unit shuts OFF when the internal amplifier reaches a set temperature of 85±5°C, preventing damage to the amplifier and providing added reliability.
CE marked	Meets conformity standards for sale within the European Economic Area (EEA).



# Coaxial High Power Amplifier

## HPA-100W-63+

50Ω 100W 2500 to 6000 MHz

### Features

- High output power at saturation, 100W typ.
- High gain, 58 dB typ.
- Excellent reverse isolation, 93 dB typ.
- Rugged 3U rack mount case style with internal fans
- Operates from AC line power: 85-264V
- Built-in over-temperature protections
- CE marked

### Applications

- Laboratory test instrument
- RF Power stress test
- EMI and antenna testing
- Reliability testing



CASE STYLE: NG1942

Model No.	Description
HPA-100W-63+	High Power Amplifier w/ N-Type Connectors

#### Included Accessories

CBL-3W-XX	AC Power Cord
-----------	---------------

#### +RoHS Compliant

The +Suffix identifies RoHS Compliance. See our web site for RoHS Compliance methodologies and qualifications

### Electrical Specifications at 25°C

Parameter	Condition	Min.	Typ.	Max.	Units
Frequency Range		2500	—	6000	MHz
Gain	2500 - 6000 MHz	52	58	64	dB
Gain Flatness	2500 - 6000 MHz	—	±2.0	±3.5	dB
Output Power at 1dB compression <sup>1</sup>	2500 - 6000 MHz	+39	+43	—	dBm
Output Power at Saturation <sup>1</sup>	2500 - 6000 MHz	—	+50	—	dBm
Noise Figure	2500 - 6000 MHz	—	15	19	dB
Output third order intercept point	2500 - 6000 MHz	—	+50	—	dBm
Input VSWR	2500 - 6000 MHz	—	2.5	3.0	:1
Output VSWR	2500 - 6000 MHz	—	2.5	3.0	:1
Isolation	2500 - 6000 MHz	—	93	—	dB
Line Supply	47-63 Hz		85/264		V
Power Consumption	110/220V	—	450	600	W

1. Power measured of fundamental tone only. Does not include power contribution of harmonics signals.

### Maximum Ratings<sup>2</sup>

Parameter	Ratings
Operating Temperature	0°C to 50°C
Storage Temperature	-20°C to 70°C (non condensing)
Input RF Power (no damage)	+3 dBm <sup>3</sup> -15 dBm <sup>4</sup>

2. Specifications apply to CW signals only permanent damage may occur if any of these limits are exceeded.

3. Into 50 ohm load

4. Into open or short load, for up to 5 minutes.


### D-Sub Male Connector Pin Functions (Front Panel)

Pin #	Function	TTL Logic Level	
		Low	High
1	Temperature Alarm	Normal	Alarm Shutdown
2	Fan Alarm	Normal	Fault
3	Ground	—	—
4-9	No connection	—	—

### LED Indicators (Front Panel)

Name	Color	LED State	
		Off	On
Power	Green	Power off	Power on
Temp	Red	Normal	Alarm Shutdown
Fan	Red	Normal	Fault

## Outline Drawing



## Outline Dimensions (inch / mm)

A	B	C	D	E	F	G	H	J	K	L	M	N	P	Q	R	wt
5.20	19.0	20.0	.13	.94	17.13	2.25	18.31	3.17	3.49	3.82	7.63	5.12	2.23	2.24	4.05	grams
132.08	482.60	508.00	3.30	23.88	435.10	57.15	465.07	80.52	88.65	97.03	193.80	130.05	56.64	56.90	102.87	13610.0

## Ordering, Pricing & Availability Information see our web site

Model	Description
HPA-100W-63+	Rack Mount High Power Amplifier







Included Accessories	Description
CBL-3W-XX	AC Power Cord (Select one power cord from below with each Rack Mount HPA)

AC Power Cords	Description
CBL-3W-US	US Power Cord
CBL-3W-EU	EU Power Cord
CBL-3W-UK	UK Power Cord



## Typical Performance Data

FREQUENCY (MHz)	GAIN (dB)	ISOLATION (dB)	VSWR (:1)		POUT at 1 dB COMPR. (dBm)	POUT at Saturation (dBm)	NOISE FIGURE (dB)	IP3 (dBm)
			IN	OUT				
2500	60.2	93.0	1.4	1.1	43.2	50.3	11.9	53.8
3000	60.4	94.0	1.6	1.0	44.2	49.1	12.2	54.0
3500	58.7	91.0	1.8	1.1	44.4	49.8	10.6	51.1
4000	59.6	114.0	1.8	1.2	42.6	49.1	10.7	51.3
4500	58.2	94.0	1.6	1.1	42.3	50.1	11.5	51.4
5000	58.3	88.0	1.2	1.1	42.7	50.1	11.6	51.1
5500	60.1	99.0	1.1	1.1	42.7	49.0	11.6	50.7
6000	58.2	93.0	1.4	1.4	43.3	48.7	11.9	50.6



### Additional Notes

- Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
- The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at [www.minicircuits.com/MCLStore/terms.jsp](http://www.minicircuits.com/MCLStore/terms.jsp)

# High Power Amplifier

# HPA-100W-63+

## Typical Performance Data

Frequency (MHz)	Gain (dB)	Directivity (dB)	VSWR In (:1)	VSWR Out (:1)	Noise Figure (dB)	Pout at 1dB Compression (dBm)	Pout at Saturation (dBm)	Output IP3 (dBm)
2500	60.29	55.47	1.42	1.10	12.14	42.77	50.33	53.85
2600	59.70	41.96	1.41	1.10	12.47	43.28	50.25	53.93
2700	59.44	39.96	1.43	1.13	12.58	43.51	50.06	53.92
2800	59.43	46.36	1.46	1.06	12.55	43.52	49.84	53.61
2900	59.64	43.03	1.51	1.05	12.66	43.68	49.70	53.35
3000	60.27	50.04	1.54	1.03	12.28	43.57	49.11	52.77
3100	59.85	46.34	1.61	1.09	12.34	43.94	49.41	52.63
3200	59.65	42.80	1.65	1.12	11.85	43.98	49.44	52.28
3300	59.21	48.57	1.74	1.09	11.69	43.99	49.93	52.04
3400	59.01	58.90	1.76	1.09	11.33	44.37	50.02	51.44
3500	58.56	35.96	1.77	1.10	11.31	44.42	49.78	50.71
3600	58.35	47.25	1.78	1.08	11.26	44.06	49.49	49.99
3700	58.59	42.04	1.76	1.11	10.91	43.62	49.31	50.09
3800	58.80	39.71	1.76	1.12	11.14	42.90	49.11	50.54
3900	59.69	40.13	1.79	1.14	10.99	42.74	49.08	50.71
4000	59.29	45.29	1.79	1.23	11.42	42.47	49.08	51.15
4100	58.78	56.46	1.80	1.28	11.38	42.06	49.08	51.19
4200	58.04	39.40	1.80	1.27	11.71	41.98	49.25	51.49
4300	58.00	57.82	1.78	1.34	11.66	42.21	49.46	51.72
4400	57.77	53.99	1.76	1.35	11.80	42.09	49.87	51.96
4500	57.86	39.30	1.62	1.29	12.05	42.54	50.12	52.34
4600	58.18	48.59	1.54	1.42	11.82	42.84	50.51	52.43
4700	58.47	38.64	1.45	1.41	11.92	43.31	50.66	52.84
4800	58.62	36.50	1.36	1.28	11.74	43.59	50.66	53.21
4900	57.68	37.22	1.26	1.09	11.92	43.30	50.47	52.74
5000	57.98	61.59	1.19	1.05	11.80	43.02	50.07	51.98
5100	57.88	41.96	1.14	1.08	11.74	43.13	49.65	51.40
5200	57.57	42.67	1.09	1.12	11.71	43.13	49.22	50.50
5300	57.69	44.94	1.11	1.18	11.62	42.82	48.98	49.82
5400	58.22	40.83	1.10	1.11	11.71	43.06	49.14	50.12
5500	59.73	47.50	1.11	1.14	11.80	42.98	48.99	50.52
5600	60.04	42.54	1.15	1.13	11.83	43.10	49.07	50.85
5700	60.37	36.14	1.17	1.06	12.04	43.41	49.16	51.30
5800	59.24	45.23	1.27	1.12	12.23	43.33	49.32	51.24
5900	58.92	34.76	1.29	1.19	12.33	43.10	49.19	50.96
6000	57.62	47.82	1.45	1.42	12.26	43.66	49.10	51.18









P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 • Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site  
 The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: [www.minicircuits.com](http://www.minicircuits.com)



IF/RF MICROWAVE COMPONENTS


REV. A  
 HPA-100W-63+  
 5/26/2017  
 Page 1 of 1

## Typical Performance Curves



## Outline Dimensions

NG1942



CASE #	A	B	C	D	E	F	G	H	J	K	L
NG1942	5.20 (132.08)	19.00 (482.60)	20.00 (508.00)	.13 (3.30)	.94 (23.88)	17.13 (435.10)	2.25 (57.15)	18.31 (465.07)	3.17 (80.52)	3.49 (88.65)	3.82 (97.03)

CASE #	M	N	P	Q	R	S	T	WT, GRAMS
NG1942	7.63 (193.80)	5.12 (130.05)	2.23 (56.64)	2.24 (56.90)	4.05 (102.87)	--	--	13610

Dimensions are in inches (mm). Tolerances: 2Pl.  $\pm .03$ ; 3Pl.  $\pm .015$

### Note:

1. Case material: Aluminum alloy.
2. Finish: Powder coating, Color: White.



INTERNET <http://www.minicircuits.com>  
 P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661  
 Distribution Centers NORTH AMERICA 800-654-7949 • 417-335-5935 • Fax 417-335-5945 • EUROPE 44-1252-832600 • Fax 44-1252-837010  
 Mini-Circuits ISO 9001 & ISO 14001 Certified



All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

Specification	Test/Inspection Condition	Reference/Spec
Operating Temperature	-0° to 50° C Ambient Environment	Individual Model Data Sheet
Storage Temperature	-20° to 70° C (non condensing)	Individual Model Data Sheet