
REFLECTIONLESS FILTERS Designer's Kit K1-XFLTR+





DC to 9.8 GHz

X-Series Reflectionless Filters

- Patented design eliminates in band spurs
- Pass band cut-off up to 9.8 GHz
- Stop band up to 34 GHz
- Excellent repeatability through IPD* process

Kit K1-XFLTR+ LOW PASS FILTERS (10 models, 4 of each, 40 total)

Model	Pass-band (MHz)		Stop-band (MHz)	VSWR (:1)	
Number	I.L.=1 dB typ.	I.L.=3 dB typ.	I.L.=14 dB typ.	pass-band	stop-band
XLF-151+	0-150	280	460-2800	1.2	1.8
XLF-221+	0-220	370	570-3500	1.2	1.7
XLF-421+	0-420	610	900-5200	1.2	1.7
XLF-551+	0-550	770	1140-5800	1.2	1.6
XLF-861+	0-860	1150	1700-7500	1.2	2.3
XLF-122+	0-1150	1510	2190-10000	1.2	1.5
XLF-192+	0-1900	2400	3480-11200	1.2	2.1
XLF-252+	0-2500	3220	4550-16000	1.3	1.8
XLF-332+	0-3250	4120	5900-17000	1.2	2.0
XLF-732+	0-7300	9800	14300-34000	1.2	3.0





^{*}IPD - Integrated Passive Device is a GaAs semiconductor process

DQ1225

Outline Dimensions

PCB Land Pattern





.009 [0.23]
TYP
.057 [1.45]
.057
[1.45]
.016 [0.41]
TYP
.020 [0.51]
TYP

SUGGESTED LAYOUT,
TOLERANCE TO BE WITHIN ±.002

Weight: .02 Grams

Dimensions are in inches (mm). Tolerances: 2Pl. \pm .01; 3 Pl. \pm .004

Notes:

1. Case material: Plastic.

2. Termination finish:

For RoHS Case Styles: Tin-Silver alloy plate over Nickel barrier or Matte-Tin. All models, (+) suffix.

See Data sheet.

For RoHS-5 Case Styles: Tin-Lead plate. All models, no (+) suffix.



INTERNET http://www.minicircuits.com


P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661

Distribution Centers NORTH AMERICA 800-654-7949 • 417-335-5935 • Fax 417-335-5945 • EUROPE 44-1252-832600 • Fax 44-1252-837010

Mini-Circuits ISO 9001 & ISO 14001 Certified

Tape & Reel Packaging TR-F66

DEVICE ORIENTATION IN T&R



DIRECTION OF FEED

Tape Width, mm	Device Cavity Pitch, mm	Reel Size, inches	Devices per Reel see note	
8	4	7	Small quantity standard	20 50 100 200 500
		7	Standard	1000, 2000, 3000

Note: Please consult individual model data sheet to determine device per reel availability.

Mini-Circuits carrier tape materials provide protection from ESD (Electro-Static Discharge) during handling and transportation. Tapes are static dissipative and comply with industry standards EIA-481/EIA-541.

Go to: www.minicircuits.com/pages/pdfs/tape.pdf



Mini-Circuits ISO 9001 & ISO 14001 Certified



ENV82



All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

Test/Inspection Condition	Reference/Spec	
-55° to 105°C Ambient Environment	Individual Model Data Sheet	
-65° to 150° C Ambient Environment	Individual Model Data Sheet	
15 psig, 100% RH, 121°C, 96 hours	JESD22-A102-C, Condition C	
-65° to 150°C, 100 cycles	JESD22-A104	
85°C/ 85% RH, 168 hours	JESD22-113	
Sn-Pb Eutetic Process: 240°C peak Pb-Free Process: 260°C peak	J-STD-020, Table 4-1, 4-2 and 5-2; Figure 5-1	
Bake at 125°C for 24 hours Soak at 85°C/85% RH for 168 hours, Reflow 3 cycles at 240°C peak (Non-RoHS) or 260°C (RoHS)	J-STD-020C	
10X magnification, 95% coverage	JESD22-B102, Method 1: Dip and Look Test	
Isopropyl alcohol + mineral spirits at 25°C; terpene defluxer at 25°C; distilled water + proylene glycol monomethyl ether + monoethanolamine at 63°C to 70°C	MIL-STD-202, Method 215	
	-55° to 105°C Ambient Environment -65° to 150° C Ambient Environment 15 psig, 100% RH, 121°C, 96 hours -65° to 150°C, 100 cycles 85°C/ 85% RH, 168 hours Sn-Pb Eutetic Process: 240°C peak Pb-Free Process: 260°C peak Bake at 125°C for 24 hours Soak at 85°C/85% RH for 168 hours, Reflow 3 cycles at 240°C peak (Non-RoHS) or 260°C (RoHS) 10X magnification, 95% coverage Isopropyl alcohol + mineral spirits at 25°C; terpene defluxer at 25°C; distilled water + proylene glycol monomethyl ether +	

ENV82 Rev: OR

10/06/15

M153215 File: ENV82.pdf

This document and its contents are the property of Mini-Circuits.