

Engineering Development Model

Power Splitter/Combiner

JCPS-ED9707/1

5 Way-0°

Important Note

This model has been designed, built and tested in our engineering department. Performance data represents model capability. At present it is a non-catalog model. On request, we can supply a final specification sheet, part number and price/delivery information.



Please click "Back", and then click "Contact Us" for Applications support.

CASE STYLE : BG291

ELECTRICAL SPECIFICATIONS 50Ω @ +25°C				
Parameter		Min.	Typ.	Max. Units
Frequency		5		750 MHz
Isolation	5 - 50 MHz		36	dB
	50 - 375 MHz		31	dB
	375 - 750 MHz		28	dB
Insertion Loss Above 7.0 dB	5 - 50 MHz		0.41	dB
	50 - 375 MHz		0.67	dB
	375 - 750 MHz		1.17	dB
Phase Unbalance	5 - 50 MHz		1.598	deg.
	50 - 375 MHz		9.492	deg.
	375 - 750 MHz		29.027	deg.
Amplitude Unbalance	5 - 50 MHz		1.835	dB
	50 - 375 MHz		1.965	dB
	375 - 750 MHz		2.044	dB
VSWR	SUM Port		1.18	(:1)
	OUT Ports		1.12	(:1)

MAXIMUM RATINGS	
Operating Temperature	-40°C to 85°C
Storage Temperature	-55°C to 100°C

PIN CONNECTIONS	
SUM PORT	11
PORT 1	1
PORT 2	2
PORT 3	5
PORT 4	6
PORT 5	7
GND EXT	3, 4, 8, 9, 10, 12, 13, 14

Functional Diagram



5 Way-0° Power Splitter/Combiner

JCPS-ED9707/1

Typical Performance Data

FREQ. (MHz)	TOTAL LOSS ¹ (dB)					AMP. UNBAL. (dB)	ISOLATION (dB)				PHASE UNBAL. (deg.)	FREQ. (MHz)	VSWR (:1)				
	S-1	S-2	S-3	S-4	S-5		1-2	2-3	3-4	2-5			S	1	2	3	4
5.0	6.27	6.42	8.09	8.09	8.09	1.82	33.01	28.45	36.62	28.43	0.73	5.0	1.09	1.26	1.30	1.18	1.18
9.5	6.26	6.39	8.08	8.08	8.08	1.83	35.70	32.03	36.97	32.00	0.76	9.5	1.07	1.19	1.23	1.12	1.12
14.0	6.26	6.39	8.08	8.09	8.09	1.83	36.98	34.23	36.62	34.19	0.93	14.0	1.07	1.17	1.20	1.09	1.09
18.5	6.27	6.40	8.10	8.10	8.10	1.83	37.39	35.63	36.06	35.57	1.13	18.5	1.06	1.15	1.19	1.08	1.08
23.0	6.27	6.40	8.10	8.11	8.10	1.83	37.46	36.56	35.44	36.51	1.34	23.0	1.07	1.15	1.18	1.07	1.07
27.5	6.28	6.41	8.11	8.12	8.12	1.84	37.30	37.18	34.79	37.12	1.54	27.5	1.07	1.14	1.18	1.07	1.07
32.0	6.29	6.42	8.12	8.12	8.12	1.84	37.01	37.57	34.19	37.52	1.77	32.0	1.07	1.14	1.17	1.07	1.07
36.5	6.30	6.43	8.13	8.13	8.14	1.84	36.67	37.80	33.58	37.75	1.99	36.5	1.07	1.14	1.17	1.06	1.07
41.0	6.30	6.44	8.14	8.14	8.14	1.84	36.28	37.89	32.99	37.86	2.22	41.0	1.08	1.14	1.17	1.06	1.07
45.5	6.31	6.44	8.15	8.15	8.15	1.84	35.85	37.95	32.41	37.91	2.46	45.5	1.08	1.14	1.17	1.06	1.07
50.0	6.32	6.45	8.15	8.16	8.16	1.84	35.42	37.96	31.86	37.93	2.71	50.0	1.08	1.14	1.17	1.06	1.07
65.0	6.33	6.46	8.18	8.18	8.18	1.85	33.99	37.79	30.14	37.78	3.52	65.0	1.10	1.13	1.17	1.06	1.07
80.0	6.36	6.49	8.21	8.22	8.22	1.86	32.71	37.54	28.67	37.54	4.32	80.0	1.11	1.13	1.17	1.06	1.07
95.0	6.38	6.50	8.24	8.25	8.24	1.87	31.56	37.32	27.42	37.33	5.11	95.0	1.13	1.13	1.17	1.07	1.08
110.0	6.40	6.52	8.28	8.28	8.28	1.89	30.56	37.09	26.35	37.12	5.89	110.0	1.14	1.13	1.17	1.07	1.08
125.0	6.40	6.54	8.30	8.31	8.30	1.90	29.66	36.90	25.40	36.91	6.69	125.0	1.16	1.13	1.16	1.07	1.08
140.0	6.43	6.55	8.33	8.34	8.34	1.92	28.86	36.75	24.58	36.74	7.48	140.0	1.17	1.13	1.16	1.07	1.09
155.0	6.44	6.57	8.36	8.37	8.37	1.93	28.15	36.61	23.86	36.59	8.28	155.0	1.19	1.12	1.16	1.07	1.09
170.0	6.46	6.59	8.40	8.41	8.40	1.95	27.50	36.49	23.21	36.46	9.02	170.0	1.20	1.12	1.16	1.07	1.10
185.0	6.47	6.60	8.42	8.43	8.43	1.97	26.90	36.37	22.62	36.35	9.82	185.0	1.21	1.12	1.16	1.07	1.10
200.0	6.49	6.61	8.47	8.48	8.47	1.99	26.35	36.32	22.11	36.25	10.57	200.0	1.23	1.12	1.15	1.08	1.10
235.0	6.53	6.66	8.56	8.56	8.55	2.03	25.27	36.26	21.10	36.11	12.23	235.0	1.25	1.12	1.15	1.08	1.11
270.0	6.57	6.69	8.62	8.63	8.62	2.06	24.35	36.25	20.31	36.05	14.01	270.0	1.28	1.11	1.14	1.09	1.11
305.0	6.59	6.70	8.69	8.70	8.68	2.11	23.56	36.34	19.70	36.01	15.71	305.0	1.29	1.11	1.14	1.09	1.12
340.0	6.64	6.76	8.76	8.77	8.74	2.13	22.92	36.51	19.25	36.04	17.32	340.0	1.30	1.11	1.14	1.10	1.12
375.0	6.67	6.77	8.81	8.81	8.79	2.14	22.32	36.74	18.94	36.09	19.19	375.0	1.31	1.11	1.13	1.10	1.12
395.0	6.69	6.79	8.85	8.86	8.83	2.17	22.00	36.88	18.83	36.16	20.12	395.0	1.31	1.11	1.13	1.11	1.12
415.0	6.72	6.82	8.88	8.89	8.85	2.17	21.71	37.05	18.74	36.20	21.00	415.0	1.31	1.11	1.13	1.11	1.11
435.0	6.76	6.86	8.89	8.90	8.86	2.15	21.46	37.23	18.68	36.26	22.09	435.0	1.31	1.11	1.13	1.11	1.11
455.0	6.79	6.87	8.92	8.92	8.88	2.13	21.18	37.40	18.68	36.33	23.29	455.0	1.30	1.11	1.13	1.12	1.11
475.0	6.80	6.88	8.95	8.95	8.90	2.15	20.92	37.61	18.74	36.40	24.36	475.0	1.30	1.11	1.13	1.12	1.10
495.0	6.83	6.91	8.97	8.97	8.91	2.14	20.68	37.77	18.81	36.46	25.36	495.0	1.29	1.11	1.13	1.13	1.10
515.0	6.87	6.95	8.97	8.97	8.91	2.10	20.46	37.87	18.90	36.46	26.52	515.0	1.28	1.11	1.13	1.13	1.10
535.0	6.91	6.98	8.98	8.98	8.91	2.08	20.21	38.00	19.07	36.53	27.83	535.0	1.27	1.12	1.13	1.14	1.09
555.0	6.94	7.00	9.00	8.99	8.92	2.06	19.95	38.04	19.27	36.53	29.14	555.0	1.26	1.12	1.13	1.14	1.09
575.0	6.98	7.04	9.02	9.01	8.93	2.04	19.71	38.03	19.51	35.50	30.43	575.0	1.24	1.12	1.13	1.15	1.08
610.0	7.06	7.11	9.03	9.03	8.93	1.97	19.30	37.75	20.03	36.36	32.91	610.0	1.22	1.12	1.13	1.16	1.08
645.0	7.14	7.17	9.07	9.04	8.94	1.93	18.89	37.21	20.63	36.08	35.68	645.0	1.19	1.13	1.14	1.17	1.07
680.0	7.24	7.26	9.10	9.07	8.95	1.86	18.47	36.40	21.22	35.63	38.69	680.0	1.15	1.13	1.14	1.18	1.07
715.0	7.35	7.36	9.17	9.13	9.00	1.82	18.05	35.41	21.61	35.03	42.08	715.0	1.13	1.14	1.14	1.18	1.08
750.0	7.48	7.47	9.26	9.22	9.06	1.79	17.62	34.36	21.47	34.29	45.74	750.0	1.12	1.14	1.14	1.19	1.09

¹ Total Loss = Insertion Loss+ 7dB Splitter Loss

REV. X2
JCPS-ED9707/1
100713
Page 1 of 1








IF/RF MICROWAVE COMPONENTS • ISO 9001 ISO 14001 AS 9100 CERTIFIED RoHS compliant
P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661



The Design Engineers Search Engine finds the model you need, Instantly • For detailed performance specs & shopping online see





Typical Performance Curves



Outline Dimensions

BG291



DENOTES METALLIZATION

Weight: 4 gram

Dimensions are in inches[mm]. Tolerances: 2PL $\pm$ 0.03[0.76]; 3 PL $\pm$ 0.015 [0.381] inches[mm], unless otherwise specified

Notes:

1. Case material: Copper-Nickel alloy.
2. Base material: Printed wiring laminate.
3. Termination finish:

For RoHS Case Styles: Tin plate over Nickel plate. All models, (+) suffix.

For RoHS-5 Case Styles: Tin-Lead plate. All models, no (+) suffix.

Mini-Circuits®
ISO 9001 ISO 14001 CERTIFIED

ALL NEW
minicircuits.com


P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site



The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: www.minicircuits.com

RF/IF MICROWAVE COMPONENTS

Tape & Reel Packaging TR-F21



Tape Width, mm	Device Cavity Pitch, mm	Reel Size, inches	Devices per Reel
32	32	13	200

Mini-Circuits carrier tape materials provide protection from ESD (Electro-Static Discharge) during handling and transportation. Tapes are static dissipative and comply with industry standards EIA-481/EIA-541.

Go to: www.minicircuits.com/pages/pdfs/tape.pdf



INTERNET <http://www.minicircuits.com>

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661

Distribution Centers NORTH AMERICA 800-654-7949 • 417-335-5935 • Fax 417-335-5945 • EUROPE 44-1252-832600 • Fax 44-1252-837010

Mini-Circuits ISO 9001 & ISO 14001 Certified



All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

Specification	Test/Inspection Condition	Reference/Spec
Operating Temperature	-40° to 85°C Ambient Environment	Individual Model Data Sheet
Storage Temperature	-55° to 100° C Ambient Environment	Individual Model Data Sheet
Humidity	90 to 95% RH, 240 hours, 50°C	MIL-STD-202, Method 103, Condition A, Except 50°C and end-point electrical test done within 12 hours
Thermal Shock	-55° to 100°C, 100 cycles	MIL-STD-202, Method 107, Condition A-3, except +100°C
Solder Reflow Heat	Sn-Pb Eutetic Process: 225°C peak Pb-Free Process 245° - 250°C peak	J-STD-020, Table 4-1, 4-2 and 5-2, Figure 5-1
Solderability	10X Magnification	J-STD-002, 95% Coverage
Vibration (High Frequency)	20g peak, 10-2000 Hz, 12 times in each of three perpendicular directions (total 36)	MIL-STD-202, Method 204, Condition D
Mechanical Shock	50g, 11 ms, 1/2-sine, 18 shocks: 3 each direction, each of 3 axes	MIL-STD-202, Method 213, Condition A
Marking Resistance to Solvents	Isopropyl alcohol + mineral spirits at 25°C; terpene defluxer at 25°C; distilled water + proylene glycol monomethyl ether + monoethanolamine at 63°C to 70°C	MIL-STD-202, Method 215