

Power Splitter/Combiner

JPS-ED7721/1

4 Way-0°

Important Note

This model has been designed, built and tested in our engineering department. Performance data represents model capability.
At present it is a non-catalog model. On request, we can supply a final specification sheet, part number and price/delivery information.



Please click "Back", and then click "Contact Us" for Applications support.

CASE STYLE : 99-01-691

ELECTRICAL SPECIFICATIONS 50Ω @ +25°C					
Parameter		Min.	Typ.	Max.	Units
Frequency		1		541	MHz
Isolation	1 - 10 MHz		45		dB
	10 - 270.5 MHz		30		dB
	270.5 - 541 MHz		26		dB
Total Loss Above 6.0 dB	1 - 10 MHz		0.62		dB
	10 - 270.5 MHz		0.62		dB
	270.5 - 541 MHz		1.18		dB
Phase Unbalance	1 - 10 MHz		1.155		deg.
	10 - 270.5 MHz		0.766		deg.
	270.5 - 541 MHz		3.462		deg.
Amplitude Unbalance	1 - 10 MHz		0.288		dB
	10 - 270.5 MHz		0.228		dB
	270.5 - 541 MHz		0.392		dB
VSWR	SUM Port		1.28		(:1)
	OUT Ports		1.17		(:1)

MAXIMUM RATINGS	
Operating Temperature	-40°C to 85°C
Storage Temperature	-55°C to 100°C

PIN CONNECTIONS	
SUM PORT	5
PORT 1	1
PORT 2	3
PORT 3	4
PORT 4	6
GND EXT	2

Functional Diagram



4 Way-0° Power Splitter/Combiner

JPS-ED7721/1

Typical Performance Data






FREQ. (MHz)	TOTAL LOSS ¹ (dB)				AMP. UNBAL. (dB)	ISOLATION (dB)			PHASE UNBAL. (deg.)	FREQ. (MHz)	VSWR (:1)				
	S-1	S-2	S-3	S-4		1-2	2-3	3-4			S	1	2	3	4
1.0	7.15	6.78	6.77	7.22	0.44	49.05	22.17	48.85	2.20	1.0	1.32	1.56	1.49	1.49	1.54
1.9	6.98	6.65	6.66	7.03	0.37	53.86	26.11	53.68	1.59	1.9	1.25	1.38	1.33	1.33	1.37
2.8	6.86	6.56	6.57	6.91	0.34	56.73	28.45	55.94	1.35	2.8	1.21	1.31	1.26	1.26	1.29
3.7	6.76	6.51	6.51	6.82	0.31	57.12	29.81	55.86	1.28	3.7	1.18	1.26	1.22	1.22	1.25
4.6	6.70	6.46	6.46	6.74	0.28	56.09	30.62	54.77	1.11	4.6	1.16	1.23	1.20	1.20	1.22
5.5	6.65	6.45	6.44	6.70	0.26	54.59	31.13	53.22	1.06	5.5	1.15	1.21	1.18	1.18	1.20
6.4	6.61	6.41	6.40	6.66	0.25	53.44	31.49	52.13	0.97	6.4	1.14	1.19	1.17	1.17	1.18
7.3	6.58	6.40	6.39	6.63	0.24	52.28	31.73	51.10	0.86	7.3	1.13	1.18	1.16	1.16	1.17
8.2	6.56	6.39	6.39	6.62	0.23	51.20	31.91	50.05	0.78	8.2	1.12	1.17	1.15	1.15	1.16
9.1	6.56	6.38	6.38	6.60	0.23	50.44	32.06	49.30	0.80	9.1	1.12	1.16	1.14	1.14	1.15
10.0	6.53	6.37	6.37	6.59	0.22	49.61	32.16	48.45	0.71	10.0	1.11	1.16	1.14	1.14	1.15
45.0	6.53	6.39	6.40	6.58	0.19	37.72	31.36	36.61	0.31	45.0	1.09	1.12	1.10	1.10	1.10
80.0	6.58	6.43	6.45	6.63	0.20	33.22	29.98	32.11	0.41	80.0	1.12	1.11	1.09	1.09	1.10
90.0	6.58	6.45	6.46	6.65	0.20	32.28	29.57	31.20	0.50	90.0	1.13	1.11	1.09	1.09	1.09
130.0	6.64	6.49	6.54	6.71	0.22	29.48	28.13	28.39	0.71	130.0	1.17	1.10	1.07	1.08	1.08
170.0	6.68	6.54	6.62	6.78	0.23	27.52	26.99	26.48	0.80	170.0	1.20	1.08	1.06	1.06	1.07
210.0	6.72	6.60	6.70	6.84	0.24	26.10	26.17	25.09	0.97	210.0	1.23	1.07	1.04	1.04	1.05
250.0	6.78	6.65	6.79	6.92	0.27	25.08	25.64	24.14	1.21	250.0	1.26	1.06	1.03	1.03	1.04
270.0	6.79	6.68	6.85	6.97	0.28	24.70	25.50	23.80	1.27	270.0	1.27	1.05	1.04	1.03	1.04
290.0	6.82	6.70	6.90	7.00	0.29	24.38	25.42	23.55	1.30	290.0	1.28	1.05	1.05	1.04	1.04
310.0	6.84	6.72	6.94	7.02	0.31	24.14	25.40	23.37	1.47	310.0	1.29	1.05	1.07	1.06	1.05
330.0	6.89	6.74	7.00	7.06	0.32	23.99	25.43	23.30	1.82	330.0	1.30	1.06	1.09	1.07	1.06
350.0	6.91	6.78	7.05	7.11	0.33	23.94	25.51	23.33	2.16	350.0	1.31	1.07	1.11	1.09	1.07
370.0	6.92	6.82	7.12	7.16	0.34	23.96	25.60	23.47	2.31	370.0	1.32	1.09	1.13	1.11	1.09
390.0	6.97	6.84	7.17	7.20	0.36	24.08	25.63	23.73	2.49	390.0	1.34	1.10	1.15	1.14	1.11
410.0	7.03	6.87	7.23	7.24	0.37	24.33	25.57	24.14	2.88	410.0	1.35	1.12	1.17	1.16	1.13
430.0	7.07	6.91	7.31	7.30	0.40	24.71	25.35	24.75	3.52	430.0	1.38	1.14	1.20	1.19	1.15
450.0	7.12	6.99	7.40	7.37	0.41	25.31	24.95	25.64	3.89	450.0	1.41	1.17	1.23	1.22	1.18
468.2	7.19	7.03	7.48	7.43	0.45	26.02	24.33	26.70	4.11	468.2	1.45	1.19	1.25	1.25	1.20
486.4	7.28	7.09	7.54	7.49	0.45	26.97	23.54	28.18	4.50	486.4	1.50	1.22	1.28	1.28	1.22
504.6	7.40	7.17	7.65	7.59	0.48	28.29	22.63	30.35	5.31	504.6	1.56	1.24	1.30	1.31	1.25
522.7	7.50	7.30	7.79	7.72	0.48	30.15	21.69	33.67	6.30	522.7	1.64	1.27	1.33	1.34	1.28
540.9	7.58	7.44	7.94	7.84	0.50	32.76	20.68	39.47	6.41	540.9	1.73	1.29	1.35	1.37	1.30

¹ Total Loss = Insertion Loss + 6dB Splitter Loss

4 Way-0° Power Splitter/Combiner


JPS-ED7721/1

Typical Performance Curves




REV. X2
JPS-ED7721/1
100707
Page 1 of 1

Outline Dimensions



PCB Land Pattern



Suggested Layout,
Tolerance to be within $\pm .002$


CASE #	A	B	C	D	E	F	G	H	J	K	L	WT. GRAM
BH292	.280 (7.11)	.310 (7.87)	- -	.100 (2.54)	.225 (5.72)	.055 (1.40)	.100 (2.54)	.047 (1.19)	.065 (1.65)	.065 (1.65)	.300 (7.62)	.45

Dimensions are in inches (mm). Tolerances: 2Pl. $\pm .01$; 3Pl. $\pm .005$

Notes:

- Case material: Ceramic.
- Termination finish:
For RoHS Case Styles: Tin plate over Nickel plate. All models, (+) suffix.
For RoHS-5 Case Styles: Tin-Lead plate. All models, no (+) suffix.

Tape & Reel Packaging TR-F24



Tape Width, mm	Device Cavity Pitch, mm	Reel Size, inches	Devices per Reel
16	12	13	500

Mini-Circuits carrier tape materials provide protection from ESD (Electro-Static Discharge) during handling and transportation. Tapes are static dissipative and comply with industry standards EIA-481/EIA-541.

Go to: www.minicircuits.com/pages/pdfs/tape.pdf



INTERNET <http://www.minicircuits.com>

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661

Distribution Centers NORTH AMERICA 800-654-7949 • 417-335-5935 • Fax 417-335-5945 • EUROPE 44-1252-832600 • Fax 44-1252-837010

Mini-Circuits ISO 9001 & ISO 14001 Certified



All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

Specification	Test/Inspection Condition	Reference/Spec
Operating Temperature	-40° to 85°C Ambient Environment	Individual Model Data Sheet
Storage Temperature	-55° to 100° C Ambient Environment	Individual Model Data Sheet
Humidity	90 to 95% RH, 240 hours, 50°C	MIL-STD-202, Method 103, Condition A, Except 50°C and end-point electrical test done within 12 hours
Thermal Shock	-55° to 100°C, 100 cycles	MIL-STD-202, Method 107, Condition A-3, except +100°C
Solder Reflow Heat	Sn-Pb Eutetic Process: 225°C peak Pb-Free Process 245° - 250°C peak	J-STD-020, Table 4-1, 4-2 and 5-2, Figure 5-1
Solderability	10X Magnification	J-STD-002, 95% Coverage
Vibration (High Frequency)	20g peak, 10-2000 Hz, 12 times in each of three perpendicular directions (total 36)	MIL-STD-202, Method 204, Condition D
Mechanical Shock	50g, 11 ms, 1/2-sine, 18 shocks: 3 each direction, each of 3 axes	MIL-STD-202, Method 213, Condition A
Marking Resistance to Solvents	Isopropyl alcohol + mineral spirits at 25°C; terpene defluxer at 25°C; distilled water + proylene glycol monomethyl ether + monoethanolamine at 63°C to 70°C	MIL-STD-202, Method 215