

Ceramic Diplexer

LDPG-272-492+

50Ω DC to 5750 MHz (DC-2700, 4900-5750 MHz)



Generic photo used for illustration purposes only

CASE STYLE: GE0805C-10

+RoHS Compliant

The +Suffix identifies RoHS Compliance. See our web site for RoHS Compliance methodologies and qualifications



Available Tape and Reel at no extra cost

Reel Size	Devices/Reel
7"	20, 50, 100, 200, 500, 1000, 4000

Maximum Ratings

Operating Temperature	-55°C to 100°C
Storage Temperature*	-55°C to 100°C
RF Power Input**	2W at 25°C

* 12 months max.


** passband rating, derate linearly to 1W at 100°C ambient.

Permanent damage may occur if any of these limits are exceeded.


Pad Connections

Low Pass Port	6
High Pass Port	4
Common Port	2
Ground	1,3,5

Outline Drawing



PCB Land Pattern




Suggested Layout, Tolerance to be within ±.002

Outline Dimensions (inch mm)

A	B	C	D	E	F
.079	.049	.020	.014	.012	.012
2.01	1.24	0.51	0.36	0.30	0.30
G	H	J	K		wt
.026	.014	.039	.110		grams
0.66	0.36	1.00	2.80		.005

Demo Board MCL P/N: TB-798+ Suggested PCB Layout (PL-441)



NOTES:

1. COPLANAR WAVEGUIDE IS SHOWN FOR ROGERS R04350B WITH DIELECTRIC THICKNESS .010" ± .001". COPPER: 1/2 OZ. EACH SIDE. FOR OTHER MATERIALS TRACE WIDTH AND GAP MAY NEED TO BE MODIFIED.

2. BOTTOM SIDE OF THE PCB IS CONTINUOUS GROUND PLANE.

DENOTES PCB COPPER LAYOUT WITH SMOBC (SOLDER MASK OVER BARE COPPER).

DENOTES COPPER LAND PATTERN FREE OF SOLDER MASK.

Notes

A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.

B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.

C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp

Features

- small size 0805(2.0 x 1.25 mm)
- low insertion loss, 0.7 dB typ.
- high rejection
- temperature stable
- LTCC construction

Applications

- communication systems
- ISM
- WiFi

Electrical Specifications^{1,2} at 25°C

Parameter	Port	Frequency (MHz)	Min.	Typ.	Max.	Unit	
Pass Band	Insertion Loss	Low Pass	DC - 2700	—	0.5	0.9	dB
		Band Pass	4900 - 5750	—	0.7	0.9	
	Return Loss	Low Pass	2300 - 2700	10	16	—	dB
		Band Pass	4900 - 5750	10	14	—	
Stop Band Isolation	Band Pass	DC - 2700	18	23	—	dB	
		9800 - 11900	—	17	—		
	Low Pass	4800 - 8000	20	30	—	dB	


¹ In Application where DC voltage is present at either input or output port, coupling capacitors are required.

² Measured on Mini-Circuits Characterization Test Board TB-798+

Typical Performance Data at 25°C






Frequency (MHz)	Insertion Loss (dB)			Return Loss (dB)	
	Low Pass Port	High Pass Port	Common Port	Low Pass Port	High Pass Port
10	0.10	58.83	47.75	37.84	0.04
50	0.05	45.92	38.49	34.75	0.03
100	0.10	41.84	33.28	32.98	0.03
800	0.34	25.56	15.37	14.76	0.08
2300	0.43	27.39	17.15	21.24	0.25
2700	0.56	37.44	18.10	19.31	0.33
3500	2.30	8.69	14.46	16.57	3.00
4000	18.88	1.05	11.25	0.80	14.70
4800	31.11	0.54	18.24	0.39	25.61
4900	31.67	0.54	19.56	0.38	26.15
5750	35.40	0.59	18.12	0.33	18.97
6000	35.94	0.72	14.00	0.31	14.49
7000	34.23	1.84	6.46	0.17	7.46
8000	34.32	6.18	2.51	0.07	2.74
9800	28.29	32.63	0.51	0.19	0.31
11900	21.63	20.94	0.43	0.49	0.51
12000	21.41	20.85	0.41	0.51	0.57

Functional Schematic



www.minicircuits.com P.O. Box 350166, Brooklyn, NY 11235-0003 (718) 934-4500 sales@minicircuits.com

REV. A
M151107
LDPG-272-492+
ED-16419/22
MY/CP/AM
190924
Page 1 of 2



Notes







- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
- C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp




Typical Performance Data

FREQUENCY (MHz)	INSERTION LOSS (dB)		CROSS OVER ISOLATION (dB) (between LPF and HPF)	RETURN LOSS (dB)		
	Low Pass port	High Pass port		Common port	Low Pass port	High Pass port
	10.0	0.10		58.83	62.01	47.75
50.0	0.05	45.92	47.73	38.49	34.75	0.03
100.0	0.10	41.84	41.73	33.28	32.98	0.03
200.0	0.12	35.89	35.78	26.83	26.13	0.03
300.0	0.15	32.52	32.34	23.48	22.67	0.03
400.0	0.18	30.20	30.02	20.74	20.11	0.04
500.0	0.22	28.54	28.21	18.98	18.31	0.04
600.0	0.26	27.24	26.85	17.44	16.84	0.05
700.0	0.30	26.30	25.73	16.33	15.68	0.07
800.0	0.34	25.56	24.85	15.37	14.76	0.08
900.0	0.38	25.00	24.10	14.54	14.02	0.09
1000.0	0.42	24.62	23.51	13.92	13.45	0.10
1100.0	0.46	24.31	23.06	13.36	12.97	0.12
1200.0	0.50	24.19	22.77	12.95	12.63	0.13
1300.0	0.52	24.06	22.52	12.66	12.43	0.15
1400.0	0.54	24.10	22.39	12.43	12.30	0.15
1500.0	0.55	24.13	22.37	12.40	12.37	0.17
1600.0	0.55	24.25	22.40	12.39	12.50	0.18
1700.0	0.55	24.40	22.51	12.54	12.78	0.19
1800.0	0.54	24.59	22.77	12.81	13.28	0.20
1900.0	0.52	24.86	23.16	13.24	13.93	0.21
2000.0	0.50	25.17	23.71	13.88	14.90	0.22
2300.0	0.43	27.39	27.40	17.15	21.24	0.25
2400.0	0.43	29.10	29.99	18.75	26.60	0.26
2700.0	0.56	37.44	32.90	18.10	19.31	0.33
3000.0	0.97	20.74	19.57	12.50	11.76	0.55
3200.0	1.36	15.83	14.31	10.86	10.26	0.91
3400.0	1.76	11.88	9.85	11.91	13.21	1.79
3800.0	11.65	1.73	11.60	11.49	1.84	12.31
4200.0	23.68	0.78	23.31	12.55	0.54	17.92
4400.0	27.21	0.65	28.35	14.17	0.45	21.26
4800.0	31.11	0.54	33.55	18.24	0.39	25.61
4900.0	31.67	0.54	34.20	19.56	0.38	26.15
5200.0	33.06	0.51	35.54	23.85	0.38	38.09
5400.0	34.00	0.52	36.35	24.56	0.36	30.43
5750.0	35.40	0.59	37.99	18.12	0.33	18.97
6000.0	35.94	0.72	39.10	14.00	0.31	14.49
6200.0	35.92	0.85	39.93	11.82	0.29	12.40
6400.0	35.68	1.03	40.48	10.04	0.25	10.72
6800.0	34.76	1.51	40.31	7.46	0.20	8.37
7000.0	34.23	1.84	40.00	6.46	0.17	7.46
7200.0	33.82	2.26	39.30	5.60	0.15	6.58
7400.0	33.58	2.84	38.81	4.78	0.12	5.63
7800.0	33.85	4.75	38.11	3.21	0.09	3.63
8000.0	34.32	6.18	37.27	2.51	0.07	2.74
8200.0	34.85	7.98	36.80	1.92	0.06	2.03
8400.0	35.03	10.16	36.06	1.44	0.07	1.46
8800.0	33.71	15.80	35.47	0.86	0.09	0.75
9000.0	32.55	19.42	34.79	0.71	0.09	0.56
9200.0	31.35	24.03	34.07	0.62	0.11	0.44
9400.0	30.24	30.81	33.17	0.57	0.13	0.38
9800.0	28.29	32.63	32.48	0.51	0.19	0.31
10000.0	27.41	28.14	31.64	0.49	0.22	0.30
10500.0	25.58	23.61	30.74	0.46	0.31	0.35
11000.0	24.02	21.91	29.88	0.43	0.39	0.40
11900.0	21.63	20.94	29.35	0.43	0.49	0.51
12000.0	21.41	20.85	28.60	0.41	0.51	0.57


Typical Performance Curves



Outline Dimensions



PCB Land Pattern



Suggested Layout,
Tolerance to be within $\pm .002$

CASE #	A	B	C	D	E	F	G	H	J	K	WT.GRAM
GE0805C-10	.079 (2.00)	.049 (1.25)	.020 (0.50)	.014 (0.35)	.012 (0.30)	.012 (0.30)	.026 (0.65)	.014 (0.35)	.039 (1.00)	.110 (2.80)	.005

Dimensions are in inches (mm). Tolerances: 2Pl. $\pm .01$; 3 Pl. $\pm .005$

Notes:

- Open style, ceramic base.
- Termination finish: For RoHS Case Styles: Tin plate over Nickel plate. All models, (+) suffix.
For RoHS-5 Case Styles: Tin-Lead plate over Nickel plate. All models, no (+) suffix.
- Line width should be designed to match 50 Ω characteristic depending on PCB material and thickness.



P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site



The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: www.minicircuits.com

RF/IF MICROWAVE COMPONENTS

Tape & Reel Packaging TR-F114

DEVICE ORIENTATION IN T&R




ILLUSTRATION 1

Applicable Case Styles	
GE0805C	JC0603C
GE0805C-1	JC0603C-4
GE0805C-1AP	JC0603C-6
GE0805C-7	
GE0805C-9	
GE0805C-10	
GE0805C-11	
GE0805C-12	




ILLUSTRATION 2

Applicable Case Styles	
GE0805C-2	JC0603C-1
GE0805C-3	JC0603C-2
GE0805C-4	JC0603C-3
GE0805C-5	JC0603C-5
GE0805C-6	JC0603C-7
GE0805C-8	JV1210C-1
GE0805C-15	

Tape Width, mm	Device Cavity Pitch, mm	Reel Size, inches	Devices per Reel	
8	4	7	Small quantity standards (see note)	20
				50
				100
				200
				500
				1000
			Standard	4000

Note: Please Consult individual model data sheet to determine device per reel availability.

Mini-Circuits carrier tape materials provide protection from ESD (Electro-Static Discharge) during handling and transportation. Tapes are static dissipative and comply with industry standards EIA-481/EIA-541.

Go to: www.minicircuits.com/pages/pdfs/tape.pdf




INTERNET <http://www.minicircuits.com>

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661

Distribution Centers NORTH AMERICA 800-654-7949 • 417-335-5935 • Fax 417-335-5945 • EUROPE 44-1252-832600 • Fax 44-1252-837010

Mini-Circuits ISO 9001 & ISO 14001 Certified


THIRD ANGLE PROJECTION



REVISIONS

REV	ECN No.	DESCRIPTION	DATE	DR	AUTH
OR	M148538	NEW RELEASE	10/14/14	GF	MY

**SUGGESTED MOUNTING CONFIGURATION
FOR GE0805C-10 CASE STYLE, "06DP03" PIN CODE**



NOTES:

1. COPLANAR WAVEGUIDE IS SHOWN FOR ROGERS R04350B WITH DIELECTRIC THICKNESS .010" ± .001". COPPER: 1/2 OZ. EACH SIDE. FOR OTHER MATERIALS TRACE WIDTH AND GAP MAY NEED TO BE MODIFIED.
2. BOTTOM SIDE OF THE PCB IS CONTINUOUS GROUND PLANE.

-  DENOTES PCB COPPER LAYOUT WITH SMOBC (SOLDER MASK OVER BARE COPPER).
-  DENOTES COPPER LAND PATTERN FREE OF SOLDER MASK.

UNLESS OTHERWISE SPECIFIED	INITIALS	DATE
DIMENSIONS ARE IN INCHES TOLERANCES ON: 2 PL DECIMALS ± 3 PL DECIMALS ± .005 ANGLES ± FRACTIONS ±	DRAWN	GF 10/07/14
	CHECKED	AV 10/14/14
	APPROVED	MY 10/14/14



 **Mini-Circuits®** 13 Neptune Avenue
Brooklyn NY 11235

PL, 06DP03, GE0805C-10, TB-798+

Mini-Circuits®
THIS DOCUMENT AND ITS CONTENTS ARE THE PROPERTY OF MINI-CIRCUITS. EXCEPT FOR USE EXPRESSLY GRANTED, IN WRITING, TO ITS VENDORS, VENDEE AND THE UNITED STATES GOVERNMENT, MINI-CIRCUITS RESERVES ALL PROPRIETARY DESIGN, USE, MANUFACTURING AND REPRODUCTION RIGHTS THERETO. THESE CONTENTS SHALL NOT BE USED, DUPLICATED OR DISCLOSED TO ANY OUTSIDE PARTY, IN WHOLE OR IN PART, WITHOUT WRITTEN PERMISSION OF MINI-CIRCUITS.

SIZE	CODE IDENT	DRAWING NO:	REV:
A	15542	98-PL-441	OR
FILE:	98PL441	SCALE: 15:1	SHEET: 1 OF 1


Evaluation Board and Circuit



Schematic Diagram

Notes:

1. 50 Ohm SMA Female connectors.
2. PCB Material: R04350 or equivalent, Dielectric Constant=3.5, Thickness=.010 inch.

 **Mini-Circuits®**

All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

Specification	Test/Inspection Condition	Reference/Spec
Operating Temperature	-55° to 100°C Ambient Environment	Individual Model Data Sheet
Storage Temperature	-55° to 100° C Ambient Environment	Individual Model Data Sheet
Humidity	90 to 95% RH, 240 hours, 50°C	MIL-STD-202, Method 103, Condition A, Except 50°C and end-point electrical test done within 12 hours
Solder Reflow Heat	Sn-Pb Eutetic Process: 225°C peak Pb-Free Process 245° - 250°C peak	J-STD-020, Table 4-1, 4-2 and 5-2, Figure 5-1
Solderability	10X Magnification	J-STD-002, Para 4.2.5, Test S, 95% Coverage
Vibration (High Frequency)	20g peak, 10-2000 Hz, 12 times in each of three perpendicular directions (total 36)	MIL-STD-202, Method 204, Condition D
Mechanical Shock	50g, 11 ms, 1/2-sine, 18 shocks: 3 each direction, each of 3 axes	MIL-STD-202, Method 213, Condition A