

Ceramic

Low Pass Filter

LFCG-1200+

50Ω DC to 1200 MHz



Generic photo used for illustration purposes only
CASE STYLE: GE0805C-2

The Big Deal

- Very good rejection, 50 dB typical
- Rugged, ceramic construction
- Tiny size, 0.079" x 0.049" x 0.037" (0805)
- Excellent power handling, 5.5W

Product Overview

Mini-Circuits' LFCG-1200+ is an LTCC low pass filter with a passband from DC to 1200 MHz, supporting a variety of applications. This model provides 1.0 dB typical passband insertion loss and provides a very good stopband rejection due to strategically constructed layout with minimal interaction between components. It handles up to 5.5W RF input power and provides a wide operating temperature range from -55 to +125°C. Housed in a tiny 0805 ceramic form factor with wraparound terminations, the filter is ideal for dense PCB layouts and with minimal performance variation due to parasitics.

Key Features

Feature	Advantages
Ultra-wide stopband	The LTCC lowpass filter provides a very good stopband rejection until 10 GHz suitable for high end applications.
LTCC Construction	Provides repeatable performance in a rugged, ceramic package well suited for tough environments such as high humidity and temperature extremes.
Tiny size (0.079" x 0.049" x 0.037")	Saves space in dense circuit board layouts and minimizes the effects of parasitics.
Excellent power handling, 5.5W	Supports a wide range of system power requirements.
Wrap-around terminations	Provides excellent solderability and easy visual inspection

Notes

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp



Ceramic

Low Pass Filter

50Ω

DC to 1200 MHz

LFCG-1200+




Features

- Low loss, 1 dB typical
- High rejection 50 dB typical
- Excellent power handling, 5.5W
- Extremely small size 0805 (2.0mm x 1.25mm)
- Temperature stable
- LTCC construction


Applications

- Harmonic Rejection
- VHF/UHF transmitters / receivers
- Military radar applications
- Test and measurement
- Telecommunications & broadband wireless applications

Functional Schematic



Typical Frequency Response



Generic photo used for illustration purposes only
CASE STYLE: GE0805C-2

+RoHS Compliant

The +Suffix identifies RoHS Compliance. See our web site for RoHS Compliance methodologies and qualifications

Electrical Specifications^{1,2} at 25°C

	Parameter	F#	Frequency (MHz)	Min.	Typ.	Max.	Unit
Pass Band	Insertion Loss	DC-F1	DC-1200	—	1.0	1.8	dB
	Freq. Cut-Off	F2	1470	—	3.0	—	dB
	Return Loss	DC-F1	DC-1200	—	26	—	dB
Stop Band	Rejection Loss	F3-F4	1865-2000	20	50	—	dB
		F4-F5	2000-3700	40	50	—	dB
		F5-F6	3700-7000	28	40	—	dB
		F6-F7	7000-10000	—	30	—	dB

1. DC de-coupling capacitors are required in Applications where DC voltage and/or current is present at either input or output ports. Please contact Mini-Circuits for alternatives if DC pass from IN-OUT is required.

2. Measured on Mini-Circuits Characterization Test Board TB-799+




Maximum Ratings

Operating Temperature	-55°C to 125°C
Storage Temperature	-55°C to 125°C
RF Power Input*	5.5W max. @25°C

*Passband rating, derate linearly to 1W at 125°C ambient
Permanent damage may occur if any of these limits are exceeded.

Typical Performance Data at 25°C

Frequency (MHz)	Insertion Loss (dB)	Return Loss (dB)
10	0.11	39.47
100	0.15	35.87
1000	0.61	31.54
1200	0.89	31.14
1460	3.03	9.12
1470	3.28	8.58
1690	20.86	5.07
1740	30.84	3.15
1865	56.75	1.38
2000	58.67	0.82
3000	76.16	0.28
3500	54.62	0.26
3700	52.03	0.26
4000	48.96	0.25
5800	45.28	0.20
6000	45.62	0.24
7500	47.30	0.35
8500	40.52	0.35
9000	38.17	0.32
10000	32.99	0.22



Notes

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
- C. The parts covered by this specification document are subject to Mini-Circuit's standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp

Mini-Circuits®


www.minicircuits.com P.O. Box 350166, Brooklyn, NY 11235-0003 (718) 934-4500 sales@minicircuits.com

Pad Connections


INPUT	8
OUTPUT	4
GROUND	1,2,3,5,6,7

Product Marking: LE

Demo Board MCL P/N: TB-799+
Suggested PCB Layout (PL-429)

NOTES:

1. COPLANAR WAVEGUIDE IS SHOWN FOR ROGERS RO4350B WITH DIELECTRIC THICKNESS .010" ± .001". COPPER: 1/2 OZ. EACH SIDE. FOR OTHER MATERIALS TRACE WIDTH AND GAP MAY NEED TO BE MODIFIED.
 2. BOTTOM SIDE OF THE PCB IS CONTINUOUS GROUND PLANE.
- DENOTES PCB COPPER LAYOUT WITH SMOBC (SOLDER MASK OVER BARE COPPER).
 ■ DENOTES COPPER LAND PATTERN FREE OF SOLDER MASK.

Outline Drawing**Outline Dimensions (inch)**

A	B	C	D	E	F	G	Wt.
.079 2.00	.049 1.25	.037 0.95	.014 0.35	.012 0.30	.012 0.30	.026 0.65	grams .008

Note: Please refer to case style drawing for details

Notes

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuits' applicable established test performance criteria and measurement instructions.
- C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp



Ceramic Low Pass Filter

LFCG-1200+

Typical Performance Data

FREQ. (MHz)	INSERTION LOSS			INPUT RETURN LOSS			OUTPUT RETURN LOSS		
	(dB)			(dB)			(dB)		
	@-55°C	@+25°C	@+125°C	@-55°C	@+25°C	@+125°C	@-55°C	@+25°C	@+125°C
10	0.11	0.11	0.14	35.32	37.15	34.58	36.89	38.46	35.83
50	0.12	0.13	0.16	42.04	39.55	38.10	40.55	38.54	37.20
100	0.13	0.16	0.18	41.06	38.66	37.23	37.32	35.71	34.71
250	0.17	0.22	0.26	48.01	45.89	40.99	31.05	30.29	29.59
400	0.21	0.27	0.33	37.73	38.09	36.62	27.23	26.49	25.78
550	0.26	0.33	0.40	30.31	30.25	30.04	24.93	24.28	23.71
700	0.32	0.40	0.49	27.18	27.08	26.89	24.25	23.75	23.37
1000	0.49	0.60	0.73	28.78	29.03	29.26	31.30	31.94	32.96
1200	0.71	0.87	1.06	32.10	30.61	28.84	31.85	31.32	30.83
1460	2.45	2.95	3.61	8.23	7.53	6.87	9.71	9.27	8.94
1470	2.65	3.19	3.89	7.64	6.99	6.38	9.10	8.73	8.47
1690	17.76	20.51	23.82	1.05	1.08	1.14	5.16	5.08	4.98
1740	26.98	30.40	34.45	0.76	0.85	0.94	3.22	3.18	3.18
1750	29.10	32.67	36.91	0.72	0.82	0.92	2.93	2.92	2.94
1865	56.04	56.33	56.66	0.52	0.63	0.74	1.27	1.37	1.49
2000	62.25	59.28	57.04	0.38	0.50	0.61	0.69	0.81	0.92
2200	54.88	54.76	54.91	0.28	0.40	0.52	0.43	0.52	0.61
2350	57.95	58.67	59.60	0.22	0.35	0.46	0.32	0.40	0.48
2500	65.24	67.02	68.55	0.18	0.31	0.42	0.26	0.34	0.40
2650	80.42	78.12	78.11	0.15	0.27	0.38	0.22	0.29	0.35
2800	70.29	71.28	72.05	0.13	0.25	0.35	0.19	0.26	0.31
2950	73.76	75.58	76.16	0.10	0.22	0.32	0.17	0.23	0.28
3000	78.26	78.12	74.07	0.10	0.21	0.31	0.16	0.22	0.28
3250	64.73	63.01	61.22	0.07	0.18	0.27	0.12	0.19	0.25
3400	58.77	57.85	56.76	0.06	0.17	0.25	0.11	0.18	0.23
3550	55.14	54.53	53.82	0.05	0.15	0.23	0.09	0.16	0.22
3700	52.64	52.20	51.67	0.04	0.14	0.22	0.08	0.15	0.22
3850	50.88	50.53	50.08	0.03	0.13	0.20	0.07	0.15	0.22
4000	49.50	49.32	48.81	0.03	0.12	0.19	0.06	0.15	0.22
4150	48.42	48.35	47.87	0.02	0.12	0.18	0.05	0.14	0.22
4300	47.71	47.59	47.17	0.02	0.11	0.17	0.04	0.14	0.23
4450	46.90	46.82	46.65	0.01	0.11	0.17	0.03	0.13	0.23
4600	46.40	46.35	46.21	0.01	0.10	0.16	0.03	0.13	0.23
4750	45.85	45.80	45.71	0.01	0.10	0.16	0.02	0.13	0.24
4900	45.32	45.41	45.68	0.01	0.10	0.16	0.02	0.13	0.25
5050	44.97	45.39	45.67	0.01	0.11	0.17	0.01	0.13	0.26
5200	45.27	45.68	45.84	0.02	0.11	0.18	0.01	0.13	0.27
5350	45.30	45.51	45.70	0.02	0.12	0.19	0.00	0.13	0.28
5500	45.33	45.56	45.99	0.02	0.12	0.19	0.01	0.13	0.29
5650	45.28	45.60	46.09	0.02	0.13	0.20	0.01	0.13	0.30
5800	46.08	46.41	47.29	0.02	0.13	0.22	0.01	0.13	0.31
5950	45.96	46.46	47.64	0.01	0.13	0.22	0.02	0.13	0.32
6100	46.25	46.80	47.38	0.01	0.14	0.24	0.03	0.13	0.32
6250	46.50	47.41	46.83	0.02	0.15	0.26	0.02	0.14	0.34
6400	46.96	47.33	47.64	0.02	0.16	0.28	0.02	0.15	0.35
6550	47.84	47.40	49.19	0.02	0.17	0.29	0.02	0.16	0.36
6700	48.87	47.68	50.29	0.02	0.17	0.30	0.02	0.16	0.36
6850	48.01	46.87	48.99	0.03	0.19	0.32	0.01	0.17	0.37
7000	47.58	46.77	48.11	0.03	0.20	0.34	0.01	0.18	0.38
7150	46.61	46.63	46.80	0.04	0.20	0.37	0.01	0.19	0.40
7300	45.60	46.95	46.16	0.04	0.20	0.38	0.02	0.19	0.40
7450	45.29	46.62	46.66	0.04	0.21	0.39	0.02	0.19	0.39
7500	45.51	46.35	46.33	0.04	0.21	0.40	0.01	0.19	0.39
7750	44.40	44.29	44.12	0.04	0.23	0.43	0.01	0.19	0.40
7900	42.78	42.48	42.78	0.04	0.24	0.46	0.02	0.22	0.41
8050	42.53	42.20	42.98	0.04	0.24	0.46	0.04	0.22	0.39
8200	42.36	42.30	41.93	0.05	0.24	0.47	0.03	0.19	0.35
8350	41.09	40.90	41.19	0.06	0.26	0.49	0.00	0.17	0.33
9000	37.21	37.29	37.17	0.07	0.29	0.55	0.03	0.13	0.27
10000	33.69	33.65	33.72	0.15	0.37	0.61	0.04	0.13	0.22



ISO 9001 ISO 14001 AS 9100 CERTIFIED

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 • Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site
 The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: www.minicircuits.com

IF/RF MICROWAVE COMPONENTS








REV. A
LFCG-1200+
210427
Page 1 of 2

Typical Performance Data

FREQ. (MHz)	GROUP DELAY		
	(nsec)		
	@-55°C	@+25°C	@+125°C
10	0.25	0.35	0.31
40	0.36	0.38	0.38
70	0.37	0.38	0.38
100	0.37	0.37	0.38
130	0.37	0.37	0.38
160	0.37	0.37	0.38
190	0.37	0.37	0.38
220	0.37	0.37	0.38
250	0.37	0.38	0.38
280	0.37	0.38	0.38
310	0.38	0.38	0.39
340	0.38	0.38	0.39
370	0.38	0.39	0.39
400	0.38	0.39	0.40
430	0.39	0.39	0.40
460	0.39	0.40	0.40
490	0.40	0.40	0.41
520	0.40	0.41	0.41
550	0.41	0.41	0.42
580	0.41	0.42	0.42
610	0.42	0.42	0.43
640	0.42	0.43	0.44
670	0.43	0.44	0.45
700	0.44	0.45	0.45
730	0.45	0.45	0.46
760	0.46	0.46	0.47
790	0.47	0.47	0.48
820	0.48	0.49	0.50
850	0.49	0.50	0.51
880	0.50	0.51	0.52
910	0.52	0.53	0.54
940	0.53	0.54	0.56
970	0.55	0.56	0.57
1000	0.57	0.58	0.59
1030	0.59	0.60	0.62
1060	0.61	0.62	0.64
1090	0.63	0.65	0.67
1120	0.66	0.68	0.70
1150	0.70	0.72	0.74
1180	0.73	0.75	0.78
1200	0.76	0.78	0.81

Typical Performance Curves




Case Style


GE

GE0805C-2

Outline Dimensions



PCB Land Pattern



Suggested Layout,
Tolerance to be within $\pm .002$

CASE #	A	B	C	D	E	F	G	H	J	K	L
GE0805C-2	.079 (2.00)	.049 (1.25)	.037 (0.95)	.014 (0.35)	.012 (0.30)	.012 (0.30)	.026 (0.65)	.025 (0.63)	.134 (3.40)	.110 (2.80)	.014 (0.35)

CASE #	M	WT. GRAM
GE0805C-2	.039 (1.00)	.008

Dimensions are in inches (mm). Tolerances: 2Pl. $\pm .01$; 3 Pl. $\pm .005$

Notes:

1. Open style, ceramic base.
2. Termination finish: For RoHS Case Styles: Tin plate over Nickel plate. All models, (+) suffix.
For RoHS-5 Case Styles: Tin-Lead plate over Nickel plate. All models, no (+) suffix.
3. Pad tolerance to be non-cumulative. Minimum spacing between each pad is .004 (0.1).

 **Mini-Circuits®**
ISO 9001 ISO 14001 CERTIFIED

ALL NEW
minicircuits.com

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site




The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: www.minicircuits.com

RF/IF MICROWAVE COMPONENTS


Tape & Reel Packaging TR-F114

DEVICE ORIENTATION IN T&R



Applicable Case Styles

GE0805C	JC0603C
GE0805C-1	JC0603C-4
GE0805C-1AP	JC0603C-6
GE0805C-7	
GE0805C-9	
GE0805C-10	
GE0805C-11	
GE0805C-12	



Applicable Case Styles

GE0805C-2	JC0603C-1
GE0805C-3	JC0603C-2
GE0805C-4	JC0603C-3
GE0805C-5	JC0603C-5
GE0805C-6	JC0603C-7
GE0805C-8	JV1210C-1
GE0805C-15	

Tape Width, mm	Device Cavity Pitch, mm	Reel Size, inches	Devices per Reel								
8	4	7	Small quantity standards (see note) <table border="1" style="margin-left: 20px;"> <tr><td>20</td></tr> <tr><td>50</td></tr> <tr><td>100</td></tr> <tr><td>200</td></tr> <tr><td>500</td></tr> <tr><td>1000</td></tr> <tr><td>Standard</td><td>4000</td></tr> </table>	20	50	100	200	500	1000	Standard	4000
20											
50											
100											
200											
500											
1000											
Standard	4000										

Note: Please Consult individual model data sheet to determine device per reel availability.

Mini-Circuits carrier tape materials provide protection from ESD (Electro-Static Discharge) during handling and transportation. Tapes are static dissipative and comply with industry standards EIA-481/EIA-541.

Go to: www.minicircuits.com/pages/pdfs/tape.pdf




Distribution Centers NORTH AMERICA 800-654-7949 • 417-335-5935 • Fax 417-335-5945 • EUROPE 44-1252-832600 • Fax 44-1252-837010

INTERNET <http://www.minicircuits.com>


P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661

Mini-Circuits ISO 9001 & ISO 14001 Certified



REVISIONS					
REV OR	ECN No.	DESCRIPTION		DATE	DR AUTH
	M148457	NEW RELEASE		10/14/14	GF MY

SUGGESTED MOUNTING CONFIGURATION
FOR GE0805C-4 CASE STYLE, "08FL07" PIN CODE



NOTES:


1. COPLANAR WAVEGUIDE IS SHOWN FOR ROGERS R04350B WITH DIELECTRIC THICKNESS $.010" \pm .001"$. COPPER: 1/2 OZ. EACH SIDE. FOR OTHER MATERIALS TRACE WIDTH AND GAP MAY NEED TO BE MODIFIED.
2. BOTTOM SIDE OF THE PCB IS CONTINUOUS GROUND PLANE.

[Solid Blue Box] DENOTES PCB COPPER LAYOUT WITH SMOBC (SOLDER MASK OVER BARE COPPER).


[Hatched Box] DENOTES COPPER LAND PATTERN FREE OF SOLDER MASK.

UNLESS OTHERWISE SPECIFIED	INITIALS		DATE	 Mini-Circuits® 13 Neptune Avenue Brooklyn NY 11235
DIMENSIONS ARE IN INCHES	DRAWN	GF	10/01/14	
TOLERANCES ON: 2 PL DECIMALS \pm 3 PL DECIMALS $\pm .005$	CHECKED	IL	10/14/14	
ANGLES \pm FRACTIONS \pm	APPROVED	MY	10/14/14	
 Mini-Circuits® THIS DOCUMENT AND ITS CONTENTS ARE THE PROPERTY OF MINI-CIRCUITS. EXCEPT FOR USE EXPRESSLY GRANTED, IN WRITING, TO ITS VENDORS, VENDEE AND THE UNITED STATES GOVERNMENT, MINI-CIRCUITS RESERVES ALL PROPRIETARY DESIGN, USE, MANUFACTURING AND REPRODUCTION RIGHTS THERETO. THESE CONTENTS SHALL NOT BE USED, DUPLICATED OR DISCLOSED TO ANY OUTSIDE PARTY, IN WHOLE OR IN PART, WITHOUT WRITTEN PERMISSION OF MINI-CIRCUITS.				
FILE: 98PL429 DRAWING NO: 98-PL-429 REV: OR FILE: 98PL429 SCALE: 15:1 SHEET: 1 OF 1				
ASHEETA1.DWG REV:A DATE:01/12/95				

Evaluation Board and Circuit



TB-799+



Schematic Diagram

Notes:

1. 50 Ohm SMA Female connectors.
2. PCB Material: RO4350 or equivalent,
Dielectric Constant=3.5, Thickness=.010 inch.

 Mini-Circuits®



Environmental Specifications

ENV06T2

All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

Specification	Test/Inspection Condition	Reference/Spec
Operating Temperature	-40° to 85° C Ambient Environment	Individual Model Data Sheet
Storage Temperature	-55° to 100° C Ambient Environment	Individual Model Data Sheet
Humidity	90 to 95% RH, 240 hours, 50°C	MIL-STD-202, Method 103, Condition A, Except 50°C and end-point electrical test done within 12 hours
Thermal Shock	-55° to 100°C, 100 cycles	MIL-STD-202, Method 107, Condition A-3, except +100°C
Solder Reflow Heat	Sn-Pb Eutetic Process: 225°C peak Pb-Free Process 245° - 250°C peak	J-STD-020, Table 4-1, 4-2 and 5-2, Figure 5-1
Solderability	10X Magnification	J-STD-002, Para 4.2.5, Test S, 95% Coverage
Vibration (High Frequency)	20g peak, 10-2000 Hz, 12 times in each of three perpendicular directions (total 36)	MIL-STD-202, Method 204, Condition D
Mechanical Shock	50g, 11 ms, 1/2-sine, 18 shocks: 3 each direction, each of 3 axes	MIL-STD-202, Method 213, Condition A