LTCC SURFACE MOUNT

Low Pass Filter

LFCG-630+

50Ω DC to 630 MHz

THE BIG DEAL

- Insertion Loss, Typ. 1.6 dB
- Stopband Rejection, Typ. 50 dB
- Passband Return Loss, Typ. 14 dB
- 0805 Surface Mount Footprint
- Power Handling: 3.5 Watts




Generic photo used for illustration purposes only

APPLICATIONS

- Harmonic Rejection
- VHF/UHF Transmitters / Receivers
- Military Radar Applications
- Test and Measurement Equipment
- Telecommunications & Broadband Wireless Applications
- Satcom Modems

FUNCTIONAL DIAGRAM



PRODUCT OVERVIEW

Mini-Circuits' LFCG-630+ is a miniature low temperature co-fired ceramic (LTCC) low pass filter with a DC to 630 MHz passband supporting a variety of applications. This model provides 1.6 dB typical insertion loss over a wide band due to its rugged monolithic construction. Housed in an 0805 ceramic form factor which is ideal for dense signal chain PCB layouts where it complements MMIC size and performance. The LTCC fabrication process assures minimal RF performance variation while delivering a product that is well suited for environmental extremes of high humidity and temperature.

KEY FEATURES

Features	Advantages
Ultra-wide Stopband	The LTCC lowpass filter provides a very good stopband rejection until 8500 MHz suitable for wide band applications.
LTCC Construction	Provides repeatable performance in a rugged, ceramic package well suited for tough environments such as high humidity and temperature extremes.
Small Size, 0805	Saves space in dense circuit board layouts and minimizes the effects of parasitics.
Rugged Power Handling, 3.5 Watts	Handles up to 3.5 Watts in a small 0805 package.

Low Pass Filter

LFCG-630+

50Ω DC to 630 MHz

ELECTRICAL SPECIFICATIONS[1,2,3] AT +25°C

Parameter		F#	Frequency (MHz)	Min.	Typ.	Max.	Units
Passband	Insertion Loss	DC-F1	DC - 630	—	1.6	2.1	dB
	Freq. Cut-Off[4]	Fc	780	—	3.0	—	dB
	Return Loss	DC-F1	DC - 630	—	14	—	dB
Stopband	Rejection	F2-F3	1050 - 1500	20	50	—	dB
		F3-F4	1500 - 3800	35	48	—	
		F4-F5	3800 - 8500	—	15	—	


1. Tested in Evaluation Board P/N TB-LFCG-630+.
2. This filter is bi-directional, RF1 and RF2 ports may be interchanged. See S-Parameters for actual performance.
3. In applications where DC voltage and/or current is present at either the input or output ports, external DC blocking capacitors are required.
4. Typical variation ± 5%.

ABSOLUTE MAXIMUM RATINGS[5]

Parameter	Ratings
Operating Temperature	-55°C to +125°C
Storage Temperature	-55°C to +125°C
Input Power[6]	3.5 W @ +25°C

5. Permanent damage may occur if any of these limits are exceeded.
6. Power rating applies only to signals within the passband. Power rating above +25°C operating temperature decreases linearly to 0.8 W at +125°C.

TYPICAL FREQUENCY RESPONSE AT +25°C




Low Pass Filter

LFCG-630+


50Ω DC to 630 MHz

TYPICAL PERFORMANCE GRAPHS


LFCG-630+
INSERTION LOSS




LFCG-630+
INSERTION LOSS (Zoomed)




LFCG-630+
RETURN LOSS



LFCG-630+
RETURN LOSS (Zoomed)



LFCG-630+
GROUP DELAY



Low Pass Filter

LFCG-630+

50Ω DC to 630 MHz

FUNCTIONAL DIAGRAM





Figure 1. LFCG-630+ Functional Diagram

PAD DESCRIPTION

Function	Pad Number	Description
RF1[2]	8	Connects to RF Input Port
RF2[2]	4	Connects to RF Output Port
GROUND	1,2,3,5,6,7	Connects to Ground on PCB, (See drawing PL-429)

SUGGESTED PCB LAYOUT (PL-429)



NOTES:


1. COPLANAR WAVEGUIDE IS SHOWN FOR ROGERS RO4350B WITH DIELECTRIC THICKNESS .010" ± .001". COPPER: 1/2 OZ. EACH SIDE. FOR OTHER MATERIALS TRACE WIDTH AND GAP MAY NEED TO BE MODIFIED.
2. BOTTOM SIDE OF THE PCB IS CONTINUOUS GROUND PLANE.

DENOTES PCB COPPER LAYOUT WITH SMOBC (SOLDER MASK OVER BARE COPPER).

DENOTES COPPER LAND PATTERN FREE OF SOLDER MASK.

Figure 2. Suggested PCB Layout PL-429

CASE STYLE DRAWING



Weight: .008 grams
Dimensions are in inches (mm). Tolerances: 2Pl. ± .01; 3 Pl. ± .005

PRODUCT MARKING*: LR

*Marking may contain other features or characters for internal lot control.

Low Pass Filter

LFCG-630+

50Ω DC to 630 MHz

ADDITIONAL DETAILED INFORMATION IS AVAILABLE ON OUR DASHBOARD. CLICK HERE

Performance Data and Graphs	Data Graphs S-Parameter (S2P Files) Data Set (.zip file) De-embedded to device pads
Case Style	GE0805C-2 Lead Finish: Tin over Nickel plating
RoHS Status	Compliant
Tape and Reel	F114
Suggested Layout for PCB Design	PL-429
Evaluation Board	TB-LFCG-630+
	Gerber File
Environmental Rating	ENV111

NOTES

A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuits' applicable established test performance criteria and measurement instructions.
C. The parts covered by this specification document are subject to Mini-Circuits' standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the standard terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/terms/viewterm.html

Ceramic Low Pass Filter LFCG-630+

Typical Performance Data


FREQ.	INSERTION LOSS			INPUT RETURN LOSS			OUTPUT RETURN LOSS		
(MHz)	(dB)			(dB)			(dB)		
	@-55°C	@+25°C	@+125°C	@-55°C	@+25°C	@+125°C	@-55°C	@+25°C	@+125°C
10	0.16	0.19	0.23	34.25	33.21	31.49	34.94	33.55	31.87
40	0.19	0.23	0.28	32.30	30.06	28.58	31.77	29.68	28.31
100	0.26	0.31	0.36	29.41	27.03	25.33	26.24	24.74	23.51
200	0.35	0.42	0.49	26.99	25.30	23.73	22.04	21.19	20.30
300	0.45	0.53	0.62	25.38	24.85	23.95	20.93	20.42	19.78
400	0.59	0.68	0.78	22.27	23.16	23.86	21.81	22.20	22.33
420	0.63	0.72	0.82	21.40	22.31	23.21	21.85	22.60	23.17
460	0.71	0.81	0.92	19.59	20.37	21.31	21.04	22.14	23.52
490	0.80	0.90	1.01	18.14	18.71	19.46	19.71	20.69	22.03
500	0.82	0.93	1.04	17.72	18.22	18.91	19.20	20.08	21.30
590	1.15	1.29	1.44	14.55	14.58	14.69	14.81	14.92	15.12
600	1.20	1.33	1.49	14.41	14.39	14.44	14.55	14.59	14.72
630	1.33	1.47	1.65	14.31	14.11	13.98	14.16	13.98	13.89
700	1.67	1.84	2.06	18.05	16.90	16.00	16.56	15.57	14.76
720	1.83	1.99	2.22	21.28	19.42	18.00	18.30	17.04	15.95
780	3.00	3.02	3.18	16.54	19.69	22.61	17.83	19.12	19.39
800	4.08	3.86	3.90	10.89	13.62	16.31	13.82	16.58	18.57
820	6.17	5.45	5.17	6.61	8.75	11.03	9.18	12.02	15.13
850	11.63	10.03	8.95	3.08	4.18	5.56	4.70	6.26	8.34
900	23.46	21.37	19.59	1.40	1.77	2.25	2.16	2.70	3.44
915	27.07	24.95	23.12	1.22	1.52	1.91	1.83	2.27	2.85
960	37.55	35.43	33.55	0.88	1.09	1.34	1.23	1.50	1.85
1000	46.17	44.18	42.38	0.72	0.89	1.08	0.93	1.13	1.39
1050	54.52	53.18	51.86	0.59	0.72	0.88	0.70	0.85	1.04
1200	59.29	59.39	59.61	0.38	0.48	0.60	0.38	0.48	0.59
1300	58.26	58.67	58.96	0.31	0.40	0.51	0.30	0.37	0.47
1500	54.24	54.85	55.58	0.22	0.30	0.40	0.22	0.27	0.35
2000	47.15	47.58	48.02	0.15	0.22	0.30	0.16	0.20	0.26
2900	45.95	46.01	46.06	0.16	0.21	0.26	0.15	0.19	0.26
3000	46.13	46.22	46.19	0.16	0.21	0.25	0.14	0.19	0.26
3300	47.59	47.54	47.42	0.16	0.21	0.25	0.14	0.19	0.28
3500	48.99	48.82	48.55	0.16	0.20	0.24	0.14	0.20	0.30
3700	50.66	50.47	50.01	0.15	0.20	0.24	0.13	0.20	0.32
3800	51.91	51.50	51.15	0.16	0.21	0.26	0.13	0.21	0.33
4000	55.65	55.10	54.44	0.17	0.22	0.27	0.14	0.22	0.35
4200	63.80	62.25	59.52	0.18	0.23	0.30	0.14	0.23	0.39
4500	55.16	57.63	59.94	0.23	0.28	0.37	0.15	0.25	0.43
4700	45.19	47.63	49.61	0.33	0.38	0.47	0.17	0.27	0.47
4900	32.52	36.58	39.93	0.67	0.61	0.67	0.35	0.36	0.54
5000	22.48	27.72	33.01	1.36	0.98	0.92	1.30	0.72	0.69
5300	21.37	22.08	23.22	8.95	5.83	3.53	0.30	0.43	0.72
5500	23.79	23.23	22.73	3.28	3.63	5.63	0.20	0.35	0.63
5700	26.58	23.90	24.00	6.26	8.76	5.61	0.28	0.39	0.63
5900	52.27	39.56	31.73	1.27	1.93	3.31	0.24	0.43	0.75
6000	46.46	60.57	44.06	0.85	1.19	1.86	0.15	0.35	0.70
6300	37.90	39.08	40.43	0.50	0.67	0.99	0.10	0.25	0.54
6500	36.07	36.61	37.81	0.48	0.63	0.92	0.10	0.26	0.54
6700	34.53	35.09	35.54	0.51	0.65	0.95	0.13	0.27	0.54
6900	33.28	33.68	34.59	0.59	0.73	1.03	0.32	0.36	0.57
7000	32.68	32.91	33.49	0.67	0.80	1.09	0.68	0.52	0.64
7300	31.35	32.03	32.60	1.05	1.11	1.37	0.35	0.60	1.06
7500	29.54	30.51	31.53	1.55	1.52	1.70	0.32	0.47	0.70
7700	28.67	29.33	30.12	2.60	2.30	2.30	0.41	0.49	0.67
7900	28.21	28.00	29.17	4.91	3.93	3.44	0.69	0.66	0.74
8000	31.69	28.80	28.89	6.68	5.36	4.45	0.83	0.85	0.86
8100	39.03	33.06	29.98	8.49	7.02	5.86	0.84	0.91	0.98
8200	41.67	41.33	35.38	9.34	8.58	7.49	1.00	0.92	1.04
8300	37.95	41.55	43.89	8.11	9.04	9.08	1.48	1.14	1.08
8400	33.50	37.14	41.53	6.16	7.74	9.51	1.92	1.64	1.31
8500	30.76	33.41	37.25	4.56	5.98	8.26	1.56	1.97	1.75

Typical Performance Data


FREQ. (MHz)	GROUP DELAY (nsec)		
	@-55°C	@+25°C	@+125°C
10	0.77	0.81	0.75
20	0.83	0.83	0.83
30	0.83	0.83	0.83
40	0.83	0.83	0.83
50	0.83	0.83	0.83
60	0.83	0.83	0.83
70	0.83	0.83	0.82
80	0.83	0.83	0.82
90	0.83	0.83	0.82
100	0.83	0.83	0.82
110	0.83	0.83	0.82
120	0.83	0.83	0.82
130	0.84	0.83	0.82
140	0.84	0.83	0.83
150	0.84	0.83	0.83
160	0.84	0.84	0.83
170	0.85	0.84	0.83
180	0.85	0.84	0.84
190	0.86	0.85	0.84
200	0.86	0.85	0.85
220	0.87	0.86	0.85
240	0.88	0.87	0.87
260	0.90	0.89	0.88
280	0.91	0.90	0.89
300	0.93	0.92	0.91
320	0.95	0.94	0.93
340	0.97	0.95	0.95
360	0.99	0.98	0.97
380	1.02	1.00	0.99
400	1.04	1.03	1.02
420	1.07	1.06	1.04
440	1.11	1.09	1.08
460	1.14	1.12	1.11
480	1.18	1.16	1.14
500	1.23	1.20	1.18
520	1.27	1.25	1.23
540	1.33	1.30	1.27
560	1.39	1.35	1.33
580	1.46	1.42	1.39
600	1.54	1.49	1.46
630	1.69	1.63	1.58

Typical Performance Curves


INSERTION LOSS vs. TEMPERATURE
INPUT POWER = 0 dBm




INSERTION LOSS vs. TEMPERATURE (Zoomed)
INPUT POWER = 0 dBm




INPUT RETURN LOSS vs. TEMPERATURE
INPUT POWER = 0 dBm



OUTPUT RETURN LOSS vs. TEMPERATURE
INPUT POWER = 0 dBm




GROUP DELAY vs. TEMPERATURE
INPUT POWER = 0 dBm




Case Style GE

GE0805C-2

Outline Dimensions



PCB Land Pattern



Suggested Layout,
Tolerance to be within ±.002

CASE #	A	B	C	D	E	F	G	H	J	K	L
GE0805C-2	.079 (2.00)	.049 (1.25)	.037 (0.95)	.014 (0.35)	.012 (0.30)	.012 (0.30)	.026 (0.65)	.025 (0.63)	.134 (3.40)	.110 (2.80)	.014 (0.35)

CASE #	M	WT. GRAM
GE0805C-2	.039 (1.00)	.008

Dimensions are in inches (mm). Tolerances: 2Pl. ± .01; 3 Pl. ± .005

Notes:

1. Open style, ceramic base.
2. Termination finish: For RoHS Case Styles: Tin plate over Nickel plate. All models, (+) suffix.
   For RoHS-5 Case Styles: Tin-Lead plate over Nickel plate. All models, no (+) suffix.
3. Pad tolerance to be non-cumulative. Minimum spacing between each pad is .004 (0.1).

This document and its contents are the property of Mini-Circuits.

Tape & Reel Packaging TR-F114

DEVICE ORIENTATION IN T&R




ILLUSTRATION 1

Applicable Case Styles	
GE0805C	JC0603C
GE0805C-1	JC0603C-4
GE0805C-1AP	JC0603C-6
GE0805C-7	
GE0805C-9	
GE0805C-10	
GE0805C-11	
GE0805C-12	




ILLUSTRATION 2

Applicable Case Styles	
GE0805C-2	JC0603C-1
GE0805C-3	JC0603C-2
GE0805C-4	JC0603C-3
GE0805C-5	JC0603C-5
GE0805C-6	JC0603C-7
GE0805C-8	
GE0805C-15	

Tape Width, mm	Device Cavity Pitch, mm	Reel Size, inches	Devices per Reel	
8	4	7	Small quantity standards (see note)	20
				50
				100
				200
				500
				1000
			Standard	4000

Note: Please Consult individual model data sheet to determine device per reel availability.

Mini-Circuits carrier tape materials provide protection from ESD (Electro-Static Discharge) during handling and transportation. Tapes are static dissipative and comply with industry standards EIA-481/EIA-541.

Go to: www.minicircuits.com/pages/pdfs/tape.pdf


Mini-Circuits®
INTERNET http://www.minicircuits.com
P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661
Distribution Centers NORTH AMERICA 800-654-7949 • 417-335-5935 • Fax 417-335-5945 • EUROPE 44-1252-832600 • Fax 44-1252-837010
Mini-Circuits ISO 9001 & ISO 14001 Certified

This document and its contents are the property of Mini-Circuits.

THIRD ANGLE PROJECTION

REVISIONS					
REV	ECN No.	DESCRIPTION	DATE	DR	AUTH
OR	M148457	NEW RELEASE	10/14/14	GF	MY

SUGGESTED MOUNTING CONFIGURATION FOR GE0805C-4 CASE STYLE, "08FL07" PIN CODE



NOTES:

1. COPLANAR WAVEGUIDE IS SHOWN FOR ROGERS RO4350B WITH DIELECTRIC THICKNESS .010" ± .001". COPPER: 1/2 OZ. EACH SIDE. FOR OTHER MATERIALS TRACE WIDTH AND GAP MAY NEED TO BE MODIFIED.
2. BOTTOM SIDE OF THE PCB IS CONTINUOUS GROUND PLANE.

DENOTES PCB COPPER LAYOUT WITH SMOBC (SOLDER MASK OVER BARE COPPER).

DENOTES COPPER LAND PATTERN FREE OF SOLDER MASK.

UNLESS OTHERWISE SPECIFIED		INITIALS	DATE
DIMENSIONS ARE IN INCHES	DRAWN	GF	10/01/14
TOLERANCES ON:	CHECKED	IL	10/14/14
2 PL DECIMALS ±	APPROVED	MY	10/14/14
3 PL DECIMALS ± .005			
ANGLES ±			
FRACTIONS ±			

Mini-Circuits®
THIS DOCUMENT AND ITS CONTENTS ARE THE PROPERTY OF MINI-CIRCUITS.
EXCEPT FOR USE EXPRESSLY GRANTED, IN WRITING, TO ITS VENDORS, VENDEE AND THE UNITED STATES GOVERNMENT, MINI-CIRCUITS RESERVES ALL PROPRIETARY DESIGN, USE , MANUFACTURING AND REPRODUCTION RIGHTS THERETO.
THESE CONTENTS SHALL NOT BE USED, DUPLICATED OR DISCLOSED TO ANY OUTSIDE PARTY, IN WHOLE OR IN PART, WITHOUT WRITTEN PERMISSION OF MINI-CIRCUITS.

ASHEETA1.DWG REV:A DATE:01/12/95


Mini-Circuits® 13 Neptune Avenue Brooklyn NY 11235

PL, 08FL07, GE0805C-4, TB-799+


SIZE	CODE IDENT	DRAWING NO:	REV:
A	15542	98-PL-429	OR

FILE:	SCALE:	SHEET:
98PL429	15:1	1 OF 1

Evaluation Board and Circuit



TB-799+



Schematic Diagram

Notes:

1. 50 Ohm SMA Female connectors.
2. PCB Material: RO4350 or equivalent,
   Dielectric Constant=3.5, Thickness=.010 inch.

Mini-Circuits®

THIS DOCUMENT AND ITS CONTENTS ARE THE PROPERTY OF MINI-CIRCUITS.

Mini-Circuits

Environmental Specifications ENV111

All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

Specification	Test/Inspection Condition	Reference/Spec
Operating Temperature	-55° to 100°C Ambient Environment	Individual Model Data Sheet
Storage Temperature	-55° to 100° C Ambient Environment	Individual Model Data Sheet
Solderability	10X Magnification	J-STD-002, Para 4.2.5, Test S, 95% Coverage
Thermal Shock	-55° to 100°C, 5 cycles	MIL-STD-202, Method 107, Condition A, Except +100°C

This document and its contents are the property of Mini-Circuits.