Ceramic

Low Pass Filter

LFCG-92+

50Ω DC[1] to 990 MHz

Generic photo used for illustration purposes only

CASE STYLE: GE0805C-2

+RoHS Compliant

The +Suffix identifies RoHS Compliance. See our web site for RoHS Compliance methodologies and qualifications

Available Tape and Reel at no extra cost

Reel Size	Devices/Reel
7"	20, 50, 100, 200, 500,1000, 4000

Features

- Low loss, 0.4 dB typ.
- Small size 0805 (2.0 x 1.25 mm)
- Temperature stable
- LTCC construction

Applications

- Harmonic Rejection
- VHF/UHF transmitters / receivers
- lab use

Specification Definition



Functional Schematic



Top View



Pad Connections

Input	8
Output	4
Ground	1,3,5,7
Isolate (Do not ground)	2,6

Electrical Specifications[1,2] at 25°C

Parameter		F#	Frequency (MHz)	Min.	Typ.	Max.	Unit
Pass Band	Insertion Loss	DC - F1	DC - 990	—	0.4	0.8	dB
	Freq. cut-off	F2	1400	—	3.0	—	dB
	VSWR	DC - F1	DC - 990	—	1.45	—	:1
Stop Band	Rejection Loss	F3	1700	—	30	—	dB
		F4 - F5	1800 - 2700	30	40	—	dB
		F6	5000	—	50	—	dB

[1] *In Application where DC voltage is present at either input or output port, coupling capacitors are required.*
[2] *Measured on Mini-Circuits Characterization Test Board TB-800+*

Maximum Ratings

Operating Temperature	-55°C to +100°C
Storage Temperature	-55°C to +100°C
RF Power Input*	2W at 25°C

*Passband rating, derate linearly to 1W at 100°C ambient
Permanent damage may occur if any of these limits are exceeded.

Typical Performance Data at 25°C

Frequency (MHz)	Insertion Loss (dB)	VSWR (:1)
10	0.06	1.03
20	0.08	1.02
100	0.11	1.11
500	0.34	1.44
700	0.35	1.32
990	0.44	1.22
1400	2.18	1.90
1500	8.83	9.15
1700	32.78	46.32
1800	40.59	62.15
2000	35.16	78.35
2500	55.61	117.43
2700	50.94	116.94
3000	43.62	128.23
3500	41.69	125.95
4000	43.14	130.99
5000	60.95	139.99





Outline Drawing



PCB Land Pattern



Suggested Layout,
Tolerance to be within .002

Pad Connections

Input	8
Output	4
Ground	1,3,5,7
Isolate (Do not ground)	2,6

Demo Board MCL P/N: TB-800+
Suggested PCB Layout (PL-427)



NOTES:

1. COPLANAR WAVEGIDE IS SHOWN FOR ROGERS RO4350B WITH DIELECTRIC THICKNESS .010" ± .001". COPPER: 1/2 OZ. EACH SIDE. FOR OTHER MATERIALS TRACE WIDTH AND GAP MAY NEED TO BE MODIFIED.
2. BOTTOM SIDE OF THE PCB IS CONTINUOUS GROUND PLANE.

DENOTES PCB COPPER LAYOUT WITH SMOBC (SOLDER MASK OVER BARE COPPER).

DENOTES COPPER LAND PATTERN FREE OF SOLDER MASK.

Outline Dimensions (inch / mm)

A	B	C	D	E	F	G
.079	.049	.037	.014	.012	.012	.026
2.01	1.24	0.94	0.36	0.30	0.30	0.66

H	J	K	L	M		wt
.025	.134	.104	0.014	.039		grams
0.64	3.40	2.64	0.36	0.99		.008

Additional Notes

A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.

B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.

C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp

Ceramic Low Pass Filter LFCG-92+

Typical Performance Data

FREQUENCY (MHz)	INSERTION LOSS (dB)	VSWR (:1)
10.0	0.06	1.03
20.0	0.08	1.02
50.0	0.10	1.04
100.0	0.11	1.11
150.0	0.14	1.17
200.0	0.17	1.23
250.0	0.20	1.28
300.0	0.24	1.33
350.0	0.27	1.37
400.0	0.30	1.41
450.0	0.32	1.43
500.0	0.34	1.44
550.0	0.36	1.44
600.0	0.36	1.41
650.0	0.36	1.37
700.0	0.35	1.32
750.0	0.34	1.25
800.0	0.33	1.18
850.0	0.33	1.09
900.0	0.35	1.04
950.0	0.39	1.13
990.0	0.44	1.22
1000.0	0.46	1.25
1100.0	0.68	1.52
1200.0	0.91	1.70
1300.0	1.04	1.43
1400.0	2.18	1.90
1500.0	8.83	9.15
1600.0	19.12	27.82
1700.0	32.78	46.32
1800.0	40.59	62.15
1900.0	35.35	72.27
2000.0	35.16	78.35
2200.0	38.91	90.88
2500.0	55.61	117.43
2700.0	50.94	116.94
3000.0	43.62	128.23
3200.0	42.17	128.69
3500.0	41.69	125.95
3600.0	41.76	138.23
3800.0	42.25	129.20
4000.0	43.14	130.99
4200.0	44.34	136.29
4400.0	46.14	139.09
4600.0	48.71	136.85
4800.0	52.51	145.61
5000.0	60.95	139.99

Ceramic Low Pass Filter LFCG-92+

Typical Performance Curves

Insertion Loss



VSWR



GE0805C-2

Outline Dimensions



PCB Land Pattern



Suggested Layout,
Tolerance to be within ±.002

CASE #	A	B	C	D	E	F	G	H	J	K	L
GE0805C-2	.079 (2.00)	.049 (1.25)	.037 (0.95)	.014 (0.35)	.012 (0.30)	.012 (0.30)	.026 (0.65)	.025 (0.63)	.134 (3.40)	.110 (2.80)	.014 (0.35)

CASE #	M	WT. GRAM
GE0805C-2	.039 (1.00)	.008

Dimensions are in inches (mm). Tolerances: 2Pl. ± .01; 3 Pl. ± .005

Notes:

1. Open style, ceramic base.
2. Termination finish: For RoHS Case Styles: Tin plate over Nickel plate. All models, (+) suffix.
   For RoHS-5 Case Styles: Tin-Lead plate over Nickel plate. All models, no (+) suffix.
3. Pad tolerance to be non-cumulative. Minimum spacing between each pad is .004 (0.1).

This document and its contents are the property of Mini-Circuits.

Tape & Reel Packaging TR-F114

DEVICE ORIENTATION IN T&R



ILLUSTRATION 1

Applicable Case Styles	
GE0805C	JC0603C
GE0805C-1	JC0603C-4
GE0805C-1AP	JC0603C-6
GE0805C-7	
GE0805C-9	
GE0805C-10	
GE0805C-11	
GE0805C-12	



ILLUSTRATION 2

Applicable Case Styles	
GE0805C-2	JC0603C-1
GE0805C-3	JC0603C-2
GE0805C-4	JC0603C-3
GE0805C-5	JC0603C-5
GE0805C-6	JC0603C-7
GE0805C-8	
GE0805C-15	

Tape Width, mm	Device Cavity Pitch, mm	Reel Size, inches	Devices per Reel	
8	4	7	Small quantity standards (see note)	20
				50
				100
				200
				500
				1000
			Standard	4000

Note: Please Consult individual model data sheet to determine device per reel availability.

Mini-Circuits carrier tape materials provide protection from ESD (Electro-Static Discharge) during handling and transportation. Tapes are static dissipative and comply with industry standards EIA-481/EIA-541.

Go to: www.minicircuits.com/pages/pdfs/tape.pdf

Mini-Circuits®
INTERNET http://www.minicircuits.com
P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661
Distribution Centers NORTH AMERICA 800-654-7949 • 417-335-5935 • Fax 417-335-5945 • EUROPE 44-1252-832600 • Fax 44-1252-837010
Mini-Circuits ISO 9001 & ISO 14001 Certified

This document and its contents are the property of Mini-Circuits.

THIRD ANGLE PROJECTION

REVISIONS					
REV	ECN No.	DESCRIPTION	DATE	DR	AUTH
OR	M148395	NEW RELEASE	10/03/14	GF	MY

SUGGESTED MOUNTING CONFIGURATION FOR GE0805C-2 CASE STYLE, "08FL06" PIN CODE



NOTES:

1. COPLANAR WAVEGIDE IS SHOWN FOR ROGERS RO4350B WITH DIELECTRIC THICKNESS .010" ± .001". COPPER: 1/2 OZ. EACH SIDE. FOR OTHER MATERIALS TRACE WIDTH AND GAP MAY NEED TO BE MODIFIED.
2. BOTTOM SIDE OF THE PCB IS CONTINUOUS GROUND PLANE.

DENOTES PCB COPPER LAYOUT WITH SMOBC (SOLDER MASK OVER BARE COPPER).

DENOTES COPPER LAND PATTERN FREE OF SOLDER MASK.

UNLESS OTHERWISE SPECIFIED		INITIALS	DATE
DIMENSIONS ARE IN INCHES	DRAWN	GF	10/01/14
TOLERANCES ON:	CHECKED	IL	10/03/14
2 PL DECIMALS ±	APPROVED	MY	10/03/14
3 PL DECIMALS ± .005			
ANGLES ±			
FRACTIONS ±			

Mini-Circuits®
THIS DOCUMENT AND ITS CONTENTS ARE THE PROPERTY OF MINI-CIRCUITS.
EXCEPT FOR USE EXPRESSLY GRANTED, IN WRITING, TO ITS VENDORS, VENDEE AND THE UNITED STATES GOVERNMENT, MINI-CIRCUITS RESERVES ALL PROPRIETARY DESIGN, USE , MANUFACTURING AND REPRODUCTION RIGHTS THERETO.
THESE CONTENTS SHALL NOT BE USED, DUPLICATED OR DISCLOSED TO ANY OUTSIDE PARTY, IN WHOLE OR IN PART, WITHOUT WRITTEN PERMISSION OF MINI-CIRCUITS.

ASHEETA1.DWG REV:A DATE:01/12/95

Mini-Circuits® 13 Neptune Avenue Brooklyn NY 11235

PL, 08FL06, GE0805C-2, TB-800+

SIZE	CODE IDENT	DRAWING NO:	REV:
A	15542	98-PL-427	OR

FILE:	SCALE:	SHEET:
98PL427	15:1	1 OF 1

Evaluation Board and Circuit



TB-800+



Schematic Diagram

Notes:

1. 50 Ohm SMA Female connectors.
2. PCB Material: RO4350 or equivalent, Dielectric Constant=3.5, Thickness=.010 inch.

Mini-Circuits®

THIS DOCUMENT AND ITS CONTENTS ARE THE PROPERTY OF MINI-CIRCUITS.

Mini-Circuits

Environmental Specifications ENV06

All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

Specification	Test/Inspection Condition	Reference/Spec
Operating Temperature	-55° to 100°C Ambient Environment	Individual Model Data Sheet
Storage Temperature	-55° to 100° C Ambient Environment	Individual Model Data Sheet
Humidity	90 to 95% RH, 240 hours, 50°C	MIL-STD-202, Method 103, Condition A, Except 50°C and end-point electrical test done within 12 hours
Solder Reflow Heat	Sn-Pb Eutetic Process: 225°C peak Pb-Free Process 245° - 250°C peak	J-STD-020, Table 4-1, 4-2 and 5-2, Figure 5-1
Solderability	10X Magnification	J-STD-002, Para 4.2.5, Test S, 95% Coverage
Vibration (High Frequency)	20g peak, 10-2000 Hz, 12 times in each of three perpendicular directions (total 36)	MIL-STD-202, Method 204, Condition D
Mechanical Shock	50g, 11 ms, 1/2-sine, 18 shocks: 3 each direction, each of 3 axes	MIL-STD-202, Method 213, Condition A

This document and its contents are the property of Mini-Circuits.