




FEATURES

- Excellent Power Handling, 8 W
- Small Size, 0.12x0.06"
- 7 Sections
- Temperature Stable
- Hermetically Sealed
- LTCC Construction
- Protected by U.S. Patent 6,943,646



Generic photo used for illustration purposes only

CASE STYLE: FV1206-4

+RoHS Compliant

The +Suffix identifies RoHS Compliance.
See our website for methodologies and qualifications

APPLICATIONS

- Harmonic Rejection
- VHF/UHF Transmitters/Receivers
- Lab Use

PRODUCT OVERVIEW

The LFCN-123+ Low Pass Filter gives microwave communication system designers the ability to reject unwanted harmonics using defined RF parameters. The multilayer construction gives high repeatability of performance. Small wrap-around terminations minimize variations in performance due to parasitics. Covering DC-12000 MHz, these units offer low insertion loss and good rejection.

KEY FEATURES

Feature	Advantages
Small Size (3.20x1.6 mm)	Allows for high layout density of circuit boards, while minimizing effects of parasitics.
Rejection Peaks at Harmonic Frequencies	Provides good rejection of signals at harmonic frequencies, for improved system performance.
Wrap-Around Termination	Provides excellent solderability and easy visual inspection capability.
LTCC Construction	Provides a rugged package that is well suited for tough environments including high humidity and high temperature extremes.



Mini-Circuits

CERAMIC

Low Pass Filter

LFCN-123+

50Ω

DC¹ to 12000 MHz

ELECTRICAL SPECIFICATIONS^{1,2} AT +25°C

Parameter		F#	Frequency (MHz)	Min.	Typ.	Max.	Units
Passband	Insertion Loss	DC-F1	DC-12000			2.5	dB
	Freq. Cut-Off	F2	13000		3.0		dB
	VSWR	DC-F1	DC-12000		1.6		:1
Stopband	Rejection Loss	F3	15000	20			dB
		F4-F5	15500-20000		40		
	VSWR	F3-F6	15500-20000		17		:1

1. In Application where DC voltage is present at either input or output ports, coupling capacitors are required.


2. Measured on Mini-Circuits Characterization Test Board TB-LFCN-123+.

ABSOLUTE MAXIMUM RATINGS


Parameter	Ratings
Operating Temperature	-55°C to +100°C
Storage Temperature	-55°C to +100°C
RF Power Input ³	8 W max. at +25°C

3. Passband rating, derate linearly to 3 W at +100°C ambient.
Permanent damage may occur if any of these limits are exceeded.

TYPICAL FREQUENCY RESPONSE



FUNCTIONAL SCHEMATIC






PIN CONNECTIONS

RF IN	1
RF OUT	3
GROUND	2,4

PRODUCT MARKING: AP


DEMO BOARD MCL P/N: TB-LFCN-123+
SUGGESTED PCB LAYOUT (PL-487)

NOTES:


- TRACE WIDTH AND GAP ARE SHOWN FOR ROGERS R04350B WITH DIELECTRIC THICKNESS .010" ± .001". COPPER: 1/2 OZ. EACH SIDE. FOR OTHER MATERIALS TRACE WIDTH AND GAP MAY NEED TO BE MODIFIED.
- BOTTOM SIDE OF THE PCB IS CONTINUOUS GROUND PLANE.

- DENOTES PCB COPPER LAYOUT WITH SMOBC (SOLDER MASK OVER BARE COPPER)
- DENOTES COPPER LAND PATTERN FREE OF SOLDER MASK

OUTLINE DRAWING



PCB Land Pattern



Suggested Layout,
Tolerance to be within ±.002

OUTLINE DIMENSIONS (Inches mm)



A	B	C	D	E	F	G	H	J
.126	.063	.037	.026	.075	.012	.182	.104	.069
3.20	1.60	0.94	0.66	1.91	0.30	4.62	2.64	1.75
K	L	M	N	P	Q	R	wt	
.119	.041	.039	.013	.024	.020	.039	grams	
3.02	1.04	0.99	0.33	0.61	0.51	0.99	.020	

TAPE & REEL INFORMATION: F75



TYPICAL PERFORMANCE DATA AT +25°C

Frequency (MHz)	Insertion Loss (dB)	VSWR (:1)
10	0.07	1.00
1280	0.31	1.44
1550	0.39	1.55
2080	0.51	1.70
3140	0.48	1.61
4200	0.26	1.05
5000	0.48	1.61
5330	0.62	1.76
6260	0.73	1.85
8450	0.77	1.92
10070	1.07	1.87
11020	0.78	1.29
12010	1.23	1.70
13220	3.56	2.12
15120	38.92	67.22
17710	43.82	57.85
20000	39.95	78.02



NOTES

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
- C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the standard. Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/terms/viewterm.html




Typical Performance Data

FREQ. (MHz)	INSERTION LOSS			INPUT RETURN LOSS			OUTPUT RETURN LOSS		
	(dB)			(dB)			(dB)		
	@ -55°C	@+25°C	@+100°C	@ -55°C	@+25°C	@+100°C	@ -55°C	@+25°C	@+100°C
10.0	0.05	0.06	0.06	68.48	66.32	58.60	63.06	66.52	59.19
50.0	0.05	0.06	0.07	44.38	48.75	54.68	44.14	48.15	52.18
100.0	0.06	0.07	0.08	37.95	40.55	44.13	37.84	40.41	43.72
340.0	0.07	0.10	0.12	29.41	28.01	26.73	29.35	28.00	26.73
390.0	0.08	0.11	0.13	28.14	26.95	25.63	28.06	26.95	25.61
500.0	0.09	0.12	0.15	24.78	24.38	23.64	24.89	24.52	23.75
610.0	0.09	0.14	0.17	22.69	22.50	22.12	22.79	22.60	22.21
720.0	0.11	0.16	0.19	21.35	20.79	20.29	21.48	20.92	20.41
830.0	0.12	0.18	0.23	20.27	19.39	18.68	20.33	19.46	18.75
940.0	0.13	0.20	0.24	19.13	18.49	17.87	19.20	18.57	17.93
1000.0	0.14	0.21	0.25	18.43	18.03	17.58	18.40	18.05	17.61
1280.0	0.19	0.28	0.33	16.16	15.69	15.41	16.16	15.71	15.43
1550.0	0.25	0.34	0.39	14.43	14.28	14.22	14.43	14.31	14.26
1810.0	0.30	0.41	0.48	13.05	12.92	12.86	12.99	12.89	12.84
2080.0	0.36	0.47	0.53	12.11	12.11	12.27	12.07	12.09	12.28
2610.0	0.43	0.55	0.62	11.30	11.46	11.83	11.19	11.38	11.79
3670.0	0.20	0.36	0.48	15.28	15.61	16.16	15.25	15.61	16.25
4200.0	0.07	0.25	0.40	25.23	25.42	25.67	25.36	25.75	26.35
4460.0	0.07	0.25	0.41	33.11	31.74	31.05	34.13	33.00	32.88
5000.0	0.13	0.32	0.47	16.26	16.90	17.96	16.15	16.80	17.90
5640.0	0.25	0.45	0.60	12.75	13.29	14.31	12.71	13.25	14.32
6260.0	0.29	0.52	0.70	12.32	12.71	13.67	12.40	12.81	13.80
6580.0	0.22	0.47	0.68	14.12	14.46	15.41	14.11	14.43	15.31
7200.0	0.07	0.35	0.61	20.90	21.00	21.83	20.73	20.70	21.28
7510.0	0.08	0.36	0.61	30.59	30.60	29.61	31.60	30.71	29.91
8140.0	0.17	0.47	0.74	18.89	18.93	19.32	19.97	20.07	21.56
8760.0	0.26	0.60	0.88	15.55	15.10	15.26	15.85	15.54	16.34
9380.0	0.41	0.78	1.09	15.73	15.68	16.16	16.32	16.75	17.78
9700.0	0.51	0.94	1.20	14.98	14.88	15.31	16.38	16.56	16.77
9830.0	0.50	0.83	1.27	16.57	17.14	17.49	17.66	18.19	18.92
10070.0	0.62	1.01	1.34	14.65	15.50	15.84	15.95	16.60	16.39
10550.0	0.62	1.03	1.37	16.34	17.31	18.46	18.09	18.76	18.66
11020.0	0.52	0.91	1.31	17.79	19.15	20.62	21.92	23.62	22.77
11520.0	0.88	1.26	1.66	14.98	15.70	16.93	25.43	23.88	23.21
11660.0	0.89	1.26	1.70	14.42	15.14	16.08	21.57	20.38	19.34
11800.0	0.88	1.32	1.78	13.93	14.46	15.05	18.69	18.03	17.27
11940.0	0.88	1.31	1.78	12.92	13.23	13.19	15.68	15.31	15.29
12010.0	0.89	1.34	1.82	12.74	12.83	12.64	14.61	14.41	14.18
12150.0	0.94	1.45	1.92	12.29	12.40	12.28	12.63	12.59	12.56
12360.0	1.07	1.61	2.15	11.65	11.55	10.95	11.34	11.22	11.19
12500.0	1.17	1.76	2.30	11.49	11.47	10.94	10.24	10.14	10.23
12750.0	1.54	2.21	2.84	11.13	11.02	10.58	8.66	8.59	8.76
12990.0	2.30	3.20	4.05	9.04	8.55	8.34	6.58	6.19	6.21
13220.0	4.02	5.19	6.34	5.53	5.40	5.62	3.77	3.69	3.84
14170.0	18.61	20.46	22.27	0.43	0.82	1.24	0.18	0.59	0.99
14640.0	27.91	30.47	32.59	0.11	0.49	0.85	0.07	0.33	0.68
14880.0	34.00	36.92	40.42	0.00	0.33	0.64	0.09	0.26	0.54
15120.0	42.47	45.71	44.95	0.07	0.35	0.70	0.15	0.27	0.61
15350.0	44.28	42.57	41.38	0.11	0.25	0.56	0.14	0.23	0.50
15590.0	39.43	38.54	38.10	0.08	0.39	0.76	0.19	0.29	0.63
16060.0	35.83	35.73	35.88	0.11	0.38	0.79	0.10	0.35	0.72
17010.0	36.25	37.06	37.48	0.06	0.52	1.11	0.02	0.46	0.93
18010.0	42.63	43.53	43.18	0.18	0.32	0.99	0.09	0.34	0.94
19010.0	53.25	49.59	49.51	0.41	0.09	0.82	0.34	0.21	1.01
19260.0	45.77	47.23	46.72	0.42	0.18	1.00	0.40	0.22	1.03
19500.0	43.27	43.75	44.79	0.47	0.07	0.79	0.37	0.21	1.02
19750.0	40.67	40.72	41.86	0.50	0.14	0.93	0.41	0.20	0.94
20000.0	39.11	38.83	38.80	0.45	0.19	0.88	0.33	0.27	1.02


Typical Performance Data

FREQ. (MHz)	GROUP DELAY (nsec)		
	@ -55°C	@+25°C	@+100°C
10.0	0.07	0.07	0.07
50.0	0.07	0.07	0.06
100.0	0.07	0.06	0.06
170.0	0.06	0.06	0.06
230.0	0.07	0.06	0.06
280.0	0.06	0.05	0.03
340.0	0.07	0.06	0.06
450.0	0.06	0.06	0.06
500.0	0.06	0.06	0.06
610.0	0.06	0.06	0.06
720.0	0.06	0.06	0.05
830.0	0.07	0.06	0.06
940.0	0.06	0.06	0.06
1000.0	0.05	0.06	0.06
1550.0	0.06	0.05	0.06
2080.0	0.05	0.04	0.05
2610.0	0.08	0.08	0.08
3140.0	0.06	0.05	0.04
4200.0	0.07	0.06	0.06
4730.0	0.07	0.06	0.06
5000.0	0.06	0.06	0.06
5640.0	0.07	0.07	0.06
6260.0	0.06	0.06	0.06
7200.0	0.10	0.09	0.08
7510.0	0.08	0.07	0.08
8140.0	0.09	0.06	0.07
8450.0	0.12	0.11	0.05
8760.0	0.12	0.12	0.09
9070.0	0.13	0.04	0.06
9380.0	0.11	0.07	0.05
9700.0	0.18	0.04	0.13
9830.0	0.11	0.14	0.12
10550.0	0.14	0.23	0.13
10780.0	0.10	0.12	0.13
11020.0	0.22	0.20	0.04
11140.0	0.12	0.21	0.13
11520.0	0.10	0.10	0.12
11590.0	0.08	0.18	0.13
11660.0	0.11	0.14	0.02
11730.0	0.15	0.12	0.22
11870.0	0.14	0.17	0.19
11940.0	0.19	0.14	0.23
12010.0	0.09	0.12	0.13

Typical Performance Data



Typical Performance Data



DEVICE ORIENTATION IN T&R




ILLUSTRATION 1




ILLUSTRATION 2




ILLUSTRATION 3

Applicable Case Styles

FV1206-1
FV1206-3

Applicable Case Styles

FV1206-4
FV1206-5
FV1206-6
FV1206-7
FV1206-9

Applicable Case Styles

FV1206-11
FV1206-12
GE0805C-18
NL1008C-6
NL1008C-7
NL1008C-9
NL1008C-10
NL1008C-12

Tape Width, mm	Device Cavity Pitch, mm	Reel Size, inches	Devices per Reel	
8	4	7	Small quantity standards (see note)	20
				50
				100
				200
				500
				1000
			Standard	3000

Note: Please consult individual model data sheet to determine device per reel availability.

Mini-Circuits carrier tape materials provide protection from ESD (Electro-Static Discharge) during handling and transportation. Tapes are static dissipative and comply with industry standards EIA-481/EIA-541.


Go to: www.minicircuits.com/pages/pdfs/tape.pdf



Distribution Centers NORTH AMERICA 800-654-7949 • 417-335-5935 • Fax 417-335-5945 • **EUROPE** 44-1252-832600 • Fax 44-1252-837010
Mini-Circuits ISO 9001 & ISO 14001 Certified


INTERNET <http://www.minicircuits.com>

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661



REVISIONS					
REV OR	ECN No.	DESCRIPTION	DATE	DR	AUTH
	M158043	NEW RELEASE	09/28/16	CA	ZL

**SUGGESTED MOUNTING CONFIGURATION
FOR FV1206-4 CASE STYLE, "04FL01" PIN CODE**




NOTES:

- TRACE WIDTH AND GAP ARE SHOWN FOR ROGERS R04350B WITH DIELECTRIC THICKNESS .010" ± .001".
COPPER: 1/2 OZ. EACH SIDE.
FOR OTHER MATERIALS TRACE WIDTH AND GAP MAY NEED TO BE MODIFIED.
- BOTTOM SIDE OF THE PCB IS CONTINUOUS GROUND PLANE.



DENOTES PCB COPPER LAYOUT WITH SMOBC (SOLDER MASK OVER BARE COPPER)



DENOTES COPPER LAND PATTERN FREE OF SOLDER MASK

UNLESS OTHERWISE SPECIFIED	INITIALS	DATE
DIMENSIONS ARE IN INCHES	DRAWN CA	09/23/16
TOLERANCES ON:	CHECKED IL	09/27/16
2 PL DECIMALS ±	APPROVED ZL	09/28/16
3 PL DECIMALS ± .005		
ANGLES ±		
FRACTIONS ±		





Mini-Circuits® 13 Neptune Avenue
Brooklyn NY 11235

PL, 04FL01, FV1206-4, TB-860+

Mini-Circuits® THIS DOCUMENT AND ITS CONTENTS ARE THE PROPERTY OF MINI-CIRCUITS. EXCEPT FOR USE EXPRESSLY GRANTED, IN WRITING, TO ITS VENDORS, VENDEE AND THE UNITED STATES GOVERNMENT, MINI-CIRCUITS RESERVES ALL PROPRIETARY DESIGN, USE, MANUFACTURING AND REPRODUCTION RIGHTS THERETO. THESE CONTENTS SHALL NOT BE USED, DUPLICATED OR DISCLOSED TO ANY OUTSIDE PARTY, IN WHOLE OR IN PART, WITHOUT WRITTEN PERMISSION OF MINI-CIRCUITS.	
ASHEETA1.DWG REV:A	DATE:01/12/95

SIZE	CODE IDENT	DRAWING NO:	REV:
A	15542	98-PL-487	OR
FILE:	98PL487	SCALE:	12:1
		SHEET:	1 OF 1

Evaluation Board and Circuit



Schematic Diagram

Notes:

1. 50 Ohm SMA Female connectors.
2. PCB Material: R04350 or equivalent,
Dielectric Constant=3.5, Thickness=.010 inch.

 **Mini-Circuits®**



All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

Specification	Test/Inspection Condition	Reference/Spec
Operating Temperature	-55° to 100°C Ambient Environment	Individual Model Data Sheet
Storage Temperature	-55° to 100° C Ambient Environment	Individual Model Data Sheet
Humidity	90 to 95% RH, 240 hours, 50°C	MIL-STD-202, Method 103, Condition A, Except 50°C and end-point electrical test done within 12 hours
Solder Reflow Heat	Sn-Pb Eutetic Process: 225°C peak Pb-Free Process 245° - 250°C peak	J-STD-020, Table 4-1, 4-2 and 5-2, Figure 5-1
Solderability	10X Magnification	J-STD-002, Para 4.2.5, Test S, 95% Coverage
Vibration (High Frequency)	20g peak, 10-2000 Hz, 12 times in each of three perpendicular directions (total 36)	MIL-STD-202, Method 204, Condition D
Mechanical Shock	50g, 11 ms, 1/2-sine, 18 shocks: 3 each direction, each of 3 axes	MIL-STD-202, Method 213, Condition A