

Engineering Development Model

Power Splitter/Combiner

2 Way-180°

JYPSJ-ED14687/1

Important Note

This model has been designed, built and tested in our engineering department. Performance data represents model capability. At present it is a non-catalog model. On request, we can supply a final specification sheet, part number and price/delivery information.

Please click "Back", and then click "Contact Us" for Applications support.




CASE STYLE : AH202-1

ELECTRICAL SPECIFICATIONS 50Ω @ +25°C				
Parameter		Min.	Typ.	Max. Units
Frequency		500		2200 MHz
Isolation	500-2200 MHz		22.0	dB
Insertion Loss Above 3 dB	500-1100 MHz 1100-2200 MHz		0.80 2.10	
Phase Unbalance	500-1100 MHz 1100-2200 MHz		2.00 6.00	deg.
Amplitude Unbalance	500-1100 MHz 1100-2200 MHz		0.80 0.30	dB
VSWR	SUM Ports OUT Ports		1.65 1.55	(:1)

MAXIMUM RATINGS	
Operating Temperature	-40°C to +85°C
Storage Temperature	-55°C to +100°C

PIN CONNECTIONS	
SUM PORT	8
PORT 1	5
PORT 2	4
GND EXT	1,2,3,6,7

Functional Diagram



P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 • Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site
The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: www.minicircuits.com



IF/RF MICROWAVE COMPONENTS



REV. X1
JYPSJ-ED14687/1
12/2/2011
Page 1 of 1

2 Way-180° Power Splitter/Combiner

JYPSJ-ED14687/1

Typical Performance Data

FREQUENCY (MHz)	TOTAL LOSS ¹ (dB)		AMPLITUDE UNBALANCE (dB)	ISOLATION (dB) 1-2	PHASE UNBALANCE (deg.)	FREQUENCY (MHz)	VSWR (:1)		
	S-1	S-2					S	1	2
500.0	3.68	4.49	0.81	21.18	178.81	500.0	1.82	1.52	1.21
600.0	3.66	4.40	0.74	21.83	179.08	600.0	1.72	1.46	1.17
700.0	3.65	4.30	0.66	22.53	179.34	700.0	1.61	1.40	1.13
800.0	3.64	4.22	0.58	23.33	179.56	800.0	1.50	1.33	1.09
825.0	3.64	4.20	0.56	23.55	179.60	825.0	1.47	1.31	1.09
850.0	3.64	4.18	0.54	23.77	179.65	850.0	1.45	1.29	1.08
875.0	3.65	4.17	0.52	23.98	179.70	875.0	1.42	1.27	1.07
900.0	3.65	4.15	0.50	24.22	179.74	900.0	1.39	1.26	1.06
925.0	3.65	4.13	0.48	24.47	179.79	925.0	1.36	1.24	1.06
950.0	3.66	4.12	0.46	24.72	179.84	950.0	1.34	1.22	1.06
975.0	3.66	4.11	0.44	24.96	179.89	975.0	1.31	1.21	1.06
1000.0	3.67	4.10	0.43	25.20	179.93	1000.0	1.28	1.19	1.06
1050.0	3.69	4.07	0.39	25.72	179.98	1050.0	1.23	1.17	1.07
1100.0	3.70	4.05	0.35	26.19	179.89	1100.0	1.18	1.14	1.09
1150.0	3.73	4.04	0.31	26.65	179.80	1150.0	1.13	1.13	1.12
1200.0	3.76	4.04	0.28	27.00	179.69	1200.0	1.08	1.12	1.14
1250.0	3.80	4.03	0.24	27.31	179.58	1250.0	1.03	1.13	1.17
1300.0	3.83	4.03	0.20	27.40	179.47	1300.0	1.01	1.15	1.21
1350.0	3.88	4.05	0.17	27.47	179.35	1350.0	1.06	1.18	1.24
1400.0	3.92	4.05	0.14	27.31	179.23	1400.0	1.10	1.21	1.28
1425.0	3.94	4.06	0.12	27.21	179.15	1425.0	1.13	1.23	1.29
1450.0	3.97	4.07	0.11	27.10	179.10	1450.0	1.15	1.25	1.31
1475.0	3.99	4.08	0.09	26.90	179.04	1475.0	1.18	1.26	1.33
1500.0	4.01	4.09	0.08	26.69	178.98	1500.0	1.20	1.28	1.35
1550.0	4.07	4.12	0.05	26.22	178.83	1550.0	1.25	1.33	1.39
1600.0	4.12	4.15	0.02	25.75	178.70	1600.0	1.30	1.38	1.44
1700.0	4.24	4.21	0.03	24.69	178.40	1700.0	1.40	1.47	1.53
1800.0	4.35	4.28	0.07	23.63	178.09	1800.0	1.50	1.58	1.64
1900.0	4.47	4.37	0.10	22.69	177.74	1900.0	1.59	1.68	1.75
2000.0	4.57	4.45	0.12	21.84	177.41	2000.0	1.67	1.79	1.86
2100.0	4.66	4.54	0.12	21.10	177.14	2100.0	1.73	1.89	1.97
2200.0	4.76	4.63	0.13	20.52	176.94	2200.0	1.78	1.97	2.08

¹Total Loss = Insertion Loss + 3dB Splitter Loss



P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 • Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site
The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: www.minicircuits.com








IF/RF MICROWAVE COMPONENTS

REV. X1
JYPSJ-ED14687/1
12/2/2011
Page 1 of 1

2 Way-180° Power Splitter/Combiner

Typical Performance Curves

JYPSJ-ED14687/1



Mini-Circuits®
ISO 9001 ISO 14001 AS 9100 CERTIFIED

minicircuits.com

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 • Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site
The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: www.minicircuits.com




IF/RF MICROWAVE COMPONENTS

REV. X1
JYPSJ-ED14687/1
12/2/2011
Page 1 of 1

Outline Dimensions

AH202-1



CASE#	A	B	C	D	E	F	G	H	J	K	L	M	N	WT, GRAM
AH202-1	.38 (9.65)	.50 (12.70)	.25 (6.35)	.020 (0.51)	.115 (2.92)	.070 (1.78)	.035 (0.89)	.050 (1.27)	.090 (2.29)	.040 (1.02)	.105 (2.67)	.140 (3.56)	.095 (2.41)	.80

Dimensions are in inches (mm). Tolerances: 2 Pl. ± 0.01 ; 3 Pl. ± 0.005

Notes:

- Case material: Nickel Silver alloy.
- Base material: Printed wiring laminate.
- Termination finish:

For RoHS 3-5 μ inch (.08-.13 microns) Gold over 120-240 μ inch (3.05-6.10 microns) Nickel plate.

All models, (+) suffix.

For RoHS-5 Case Styles: Tin-Lead plate. All models, no (+) suffix.

Mini-Circuits
ISO 9001 ISO 14001 CERTIFIED

ALL NEW
minicircuits.com


P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site



The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: www.minicircuits.com

RF/IF MICROWAVE COMPONENTS

Tape & Reel Packaging TR-F61



Tape Width, mm	Device Cavity Pitch, mm	Reel Size, inches	Devices per Reel
24	12	13	200

Mini-Circuits carrier tape materials provide protection from ESD (Electro-Static Discharge) during handling and transportation. Tapes are static dissipative and comply with industry standards EIA-481/EIA-541.

Go to: www.minicircuits.com/pages/pdfs/tape.pdf




INTERNET <http://www.minicircuits.com>

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661

Distribution Centers NORTH AMERICA 800-654-7949 • 417-335-5935 • Fax 417-335-5945 • EUROPE 44-1252-832600 • Fax 44-1252-837010

Mini-Circuits ISO 9001 & ISO 14001 Certified


THIRD ANGLE PROJECTION



REVISIONS

REV	ECN No.	DESCRIPTION	DATE	DR	AUTH
OR	M110938	NEW RELEASE	04/12/07	AV	HY

SUGGESTED MOUNTING CONFIGURATION FOR
AH202-2 CASE STYLE, "sb" PIN CONNECTION



- NOTES: 1. TRACE WIDTH IS SHOWN FOR ROGERS RO4350B WITH DIELECTRIC THICKNESS .030" $\pm$.002"; COPPER: 1/2 OZ. EACH SIDE. FOR OTHER MATERIALS TRACE WIDTH MAY NEED TO BE MODIFIED.
2. BOTTOM SIDE OF THE PCB IS CONTINUOUS GROUND PLANE.



DENOTES PCB COPPER LAYOUT WITH SMOBC
(SOLDER MASK OVER BARE COPPER)



DENOTES COPPER LAND PATTERN FREE OF SOLDER MASK

UNLESS OTHERWISE SPECIFIED

INITIALS

DATE

DIMENSIONS ARE IN INCHES

DRAWN

AV

04/11/07

TOLERANCES ON:

CHECKED

IL

04/12/07

2 PL DECIMALS $\pm$

APPROVED

HY

04/12/07

3 PL DECIMALS $\pm$.005ANGLES $\pm$ FRACTIONS $\pm$

Mini-Circuits®

THIS DOCUMENT AND ITS CONTENTS ARE THE PROPERTY OF MINI-CIRCUITS. EXCEPT FOR USE EXPRESSLY GRANTED, IN WRITING, TO ITS VENDORS, VENDEE AND THE UNITED STATES GOVERNMENT, MINI-CIRCUITS RESERVES ALL PROPRIETARY DESIGN, USE, MANUFACTURING AND REPRODUCTION RIGHTS THERETO. THESE CONTENTS SHALL NOT BE USED, DUPLICATED OR DISCLOSED TO ANY OUTSIDE PARTY, IN WHOLE OR IN PART, WITHOUT WRITTEN PERMISSION OF MINI-CIRCUITS.

ASHEETA1.DWG REV:A DATE:01/12/95



Mini-Circuits®

13 Neptune Avenue
Brooklyn NY 11235

PL, sb, AH202-2, SYPS-2, TB-427+

SIZE
A

CODE IDENT
15542

DRAWING NO:
98-PL-274


REV:
OR

FILE: 98PL274


SCALE: 6:1

SHEET: 1 OF 1

Evaluation Board and Circuit



TB-427+



Schematic Diagram

Notes:

1. SMA Female connectors.
2. PCB Material: Rogers R04350 or its equivalent, Dielectric Constant=3.5, Thickness=.030"

 **Mini-Circuits®**



All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

Specification	Test/Inspection Condition	Reference/Spec
Operating Temperature	-40° to 85°C Ambient Environment	Individual Model Data Sheet
Storage Temperature	-55° to 100° C Ambient Environment	Individual Model Data Sheet
Humidity	90 to 95% RH, 240 hours, 50°C	MIL-STD-202, Method 103, Condition A, Except 50°C and end-point electrical test done within 12 hours
Thermal Shock	-55° to 100°C, 100 cycles	MIL-STD-202, Method 107, Condition A-3, except +100°C
Solder Reflow Heat	Sn-Pb Eutetic Process: 225°C peak Pb-Free Process 245° - 250°C peak	J-STD-020, Table 4-1, 4-2 and 5-2, Figure 5-1
Solderability	10X Magnification	J-STD-002, 95% Coverage
Vibration (High Frequency)	20g peak, 10-2000 Hz, 12 times in each of three perpendicular directions (total 36)	MIL-STD-202, Method 204, Condition D
Mechanical Shock	50g, 11 ms, 1/2-sine, 18 shocks: 3 each direction, each of 3 axes	MIL-STD-202, Method 213, Condition A
Marking Resistance to Solvents	Isopropyl alcohol + mineral spirits at 25°C; terpene defluxer at 25°C; distilled water + proylene glycol monomethyl ether + monoethanolamine at 63°C to 70°C	MIL-STD-202, Method 215