



Fixed Attenuators



FEATURES

- One unit each of 3, 6, 10, 20 and 30 dB precision attenuators
- Input power up to 2W Max.
- Excellent VSWR, 1.20:1 to 1.60:1 typ.
- Excellent flatness, 0.20 to 0.60 dB typ.
- BNC Male and Female connectors
- Length less than 2"
- Wideband, DC to 2 GHz, 50Ω

MINI-CIRCUITS DESIGNER'S KITS
SPEED UP
THE SOLUTION



PRODUCT OVERVIEW

K1-HAT-A+ is a designer's kit consisting of five different attenuator models in the HAT-A+ family. There is one unit per model for a total of five units. Mini-Circuits' HAT-A series are fixed attenuators operating from DC to 2000 MHz with excellent attenuation flatness. This attenuator series supports testing and measurement applications. Precise performance, excellent VSWR and rugged unibody construction make these models an ideal solution for systems requiring precise attenuation.

K1-HAT-A+ ELECTRICAL SPECIFICATIONS

(5 models, 1 of each, 5 total)

Model No. ¹	Frequency (GHz) f_L - f_U	Nominal Attenuation ² (dB) DC-2 GHz Typ.	Attenuation Flatness ³ (dB)				VSWR (:1)			Input Power ⁴ (W) Max.
			DC-0.5 GHz	DC-1 GHz	DC-2 GHz	DC-0.5 GHz	DC-1 GHz	DC-2 GHz		
			Typ.	Typ.	Typ.	Typ.	Typ.	Typ.		
HAT-3A+	DC-2	3	0.10	0.15	0.20	1.15	1.20	1.30	2.0	
HAT-6A+	DC-2	6	0.10	0.15	0.20	1.10	1.15	1.20	1.6	
HAT-10A+	DC-2	10	0.20	0.25	0.30	1.20	1.20	1.25	1.7	
HAT-20A+	DC-2	20	0.15	0.20	0.30	1.20	1.30	1.30	0.8	
HAT-30A+	DC-2	30	0.20	0.30	0.60	1.30	1.30	1.60	1.0	

1. See individual model data sheets for more info.

2. Attenuation varies by 0.3 dB max over temperature.

3. Flatness = variation over band divided by 2.


4. RF Power at 25°C. Check individual model datasheet for derated power at 85°C.

Case Style

FF

Outline Dimensions

FF747



CASE #.	A	B	C	D	E	WT GRAMS
FF747	--	.62 (15.75)	--	1.94 (49.28)	--	30.0

Dimensions are in inches (mm). Tolerances: 2Pl. ± .04; 3Pl. ± .030

Notes:

1. Case material: Brass.
2. Case finish: Nickel plate.



P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site



The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: www.minicircuits.com

RF/IF MICROWAVE COMPONENTS



All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

Specification	Test/Inspection Condition	Reference/Spec
Operating Temperature	-45° to 100° C Ambient Environment	Individual Model Data Sheet
Storage Temperature	-55° to 100° C Ambient Environment	Individual Model Data Sheet
Barometric Pressure	100,000 Feet	MIL-STD-202, Method 105, Condition D
Humidity	90% RH, 65°C Units may require bake-out after humidity to restore full performance.	MIL-STD-202, Method 103
Thermal Shock	-65° to 125°C, 5 cycles	MIL-STD-202, Method 107, Condition B
Vibration (High Frequency)	20g peak, 10-2000 Hz, 12 times in each of three perpendicular directions (total 36)	MIL-STD-202, Method 204, Condition D
Mechanical Shock	100g, 6ms sawtooth, 3 shocks each direction 3 axes (total 18)	MIL-STD-202, Method 213, Condition I