

Ceramic

Low Pass Filter

LFCN-2500

50Ω DC⁽¹⁾ to 2500 MHz



Generic photo used for illustration purposes only

CASE STYLE: FV1206

Maximum Ratings


Operating Temperature	-55°C to 100°C
Storage Temperature	-55°C to 100°C
RF Power Input*	10W max. at 25°C

* Passband rating, derate linearly to 3.5W at 100°C ambient. Permanent damage may occur if any of these limits are exceeded.

Pin Connections

RF IN	1
RF OUT	3
GROUND	2,4


Outline Drawing



Outline Dimensions (inch/mm)

A	B	C	D	E	F	G	
.126	.063	.037	.020	.032	.009	.169	
3.20	1.60	0.94	0.51	0.81	0.23	4.29	
H	J	K	L	M	N	P	wt
.087	.024	.122	.024	.087	.012	.071	grams
2.21	0.61	3.10	0.61	2.21	0.30	1.80	.020

Demo Board MCL P/N: TB-270 Suggested PCB Layout (PL-137)



Features

- excellent power handling, 10W
- small size
- 7 sections
- temperature stable
- LTCC construction
- protected by U.S. Patent 6,943,646

Applications

- harmonic rejection
- VHF/UHF transmitters/receivers
- lab use


Electrical Specifications^(1,2) at 25°C

Parameter	F#	Frequency (MHz)	Min.	Typ.	Max.	Unit	
Pass Band	Insertion Loss	DC-F1	DC-2500	—	—	1.0	dB
	Freq. Cut-Off	F2	3075	—	3.0	—	dB
	VSWR	DC-F1	DC-2500	—	1.2	—	:1
Stop Band	Rejection Loss	F3	3675	20	—	—	dB
		F4-F5	3800-6100	—	30	—	dB
		F6	8000	—	20	—	dB
	VSWR	F3-F6	3675-8000	—	20	—	:1

(1) In Application where DC voltage is present at either input or output ports, coupling capacitors are required. Alternatively, if DC pass IN-OUT is required, Mini-Circuits' "D" suffix version of this model will support DC IN-OUT, and provide >100 MOhm isolation to ground.

(2) Measured on Mini-Circuits Characterization Test Board TB-270.

Typical Frequency Response





Electrical Schematic



Typical Performance Data at 25°C

Frequency (MHz)	Insertion Loss (dB)	VSWR (:1)
50.00	0.05	1.02
2000.00	0.50	1.26
2530.00	0.80	1.24
3000.00	2.72	2.58
3660.00	24.30	23.81
3760.00	29.63	28.03
4000.00	43.19	31.03
5000.00	34.98	26.33
6000.00	34.38	24.48
7000.00	26.29	26.74
8000.00	22.85	27.59
10000.00	19.22	18.30
12000.00	14.60	13.09
15000.00	17.48	3.73
20000.00	15.48	4.84



Notes

- Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
- The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp



Ceramic Low Pass Filter

LFCN-2500

Typical Performance Data

FREQ. (MHz)	INSERTION LOSS (dB)			INPUT RETURN LOSS (dB)			OUTPUT RETURN LOSS (dB)		
	@ -55° C	@ +25° C	@ +100° C	@ -55° C	@ +25° C	@ +100° C	@ -55° C	@ +25° C	@ +100° C
50	0.06	0.08	0.08	38.66	36.61	35.50	39.34	37.48	36.01
100	0.07	0.08	0.11	38.82	36.80	35.66	38.89	36.83	35.56
200	0.10	0.12	0.15	34.97	35.46	36.08	35.19	35.74	36.43
300	0.11	0.14	0.16	32.81	34.45	36.47	32.84	34.52	36.99
400	0.12	0.15	0.19	32.65	33.97	36.30	32.89	34.07	36.26
500	0.15	0.18	0.21	32.94	34.08	36.19	33.26	34.06	35.50
600	0.14	0.19	0.24	33.11	34.50	36.97	33.12	33.83	34.91
700	0.16	0.21	0.26	32.80	34.85	37.58	33.14	34.42	35.91
800	0.17	0.23	0.27	33.76	37.00	41.17	32.60	34.00	34.93
900	0.17	0.25	0.30	35.95	40.87	50.14	33.67	34.29	34.00
1000	0.18	0.26	0.32	40.50	48.31	46.84	35.22	34.38	32.96
1200	0.22	0.30	0.37	34.14	33.51	33.43	31.35	30.24	29.47
1300	0.23	0.32	0.40	30.16	29.74	29.79	28.89	28.01	27.37
1500	0.28	0.37	0.46	25.53	24.96	25.14	25.18	24.35	24.01
2000	0.42	0.54	0.65	18.48	18.79	19.11	18.58	18.77	18.89
2500	0.61	0.78	0.95	18.37	18.59	18.91	17.23	17.40	17.77
2530	0.63	0.80	0.96	18.46	18.63	18.91	17.11	17.29	17.60
3000	2.33	2.78	3.26	6.98	6.77	6.52	6.73	6.53	6.31
3500	15.63	16.67	17.75	0.94	1.09	1.25	1.19	1.39	1.55
3660	22.24	23.42	24.64	0.73	0.89	1.03	1.03	1.25	1.45
3760	26.79	28.04	29.33	0.60	0.76	0.90	1.01	1.24	1.44
4000	37.32	38.07	38.76	0.53	0.69	0.82	1.05	1.32	1.58
4500	35.25	35.21	35.18	0.46	0.63	0.76	1.08	1.36	1.64
5000	33.25	33.54	34.08	0.41	0.63	0.81	0.74	0.96	1.13
5500	36.18	36.41	36.70	0.45	0.63	0.85	0.52	0.71	0.86
6000	30.28	31.21	32.18	0.60	0.72	0.88	0.51	0.68	0.83
6500	27.39	27.42	28.40	0.56	0.71	0.88	0.46	0.66	0.84
7000	25.45	26.42	27.08	0.52	0.68	0.90	0.42	0.62	0.89
7500	24.28	23.81	24.85	0.61	0.72	0.90	0.53	0.74	1.02
8000	22.54	22.47	23.37	0.68	0.76	0.95	0.47	0.69	1.01
8500	20.42	21.29	21.79	0.72	0.81	0.99	0.61	0.78	1.13
9000	20.00	20.60	20.65	0.69	0.82	1.03	0.74	0.87	1.29
9500	19.35	19.61	18.89	0.55	0.78	1.10	0.77	1.00	1.35
10000	18.19	18.05	17.03	0.62	0.86	1.20	0.82	1.10	1.36
10500	16.87	17.16	16.36	0.64	0.85	1.15	0.83	1.05	1.19
11000	15.83	16.05	15.78	0.58	0.81	1.07	0.82	1.01	1.13
11500	14.66	15.04	15.01	0.70	0.96	1.26	0.75	0.96	1.10
12000	13.73	13.96	13.97	0.68	0.99	1.40	0.72	1.01	1.24
12500	12.93	12.85	12.77	0.76	1.24	1.79	0.79	1.16	1.44
13000	11.84	11.79	11.97	1.00	1.51	2.10	0.92	1.31	1.69
13500	10.74	11.15	11.73	1.67	2.19	2.69	1.12	1.53	2.04
14000	10.30	11.63	13.87	4.47	6.38	8.77	1.61	2.00	2.45
14500	19.30	19.65	21.06	2.67	2.70	2.96	1.48	2.01	2.65
15000	28.64	32.48	23.04	4.54	5.42	4.78	3.51	5.68	9.57
15500	13.60	14.11	15.17	2.50	3.01	3.53	4.04	3.71	3.77
16000	15.66	15.88	16.91	2.44	3.26	4.16	2.36	2.89	3.51
16500	16.06	16.30	18.44	2.33	2.83	3.45	2.58	3.07	3.41
17000	16.95	17.85	20.37	2.31	2.62	3.25	2.71	3.06	3.30
17500	21.07	22.06	24.04	2.81	3.82	4.84	2.35	2.80	3.20
18000	20.53	18.84	17.42	7.33	10.68	14.76	2.01	2.53	3.13
18500	12.79	13.45	14.72	8.60	7.47	8.31	2.00	2.61	3.42
19000	13.52	14.00	14.77	4.14	4.76	5.89	2.35	3.50	4.98
19500	11.39	12.98	15.48	4.79	4.71	4.33	7.44	8.67	8.29
20000	16.84	18.67	20.09	2.65	2.39	2.44	5.04	4.91	5.14

REV. X2
LFCN-2500
100928
Page 1 of 1



IF/RF MICROWAVE COMPONENTS • ISO 9001 ISO 14001 AS 9100 CERTIFIED • RoHS compliant
P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661




The Design Engineers Search Engine finds the model you need, Instantly • For detailed performance specs & shopping online see




Typical Performance Curves


INSERTION LOSS vs. TEMPERATURE




INPUT RETURN LOSS vs. TEMPERATURE




OUTPUT RETURN LOSS vs. TEMPERATURE



Outline Dimensions



PCB Land Pattern



Suggested Layout,
Tolerance to be within $\pm .002$

CASE #	A	B	C	D	E	F	G	H	J	K	L	M	N	P	WT. GRAM
FV1206	.126 (3.20)	.063 (1.60)	.037 (0.94)	.020 (0.51)	.032 (0.81)	.009 (0.23)	.169 (4.29)	.087 (2.21)	.024 (0.61)	.122 (3.10)	.024 (0.61)	.087 (2.21)	.012 (0.30)	.071 (1.80)	.020

Dimensions are in inches (mm). Tolerances: 2 Pl. $\pm .01$; 3 Pl. $\pm .005$

Notes:

- Open style, ceramic base.
- Termination finish: **as shown below or indicated on Data Sheet.**
For RoHS Case Styles: Tin plate over Nickel plate. All models, (+) suffix.
For RoHS-5 Case Styles: Tin-Lead plate. All models, no (+) suffix.



P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site



The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: www.minicircuits.com

RF/IF MICROWAVE COMPONENTS

Tape & Reel Packaging TR-F71




ILLUSTRATION 1

Tape Width, mm	Device Cavity Pitch, mm	Reel Size, inches	Devices per Reel	
8	4	7	Small quantity standards (see note)	20
				50
				100
				200
				500
				1000
			Standard	3000

Note: Please Consult individual model data sheet to determine device per reel availability.

Mini-Circuits carrier tape materials provide protection from ESD (Electro-Static Discharge) during handling and transportation. Tapes are static dissipative and comply with industry standards EIA-481/EIA-541.

Go to: www.minicircuits.com/pages/pdfs/tape.pdf




P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site



The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: www.minicircuits.com

RF/IF MICROWAVE COMPONENTS


THIRD ANGLE PROJECTION



REVISIONS

REV	ECN No.	DESCRIPTION	DATE	DR	AUTH
OR	M88634	NEW RELEASE	08/28/03	GF	ABD
A	M102713	ADDED "...WITH SMOBC"	01/17/06	MMG	IL

SUGGESTED MOUNTING CONFIGURATION
FOR FV1206 CASE STYLE, "nx" PIN CONNECTION



- NOTES:**
- COPLANAR WAVEGUIDE PARAMETERS ARE SHOWN FOR ROGERS R04350B WITH THICKNESS .020" ± .0015".
 COPPER: 1/2 OZ. EACH SIDE.
 FOR OTHER MATERIALS TRACE WIDTH & GAP MAY NEED TO BE MODIFIED.

2. BOTTOM SIDE OF THE PCB IS CONTINUOUS GROUND PLANE.



DENOTES PCB COPPER LAYOUT WITH SMOBC
 (SOLDER MASK OVER BARE COPPER)



DENOTES COPPER LAND PATTERN FREE OF SOLDER MASK

UNLESS OTHERWISE SPECIFIED

INITIALS

DATE

DIMENSIONS ARE IN INCHES

DRAWN

GF

08/27/03

TOLERANCES ON:

CHECKED

AV

08/28/03

2 PL DECIMALS ±

APPROVED


ABD

08/28/03

3 PL DECIMALS ± .005

ANGLES ±

FRACTIONS ±



Mini-Circuits®

13 Neptune Avenue
 Brooklyn NY 11235

PL, nx, FV1206, LFCN/HFCN, TB-270

THIS DOCUMENT AND ITS CONTENTS ARE THE PROPERTY OF MINI-CIRCUITS. EXCEPT FOR USE EXPRESSLY GRANTED, IN WRITING, TO ITS VENDORS, VENDEE AND THE UNITED STATES GOVERNMENT, MINI-CIRCUITS RESERVES ALL PROPRIETARY DESIGN, USE, MANUFACTURING AND REPRODUCTION RIGHTS THERETO. THESE CONTENTS SHALL NOT BE USED, DUPLICATED OR DISCLOSED TO ANY OUTSIDE PARTY, IN WHOLE OR IN PART, WITHOUT WRITTEN PERMISSION OF MINI-CIRCUITS.

SIZE

CODE IDENT

DRAWING NO:

REV:

A

15542

98-PL-137

A

FILE: 98PL137

SCALE:


10:1

SHEET:

1 OF 1

ASHEETA1.DWG REV:A DATE:01/12/95


Evaluation Board and Circuit



Schematic Diagram

Notes:

1. SMA Female connectors.
2. PCB Material: ROGERS R04350 or equivalent, Dielectric Constant=3.5, Thickness=.020 inch.

 **Mini-Circuits®**

All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

Specification	Test/Inspection Condition	Reference/Spec
Operating Temperature	-55° to 100°C Ambient Environment	Individual Model Data Sheet
Storage Temperature	-55° to 100° C Ambient Environment	Individual Model Data Sheet
Humidity	90 to 95% RH, 240 hours, 50°C	MIL-STD-202, Method 103, Condition A, Except 50°C and end-point electrical test done within 12 hours
Solder Reflow Heat	Sn-Pb Eutetic Process: 225°C peak Pb-Free Process 245° - 250°C peak	J-STD-020, Table 4-1, 4-2 and 5-2, Figure 5-1
Solderability	10X Magnification	J-STD-002, Para 4.2.5, Test S, 95% Coverage
Vibration (High Frequency)	20g peak, 10-2000 Hz, 12 times in each of three perpendicular directions (total 36)	MIL-STD-202, Method 204, Condition D
Mechanical Shock	50g, 11 ms, 1/2-sine, 18 shocks: 3 each direction, each of 3 axes	MIL-STD-202, Method 213, Condition A