



DESIGNER'S KIT K5-BW2+

Fixed Attenuators

50Ω DC to 18GHz



FEATURES

- Wideband, 50Ω
- 3,6 and 10dB precision attenuation
- Input power 5W max.
- Excellent VSWR, 1.25:1 typ.
- Stainless steel SMA Male & Female connectors
- Length 1.20

MINI-CIRCUITS DESIGNER'S KITS
SPEED UP
THE SOLUTION



K5-BW2+ ELECTRICAL SPECIFICATIONS

(3dB,6dB Qty.1ea.) (10dBQty.2) 4 total

Model	Frequency (GHz) f_L - f_U	Attenuation ¹ (dB)		VSWR ² (:1)			Input Power ³ (W) Max.
		Nominal	Accuracy	DC-4GHz Typ.	4-8GHz Max.	8-12.4GHz Max.	
BW-S3W5+	DC - 18	3	±0.40	1.20	1.25	1.30	5
BW-S6W5+	DC - 18	6	±0.40	1.20	1.25	1.30	5
BW-S10W5+	DC - 18	10	±0.60	1.20	1.25	1.30	5

¹. At 25°C, accuracy includes frequency and power variations. Temperature coefficient for attention .0004dB/dB/C° typ.

². VSWR from 12.4 to 18GHz, 1.6:1 typ.

³. Average power at 25°C ambient, derate linearly to 2W at 100°C. Peak power 125W max. 5μsec pulse width, 100Hz PRF.

