

# Frequency Mixer

# LAVI-ED12344A/1

Level 21 (LO Power + 21 dBm)

## Important Note

This model has been designed, built and tested in our engineering department. Performance data represents model capability. At present it is a non-catalog model. On request, we can supply a final specification sheet, part number and price/delivery information.



CASE STYLE : CK605


Please click "Back", and then click "Contact Us" for Applications support.

| ELECTRICAL SPECIFICATIONS 50Ω @ +25°C |                                        |      |      |      |       |
|---------------------------------------|----------------------------------------|------|------|------|-------|
| Parameter                             |                                        | Min. | Typ. | Max. | Units |
| Frequency                             | LO (f <sub>L</sub> to f <sub>U</sub> ) | 270  |      | 970  | MHz   |
|                                       | RF (f <sub>L</sub> to f <sub>U</sub> ) | 270  |      | 970  | MHz   |
|                                       | IF                                     | 10   |      | 600  | MHz   |
| Conversion Loss                       | Total Range                            |      | 7.5  |      | dB    |
| LO-RF Isolation                       |                                        |      | 48   |      | dB    |
| LO-IF Isolation                       |                                        |      | 36   |      | dB    |
| Input IP3                             |                                        |      | +32  |      | dBm   |
| 1 dB Compression                      |                                        |      | +20  |      | dBm   |

| MAXIMUM RATINGS       |                 |
|-----------------------|-----------------|
| Operating Temperature | -45°C to 85°C   |
| Storage Temperature   | -55°C to +100°C |

| PIN CONNECTIONS |                                |
|-----------------|--------------------------------|
| LO              | 10                             |
| RF              | 2                              |
| IF              | 14                             |
| GROUND          | 1,3,4,5,6,7,8,9,11,12,13,15,16 |

## Electrical Schematic



# Frequency Mixer

LAVI-ED12344A/1

## Typical Performance Data

| RF<br>(IN)<br>(MHz) | LO<br>(MHz) | CONVERSION LOSS<br>IF FIXED<br>@IF(OUT)=70MHz<br>(dB) |       |       |
|---------------------|-------------|-------------------------------------------------------|-------|-------|
|                     |             | @LO (dBm)                                             |       |       |
|                     |             | +19                                                   | +21   | +23   |
| 10.1                | 80.1        | 7.00                                                  | 6.90  | 6.81  |
| 40.1                | 110.1       | 7.06                                                  | 6.95  | 6.88  |
| 70.1                | 140.1       | 7.28                                                  | 7.21  | 7.14  |
| 100.1               | 170.1       | 7.41                                                  | 7.33  | 7.26  |
| 130.1               | 200.1       | 7.39                                                  | 7.30  | 7.23  |
| 160.1               | 230.1       | 7.45                                                  | 7.37  | 7.31  |
| 190.1               | 260.1       | 7.47                                                  | 7.39  | 7.33  |
| 220.1               | 290.1       | 7.36                                                  | 7.29  | 7.23  |
| 250.1               | 320.1       | 7.37                                                  | 7.30  | 7.24  |
| 280.1               | 350.1       | 7.51                                                  | 7.43  | 7.37  |
| 310.1               | 380.1       | 7.40                                                  | 7.32  | 7.26  |
| 340.1               | 410.1       | 7.41                                                  | 7.34  | 7.29  |
| 370.1               | 440.1       | 7.52                                                  | 7.45  | 7.40  |
| 400.1               | 470.1       | 7.52                                                  | 7.45  | 7.40  |
| 430.1               | 500.1       | 7.56                                                  | 7.49  | 7.45  |
| 460.1               | 530.1       | 7.63                                                  | 7.58  | 7.54  |
| 490.1               | 560.1       | 7.63                                                  | 7.57  | 7.53  |
| 520.1               | 590.1       | 7.64                                                  | 7.58  | 7.53  |
| 550.1               | 620.1       | 7.74                                                  | 7.69  | 7.65  |
| 580.1               | 650.1       | 7.85                                                  | 7.80  | 7.75  |
| 610.1               | 680.1       | 7.95                                                  | 7.88  | 7.83  |
| 640.1               | 710.1       | 8.00                                                  | 7.93  | 7.88  |
| 670.1               | 740.1       | 8.01                                                  | 7.94  | 7.89  |
| 700.1               | 770.1       | 8.00                                                  | 7.94  | 7.86  |
| 730.1               | 800.1       | 8.05                                                  | 7.98  | 7.94  |
| 760.1               | 830.1       | 8.09                                                  | 8.02  | 7.97  |
| 790.1               | 860.1       | 8.12                                                  | 8.04  | 7.99  |
| 820.1               | 890.1       | 8.20                                                  | 8.12  | 8.06  |
| 850.1               | 920.1       | 8.28                                                  | 8.21  | 8.14  |
| 880.1               | 950.1       | 8.40                                                  | 8.32  | 8.27  |
| 910.1               | 980.1       | 8.56                                                  | 8.49  | 8.43  |
| 940.1               | 1010.1      | 8.71                                                  | 8.62  | 8.56  |
| 970.1               | 1040.1      | 8.80                                                  | 8.70  | 8.64  |
| 1000.1              | 1070.1      | 8.90                                                  | 8.80  | 8.72  |
| 1040.1              | 1110.1      | 9.07                                                  | 8.95  | 8.84  |
| 1070.1              | 1140.1      | 9.23                                                  | 9.09  | 8.96  |
| 1110.1              | 1180.1      | 9.73                                                  | 9.55  | 9.40  |
| 1140.1              | 1210.1      | 10.35                                                 | 10.16 | 10.02 |
| 1180.1              | 1250.1      | 11.45                                                 | 11.24 | 11.07 |
| 1210.1              | 1280.1      | 12.83                                                 | 12.58 | 12.38 |

| RF<br>(IN)<br>(MHz) | LO<br>(MHz) | IP3 INPUT<br>(dBm) |       |       |
|---------------------|-------------|--------------------|-------|-------|
|                     |             | @LO (dBm)          |       |       |
|                     |             | +19                | +21   | +23   |
| 10.1                | 80.1        | 23.69              | 25.84 | 27.71 |
| 40.1                | 110.1       | 26.99              | 27.60 | 28.34 |
| 70.1                | 140.1       | 26.88              | 27.85 | 28.88 |
| 100.1               | 170.1       | 27.08              | 28.31 | 29.03 |
| 130.1               | 200.1       | 27.35              | 28.46 | 29.48 |
| 160.1               | 230.1       | 27.66              | 28.58 | 29.69 |
| 190.1               | 260.1       | 28.49              | 29.63 | 30.73 |
| 220.1               | 290.1       | 28.91              | 30.11 | 31.29 |
| 250.1               | 320.1       | 28.40              | 29.68 | 30.86 |
| 280.1               | 350.1       | 28.23              | 29.44 | 30.67 |
| 310.1               | 380.1       | 29.09              | 30.44 | 31.95 |
| 340.1               | 410.1       | 28.96              | 30.47 | 31.79 |
| 370.1               | 440.1       | 29.39              | 30.79 | 32.05 |
| 400.1               | 470.1       | 29.92              | 31.57 | 32.78 |
| 430.1               | 500.1       | 30.34              | 31.87 | 33.81 |
| 460.1               | 530.1       | 31.02              | 32.74 | 34.27 |
| 490.1               | 560.1       | 31.56              | 33.26 | 34.83 |
| 520.1               | 590.1       | 32.19              | 34.06 | 35.95 |
| 550.1               | 620.1       | 33.25              | 34.60 | 36.38 |
| 580.1               | 650.1       | 32.73              | 34.40 | 36.02 |
| 610.1               | 680.1       | 32.92              | 34.76 | 35.94 |
| 640.1               | 710.1       | 33.16              | 34.45 | 35.96 |
| 670.1               | 740.1       | 32.85              | 34.48 | 35.92 |
| 700.1               | 770.1       | 33.45              | 35.15 | 37.16 |
| 730.1               | 800.1       | 33.03              | 34.99 | 36.42 |
| 760.1               | 830.1       | 32.59              | 34.51 | 35.93 |
| 790.1               | 860.1       | 32.21              | 34.04 | 36.33 |
| 820.1               | 890.1       | 31.27              | 33.32 | 34.73 |
| 850.1               | 920.1       | 30.36              | 31.99 | 33.65 |
| 880.1               | 950.1       | 30.04              | 31.61 | 33.29 |
| 910.1               | 980.1       | 29.71              | 31.36 | 33.02 |
| 940.1               | 1010.1      | 29.27              | 31.18 | 33.41 |
| 970.1               | 1040.1      | 28.65              | 30.72 | 32.56 |
| 1000.1              | 1070.1      | 27.47              | 29.57 | 31.56 |
| 1040.1              | 1110.1      | 25.47              | 27.36 | 29.26 |
| 1070.1              | 1140.1      | 23.53              | 25.39 | 27.26 |
| 1110.1              | 1180.1      | 20.30              | 21.83 | 23.48 |
| 1140.1              | 1210.1      | 18.96              | 20.48 | 22.13 |
| 1180.1              | 1250.1      | 16.93              | 18.58 | 20.61 |
| 1210.1              | 1280.1      | 15.41              | 16.69 | 18.43 |

| RF<br>(IN)<br>(MHz) | LO<br>(MHz) | COMPRESSION<br>@RF IN=+20dBm<br>(dB) |      |      |
|---------------------|-------------|--------------------------------------|------|------|
|                     |             | @LO (dBm)                            |      |      |
|                     |             | +19                                  | +21  | +23  |
| 10.1                | 80.1        | 3.07                                 | 1.92 | 1.15 |
| 40.1                | 110.1       | 1.13                                 | 0.65 | 0.42 |
| 70.1                | 140.1       | 0.64                                 | 0.41 | 0.28 |
| 100.1               | 170.1       | 0.60                                 | 0.39 | 0.27 |
| 130.1               | 200.1       | 0.55                                 | 0.36 | 0.25 |
| 160.1               | 230.1       | 0.55                                 | 0.36 | 0.24 |
| 190.1               | 260.1       | 0.45                                 | 0.30 | 0.20 |
| 220.1               | 290.1       | 0.39                                 | 0.26 | 0.17 |
| 250.1               | 320.1       | 0.43                                 | 0.28 | 0.19 |
| 280.1               | 350.1       | 0.52                                 | 0.34 | 0.22 |
| 310.1               | 380.1       | 0.41                                 | 0.26 | 0.17 |
| 340.1               | 410.1       | 0.37                                 | 0.24 | 0.16 |
| 370.1               | 440.1       | 0.37                                 | 0.24 | 0.16 |
| 400.1               | 470.1       | 0.39                                 | 0.25 | 0.16 |
| 430.1               | 500.1       | 0.32                                 | 0.19 | 0.13 |
| 460.1               | 530.1       | 0.27                                 | 0.16 | 0.11 |
| 490.1               | 560.1       | 0.27                                 | 0.16 | 0.11 |
| 520.1               | 590.1       | 0.33                                 | 0.20 | 0.13 |
| 550.1               | 620.1       | 0.30                                 | 0.17 | 0.11 |
| 580.1               | 650.1       | 0.30                                 | 0.18 | 0.11 |
| 610.1               | 680.1       | 0.29                                 | 0.16 | 0.10 |
| 640.1               | 710.1       | 0.30                                 | 0.18 | 0.11 |
| 670.1               | 740.1       | 0.34                                 | 0.20 | 0.13 |
| 700.1               | 770.1       | 0.34                                 | 0.21 | 0.13 |
| 730.1               | 800.1       | 0.40                                 | 0.24 | 0.15 |
| 760.1               | 830.1       | 0.45                                 | 0.27 | 0.17 |
| 790.1               | 860.1       | 0.49                                 | 0.29 | 0.17 |
| 820.1               | 890.1       | 0.61                                 | 0.37 | 0.23 |
| 850.1               | 920.1       | 0.71                                 | 0.45 | 0.26 |
| 880.1               | 950.1       | 0.80                                 | 0.48 | 0.28 |
| 910.1               | 980.1       | 0.96                                 | 0.57 | 0.32 |
| 940.1               | 1010.1      | 1.21                                 | 0.67 | 0.37 |
| 970.1               | 1040.1      | 1.48                                 | 0.82 | 0.45 |
| 1000.1              | 1070.1      | 1.85                                 | 1.08 | 0.60 |
| 1040.1              | 1110.1      | 2.63                                 | 1.69 | 0.98 |
| 1070.1              | 1140.1      | 3.28                                 | 2.30 | 1.43 |
| 1110.1              | 1180.1      | 4.11                                 | 3.07 | 2.13 |
| 1140.1              | 1210.1      | 4.68                                 | 3.61 | 2.58 |
| 1180.1              | 1250.1      | 5.16                                 | 4.13 | 3.09 |
| 1210.1              | 1280.1      | 5.27                                 | 4.24 | 3.22 |

REV. X2

LAVI-ED12344A/1

101012

Page 1 of 5



IF/RF MICROWAVE COMPONENTS • ISO 9001 ISO 14001 AS9100 CERTIFIED • RoHS compliant  
P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661



The Design Engineers Search Engine finds the model you need, instantly • For detailed performance specs & shopping online see



# Frequency Mixer

LAVI-ED12344A/1

## Typical Performance Data

| IF<br>(OUT)<br>(MHz) | LO<br>(MHz) | CONVERSION LOSS<br>VS. IF FREQUENCY<br>@RF(IN)=490.1MHz<br>(dB) |
|----------------------|-------------|-----------------------------------------------------------------|
|                      |             | @LO (dBm)                                                       |
|                      |             | +21                                                             |
| 480.0                | 10.1        | 9.76                                                            |
| 447.6                | 42.5        | 8.15                                                            |
| 415.2                | 74.9        | 7.95                                                            |
| 399.0                | 91.1        | 7.96                                                            |
| 366.6                | 123.5       | 7.92                                                            |
| 350.3                | 139.8       | 7.86                                                            |
| 317.9                | 172.2       | 7.84                                                            |
| 301.7                | 188.4       | 7.82                                                            |
| 269.3                | 220.8       | 7.72                                                            |
| 253.1                | 237.0       | 7.72                                                            |
| 220.7                | 269.4       | 7.68                                                            |
| 204.5                | 285.6       | 7.63                                                            |
| 172.1                | 318.0       | 7.67                                                            |
| 155.9                | 334.2       | 7.63                                                            |
| 123.4                | 366.7       | 7.65                                                            |
| 107.2                | 382.9       | 7.66                                                            |
| 74.8                 | 415.3       | 7.67                                                            |
| 58.6                 | 431.5       | 7.66                                                            |
| 26.2                 | 463.9       | 7.64                                                            |
| 10.0                 | 480.1       | 7.78                                                            |
| 34.8                 | 524.9       | 7.53                                                            |
| 59.7                 | 549.8       | 7.60                                                            |
| 109.3                | 599.4       | 7.58                                                            |
| 134.1                | 624.2       | 7.54                                                            |
| 183.8                | 673.9       | 7.84                                                            |
| 208.6                | 698.7       | 7.84                                                            |
| 258.3                | 748.4       | 7.75                                                            |
| 283.1                | 773.2       | 7.76                                                            |
| 332.8                | 822.9       | 7.87                                                            |
| 357.6                | 847.7       | 7.94                                                            |
| 407.2                | 897.3       | 8.09                                                            |
| 432.1                | 922.2       | 8.12                                                            |
| 481.7                | 971.8       | 8.38                                                            |
| 506.6                | 996.7       | 8.41                                                            |
| 556.2                | 1046.3      | 8.58                                                            |
| 581.0                | 1071.1      | 8.72                                                            |
| 630.7                | 1120.8      | 8.88                                                            |
| 655.5                | 1145.6      | 9.03                                                            |
| 705.2                | 1195.3      | 9.81                                                            |
| 730.0                | 1220.1      | 10.43                                                           |

| IF<br>(OUT)<br>(MHz) | LO<br>(MHz) | CONVERSION LOSS<br>VS. IF FREQUENCY<br>@RF(IN)=10.1MHz<br>(dB) |
|----------------------|-------------|----------------------------------------------------------------|
|                      |             | @LO (dBm)                                                      |
|                      |             | +21                                                            |
| 10.0                 | 20.1        | 7.82                                                           |
| 50.0                 | 60.1        | 6.94                                                           |
| 90.0                 | 100.1       | 6.84                                                           |
| 130.0                | 140.1       | 6.87                                                           |
| 170.0                | 180.1       | 6.87                                                           |
| 190.0                | 200.1       | 6.96                                                           |
| 230.0                | 240.1       | 7.05                                                           |
| 250.0                | 260.1       | 7.01                                                           |
| 290.0                | 300.1       | 6.97                                                           |
| 310.0                | 320.1       | 7.10                                                           |
| 350.0                | 360.1       | 7.11                                                           |
| 370.0                | 380.1       | 7.08                                                           |
| 410.0                | 420.1       | 7.10                                                           |
| 430.0                | 440.1       | 7.14                                                           |
| 470.0                | 480.1       | 7.18                                                           |
| 490.0                | 500.1       | 7.19                                                           |
| 530.0                | 540.1       | 7.26                                                           |
| 550.0                | 560.1       | 7.30                                                           |
| 590.0                | 600.1       | 7.37                                                           |
| 610.0                | 620.1       | 7.33                                                           |
| 650.0                | 660.1       | 7.26                                                           |
| 670.0                | 680.1       | 7.34                                                           |
| 710.0                | 720.1       | 7.31                                                           |
| 730.0                | 740.1       | 7.38                                                           |
| 770.0                | 780.1       | 7.58                                                           |
| 790.0                | 800.1       | 7.55                                                           |
| 830.0                | 840.1       | 7.68                                                           |
| 850.0                | 860.1       | 7.60                                                           |
| 890.0                | 900.1       | 7.74                                                           |
| 910.0                | 920.1       | 7.89                                                           |
| 950.0                | 960.1       | 8.09                                                           |
| 970.0                | 980.1       | 8.18                                                           |
| 1010.0               | 1020.1      | 8.27                                                           |
| 1030.0               | 1040.1      | 8.25                                                           |
| 1070.0               | 1080.1      | 8.53                                                           |
| 1090.0               | 1100.1      | 8.50                                                           |
| 1130.0               | 1140.1      | 8.87                                                           |
| 1150.0               | 1160.1      | 8.97                                                           |
| 1190.0               | 1200.1      | 9.61                                                           |
| 1210.0               | 1220.1      | 10.00                                                          |

| IF<br>(OUT)<br>(MHz) | LO<br>(MHz) | CONVERSION LOSS<br>VS. IF FREQUENCY<br>@RF(IN)=970.1MHz<br>(dB) |
|----------------------|-------------|-----------------------------------------------------------------|
|                      |             | @LO (dBm)                                                       |
|                      |             | +21                                                             |
| 960.0                | 10.1        | 10.88                                                           |
| 940.0                | 30.1        | 9.54                                                            |
| 920.0                | 50.1        | 9.40                                                            |
| 900.0                | 70.1        | 9.29                                                            |
| 880.0                | 90.1        | 9.17                                                            |
| 860.0                | 110.1       | 9.14                                                            |
| 840.0                | 130.1       | 9.10                                                            |
| 810.0                | 160.1       | 9.07                                                            |
| 790.0                | 180.1       | 9.04                                                            |
| 760.0                | 210.1       | 9.02                                                            |
| 740.0                | 230.1       | 9.09                                                            |
| 710.0                | 260.1       | 8.94                                                            |
| 690.0                | 280.1       | 8.96                                                            |
| 660.0                | 310.1       | 8.98                                                            |
| 640.0                | 330.1       | 8.91                                                            |
| 610.0                | 360.1       | 8.94                                                            |
| 590.0                | 380.1       | 8.96                                                            |
| 560.0                | 410.1       | 8.91                                                            |
| 540.0                | 430.1       | 8.87                                                            |
| 510.0                | 460.1       | 8.81                                                            |
| 490.0                | 480.1       | 8.77                                                            |
| 460.0                | 510.1       | 8.73                                                            |
| 440.0                | 530.1       | 8.64                                                            |
| 410.0                | 560.1       | 8.68                                                            |
| 390.0                | 580.1       | 8.65                                                            |
| 360.0                | 610.1       | 8.65                                                            |
| 340.0                | 630.1       | 8.58                                                            |
| 310.0                | 660.1       | 8.52                                                            |
| 290.0                | 680.1       | 8.40                                                            |
| 260.0                | 710.1       | 8.45                                                            |
| 240.0                | 730.1       | 8.44                                                            |
| 210.0                | 760.1       | 8.41                                                            |
| 190.0                | 780.1       | 8.34                                                            |
| 160.0                | 810.1       | 8.30                                                            |
| 140.0                | 830.1       | 8.28                                                            |
| 110.0                | 860.1       | 8.27                                                            |
| 90.0                 | 880.1       | 8.27                                                            |
| 60.0                 | 910.1       | 8.34                                                            |
| 40.0                 | 930.1       | 8.36                                                            |
| 10.0                 | 960.1       | 8.63                                                            |

REV. X2

LAVI-ED12344A/1

101012

Page 2 of 5



IF/RF MICROWAVE COMPONENTS • ISO 9001 ISO 14001 AS9100 CERTIFIED • RoHS compliant  
P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661



The Design Engineers Search Engine finds the model you need, instantly • For detailed performance specs & shopping online see



# Frequency Mixer

LAVI-ED12344A/1

## Typical Performance Data

| LO<br>(MHz) | LO-RF ISOLATION<br>(dB) |       |       | LO-IF ISOLATION<br>(dB) |       |       |
|-------------|-------------------------|-------|-------|-------------------------|-------|-------|
|             | @LO (dBm)               |       |       | @LO (dBm)               |       |       |
|             | +19                     | +21   | +23   | +19                     | +21   | +23   |
| 80.1        | 62.50                   | 62.12 | 61.79 | 44.80                   | 44.52 | 44.35 |
| 110.1       | 59.11                   | 58.54 | 58.05 | 44.15                   | 44.02 | 43.88 |
| 140.1       | 57.94                   | 56.90 | 56.54 | 44.10                   | 44.03 | 44.00 |
| 170.1       | 56.60                   | 55.81 | 55.08 | 44.00                   | 43.94 | 43.93 |
| 200.1       | 56.53                   | 55.76 | 55.25 | 43.36                   | 43.22 | 43.09 |
| 230.1       | 56.27                   | 55.49 | 54.89 | 42.77                   | 42.65 | 42.58 |
| 260.1       | 55.44                   | 54.71 | 54.13 | 41.89                   | 41.77 | 41.70 |
| 290.1       | 54.95                   | 54.27 | 53.63 | 40.93                   | 40.82 | 40.76 |
| 320.1       | 54.95                   | 54.30 | 53.72 | 40.16                   | 40.00 | 39.89 |
| 350.1       | 54.72                   | 54.07 | 53.52 | 39.63                   | 39.44 | 39.29 |
| 380.1       | 53.02                   | 52.55 | 52.27 | 38.96                   | 38.79 | 38.68 |
| 410.1       | 51.53                   | 51.18 | 50.89 | 38.27                   | 38.10 | 37.98 |
| 440.1       | 50.00                   | 49.69 | 49.42 | 37.76                   | 37.58 | 37.47 |
| 470.1       | 49.64                   | 49.37 | 49.10 | 37.94                   | 37.78 | 37.68 |
| 500.1       | 48.67                   | 48.36 | 48.28 | 38.17                   | 37.98 | 38.03 |
| 530.1       | 47.67                   | 47.36 | 47.36 | 37.99                   | 37.76 | 37.49 |
| 560.1       | 46.09                   | 45.82 | 45.70 | 37.70                   | 37.49 | 37.47 |
| 590.1       | 44.67                   | 44.38 | 44.34 | 37.37                   | 37.13 | 37.16 |
| 620.1       | 43.90                   | 43.84 | 43.70 | 37.30                   | 37.26 | 37.03 |
| 650.1       | 43.65                   | 43.62 | 43.48 | 36.97                   | 36.89 | 36.63 |
| 680.1       | 42.96                   | 42.76 | 42.71 | 36.18                   | 36.01 | 36.02 |
| 710.1       | 41.68                   | 41.45 | 41.41 | 35.90                   | 35.69 | 35.65 |
| 740.1       | 41.06                   | 40.85 | 40.83 | 35.88                   | 35.54 | 35.43 |
| 770.1       | 41.02                   | 41.10 | 40.98 | 36.18                   | 36.07 | 35.80 |
| 800.1       | 41.48                   | 41.44 | 41.62 | 36.57                   | 36.25 | 36.26 |
| 830.1       | 42.22                   | 42.31 | 42.59 | 37.11                   | 36.85 | 36.86 |
| 860.1       | 43.92                   | 44.05 | 44.39 | 38.03                   | 37.72 | 37.67 |
| 890.1       | 46.00                   | 46.04 | 46.36 | 39.19                   | 38.77 | 38.74 |
| 920.1       | 48.24                   | 48.16 | 47.92 | 41.00                   | 40.85 | 40.66 |
| 950.1       | 46.29                   | 45.89 | 45.35 | 42.77                   | 42.79 | 42.83 |
| 980.1       | 42.95                   | 42.51 | 41.96 | 43.53                   | 43.50 | 43.38 |
| 1010.1      | 40.52                   | 39.92 | 39.67 | 42.63                   | 42.30 | 42.19 |
| 1040.1      | 39.53                   | 39.03 | 38.84 | 42.72                   | 42.41 | 42.33 |
| 1070.1      | 39.51                   | 39.00 | 38.80 | 43.20                   | 42.81 | 42.72 |
| 1110.1      | 39.96                   | 39.63 | 39.19 | 44.47                   | 44.23 | 43.84 |
| 1140.1      | 40.35                   | 39.96 | 39.41 | 45.84                   | 45.44 | 44.89 |
| 1180.1      | 40.67                   | 40.20 | 39.49 | 47.43                   | 46.80 | 45.85 |
| 1210.1      | 41.19                   | 40.70 | 40.02 | 49.72                   | 49.14 | 48.26 |
| 1250.1      | 42.23                   | 41.76 | 41.05 | 52.09                   | 52.36 | 52.18 |
| 1280.1      | 43.20                   | 42.73 | 42.09 | 50.04                   | 50.39 | 50.57 |

| RF<br>(IN)<br>(MHz) | LO<br>(MHz) | RF-IF ISOLATION<br>(dB) |       |       |
|---------------------|-------------|-------------------------|-------|-------|
|                     |             | @LO (dBm)               |       |       |
|                     |             | +19                     | +21   | +23   |
| 10.1                | 80.1        | 34.89                   | 35.34 | 36.57 |
| 40.1                | 110.1       | 37.77                   | 38.07 | 38.57 |
| 70.1                | 140.1       | 38.49                   | 38.29 | 37.88 |
| 100.1               | 170.1       | 39.93                   | 39.25 | 38.13 |
| 130.1               | 200.1       | 47.89                   | 48.63 | 52.26 |
| 160.1               | 230.1       | 57.28                   | 63.54 | 64.02 |
| 190.1               | 260.1       | 60.39                   | 58.46 | 55.10 |
| 220.1               | 290.1       | 44.21                   | 43.61 | 42.44 |
| 250.1               | 320.1       | 43.49                   | 42.74 | 41.33 |
| 280.1               | 350.1       | 44.18                   | 43.38 | 42.18 |
| 310.1               | 380.1       | 45.54                   | 45.67 | 45.73 |
| 340.1               | 410.1       | 43.89                   | 43.71 | 43.24 |
| 370.1               | 440.1       | 41.86                   | 41.36 | 40.76 |
| 400.1               | 470.1       | 40.03                   | 39.39 | 38.38 |
| 430.1               | 500.1       | 39.05                   | 38.31 | 37.26 |
| 460.1               | 530.1       | 39.90                   | 39.46 | 39.85 |
| 490.1               | 560.1       | 39.55                   | 39.20 | 38.83 |
| 520.1               | 590.1       | 39.59                   | 39.27 | 38.84 |
| 550.1               | 620.1       | 39.55                   | 39.19 | 38.67 |
| 580.1               | 650.1       | 40.51                   | 40.30 | 39.99 |
| 610.1               | 680.1       | 40.57                   | 40.37 | 40.27 |
| 640.1               | 710.1       | 40.28                   | 40.04 | 39.85 |
| 670.1               | 740.1       | 39.75                   | 39.65 | 39.56 |
| 700.1               | 770.1       | 39.47                   | 39.32 | 39.25 |
| 730.1               | 800.1       | 39.62                   | 39.56 | 39.54 |
| 760.1               | 830.1       | 39.59                   | 39.54 | 39.59 |
| 790.1               | 860.1       | 39.62                   | 39.48 | 39.41 |
| 820.1               | 890.1       | 38.96                   | 38.74 | 38.70 |
| 850.1               | 920.1       | 39.24                   | 39.05 | 38.95 |
| 880.1               | 950.1       | 39.68                   | 39.60 | 39.64 |
| 910.1               | 980.1       | 39.30                   | 39.30 | 39.28 |
| 940.1               | 1010.1      | 38.56                   | 38.43 | 38.33 |
| 970.1               | 1040.1      | 37.32                   | 37.25 | 37.19 |
| 1000.1              | 1070.1      | 35.95                   | 35.88 | 35.87 |
| 1040.1              | 1110.1      | 34.14                   | 34.08 | 34.18 |
| 1070.1              | 1140.1      | 32.71                   | 32.65 | 32.69 |
| 1110.1              | 1180.1      | 32.34                   | 32.35 | 32.66 |
| 1140.1              | 1210.1      | 32.39                   | 32.31 | 32.50 |
| 1180.1              | 1250.1      | 30.47                   | 29.60 | 28.77 |
| 1210.1              | 1280.1      | 29.42                   | 27.97 | 26.65 |

# Frequency Mixer

LAVI-ED12344A/1

## Typical Performance Data

| RF<br>(IN)<br>(MHz) | LO<br>(MHz) | RF VSWR<br>(:1) |      |      |
|---------------------|-------------|-----------------|------|------|
|                     |             | @LO (dBm)       |      |      |
|                     |             | +19             | +21  | +23  |
| 10.1                | 80.1        | 1.18            | 1.20 | 1.22 |
| 40.1                | 110.1       | 1.20            | 1.22 | 1.25 |
| 70.1                | 140.1       | 1.18            | 1.21 | 1.23 |
| 100.1               | 170.1       | 1.19            | 1.21 | 1.23 |
| 130.1               | 200.1       | 1.20            | 1.22 | 1.24 |
| 160.1               | 230.1       | 1.22            | 1.24 | 1.26 |
| 190.1               | 260.1       | 1.25            | 1.27 | 1.29 |
| 220.1               | 290.1       | 1.27            | 1.29 | 1.31 |
| 250.1               | 320.1       | 1.27            | 1.30 | 1.32 |
| 280.1               | 350.1       | 1.27            | 1.29 | 1.31 |
| 310.1               | 380.1       | 1.28            | 1.30 | 1.32 |
| 340.1               | 410.1       | 1.28            | 1.30 | 1.32 |
| 370.1               | 440.1       | 1.27            | 1.29 | 1.30 |
| 400.1               | 470.1       | 1.26            | 1.28 | 1.30 |
| 430.1               | 500.1       | 1.26            | 1.28 | 1.29 |
| 460.1               | 530.1       | 1.25            | 1.27 | 1.29 |
| 490.1               | 560.1       | 1.24            | 1.26 | 1.27 |
| 520.1               | 590.1       | 1.22            | 1.23 | 1.24 |
| 550.1               | 620.1       | 1.20            | 1.21 | 1.22 |
| 580.1               | 650.1       | 1.18            | 1.19 | 1.19 |
| 610.1               | 680.1       | 1.17            | 1.17 | 1.17 |
| 640.1               | 710.1       | 1.17            | 1.16 | 1.16 |
| 670.1               | 740.1       | 1.17            | 1.17 | 1.16 |
| 700.1               | 770.1       | 1.18            | 1.17 | 1.16 |
| 730.1               | 800.1       | 1.20            | 1.19 | 1.17 |
| 760.1               | 830.1       | 1.23            | 1.21 | 1.20 |
| 790.1               | 860.1       | 1.25            | 1.23 | 1.21 |
| 820.1               | 890.1       | 1.28            | 1.25 | 1.23 |
| 850.1               | 920.1       | 1.29            | 1.27 | 1.24 |
| 880.1               | 950.1       | 1.29            | 1.27 | 1.24 |
| 910.1               | 980.1       | 1.30            | 1.27 | 1.24 |
| 940.1               | 1010.1      | 1.31            | 1.27 | 1.25 |
| 970.1               | 1040.1      | 1.33            | 1.30 | 1.27 |
| 1000.1              | 1070.1      | 1.37            | 1.33 | 1.30 |
| 1040.1              | 1110.1      | 1.43            | 1.39 | 1.36 |
| 1070.1              | 1140.1      | 1.48            | 1.44 | 1.40 |
| 1110.1              | 1180.1      | 1.53            | 1.49 | 1.44 |
| 1140.1              | 1210.1      | 1.55            | 1.51 | 1.46 |
| 1180.1              | 1250.1      | 1.58            | 1.55 | 1.51 |
| 1210.1              | 1280.1      | 1.57            | 1.54 | 1.51 |

| LO<br>(MHz) | LO VSWR<br>(:1) |      |      |
|-------------|-----------------|------|------|
|             | @LO (dBm)       |      |      |
|             | +19             | +21  | +23  |
| 80.1        | 7.31            | 7.31 | 7.28 |
| 110.1       | 6.89            | 6.89 | 6.89 |
| 140.1       | 7.38            | 7.34 | 7.34 |
| 170.1       | 7.66            | 7.66 | 7.66 |
| 200.1       | 8.01            | 8.01 | 8.01 |
| 230.1       | 8.20            | 8.20 | 8.16 |
| 260.1       | 8.23            | 8.23 | 8.20 |
| 290.1       | 8.05            | 8.05 | 8.05 |
| 320.1       | 7.73            | 7.73 | 7.73 |
| 350.1       | 7.34            | 7.31 | 7.31 |
| 380.1       | 6.73            | 6.73 | 6.73 |
| 410.1       | 6.09            | 6.09 | 6.09 |
| 440.1       | 5.52            | 5.52 | 5.52 |
| 470.1       | 4.87            | 4.88 | 4.88 |
| 500.1       | 4.25            | 4.25 | 4.26 |
| 530.1       | 3.70            | 3.71 | 3.70 |
| 560.1       | 3.25            | 3.26 | 3.26 |
| 590.1       | 2.84            | 2.85 | 2.86 |
| 620.1       | 2.49            | 2.50 | 2.50 |
| 650.1       | 2.22            | 2.22 | 2.22 |
| 680.1       | 2.03            | 2.04 | 2.04 |
| 710.1       | 1.94            | 1.95 | 1.96 |
| 740.1       | 1.95            | 1.96 | 1.97 |
| 770.1       | 2.06            | 2.07 | 2.09 |
| 800.1       | 2.25            | 2.26 | 2.27 |
| 830.1       | 2.50            | 2.51 | 2.52 |
| 860.1       | 2.78            | 2.79 | 2.80 |
| 890.1       | 3.05            | 3.06 | 3.08 |
| 920.1       | 3.31            | 3.31 | 3.32 |
| 950.1       | 3.52            | 3.53 | 3.54 |
| 980.1       | 3.65            | 3.67 | 3.68 |
| 1010.1      | 3.68            | 3.68 | 3.67 |
| 1040.1      | 3.64            | 3.65 | 3.65 |
| 1070.1      | 3.47            | 3.48 | 3.50 |
| 1110.1      | 3.14            | 3.14 | 3.14 |
| 1140.1      | 2.86            | 2.87 | 2.88 |
| 1180.1      | 2.46            | 2.47 | 2.47 |
| 1210.1      | 2.20            | 2.20 | 2.20 |
| 1250.1      | 1.88            | 1.89 | 1.89 |
| 1280.1      | 1.68            | 1.68 | 1.69 |

| IF<br>(OUT)<br>(MHz) | IF VSWR<br>@LO=1040MHz<br>(:1) |      |      |
|----------------------|--------------------------------|------|------|
|                      | @LO (dBm)                      |      |      |
|                      | +19                            | +21  | +23  |
| 10.0                 | 1.18                           | 1.22 | 1.25 |
| 30.0                 | 1.22                           | 1.26 | 1.29 |
| 50.0                 | 1.21                           | 1.25 | 1.28 |
| 70.0                 | 1.25                           | 1.29 | 1.32 |
| 90.0                 | 1.28                           | 1.31 | 1.34 |
| 110.0                | 1.30                           | 1.33 | 1.35 |
| 130.0                | 1.38                           | 1.40 | 1.42 |
| 150.0                | 1.39                           | 1.41 | 1.43 |
| 170.0                | 1.43                           | 1.45 | 1.47 |
| 190.0                | 1.50                           | 1.52 | 1.53 |
| 210.0                | 1.53                           | 1.54 | 1.56 |
| 230.0                | 1.61                           | 1.62 | 1.64 |
| 250.0                | 1.62                           | 1.63 | 1.64 |
| 270.0                | 1.68                           | 1.68 | 1.69 |
| 290.0                | 1.76                           | 1.76 | 1.76 |
| 310.0                | 1.77                           | 1.77 | 1.77 |
| 350.0                | 1.86                           | 1.86 | 1.85 |
| 370.0                | 1.90                           | 1.90 | 1.90 |
| 410.0                | 1.97                           | 1.96 | 1.96 |
| 430.0                | 2.04                           | 2.03 | 2.02 |
| 470.0                | 2.08                           | 2.06 | 2.05 |
| 490.0                | 2.15                           | 2.13 | 2.12 |
| 530.0                | 2.16                           | 2.13 | 2.11 |
| 550.0                | 2.15                           | 2.12 | 2.10 |
| 590.0                | 2.23                           | 2.20 | 2.17 |
| 610.0                | 2.16                           | 2.12 | 2.10 |
| 650.0                | 2.21                           | 2.17 | 2.13 |
| 670.0                | 2.22                           | 2.17 | 2.14 |
| 710.0                | 2.13                           | 2.08 | 2.04 |
| 730.0                | 2.17                           | 2.12 | 2.08 |
| 770.0                | 2.13                           | 2.08 | 2.03 |
| 790.0                | 2.14                           | 2.08 | 2.04 |
| 830.0                | 2.12                           | 2.07 | 2.02 |
| 850.0                | 2.12                           | 2.07 | 2.01 |
| 890.0                | 2.11                           | 2.05 | 2.00 |
| 910.0                | 2.06                           | 2.00 | 1.94 |
| 950.0                | 2.09                           | 2.03 | 1.97 |
| 970.0                | 2.05                           | 1.99 | 1.93 |
| 1010.0               | 2.00                           | 1.93 | 1.88 |
| 1030.0               | 2.04                           | 1.97 | 1.92 |

REV. X2

LAVI-ED12344A/1

101012

Page 4 of 5



IF/RF MICROWAVE COMPONENTS • ISO 9001 ISO 14001 AS9100 CERTIFIED • RoHS compliant  
P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661



The Design Engineers Search Engine finds the model you need, instantly • For detailed performance specs & shopping online see



## Harmonics Tables

RF HARMONICS ORDER

|        | (-dBm) | (-dBc) |     |     |     |     |     |     |     |     |     |     |
|--------|--------|--------|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|
| 0      | -      | -      | 14  | 19  | 16  | 26  | 35  | 45  | 37  | 46  | 50  | 55  |
| 1      | -      | 33     | +0  | 37  | 12  | 42  | 22  | 44  | 33  | 46  | 41  | 51  |
| 2      | 55     | 61     | 63  | 63  | 63  | 55  | 54  | 54  | 55  | 56  | 57  | 58  |
| 3      | 83     | 86     | 68  | 82  | 65  | 81  | 69  | 79  | 72  | 80  | 78  | 84  |
| 4      | >90    | >87    | >87 | >87 | >87 | >87 | >87 | >87 | >87 | >87 | >87 | >87 |
| 5      | >90    | >87    | >87 | >87 | >87 | >87 | >87 | >87 | >87 | >87 | >87 | >87 |
| 6      | >90    | >87    | >87 | >87 | >87 | >87 | >87 | >87 | >87 | >87 | >87 | >87 |
| 7      | >90    | >87    | >87 | >87 | >87 | >87 | >87 | >87 | >87 | >87 | >87 | >87 |
| 8      | >90    | >87    | >87 | >87 | >87 | >87 | >87 | >87 | >87 | >87 | >87 | >87 |
| 9      | >90    | >87    | >87 | >87 | >87 | >87 | >87 | >87 | >87 | >87 | >87 | >87 |
| 10     | >90    | >87    | >87 | >87 | >87 | >87 | >87 | >87 | >87 | >87 | >87 | >87 |
| RF CAL | 0      | 1      | 2   | 3   | 4   | 5   | 6   | 7   | 8   | 9   | 10  |     |

## LO HARMONICS ORDER

Test conditions:

RF IN: 490.1 MHz; 5.00 dBm.

LO IN: 560.1 MHz; +21.00 dBm

IF OUT: 70 MHz; -2.95 dBm

RF HARMONICS ORDER

|        | (-dBm) | (-dBc) |     |     |     |     |     |     |     |     |     |     |
|--------|--------|--------|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|
| 0      | -      | -      | 24  | 27  | 25  | 34  | 44  | 52  | 43  | 52  | 46  | 57  |
| 1      | -      | 33     | +0  | 37  | 13  | 43  | 23  | 45  | 36  | 48  | 39  | 53  |
| 2      | 36     | 52     | 53  | 53  | 54  | 46  | 45  | 45  | 46  | 46  | 49  | 50  |
| 3      | 55     | 70     | 50  | 67  | 48  | 63  | 50  | 62  | 53  | 63  | 59  | 66  |
| 4      | 76     | 90     | 81  | 80  | 77  | 76  | 78  | 74  | 75  | 72  | 74  | 73  |
| 5      | >90    | 94     | 76  | 92  | 76  | 86  | 75  | 84  | 80  | 85  | 79  | 89  |
| 6      | >90    | >96    | >96 | >96 | 95  | >96 | 91  | >96 | 91  | >96 | >96 | >96 |
| 7      | >90    | >96    | >96 | >96 | >96 | >96 | >96 | >96 | >96 | 92  | >96 | >96 |
| 8      | >90    | >96    | >96 | >96 | >96 | >96 | >96 | >96 | 94  | >96 | >96 | >96 |
| 9      | >90    | >96    | >96 | >96 | >96 | >96 | >96 | 92  | >96 | >96 | >96 | >96 |
| 10     | >90    | >96    | >96 | >96 | >96 | >96 | >96 | >96 | >96 | >96 | >96 | >96 |
| RF CAL | 0      | 1      | 2   | 3   | 4   | 5   | 6   | 7   | 8   | 9   | 10  |     |

## LO HARMONICS ORDER

Test conditions:

RF IN: 490.1 MHz; 15.00 dBm.

LO IN: 560.1 MHz; +21.00 dBm

IF OUT: 70 MHz; 6.38 dBm

Notes: 1. All Harmonics are in (dBc) relative to IF OUTPUT.

2. + entry denotes harmonics are in (dBc) above IF OUTPUT.

3. RF Cal represent the Harmonics level of the RF input signal to the mixer.

REV. X2

LAVI-ED12344A/1

101012

Page 5 of 5



IF/RF MICROWAVE COMPONENTS • ISO 9001 ISO 14001 AS9100 CERTIFIED • RoHS compliant  
P.O. Box 350186, Brooklyn, New York 11235-0008 (718) 934-4500 Fax (718) 332-4661



The Design Engineers Search Engine finds the model you need, instantly • For detailed performance specs & shopping online see




# Frequency Mixer


LAVI-ED12344A/1

## Typical Performance Curves


Conversion Loss @ IF=70MHz




Conversion Loss vs. LO @ RF=490.1MHz




Conversion Loss vs. IF @ RF=490.1MHz




Conversion Loss vs. IF @ RF=10.1MHz




Conversion Loss vs. IF @ RF=970.1MHz



IP3 Input




Compression @ RF IN=+20dBm




## Typical Performance Curves


LO-RF Isolation




LO-IF Isolation




RF-IF Isolation




RF VSWR



LO VSWR



IF VSWR



## Harmonics Tables

RF HARMONICS ORDER

|        | (-dBm) | (-dBc) |     |     |     |     |     |     |     |     |     |     |
|--------|--------|--------|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|
| 0      | -      | -      | 14  | 19  | 16  | 26  | 35  | 45  | 37  | 46  | 50  | 55  |
| 1      | -      | 33     | +0  | 37  | 12  | 42  | 22  | 44  | 33  | 46  | 41  | 51  |
| 2      | 55     | 61     | 63  | 63  | 63  | 55  | 54  | 54  | 55  | 56  | 57  | 58  |
| 3      | 83     | 86     | 68  | 82  | 65  | 81  | 69  | 79  | 72  | 80  | 78  | 84  |
| 4      | >90    | >87    | >87 | >87 | >87 | >87 | >87 | >87 | >87 | >87 | >87 | >87 |
| 5      | >90    | >87    | >87 | >87 | >87 | >87 | >87 | >87 | >87 | >87 | >87 | >87 |
| 6      | >90    | >87    | >87 | >87 | >87 | >87 | >87 | >87 | >87 | >87 | >87 | >87 |
| 7      | >90    | >87    | >87 | >87 | >87 | >87 | >87 | >87 | >87 | >87 | >87 | >87 |
| 8      | >90    | >87    | >87 | >87 | >87 | >87 | >87 | >87 | >87 | >87 | >87 | >87 |
| 9      | >90    | >87    | >87 | >87 | >87 | >87 | >87 | >87 | >87 | >87 | >87 | >87 |
| 10     | >90    | >87    | >87 | >87 | >87 | >87 | >87 | >87 | >87 | >87 | >87 | >87 |
| RF CAL | 0      | 1      | 2   | 3   | 4   | 5   | 6   | 7   | 8   | 9   | 10  |     |

### LO HARMONICS ORDER

Test conditions: RF IN: 490.1 MHz; 5.00 dBm.  
LO IN: 560.1 MHz; +21.00 dBm  
IF OUT: 70 MHz; -2.95 dBm

RF HARMONICS ORDER

|        | (-dBm) | (-dBc) |     |     |     |     |     |     |     |     |     |     |
|--------|--------|--------|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|
| 0      | -      | -      | 24  | 27  | 25  | 34  | 44  | 52  | 43  | 52  | 46  | 57  |
| 1      | -      | 33     | +0  | 37  | 13  | 43  | 23  | 45  | 36  | 48  | 39  | 53  |
| 2      | 36     | 52     | 53  | 53  | 54  | 46  | 45  | 45  | 46  | 46  | 49  | 50  |
| 3      | 55     | 70     | 50  | 67  | 48  | 63  | 50  | 62  | 53  | 63  | 59  | 66  |
| 4      | 76     | 90     | 81  | 80  | 77  | 76  | 78  | 74  | 75  | 72  | 74  | 73  |
| 5      | >90    | 94     | 76  | 92  | 76  | 86  | 75  | 84  | 80  | 85  | 79  | 89  |
| 6      | >90    | >96    | >96 | >96 | 95  | >96 | 91  | >96 | 91  | >96 | >96 | >96 |
| 7      | >90    | >96    | >96 | >96 | >96 | >96 | >96 | >96 | >96 | 92  | >96 | >96 |
| 8      | >90    | >96    | >96 | >96 | >96 | >96 | >96 | >96 | 94  | >96 | >96 | >96 |
| 9      | >90    | >96    | >96 | >96 | >96 | >96 | >96 | 92  | >96 | >96 | >96 | >96 |
| 10     | >90    | >96    | >96 | >96 | >96 | >96 | >96 | >96 | >96 | >96 | >96 | >96 |
| RF CAL | 0      | 1      | 2   | 3   | 4   | 5   | 6   | 7   | 8   | 9   | 10  |     |

### LO HARMONICS ORDER



Test conditions: RF IN: 490.1 MHz; 15.00 dBm.  
LO IN: 560.1 MHz; +21.00 dBm  
IF OUT: 70 MHz; 6.38 dBm

- Notes: 1. All Harmonics are in (dBc) relative to IF OUTPUT.  
2. + entry denotes harmonics are in (dBc) above IF OUTPUT.  
3. RF Cal represent the Harmonics level of the RF input signal to the mixer.

## Outline Dimensions

CK605

## PCB Land Pattern



Suggested Layout,  
Tolerance to be within  $\pm .002$

| CASE # | A               | B               | C              | D              | E              | F              | G              | H              | J               | K              |
|--------|-----------------|-----------------|----------------|----------------|----------------|----------------|----------------|----------------|-----------------|----------------|
| CK605  | .500<br>(12.70) | .500<br>(12.70) | .180<br>(4.57) | .100<br>(2.54) | .080<br>(2.03) | .115<br>(2.92) | .060<br>(1.52) | .040<br>(1.02) | .540<br>(13.72) | .060<br>(1.52) |

| CASE # | L              | M              | N              | P              | Q              | R              | S              | T              | WT. GRAM            |
|--------|----------------|----------------|----------------|----------------|----------------|----------------|----------------|----------------|---------------------|
| CK605  | .100<br>(2.54) | .135<br>(3.43) | .135<br>(3.43) | .115<br>(2.92) | .140<br>(3.56) | .070<br>(1.78) | .150<br>(3.81) | .070<br>(1.78) | 1.2<br>+0.5<br>-0.0 |

Dimensions are in inches (mm). Tolerances: 2 Pl.  $\pm .03$ ; 3Pl.  $\pm .015$

### Notes:

- Case material: Nickel-Silver alloy.
- Base: Printed wiring laminate.
- Termination finish:  
For RoHS Case Styles: 3-5  $\mu$  inch (.08-.13 microns) Gold over 120-240  $\mu$  inch (3.05-6.10 microns) Nickel plate.  
All models, (+) suffix.




P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site



The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: [www.minicircuits.com](http://www.minicircuits.com)

RF/IF MICROWAVE COMPONENTS

# Tape & Reel Packaging TR-F37



| Tape Width, mm | Device Cavity Pitch, mm | Reel Size, inches | Devices per Reel                    |     |
|----------------|-------------------------|-------------------|-------------------------------------|-----|
| 24             | 16                      | 7                 | Small quantity standards (see note) | 10  |
|                |                         |                   |                                     | 20  |
|                |                         |                   |                                     | 50  |
|                |                         |                   |                                     | 100 |
|                |                         | 13                | Standard                            | 200 |
|                |                         |                   |                                     | 500 |

Note: Please consult individual model data sheet to determine device per reel availability.

Mini-Circuits carrier tape materials provide protection from ESD (Electro-Static Discharge) during handling and transportation. Tapes are static dissipative and comply with industry standards EIA-481/EIA-541.

Go to: [www.minicircuits.com/pages/pdfs/tape.pdf](http://www.minicircuits.com/pages/pdfs/tape.pdf)




INTERNET <http://www.minicircuits.com>

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661

Distribution Centers NORTH AMERICA 800-654-7949 • 417-335-5935 • Fax 417-335-5945 • EUROPE 44-1252-832600 • Fax 44-1252-837010

Mini-Circuits ISO 9001 & ISO 14001 Certified


## THIRD ANGLE PROJECTION



## REVISIONS

| REV | ECN No. | DESCRIPTION               | DATE     | DR  | AUTH |
|-----|---------|---------------------------|----------|-----|------|
| E   | M105563 | ADDED "rl" PIN CONNECTION | 06/02/06 | MMG | DJ   |
| F   | M105640 | CORRECTED NOTE 2          | 06/08/06 | MMG | MM   |
| G   | M124395 | ADDED "RAMP"              | 09/09    | EM  | HH   |
| G   | R77589  | ADDED "RAMP"              | 09/09    | EM  | HH   |


SUGGESTED MOUNTING CONFIGURATION FOR  
CK605 CASE STYLE, "kg/rl/16AM01" PIN CONNECTION

NOTES:

1. TRACE WIDTH IS SHOWN FOR FR4 WITH DIELECTRIC THICKNESS .030"  $\pm$  .002"; COPPER: 1/2 OZ. EACH SIDE. FOR OTHER MATERIALS TRACE WIDTH MAY NEED TO BE MODIFIED.
2. BOTTOM SIDE OF THE BOTTOM IS CONTINUOUS GROUND PLANE.



DENOTES PCB COPPER LAYOUT WITH SMOBC  
(SOLDER MASK OVER BARE COPPER)



DENOTES COPPER LAND PATTERN FREE OF SOLDER MASK

UNLESS OTHERWISE SPECIFIED

INITIALS

DATE

DIMENSIONS ARE IN INCHES

TOLERANCES ON:

2 PL DECIMALS  $\pm$ 3 PL DECIMALS  $\pm$  .005ANGLES  $\pm$ FRACTIONS  $\pm$ 

DRAWN

AV

08/07/00

CHECKED

SK

08/08/00

APPROVED

DB

08/08/00

Mini-Circuits®

THIS DOCUMENT AND ITS CONTENTS ARE THE PROPERTY OF MINI-CIRCUITS. EXCEPT FOR USE EXPRESSLY GRANTED, IN WRITING, TO ITS VENDORS, VENDEE AND THE UNITED STATES GOVERNMENT, MINI-CIRCUITS RESERVES ALL PROPRIETARY DESIGN, USE, MANUFACTURING AND REPRODUCTION RIGHTS THERETO. THESE CONTENTS SHALL NOT BE USED, DUPLICATED OR DISCLOSED TO ANY OUTSIDE PARTY, IN WHOLE OR IN PART, WITHOUT WRITTEN PERMISSION OF MINI-CIRCUITS.

ASHEETA1.DWG REV:A DATE:01/12/95



**Mini-Circuits®** 13 Neptune Avenue  
Brooklyn NY 11235

PL,kg/rl/16AM01,CK605,ROS/LAVI/RAMP

SIZE  
A

CODE IDENT  
15542

DRAWING NO:  
98-PL-012



REV:  
G

FILE: 98PL012

SCALE: 5:1

SHEET: 1 OF 1

# Evaluation Board and Circuit



## Notes:

1. SMA Female connectors.
2. PCB Material: Rogers R04350 or equivalent,  
Dielectric Constant=3.5, Thickness=.028 inch.

## Schematic Diagram

 **Mini-Circuits®**



All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

| Specification                  | Test/Inspection Condition                                                                                                                                       | Reference/Spec                                                                                       |
|--------------------------------|-----------------------------------------------------------------------------------------------------------------------------------------------------------------|------------------------------------------------------------------------------------------------------|
| Operating Temperature          | -45° to 85°C<br>Ambient Environment                                                                                                                             | Individual Model Data Sheet                                                                          |
| Storage Temperature            | -55° to 100° C<br>Ambient Environment                                                                                                                           | Individual Model Data Sheet                                                                          |
| Humidity                       | 90 to 95% RH, 240 hours, 50°C                                                                                                                                   | MIL-STD-202, Method 103, Condition A, Except 50°C and end-point electrical test done within 12 hours |
| Thermal Shock                  | -55° to 100°C, 100 cycles                                                                                                                                       | MIL-STD-202, Method 107, Condition A-3, except +100°C                                                |
| Solder Reflow Heat             | Sn-Pb Eutectic Process: 225°C peak<br>Pb-Free Process, 245°C peak                                                                                               | J-STD-020, Table 4-1, 4-2 and 5-2, Figure 5-1                                                        |
| Solderability                  | 10X Magnification                                                                                                                                               | J-STD-002, 95% Coverage                                                                              |
| Vibration (High Frequency)     | 20g peak, 10-2000 Hz, 12 times in each of three perpendicular directions (total 36)                                                                             | MIL-STD-202, Method 204, Condition D                                                                 |
| Mechanical Shock               | 50g, 11 ms, 1/2-sine, 18 shocks: 3 each direction, each of 3 axes                                                                                               | MIL-STD-202, Method 213, Condition A                                                                 |
| Marking Resistance to Solvents | Isopropyl alcohol + mineral spirits at 25°C; terpene defluxer at 25°C;<br>distilled water + proylene glycol monomethyl ether + monoethanolamine at 63°C to 70°C | MIL-STD-202, Method 215                                                                              |