

# Ceramic Diplexer

## LDPW-162-242+

50Ω DC to 6000 MHz (DC-1650, 2400-6000 MHz)



CASE STYLE: JC0603C

### Maximum Ratings


Operating Temperature	-55°C to 100°C
Storage Temperature*	-55°C to 100°C
RF Power Input**	2W at 25°C

\* 12 months max.  
\*\* passband rating, derate linearly to 1W at 100°C ambient.  
Permanent damage may occur if any of these limits are exceeded.


### Pad Connections

Low Pass Port	6
High Pass Port	4
Common Port	2
Ground	1,3,5

### Outline Drawing



#### PCB Land Pattern




Suggested Layout,  
Tolerance to be within ±0.02

### Outline Dimensions ( inch mm )

A	B	C	D	E	F
.063	.031	.024	.012	.008	.006
1.60	0.79	0.61	0.30	0.20	0.15
G	H	J	K	wt	
.020	.010	.022	.053	grams	
0.51	0.25	0.56	1.35	0.005	

### Demo Board MCL P/N: TB-796+ Suggested PCB Layout (PL-428)



#### NOTES:

- COPLANAR WAVEGUIDE IS SHOWN FOR ROGERS RO4350B WITH DIELECTRIC THICKNESS .010" ± .001". COPPER: 1/2 OZ. EACH SIDE. FOR OTHER MATERIALS TRACE WIDTH AND GAP MAY NEED TO BE MODIFIED.
  - BOTTOM SIDE OF THE PCB IS CONTINUOUS GROUND PLANE.
- DENOTES PCB COPPER LAYOUT WITH SMOBC (SOLDER MASK OVER BARE COPPER).  
■ DENOTES COPPER LAND PATTERN FREE OF SOLDER MASK.

#### Notes

- Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
- The parts covered by this specification document are subject to Mini-Circuit's standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuit's website at [www.minicircuits.com/MCLStore/terms.jsp](http://www.minicircuits.com/MCLStore/terms.jsp)

### Features

- small size 0603 (1.6 x 0.8 mm)
- low insertion loss, 0.6 dB typ.
- high rejection
- temperature stable
- LTCC construction

### Applications

- communication systems
- cellular
- GPS
- WCDMA

#### +RoHS Compliant

The +Suffix identifies RoHS Compliance. See our web site for RoHS Compliance methodologies and qualifications



Available Tape and Reel  
at no extra cost

Reel Size	Devices/Reel
7"	20, 50, 100, 200, 500, 1000, 4000

### Electrical Specifications<sup>1,2</sup> at 25°C


Parameter	Port	Frequency (MHz)	Min.	Typ.	Max.	Unit	
Pass Band	Insertion Loss	Low Pass	DC - 1650	—	0.6	0.9	dB
		High Pass	2400 - 2500 4900 - 6000	—	0.6 0.3	1.3 0.8	
	Return Loss	Low Pass	DC - 1650	10	20	—	dB
		High Pass	2400 - 2500 4900 - 6000	10 10	23 16	— —	
Stop Band Isolation	High Pass	DC - 200	—	25	—	dB	
		200 - 1400	—	15	—		
Stop Band Isolation	Low Pass	1400 - 1650	—	20	—	dB	
		2500 - 6000	—	20	—		






- In Application where DC voltage is present at either input or output port, coupling capacitors are required.
- Measured on Mini-Circuits Characterization Test Board TB-796+

### Typical Performance Data at 25°C

Frequency (MHz)	Insertion Loss (dB)		Return Loss (dB)		
	Low Pass Port	High Pass Port	Common Port	Low Pass Port	High Pass Port
10	0.13	47.51	42.31	37.69	0.04
200	0.14	21.72	34.81	36.27	0.09
500	0.30	14.79	27.23	29.10	0.38
1000	0.48	12.64	23.25	26.89	0.84
1400	0.43	18.92	22.09	23.60	0.84
1650	0.63	18.42	22.33	24.79	1.38
2400	16.56	0.63	25.67	1.37	23.73
2500	22.87	0.49	23.79	1.06	24.19
3000	18.21	0.40	18.95	0.73	18.81
3500	16.56	0.41	17.03	0.60	16.78
4900	22.69	0.30	17.07	0.23	18.05
5500	28.56	0.26	18.00	0.20	19.46
6000	41.60	0.28	16.94	0.24	17.80
7000	25.23	0.39	13.98	0.39	13.64
8000	18.18	0.49	13.75	0.52	12.56
9000	14.80	0.61	14.12	0.55	12.14
10000	13.22	0.76	13.03	0.58	11.24

### Functional Schematic





**Notes**







- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
- C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at [www.minicircuits.com/MCLStore/terms.jsp](http://www.minicircuits.com/MCLStore/terms.jsp)



## Typical Performance Data

FREQUENCY (MHz)	INSERTION LOSS (dB)		CROSS OVER ISOLATION (dB) (between LPF and HPF)	RETURN LOSS (dB)		
	Low Pass port	High Pass port		Common port	Low Pass port	High Pass port
10.0	0.13	47.51	49.30	42.31	37.69	0.04
50.0	0.07	33.61	46.74	44.64	37.42	0.03
100.0	0.10	27.61	43.46	41.87	41.54	0.04
200.0	0.14	21.72	37.64	34.81	36.27	0.09
300.0	0.19	18.47	32.65	31.01	32.45	0.17
400.0	0.24	16.29	31.40	28.73	30.76	0.26
500.0	0.30	14.79	29.25	27.23	29.10	0.38
600.0	0.35	13.75	28.02	25.77	27.90	0.50
700.0	0.41	13.06	26.35	24.88	27.34	0.62
800.0	0.45	12.65	26.02	24.28	26.75	0.72
900.0	0.47	12.50	24.39	23.57	26.69	0.79
1000.0	0.48	12.64	24.06	23.25	26.89	0.84
1100.0	0.48	13.11	23.76	22.79	26.81	0.86
1200.0	0.47	14.05	23.18	22.58	26.32	0.85
1300.0	0.45	15.74	23.09	22.24	25.15	0.85
1400.0	0.43	18.92	22.58	22.09	23.60	0.84
1500.0	0.44	26.07	21.94	22.14	22.73	0.90
1650.0	0.63	18.42	22.69	22.33	24.79	1.38
1700.0	0.78	14.78	22.93	22.63	28.80	1.71
1800.0	1.28	9.71	23.73	23.46	26.60	2.86
1900.0	2.19	6.32	26.58	25.40	14.51	4.84
2000.0	3.66	3.95	31.12	28.91	8.57	7.92
2400.0	16.56	0.63	29.09	25.67	1.37	23.73
2500.0	22.87	0.49	27.57	23.79	1.06	24.19
2800.0	21.74	0.39	24.31	20.44	0.77	20.81
3000.0	18.21	0.40	22.34	18.95	0.73	18.81
3200.0	16.92	0.41	22.38	17.96	0.68	17.72
3400.0	16.56	0.41	20.01	17.20	0.62	16.85
3800.0	17.11	0.40	17.92	16.44	0.50	16.41
4000.0	17.75	0.38	18.02	16.23	0.43	16.32
4200.0	18.60	0.37	17.38	16.09	0.38	16.22
4400.0	19.59	0.35	17.84	16.19	0.33	16.59
4800.0	22.02	0.30	17.10	17.02	0.24	17.81
5000.0	23.50	0.28	17.74	17.57	0.23	18.79
5200.0	25.24	0.27	19.52	17.97	0.21	19.56
5400.0	27.34	0.27	19.45	18.11	0.21	19.62
5800.0	33.99	0.27	19.14	17.50	0.22	18.67
6000.0	41.60	0.28	16.95	16.94	0.24	17.80
6200.0	48.72	0.29	16.67	16.42	0.26	16.88
6400.0	36.01	0.31	15.59	15.77	0.28	16.06
6800.0	27.69	0.37	16.36	14.49	0.35	14.25
7000.0	25.23	0.39	14.92	13.98	0.39	13.64
7200.0	23.30	0.41	13.79	13.86	0.42	13.36
7400.0	21.69	0.43	12.96	13.78	0.46	13.10
7800.0	19.19	0.47	14.34	13.73	0.49	12.81
8000.0	18.18	0.49	12.47	13.75	0.52	12.56
8200.0	17.29	0.52	12.30	13.84	0.55	12.44
8400.0	16.52	0.54	12.02	13.93	0.54	12.38
8800.0	15.29	0.58	13.22	14.29	0.56	12.27
9000.0	14.80	0.61	11.69	14.12	0.55	12.14
9200.0	14.36	0.64	12.03	14.04	0.55	11.95
9400.0	14.01	0.67	10.03	13.92	0.56	11.83
9800.0	13.45	0.72	8.97	13.46	0.55	11.52
10000.0	13.22	0.76	9.04	13.03	0.58	11.24

## Typical Performance Curves





# Case Style

# JC

## Outline Dimensions

## JC0603C



Weight: .005 grams

Dimensions are in mm [inch]. Tolerances:  $\pm 0.13$  mm

### Notes:

1. Open style, ceramic base.
2. Termination finish:

For RoHS Case Styles: Tin plate over Nickel plate. All models, (+) suffix.

**Mini-Circuits®**  
ISO 9001 ISO 14001 CERTIFIED

ALL NEW  
minicircuits.com

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site



The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: [www.minicircuits.com](http://www.minicircuits.com)

RF/IF MICROWAVE COMPONENTS

# Tape & Reel Packaging TR-F114

## DEVICE ORIENTATION IN T&R



ILLUSTRATION 1

Applicable Case Styles	
GE0805C	JC0603C
GE0805C-1	JC0603C-4
GE0805C-1AP	JC0603C-6
GE0805C-7	
GE0805C-9	
GE0805C-10	
GE0805C-11	
GE0805C-12	




ILLUSTRATION 2

Applicable Case Styles	
GE0805C-2	JC0603C-1
GE0805C-3	JC0603C-2
GE0805C-4	JC0603C-3
GE0805C-5	JC0603C-5
GE0805C-6	JC0603C-7
GE0805C-8	
GE0805C-15	

Tape Width, mm	Device Cavity Pitch, mm	Reel Size, inches	Devices per Reel	
8	4	7	Small quantity standards (see note)	20
				50
				100
				200
				500
			Standard	1000
			Standard	4000

Note: Please Consult individual model data sheet to determine device per reel availability.

Mini-Circuits carrier tape materials provide protection from ESD (Electro-Static Discharge) during handling and transportation. Tapes are static dissipative and comply with industry standards EIA-481/EIA-541.

Go to: [www.minicircuits.com/pages/pdfs/tape.pdf](http://www.minicircuits.com/pages/pdfs/tape.pdf)




INTERNET <http://www.minicircuits.com>

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661

Distribution Centers NORTH AMERICA 800-654-7949 • 417-335-5935 • Fax 417-335-5945 • EUROPE 44-1252-832600 • Fax 44-1252-837010

Mini-Circuits ISO 9001 & ISO 14001 Certified

THIRD ANGLE PROJECTION




REVISIONS

REV	ECN No.	DESCRIPTION	DATE	DR	AUTH
OR	M148455	NEW RELEASE	10/02/14	GF	MY
A	M149968	CHANGED LOCATION OF PIN 1	02/12/15	ITG	WP

SUGGESTED MOUNTING CONFIGURATION  
FOR JC0603C CASE STYLE, "06DP02" PIN CODE

∅.013 PTH  
FOR GROUND




PIN 1

COPLANAR WAVEGUIDE:  
.022 TRACE WIDTH &  
.014 GAP, 3 PL.  
(SEE NOTE BELOW)

PACKAGE  
OUTLINE

NOTES:

1. COPLANAR WAVEGUIDE IS SHOWN FOR ROGERS R04350B WITH DIELECTRIC THICKNESS .010" ± .001". COPPER: 1/2 OZ. EACH SIDE. FOR OTHER MATERIALS TRACE WIDTH AND GAP MAY NEED TO BE MODIFIED.
2. BOTTOM SIDE OF THE PCB IS CONTINUOUS GROUND PLANE.



DENOTES PCB COPPER LAYOUT WITH SMOBC (SOLDER MASK OVER BARE COPPER).



DENOTES COPPER LAND PATTERN FREE OF SOLDER MASK.

UNLESS OTHERWISE SPECIFIED	INITIALS		DATE
DIMENSIONS ARE IN INCHES TOLERANCES ON: 2 PL DECIMALS ± 3 PL DECIMALS ± .005 ANGLES ± FRACTIONS ±	DRAWN	GF	10/01/14
	CHECKED	IL	10/02/14
	APPROVED	MY	10/02/14




**Mini-Circuits®** 13 Neptune Avenue  
Brooklyn NY 11235

PL, 06DP02, JC0603C, TB-796+


Mini-Circuits®  
THIS DOCUMENT AND ITS CONTENTS ARE THE PROPERTY OF MINI-CIRCUITS. EXCEPT FOR USE EXPRESSLY GRANTED, IN WRITING, TO ITS VENDORS, VENDEE AND THE UNITED STATES GOVERNMENT, MINI-CIRCUITS RESERVES ALL PROPRIETARY DESIGN, USE, MANUFACTURING AND REPRODUCTION RIGHTS THERETO. THESE CONTENTS SHALL NOT BE USED, DUPLICATED OR DISCLOSED TO ANY OUTSIDE PARTY, IN WHOLE OR IN PART, WITHOUT WRITTEN PERMISSION OF MINI-CIRCUITS.

SIZE A	CODE IDENT 15542	DRAWING NO: 98-PL-428	REV: A
FILE: 98PL428	SCALE: 15:1	SHEET: 1 OF 1	

# Evaluation Board and Circuit




TB-796+



Schematic Diagram

**Notes:**

1. 50 Ohm SMA Female connectors.
2. PCB Material: R04350 or equivalent,  
Dielectric Constant=3.5, Thickness=.010 inch.

 **Mini-Circuits®**

All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

Specification	Test/Inspection Condition	Reference/Spec
Operating Temperature	-55° to 100°C Ambient Environment	Individual Model Data Sheet
Storage Temperature	-55° to 100° C Ambient Environment	Individual Model Data Sheet
Humidity	90 to 95% RH, 240 hours, 50°C	MIL-STD-202, Method 103, Condition A, Except 50°C and end-point electrical test done within 12 hours
Solder Reflow Heat	Sn-Pb Eutetic Process: 225°C peak Pb-Free Process 245° - 250°C peak	J-STD-020, Table 4-1, 4-2 and 5-2, Figure 5-1
Solderability	10X Magnification	J-STD-002, Para 4.2.5, Test S, 95% Coverage
Vibration (High Frequency)	20g peak, 10-2000 Hz, 12 times in each of three perpendicular directions (total 36)	MIL-STD-202, Method 204, Condition D
Mechanical Shock	50g, 11 ms, 1/2-sine, 18 shocks: 3 each direction, each of 3 axes	MIL-STD-202, Method 213, Condition A