

Ceramic

Low Pass Filter

LFCG-1000+

50Ω DC to 1000 MHz



Generic photo used for illustration purposes only
CASE STYLE: GE0805C-2

The Big Deal

- Very good rejection, 45 dB typical
- Rugged, ceramic construction
- Tiny size, 0.079" x 0.049" x 0.037" (0805)
- Excellent power handling, 5.5W

Product Overview

Mini-Circuits' LFCG-1000+ is an LTCC low pass filter with a passband from DC to 1000 MHz, supporting a variety of applications. This model provides 0.8 dB typical passband insertion loss and provides a very good stopband rejection due to strategically constructed layout with minimal interaction between components. It handles up to 5.5W RF input power and provides a wide operating temperature range from -55°C to 125°C. Housed in a tiny 0805 ceramic form factor with wraparound terminations, the filter is ideal for dense PCB layouts and with minimal performance variation due to parasitics.

Key Features

| Feature | Advantages |
|---|---|
| Very good stopband rejection, 45 dB typical | The LTCC lowpass filter provides a very good stopband rejection until 10 GHz suitable for high end applications. |
| LTCC Construction | Provides repeatable performance in a rugged, ceramic package well suited for tough environments such as high humidity and temperature extremes. |
| Tiny size (0.079" x 0.049" x 0.037") | Saves space in dense circuit board layouts and minimizes the effects of parasitics. |
| Excellent power handling, 5.5W | Supports a wide range of system power requirements. |
| Wrap-around terminations | Provides excellent solderability and easy visual inspection |

Notes

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp



Ceramic

Low Pass Filter

50Ω

DC to 1000 MHz

LFCG-1000+




Features

- Low loss, 0.8 dB typical
- High rejection 45 dB typical
- Excellent power handling, 5.5W
- Extremely small size 0805 (2.0mm x 1.25mm)
- Temperature stable
- LTCC construction

Applications

- Harmonic Rejection
- VHF/UHF transmitters / receivers
- Lab use

Functional Schematic



| Electrical Specifications ^{1,2} at 25°C | | | | | | |
|--|----------------|-------|-----------------|------|------|------|
| | Parameter | F# | Frequency (MHz) | Min. | Typ. | Max. |
| Pass Band | Insertion Loss | DC-F1 | DC-1000 | — | 0.8 | 1.8 |
| | Freq. Cut-Off | F2 | 1370 | — | 3.0 | — |
| | Return Loss | DC-F1 | DC-1000 | — | 21 | — |
| Stop Band | Rejection Loss | F3-F4 | 1550-1900 | 20 | 30 | — |
| | | F4-F5 | 1900-3000 | 35 | 45 | — |
| | | F5-F6 | 3000-6000 | 30 | 35 | — |
| | | F6-F7 | 6000-10000 | — | 30 | — |

1. DC de-coupling capacitors are required in Applications where DC voltage and/or current is present at either input or output ports.


Please contact Mini-Circuits for alternatives if DC pass from IN-OUT is required.

2. Measured on Mini-Circuits Characterization Test Board TB-799+

| Maximum Ratings | |
|-----------------------|------------------|
| Operating Temperature | -55°C to 125°C |
| Storage Temperature | -55°C to 125°C |
| RF Power Input* | 5.5W max. @ 25°C |




*Passband rating, derate linearly to 1W at 125°C ambient
Permanent damage may occur if any of these limits are exceeded.

Typical Frequency Response



Typical Performance Data at 25°C

| Frequency (MHz) | Insertion Loss (dB) | Return Loss (dB) |
|-----------------|---------------------|------------------|
| 10 | 0.12 | 39.37 |
| 100 | 0.18 | 30.94 |
| 1000 | 0.74 | 23.43 |
| 1370 | 3.39 | 11.65 |
| 1450 | 9.47 | 7.28 |
| 1510 | 20.39 | 4.42 |
| 1550 | 31.51 | 3.12 |
| 1750 | 42.02 | 1.00 |
| 1900 | 59.59 | 0.65 |
| 2000 | 52.69 | 0.53 |
| 2500 | 49.74 | 0.32 |
| 3000 | 44.29 | 0.24 |
| 4000 | 38.87 | 0.14 |
| 5000 | 37.65 | 0.09 |
| 6000 | 37.95 | 0.11 |
| 7000 | 37.04 | 0.24 |
| 7500 | 49.61 | 0.27 |
| 8000 | 48.29 | 0.29 |
| 9000 | 45.40 | 0.32 |
| 10000 | 40.34 | 0.32 |



Notes



- Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
- The parts covered by this specification document are subject to Mini-Circuit's standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp

Pad Connections

| | |
|--------|-------------|
| INPUT | 8 |
| OUTPUT | 4 |
| GROUND | 1,2,3,5,6,7 |

Product Marking: KC

**Demo Board MCL P/N: TB-799+
Suggested PCB Layout (PL-429)**

**Outline Drawing****Outline Dimensions (inch)**

| A | B | C | D | E | F | G | Wt. |
|------|------|------|------|------|------|------|-------|
| .079 | .049 | .037 | .014 | .012 | .012 | .026 | grams |
| 2.00 | 1.25 | 0.95 | 0.35 | 0.30 | 0.30 | 0.65 | .008 |

Note: Please refer to case style drawing for details

Notes

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuits' applicable established test performance criteria and measurement instructions.
- C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp

Ceramic Low Pass Filter

LFCG-1000+

Typical Performance Data

| FREQ. (MHz) | INSERTION LOSS | | | INPUT RETURN LOSS | | | OUTPUT RETURN LOSS | | |
|----------------|----------------|--------|---------|-------------------|--------|---------|--------------------|--------|---------|
| | (dB) | | | (dB) | | | (dB) | | |
| | @-55°C | @+25°C | @+125°C | @-55°C | @+25°C | @+125°C | @-55°C | @+25°C | @+125°C |
| 10 | 0.12 | 0.13 | 0.15 | 36.05 | 36.82 | 34.90 | 36.35 | 37.57 | 35.54 |
| 60 | 0.14 | 0.17 | 0.19 | 35.95 | 34.06 | 33.72 | 34.48 | 33.02 | 32.47 |
| 100 | 0.16 | 0.19 | 0.22 | 32.80 | 31.78 | 31.40 | 31.78 | 30.89 | 30.34 |
| 140 | 0.17 | 0.21 | 0.25 | 30.64 | 30.22 | 30.15 | 29.55 | 29.13 | 28.84 |
| 180 | 0.19 | 0.23 | 0.27 | 28.83 | 28.98 | 29.26 | 27.79 | 27.81 | 27.77 |
| 200 | 0.19 | 0.24 | 0.28 | 28.20 | 28.52 | 29.00 | 27.11 | 27.26 | 27.32 |
| 240 | 0.21 | 0.26 | 0.30 | 27.25 | 27.87 | 28.61 | 25.98 | 26.36 | 26.51 |
| 300 | 0.23 | 0.28 | 0.33 | 26.04 | 26.83 | 27.78 | 24.75 | 25.17 | 25.40 |
| 400 | 0.25 | 0.32 | 0.38 | 24.98 | 25.82 | 26.90 | 23.34 | 23.70 | 23.98 |
| 500 | 0.28 | 0.36 | 0.43 | 24.36 | 25.40 | 26.45 | 22.66 | 23.12 | 23.41 |
| 800 | 0.40 | 0.52 | 0.63 | 30.73 | 32.17 | 33.39 | 28.36 | 29.05 | 29.81 |
| 1000 | 0.58 | 0.74 | 0.92 | 25.88 | 25.55 | 25.20 | 24.03 | 23.75 | 23.20 |
| 1100 | 0.73 | 0.93 | 1.15 | 22.57 | 22.78 | 23.06 | 20.66 | 20.70 | 20.66 |
| 1150 | 0.83 | 1.05 | 1.30 | 22.66 | 23.42 | 24.33 | 20.53 | 20.82 | 21.15 |
| 1200 | 0.94 | 1.19 | 1.50 | 25.27 | 27.47 | 30.87 | 21.92 | 22.65 | 23.49 |
| 1250 | 1.10 | 1.42 | 1.82 | 36.47 | 37.10 | 28.91 | 24.71 | 25.10 | 24.55 |
| 1300 | 1.40 | 1.82 | 2.41 | 21.95 | 19.27 | 16.74 | 20.97 | 19.53 | 17.95 |
| 1325 | 1.64 | 2.17 | 2.91 | 17.09 | 15.11 | 13.13 | 17.35 | 16.15 | 14.99 |
| 1350 | 2.00 | 2.67 | 3.65 | 13.39 | 11.79 | 10.14 | 14.26 | 13.41 | 12.67 |
| 1370 | 2.42 | 3.26 | 4.50 | 10.95 | 9.56 | 8.11 | 12.27 | 11.66 | 11.25 |
| 1400 | 3.38 | 4.60 | 6.45 | 7.89 | 6.73 | 5.59 | 9.90 | 9.66 | 9.65 |
| 1450 | 6.61 | 9.05 | 12.39 | 4.01 | 3.36 | 2.89 | 7.28 | 7.24 | 7.24 |
| 1500 | 13.50 | 17.50 | 22.43 | 1.88 | 1.78 | 1.76 | 4.97 | 4.84 | 4.79 |
| 1510 | 15.40 | 19.71 | 24.98 | 1.66 | 1.62 | 1.65 | 4.53 | 4.43 | 4.40 |
| 1550 | 24.92 | 30.72 | 35.66 | 1.14 | 1.24 | 1.34 | 3.10 | 3.12 | 3.19 |
| 1600 | 39.37 | 37.18 | 35.59 | 0.88 | 1.02 | 1.13 | 2.03 | 2.14 | 2.27 |
| 1700 | 36.87 | 37.76 | 39.05 | 0.62 | 0.77 | 0.88 | 1.07 | 1.22 | 1.37 |
| 1800 | 44.32 | 46.36 | 48.92 | 0.49 | 0.64 | 0.75 | 0.69 | 0.82 | 0.97 |
| 1850 | 50.55 | 53.46 | 56.52 | 0.44 | 0.58 | 0.70 | 0.58 | 0.70 | 0.84 |
| 1900 | 59.63 | 60.77 | 58.80 | 0.39 | 0.53 | 0.64 | 0.50 | 0.62 | 0.75 |
| 1950 | 58.37 | 56.43 | 55.06 | 0.37 | 0.51 | 0.62 | 0.43 | 0.55 | 0.67 |
| 2000 | 54.02 | 53.47 | 53.02 | 0.33 | 0.47 | 0.58 | 0.39 | 0.50 | 0.61 |
| 2100 | 51.17 | 51.47 | 51.77 | 0.27 | 0.41 | 0.52 | 0.32 | 0.42 | 0.52 |
| 2250 | 50.53 | 51.10 | 51.64 | 0.22 | 0.36 | 0.47 | 0.27 | 0.35 | 0.44 |
| 2500 | 49.50 | 49.90 | 50.11 | 0.15 | 0.29 | 0.38 | 0.21 | 0.28 | 0.36 |
| 2750 | 46.98 | 47.10 | 47.11 | 0.11 | 0.24 | 0.32 | 0.18 | 0.24 | 0.31 |
| 3000 | 44.37 | 44.38 | 44.28 | 0.07 | 0.19 | 0.27 | 0.16 | 0.22 | 0.29 |
| 3250 | 42.26 | 42.24 | 42.16 | 0.05 | 0.16 | 0.23 | 0.14 | 0.20 | 0.26 |
| 3500 | 40.71 | 40.69 | 40.61 | 0.03 | 0.14 | 0.20 | 0.11 | 0.18 | 0.25 |
| 3750 | 39.60 | 39.60 | 39.53 | 0.02 | 0.13 | 0.17 | 0.10 | 0.17 | 0.25 |
| 4000 | 38.81 | 38.84 | 38.80 | 0.01 | 0.12 | 0.16 | 0.08 | 0.16 | 0.25 |
| 4250 | 38.27 | 38.32 | 38.27 | 0.01 | 0.12 | 0.16 | 0.07 | 0.16 | 0.27 |
| 4500 | 37.89 | 37.96 | 37.96 | 0.01 | 0.12 | 0.16 | 0.06 | 0.15 | 0.28 |
| 4750 | 37.68 | 37.76 | 37.76 | 0.02 | 0.13 | 0.17 | 0.05 | 0.15 | 0.30 |
| 5000 | 37.50 | 37.64 | 37.69 | 0.01 | 0.13 | 0.18 | 0.04 | 0.15 | 0.32 |
| 5250 | 37.60 | 37.83 | 37.83 | 0.03 | 0.15 | 0.21 | 0.03 | 0.16 | 0.34 |
| 5500 | 37.53 | 37.65 | 37.84 | 0.02 | 0.15 | 0.22 | 0.01 | 0.15 | 0.35 |
| 5750 | 37.50 | 37.57 | 37.88 | 0.04 | 0.18 | 0.25 | 0.01 | 0.16 | 0.37 |
| 6000 | 37.94 | 37.89 | 38.19 | 0.03 | 0.18 | 0.27 | 0.00 | 0.16 | 0.39 |
| 6250 | 38.01 | 38.18 | 38.41 | 0.03 | 0.19 | 0.30 | 0.01 | 0.16 | 0.39 |
| 6500 | 38.16 | 38.44 | 38.50 | 0.03 | 0.21 | 0.34 | 0.01 | 0.17 | 0.41 |
| 6750 | 38.65 | 38.59 | 38.22 | 0.03 | 0.22 | 0.37 | 0.00 | 0.19 | 0.44 |
| 7000 | 37.40 | 37.24 | 36.66 | 0.05 | 0.25 | 0.42 | 0.01 | 0.21 | 0.52 |
| 7250 | 33.29 | 34.77 | 42.95 | 0.06 | 0.28 | 0.44 | 0.38 | 0.85 | 0.66 |
| 7500 | 49.74 | 47.81 | 48.53 | 0.04 | 0.27 | 0.47 | 0.06 | 0.23 | 0.44 |
| 8000 | 44.01 | 46.90 | 51.26 | 0.10 | 0.32 | 0.55 | 0.02 | 0.19 | 0.39 |
| 8500 | 53.75 | 52.89 | 51.95 | 0.07 | 0.31 | 0.57 | 0.03 | 0.14 | 0.32 |
| 9000 | 44.91 | 43.88 | 45.26 | 0.10 | 0.38 | 0.61 | 0.04 | 0.13 | 0.28 |
| 9500 | 40.29 | 40.96 | 42.78 | 0.18 | 0.46 | 0.66 | 0.05 | 0.12 | 0.23 |
| 10000 | 39.50 | 39.68 | 40.24 | 0.28 | 0.56 | 0.79 | 0.04 | 0.14 | 0.24 |



ISO 9001 ISO 14001 AS 9100 CERTIFIED

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 • Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site
 The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: www.minicircuits.com

IF/RF MICROWAVE COMPONENTS








REV. A
LFCG-1000+
210426
Page 1 of 2

Typical Performance Data

| FREQ. (MHz) | GROUP DELAY | | |
|----------------|-------------|--------|---------|
| | (nsec) | | |
| | @-55°C | @+25°C | @+125°C |
| 10 | 0.33 | 0.38 | 0.36 |
| 20 | 0.36 | 0.40 | 0.39 |
| 40 | 0.38 | 0.40 | 0.40 |
| 60 | 0.39 | 0.41 | 0.41 |
| 80 | 0.40 | 0.41 | 0.41 |
| 100 | 0.40 | 0.40 | 0.41 |
| 120 | 0.40 | 0.40 | 0.41 |
| 140 | 0.40 | 0.40 | 0.41 |
| 160 | 0.40 | 0.40 | 0.41 |
| 180 | 0.40 | 0.40 | 0.41 |
| 200 | 0.40 | 0.40 | 0.41 |
| 220 | 0.40 | 0.40 | 0.41 |
| 240 | 0.40 | 0.41 | 0.41 |
| 260 | 0.40 | 0.41 | 0.42 |
| 280 | 0.40 | 0.41 | 0.42 |
| 300 | 0.41 | 0.41 | 0.42 |
| 320 | 0.41 | 0.41 | 0.42 |
| 340 | 0.41 | 0.42 | 0.42 |
| 360 | 0.41 | 0.42 | 0.43 |
| 380 | 0.42 | 0.42 | 0.43 |
| 400 | 0.42 | 0.42 | 0.43 |
| 420 | 0.42 | 0.43 | 0.44 |
| 440 | 0.43 | 0.43 | 0.44 |
| 460 | 0.43 | 0.43 | 0.44 |
| 480 | 0.43 | 0.44 | 0.45 |
| 500 | 0.44 | 0.44 | 0.45 |
| 520 | 0.44 | 0.45 | 0.46 |
| 540 | 0.45 | 0.45 | 0.46 |
| 560 | 0.45 | 0.46 | 0.47 |
| 580 | 0.46 | 0.46 | 0.47 |
| 600 | 0.46 | 0.47 | 0.48 |
| 620 | 0.47 | 0.48 | 0.49 |
| 640 | 0.48 | 0.48 | 0.49 |
| 660 | 0.48 | 0.49 | 0.50 |
| 680 | 0.49 | 0.50 | 0.51 |
| 700 | 0.50 | 0.51 | 0.52 |
| 800 | 0.54 | 0.55 | 0.57 |
| 820 | 0.56 | 0.57 | 0.58 |
| 840 | 0.57 | 0.58 | 0.59 |
| 900 | 0.60 | 0.61 | 0.63 |
| 1000 | 0.69 | 0.71 | 0.73 |

Typical Performance Curves




Case Style


GE

GE0805C-2

Outline Dimensions



PCB Land Pattern



Suggested Layout,
Tolerance to be within ±.002

| CASE # | A | B | C | D | E | F | G | H | J | K | L |
|-----------|----------------|----------------|----------------|----------------|----------------|----------------|----------------|----------------|----------------|----------------|----------------|
| GE0805C-2 | .079 (2.00) | .049 (1.25) | .037 (0.95) | .014 (0.35) | .012 (0.30) | .012 (0.30) | .026 (0.65) | .025 (0.63) | .134 (3.40) | .110 (2.80) | .014 (0.35) |

| CASE # | M | WT. GRAM |
|-----------|----------------|----------|
| GE0805C-2 | .039 (1.00) | .008 |

Dimensions are in inches (mm). Tolerances: 2Pl. ± .01; 3 Pl. ± .005

Notes:

1. Open style, ceramic base.
2. Termination finish: For RoHS Case Styles: Tin plate over Nickel plate. All models, (+) suffix.
For RoHS-5 Case Styles: Tin-Lead plate over Nickel plate. All models, no (+) suffix.
3. Pad tolerance to be non-cumulative. Minimum spacing between each pad is .004 (0.1).

 **Mini-Circuits®**
ISO 9001 ISO 14001 CERTIFIED

ALL NEW
minicircuits.com

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site




The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: www.minicircuits.com

RF/IF MICROWAVE COMPONENTS


Tape & Reel Packaging TR-F114

DEVICE ORIENTATION IN T&R



Applicable Case Styles

| | |
|-------------|-----------|
| GE0805C | JC0603C |
| GE0805C-1 | JC0603C-4 |
| GE0805C-1AP | JC0603C-6 |
| GE0805C-7 | |
| GE0805C-9 | |
| GE0805C-10 | |
| GE0805C-11 | |
| GE0805C-12 | |



Applicable Case Styles

| | |
|------------|-----------|
| GE0805C-2 | JC0603C-1 |
| GE0805C-3 | JC0603C-2 |
| GE0805C-4 | JC0603C-3 |
| GE0805C-5 | JC0603C-5 |
| GE0805C-6 | JC0603C-7 |
| GE0805C-8 | JV1210C-1 |
| GE0805C-15 | |

| Tape Width, mm | Device Cavity Pitch, mm | Reel Size, inches | Devices per Reel | | | | | | | | |
|-------------------|----------------------------|----------------------|---|----|----|-----|-----|-----|------|----------|------|
| 8 | 4 | 7 | Small quantity standards (see note) <table border="1" style="margin-left: 20px;"> <tr><td>20</td></tr> <tr><td>50</td></tr> <tr><td>100</td></tr> <tr><td>200</td></tr> <tr><td>500</td></tr> <tr><td>1000</td></tr> <tr><td>Standard</td><td>4000</td></tr> </table> | 20 | 50 | 100 | 200 | 500 | 1000 | Standard | 4000 |
| 20 | | | | | | | | | | | |
| 50 | | | | | | | | | | | |
| 100 | | | | | | | | | | | |
| 200 | | | | | | | | | | | |
| 500 | | | | | | | | | | | |
| 1000 | | | | | | | | | | | |
| Standard | 4000 | | | | | | | | | | |

Note: Please Consult individual model data sheet to determine device per reel availability.

Mini-Circuits carrier tape materials provide protection from ESD (Electro-Static Discharge) during handling and transportation. Tapes are static dissipative and comply with industry standards EIA-481/EIA-541.

Go to: www.minicircuits.com/pages/pdfs/tape.pdf




Distribution Centers NORTH AMERICA 800-654-7949 • 417-335-5935 • Fax 417-335-5945 • EUROPE 44-1252-832600 • Fax 44-1252-837010

INTERNET <http://www.minicircuits.com>


P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661

Mini-Circuits ISO 9001 & ISO 14001 Certified



| REVISIONS | | | | | |
|-----------|---------|-------------|----------|----|------|
| REV OR | ECN No. | DESCRIPTION | DATE | DR | AUTH |
| | M148457 | NEW RELEASE | 10/14/14 | GF | MY |
| | | | | | |
| | | | | | |
| | | | | | |

SUGGESTED MOUNTING CONFIGURATION
FOR GE0805C-4 CASE STYLE, "08FL07" PIN CODE



NOTES:


1. COPLANAR WAVEGUIDE IS SHOWN FOR ROGERS R04350B WITH DIELECTRIC THICKNESS $.010" \pm .001"$. COPPER: 1/2 OZ. EACH SIDE. FOR OTHER MATERIALS TRACE WIDTH AND GAP MAY NEED TO BE MODIFIED.
2. BOTTOM SIDE OF THE PCB IS CONTINUOUS GROUND PLANE.

[Solid Blue Box] DENOTES PCB COPPER LAYOUT WITH SMOBC (SOLDER MASK OVER BARE COPPER).


[Hatched Box] DENOTES COPPER LAND PATTERN FREE OF SOLDER MASK.

| | | | | |
|--|----------|----|----------|--|
| UNLESS OTHERWISE SPECIFIED | INITIALS | | DATE |  Mini-Circuits® 13 Neptune Avenue Brooklyn NY 11235 |
| DIMENSIONS ARE IN INCHES | DRAWN | GF | 10/01/14 | |
| TOLERANCES ON: 2 PL DECIMALS \pm 3 PL DECIMALS $\pm .005$ | CHECKED | IL | 10/14/14 | |
| ANGLES \pm FRACTIONS \pm | APPROVED | MY | 10/14/14 | |
|  Mini-Circuits® THIS DOCUMENT AND ITS CONTENTS ARE THE PROPERTY OF MINI-CIRCUITS. EXCEPT FOR USE EXPRESSLY GRANTED, IN WRITING, TO ITS VENDORS, VENDEE AND THE UNITED STATES GOVERNMENT, MINI-CIRCUITS RESERVES ALL PROPRIETARY DESIGN, USE, MANUFACTURING AND REPRODUCTION RIGHTS THERETO. THESE CONTENTS SHALL NOT BE USED, DUPLICATED OR DISCLOSED TO ANY OUTSIDE PARTY, IN WHOLE OR IN PART, WITHOUT WRITTEN PERMISSION OF MINI-CIRCUITS. | | | | |
| FILE: 98PL429 DRAWING NO: 98-PL-429 REV: OR SCALE: 15:1 SHEET: 1 OF 1 | | | | |
| ASHEETA1.DWG REV:A DATE:01/12/95 | | | | |

Evaluation Board and Circuit



TB-799+



Schematic Diagram

Notes:

1. 50 Ohm SMA Female connectors.
2. PCB Material: RO4350 or equivalent,
Dielectric Constant=3.5, Thickness=.010 inch.

Mini-Circuits®



Environmental Specifications

ENV06

All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

| Specification | Test/Inspection Condition | Reference/Spec |
|----------------------------|---|--|
| Operating Temperature | -55° to 100°C Ambient Environment | Individual Model Data Sheet |
| Storage Temperature | -55° to 100° C Ambient Environment | Individual Model Data Sheet |
| Humidity | 90 to 95% RH, 240 hours, 50°C | MIL-STD-202, Method 103, Condition A, Except 50°C and end-point electrical test done within 12 hours |
| Solder Reflow Heat | Sn-Pb Eutetic Process: 225°C peak Pb-Free Process 245° - 250°C peak | J-STD-020, Table 4-1, 4-2 and 5-2, Figure 5-1 |
| Solderability | 10X Magnification | J-STD-002, Para 4.2.5, Test S, 95% Coverage |
| Vibration (High Frequency) | 20g peak, 10-2000 Hz, 12 times in each of three perpendicular directions (total 36) | MIL-STD-202, Method 204, Condition D |
| Mechanical Shock | 50g, 11 ms, 1/2-sine, 18 shocks: 3 each direction, each of 3 axes | MIL-STD-202, Method 213, Condition A |