



LTCC SURFACE MOUNT

Low Pass Filter

LFCG-1325+

Mini-Circuits

50Ω DC to 1325 MHz

THE BIG DEAL


- Insertion Loss, Typ. 1.0 dB
- Stopband Rejection, Typ. 50 dB
- Passband Return Loss, Typ. 26 dB
- 0805 Surface Mount Footprint
- Power Handling: 5.5 Watts



Generic photo used for illustration purposes only

APPLICATIONS

- Military Radio Applications
- Police Mobile Radio

FUNCTIONAL DIAGRAM**PRODUCT OVERVIEW**

Mini-Circuits' LFCG-1325+ is a miniature low temperature co-fired ceramic (LTCC) low pass filter with a DC to 1325 MHz passband supporting a variety of applications. This model provides 1.0 dB typical insertion loss over a wide band due to its rugged monolithic construction. Housed in an 0805 ceramic form factor which is ideal for dense signal chain PCB layouts where it complements MMIC size and performance. The LTCC fabrication process assures minimal RF performance variation while delivering a product that is well suited for environmental extremes of high humidity and temperature.

KEY FEATURES

Features	Advantages
Ultra-wide Stopband	The LTCC lowpass filter provides a very good stopband rejection until 11.6 GHz suitable for wide band applications.
LTCC Construction	Provides repeatable performance in a rugged, ceramic package well suited for tough environments such as high humidity and temperature extremes.
Small Size, 0805	Saves space in dense circuit board layouts and minimizes the effects of parasitics.
Rugged Power Handling, 5.5 Watts	Handles up to 5.5 Watts in a small 0805 package.



LTCC SURFACE MOUNT

Low Pass Filter

LFCG-1325+

Mini-Circuits

50Ω DC to 1325 MHz

ELECTRICAL SPECIFICATIONS^{1,2,3} AT +25°C

Parameter	F#	Frequency (MHz)	Min.	Typ.	Max.	Units
Passband	Insertion Loss	DC-F1	DC - 1325	—	1.0	1.8
	Freq. Cut-Off ⁴	F _c	1550	—	3.0	—
	Return Loss	DC-F1	DC - 1325	—	26	—
Stopband	Rejection	F2-F3	1900 - 2150	20	45	—
		F3-F4	2150 - 6500	40	50	—
		F4-F5	6500 - 11600	—	35	—

1. Tested in Evaluation Board P/N TB-LFCG-1325+.

2. This filter is bi-directional, RF1 and RF2 ports may be interchanged. See S-Parameters for actual performance.

3. In applications where DC voltage and/or current is present at either the input or output ports, external DC blocking capacitors are required.

4. Typical variation ± 5%.


ABSOLUTE MAXIMUM RATINGS⁵

Parameter	Ratings
Operating Temperature	-55°C to +125°C
Storage Temperature	-55°C to +125°C
Input Power ⁶	5.5 W @ +25°C

5. Permanent damage may occur if any of these limits are exceeded.

6. Power rating applies only to signals within the passband. Power rating above +25°C operating temperature decreases linearly to 1 W at +125°C.

TYPICAL FREQUENCY RESPONSE AT +25°C










LTCC SURFACE MOUNT

Low Pass Filter

LFCG-1325+

50Ω DC to 1325 MHz

TYPICAL PERFORMANCE GRAPHS

**Mini-Circuits®**



LTCC SURFACE MOUNT

Low Pass Filter

LFCG-1325+

50Ω DC to 1325 MHz

FUNCTIONAL DIAGRAM





Figure 1. LFCG-1325+ Functional Diagram

CASE STYLE DRAWING



METALLIZATION


Weight: .008 grams

Dimensions are in inches (mm). Tolerances: 2Pl. $\pm .01$; 3 Pl. $\pm .005$

PAD DESCRIPTION

Function	Pad Number	Description
RF1 ²	8	Connects to RF Input Port
RF2 ²	4	Connects to RF Output Port
GROUND	1,2,3,5,6,7	Connects to Ground on PCB, (See drawing PL-429)

SUGGESTED PCB LAYOUT (PL-429)



NOTES:

1. COPLANAR WAVEGUIDE IS SHOWN FOR ROGERS RO4350B WITH DIELECTRIC THICKNESS .010" ± .001". COPPER: 1/2 OZ. EACH SIDE. FOR OTHER MATERIALS TRACE WIDTH AND GAP MAY NEED TO BE MODIFIED.
2. BOTTOM SIDE OF THE PCB IS CONTINUOUS GROUND PLANE.

DENOTES PCB COPPER LAYOUT WITH SMOBC (SOLDER MASK OVER BARE COPPER).

DENOTES COPPER LAND PATTERN FREE OF SOLDER MASK.

Figure 2. Suggested PCB Layout PL-429

PRODUCT MARKING*: MJ

*Marking may contain other features or characters for internal lot control.



LTCC SURFACE MOUNT

Low Pass Filter

LFCG-1325+

50Ω DC to 1325 MHz

ADDITIONAL DETAILED INFORMATION IS AVAILABLE ON OUR DASHBOARD.**CLICK HERE**

Performance Data and Graphs	Data Graphs S-Parameter (S2P Files) Data Set (.zip file) De-embedded to device pads
Case Style	GE0805C-2 Lead Finish: Tin over Nickel plating
RoHS Status	Compliant
Tape and Reel	F114
Suggested Layout for PCB Design	PL-429
Evaluation Board	TB-LFCG-1325+ Gerber File
Environmental Rating	ENV06

NOTES

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuits' applicable established test performance criteria and measurement instructions.
- C. The parts covered by this specification document are subject to Mini-Circuits' standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the standard terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/terms/viewterm.html

Mini-Circuits®www.minicircuits.com P.O. Box 350166, Brooklyn, NY 11235-0003 (718) 934-4500 sales@minicircuits.com

PAGE 5 OF 5

Ceramic Low Pass Filter

LFCG-1325+

Typical Performance Data

FREQ. (MHz)	INSERTION LOSS (dB)			INPUT RETURN LOSS (dB)			OUTPUT RETURN LOSS (dB)		
	@-55°C	@+25°C	@+125°C	@-55°C	@+25°C	@+125°C	@-55°C	@+25°C	@+125°C
	0.12	0.14	0.15	40.26	40.31	39.07	41.01	41.58	40.18
100	0.16	0.18	0.21	34.89	33.92	33.43	34.48	33.49	32.88
200	0.20	0.24	0.27	29.80	30.17	30.55	28.63	28.71	28.64
250	0.22	0.26	0.30	28.41	29.11	29.82	26.91	27.18	27.22
300	0.24	0.28	0.33	27.43	28.26	29.18	25.63	25.91	25.98
350	0.25	0.30	0.35	26.67	27.53	28.51	24.63	24.87	24.92
400	0.27	0.33	0.38	25.98	26.87	27.84	23.79	23.99	24.02
500	0.30	0.37	0.43	24.67	25.65	26.51	22.44	22.64	22.65
550	0.32	0.39	0.45	24.11	25.10	25.89	21.94	22.16	22.18
600	0.34	0.41	0.48	23.70	24.65	25.38	21.60	21.81	21.85
650	0.36	0.43	0.51	23.42	24.31	24.99	21.42	21.61	21.69
700	0.37	0.45	0.53	23.26	24.10	24.74	21.38	21.57	21.67
750	0.39	0.47	0.56	23.26	24.08	24.69	21.50	21.70	21.82
800	0.41	0.50	0.59	23.45	24.26	24.86	21.85	22.07	22.22
850	0.43	0.52	0.62	23.88	24.70	25.30	22.50	22.75	22.94
1000	0.50	0.61	0.74	27.48	28.48	29.59	27.34	27.87	28.50
1325	0.86	1.05	1.28	26.08	26.36	26.35	23.76	23.40	22.74
1400	1.03	1.26	1.56	25.17	25.70	25.69	22.14	21.80	20.98
1550	2.01	2.58	3.41	14.15	12.71	11.17	13.45	12.32	11.06
1700	9.45	11.85	14.82	2.98	2.69	2.53	4.37	4.30	4.43
1775	18.91	22.44	26.71	1.51	1.55	1.63	3.00	3.14	3.37
1820	27.14	31.72	36.99	1.17	1.27	1.38	2.46	2.61	2.82
1900	42.64	44.38	44.65	0.89	1.01	1.14	1.80	1.95	2.13
2000	45.96	46.53	47.72	0.69	0.82	0.94	1.22	1.36	1.52
2100	52.78	55.75	59.03	0.55	0.68	0.81	0.88	1.01	1.15
2150	59.82	62.58	63.55	0.50	0.63	0.75	0.76	0.89	1.02
2200	65.23	65.08	63.33	0.46	0.59	0.71	0.67	0.79	0.92
2230	65.87	64.16	62.12	0.43	0.56	0.68	0.63	0.75	0.86
2400	66.30	68.02	69.09	0.31	0.43	0.55	0.45	0.56	0.66
2500	70.47	67.69	64.07	0.25	0.37	0.49	0.39	0.49	0.58
3000	51.29	51.12	50.93	0.06	0.18	0.29	0.25	0.33	0.39
3100	51.20	51.15	51.08	0.05	0.17	0.28	0.23	0.31	0.37
3200	51.45	51.51	51.54	0.05	0.17	0.27	0.22	0.30	0.35
3220	51.54	51.62	51.67	0.05	0.17	0.27	0.22	0.30	0.35
3280	51.89	52.03	52.15	0.06	0.17	0.27	0.21	0.29	0.35
3400	52.93	53.19	53.44	0.07	0.19	0.28	0.20	0.28	0.34
3600	55.75	56.29	56.84	0.11	0.22	0.30	0.19	0.27	0.33
3800	60.55	61.67	62.96	0.15	0.25	0.33	0.18	0.26	0.33
4000	70.15	70.41	69.97	0.18	0.28	0.35	0.17	0.26	0.35
4200	66.76	64.82	62.94	0.20	0.30	0.36	0.17	0.27	0.36
4400	59.84	58.97	57.84	0.21	0.31	0.37	0.18	0.28	0.39
4600	56.03	55.45	54.83	0.22	0.32	0.37	0.18	0.29	0.42
4800	53.92	53.53	53.06	0.22	0.32	0.37	0.19	0.30	0.44
5000	52.45	52.23	51.87	0.21	0.31	0.37	0.19	0.32	0.47
5200	51.67	51.53	51.18	0.20	0.30	0.36	0.19	0.32	0.50
5400	51.32	51.19	50.91	0.18	0.29	0.36	0.19	0.33	0.52
5600	50.94	51.01	50.95	0.17	0.28	0.35	0.19	0.34	0.54
5800	51.34	51.37	50.88	0.15	0.27	0.35	0.18	0.34	0.55
6000	51.07	51.19	51.45	0.13	0.26	0.35	0.16	0.33	0.56
6200	51.68	51.88	51.65	0.11	0.25	0.35	0.16	0.34	0.57
6500	52.63	52.84	53.02	0.09	0.24	0.36	0.14	0.32	0.56
6600	54.23	54.16	54.65	0.08	0.24	0.36	0.13	0.32	0.56
6800	53.84	53.80	54.36	0.07	0.23	0.38	0.11	0.31	0.55
7000	53.38	53.18	53.29	0.07	0.24	0.39	0.10	0.30	0.54
7200	53.99	53.95	53.84	0.06	0.24	0.41	0.08	0.27	0.51
7400	52.59	50.86	48.85	0.06	0.24	0.43	0.06	0.26	0.52
7600	45.65	41.75	39.90	0.07	0.26	0.46	0.10	0.39	0.66
8000	42.45	42.95	43.30	0.06	0.26	0.49	0.03	0.15	0.35
10000	33.79	33.84	33.94	0.20	0.42	0.64	0.25	0.09	0.02
11600	29.64	29.83	30.06	0.34	0.57	0.75	0.17	0.04	0.25



ISO 9001 ISO 14001 AS 9100 CERTIFIED

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 • Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site



The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: www.minicircuits.com

IF/RF MICROWAVE COMPONENTS



REV. A

LFCG-1325+






210427

Page 1 of 2

Typical Performance Data

FREQ. (MHz)	GROUP DELAY		
	(nsec)		
	@-55°C	@+25°C	@+125°C
10	0.34	0.37	0.37
50	0.34	0.36	0.37
80	0.34	0.36	0.36
110	0.35	0.35	0.36
140	0.35	0.35	0.36
170	0.35	0.35	0.36
200	0.35	0.35	0.36
230	0.35	0.35	0.36
260	0.35	0.35	0.36
290	0.35	0.35	0.36
320	0.35	0.36	0.36
350	0.35	0.36	0.36
380	0.36	0.36	0.37
410	0.36	0.36	0.37
440	0.36	0.37	0.37
470	0.37	0.37	0.38
500	0.37	0.37	0.38
530	0.37	0.38	0.38
560	0.38	0.38	0.39
590	0.38	0.39	0.39
620	0.39	0.39	0.40
650	0.39	0.40	0.40
680	0.40	0.40	0.41
710	0.40	0.41	0.42
740	0.41	0.42	0.43
770	0.42	0.43	0.43
800	0.43	0.43	0.44
830	0.44	0.44	0.45
860	0.45	0.45	0.46
890	0.46	0.46	0.47
920	0.47	0.48	0.49
950	0.48	0.49	0.50
980	0.49	0.50	0.51
1010	0.51	0.52	0.53
1040	0.52	0.53	0.55
1100	0.56	0.57	0.59
1110	0.57	0.58	0.60
1200	0.63	0.65	0.67
1260	0.69	0.72	0.74
1300	0.74	0.77	0.80
1325	0.78	0.81	0.85

Typical Performance Curves




Case Style


GE

GE0805C-2

Outline Dimensions



PCB Land Pattern



Suggested Layout,
Tolerance to be within $\pm .002$

CASE #	A	B	C	D	E	F	G	H	J	K	L
GE0805C-2	.079 (2.00)	.049 (1.25)	.037 (0.95)	.014 (0.35)	.012 (0.30)	.012 (0.30)	.026 (0.65)	.025 (0.63)	.134 (3.40)	.110 (2.80)	.014 (0.35)

CASE #	M	WT. GRAM
GE0805C-2	.039 (1.00)	.008

Dimensions are in inches (mm). Tolerances: 2Pl. $\pm .01$; 3 Pl. $\pm .005$

Notes:

1. Open style, ceramic base.
2. Termination finish: For RoHS Case Styles: Tin plate over Nickel plate. All models, (+) suffix.
For RoHS-5 Case Styles: Tin-Lead plate over Nickel plate. All models, no (+) suffix.
3. Pad tolerance to be non-cumulative. Minimum spacing between each pad is .004 (0.1).

 **Mini-Circuits®**
ISO 9001 ISO 14001 CERTIFIED

ALL NEW
minicircuits.com

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site




The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: www.minicircuits.com

RF/IF MICROWAVE COMPONENTS


Tape & Reel Packaging TR-F114

DEVICE ORIENTATION IN T&R



Applicable Case Styles

GE0805C	JC0603C
GE0805C-1	JC0603C-4
GE0805C-1AP	JC0603C-6
GE0805C-7	
GE0805C-9	
GE0805C-10	
GE0805C-11	
GE0805C-12	



Applicable Case Styles

GE0805C-2	JC0603C-1
GE0805C-3	JC0603C-2
GE0805C-4	JC0603C-3
GE0805C-5	JC0603C-5
GE0805C-6	JC0603C-7
GE0805C-8	JV1210C-1
GE0805C-15	

Tape Width, mm	Device Cavity Pitch, mm	Reel Size, inches	Devices per Reel								
8	4	7	Small quantity standards (see note) <table border="1" style="margin-left: 20px;"> <tr><td>20</td></tr> <tr><td>50</td></tr> <tr><td>100</td></tr> <tr><td>200</td></tr> <tr><td>500</td></tr> <tr><td>1000</td></tr> <tr><td>Standard</td><td>4000</td></tr> </table>	20	50	100	200	500	1000	Standard	4000
20											
50											
100											
200											
500											
1000											
Standard	4000										

Note: Please Consult individual model data sheet to determine device per reel availability.

Mini-Circuits carrier tape materials provide protection from ESD (Electro-Static Discharge) during handling and transportation. Tapes are static dissipative and comply with industry standards EIA-481/EIA-541.


Go to: www.minicircuits.com/pages/pdfs/tape.pdf



Distribution Centers NORTH AMERICA 800-654-7949 • 417-335-5935 • Fax 417-335-5945 • EUROPE 44-1252-832600 • Fax 44-1252-837010


Mini-Circuits ISO 9001 & ISO 14001 Certified

INTERNET <http://www.minicircuits.com>



REVISIONS					
REV OR	ECN No.	DESCRIPTION		DATE	DR AUTH
	M148457	NEW RELEASE		10/14/14	GF MY

SUGGESTED MOUNTING CONFIGURATION
FOR GE0805C-4 CASE STYLE, "08FL07" PIN CODE





NOTES:

1. COPLANAR WAVEGUIDE IS SHOWN FOR ROGERS R04350B WITH DIELECTRIC THICKNESS $.010" \pm .001"$. COPPER: 1/2 OZ. EACH SIDE. FOR OTHER MATERIALS TRACE WIDTH AND GAP MAY NEED TO BE MODIFIED.
2. BOTTOM SIDE OF THE PCB IS CONTINUOUS GROUND PLANE.


 DENOTES PCB COPPER LAYOUT WITH SMOBC (SOLDER MASK OVER BARE COPPER).

 DENOTES COPPER LAND PATTERN FREE OF SOLDER MASK.


UNLESS OTHERWISE SPECIFIED	INITIALS		DATE
DIMENSIONS ARE IN INCHES	DRAWN	GF	10/01/14
TOLERANCES ON: 2 PL DECIMALS \pm 3 PL DECIMALS $\pm .005$	CHECKED	IL	10/14/14
ANGLES \pm FRACTIONS \pm	APPROVED	MY	10/14/14
			
	THIS DOCUMENT AND ITS CONTENTS ARE THE PROPERTY OF MINI-CIRCUITS. EXCEPT FOR USE EXPRESSLY GRANTED, IN WRITING, TO ITS VENDORS, VENDEE AND THE UNITED STATES GOVERNMENT, MINI-CIRCUITS RESERVES ALL PROPRIETARY DESIGN, USE, MANUFACTURING AND REPRODUCTION RIGHTS THERETO. THESE CONTENTS SHALL NOT BE USED, DUPLICATED OR DISCLOSED TO ANY OUTSIDE PARTY, IN WHOLE OR IN PART, WITHOUT WRITTEN PERMISSION OF MINI-CIRCUITS.		
ASHEETA1.DWG REV:A DATE:01/12/95			

	Mini-Circuits® 13 Neptune Avenue Brooklyn NY 11235		
PL, 08FL07, GE0805C-4, TB-799+			
SIZE A	CODE IDENT 15542	DRAWING NO: 98-PL-429	REV: OR
FILE: 98PL429	SCALE: 15:1	SHEET: 1 OF 1	

Evaluation Board and Circuit



TB-799+



Schematic Diagram

Notes:

1. 50 Ohm SMA Female connectors.
2. PCB Material: RO4350 or equivalent,
Dielectric Constant=3.5, Thickness=.010 inch.

Mini-Circuits®



Environmental Specifications

ENV06

All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

Specification	Test/Inspection Condition	Reference/Spec
Operating Temperature	-55° to 100°C Ambient Environment	Individual Model Data Sheet
Storage Temperature	-55° to 100° C Ambient Environment	Individual Model Data Sheet
Humidity	90 to 95% RH, 240 hours, 50°C	MIL-STD-202, Method 103, Condition A, Except 50°C and end-point electrical test done within 12 hours
Solder Reflow Heat	Sn-Pb Eutetic Process: 225°C peak Pb-Free Process 245° - 250°C peak	J-STD-020, Table 4-1, 4-2 and 5-2, Figure 5-1
Solderability	10X Magnification	J-STD-002, Para 4.2.5, Test S, 95% Coverage
Vibration (High Frequency)	20g peak, 10-2000 Hz, 12 times in each of three perpendicular directions (total 36)	MIL-STD-202, Method 204, Condition D
Mechanical Shock	50g, 11 ms, 1/2-sine, 18 shocks: 3 each direction, each of 3 axes	MIL-STD-202, Method 213, Condition A