

Ceramic

Low Pass Filter

LFCG-1700+

50Ω DC to 1700 MHz



Generic photo used for illustration purposes only
CASE STYLE: GE0805C-2

The Big Deal

- Very good rejection, 50 dB typical
- Rugged, ceramic construction
- Tiny size, 0.079" x 0.049" x 0.037" (0805)
- Excellent power handling, 5.5W

Product Overview

Mini-Circuits' LFCG-1700+ is an LTCC low pass filter with a passband from DC to 1700 MHz, supporting a variety of applications. This model provides 0.9 dB passband insertion loss and provides a very good stopband rejection due to strategically constructed layout with minimal interaction between components. It handles up to 5.5W RF input power and provides a wide operating temperature range from -55°C to +125°C. Housed in a tiny 0805 ceramic form factor with wraparound terminations, the filter is ideal for dense PCB layouts and with minimal performance variation due to parasitics.

Key Features

Feature	Advantages
Very good stopband rejection, 50 dB typical	The LTCC lowpass filter provides a very good stopband rejection until 13 GHz suitable for high end applications.
LTCC Construction	Provides repeatable performance in a rugged, ceramic package well suited for tough environments such as high humidity and temperature extremes.
Tiny size (0.079" x 0.049" x 0.037")	Saves space in dense circuit board layouts and minimizes the effects of parasitics.
Excellent power handling, 5.5W	Supports a wide range of system power requirements.
Wrap-around terminations	Provides excellent solderability and easy visual inspection

Notes

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp



Ceramic

Low Pass Filter

50Ω

DC to 1700 MHz

LFCG-1700+



Features

- Low loss, 0.9 dB typical
- High rejection 50 dB typical
- Excellent power handling, 5.5W
- Extremely small size 0805 (2.0mm x 1.25mm)
- Temperature stable
- LTCC construction

Generic photo used for illustration purposes only
CASE STYLE: GE0805C-2

+RoHS Compliant

The +Suffix identifies RoHS Compliance. See our web site for RoHS Compliance methodologies and qualifications

Applications

- Harmonic Rejection
- VHF/UHF transmitters / receivers
- Lab use


Electrical Specifications^{1,2} at 25°C

	Parameter	F#	Frequency (MHz)	Min.	Typ.	Max.	Unit
Pass Band	Insertion Loss	DC-F1	DC-1700	—	0.9	1.8	dB
	Freq. Cut-Off	F2	2025	—	3.0	—	dB
	Return Loss	DC-F1	DC-1700	—	18	—	dB
Stop Band	Rejection Loss	F3-F4	2400-2800	20	30	—	dB
		F4-F5	2800-8000	35	50	—	dB
		F5-F6	8000-13000	—	35	—	dB

1 DC de-coupling capacitors are required in Applications where DC voltage and/or current is present at either input or output ports. Please contact Mini-Circuits for alternatives if DC pass from IN-OUT is required.

2 Measured on Mini-Circuits Characterization Test Board TB-799+

Functional Schematic







Maximum Ratings	
Operating Temperature	-55°C to 125°C
Storage Temperature	-55°C to 125°C
RF Power Input*	5.5W max. @ 25°C

*Passband rating, derate linearly to 1W at 125°C ambient
Permanent damage may occur if any of these limits are exceeded.

Typical Performance Data at 25°C

Frequency (MHz)	Insertion Loss (dB)	Return Loss (dB)
10	0.10	40.69
100	0.14	34.39
1000	0.43	18.66
1700	0.91	27.84
2025	3.33	8.44
2180	13.23	2.52
2245	20.38	1.96
2315	30.42	1.70
2400	43.51	1.52
2500	39.17	1.35
2750	50.67	1.00
2800	55.91	0.95
4000	53.07	0.34
5000	52.51	0.18
8000	41.89	0.30
10000	35.78	0.31
11000	33.88	0.26
12000	31.05	0.23
12500	30.53	0.23
13000	30.38	0.26

Typical Frequency Response



Notes

- Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
- The parts covered by this specification document are subject to Mini-Circuit's standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp

 **Mini-Circuits®**



www.minicircuits.com P.O. Box 350166, Brooklyn, NY 11235-0003 (718) 934-4500 sales@minicircuits.com

Pad Connections

INPUT	8
OUTPUT	4
GROUND	1,2,3,5,6,7

Product Marking: KE

**Demo Board MCL P/N: TB-799+
Suggested PCB Layout (PL-429)**

**Outline Drawing****Outline Dimensions (inch)**

A	B	C	D	E	F	G	Wt.
.079 2.00	.049 1.25	.037 0.95	.014 0.35	.012 0.30	.012 0.30	.026 0.65	grams .008

Note: Please refer to case style drawing for details

Notes

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuits' applicable established test performance criteria and measurement instructions.
- C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp

Ceramic Low Pass Filter

LFCG-1700+

Typical Performance Data

FREQ. (MHz)	INSERTION LOSS			INPUT RETURN LOSS			OUTPUT RETURN LOSS		
	(dB)			(dB)			(dB)		
	@-55°C	@+25°C	@+125°C	@-55°C	@+25°C	@+125°C	@-55°C	@+25°C	@+125°C
10	0.10	0.11	0.13	36.96	37.78	35.55	38.24	39.06	36.47
60	0.12	0.14	0.16	39.58	37.45	36.01	38.90	36.87	35.48
100	0.13	0.15	0.18	37.39	35.66	34.51	35.75	34.27	33.18
140	0.14	0.17	0.20	35.29	34.41	33.67	33.44	32.57	31.77
180	0.15	0.18	0.22	33.54	33.52	33.33	31.50	31.18	30.70
200	0.15	0.19	0.23	32.82	33.20	33.31	30.75	30.62	30.28
240	0.16	0.20	0.25	31.77	32.73	33.43	29.43	29.56	29.42
300	0.17	0.22	0.27	30.66	32.06	33.47	27.82	28.04	28.05
400	0.19	0.24	0.30	29.29	30.59	32.42	25.82	25.85	25.87
500	0.21	0.27	0.34	27.51	28.56	30.04	24.14	24.06	24.03
800	0.28	0.36	0.46	21.97	22.47	22.95	20.05	20.01	20.00
1000	0.35	0.44	0.56	19.51	19.78	20.02	18.66	18.60	18.60
1500	0.55	0.69	0.87	20.51	20.98	21.51	21.60	21.99	22.32
1700	0.72	0.90	1.14	31.84	33.32	35.17	29.60	28.95	27.72
2000	2.10	2.67	3.55	12.77	11.92	10.75	11.26	10.27	9.10
2025	2.56	3.26	4.34	10.76	9.93	8.87	9.48	8.58	7.56
2050	3.20	4.07	5.40	8.86	8.10	7.22	7.81	7.03	6.21
2100	5.24	6.52	8.38	5.69	5.20	4.73	5.00	4.56	4.19
2200	12.88	14.94	17.68	2.34	2.35	2.40	2.22	2.30	2.48
2245	17.65	20.02	23.18	1.75	1.84	1.98	1.78	1.95	2.20
2300	24.63	27.55	31.49	1.33	1.46	1.63	1.50	1.72	2.00
2320	27.63	30.86	35.15	1.23	1.37	1.54	1.44	1.66	1.95
2400	42.59	43.04	41.53	0.94	1.09	1.28	1.25	1.48	1.77
2500	38.97	39.02	39.37	0.72	0.87	1.07	1.08	1.30	1.57
2700	44.55	46.16	48.34	0.47	0.63	0.82	0.82	1.01	1.24
2800	52.30	54.98	58.52	0.40	0.55	0.73	0.71	0.89	1.10
2900	64.97	63.94	61.27	0.34	0.49	0.67	0.62	0.78	0.97
3000	58.86	57.92	57.33	0.29	0.44	0.61	0.56	0.70	0.87
3250	59.21	60.33	62.00	0.22	0.35	0.52	0.42	0.54	0.68
3500	66.71	64.15	61.96	0.16	0.29	0.43	0.32	0.42	0.53
3600	63.20	61.36	59.74	0.16	0.28	0.42	0.30	0.40	0.51
4000	53.58	53.37	53.11	0.12	0.23	0.34	0.22	0.31	0.41
4250	52.23	52.19	52.11	0.10	0.20	0.31	0.19	0.28	0.38
4500	51.98	52.03	52.10	0.09	0.18	0.28	0.15	0.25	0.36
4750	52.24	52.43	52.47	0.07	0.16	0.25	0.12	0.23	0.35
5000	52.81	52.85	52.71	0.06	0.15	0.24	0.10	0.21	0.36
5250	52.97	53.03	52.89	0.04	0.14	0.23	0.08	0.20	0.37
5500	52.89	53.12	53.12	0.03	0.13	0.23	0.06	0.20	0.38
5750	52.38	52.85	52.73	0.02	0.12	0.23	0.06	0.20	0.40
6000	52.41	52.43	52.13	0.00	0.12	0.24	0.05	0.21	0.43
6250	51.64	51.69	51.11	0.01	0.12	0.26	0.05	0.22	0.45
6500	50.29	50.29	50.03	0.01	0.12	0.28	0.06	0.24	0.48
6750	49.51	49.16	49.11	0.02	0.13	0.31	0.06	0.25	0.50
7000	48.13	47.74	47.65	0.01	0.14	0.34	0.08	0.27	0.52
7500	45.23	45.49	45.22	0.01	0.17	0.41	0.09	0.28	0.54
8000	42.05	41.88	41.40	0.01	0.21	0.49	0.09	0.27	0.51
8500	41.67	42.35	43.00	0.04	0.25	0.57	0.13	0.30	0.49
9000	39.29	39.45	39.14	0.05	0.27	0.61	0.04	0.19	0.36
9500	37.03	37.03	37.06	0.07	0.30	0.63	0.00	0.15	0.29
10000	35.74	35.65	35.78	0.08	0.30	0.63	0.02	0.13	0.26
10500	34.63	34.55	35.01	0.09	0.31	0.60	0.04	0.11	0.24
10750	34.04	34.20	34.37	0.09	0.30	0.57	0.05	0.10	0.24
11000	33.46	33.63	33.58	0.08	0.28	0.54	0.06	0.10	0.25
11250	32.77	32.73	32.98	0.08	0.28	0.51	0.07	0.10	0.26
11500	32.00	32.00	32.20	0.08	0.27	0.48	0.06	0.12	0.30
11750	31.25	31.33	31.55	0.07	0.26	0.45	0.06	0.13	0.34
12000	30.81	30.95	31.19	0.07	0.25	0.43	0.06	0.14	0.37
12250	30.47	30.68	30.78	0.07	0.24	0.42	0.06	0.15	0.42
12500	30.31	30.49	30.60	0.08	0.25	0.42	0.06	0.17	0.46
13000	30.07	30.33	30.57	0.11	0.31	0.48	0.05	0.21	0.57



ISO 9001 ISO 14001 AS 9100 CERTIFIED

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 • Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site
 minicircuits.com






IF/RF MICROWAVE COMPONENTS

REV. A
LFCG-1700+
210428
Page 1 of 2

Typical Performance Data

FREQ. (MHz)	GROUP DELAY		
	(nsec)		
	@-55°C	@+25°C	@+125°C
10	0.23	0.27	0.26
50	0.27	0.29	0.29
100	0.28	0.29	0.29
110	0.28	0.29	0.29
140	0.28	0.28	0.29
170	0.28	0.28	0.29
200	0.28	0.28	0.29
230	0.28	0.28	0.29
260	0.28	0.28	0.29
290	0.28	0.28	0.29
320	0.28	0.29	0.29
350	0.28	0.29	0.29
380	0.28	0.29	0.29
410	0.29	0.29	0.29
440	0.29	0.29	0.30
470	0.29	0.29	0.30
500	0.29	0.29	0.30
530	0.29	0.29	0.30
560	0.29	0.30	0.30
590	0.30	0.30	0.30
620	0.30	0.30	0.31
650	0.30	0.30	0.31
680	0.30	0.31	0.31
710	0.31	0.31	0.31
740	0.31	0.31	0.32
770	0.31	0.31	0.32
800	0.31	0.32	0.32
830	0.32	0.32	0.33
850	0.32	0.32	0.33
900	0.33	0.33	0.34
950	0.33	0.34	0.34
1000	0.34	0.34	0.35
1050	0.35	0.35	0.36
1100	0.36	0.36	0.37
1150	0.37	0.37	0.38
1200	0.38	0.38	0.39
1250	0.39	0.40	0.41
1300	0.40	0.41	0.42
1500	0.48	0.49	0.51
1600	0.54	0.55	0.57
1700	0.63	0.64	0.67

Typical Performance Curves




Case Style


GE

GE0805C-2

Outline Dimensions



PCB Land Pattern



Suggested Layout,
Tolerance to be within ±.002

CASE #	A	B	C	D	E	F	G	H	J	K	L
GE0805C-2	.079 (2.00)	.049 (1.25)	.037 (0.95)	.014 (0.35)	.012 (0.30)	.012 (0.30)	.026 (0.65)	.025 (0.63)	.134 (3.40)	.110 (2.80)	.014 (0.35)

CASE #	M	WT. GRAM
GE0805C-2	.039 (1.00)	.008

Dimensions are in inches (mm). Tolerances: 2Pl. ± .01; 3 Pl. ± .005

Notes:

1. Open style, ceramic base.
2. Termination finish: For RoHS Case Styles: Tin plate over Nickel plate. All models, (+) suffix.
For RoHS-5 Case Styles: Tin-Lead plate over Nickel plate. All models, no (+) suffix.
3. Pad tolerance to be non-cumulative. Minimum spacing between each pad is .004 (0.1).

 **Mini-Circuits®**
ISO 9001 ISO 14001 CERTIFIED

ALL NEW
minicircuits.com

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site




The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: www.minicircuits.com

RF/IF MICROWAVE COMPONENTS


Tape & Reel Packaging TR-F114

DEVICE ORIENTATION IN T&R



Applicable Case Styles

GE0805C	JC0603C
GE0805C-1	JC0603C-4
GE0805C-1AP	JC0603C-6
GE0805C-7	
GE0805C-9	
GE0805C-10	
GE0805C-11	
GE0805C-12	



Applicable Case Styles

GE0805C-2	JC0603C-1
GE0805C-3	JC0603C-2
GE0805C-4	JC0603C-3
GE0805C-5	JC0603C-5
GE0805C-6	JC0603C-7
GE0805C-8	JV1210C-1
GE0805C-15	

Tape Width, mm	Device Cavity Pitch, mm	Reel Size, inches	Devices per Reel								
8	4	7	Small quantity standards (see note) <table border="1" style="margin-left: 20px;"> <tr><td>20</td></tr> <tr><td>50</td></tr> <tr><td>100</td></tr> <tr><td>200</td></tr> <tr><td>500</td></tr> <tr><td>1000</td></tr> <tr><td>Standard</td><td>4000</td></tr> </table>	20	50	100	200	500	1000	Standard	4000
20											
50											
100											
200											
500											
1000											
Standard	4000										

Note: Please Consult individual model data sheet to determine device per reel availability.

Mini-Circuits carrier tape materials provide protection from ESD (Electro-Static Discharge) during handling and transportation. Tapes are static dissipative and comply with industry standards EIA-481/EIA-541.

Go to: www.minicircuits.com/pages/pdfs/tape.pdf




Distribution Centers NORTH AMERICA 800-654-7949 • 417-335-5935 • Fax 417-335-5945 • EUROPE 44-1252-832600 • Fax 44-1252-837010

INTERNET <http://www.minicircuits.com>


P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661

Mini-Circuits ISO 9001 & ISO 14001 Certified



REVISIONS					
REV OR	ECN No.	DESCRIPTION		DATE	DR AUTH
	M148457	NEW RELEASE		10/14/14	GF MY

SUGGESTED MOUNTING CONFIGURATION
FOR GE0805C-4 CASE STYLE, "08FL07" PIN CODE



NOTES:


1. COPLANAR WAVEGUIDE IS SHOWN FOR ROGERS R04350B WITH DIELECTRIC THICKNESS $.010" \pm .001"$. COPPER: 1/2 OZ. EACH SIDE. FOR OTHER MATERIALS TRACE WIDTH AND GAP MAY NEED TO BE MODIFIED.
2. BOTTOM SIDE OF THE PCB IS CONTINUOUS GROUND PLANE.

[Solid Blue Box] DENOTES PCB COPPER LAYOUT WITH SMOBC (SOLDER MASK OVER BARE COPPER).


[Hatched Box] DENOTES COPPER LAND PATTERN FREE OF SOLDER MASK.

UNLESS OTHERWISE SPECIFIED	INITIALS		DATE	 13 Neptune Avenue Brooklyn NY 11235
DIMENSIONS ARE IN INCHES	DRAWN	GF	10/01/14	
TOLERANCES ON: 2 PL DECIMALS $\pm .005$	CHECKED	IL	10/14/14	
3 PL DECIMALS $\pm .005$	APPROVED	MY	10/14/14	
FRACTIONS \pm				
 THIS DOCUMENT AND ITS CONTENTS ARE THE PROPERTY OF MINI-CIRCUITS. EXCEPT FOR USE EXPRESSLY GRANTED, IN WRITING, TO ITS VENDORS, VENDEE AND THE UNITED STATES GOVERNMENT, MINI-CIRCUITS RESERVES ALL PROPRIETARY DESIGN, USE, MANUFACTURING AND REPRODUCTION RIGHTS THERETO. THESE CONTENTS SHALL NOT BE USED, DUPLICATED OR DISCLOSED TO ANY OUTSIDE PARTY, IN WHOLE OR IN PART, WITHOUT WRITTEN PERMISSION OF MINI-CIRCUITS.				
PL, 08FL07, GE0805C-4, TB-799+				
SIZE A	CODE IDENT 15542	DRAWING NO: 98-PL-429		REV: OR
FILE: 98PL429	SCALE: 15:1	SHEET: 1 OF 1		
ASHEETA1.DWG REV:A DATE:01/12/95				

Evaluation Board and Circuit



TB-799+



Schematic Diagram

Notes:

1. 50 Ohm SMA Female connectors.
2. PCB Material: RO4350 or equivalent,
Dielectric Constant=3.5, Thickness=.010 inch.

 Mini-Circuits®



Environmental Specifications

ENV06

All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

Specification	Test/Inspection Condition	Reference/Spec
Operating Temperature	-55° to 100°C Ambient Environment	Individual Model Data Sheet
Storage Temperature	-55° to 100° C Ambient Environment	Individual Model Data Sheet
Humidity	90 to 95% RH, 240 hours, 50°C	MIL-STD-202, Method 103, Condition A, Except 50°C and end-point electrical test done within 12 hours
Solder Reflow Heat	Sn-Pb Eutetic Process: 225°C peak Pb-Free Process 245° - 250°C peak	J-STD-020, Table 4-1, 4-2 and 5-2, Figure 5-1
Solderability	10X Magnification	J-STD-002, Para 4.2.5, Test S, 95% Coverage
Vibration (High Frequency)	20g peak, 10-2000 Hz, 12 times in each of three perpendicular directions (total 36)	MIL-STD-202, Method 204, Condition D
Mechanical Shock	50g, 11 ms, 1/2-sine, 18 shocks: 3 each direction, each of 3 axes	MIL-STD-202, Method 213, Condition A