



LTCC SURFACE MOUNT

Low Pass Filter


LFHK-1000+

50Ω

DC to 1000 MHz

THE BIG DEAL

- Low Insertion Loss, Typ. 1.5 dB
- Passband Return Loss, Typ. 19 dB
- Stopband Rejection, Typ. 78 dB
- 1008 Surface Mount Footprint
- Power Handling: 10 W




Generic photo used for illustration purposes only

APPLICATIONS

- Harmonic Rejection and Spurious Cleanup
- Tactical Radio
- Test and Measurement Equipment
- UHF Transmitters / Receivers

FUNCTIONAL DIAGRAM



PRODUCT OVERVIEW

Mini-Circuits' LFHK-1000+ is a miniature low temperature co-fired ceramic (LTCC) low pass filter with a DC to 1000 MHz passband supporting a variety of applications. This model provides 1.5 dB typical insertion loss over a wide band due to its rugged monolithic construction. Housed in a small 1008 ceramic form factor the filter is ideal for dense signal chain PCB layouts where it complements MMIC size and performance. The LTCC fabrication process assures minimal RF performance variation while delivering a product that is well suited for environmental extremes of high humidity and temperature.

KEY FEATURES

Features	Advantages
Ultra-Wide Stopband	The LTCC lowpass filter provides a very good stopband rejection up to 40 GHz, suitable for wide band applications.
LTCC Construction	Provides repeatable performance in a rugged, ceramic package well suited for tough environments such as high humidity and temperature extremes.
Small Size, 1008	Saves space in dense circuit board layouts and minimizes the effects of parasitics.
Rugged Power Handling, 10 Watts	Handles up to 10 Watts in a small 1008 package.



LTCC SURFACE MOUNT

Low Pass Filter

LFHK-1000+

50Ω

DC to 1000 MHz

ELECTRICAL SPECIFICATIONS^{1,2,3} AT +25°C

Parameter	F#	Frequency (MHz)	Min.	Typ.	Max.	Units	
Passband	Insertion Loss	DC-F1	DC - 1000	—	1.5	2.0	dB
	Freq. Cut-Off ⁴	Fc	1300	—	3	—	dB
	Return Loss	DC-F1	DC - 1000	10	19	—	dB
Stopband	Rejection	F2-F3	1700 - 2500	20	35	—	dB
		F3-F4	2500 - 7500	65	78	—	
		F4-F5	7500 - 14500	30	50	—	
		F5-F6	14500 - 25000	20	29	—	
		F6-F7	25000 - 40000	—	25	—	


1. Tested on Evaluation Board P/N TB-LFHK-1000+ with connectors and feedline de-embedded with thru-line compensation.
2. This filter is bi-directional, RF1 and RF2 ports may be interchanged.
3. In applications where DC voltage and/or current is present at either the input or output ports, external DC blocking capacitors are required.
4. Typical variation ±5%.

ABSOLUTE MAXIMUM RATINGS⁵

Parameter	Ratings
Operating Temperature	-55°C to +125°C
Storage Temperature	-55°C to +125°C
Input Power ⁶	10 W @ +25°C






5. Permanent damage may occur if any of these limits are exceeded.
6. Power rating applies only to signals within the passband. Power rating above +25°C operating temperature decreases linearly to 1.5 W at +125°C.

TYPICAL FREQUENCY RESPONSE AT +25°C





TYPICAL PERFORMANCE GRAPHS





FUNCTIONAL DIAGRAM





Figure 1. LFHK-1000+ Functional Diagram

PAD DESCRIPTION

Function	Pad Number	Description
RF1 ²	1	Connects to RF Input Port
RF2 ²	2	Connects to RF Output Port
GROUND	3	Connects to Ground on PCB, (See drawing PL-798)
NC	-	No connection, not used internally. See drawing PL-798 for connection to PCB

CASE STYLE DRAWING



Weight: .019 grams.

Dimensions are in inches (mm). Tolerances: 2Pl. ± .01; 3Pl. ± .005

PRODUCT MARKING*: ZW

*Marking may contain other features or characters for internal lot control.



SUGGESTED PCB LAYOUT (PL-798)




Figure 2. Suggested PCB Layout PL-798



LTCC SURFACE MOUNT

Low Pass Filter

LFHK-1000+

50Ω

DC to 1000 MHz

ADDITIONAL DETAILED INFORMATION IS AVAILABLE ON OUR DASHBOARD.

[CLICK HERE](#)

Performance Data and Graphs	Data Graphs S-Parameter (S2P Files) Data Set (.zip file) De-embedded to device pads
Case Style	NL1008C-9 Lead Finish: Gold over Electroless Nickel
RoHS Status	Compliant
Tape and Reel	TR-F75
Suggested Layout for PCB Design	PL-798
Evaluation Board	TB-LFHK-1000+
	Gerber File
Environmental Rating	ENV06T10

NOTES

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuits' applicable established test performance criteria and measurement instructions.
- C. The parts covered by this specification document are subject to Mini-Circuits' standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the standard terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/terms/viewterm.html








Typical Performance Data

FREQ. (MHz)	INSERTION LOSS			INPUT RETURN LOSS			OUTPUT RETURN LOSS		
	(dB)			(dB)			(dB)		
	@-55°C	@+25°C	@+125°C	@-55°C	@+25°C	@+125°C	@-55°C	@+25°C	@+125°C
10	0.11	0.13	0.17	37.36	35.31	33.46	37.11	35.07	33.22
50	0.15	0.18	0.22	28.80	28.02	27.37	28.85	28.05	27.39
100	0.20	0.24	0.28	24.77	24.38	24.09	24.79	24.36	24.08
200	0.30	0.34	0.38	20.49	20.77	21.00	20.51	20.74	21.00
500	0.49	0.56	0.64	19.16	19.32	19.80	19.17	19.32	19.79
1000	0.89	1.03	1.22	35.61	34.01	30.56	33.66	32.19	29.54
1300	2.71	3.33	4.30	10.92	9.60	8.06	11.63	10.17	8.50
1700	35.33	36.14	37.20	0.61	0.71	0.83	0.61	0.71	0.83
1800	41.98	42.74	43.74	0.57	0.65	0.77	0.57	0.65	0.77
2000	53.79	54.55	55.54	0.51	0.59	0.70	0.52	0.60	0.71
2400	73.74	74.30	75.60	0.45	0.52	0.61	0.46	0.53	0.63
2500	79.04	79.65	82.11	0.43	0.50	0.59	0.44	0.51	0.60
2800	98.17	97.76	104.89	0.37	0.44	0.52	0.39	0.46	0.55
3000	99.52	93.68	100.14	0.34	0.41	0.49	0.36	0.43	0.52
3400	93.15	90.10	107.16	0.28	0.37	0.45	0.31	0.39	0.48
3600	96.45	90.38	93.50	0.27	0.35	0.43	0.30	0.38	0.47
4000	92.25	101.89	89.93	0.26	0.36	0.44	0.29	0.38	0.47
4500	90.26	87.98	96.22	0.30	0.40	0.48	0.32	0.42	0.50
5000	101.99	94.71	94.56	0.36	0.46	0.54	0.37	0.47	0.56
5500	103.19	95.79	100.03	0.42	0.53	0.61	0.43	0.53	0.62
5800	96.67	96.18	92.66	0.45	0.56	0.65	0.46	0.57	0.67
6000	97.32	93.02	93.47	0.47	0.58	0.67	0.49	0.60	0.70
6200	104.16	92.62	91.47	0.48	0.60	0.69	0.52	0.63	0.73
6400	94.48	104.84	99.52	0.49	0.61	0.70	0.54	0.65	0.75
6600	98.12	94.40	98.93	0.49	0.61	0.70	0.57	0.68	0.78
6800	93.92	91.60	96.58	0.51	0.63	0.72	0.59	0.70	0.80
7000	102.78	109.82	107.35	0.52	0.65	0.74	0.60	0.72	0.82
7500	94.99	97.06	99.22	0.56	0.68	0.78	0.65	0.76	0.86
7800	103.35	109.02	94.29	0.59	0.71	0.81	0.66	0.77	0.87
8000	111.93	93.78	86.59	0.62	0.74	0.84	0.67	0.78	0.88
8500	68.41	63.86	59.31	0.74	0.92	1.12	0.73	0.88	1.07
8600	59.11	55.10	53.68	0.87	1.08	1.15	0.81	1.01	1.16
8800	49.19	51.49	53.63	0.86	0.91	0.97	0.94	0.96	1.01
9000	49.59	53.41	59.97	0.75	0.86	0.91	0.80	0.88	0.93
9400	73.78	75.93	79.44	0.62	0.75	0.84	0.61	0.74	0.83
9600	79.54	81.41	80.79	0.58	0.73	0.82	0.58	0.72	0.82
10000	79.50	81.46	80.67	0.56	0.73	0.83	0.57	0.74	0.85
11000	55.81	60.48	66.96	1.73	1.42	1.21	2.73	2.14	1.62
14500	59.97	63.80	68.38	0.93	1.12	1.19	0.99	1.17	1.28
16000	76.18	71.20	68.49	0.84	1.10	1.27	0.86	1.09	1.28
18000	49.17	49.98	50.23	1.10	1.39	1.58	0.98	1.27	1.45
20000	32.62	38.01	46.96	2.59	2.95	2.59	2.72	2.94	3.36
21000	76.22	78.48	80.91	1.15	1.48	1.65	1.50	1.76	1.92
22000	78.33	79.74	78.02	1.34	1.69	1.90	1.28	1.60	1.81
23000	77.12	77.33	76.81	1.53	1.85	2.09	1.34	1.63	1.86
24000	74.89	75.14	75.25	1.35	1.70	1.91	1.26	1.59	1.82
25000	73.20	73.54	73.31	1.01	1.45	1.65	1.14	1.57	1.80
26000	72.90	73.06	74.35	1.23	1.69	1.94	1.34	1.80	2.06
27000	62.55	59.60	56.80	1.86	2.42	2.78	1.88	2.37	2.85
29000	58.18	57.63	56.80	1.65	2.10	2.47	1.62	2.03	2.34
30000	49.70	46.86	42.58	1.92	2.71	3.67	1.59	2.19	2.81
31000	28.15	28.44	31.00	5.96	5.55	4.68	4.00	4.64	4.10
32000	30.39	30.56	30.90	3.73	4.95	6.72	3.27	4.28	5.78
33000	33.88	39.63	45.00	4.31	3.77	3.55	5.07	4.21	3.89
34000	50.06	51.80	52.87	1.85	2.40	2.74	2.29	2.88	3.26
35000	49.39	47.97	45.42	2.50	3.26	3.96	2.80	3.48	4.06
36000	35.37	38.07	42.73	4.22	4.09	4.04	3.83	3.98	3.88
37000	46.69	47.39	47.64	2.38	3.21	4.04	2.07	2.70	3.22
38000	48.16	57.26	61.18	3.90	3.86	3.78	3.37	3.82	3.55
40000	37.72	40.75	42.90	2.90	3.42	3.56	3.41	4.01	4.24

Typical Performance Data

FREQ. (MHz)	GROUP DELAY		
	(nsec)		
	@-55°C	@+25°C	@+125°C
10	1.08	1.09	1.10
20	1.08	1.09	1.10
30	1.08	1.09	1.10
40	1.08	1.08	1.10
50	1.07	1.08	1.10
100	1.07	1.08	1.09
200	1.06	1.07	1.08
220	1.06	1.07	1.08
240	1.06	1.07	1.08
260	1.07	1.07	1.08
280	1.07	1.07	1.09
300	1.07	1.08	1.09
320	1.07	1.08	1.09
340	1.07	1.08	1.09
360	1.08	1.08	1.10
380	1.08	1.09	1.10
400	1.08	1.09	1.10
440	1.09	1.10	1.11
460	1.10	1.10	1.12
480	1.10	1.11	1.12
500	1.11	1.12	1.13
520	1.11	1.12	1.13
540	1.12	1.13	1.14
560	1.13	1.13	1.15
580	1.13	1.14	1.15
600	1.14	1.15	1.16
640	1.16	1.17	1.18
680	1.18	1.18	1.20
700	1.19	1.19	1.21
720	1.20	1.20	1.22
740	1.21	1.22	1.23
760	1.22	1.23	1.24
800	1.24	1.25	1.27
860	1.29	1.30	1.32
900	1.32	1.33	1.35
1000	1.43	1.45	1.47

Typical Performance Curves




Case Style




NL

Outline Dimensions

NL1008C-9



SIDE VIEW



BOTTOM VIEW

 METALLIZATION

SUGGESTED LAYOUT FOR PCB LAND PATTERN
PATTERN TO BE WITHIN ±.002

Dimensions are in inches (mm). Tolerances: 2Pl. ± .01; 3Pl. ± .005

Notes:

1. Open style, Ceramic base.
2. Termination finish: **as shown below or indicated on Data sheet.**
For RoHS Case Styles: Gold plate over nickel plate. All models, (+) suffix.
3. Weight: .019 grams.
4. Pad tolerance is non-cumulative.

 **Mini-Circuits**[®]
ISO 9001 ISO 14001 CERTIFIED

ALL NEW
 minicircuits.com

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site



The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: www.minicircuits.com

RF/IF MICROWAVE COMPONENTS

DEVICE ORIENTATION IN T&R




ILLUSTRATION 1

Applicable Case Styles
FV1206-1 FV1206-3




ILLUSTRATION 2

Applicable Case Styles
FV1206-4 FV1206-5 FV1206-6 FV1206-7 FV1206-9




ILLUSTRATION 3

Applicable Case Styles
FV1206-11 FV1206-12 GE0805C-18 NL1008C-6 NL1008C-7 NL1008C-9 NL1008C-10 NL1008C-12

Tape Width, mm	Device Cavity Pitch, mm	Reel Size, inches	Devices per Reel	
8	4	7	Small quantity standards (see note)	20
				50
				100
				200
				500
				1000
			Standard	3000

Note: Please consult individual model data sheet to determine device per reel availability.


Mini-Circuits carrier tape materials provide protection from ESD (Electro-Static Discharge) during handling and transportation. Tapes are static dissipative and comply with industry standards EIA-481/EIA-541.

Go to: www.minicircuits.com/pages/pdfs/tape.pdf



INTERNET <http://www.minicircuits.com>
 P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661
 Distribution Centers NORTH AMERICA 800-654-7949 • 417-335-5935 • Fax 417-335-5945 • EUROPE 44-1252-832600 • Fax 44-1252-837010
 Mini-Circuits ISO 9001 & ISO 14001 Certified


THIRD ANGLE PROJECTION




REVISIONS

REV	ECN No.	DESCRIPTION	DATE	DR	AUTH
OR	ECO-023057	NEW RELEASE	SEP 24	AGS	GT
OR1	NPO-004738	ADDED NL1008C-10 CASE STYLE	OCT 24	AGS	GT
OR2	ECO-023820	NOTES & TOLERANCES UPDATED	NOV 24	AGS	GT

SUGGESTED MOUNTING CONFIGURATION FOR NL1008C-9, NL1008C-10 CASE STYLE



STACK-UP DIAGRAM




1. TOTAL FINISHED THICKNESS 0.0228±.004
2. B-VIA PRESENT FROM COPPER LAYER 1 TO COPPER LAYER 2.
3. PTH PRESENT FROM COPPER LAYER 1 TO COPPER LAYER 4.
4. INDICATED ON TOP VIEW PTH'S ARE PLUGGED WITH EPOXY AND CAPPED WITH COPPER FROM TOP SIDE.
5. L4 IS CONTINUOUS GROUND PLANE.

NOTES:

1. DIMENSIONS ARE IN INCHES ; \boxed{CD} DENOTES CRITICAL DIMENSIONS.
2. PCB IS MULTILAYER, SEE STACK-UP DIAGRAM AND SHEET-2 FOR ILLUSTRATION.
3. TRACE WIDTH & GAP PARAMETERS ARE SHOWN FOR MEGTRON 6 R-5775(G), CLOTH STYLE:1080 WITH DIELECTRIC THICKNESS .0051; COPPER: 1/2 OZ.+PLATING. FOR OTHER MATERIALS TRACE WIDTH AND GAP MAY NEED TO BE MODIFIED.
4. COPPER LAYER 4 OF THE PCB ARE CONTINUOUS GROUND PLANE.



DENOTES PCB COPPER LAYOUT WITH SMOBC (SOLDER MASK OVER BARE COPPER)



DENOTES COPPER LAND PATTERN FREE OF SOLDER MASK

UNLESS OTHERWISE SPECIFIED	INITIALS	DATE
DIMENSIONS ARE IN INCHES	DRAWN AGS	14 SEP 24
TOLERANCES ON:	CHECKED MD	16 SEP 24
2 PL DECIMALS ±	APPROVED GTP	17 SEP 24
3 PL DECIMALS ± .002		
ANGLES ±		
FRACTIONS ±		



Mini-Circuits®

13 Neptune Avenue
Brooklyn NY 11235


PL, NL1008C-9/10, TB-LFHK-XXXX+

Mini-Circuits®
THIS DOCUMENT AND ITS CONTENTS ARE THE PROPERTY OF MINI-CIRCUITS. EXCEPT FOR USE EXPRESSLY GRANTED, IN WRITING, TO ITS VENDORS, VENDEE AND THE UNITED STATES GOVERNMENT, MINI-CIRCUITS RESERVES ALL PROPRIETARY DESIGN, USE, MANUFACTURING AND REPRODUCTION RIGHTS THERETO. THESE CONTENTS SHALL NOT BE USED, DUPLICATED OR DISCLOSED TO ANY OUTSIDE PARTY, IN WHOLE OR IN PART, WITHOUT WRITTEN PERMISSION OF MINI-CIRCUITS.


SIZE	CODE IDENT	DRAWING NO:	REV:
A	15542	98-PL-798	OR2

FILE:	SCALE:	SHEET:
98-PL-798	9:1	1 OF 2


LAYER 1, SOLDER MASK & PTH




LAYER 2, B-VIA & PTH



LAYER 3 & PTH



LAYER 4 & PTH



Mini-Circuits

THIS DOCUMENT AND ITS CONTENTS ARE THE PROPERTY OF MINI-CIRCUITS. EXCEPT FOR USE EXPRESSLY GRANTED, IN WRITING, TO ITS VENDORS, VENDEE AND THE UNITED STATES GOVERNMENT, MINI-CIRCUITS RESERVES ALL PROPRIETARY DESIGN, USE, MANUFACTURING AND REPRODUCTION RIGHTS THERETO. THESE CONTENTS SHALL NOT BE USED, DUPLICATED OR DISCLOSED TO ANY OUTSIDE PARTY, IN WHOLE OR IN PART, WITHOUT WRITTEN PERMISSION OF MINI-CIRCUITS.

ALL DIMENSIONS ARE IN INCHES EXCEPT OTHERWISE SPECIFIED


SIZE A	CODE IDENT 15542	DRAWING NO: 98-PL-798	REV: OR2
-----------	---------------------	--------------------------	-------------

ASHEETA2.DWG REV:A DATE: 01/12/94


FILE: 98-PL-798	SCALE: 7.7:1	SHEET: 2 OF 2
--------------------	-----------------	------------------

Evaluation Board and Circuit

TB-LFHK-1000+




STACK-UP DIAGRAM



Notes:

1. PCB Material: MEGTRON-6 R5775(G) OR Equivalent, Dielectric Constant=3.6
2. Total finished thickness: .023
3. 50 Ohm 2.92mm Female End Launch Connector.

 **Mini-Circuits®**

All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

Specification	Test/Inspection Condition	Reference/Spec
Operating Temperature	-55° to 125° C Ambient Environment	Individual Model Data Sheet
Storage Temperature	-55° to 125° C Ambient Environment	Individual Model Data Sheet
Humidity	90 to 95% RH, 240 hours, 50°C	MIL-STD-202, Method 103, Condition A, Except 50°C and end-point electrical test done within 12 hours
Solder Reflow Heat	Sn-Pb Eutectic Process 225°C peak Pb-Free Process 245° - 250°C peak	J-STD-020C, Table 4-1, 4-2 and 5-2, Figure 5-1
Solderability	10X Magnification	J-STD-002, Test B,B1, 95% Coverage
Thermal Shock	-55° to +125°C, 15 min dwell,250 cycles	MIL-STD-202, Method 107
Bend Test	1mm, deflection for 5 seconds Span of bending: 2.75"	--
High Temp Storage	125°C to 1000 Hrs	---