

50Ω

DC to 850 MHz

The Big Deal

- Very good rejection, 50 dB typical
- Rugged, ceramic construction
- Tiny size, 0.079" x 0.049" x 0.037" (0805)
- Excellent power handling, 4.5W

*Generic photo used for illustration purposes only*

CASE STYLE: GE0805C-2

Product Overview

Mini-Circuits' LFCG-900+ is an LTCC low pass filter with a passband from DC to 850 MHz, supporting a variety of applications. This model provides 1.3 dB typical passband insertion loss and provides a very good stopband rejection due to strategically constructed layout with minimal interaction between components. It handles up to 4.5W RF input power and provides a wide operating temperature range from -55 to +125°C. Housed in a tiny 0805 ceramic form factor with wraparound terminations, the filter is ideal for dense PCB layouts and with minimal performance variation due to parasitics.

Key Features

Feature	Advantages
Ultra-wide stopband	The LTCC lowpass filter provides a very good stopband rejection until 11 GHz suitable for high end applications.
LTCC Construction	Provides repeatable performance in a rugged, ceramic package well suited for tough environments such as high humidity and temperature extremes.
Tiny size (0.079" x 0.049" x 0.037")	Saves space in dense circuit board layouts and minimizes the effects of parasitics.
Excellent power handling, 4.5W	Supports a wide range of system power requirements.
Wrap-around terminations	Provides excellent solderability and easy visual inspection

Notes

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp



Low Pass Filter

50Ω

DC to 850 MHz

LFCG-900+



Generic photo used for illustration purposes only
CASE STYLE: GE0805C-2

+RoHS Compliant

The +Suffix identifies RoHS Compliance. See our web site for RoHS Compliance methodologies and qualifications


Features

- Low loss, 1.3 dB typical
- High rejection 50 dB typical
- Excellent power handling, 4.5W
- Extremely small size 0805 (2.0mm x 1.25mm)
- Temperature stable
- LTCC construction

Applications

- Harmonic Rejection
- VHF/UHF transmitters / receivers
- Military radar applications
- Test and measurement
- Telecommunications & broadband wireless applications
- Medical telemetry

Functional Schematic



Electrical Specifications^{1,2} at 25°C

Parameter		F#	Frequency (MHz)	Min.	Typ.	Max.	Unit
Pass Band	Insertion Loss	DC-F1	DC - 850	—	1.3	2.2	dB
	Freq. Cut-Off	F2	1000	—	3.0	—	dB
	Return Loss	DC-F1	DC - 850	—	18	—	dB
Stop Band	Rejection Loss	F3-F4	1300 - 1600	20	48	—	dB
		F4-F5	1600 - 4500	33	46	—	dB
		F5-F6	4500-11000	—	20	—	dB

1. DC de-coupling capacitors are required in Applications where DC voltage and/or current is present at either input or output ports. Please contact Mini-Circuits for alternatives if DC pass from IN-OUT is required.

2. Measured on Mini-Circuits Characterization Test Board TB-799+

Maximum Ratings





Operating Temperature	-55°C to 125°C
Storage Temperature	-55°C to 125°C
RF Power Input*	4.5W max. @25°C

*Passband rating, derate linearly to 1.1W at 125°C ambient
Permanent damage may occur if any of these limits are exceeded.

Typical Performance Data at 25°C

Frequency (MHz)	Insertion Loss (dB)	Return Loss (dB)
10	0.15	35.63
100	0.24	27.53
400	0.49	18.01
500	0.60	16.69
600	0.71	16.77
850	1.23	23.45
900	1.50	23.55
1000	3.00	13.27
1100	13.41	4.44
1135	20.67	3.82
1175	31.20	3.35
1300	50.87	1.96
1600	55.16	0.68
4000	43.61	0.28
4500	43.92	0.26
6000	36.98	0.40
7000	38.43	0.40
8500	33.27	0.34
10000	23.27	0.19
11000	23.00	0.21

Typical Frequency Response



Notes

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp




www.minicircuits.com P.O. Box 350166, Brooklyn, NY 11235-0003 (718) 934-4500 sales@minicircuits.com

Pad Connections

INPUT	8
OUTPUT	4
GROUND	1,2,3,5,6,7


Product Marking: LN

Demo Board MCL P/N: TB-799+
Suggested PCB Layout (PL-429)



- NOTES:
1. COPLANAR WAVEGUIDE IS SHOWN FOR ROGERS RO4350B WITH DIELECTRIC THICKNESS .010" ± .001". COPPER: 1/2 OZ. EACH SIDE. FOR OTHER MATERIALS TRACE WIDTH AND GAP MAY NEED TO BE MODIFIED.
 2. BOTTOM SIDE OF THE PCB IS CONTINUOUS GROUND PLANE.
- DENOTES PCB COPPER LAYOUT WITH SMOBC (SOLDER MASK OVER BARE COPPER).
- DENOTES COPPER LAND PATTERN FREE OF SOLDER MASK.

Outline Drawing



Outline Dimensions (inch mm)

A	B	C	D	E	F	G	Wt.
.079	.049	.037	.014	.012	.012	.026	grams
2.00	1.25	0.95	0.35	0.30	0.30	0.65	.008

Note: Please refer to case style drawing for details

Notes

A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.

B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.

C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp






Typical Performance Data

FREQ.	INSERTION LOSS			INPUT RETURN LOSS			OUTPUT RETURN LOSS		
(MHz)	(dB)			(dB)			(dB)		
	@-55°C	@+25°C	@+125°C	@-55°C	@+25°C	@+125°C	@-55°C	@+25°C	@+125°C
10	0.11	0.13	0.16	32.95	34.28	32.65	33.20	33.23	32.10
40	0.13	0.16	0.19	34.68	33.07	32.33	35.09	33.21	32.52
100	0.18	0.23	0.27	30.78	29.83	29.49	28.57	27.73	27.27
160	0.22	0.28	0.33	27.62	27.76	28.16	25.20	24.83	24.64
220	0.26	0.33	0.39	25.44	26.06	27.00	22.74	22.65	22.61
280	0.31	0.38	0.45	23.40	24.11	25.07	20.63	20.63	20.56
340	0.35	0.43	0.51	21.56	22.16	22.91	19.11	19.07	19.02
400	0.40	0.49	0.58	19.99	20.49	21.04	17.89	17.84	17.78
460	0.45	0.55	0.66	18.71	19.15	19.55	16.92	16.91	16.86
520	0.51	0.62	0.74	17.84	18.23	18.54	16.41	16.45	16.41
580	0.57	0.69	0.82	17.43	17.79	18.04	16.36	16.43	16.43
640	0.63	0.77	0.92	17.62	17.94	18.17	16.83	16.95	16.97
700	0.70	0.86	1.03	18.46	18.79	19.00	17.93	18.10	18.07
760	0.79	0.96	1.17	20.22	20.54	20.67	19.81	19.94	19.71
850	1.01	1.24	1.52	25.31	25.42	25.30	23.24	22.73	21.96
880	1.13	1.39	1.71	28.18	28.30	28.41	23.86	23.14	22.26
900	1.23	1.51	1.86	31.39	31.89	32.73	23.88	23.09	22.17
1000	2.41	3.03	3.92	16.08	14.52	12.71	14.08	12.89	11.58
1120	14.91	17.31	20.16	2.40	2.42	2.50	3.69	4.02	4.52
1130	16.94	19.46	22.45	2.14	2.21	2.31	3.53	3.89	4.41
1135	18.00	20.59	23.66	2.03	2.11	2.23	3.46	3.83	4.36
1175	27.82	31.08	34.93	1.49	1.63	1.79	3.03	3.40	3.89
1300	49.15	50.57	52.45	0.88	1.03	1.19	1.78	2.00	2.27
1360	58.68	61.13	62.44	0.74	0.88	1.04	1.34	1.53	1.75
1400	66.10	64.38	63.04	0.67	0.81	0.97	1.12	1.29	1.48
1600	56.88	55.42	54.14	0.45	0.59	0.74	0.56	0.68	0.81
2500	61.96	63.71	66.66	0.13	0.27	0.40	0.20	0.26	0.32
2850	53.17	52.60	51.98	0.10	0.22	0.35	0.17	0.24	0.29
2900	51.74	51.36	50.94	0.09	0.21	0.34	0.16	0.23	0.29
2950	50.59	50.33	49.95	0.08	0.20	0.33	0.17	0.24	0.30
3000	49.74	49.41	49.15	0.08	0.20	0.32	0.16	0.23	0.29
3100	48.24	48.03	47.83	0.06	0.18	0.30	0.15	0.22	0.28
3200	47.06	47.02	46.77	0.06	0.18	0.29	0.14	0.21	0.28
3300	46.20	46.17	45.98	0.06	0.18	0.29	0.13	0.21	0.28
3500	44.95	44.95	44.87	0.05	0.17	0.27	0.11	0.20	0.28
3700	44.09	44.13	44.13	0.04	0.16	0.25	0.10	0.19	0.29
4000	43.52	43.67	43.75	0.06	0.17	0.25	0.08	0.19	0.32
4500	43.63	43.89	44.05	0.09	0.20	0.28	0.06	0.20	0.38
5500	51.10	52.94	57.04	0.18	0.30	0.40	0.06	0.25	0.58
5650	61.59	59.53	50.50	0.19	0.32	0.43	0.08	0.30	0.67
5800	45.64	40.17	35.18	0.22	0.36	0.51	0.15	0.48	1.14
5950	31.66	34.20	37.28	0.27	0.37	0.47	0.69	0.56	0.77
6000	33.83	36.42	38.85	0.24	0.36	0.48	0.35	0.41	0.72
6250	41.10	42.11	43.09	0.21	0.36	0.51	0.08	0.31	0.70
6400	42.22	42.53	42.32	0.21	0.38	0.54	0.09	0.33	0.73
6550	41.99	39.98	39.37	0.23	0.40	0.59	0.10	0.35	0.77
6600	40.41	39.30	36.87	0.23	0.41	0.62	0.10	0.37	0.82
6850	29.71	33.03	35.98	0.41	0.48	0.64	0.43	0.47	0.77
7000	36.36	37.64	38.58	0.26	0.44	0.66	0.12	0.35	0.72
7150	38.65	39.14	39.50	0.23	0.43	0.67	0.09	0.33	0.71
7300	38.45	39.15	39.03	0.25	0.45	0.70	0.10	0.33	0.69
7450	38.56	38.26	37.98	0.24	0.45	0.73	0.06	0.30	0.66
7600	37.52	37.54	37.61	0.25	0.47	0.77	0.07	0.31	0.65
7750	36.91	36.81	36.90	0.26	0.49	0.81	0.07	0.30	0.64
7900	36.14	35.81	36.34	0.27	0.51	0.85	0.06	0.29	0.60
8000	34.99	35.01	34.86	0.29	0.53	0.89	0.07	0.29	0.60
8200	34.35	33.87	34.67	0.29	0.55	0.92	0.05	0.27	0.55
9000	31.08	31.92	31.81	0.45	0.76	1.22	0.03	0.24	0.47
9800	25.87	24.23	24.16	3.35	3.25	2.77	0.03	0.24	0.48
11000	23.65	23.20	23.27	1.65	1.58	1.71	0.04	0.22	0.58


Typical Performance Data

FREQ.	GROUP DELAY		
(MHz)	(nsec)		
	@-55°C	@+25°C	@+125°C
10	0.45	0.49	0.49
20	0.50	0.52	0.53
40	0.51	0.52	0.54
60	0.51	0.53	0.54
80	0.51	0.53	0.54
100	0.52	0.53	0.54
120	0.52	0.53	0.54
140	0.52	0.53	0.54
160	0.52	0.53	0.54
180	0.52	0.53	0.54
200	0.52	0.53	0.54
220	0.53	0.53	0.55
240	0.53	0.54	0.55
260	0.53	0.54	0.55
280	0.54	0.55	0.56
300	0.54	0.55	0.56
320	0.55	0.56	0.57
340	0.56	0.56	0.57
360	0.56	0.57	0.58
380	0.57	0.58	0.59
400	0.58	0.58	0.60
420	0.58	0.59	0.60
440	0.59	0.60	0.61
460	0.60	0.61	0.63
480	0.61	0.62	0.64
500	0.63	0.64	0.65
520	0.64	0.65	0.66
540	0.65	0.66	0.68
560	0.67	0.68	0.69
580	0.68	0.70	0.71
600	0.70	0.72	0.73
620	0.72	0.74	0.76
640	0.75	0.76	0.78
660	0.77	0.79	0.81
680	0.80	0.81	0.84
700	0.83	0.85	0.87
800	1.02	1.04	1.08
820	1.06	1.09	1.13
840	1.10	1.14	1.18
850	1.15	1.18	1.23
900	1.36	1.41	1.48


Typical Performance Curves



Outline Dimensions



PCB Land Pattern



Suggested Layout,
Tolerance to be within ± 0.002

CASE #	A	B	C	D	E	F	G	H	J	K	L
GE0805C-2	.079 (2.00)	.049 (1.25)	.037 (0.95)	.014 (0.35)	.012 (0.30)	.012 (0.30)	.026 (0.65)	.025 (0.63)	.134 (3.40)	.110 (2.80)	.014 (0.35)

CASE #	M	WT. GRAM
GE0805C-2	.039 (1.00)	.008

Dimensions are in inches (mm). Tolerances: 2Pl. $\pm .01$; 3 Pl. $\pm .005$

Notes:

1. Open style, ceramic base.
2. Termination finish: For RoHS Case Styles: Tin plate over Nickel plate. All models, (+) suffix.
For RoHS-5 Case Styles: Tin-Lead plate over Nickel plate. All models, no (+) suffix.
3. Pad tolerance to be non-cumulative. Minimum spacing between each pad is .004 (0.1).



P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site



Provides ACTUAL Data Instantly From MINI-CIRCUITS At: www.minicircuits.com

RF/IF MICROWAVE COMPONENTS

Tape & Reel Packaging TR-F114

DEVICE ORIENTATION IN T&R




ILLUSTRATION 1

Applicable Case Styles	
GE0805C	JC0603C
GE0805C-1	JC0603C-4
GE0805C-1AP	JC0603C-6
GE0805C-7	
GE0805C-9	
GE0805C-10	
GE0805C-11	
GE0805C-12	




ILLUSTRATION 2

Applicable Case Styles	
GE0805C-2	JC0603C-1
GE0805C-3	JC0603C-2
GE0805C-4	JC0603C-3
GE0805C-5	JC0603C-5
GE0805C-6	JC0603C-7
GE0805C-8	
GE0805C-15	

Tape Width, mm	Device Cavity Pitch, mm	Reel Size, inches	Devices per Reel	
8	4	7	Small quantity standards (see note)	20
				50
				100
				200
				500
				1000
			Standard	4000

Note: Please Consult individual model data sheet to determine device per reel availability.

Mini-Circuits carrier tape materials provide protection from ESD (Electro-Static Discharge) during handling and transportation. Tapes are static dissipative and comply with industry standards EIA-481/EIA-541.

Go to: www.minicircuits.com/pages/pdfs/tape.pdf




INTERNET <http://www.minicircuits.com>

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661

Distribution Centers NORTH AMERICA 800-654-7949 • 417-335-5935 • Fax 417-335-5945 • EUROPE 44-1252-832600 • Fax 44-1252-837010

Mini-Circuits ISO 9001 & ISO 14001 Certified


THIRD ANGLE PROJECTION



REVISIONS


REV	ECN No.	DESCRIPTION	DATE	DR	AUTH
OR	M148457	NEW RELEASE	10/14/14	GF	MY

SUGGESTED MOUNTING CONFIGURATION
FOR GE0805C-4 CASE STYLE, "08FL07" PIN CODE

NOTES:

1. COPLANAR WAVEGUIDE IS SHOWN FOR ROGERS R04350B WITH DIELECTRIC THICKNESS .010" $\pm$.001". COPPER: 1/2 OZ. EACH SIDE. FOR OTHER MATERIALS TRACE WIDTH AND GAP MAY NEED TO BE MODIFIED.
2. BOTTOM SIDE OF THE PCB IS CONTINUOUS GROUND PLANE.

 DENOTES PCB COPPER LAYOUT WITH SMOBC (SOLDER MASK OVER BARE COPPER).

 DENOTES COPPER LAND PATTERN FREE OF SOLDER MASK.

UNLESS OTHERWISE SPECIFIED

DIMENSIONS ARE IN INCHES

TOLERANCES ON:

2 PL DECIMALS $\pm$ 3 PL DECIMALS $\pm$.005ANGLES $\pm$ FRACTIONS $\pm$

INITIALS

DATE

DRAWN

GF

10/01/14

CHECKED

IL

10/14/14

APPROVED

MY

10/14/14



Mini-Circuits®

13 Neptune Avenue
Brooklyn NY 11235

PL, 08FL07, GE0805C-4, TB-799+

THIS DOCUMENT AND ITS CONTENTS ARE THE PROPERTY OF MINI-CIRCUITS. EXCEPT FOR USE EXPRESSLY GRANTED, IN WRITING, TO ITS VENDORS, VENDEE AND THE UNITED STATES GOVERNMENT, MINI-CIRCUITS RESERVES ALL PROPRIETARY DESIGN, USE, MANUFACTURING AND REPRODUCTION RIGHTS THERETO. THESE CONTENTS SHALL NOT BE USED, DUPLICATED OR DISCLOSED TO ANY OUTSIDE PARTY, IN WHOLE OR IN PART, WITHOUT WRITTEN PERMISSION OF MINI-CIRCUITS.

Mini-Circuits®

ASHEETA1.DWG REV:A DATE:01/12/95

SIZE
ACODE IDENT
15542

DRAWING NO:

98-PL-429

REV:

OR


FILE: 98PL429

SCALE: 15:1

SHEET:

1 OF 1

Evaluation Board and Circuit



Schematic Diagram

Notes:

1. 50 Ohm SMA Female connectors.
2. PCB Material: R04350 or equivalent,
Dielectric Constant=3.5, Thickness=.010 inch.

 **Mini-Circuits®**



All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

Specification	Test/Inspection Condition	Reference/Spec
Operating Temperature	-55° to 100°C Ambient Environment	Individual Model Data Sheet
Storage Temperature	-55° to 100° C Ambient Environment	Individual Model Data Sheet
Humidity	90 to 95% RH, 240 hours, 50°C	MIL-STD-202, Method 103, Condition A, Except 50°C and end-point electrical test done within 12 hours
Solder Reflow Heat	Sn-Pb Eutetic Process: 225°C peak Pb-Free Process 245° - 250°C peak	J-STD-020, Table 4-1, 4-2 and 5-2, Figure 5-1
Solderability	10X Magnification	J-STD-002, Para 4.2.5, Test S, 95% Coverage
Vibration (High Frequency)	20g peak, 10-2000 Hz, 12 times in each of three perpendicular directions (total 36)	MIL-STD-202, Method 204, Condition D
Mechanical Shock	50g, 11 ms, 1/2-sine, 18 shocks: 3 each direction, each of 3 axes	MIL-STD-202, Method 213, Condition A