



Mini-Circuits®

CERAMIC


Low Pass Filter

50Ω DC¹ to 1325 MHz

LFCN-1325+

FEATURES

- Excellent power handling, 9 W
- Small size
- 5 sections
- Temperature stable
- LTCC construction



Generic photo used for illustration purposes only

CASE STYLE: FV1206

APPLICATIONS

- Harmonic rejection
- VHF/UHF transmitters/receivers
- Lab use

+RoHS Compliant

The +Suffix identifies RoHS Compliance.
See our website for methodologies and qualifications

ELECTRICAL SPECIFICATIONS^{1,2} AT +25°C

Parameter		F#	Frequency (MHz)	Min.	Typ.	Max.	Units
Passband	Insertion Loss	DC-F1	DC-1325	—	—	1.3	dB
	Freq. Cut-Off	F2	1560	—	3.0	—	dB
	VSWR	DC-F1	DC-1325	—	1.4	—	:1
Stopband	Rejection Loss	F3	2100	20	—	—	dB
		F4-F5	2200	—	30	—	
		F6	4250	—	20	—	
	VSWR	F3-F6	2100-4250	—	20	—	:1

1. In Application where DC voltage is present at either input or output ports, coupling capacitors are required.


2. Measured on Mini-Circuits Characterization Test Board TB-LFCN-1325+.

ABSOLUTE MAXIMUM RATINGS


Parameter	Ratings
Operating Temperature	-55°C to +100°C
Storage Temperature	-55°C to +100°C
RF Power Input ³	9 W max. at +25°C

3. Passband rating, derate linearly to 4 W at +100°C ambient.
Permanent damage may occur if any of these limits are exceeded.

TYPICAL FREQUENCY RESPONSE



FUNCTIONAL SCHEMATIC





Mini-Circuits®

CERAMIC

Low Pass Filter

LFCN-1325+

50Ω DC¹ to 1325 MHz

PIN CONNECTIONS

RF IN	1
RF OUT	3
GROUND	2,4

PRODUCT MARKING: A6

DEMO BOARD MCL P/N: TB-LFCN-1325+
SUGGESTED PCB LAYOUT (PL-137)


NOTES: 1. COPLANAR WAVEGUIDE PARAMETERS ARE SHOWN FOR ROGERS RO4350B WITH THICKNESS .020" ± .0015".
COPPER: 1/2 OZ. EACH SIDE.
FOR OTHER MATERIALS TRACE WIDTH & GAP MAY NEED TO BE MODIFIED.

2. BOTTOM SIDE OF THE PCB IS CONTINUOUS GROUND PLANE.
-  DENOTES PCB COPPER LAYOUT WITH SMOBC (SOLDER MASK OVER BARE COPPER)
-  DENOTES COPPER LAND PATTERN FREE OF SOLDER MASK

OUTLINE DRAWING



PCB Land Pattern



OUTLINE DIMENSIONS (Inches mm)


A	B	C	D	E	F	G	
.126	.063	.037	.020	.032	.009	.169	
3.20	1.60	0.94	0.51	0.81	0.23	4.29	
H	J	K	L	M	N	P	wt
.087	.024	.122	.024	.087	.012	.071	grams
2.21	0.61	3.10	0.61	2.21	0.30	1.80	.020

TAPE & REEL INFORMATION: F71



TYPICAL PERFORMANCE DATA AT +25°C

Frequency (MHz)	Insertion Loss (dB)	VSWR (:1)
10	0.12	1.03
174	0.23	1.17
338	0.36	1.32
503	0.50	1.40
667	0.56	1.38
1160	0.71	1.11
1325	1.06	1.47
1518	3.52	3.91
2003	23.27	32.79
2577	28.97	51.10
3055	24.14	41.37
3533	22.45	51.10
3772	21.83	44.55
4011	21.11	40.41
4250	20.18	34.75



NOTES

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
- C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the standard. Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp

Ceramic Low Pass Filter

LFCN-1325+

Typical Performance Data

FREQ. (MHz)	INSERTION LOSS (dB)			INPUT RETURN LOSS (dB)			OUTPUT RETURNLOSS (dB)		
	@ -55° C	@ +25° C	@ +100° C	@ -55° C	@ +25° C	@ +100° C	@ -55° C	@ +25° C	@ +100° C
40	0.05	0.06	0.08	38.21	41.41	42.69	37.43	40.04	40.99
100	0.10	0.11	0.13	27.05	28.17	29.78	27.11	27.99	29.19
200	0.14	0.18	0.21	23.01	21.45	20.45	22.87	21.39	20.47
400	0.26	0.32	0.39	17.32	16.66	15.62	17.21	16.56	15.54
800	0.37	0.44	0.51	17.60	17.82	18.36	17.47	17.68	18.14
1000	0.38	0.47	0.55	23.21	23.35	24.99	23.14	23.23	24.48
1200	0.48	0.58	0.69	23.56	24.17	24.59	24.51	25.14	25.91
1325	0.67	0.81	0.96	16.64	16.38	15.91	17.03	16.78	16.27
1400	0.97	1.16	1.37	11.96	11.61	11.14	12.13	11.80	11.26
1560	3.07	3.42	3.84	4.51	4.39	4.24	4.56	4.43	4.21
1800	10.92	11.40	11.94	0.88	0.95	1.01	0.87	0.93	0.95
2000	18.74	19.35	19.95	0.39	0.47	0.53	0.38	0.44	0.47
2100	22.92	23.61	24.29	0.31	0.39	0.44	0.30	0.36	0.38
2200	27.40	28.23	29.03	0.27	0.35	0.40	0.26	0.32	0.34
2400	40.97	43.00	45.65	0.22	0.30	0.36	0.23	0.28	0.29
2800	34.14	33.92	33.56	0.15	0.26	0.34	0.19	0.25	0.28
3000	31.35	31.19	31.18	0.13	0.25	0.35	0.18	0.24	0.27
3200	30.31	30.33	30.22	0.12	0.24	0.36	0.17	0.24	0.29
3400	29.29	29.37	29.30	0.11	0.24	0.37	0.17	0.25	0.30
3800	27.59	27.57	27.52	0.12	0.25	0.40	0.17	0.27	0.34
4000	26.60	26.77	27.16	0.18	0.29	0.43	0.20	0.29	0.36
4200	26.91	27.08	27.24	0.19	0.31	0.47	0.16	0.28	0.38
4250	26.89	26.95	26.85	0.17	0.31	0.47	0.18	0.30	0.40
4400	25.55	25.81	25.90	0.18	0.31	0.47	0.23	0.34	0.43
4800	24.55	24.74	25.01	0.25	0.37	0.54	0.25	0.37	0.48
5000	24.93	25.08	24.97	0.23	0.40	0.59	0.22	0.39	0.53
5400	23.30	23.34	23.47	0.30	0.46	0.64	0.32	0.47	0.60
5800	22.82	22.86	22.74	0.30	0.50	0.68	0.35	0.51	0.65
6000	21.82	21.93	22.08	0.34	0.51	0.69	0.40	0.51	0.64
6200	21.56	21.80	21.88	0.33	0.50	0.67	0.37	0.50	0.63
6400	21.66	21.41	21.47	0.38	0.57	0.71	0.40	0.52	0.64
6800	20.50	20.51	20.55	0.42	0.58	0.71	0.41	0.55	0.67
7000	19.58	19.63	19.83	0.48	0.59	0.68	0.42	0.53	0.65
7200	19.33	19.32	19.50	0.49	0.62	0.69	0.44	0.55	0.65
7400	18.82	18.92	19.11	0.47	0.66	0.80	0.48	0.59	0.72
7800	18.43	18.51	18.79	0.50	0.63	0.69	0.51	0.58	0.68
8000	17.74	17.92	18.00	0.44	0.63	0.72	0.49	0.56	0.66
8200	17.55	17.41	17.44	0.51	0.67	0.75	0.53	0.64	0.73
8400	17.11	17.02	17.09	0.47	0.66	0.77	0.54	0.63	0.71
8800	16.07	15.99	15.86	0.49	0.71	0.89	0.58	0.73	0.80
9000	15.73	15.37	15.23	0.53	0.73	0.91	0.60	0.77	0.84
9200	14.81	14.62	14.41	0.55	0.79	1.03	0.67	0.84	0.92
9400	14.09	13.92	13.72	0.55	0.77	1.01	0.63	0.83	0.93
9800	12.76	12.66	12.43	0.64	0.83	1.11	0.65	0.89	1.04
10000	11.94	11.96	11.71	0.72	0.92	1.22	0.73	1.00	1.17
10200	10.89	11.01	10.87	0.86	1.02	1.33	0.83	1.10	1.30
10400	9.78	9.97	9.88	1.04	1.19	1.52	1.03	1.27	1.51
10800	7.23	7.27	7.22	1.73	2.02	2.45	1.79	2.17	2.60
11200	3.92	3.76	3.81	4.28	5.48	6.57	4.65	6.12	8.26
11400	2.51	2.64	3.08	8.73	10.82	10.32	10.54	15.46	24.87
11800	3.50	4.19	5.11	5.52	5.12	4.60	6.34	5.54	4.87
12000	4.96	5.41	6.16	3.26	3.65	3.85	3.66	3.72	3.68

REV. X1
LFCN-1325+
080729
Page 1 of 1



IF/RF MICROWAVE COMPONENTS • ISO 9001 ISO 14001 AS9100 CERTIFIED • RoHS compliant

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661



The Design Engineers Search Engine finds the model you need, Instantly • For detailed performance specs & shopping online see




Ceramic Low Pass Filter


Typical Performance Curves

LFCN-1325+


INSERTION LOSS vs. TEMPERATURE



INPUT RETURN LOSS vs. TEMPERATURE



OUTPUT RETURN LOSS vs. TEMPERATURE




REV. X1
LFCN-1325+
080729
Page 1 of 1

Outline Dimensions



PCB Land Pattern



Suggested Layout,
Tolerance to be within $\pm .002$

CASE #	A	B	C	D	E	F	G	H	J	K	L	M	N	P	WT. GRAM
FV1206	.126 (3.20)	.063 (1.60)	.037 (0.94)	.020 (0.51)	.032 (0.81)	.009 (0.23)	.169 (4.29)	.087 (2.21)	.024 (0.61)	.122 (3.10)	.024 (0.61)	.087 (2.21)	.012 (0.30)	.071 (1.80)	.020

Dimensions are in inches (mm). Tolerances: 2 Pl. $\pm .01$; 3 Pl. $\pm .005$

Notes:

- Open style, ceramic base.
- Termination finish: **as shown below or indicated on Data Sheet.**
For RoHS Case Styles: Tin plate over Nickel plate. All models, (+) suffix.
For RoHS-5 Case Styles: Tin-Lead plate. All models, no (+) suffix.



P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site



The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: www.minicircuits.com

RF/IF MICROWAVE COMPONENTS

Tape & Reel Packaging TR-F71



ILLUSTRATION 1

Tape Width, mm	Device Cavity Pitch, mm	Reel Size, inches	Devices per Reel	
8	4	7	Small quantity standards (see note)	20
				50
				100
				200
				500
				1000
			Standard	3000

Note: Please Consult individual model data sheet to determine device per reel availability.

Mini-Circuits carrier tape materials provide protection from ESD (Electro-Static Discharge) during handling and transportation. Tapes are static dissipative and comply with industry standards EIA-481/EIA-541.

Go to: www.minicircuits.com/pages/pdfs/tape.pdf



P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site



The Design Engineers Search Engine Provides ACTUAL Data Instantly From Mini-Circuits At: www.minicircuits.com

RF/IF MICROWAVE COMPONENTS

THIRD ANGLE PROJECTION



REVISIONS

REV	ECN No.	DESCRIPTION	DATE	DR	AUTH
OR	M88634	NEW RELEASE	08/28/03	GF	ABD
A	M102713	ADDED "...WITH SMOBC"	01/17/06	MMG	IL

**SUGGESTED MOUNTING CONFIGURATION
FOR FV1206 CASE STYLE, "nx" PIN CONNECTION**



NOTES: 1. COPLANAR WAVEGUIDE PARAMETERS ARE SHOWN FOR ROGERS R04350B WITH THICKNESS .020" $\pm$.0015".
COPPER: 1/2 OZ. EACH SIDE.
FOR OTHER MATERIALS TRACE WIDTH & GAP MAY NEED TO BE MODIFIED.

2. BOTTOM SIDE OF THE PCB IS CONTINUOUS GROUND PLANE.



DENOTES PCB COPPER LAYOUT WITH SMOBC
(SOLDER MASK OVER BARE COPPER)



DENOTES COPPER LAND PATTERN FREE OF SOLDER MASK

UNLESS OTHERWISE SPECIFIED

INITIALS

DATE

DIMENSIONS ARE IN INCHES

TOLERANCES ON:

2 PL DECIMALS $\pm$ 3 PL DECIMALS $\pm$.005ANGLES $\pm$ FRACTIONS $\pm$

DRAWN

GF

08/27/03

CHECKED

AV

08/28/03

APPROVED

ABD

08/28/03



Mini-Circuits®

13 Neptune Avenue
Brooklyn NY 11235

PL, nx, FV1206, LFCN/HFCN, TB-270

SIZE

A

CODE IDENT

15542

DRAWING NO:

98-PL-137

REV:

A

FILE:


98PL137

SCALE:

10:1

SHEET:



1 OF 1



THIS DOCUMENT AND ITS CONTENTS ARE THE PROPERTY OF MINI-CIRCUITS. EXCEPT FOR USE EXPRESSLY GRANTED, IN WRITING, TO ITS VENDORS, VENDEE AND THE UNITED STATES GOVERNMENT, MINI-CIRCUITS RESERVES ALL PROPRIETARY DESIGN, USE, MANUFACTURING AND REPRODUCTION RIGHTS THERETO. THESE CONTENTS SHALL NOT BE USED, DUPLICATED OR DISCLOSED TO ANY OUTSIDE PARTY, IN WHOLE OR IN PART, WITHOUT WRITTEN PERMISSION OF MINI-CIRCUITS.

ASHEETA1.DWG REV:A DATE:01/12/95

Evaluation Board and Circuit



Schematic Diagram

Notes:

1. SMA Female connectors.
2. PCB Material: ROGERS RO4350 or equivalent,
Dielectric Constant=3.5, Thickness=.020 inch.

 **Mini-Circuits®**



All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

Specification	Test/Inspection Condition	Reference/Spec
Operating Temperature	-55° to 100°C Ambient Environment	Individual Model Data Sheet
Storage Temperature	-55° to 100° C Ambient Environment	Individual Model Data Sheet
Humidity	90 to 95% RH, 240 hours, 50°C	MIL-STD-202, Method 103, Condition A, Except 50°C and end-point electrical test done within 12 hours
Solder Reflow Heat	Sn-Pb Eutetic Process: 225°C peak Pb-Free Process 245° - 250°C peak	J-STD-020, Table 4-1, 4-2 and 5-2, Figure 5-1
Solderability	10X Magnification	J-STD-002, Para 4.2.5, Test S, 95% Coverage
Vibration (High Frequency)	20g peak, 10-2000 Hz, 12 times in each of three perpendicular directions (total 36)	MIL-STD-202, Method 204, Condition D
Mechanical Shock	50g, 11 ms, 1/2-sine, 18 shocks: 3 each direction, each of 3 axes	MIL-STD-202, Method 213, Condition A