

Surface Mount Frequency Mixer

LRMS-2H+

Level 17 (LO Power +17dBm) 5 to 1000 MHz



Generic photo used for illustration purposes only
CASE STYLE: QQQ130

Maximum Ratings

Operating Temperature	-40°C to 85°C
Storage Temperature	-55°C to 100°C
RF Power	200mW
IF Current	40mA
Permanent damage may occur if any of these limits are exceeded.	

Pin Connections

LO	1
RF	4
IF	5
GROUND	2,3,6

Features

- low conversion loss, 6.98 dB typ.
- excellent L-R isolation, 39 dB typ.;
- L-I isolation, 45 dB typ.

Applications

- VHF/UHF
- instrumentation
- cellular


+RoHS Compliant

The +Suffix identifies RoHS Compliance. See our web site for RoHS Compliance methodologies and qualifications


Available Tape and Reel at no extra cost

Reel Size	Devices/Reel
7"	10, 20, 50, 100, 200
13"	500

Outline Drawing




PCB Land Pattern



Outline Dimensions (inch/mm)

A	B	C	D	E	F	G	wt
.400	.31	.200	.10	.010	.100	.050	
10.16	7.87	5.08	2.54	0.25	2.54	1.27	
H	J	K	L	M			grams
.420	.120	.060	.100	.020			0.55
10.67	3.05	1.52	2.54	0.51			

Demo Board MCL P/N: TB-44+ Suggested PCB Layout (PL-083)



- NOTES: 1. TRACE WIDTH IS SHOWN FOR ROGERS RO4350B WITH DIELECTRIC THICKNESS 0.030" ± 0.002"; COPPER: 1/2 OZ. EACH SIDE. FOR OTHER MATERIALS TRACE WIDTH MAY NEED TO BE MODIFIED.
2. BOTTOM SIDE OF THE PCB IS CONTINUOUS GROUND PLANE.
- DENOTES PCB COPPER LAYOUT WITH SMOBC (SOLDER MASK OVER BARE COPPER)
- DENOTES COPPER LAND PATTERN FREE OF SOLDER MASK

Notes

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
- C. The parts covered by this specification document are subject to Mini-Circuit's standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuit's website at www.minicircuits.com/MCLStore/terms.jsp

Electrical Specifications

FREQUENCY (MHz)	CONVERSION LOSS (dB)	LO-RF ISOLATION (dB)						LO-IF ISOLATION (dB)									
		Mid-Band		Total Range		L		M		U		L		M		U	
LO/RF	IF	\bar{X}	σ	Max.	Max.	Typ.	Min.	Typ.	Min.	Typ.	Min.	Typ.	Min.	Typ.	Min.	Typ.	Min.
5-1000	DC-900	6.98	.054	8.5	9.3	55	40	39	22	33	20	52	30	45	22	30	17


1 dB COMP.: +14 dBm typ.







L = low range [f_L to $10 f_L$]
M = mid band [$2 f_L$ to $f_U/2$]
U = upper range [$f_U/2$ to f_U]

Typical Performance Data

Frequency (MHz)		Conversion Loss (dB)	Isolation L-R (dB)	Isolation L-I (dB)	VSWR RF Port (:1)	VSWR LO Port (:1)
RF	LO	LO +17dBm	LO +17dBm	LO +17dBm	LO +17dBm	LO +17dBm
5.00	35.00	7.85	66.33	72.89	1.54	1.95
10.00	40.00	7.64	63.63	68.70	1.49	1.85
20.00	50.00	7.69	58.93	63.79	1.47	1.79
50.00	80.00	7.55	52.00	56.89	1.45	1.91
95.45	65.45	7.54	46.41	50.84	1.44	1.79
100.00	70.00	7.53	46.04	50.67	1.43	1.79
185.91	155.91	7.51	40.70	46.79	1.43	1.69
200.00	170.00	7.37	40.02	46.99	1.42	1.68
276.36	246.36	7.35	37.35	44.46	1.40	1.56
366.82	336.82	7.22	35.28	42.69	1.34	1.47
457.27	427.27	7.11	33.66	39.45	1.25	1.36
487.42	457.42	7.17	33.17	37.61	1.24	1.34
500.00	470.00	7.07	33.04	37.36	1.21	1.34
547.73	517.73	7.11	32.95	35.68	1.11	1.28
638.18	608.18	7.46	32.78	31.60	1.06	1.29
728.64	698.64	7.45	31.90	30.61	1.27	1.46
819.09	789.09	7.76	30.74	28.78	1.54	1.81
909.55	879.55	8.24	29.67	27.10	1.90	2.21
969.85	939.85	8.54	29.46	25.48	2.06	2.34
1000.00	970.00	8.75	29.31	24.84	2.10	2.40

Electrical Schematic





Notes

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
- C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp



Frequency Mixer

LRMS-2H+

Typical Performance Data

RF (IN) (MHz)	LO (MHz)	CONVERSION LOSS IF FIXED @IF(OUT)=30MHz (dB)			RF (IN) (MHz)	LO (MHz)	IP3 INPUT (dBm)			RF (IN) (MHz)	LO (MHz)	COMPRESSION @RF IN=+14dBm (dB)		
		@LO (dBm)					@LO (dBm)					@LO (dBm)		
		+14	+17	+20			+14	+17	+20			+14	+17	+20
5.0	35.0	9.06	7.85	7.26	10.1	40.1	22.84	26.80	30.39	10.1	40.1	0.31	0.12	0.07
10.0	40.0	8.86	7.64	7.07	49.8	79.8	21.92	25.30	28.79	49.8	79.8	0.37	0.12	0.07
49.8	79.8	8.24	7.17	6.71	89.6	119.6	22.36	25.71	28.52	89.6	119.6	0.18	0.05	0.04
89.6	119.6	8.21	7.14	6.69	129.3	159.3	23.01	26.45	29.20	129.3	159.3	0.29	0.08	0.07
129.3	159.3	8.17	7.11	6.65	169.0	199.0	22.30	26.01	30.20	169.0	199.0	0.20	0.10	0.08
169.0	199.0	8.11	7.09	6.64	208.8	238.8	23.45	27.03	29.60	208.8	238.8	0.34	0.16	0.09
208.8	238.8	7.97	6.92	6.60	248.5	278.5	21.25	25.25	29.52	248.5	278.5	0.21	0.14	0.08
248.5	278.5	8.16	7.07	6.68	288.2	318.2	24.07	29.61	26.31	288.2	318.2	0.47	0.21	0.10
288.2	318.2	7.75	6.90	6.61	328.0	358.0	23.85	27.12	26.04	328.0	358.0	0.50	0.15	0.08
328.0	358.0	7.82	6.98	6.69	367.7	397.7	24.88	27.20	26.09	367.7	397.7	0.56	0.15	0.09
367.7	397.7	7.68	6.96	6.67	407.4	437.4	28.61	24.99	25.00	407.4	437.4	0.61	0.20	0.12
407.4	437.4	7.57	6.90	6.63	447.2	477.2	25.62	22.87	24.16	447.2	477.2	0.52	0.20	0.14
447.2	477.2	7.68	6.98	6.66	486.9	516.9	23.05	22.12	23.62	486.9	516.9	0.56	0.19	0.17
486.9	516.9	7.65	6.98	6.65	526.6	556.6	23.16	22.27	23.47	526.6	556.6	0.57	0.15	0.14
526.6	556.6	7.79	7.16	6.77	566.4	596.4	23.94	23.60	25.13	566.4	596.4	0.58	0.18	0.18
566.4	596.4	7.75	7.15	6.78	606.1	636.1	25.57	25.04	27.42	606.1	636.1	0.67	0.26	0.23
606.1	636.1	7.79	7.10	6.76	645.8	675.8	25.93	24.77	26.79	645.8	675.8	0.68	0.35	0.29
645.8	675.8	7.79	7.07	6.70	685.6	715.6	24.57	24.29	26.17	685.6	715.6	0.72	0.39	0.32
685.6	715.6	7.76	7.07	6.69	725.3	755.3	20.87	22.91	24.99	725.3	755.3	0.79	0.45	0.37
725.3	755.3	7.87	7.18	6.80	765.0	795.0	19.17	21.53	25.10	765.0	795.0	0.79	0.51	0.41
765.0	795.0	7.91	7.26	6.87	804.8	834.8	17.87	19.95	23.59	804.8	834.8	0.84	0.48	0.40
804.8	834.8	8.11	7.46	7.04	844.5	874.5	17.12	19.07	21.85	844.5	874.5	0.85	0.56	0.44
844.5	874.5	8.30	7.63	7.17	884.2	914.2	16.62	18.83	22.08	884.2	914.2	0.78	0.55	0.46
884.2	914.2	8.50	7.77	7.29	924.0	954.0	16.54	18.88	22.15	924.0	954.0	0.72	0.55	0.50
924.0	954.0	8.70	7.89	7.37	963.7	993.7	16.34	18.21	21.66	963.7	993.7	0.53	0.54	0.54
1003.4	1033.4	9.11	8.07	7.41	1003.4	1033.4	16.81	19.21	23.82	1003.4	1033.4	0.57	0.61	0.64
1043.2	1073.2	9.09	7.95	7.32	1043.2	1073.2	17.40	20.92	26.28	1043.2	1073.2	0.64	0.71	0.71
1082.9	1112.9	9.37	8.14	7.43	1082.9	1112.9	17.12	20.98	26.79	1082.9	1112.9	0.56	0.69	0.73
1122.6	1152.6	9.40	8.13	7.38	1122.6	1152.6	17.92	22.26	28.84	1122.6	1152.6	0.55	0.75	0.79
1162.4	1192.4	9.57	8.31	7.53	1162.4	1192.4	18.68	23.24	27.34	1162.4	1192.4	0.49	0.69	0.75
1202.1	1232.1	9.72	8.47	7.67	1202.1	1232.1	19.16	23.23	24.94	1202.1	1232.1	0.45	0.65	0.73
1241.8	1271.8	9.86	8.63	7.82	1241.8	1271.8	18.72	21.75	23.84	1241.8	1271.8	0.44	0.63	0.72
1281.6	1311.6	10.15	8.93	8.12	1281.6	1311.6	17.96	20.46	22.00	1281.6	1311.6	0.39	0.57	0.68
1321.3	1351.3	10.25	9.05	8.25	1321.3	1351.3	17.55	19.50	21.71	1321.3	1351.3	0.47	0.62	0.72
1361.0	1391.0	10.49	9.33	8.57	1361.0	1391.0	17.14	19.30	22.02	1361.0	1391.0	0.53	0.66	0.73
1380.9	1410.9	10.55	9.44	8.66	1380.9	1410.9	17.05	19.22	22.35	1380.9	1410.9	0.56	0.67	0.73
1420.6	1450.6	10.71	9.60	8.87	1420.6	1450.6	17.30	20.43	23.91	1420.6	1450.6	0.65	0.71	0.74
1440.5	1470.5	10.73	9.64	8.93	1440.5	1470.5	17.67	21.45	26.72	1440.5	1470.5	0.72	0.79	0.81
1480.2	1510.2	10.89	9.91	9.23	1480.2	1510.2	18.42	22.63	27.75	1480.2	1510.2	0.83	0.84	0.86
1500.1	1530.1	10.98	10.04	9.40	1500.1	1530.1	19.22	25.03	27.28	1500.1	1530.1	0.84	0.85	0.88

Frequency Mixer

LRMS-2H+

Typical Performance Data

IF (OUT) (MHz)	LO (MHz)	CONVERSION LOSS VS. IF FREQUENCY @RF(IN)=500.1MHz (dB)	IF (OUT) (MHz)	LO (MHz)	CONVERSION LOSS VS. IF FREQUENCY @RF(IN)=10.1MHz (dB)	IF (OUT) (MHz)	LO (MHz)	CONVERSION LOSS VS. IF FREQUENCY @RF(IN)=1000.1MHz (dB)
		@LO (dBm)			@LO (dBm)			@LO (dBm)
		+17			+17			+17
490.0	10.1	7.14	10.0	20.1	6.99	900.0	100.1	7.49
477.7	22.4	7.08	29.8	39.9	6.87	880.2	119.9	7.42
465.4	34.7	7.05	49.6	59.7	7.02	860.4	139.7	7.39
453.1	47.0	7.13	69.3	79.4	7.08	840.7	159.4	7.31
440.8	59.3	7.18	89.1	99.2	7.01	820.9	179.2	7.27
428.5	71.6	7.01	108.9	119.0	7.02	801.1	199.0	7.22
416.2	83.9	7.07	128.7	138.8	7.04	781.3	218.8	7.13
403.8	96.3	7.04	148.4	158.5	7.08	761.6	238.5	7.12
391.5	108.6	7.02	168.2	178.3	7.08	741.8	258.3	7.11
379.2	120.9	6.99	188.0	198.1	7.15	722.0	278.1	7.13
366.9	133.2	6.82	207.8	217.9	7.11	702.2	297.9	7.03
354.6	145.5	6.78	227.6	237.7	7.07	682.4	317.7	7.05
342.3	157.8	6.85	247.3	257.4	7.16	662.7	337.4	7.09
330.0	170.1	6.89	267.1	277.2	7.31	642.9	357.2	7.12
317.7	182.4	6.83	286.9	297.0	7.21	623.1	377.0	7.18
305.4	194.7	6.74	306.7	316.8	7.14	603.3	396.8	7.15
293.1	207.0	6.65	326.4	336.5	7.26	583.6	416.5	7.19
280.8	219.3	6.61	346.2	356.3	7.23	563.8	436.3	7.20
268.5	231.6	6.69	366.0	376.1	7.27	544.0	456.1	7.24
256.2	243.9	6.63	385.8	395.9	7.29	524.2	475.9	7.26
243.8	256.3	6.59	405.6	415.7	7.27	504.4	495.7	7.22
231.5	268.6	6.64	425.3	435.4	7.30	484.7	515.4	7.29
219.2	280.9	6.62	445.1	455.2	7.28	464.9	535.2	7.28
206.9	293.2	6.65	464.9	475.0	7.38	445.1	555.0	7.35
194.6	305.5	6.67	484.7	494.8	7.32	425.3	574.8	7.31
182.3	317.8	6.62	504.4	514.5	7.29	405.6	594.5	7.31
170.0	330.1	6.65	524.2	534.3	7.31	385.8	614.3	7.36
157.7	342.4	6.70	544.0	554.1	7.35	366.0	634.1	7.35
145.4	354.7	6.70	583.6	593.7	7.29	326.4	673.7	7.39
133.1	367.0	6.76	603.3	613.4	7.36	306.7	693.4	7.42
120.8	379.3	6.75	642.9	653.0	7.36	267.1	733.0	7.54
108.5	391.6	6.72	662.7	672.8	7.44	247.3	752.8	7.64
96.2	403.9	6.77	702.2	712.3	7.48	207.8	792.3	7.79
83.8	416.3	6.77	722.0	732.1	7.51	188.0	812.1	7.86
71.5	428.6	6.78	761.6	771.7	7.60	148.4	851.7	8.00
59.2	440.9	6.84	781.3	791.4	7.56	128.7	871.4	8.08
46.9	453.2	6.83	820.9	831.0	7.56	89.1	911.0	8.02
34.6	465.5	6.90	840.7	850.8	7.58	69.3	930.8	8.10
22.3	477.8	6.95	880.2	890.3	7.50	29.8	970.3	8.12
10.0	490.1	6.97	900.0	910.1	7.49	10.0	990.1	8.02



Typical Performance Data

LO (MHz)	LO-RF ISOLATION (dB)			LO-IF ISOLATION (dB)		
	@LO (dBm)			@LO (dBm)		
	+14	+17	+20	+14	+17	+20
5.0	64.63	66.33	68.05	72.73	72.89	71.08
10.0	62.11	63.63	65.24	71.84	68.70	65.74
49.8	49.30	50.68	51.94	61.86	53.37	49.96
89.6	44.13	45.37	46.65	60.65	51.25	46.58
129.3	40.91	42.33	43.56	58.08	47.67	43.25
169.0	38.83	40.06	41.21	58.54	46.33	41.40
208.8	37.11	38.44	39.68	57.83	44.39	41.02
248.5	35.83	37.11	38.28	55.21	43.73	40.36
288.2	34.72	36.10	37.15	54.32	46.57	41.33
328.0	33.95	35.35	36.34	51.61	48.50	40.86
367.7	33.26	34.61	35.66	49.75	49.98	40.97
407.4	32.71	33.97	34.94	45.04	49.89	40.93
447.2	32.29	33.28	34.10	42.01	46.73	40.41
486.9	31.97	32.79	33.48	38.67	43.23	39.92
526.6	31.77	32.77	33.52	36.78	40.45	38.65
566.4	31.63	32.76	33.47	34.28	36.84	37.44
606.1	31.65	32.88	33.50	32.84	35.21	36.16
645.8	31.57	32.55	32.99	31.35	33.89	34.77
685.6	31.37	32.05	32.37	29.98	33.45	34.05
725.3	30.90	31.54	31.89	28.81	32.95	33.56
765.0	30.27	30.90	31.49	27.64	31.91	34.17
804.8	29.60	30.43	31.18	26.94	31.01	34.22
844.5	29.07	29.98	30.97	26.13	29.77	33.73
884.2	28.88	29.88	31.03	25.59	29.06	32.72
924.0	28.84	30.06	31.49	24.99	28.27	31.41
1003.4	29.59	31.23	32.85	24.23	27.04	29.42
1043.2	30.28	32.06	33.43	23.66	26.15	28.13
1082.9	30.92	32.32	33.09	23.33	25.48	27.24
1122.6	31.56	32.48	32.73	22.82	24.71	26.31
1162.4	31.69	31.91	31.73	22.52	24.32	25.81
1202.1	31.06	30.89	30.62	22.16	24.12	25.63
1241.8	30.36	29.90	29.49	21.96	24.41	26.05
1281.6	29.71	29.08	28.68	21.48	24.36	26.44
1321.3	29.00	28.19	27.81	20.92	24.15	26.71
1361.0	28.25	27.41	26.85	20.51	24.03	27.11
1380.9	27.86	27.08	26.80	20.23	23.75	27.18
1420.6	26.95	26.51	26.32	19.53	23.14	27.06
1440.5	26.43	26.02	25.82	19.32	23.06	27.32
1480.2	25.68	25.59	25.63	19.09	22.96	27.43
1500.1	25.08	25.19	25.31	18.74	22.62	27.23

RF (IN) (MHz)	LO (MHz)	RF-IF ISOLATION (dB)		
		@LO (dBm)		
		+14	+17	+20
10.1	40.1	56.55	47.57	49.50
49.8	79.8	38.58	38.61	38.91
89.6	119.6	34.36	34.54	34.57
129.3	159.3	31.81	32.12	32.55
169.0	199.0	30.08	30.67	30.98
208.8	238.8	29.08	29.73	30.07
248.5	278.5	28.39	28.99	29.51
288.2	318.2	28.34	28.89	29.37
328.0	358.0	28.13	29.28	29.81
367.7	397.7	27.83	29.41	30.46
407.4	437.4	27.58	29.45	31.21
447.2	477.2	27.42	29.24	30.84
486.9	516.9	27.77	29.10	29.45
526.6	556.6	27.12	27.94	28.28
566.4	596.4	25.54	26.01	26.64
606.1	636.1	23.51	23.90	24.52
645.8	675.8	21.45	21.57	21.90
685.6	715.6	19.68	19.51	19.53
725.3	755.3	18.19	17.74	17.52
765.0	795.0	16.93	16.39	16.06
804.8	834.8	15.90	15.35	15.03
844.5	874.5	15.07	14.44	14.10
884.2	914.2	14.34	13.65	13.30
924.0	954.0	13.60	13.02	12.68
963.7	993.7	13.04	12.52	12.30
1003.4	1033.4	12.46	12.03	11.79
1043.2	1073.2	11.98	11.72	11.51
1082.9	1112.9	11.71	11.53	11.45
1122.6	1152.6	11.35	11.30	11.33
1162.4	1192.4	11.11	11.13	11.20
1202.1	1232.1	10.91	10.97	11.05
1241.8	1271.8	10.78	10.87	10.88
1281.6	1311.6	10.66	10.78	10.76
1321.3	1351.3	10.48	10.62	10.59
1361.0	1391.0	10.25	10.45	10.42
1380.9	1410.9	10.11	10.34	10.32
1420.6	1450.6	9.87	10.03	9.92
1440.5	1470.5	9.76	9.85	9.77
1480.2	1510.2	9.44	9.43	9.29
1500.1	1530.1	9.26	9.19	9.02

Frequency Mixer

LRMS-2H+

Typical Performance Data

RF (IN) (MHz)	LO (MHz)	RF VSWR (:1)			LO (MHz)	LO VSWR (:1)			IF (OUT) (MHz)	IF VSWR @LO=1000.1MHz (:1)		
		@LO (dBm)				@LO (dBm)				@LO (dBm)		
		+14	+17	+20		+14	+17	+20		+14	+17	+20
5.0	35.0	1.40	1.54	1.67	5.0	1.52	1.95	2.77	5.0	1.31	1.07	1.07
10.0	40.0	1.32	1.49	1.62	10.0	1.31	1.85	2.65	10.0	1.32	1.08	1.06
49.8	79.8	1.03	1.12	1.22	49.7	1.09	1.74	2.66	29.9	3.09	2.25	1.87
89.6	119.6	1.04	1.14	1.24	89.5	1.08	1.62	2.39	49.7	3.00	2.25	1.80
129.3	159.3	1.06	1.15	1.25	129.2	1.10	1.70	2.57	69.4	3.16	2.39	1.90
169.0	199.0	1.07	1.16	1.26	168.9	1.09	1.64	2.43	89.2	3.12	2.33	1.88
208.8	238.8	1.09	1.20	1.30	208.7	1.10	1.65	2.47	109.0	2.95	2.20	1.79
248.5	278.5	1.09	1.17	1.29	248.4	1.12	1.68	2.51	128.8	3.06	2.30	1.88
288.2	318.2	1.10	1.22	1.33	288.2	1.10	1.64	2.43	148.5	3.08	2.32	1.87
328.0	358.0	1.10	1.23	1.33	327.9	1.12	1.70	2.54	168.3	2.94	2.23	1.81
367.7	397.7	1.11	1.24	1.34	367.6	1.10	1.67	2.47	188.1	2.97	2.25	1.84
407.4	437.4	1.13	1.28	1.38	407.4	1.11	1.71	2.53	207.9	3.03	2.32	1.90
447.2	477.2	1.12	1.27	1.38	447.1	1.12	1.73	2.54	227.7	2.95	2.25	1.86
486.9	516.9	1.15	1.28	1.38	486.8	1.12	1.72	2.53	247.4	2.86	2.20	1.82
526.6	556.6	1.14	1.27	1.36	526.6	1.14	1.77	2.60	267.2	2.91	2.25	1.86
566.4	596.4	1.16	1.28	1.37	566.3	1.16	1.77	2.57	287.0	2.91	2.26	1.88
606.1	636.1	1.18	1.32	1.41	606.0	1.18	1.81	2.63	306.8	2.84	2.21	1.85
645.8	675.8	1.19	1.35	1.45	645.8	1.21	1.83	2.63	326.5	2.82	2.21	1.86
685.6	715.6	1.24	1.40	1.50	685.5	1.24	1.85	2.65	346.3	2.85	2.25	1.90
725.3	755.3	1.25	1.41	1.51	725.2	1.27	1.89	2.70	366.1	2.80	2.22	1.88
765.0	795.0	1.26	1.41	1.51	765.0	1.32	1.92	2.71	385.9	2.76	2.17	1.84
804.8	834.8	1.26	1.40	1.49	804.7	1.35	1.97	2.78	405.7	2.74	2.18	1.87
844.5	874.5	1.24	1.36	1.45	844.5	1.38	1.99	2.78	425.4	2.71	2.18	1.88
884.2	914.2	1.22	1.33	1.41	884.2	1.42	2.03	2.81	445.2	2.61	2.10	1.82
924.0	954.0	1.21	1.30	1.38	923.9	1.45	2.04	2.82	465.0	2.64	2.12	1.83
963.7	993.7	1.19	1.27	1.36	963.7	1.49	2.07	2.85	484.8	2.68	2.16	1.87
1003.4	1033.4	1.24	1.31	1.40	1003.4	1.51	2.08	2.85	504.5	2.62	2.12	1.85
1043.2	1073.2	1.31	1.38	1.47	1043.1	1.52	2.07	2.83	524.3	2.52	2.04	1.79
1082.9	1112.9	1.40	1.46	1.53	1082.9	1.57	2.11	2.86	544.1	2.55	2.07	1.82
1122.6	1152.6	1.54	1.58	1.64	1122.6	1.60	2.11	2.84	583.7	2.51	2.05	1.81
1162.4	1192.4	1.68	1.71	1.75	1162.3	1.65	2.15	2.88	603.4	2.49	2.03	1.79
1202.1	1232.1	1.84	1.86	1.89	1202.1	1.73	2.20	2.89	643.0	2.43	1.99	1.78
1241.8	1271.8	2.02	2.01	2.03	1241.8	1.80	2.25	2.93	662.8	2.40	1.96	1.75
1281.6	1311.6	2.21	2.19	2.18	1281.6	1.87	2.29	2.96	702.3	2.46	2.01	1.78
1321.3	1351.3	2.42	2.38	2.35	1321.3	1.92	2.31	2.95	722.1	2.37	1.94	1.72
1361.0	1391.0	2.62	2.58	2.53	1361.0	1.99	2.37	3.01	761.7	2.37	1.93	1.72
1380.9	1410.9	2.71	2.66	2.60	1380.9	2.02	2.37	3.00	781.4	2.34	1.91	1.70
1420.6	1450.6	2.88	2.82	2.73	1420.6	2.07	2.37	2.96	821.0	2.31	1.87	1.65
1440.5	1470.5	2.93	2.87	2.78	1440.5	2.09	2.39	2.99	840.8	2.26	1.84	1.64
1480.2	1510.2	3.04	2.97	2.87	1480.2	2.17	2.42	3.00	880.3	2.23	1.80	1.59
1500.1	1530.1	3.08	3.00	2.90	1500.1	2.20	2.42	2.97	900.1	2.25	1.82	1.61

Harmonics Tables

RF HARMONICS ORDER

	(-dBm)	(-dBc)										
0	-	-	15	40	6	20	17	34	32	39	33	39
1	-	22	+0	28	14	30	27	36	40	42	35	48
2	96	47	43	47	43	49	41	48	54	60	63	60
3	>100	69	54	70	54	70	51	65	55	78	64	72
4	>100	78	80	81	>92	79	77	73	72	74	83	82
5	>100	>92	88	86	88	87	83	83	80	83	82	>92
6	>100	>92	>92	>92	>92	>92	>92	89	>92	91	90	>92
7	>100	>92	>92	>92	>92	>92	>92	>92	>92	>92	>92	>92
8	>100	>92	>92	>92	>92	>92	>92	>92	>92	>92	>92	>92
9	>100	>92	>92	>92	>92	>92	>92	>92	>92	>92	>92	>92
10	>100	>92	>92	>92	>92	>92	>92	>92	>92	>92	>92	>92
	RF CAL	0	1	2	3	4	5	6	7	8	9	10

LO HARMONICS ORDER

Test conditions: RF IN: 500.1 MHz; -1.00 dBm.
 LO IN: 530.01 MHz; +17.00 dBm
 IF OUT: 29.91 MHz; -8.25 dBm

RF HARMONICS ORDER

	(-dBm)	(-dBc)										
0	-	-	25	40	19	38	32	46	48	56	44	57
1	-	22	+0	28	14	32	26	39	47	49	41	51
2	78	44	36	44	35	48	34	44	45	65	55	59
3	>100	54	40	56	41	55	36	50	45	56	52	59
4	>100	54	55	55	54	58	54	57	51	61	74	63
5	>100	76	57	67	52	74	52	64	50	69	54	73
6	>100	81	73	71	77	67	66	66	62	65	57	65
7	>100	82	93	87	74	76	73	78	68	73	64	84
8	>100	94	94	100	86	78	78	74	73	72	70	73
9	>100	>102	101	97	>102	89	80	77	77	79	76	76
10	>100	98	101	>102	98	99	90	82	82	81	79	81
	RF CAL	0	1	2	3	4	5	6	7	8	9	10

LO HARMONICS ORDER

Test conditions: RF IN: 500.1 MHz; 9.00 dBm.
 LO IN: 530.01 MHz; +17.00 dBm
 IF OUT: 29.91 MHz; 1.7 dBm

- Notes: 1. All Harmonics are in (dBc) relative to IF OUTPUT.
 2. + entry denotes harmonics are in (dBc) above IF OUTPUT.
 3. RF Cal represent the Harmonics level of the RF input signal to the mixer.

REV. X2
 LRMS-2H+
 100817
 Page 5 of 5




IF/RF MICROWAVE COMPONENTS • ISO 9001 ISO 14001 AS 9100 CERTIFIED • RoHS compliant
 P.O. Box 350166, Brooklyn, New York 11235-0006 (718) 934-4500 Fax (718) 332-4661




The Design Engineers Search Engine finds the model you need, Instantly • For detailed performance specs & shopping online see [minicircuits.com](http://www.minicircuits.com)

Typical Performance Curves


Conversion Loss @ IF=30MHz




Conversion Loss vs. IF @ RF=500.1MHz




Conversion Loss vs. IF @ RF=10.1MHz




Conversion Loss vs. IF @ RF=1000.1MHz



IP3 Input




Compression @ RF IN=+14dBm




Typical Performance Curves


LO-RF Isolation




LO-IF Isolation




RF-IF Isolation




RF VSWR



LO VSWR



IF VSWR



Harmonics Tables

RF HARMONICS ORDER

	(-dBm)	(-dBc)										
0	-	-	15	40	6	20	17	34	32	39	33	39
1	-	22	+0	28	14	30	27	36	40	42	35	48
2	96	47	43	47	43	49	41	48	54	60	63	60
3	>100	69	54	70	54	70	51	65	55	78	64	72
4	>100	78	80	81	>92	79	77	73	72	74	83	82
5	>100	>92	88	86	88	87	83	83	80	83	82	>92
6	>100	>92	>92	>92	>92	>92	>92	89	>92	91	90	>92
7	>100	>92	>92	>92	>92	>92	>92	>92	>92	>92	>92	>92
8	>100	>92	>92	>92	>92	>92	>92	>92	>92	>92	>92	>92
9	>100	>92	>92	>92	>92	>92	>92	>92	>92	>92	>92	>92
10	>100	>92	>92	>92	>92	>92	>92	>92	>92	>92	>92	>92
	RF CAL	0	1	2	3	4	5	6	7	8	9	10

LO HARMONICS ORDER

Test conditions: RF IN: 500.1 MHz; -1.00 dBm.
 LO IN: 530.01 MHz; +17.00 dBm
 IF OUT: 29.91 MHz; -8.25 dBm

RF HARMONICS ORDER

	(-dBm)	(-dBc)										
0	-	-	25	40	19	38	32	46	48	56	44	57
1	-	22	+0	28	14	32	26	39	47	49	41	51
2	78	44	36	44	35	48	34	44	45	65	55	59
3	>100	54	40	56	41	55	36	50	45	56	52	59
4	>100	54	55	55	54	58	54	57	51	61	74	63
5	>100	76	57	67	52	74	52	64	50	69	54	73
6	>100	81	73	71	77	67	66	66	62	65	57	65
7	>100	82	93	87	74	76	73	78	68	73	64	84
8	>100	94	94	100	86	78	78	74	73	72	70	73
9	>100	>102	101	97	>102	89	80	77	77	79	76	76
10	>100	98	101	>102	98	99	90	82	82	81	79	81
	RF CAL	0	1	2	3	4	5	6	7	8	9	10

LO HARMONICS ORDER

Test conditions: RF IN: 500.1 MHz; 9.00 dBm.
 LO IN: 530.01 MHz; +17.00 dBm
 IF OUT: 29.91 MHz; 1.7 dBm

- Notes: 1. All Harmonics are in (dBc) relative to IF OUTPUT.
 2. + entry denotes harmonics are in (dBc) above IF OUTPUT.
 3. RF Cal represent the Harmonics level of the RF input signal to the mixer.

REV. X2
 LRMS-2H+
 100817
 Page 3 of 3



IF/RF MICROWAVE COMPONENTS • ISO 9001 ISO 14001 AS 9100 CERTIFIED • RoHS compliant
 P.O. Box 350166, Brooklyn, New York 11235-0006 (718) 934-4500 Fax (718) 332-4661




The Design Engineers Search Engine finds the model you need, Instantly • For detailed performance specs & shopping online see [minicircuits.com](http://www.minicircuits.com)

Case Style


QQQ

QQQ130 (non-waterproof)
QQQ828 (washable)

Outline Dimensions



PCB Land Pattern



Suggested Layout,
Tolerance to be within $\pm .002$

CASE#	A	B	C	D	E	F	G	H	J	K	L	M	WT, GRAM
QQQ130	.400 (10.16)	.31 (7.87)	.200 (5.08)	.10 (2.54)	.010 (.25)	.100 (2.54)	.050 (1.27)	.420 (10.67)	.120 (3.05)	.060 (1.52)	.100 (2.54)	.020 (.51)	.55
QQQ828			.050 (1.27)										.20

Dimensions are in inches (mm). Tolerances: 2 Pl. $\pm .01$; 3 Pl. $\pm .005$

Notes:

- Case material: Ceramic.
- Termination finish:
 - For RoHS Case Styles: Tin plate over Nickel plate.
 - For RoHS-5 Case Styles: Tin-Lead plate.




INTERNET <http://www.minicircuits.com>

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661

Distribution Centers NORTH AMERICA 800-654-7949 • 417-335-5935 • Fax 417-335-5945 • EUROPE 44-1252-832600 • Fax 44-1252-837010

Mini-Circuits ISO 9001 & ISO 14001 Certified

Tape & Reel Packaging TR-F10



Tape Width, mm	Device Cavity Pitch, mm	Reel Size, inches	Devices per Reel
24	16	7	10,20,50,100
		13	200,500

Mini-Circuits carrier tape materials provide protection from ESD (Electro-Static Discharge) during handling and transportation. Tapes are static dissipative and comply with industry standards EIA-481/EIA-541.

Go to: www.minicircuits.com/pages/pdfs/tape.pdf

Note: Please consult individual model data sheet to determine device per reel availability.




INTERNET <http://www.minicircuits.com>

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661

Distribution Centers NORTH AMERICA 800-654-7949 • 417-335-5935 • Fax 417-335-5945 • EUROPE 44-1252-832600 • Fax 44-1252-837010

Mini-Circuits ISO 9001 & ISO 14001 Certified


THIRD ANGLE PROJECTION



REVISIONS

REV	ECN No.	DESCRIPTION	DATE	DR	AUTH
OR	M82272	NEW RELEASE	08/02/02	AV	DJ
A	M102713	UPDATED NOTES	01/14/06	GF	IL

SUGGESTED MOUNTING CONFIGURATION FOR QQQ569 CASE STYLE, "w" PIN CONNECTION



NOTES: 1. TRACE WIDTH IS SHOWN FOR ROGERS R04350B WITH DIELECTRIC THICKNESS 0.030" ± 0.002"; COPPER: 1/2 OZ. EACH SIDE. FOR OTHER MATERIALS TRACE WIDTH MAY NEED TO BE MODIFIED.

2. BOTTOM SIDE OF THE PCB IS CONTINUOUS GROUND PLANE.



DENOTES PCB COPPER LAYOUT WITH SMOBC (SOLDER MASK OVER BARE COPPER)



DENOTES COPPER LAND PATTERN FREE OF SOLDER MASK

UNLESS OTHERWISE SPECIFIED

INITIALS DATE

DIMENSIONS ARE IN INCHES


DRAWN AV 07/19/02

TOLERANCES ON:
2 PL DECIMALS ±
3 PL DECIMALS ± .005

CHECKED WL 08/02/02

ANGLES ±
FRACTIONS ±

APPROVED DJ 08/02/02



THIS DOCUMENT AND ITS CONTENTS ARE THE PROPERTY OF MINI-CIRCUITS. EXCEPT FOR USE EXPRESSLY GRANTED, IN WRITING, TO ITS VENDORS, VENDEE AND THE UNITED STATES GOVERNMENT, MINI-CIRCUITS RESERVES ALL PROPRIETARY DESIGN, USE, MANUFACTURING AND REPRODUCTION RIGHTS THERETO. THESE CONTENTS SHALL NOT BE USED, DUPLICATED OR DISCLOSED TO ANY OUTSIDE PARTY, IN WHOLE OR IN PART, WITHOUT WRITTEN PERMISSION OF MINI-CIRCUITS.




Mini-Circuits®

13 Neptune Avenue
Brooklyn NY 11235


PL, w, QQQ569, LRMS-J, TB-44

SIZE A	CODE IDENT 15542	DRAWING NO: 98-PL-083	REV: A
FILE: 98PL083	SCALE: 6:1	SHEET: 1 OF 1	

Evaluation Board and Circuit




TB-44+



Schematic Diagram

Notes:

1. SMA Female connectors.
2. PCB Material: Rogers R04350 or equivalent,
Dielectric Constant=3.5, Thickness=.030 inch.

 Mini-Circuits®

All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

Specification	Test/Inspection Condition	Reference/Spec
Operating Temperature	-40° to 85°C Ambient Environment	Individual Model Data Sheet
Storage Temperature	-55° to 100° C Ambient Environment	Individual Model Data Sheet
Humidity	90 to 95% RH, 240 hours, 50°C	MIL-STD-202, Method 103, Condition A, Except 50°C and end-point electrical test done within 12 hours
Thermal Shock	-55° to 100°C, 100 cycles	MIL-STD-202, Method 107, Condition A-3, except +100°C
Solder Reflow Heat	Sn-Pb Eutetic Process: 225°C peak Pb-Free Process 245° - 250°C peak	J-STD-020, Table 4-1, 4-2 and 5-2, Figure 5-1
Solderability	10X Magnification	J-STD-002, 95% Coverage
Vibration (High Frequency)	20g peak, 10-2000 Hz, 12 times in each of three perpendicular directions (total 36)	MIL-STD-202, Method 204, Condition D
Mechanical Shock	50g, 11 ms, 1/2-sine, 18 shocks: 3 each direction, each of 3 axes	MIL-STD-202, Method 213, Condition A
Marking Resistance to Solvents	Isopropyl alcohol + mineral spirits at 25°C; terpene defluxer at 25°C; distilled water + proylene glycol monomethyl ether + monoethanolamine at 63°C to 70°C	MIL-STD-202, Method 215