

Frequency Mixer

LRMS-ED6047/1

Level 7 (LO Power +7 dBm)

Important Note

This model has been designed, built and tested in our engineering department. Performance data represents model capability. At present it is a non-catalog model. On request, we can supply a final specification sheet, part number and price/delivery information.



Please click "Back", and then click "Contact Us" for Applications support.

CASE STYLE : 99-01-532

ELECTRICAL SPECIFICATIONS 50Ω @ +25°C					
Parameter		Min.	Typ.	Max.	Units
Frequency	LO (f _L to f _U)	1		675	MHz
	RF (f _L to f _U)	1		675	MHz
	IF	1		510	MHz
Conversion Loss	mid band		6.0		dB
	Total Range		7.0		dB
LO-RF Isolation	Low Range		63		dB
	Mid Range		43		dB
	Upper Range		36		dB
LO-IF Isolation	Low Range		50		dB
	Mid Range		35		dB
	Upper Range		26		dB

Note: Low Range = [f_L to 10f_L]
mid band = [2f_L to f_U/2]

Mid Range = [10f_L to f_U/2]

Upper Range = [f_U/2 to f_U]

MAXIMUM RATINGS	
Operating Temperature	-40°C to 85°C
Storage Temperature	-55°C to 100°C

PIN CONNECTIONS	
LO	6
RF	3
IF	2
GROUND	1, 4, 5

Frequency Mixer

LRMS-ED6047/1

Typical Performance Data

RF (MHz)	LO (MHz)	CONVERSION LOSS (dB)			LO (MHz)	LO-RF ISOLATION (dB)			LO-IF ISOLATION (dB)		
		@LO (dBm)				@LO (dBm)			@LO (dBm)		
		+4	+7	+10		+4	+7	+10	+4	+7	+10
1.0	31.0	7.36	6.86	6.66	31.0	62.4	63.9	65.3	53.2	50.3	48.8
1.5	31.5	6.98	6.48	6.28	31.5	62.5	63.9	64.9	53.2	50.0	48.8
2.0	32.0	6.81	6.31	6.11	32.0	62.1	63.8	64.9	52.8	50.0	48.7
2.5	32.5	6.72	6.22	6.02	32.5	62.0	64.0	64.8	52.9	49.8	48.5
5.0	35.0	6.40	6.00	5.80	35.0	61.7	63.3	64.2	52.4	49.4	47.9
10.0	40.0	6.31	5.91	5.81	40.0	60.7	62.3	63.1	51.4	48.3	46.8
20.0	50.0	6.37	5.97	5.77	50.0	59.0	60.2	61.3	49.4	46.4	45.1
75.1	105.1	6.34	5.94	5.84	105.1	51.5	52.6	53.6	44.3	41.2	39.8
150.1	180.1	6.37	5.97	5.87	180.1	46.1	47.5	48.3	41.1	37.9	36.3
220.0	250.0	6.40	6.10	5.90	250.0	43.1	43.9	44.7	38.3	35.9	34.4
225.1	255.1	6.35	6.05	5.95	255.1	42.9	43.7	44.3	38.1	35.7	34.1
250.0	280.0	6.41	6.01	5.91	280.0	42.3	43.1	43.6	37.0	34.9	33.2
300.1	330.1	6.44	6.04	5.84	330.1	40.1	40.8	41.5	34.7	33.4	32.3
375.1	405.1	6.55	6.15	6.05	405.1	38.8	39.3	39.8	31.4	31.2	30.4
450.1	480.1	6.55	6.25	6.05	480.1	37.5	38.4	38.9	28.3	28.5	28.2
470.0	500.0	6.55	6.25	6.05	500.0	37.1	37.9	38.2	27.6	27.9	27.5
500.0	530.0	6.53	6.23	6.13	530.0	36.5	37.2	37.6	26.8	26.9	26.5
525.1	555.1	6.54	6.24	6.14	555.1	36.0	36.8	37.3	26.5	26.4	26.1
600.1	630.1	6.92	6.42	6.32	630.1	34.3	35.7	36.5	25.1	25.6	25.1
675.1	705.1	7.19	6.79	6.49	705.1	32.8	34.6	35.5	23.5	25.0	24.8

Frequency Mixer


LRMS-ED6047/1

Typical Performance Data


RF/LO (MHz)	RF VSWR (:1)			LO VSWR (:1)			IF (MHz)	IF VSWR (:1)		
	@LO (dBm)			@LO (dBm)				@LO (dBm)		
	+4	+7	+10	+4	+7	+10		+4	+7	+10
31.0	1.48	2.40	3.26	1.57	1.59	1.60	1.0	1.77	1.49	1.35
31.5	1.48	2.43	3.26	1.41	1.42	1.44	5.0	1.75	1.47	1.33
32.0	1.49	2.37	3.26	1.33	1.33	1.35	10.0	1.75	1.46	1.33
32.5	1.48	2.43	3.26	1.27	1.28	1.30	30.1	1.74	1.46	1.32
35.0	1.47	2.43	3.32	1.16	1.15	1.17	60.1	1.74	1.46	1.32
40.0	1.48	2.43	3.26	1.11	1.07	1.11	90.1	1.73	1.45	1.32
50.0	1.48	2.43	3.32	1.08	1.04	1.09	120.1	1.69	1.43	1.31
105.1	1.47	2.37	3.32	1.04	1.08	1.13	150.1	1.66	1.42	1.30
180.1	1.48	2.46	3.26	1.06	1.09	1.14	180.1	1.66	1.41	1.30
250.0	1.53	2.49	3.38	1.02	1.10	1.15	210.1	1.66	1.41	1.31
255.1	1.54	2.49	3.38	1.01	1.10	1.15	240.1	1.65	1.41	1.30
280.0	1.54	2.43	3.26	1.02	1.13	1.18	270.1	1.65	1.41	1.31
330.1	1.59	2.55	3.50	1.05	1.16	1.22	300.1	1.65	1.43	1.32
405.1	1.71	2.65	3.50	1.09	1.19	1.25	330.0	1.66	1.44	1.34
480.1	1.74	2.72	3.50	1.23	1.32	1.38	360.0	1.70	1.46	1.35
500.0	1.81	2.80	3.64	1.28	1.39	1.45	390.0	1.70	1.48	1.37
530.0	1.82	2.80	3.79	1.34	1.46	1.52	420.0	1.71	1.48	1.40
555.1	1.87	2.76	3.50	1.37	1.48	1.55	450.0	1.71	1.50	1.41
630.1	1.96	2.92	3.71	1.43	1.57	1.64	480.0	1.74	1.53	1.44
705.1	2.06	3.06	4.03	1.50	1.62	1.70	510.0	1.73	1.51	1.43

Typical Performance Curves


Conversion Loss




LO-RF Isolation




LO-IF Isolation




RF VSWR




LO VSWR



IF VSWR




THIRD ANGLE PROJECTION



REVISIONS

REV	ECN No.	DESCRIPTION	DATE	DR	AUTH
OR	M82272	NEW RELEASE	08/02/02	AV	DJ
A	M102713	UPDATED NOTES	01/14/06	GF	IL

SUGGESTED MOUNTING CONFIGURATION FOR QQQ569 CASE STYLE, "w" PIN CONNECTION



NOTES: 1. TRACE WIDTH IS SHOWN FOR ROGERS RO4350B WITH DIELECTRIC THICKNESS 0.030" $\pm$ 0.002"; COPPER: 1/2 OZ. EACH SIDE. FOR OTHER MATERIALS TRACE WIDTH MAY NEED TO BE MODIFIED.

2. BOTTOM SIDE OF THE PCB IS CONTINUOUS GROUND PLANE.



DENOTES PCB COPPER LAYOUT WITH SMOBC (SOLDER MASK OVER BARE COPPER)



DENOTES COPPER LAND PATTERN FREE OF SOLDER MASK

UNLESS OTHERWISE SPECIFIED

INITIALS

DATE

DIMENSIONS ARE IN INCHES

DRAWN

AV

07/19/02

TOLERANCES ON:

CHECKED

WL

08/02/02

2 PL DECIMALS $\pm$

APPROVED

DJ

08/02/02

3 PL DECIMALS $\pm$.005

ANGLES $\pm$

FRACTIONS $\pm$

Mini-Circuits®

THIS DOCUMENT AND ITS CONTENTS ARE THE PROPERTY OF MINI-CIRCUITS. EXCEPT FOR USE EXPRESSLY GRANTED, IN WRITING, TO ITS VENDORS, VENDEE AND THE UNITED STATES GOVERNMENT, MINI-CIRCUITS RESERVES ALL PROPRIETARY DESIGN, USE, MANUFACTURING AND REPRODUCTION RIGHTS THERETO. THESE CONTENTS SHALL NOT BE USED, DUPLICATED OR DISCLOSED TO ANY OUTSIDE PARTY, IN WHOLE OR IN PART, WITHOUT WRITTEN PERMISSION OF MINI-CIRCUITS.

ASHEETA1.DWG REV:A DATE:01/12/95



Mini-Circuits®

13 Neptune Avenue
Brooklyn NY 11235

PL, w, QQQ569, LRMS-J, TB-44

SIZE

A

CODE IDENT

15542

DRAWING NO:

98-PL-083

REV:

A

FILE: 98PL083


SCALE:

6:1


SHEET:

1 OF 1

Evaluation Board and Circuit



TB-44+



Schematic Diagram

Notes:

1. SMA Female connectors.
2. PCB Material: Rogers R04350 or equivalent,
Dielectric Constant=3.5, Thickness=.030 inch.

 Mini-Circuits®



All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

Specification	Test/Inspection Condition	Reference/Spec
Operating Temperature	-40° to 85°C Ambient Environment	Individual Model Data Sheet
Storage Temperature	-55° to 100° C Ambient Environment	Individual Model Data Sheet
Humidity	90 to 95% RH, 240 hours, 50°C	MIL-STD-202, Method 103, Condition A, Except 50°C and end-point electrical test done within 12 hours
Thermal Shock	-55° to 100°C, 100 cycles	MIL-STD-202, Method 107, Condition A-3, except +100°C
Solder Reflow Heat	Sn-Pb Eutetic Process: 225°C peak Pb-Free Process 245° - 250°C peak	J-STD-020, Table 4-1, 4-2 and 5-2, Figure 5-1
Solderability	10X Magnification	J-STD-002, 95% Coverage
Vibration (High Frequency)	20g peak, 10-2000 Hz, 12 times in each of three perpendicular directions (total 36)	MIL-STD-202, Method 204, Condition D
Mechanical Shock	50g, 11 ms, 1/2-sine, 18 shocks: 3 each direction, each of 3 axes	MIL-STD-202, Method 213, Condition A
Marking Resistance to Solvents	Isopropyl alcohol + mineral spirits at 25°C; terpene defluxer at 25°C; distilled water + proylene glycol monomethyl ether + monoethanolamine at 63°C to 70°C	MIL-STD-202, Method 215