




Typical Performance Data

FREQ. (MHz)	ON	INSERTION LOSS (dB)		OFF ISOLATION (dB)		VSWR		
		IN-OUT		IN-OUT		IN	OUT	OFF
		$\overline{x}$	σ	$\overline{x}$	σ			
0.03	0.46	0.01	90.55	2.57	1.12	1.12	5.61	
0.10	0.47	0.01	89.66	3.24	1.12	1.12	5.61	
1.00	0.54	0.01	102.38	5.74	1.12	1.12	5.41	
10.00	0.54	0.01	93.55	1.66	1.11	1.11	5.39	
20.00	0.56	0.01	88.66	1.05	1.11	1.11	5.37	
60.00	0.58	0.01	79.56	0.62	1.10	1.10	5.31	
100.00	0.59	0.01	74.67	0.50	1.10	1.10	5.27	
400.00	0.65	0.01	61.97	0.33	1.11	1.10	5.19	
600.00	0.68	0.01	58.10	0.29	1.11	1.10	5.22	
1000.00	0.71	0.01	53.36	0.28	1.09	1.12	5.23	
1400.00	0.75	0.01	49.71	0.24	1.07	1.17	5.10	
1600.00	0.78	0.01	48.08	0.24	1.09	1.20	4.98	
1800.00	0.81	0.01	46.53	0.22	1.12	1.23	4.85	
2000.00	0.85	0.01	45.10	0.21	1.14	1.27	4.75	
2500.00	0.90	0.01	42.61	0.21	1.16	1.32	4.80	
3000.00	0.96	0.01	39.91	0.19	1.11	1.22	5.06	
3500.00	1.05	0.01	38.53	0.20	1.03	1.16	5.26	
4000.00	1.31	0.02	36.88	0.20	1.10	1.20	5.04	
4250.00	1.45	0.02	35.73	0.18	1.15	1.27	4.86	
4500.00	1.57	0.02	34.73	0.14	1.18	1.33	4.74	



Notes

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
- C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp






Switch SPDT , 50W

M3SW-2-50DR+


Typical Performance Data

FREQUENCY (MHz)	INSERTION LOSS	ISOLATION	VSWR		
	(dB) IN-OUT , "ON"	(dB) IN-OUT , "OFF"	IN	(:1) OUT , "ON"	OUT , "OFF"
0.03	0.46	90.55	1.12	1.12	5.61
0.1	0.47	89.66	1.12	1.12	5.61
0.5	0.53	86.66	1.12	1.12	5.48
1	0.54	102.38	1.12	1.12	5.41
2	0.53	102.16	1.12	1.12	5.40
4	0.53	98.56	1.11	1.11	5.39
6	0.53	97.30	1.11	1.11	5.39
8	0.54	94.00	1.11	1.11	5.38
10	0.54	93.55	1.11	1.11	5.39
20	0.56	88.66	1.11	1.11	5.37
40	0.57	83.41	1.10	1.10	5.34
60	0.58	79.56	1.10	1.10	5.31
80	0.58	76.94	1.10	1.10	5.29
100	0.59	74.67	1.10	1.10	5.27
200	0.62	68.29	1.11	1.10	5.23
400	0.65	61.97	1.11	1.10	5.19
500	0.66	59.86	1.11	1.10	5.20
600	0.68	58.10	1.11	1.10	5.22
800	0.69	55.68	1.10	1.10	5.25
1000	0.71	53.36	1.09	1.12	5.23
1200	0.73	51.48	1.08	1.14	5.19
1400	0.75	49.71	1.07	1.17	5.10
1600	0.78	48.08	1.09	1.20	4.98
1800	0.81	46.53	1.12	1.23	4.85
2000	0.85	45.10	1.14	1.27	4.75
2250	0.88	43.81	1.16	1.31	4.72
2500	0.90	42.61	1.16	1.32	4.80
2750	0.92	41.19	1.14	1.28	4.92
3000	0.96	39.91	1.11	1.22	5.06
3250	0.99	39.51	1.07	1.19	5.23
3500	1.05	38.53	1.03	1.16	5.26
3750	1.16	37.71	1.04	1.16	5.19
4000	1.31	36.88	1.10	1.20	5.04
4250	1.45	35.73	1.15	1.27	4.86
4500	1.57	34.73	1.18	1.33	4.74


Typical Performance Curves



Outline Dimensions



PCB Land Pattern



Suggested Layout,
Tolerance to be within $\pm .002$

CASE #	A	B	C	D	E	F	G	H	J	K	L	M	N
DL805	.128 (3.25)	.128 (3.25)	.035 (0.90)	.008 (0.20)	.080 (2.03)	.047 (1.19)	.013 (0.33)	-- --	.014 (0.36)	.026 (0.66)	.158 (4.01)	.158 (4.01)	.084 (2.13)

CASE #	P	Q	R	S	T	WT. GRAM
DL805	.013 (0.33)	.030 (0.76)	.048 (1.22)	.020 (0.51)	.025 (0.64)	.02

Dimensions are in inches (mm). Tolerances: 2 Pl. $\pm .01$; 3Pl. $\pm .004$

Notes:

- Case material: Plastic.
- Termination finish:

For RoHS Case Styles: Tin-Silver alloy plate over Nickel barrier or Matte-Tin. All models, (+) suffix.
See model data sheet.

For RoHS-5 Case Styles: Tin-Lead plate. All models, no (+) suffix.



P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site




The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: www.minicircuits.com

RF/IF MICROWAVE COMPONENTS

Tape & Reel Packaging TR-F58

DEVICE ORIENTATION IN T&R



Tape Width, mm	Device Cavity Pitch, mm	Reel Size, inches	Devices per Reel
12	8	7	1000
		13	2000, 4000

Mini-Circuits carrier tape materials provide protection from ESD (Electro-Static Discharge) during handling and transportation. Tapes are static dissipative and comply with industry standards EIA-481/EIA-541.

Go to: www.minicircuits.com/pages/pdfs/tape.pdf




INTERNET <http://www.minicircuits.com>

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661


Distribution Centers NORTH AMERICA 800-654-7949 • 417-335-5935 • Fax 417-335-5945 • EUROPE 44-1252-832600 • Fax 44-1252-837010

Mini-Circuits ISO 9001 & ISO 14001 Certified



REVISIONS					
REV	ECN No.	DESCRIPTION	DATE	DR	AUTH
OR	M82940	NEW RELEASE	11/15/02	MMG	MM
A	M91639	REMOVED NOTE 2	04/14/04	AV	DJ
B	M102713	CHNG DESCRIPTION, ADDED "...WITH SMOBC"	01/16/06	GF	IL
C	M175851	UPDATED DESCRIPTION INFORMATION	08/09/19	CA	IL

**SUGGESTED MOUNTING CONFIGURATION
FOR DL805 CASE STYLE, "08SW06" PIN CONNECTION.**



CAPACITORS C1 & C2: 0603 SIZE.

- NOTES: 1. TRACE WIDTH IS SHOWN FOR ROGERS RO4350B WITH DIELECTRIC THICKNESS 0.020" $\pm$ 0.0015"; COPPER: 1/2 OZ. EACH SIDE. FOR OTHER MATERIALS TRACE WIDTH MAY NEED TO BE MODIFIED.
2. CHIP COMPONENTS FOOT PRINTS SHOWN FOR REFERENCE, FOR COMPONENT VALUES REFER TO TB-M3SW-250DRA+/TB-M3SWA250DRB+.
3. BOTTOM SIDE OF THE PCB IS CONTINUOUS GROUND PLANE.



DENOTES PCB COPPER LAYOUT WITH SMOBC (SOLDER MASK OVER BARE COPPER)



DENOTES COPPER LAND PATTERN FREE OF SOLDER MASK

UNLESS OTHERWISE SPECIFIED	INITIALS	DATE
DIMENSIONS ARE IN INCHES	DRAWN	MMG 11/13/02
TOLERANCES ON:	CHECKED	AV 11/15/02
2 PL DECIMALS $\pm$	APPROVED	MM 11/15/02
3 PL DECIMALS $\pm$.005		
ANGLES $\pm$ 1°		
FRACTIONS $\pm$		



Mini-Circuits® 13 Neptune Avenue
Brooklyn NY 11235



PL, DL805, TB-M3SW-250DRA+/TB-M3SWA250DRB+

SIZE	CODE IDENT	DRAWING NO:	REV:
A	15542	98-PL-120	C
FILE:	98PL120	SCALE:	8:1
		SHEET:	1 OF 1

THIS DOCUMENT AND ITS CONTENTS ARE THE PROPERTY OF MINI-CIRCUITS. EXCEPT FOR USE EXPRESSLY GRANTED, IN WRITING, TO ITS VENDORS, VENDEE AND THE UNITED STATES GOVERNMENT, MINI-CIRCUITS RESERVES ALL PROPRIETARY DESIGN, USE, MANUFACTURING AND REPRODUCTION RIGHTS THERETO. THESE CONTENTS SHALL NOT BE USED, DUPLICATED OR DISCLOSED TO ANY OUTSIDE PARTY, IN WHOLE OR IN PART, WITHOUT WRITTEN PERMISSION OF MINI-CIRCUITS.

ASHEETA1.DWG REV:A DATE:01/12/95

Evaluation Board and Circuit



Schematic Diagram

ITEM	DESCRIPTION	SIZE
DUT	MCL SWITCH	3.25X3.25 MM
C1,C2	Capacitor 10 pF	0603
D1,D2	Diod Zener 5.6V	SOT-123
R1,R2	Resistor 11.5 Ohm	0603
R3	Resistor 100 Ohm	

Notes:

1. SMA Female connectors.
2. PCB Material: Rogers R04350 or equivalent,
Dielectric Constant=3.5, Thickness=.020 inch.

 **Mini-Circuits®**



All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

Specification	Test/Inspection Condition	Reference/Spec
Operating Temperature	-55° to 100°C Ambient Environment	Individual Model Data Sheet
Storage Temperature	-55° to 100° C Ambient Environment	Individual Model Data Sheet
Temperature Cycling	-55° to 100°C, 100 cycles	MIL-STD-883, Method 1010, Condition B, except 100°C
Solder Reflow Profile	Sn-Pb Eutetic Process: 240°C peak PB-Free Process: 250°C peak	J-STD-020, table 4-1,4-2 and 5-2; figure 5-1
Vibration (Variable Frequency)	50g peak	MIL-STD-883, Method 2007, Condition B
Mechanical Shock	1.5Kg, 0.5 ms, 5 shock pulses, Y1 direction only	MIL-STD-883, Method 2002, Condition B, except Y1 direction only
Moisture Sensitivity: Level 1	Bake at 125°C for 24 hours. Soak at 85°C/85%RH for 168 hours Reflow 3 cycles at 260°C peak	J-STD-020
Marking Resistance to Solvents	Isopropyl alcohol + mineral spirits at 25°C; terpene defluxer at 25°C; distilled water + proylene glycol monomethyl ether + monoethanolamine at 63°C to 70°C	MIL-STD-202, Method 215