



Mini-Circuits

MMIC SURFACE MOUNT

Monolithic Amplifier

MAR-1SM+

50 Ω DC to 1 GHz

FEATURES

- Wideband, DC to 1 GHz
- Exact Footprint Substitute for Avago's MSA-0186
- Internally Matched to 50 Ω
- Low Current, 17 mA
- Unconditionally Stable
- Protected by US Patent, 6,943,629



Generic photo used for illustration purposes only

CASE STYLE: WW107

+RoHS Compliant

The +Suffix identifies RoHS Compliance.
See our website for methodologies and qualifications



APPLICATIONS

- Cellular
- Instrumentation
- VHF/UHF Receivers/Transmitters

PRODUCT OVERVIEW

MAR-1SM+ (RoHS compliant) is a wideband amplifier offering high dynamic range. It has repeatable performance from lot to lot. It is enclosed in a Micro-X package. MAR-1SM+ uses Darlington configuration and is fabricated using InGaP HBT technology. Expected MTTF is 14,000 years at +85°C case temperature.

SIMPLIFIED SCHEMATIC AND PIN DESCRIPTION



| Function | Pin Number | Description |
|------------------|------------|--|
| RF-IN | 1 | RF input pin. This pin requires the use of an external DC blocking capacitor chosen for the frequency of operation. |
| RF-OUT and DC-IN | 3 | RF output and bias pin. DC voltage is present on this pin; therefore a DC blocking capacitor is necessary for proper operation. An RF choke is needed to feed DC bias without loss of RF signal due to the bias connection, as shown in "Recommended Application Circuit". |
| GND | 2,4 | Connections to ground. Use via holes as shown in "Suggested Layout for PCB Design" to reduce ground path inductance for best performance. |

Mini-Circuits



MMIC SURFACE MOUNT

Monolithic Amplifier

MAR-1SM+

Mini-Circuits

50Ω DC to 1 GHz

ELECTRICAL SPECIFICATIONS AT +25°C AND 17 mA UNLESS NOTED OTHERWISE

| Parameter | Conditions (GHz) | Min. | Typ. | Max. | Units |
|---|------------------|-----------------|--------------|------|-------|
| Frequency Range ¹ | | DC | | 1 | GHz |
| Gain | 0.1 1 | 15 ² | 17.8 16.5 | | dB |
| Input Return Loss | DC - 1 | | 17.5 | | dB |
| Output Return Loss | DC - 1 | | 21 | | dB |
| Output Power @ 1 dB Compression | 0.5 | | +2.5 | | dBm |
| Output IP3 | 0.5 | | +14 | | dBm |
| Noise Figure | 0.5 | | 3.3 | | dB |
| Recommended Device Operating Current | | | 17 | | mA |
| Device Operating Voltage | | | +5.0 | | V |
| Device Voltage Variation vs. Temperature at 17 mA | | | -2.9 | | mV/°C |
| Device Voltage Variation vs. Current at +25°C | | | 15.0 | | mV/mA |
| Thermal Resistance, Junction-to-Case ³ | | | 208 | | °C/W |

1. Guaranteed specification DC-1 GHz. Low frequency cut off determined by external coupling capacitors.

2. Full temperature range.

3. Case is defined as ground leads.

ABSOLUTE MAXIMUM RATINGS

| Parameter | Ratings |
|-----------------------|-----------------|
| Operating Temperature | -40°C to +85°C |
| Storage Temperature | -55°C to +100°C |
| Operating Current | 40 mA |
| Power Dissipation | 200 mW |
| Input Power | +13 dBm |

Permanent damage may occur if any of these limits are exceeded. These ratings are not intended for continuous normal operation.





Mini-Circuits


MMIC SURFACE MOUNT

Monolithic Amplifier

MAR-1SM+

50Ω DC to 1 GHz


RECOMMENDED APPLICATION CIRCUIT



Test Board includes case, connectors, and components (in bold) soldered to PCB

| R BIAS | |
|--------|--|
| Vcc | "1%" Res. Values (Ohms) for Optimum Biasing |
| 7 | 118 |
| 8 | 178 |
| 9 | 237 |
| 10 | 294 |
| 11 | 357 |
| 12 | 412 |
| 13 | 464 |
| 14 | 536 |
| 15 | 590 |

PRODUCT MARKING



Markings in addition to model number designation may appear for internal quality control purposes.





MMIC SURFACE MOUNT

Monolithic Amplifier

MAR-1SM+

50Ω DC to 1 GHz

ADDITIONAL DETAILED TECHNICAL INFORMATION IS AVAILABLE ON OUR DASHBOARD. [CLICK HERE](#)

| | |
|--|--|
| Performance Data & Graphs | Data Table |
| | Swept Graphs |
| | S-Parameter Data Set (.zip file) |
| Case Style | WW107 Plastic micro-x package, 0.085 body diameter, Lead Finish: Matte-Tin |
| Tape & Reel Standard Quantities Available on Reel | F4 7" Reels with 20, 50, 100, 200, 500 or 1K devices |
| Suggested Layout for PCB Design | PL-253 |
| Evaluation Board | TB-411-1+ |
| Environmental Ratings | ENV08T3 |

ESD RATING

Human Body Model (HBM): Class 1B (500 V to < 1,000 V) in accordance with ANSI/ESD STM 5.1 - 2001


Machine Model (MM): Class M1 (< 100 V) in accordance with ESD STM 5.2 - 1999

MSL RATING

Moisture Sensitivity: MSL1 in accordance with IPC/JEDECJ-STD-020C

| No. | Test Required | Condition | Standard | Quantity |
|-----|---------------------------------|---|--------------------------------|----------|
| 1 | Visual Inspection | Low Power Microscope Magnification 40x | MIP-IN-0003 (MCT spec) | 45 units |
| 2 | Electrical Test | Room Temperature | SCD (MCL spec) | 45 units |
| 3 | SAM Analysis | Less than 10% growth in term of delamination | J-Std-020C (Jedec Standard) | 45 units |
| 4 | Moisture Sensitivity Level 1 | Bake at 125°C for 24 hours Soak at 85°C/85%RH for 168 hours Reflow 3 cycles at 260°C peak | J-Std-020C (Jedec Standard) | 45 units |

MSL TEST FLOW CHART



NOTES

- Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- Electrical specifications and performance data contained in this specification document are based on Mini-Circuits' applicable established test performance criteria and measurement instructions.
- The parts covered by this specification document are subject to Mini-Circuits' standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the standard terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/terms/viewterm.html



MMIC Amplifier

MAR-1SM+

Typical Performance Data

| FREQUENCY (MHz) | GAIN (dB) 17 mA | ISOLATION (dB) 17 mA | RETURN LOSS IN (dB) 17 mA | RETURN LOSS OUT (dB) 17 mA |
|--------------------|-----------------------|----------------------------|------------------------------------|-------------------------------------|
| 100 | 18.50 | 21.94 | 23.10 | 23.10 |
| 500 | 17.50 | 21.94 | 24.44 | 23.10 |
| 1000 | 15.50 | 20.00 | 24.44 | 20.92 |
| 1500 | 13.70 | 17.72 | 27.96 | 20.00 |
| 2000 | 12.30 | 15.92 | 24.44 | 15.92 |
| 2500 | 10.60 | 14.89 | 20.00 | 15.92 |
| 3000 | 9.30 | 13.98 | 18.42 | 16.48 |
| 3500 | 7.90 | 13.15 | 13.97 | 15.92 |
| 4000 | 6.60 | 12.04 | 11.06 | 15.39 |

REV. X1
MAR-1SM+
061031
Page 1 of 1







IF/RF MICROWAVE COMPONENTS • ISO 9001 ISO 14001 AS 9100 CERTIFIED RoHS compliant
P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661




The Design Engineers Search Engine finds the model you need, Instantly • For detailed performance specs & shopping online see




Typical Performance Curves



Outline Dimensions



PCB Land Pattern



Suggested Layout,
Tolerance to be within $\pm .002$

| CASE# | A | B | C | D | E | F | G | H | J | K | L | M | N | P | Q | WT. GRAMS |
|-------|----------------|---------------|----------------|----------------|----------------|----------------|----------------|----------------|----------------|----------------|----------------|----------------|----------------|----------------|----------------|--------------|
| WW107 | .012 (0.30) | .10 (2.54) | .020 (0.51) | .092 (2.34) | .085 (2.16) | .060 (1.52) | .007 (0.18) | .026 (0.66) | .235 (5.97) | .118 (3.00) | .235 (5.97) | .118 (3.00) | .072 (1.83) | .040 (1.02) | .020 (0.51) | .015 |

Dimensions are in inches (mm). Tolerances: 2 Pl. $\pm .03$; 3 Pl. $\pm .015$

Notes:

- Case material: Plastic.
- Termination finish:
For RoHS Case Styles: Matte tin Plate.
For RoHS-5 Case Styles: Tin-Lead plate.
- RF input termination (1) identified by one or both of the following at factory option:
 - diagonally cut termination, which may be 45° (ref) in either direction;
 - orientation mark on the case. Model dash number is identified by color dot or alphanumeric code on case. See specification data sheet.

Mini-Circuits®

INTERNET <http://www.minicircuits.cc>


P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500

Distribution Centers NORTH AMERICA 800-654-7949 • 417-335-5935 • Fax 417-335-5945 • EUROPE 44-1252-1

Mini-Circuits ISO 9001 & ISO 14001 Certified

Tape & Reel Packaging TR-F4

DEVICE ORIENTATION IN T&R



| Tape Width, mm | Device Cavity Pitch, mm | Reel Size, inches | Devices per Reel | |
|-------------------|----------------------------|----------------------|--|------|
| 12 | 8 | 7 | Small quantity standards (see note) | 20 |
| | | | | 50 |
| | | | | 100 |
| | | | | 200 |
| | | | | 500 |
| | | 7 | Standard | 1000 |

Note: Please Consult individual model data sheet to determine device per reel availability.

Mini-Circuits carrier tape materials provide protection from ESD (Electro-Static Discharge) during handling and transportation. Tapes are static dissipative and comply with industry standards EIA-481/EIA-541.

Go to: www.minicircuits.com/pages/pdfs/tape.pdf




INTERNET <http://www.minicircuits.com>

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661

Distribution Centers NORTH AMERICA 800-654-7949 • 417-335-5935 • Fax 417-335-5945 • EUROPE 44-1252-832600 • Fax 44-1252-837010

Mini-Circuits ISO 9001 & ISO 14001 Certified



| | | | | | |
|-----|---------|-------------|----------|----|------|
| REV | ECN No. | DESCRIPTION | DATE | DR | AUTH |
| OR | M108436 | NEW RELEASE | 11/14/06 | PW | IG |
| | | | | | |
| | | | | | |

.315
 .050
 .028 TYP
 PACKAGE OUTLINE
 12 X ϕ .020 PTH, FOR GROUND
 .097 TYP
 .055 TYP
 .020 TYP
 .140
 .047 TYP
 .020 TYP
 PIN 1
 .010 X 45° CHAMFER, 4 PL.
 .013 TYP
 .066 TRACE WIDTH, 2 PL. (SEE BELOW)

1. TRACE WIDTH IS SHOWN FOR ROGERS RO4350B WITH DIELECTRIC THICKNESS .030" \pm .002"; COPPER: 1/2 OZ. EACH SIDE. FOR OTHER MATERIALS TRACE WIDTH MAY NEED TO BE MODIFIED.
2. BOTTOM SIDE OF THE PCB IS CONTINUOUS GROUND PLANE.
3. IF PCB DESIGN RULES ALLOW, PLACE GROUND VIAS UNDER THE LAND PATTERN FOR BETTER RF PERFORMANCE. OTHERWISE PLACE GROUND VIAS AS CLOSE TO LAND PATTERN AS POSSIBLE.


DENOTES PCB COPPER LAYOUT WITH SMOBC (SOLDER MASK OVER BARE COPPER)
DENOTES COPPER LAND PATTERN FREE OF SOLDER MASK

| UNLESS OTHERWISE SPECIFIED | INITIALS | | DATE |
|----------------------------|----------|----|----------|
| DIMENSIONS ARE IN INCHES | DRAWN | PW | 11/11/06 |
| TOLERANCES ON: | CHECKED | IL | 11/14/06 |
| 2 PL DECIMALS ± | APPROVED | IG | 11/14/06 |
| 3 PL DECIMALS ± .005 | | | |
| ANGLES ± | | | |
| FRACTIONS ± | | | |

11

Mini-Circuits® 13 Neptune Avenue
Brooklyn NY 11235


PL, cb, WW107, MAR, TB-411-XX+

 Mini-Circuits®


THIS DOCUMENT AND ITS CONTENTS ARE THE PROPERTY OF MINI-CIRCUITS. EXCEPT FOR USE EXPRESSLY GRANTED, IN WRITING, TO ITS VENDORS, VENDEE AND THE UNITED STATES GOVERNMENT, MINI-CIRCUITS RESERVES ALL PROPRIETARY DESIGN, USE , MANUFACTURING AND REPRODUCTION RIGHTS THERETO. THESE CONTENTS SHALL NOT BE USED, DUPLICATED OR DISCLOSED TO ANY OUTSIDE PARTY, IN WHOLE OR IN PART, WITHOUT WRITTEN PERMISSION OF MINI-CIRCUITS.

| | | | | |
|---------------|---------------------|--------------------------|---------------|------------|
| SIZE A | CODE IDENT 15542 | DRAWING NO: 98-PL-253 | | REV: OR |
| FILE: 98PL253 | | SCALE: 8:1 | SHEET: 1 OF 1 | |

Evaluation Board and Circuit



TB-411-1+




| COMPONENT | VALUE |
|-------------|------------------------|
| A1 | MAR-1SM(+) |
| C1 (NOTE 4) | 2400 pF |
| C2 (NOTE 4) | 2400 pF |
| C3 (bypass) | 0.1 uF |
| R1 | 412 Ohms, 0.75W |
| R2 | 0 Ohm, 0.25W |
| CHK | Mini-Circuits TCCH-80+ |

Schematic Diagram

NOTE:

1. Vcc voltage: $+12 \pm 0.2V$.
2. SMA Female connectors.
3. PCB material: Rogers R04350 or equivalent, dielectric constant=3.5, dielectric thickness=.030 inch.
4. Capacitors, C1 & C2 should be free of resonance up to the highest frequency specified.

 **Mini-Circuits®**



All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

| Specification | Test/Inspection Condition | Reference/Spec |
|--------------------------------|--|---|
| Operating Temperature | -40° to 85°C Ambient Environment | Individual Model Data Sheet |
| Storage Temperature | -55° to 100° C Ambient Environment | Individual Model Data Sheet |
| Thermal Shock | -55° to 100°C, 100 cycles | MIL-STD-202, Method 107, Condition A-3, except +100°C |
| Mechanical Shock | 1.5Kg, 0.5 ms, 5 shock pulses, Y1 direction only | MIL-STD-883, Method 2002, Condition B, except Y1 direction only |
| Vibration (Variable Frequency) | 50g peak | MIL-STD-883, Method 2007, Condition B |
| Autoclave | 15 psig, 100% RH, 121°C, 96 hours | JESD22-A102, Condition C |
| HAST | 130°C, 85% RH, 96 hours | JESD22-A110 |
| Solderability | 10X Magnification | J-STD-002, Para 4.2.5, Test S, 95% Coverage |
| Solder Reflow Heat | Sn-Pb Eutetic Process: 240°C peak Pb-Free Process: 260°C peak | J-STD-020, Table 4-1, 4-2 and 5-2; Figure 5-1 |
| Moisture Sensitivity: Level 1 | Bake at 125°C for 24 hours Soak at 85°C/85% RH for 168 hours, Reflow 3 cycles at 260°C peak | J-STD-020 |
| Marking Resistance to Solvents | Isopropyl alcohol + mineral spirits at 25°C; terpene defluxer at 25°C; distilled water + proylene glycol monomethyl ether + | MIL-STD-202, Method 215 |



All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

| Specification | Test/Inspection Condition | Reference/Spec |
|---------------|----------------------------------|----------------|
| | monoethanolamine at 63°C to 70°C | |